

# Parallel Type Air Gripper

# MHZ Series

ø6, ø10, ø16, ø20, ø25, ø32, ø40




# Integral linear guide used for high rigidity



Martensitic stainless steel ---i-.


## High degree of mounting flexibility


Can be mounted five ways from three directions.



## Body option/Piping port location

#### Finger positions can be selected. (Standard type/MHZ2)





**SMC** 


# and high precision

Integral

construction

guide rail

- Body thickness tolerance: +0.05 mm
- No guide protrusion in direction of body thickness
- Improved remounting accuracy Positioning dowel pin holes provided
- Top mounting centering location Mounting is more secure with a depth 0.5 to 2 mm greater than current types.



## With Dust Cover Page 440 MHZJ2 Series

Prevents entry of chips, dust, water, etc. Prevents dispersion of grease and external leakage of dust.

#### **Cover materials**


- · Chloroprene rubber (Black)
- · Fluororubber (Black)

Series

· Silicone rubber (White)

#### Made to Order

- Dust cover adhesion (Powerful adhesive used): -X77
- Dust cover caulking (Silicone caulking agent used): -X78







-X

MRHO

MA

D-

ø6


# Parallel Type Air Gripper *MHZ2* Series Series Variations

			Body option End boss type						
			Basic type Side ported	Side ported	With One-touch	With One-touch	With	With	
			ponou	2.22 portod	With One-touch fitting for coaxial tubing	With One-touch fitting	M3 port	M5 port	
	Bore								
Series	size (mm)	Action		o		o	0     0	o     o	
Standard MHZA2-6 Page 398	6	Double acting Single acting (Normally open) Single acting (Normally closed)	•	•		•	•		
With dust cover MHZAJ2-6 Page 398	6	Double acting Single acting (Normally open) Single acting (Normally closed)	•	•		•	•		
	6	Double acting Single acting (Normally open) Single acting (Normally closed)	• • •						
Standard MHZ2 Page 408	10, 16 20, 25	Double acting Single acting (Normally open) Single acting (Normally closed)	•	•	•	•		•	
ALCON	32, 40	Double acting Single acting (Normally open) Single acting (Normally closed)	• • •						
Long stroke MHZL2 Page 426	10, 16 20, 25	Double acting Single acting (Normally open) Single acting (Normally closed)	• • •	• • •	•	•		•	
Long stroke With dust cover MHZL2 Page 436	10, 16 20	Double acting	•						
		Double acting Single acting	•						
With dust cover	6	(Normally open) Single acting (Normally closed)	•						
MHZJ2 Page 440		Double acting	•	•	•				
Page 451	10, 16 20, 25	Single acting (Normally open)	•	•		•		•	
		Single acting (Normally closed)	•	•		•		•	
	32, 40	Double acting	•						


	- Finger option						
With hose nipple	Basic type (tapped in open/close direction)	Side tapped	Through-holes in open/close direction	Flat type finger			
					Made to Order common specifications	Page	
	•	•	•	•			
•	•	•	•	•			
•	•	•	•	•			
	•					Page 398	
•	•						
•	•				* Availability varies depending on the model.		
					For details, refer to "Made to Order" on pages 725 to 748.		
	•	•	•	•	<b>M</b>		84117
	•	•	•	•	-X4 Heat resistance (-10 to 100 °C) -X5 Fluororubber seal		MHZ
			•	•	-X7 Closing direction spring assist     -X12 Opening direction spring assist		MHF
	•	•	•	•	-X46 Built-in needle valve for finger speed control		MHL
	•	•	•	•	-X50 Without magnet -X51 MHQ2/MHQG2 compatible flat type fingers	Page 408	MHR
	<u> </u>	•	•	•	-X53 Ethylene propylene rubber seal (EPDM)		МНК
	•	•	•	•	-X56 Axial ported -X63 Fluorine grease		
	•	•	•	•	-X64 Finger: Side tapped -X65 Finger: Through-holes in opening/closing		MHS
		•	•	•	-X65 Finger: Through-holes in opening/closing directions		MHC
	•	•	•	•	-X77A Dust cover adhesion -X77B Dust cover adhesion/Finger part only		MHT
	•	•	•	•	-X78A Dust cover caulking	Page 426	MHY
	<u> </u>	•	•	•	-X78B Dust cover caulking/Finger part only -X79 Grease for food processing machines/Fluorine		МНЖ
					grease		
	•				-X79A Grease for food processing machines/ Aluminum complex soap base grease	Page 436	-X□
	<u> </u>				-X81A Special black chromium treatment is made on only the finger.		MRHQ
	•				-X81B Special black chromium treatment is made on		MA
	•				the finger and guide.		D-🗆
	<u> </u>					Page 440	
	•					-	
	•						
	<u> </u>						
	•					Page 451	

# MHZ Series **Model Selection**

## Model Selection



Model Selection Illustration




When gripping a workpiece as in the figure to the left, and with the following definitions,

attachments and the workpiece

g: Gravitational acceleration (= 9.8 m/s<sup>2</sup>)

the conditions under which the workpiece will

With "a" representing the extra margin, "F" is determined by the following formula:



**SMC** 


# MHZ Series

## **Model Selection**


## Step 1 Effective Gripping Force: MHZD2 Series/Double Acting/Internal Gripping Force —


Internal Gripping Force








Internal Grip













@SMC



388




# MHZ Series


## **Model Selection**


## Step 1 Effective Gripping Force: MHZD2 Series/Single Acting/Internal Gripping Force


 Indication of effective gripping force
 The effective gripping force shown in the graphs to the right is expressed as F, which is the thrust of one finger, when both fingers and attachments are in full contact with the workpiece as shown in the figure below.




Internal Grip









0.6 MPa

0.5 MPa

Gripping point L (mm)

@SMC

0.4 MPa

0.3 MPa

0.2 MPa

50 Î

30

20

10 0 20 40 60 80

Gripping force 40

MHF
MHL
MHR
МНК
MHS
MHC
MHT
MHY
MHW
-X□
MRHQ
MA
D-🗆

391

.....

# MHZ Series

## **Model Selection**


## Step 1 Effective Gripping Force: MHZ 2 Series/Double Acting/Internal Gripping Force —


Internal Gripping Force


Internal Gripping Force


















#### **External Gripping Force External Gripping Force** · Indication of effective gripping force MHZJ2-6S/MHZAJ2-6S MHZJ2-25S The effective gripping force shown in the graphs to the right is expressed as F, which is the thrust of one finger, when both fingers and attach-80 ments are in full contact with the workpiece as Pressure 0.7 MPa shown in the figure below. ŝ ŝ 60 3 Gripping force Gripping force 0.6 MPa 0.5 MPa 4 2 40 0.4 MPa 20 0.3 MPa 0 20 30 0 20 40 60 Gripping point L (mm) **External Grip** MHZJ2-10S MHZAJ2, MHZJ2 12 Pressure 0.7 MPa 10 ¢ 0.6 MPa ŝ ۶ Gripping force 0.5 MPa ÷ 6 .....

Step 1 Effective Gripping Force: MHZD2 Series/Single Acting/External Gripping Force -

Pressure 0.7 MPa 0.6 MPa 0.5 MPa 0.4 MPa 0.3 MPa 0.25 MPa 80 100 Gripping point L (mm)

MHZ
MHF
MHL
MHR
MHK
MHS
MHC
MHT
MHY
MHW
-X□
MRHQ
MA
D-🗆
-



# MHZ Series


## **Model Selection**

## Step1 Effective Gripping Force: MHZD2 Series/Single Acting/Internal Gripping Force


Internal Gripping Force


Internal Gripping Force







Internal Grip

















@SMC


395

# MHZ Series


## **Model Selection**


## Step 2 Confirmation of Gripping Point: MHZ

#### Internal Grip




- The air gripper should be operated so that the workpiece gripping point "L" and the amount of overhang "H" stay within the range shown for each operating pressure given in the graphs to the right.
- If the workpiece gripping point goes beyond the range limits, this will have an adverse effect on the life of the air gripper.









L: Distance to the point at which the load is applied (mm)

	Maximum allowable moment				
Allowable vertical load Fv (N)	Pitch moment: Mp (N·m)	Yaw moment: <b>My</b> (N·m)	Roll moment: <b>Mr</b> (N·m)		
10	0.04	0.04	0.08		
58	0.26	0.26	0.53		
98	0.68	0.68	1.36		
147	1.32	1.32	2.65		
255	1.94	1.94	3.88		
343	3	3	6		
490	4.5	4.5	9		
	10 58 98 147 255 343	Allowable vertical load         Pitch moment: Mp (N-m)           10         0.04           58         0.26           98         0.68           147         1.32           255         1.94           343         3	Allowable vertical load Fv (N)         Pitch moment: Mp (N-m)         Yaw moment: My (N-m)           10         0.04         0.04           58         0.26         0.26           98         0.68         0.68           147         1.32         1.32           255         1.94         1.94           343         3         3		

Note) Values for load and moment in the table indicate static values.

Calculation of allowable external force (when moment load is applied)	Calculation example
Allowable load F (N) = $\frac{(\text{maximum allowable moment})(\text{N-m})}{\text{L x } 10^{-3}}$ (*: Constant for unit conversion)	When a static load of f = 10 N is operating, which applies pitch moment to point L = 30 mm from the MHZII2-16D guide. Therefore, it can be used. Allowable load F = $\frac{0.68}{30 \times 10^{-3}}$ = 22.7 (N) Load f = 10 (N) < 22.7 (N)

MHZ
MHF
MHL
MHR
MHK
MHS
MHC
MHT
MHY
MHW
-X□
MRHQ
MA
<b>D-</b> □

# Parallel Type Air Gripper (Standard) Compact Series (Without Auto Switch) MHZA2-6/MHZAJ2-6 Series

How to Order MHZA 6 2 MHZAJ 2 6 Made to Order Refer to page 399 for details. With dust cover Dust cover type Nil Chloroprene rubber (CR) Number of fingers Fluororubber (FKM) F 2 2 fingers S Silicone rubber (Si) Bore size Body option 6 6 mm Nil: Basic type E: End boss type K: End boss type Port Side ported Axial ported Action (Double acting/Single acting) with ø4 One-touch fitting D Double acting (Single acting) S Single acting (Normally open) Port C Single acting (Normally closed) Port Finger option [Standard] Nil: Basic type Port Port H: End boss type M: End boss type 1: Side tapped mounting Axial ported Axial ported with ø4 hose nipple with M3 port (Single acting) (Single acting) Ø 2: Through-holes in opening/closing direction 3: Flat type fingers

epoolineatione						
	Flu	id	Air			
•	Double acting		0.15 to 0.7 MPa			
Operating pressure	Single	Normally open	0.3 to 0.7 MPa			
	acting	Normally closed	0.3 to 0.7 MFa			
Ambient ar	nd fluid ter	nperature	-10 to 60°C			
Repeatabil	ity		±0.01 mm			
Max. opera	ting frequ	ency	180 c.p.m.			
Lubrication			Not required			
Action			Double acting/Single acting			

\* Use the gripper with dust cover when used in a place where there may be dust.

#### Model

			-	Gripping f	Opening/		
				Bore Gripping force per finger		Closing	Weight
Actio	n	Model	size (mm)	Effective	(Both sides)	(g)	
				External	Internal	(mm)	
Double		MHZA2-6D	6	3.3	6.1	4	26
acting	3	MHZAJ2-6D	6	0.0	0.1	4	27
	Normally open	MHZA2-6S	6	1.9		4	26
Single	Norn	MHZAJ2-6S	6	1.5	_	4	27
acting	valy	MHZA2-6C	6	_	3.7	4	26
Morm	Normally closed	MHZAJ2-6C	6			4	27

Note) Values based on pressure of 0.5 MPa, gripping point L = 20 mm, at center of stroke.

#### Option

#### Body Option/End Boss Type

**SMC** 

Body Option/End Boss Type					
Symbol	Piping port location	Type of piping port	Applicat	Applicable model	
Symbol	Piping port location	MHZA2-6/MHZAJ2-6	Double acting	Single acting	MHR
Nil	Basic type	M3 x 0.5	•		
E	Side ported	M3 x 0.5	•		MHK
к		With ø4 One-touch fitting	_		
н	Axial ported	With ø4 hose nipple	-		MHS
М		M3 x 0.5	—		

## Symbol

Double acting: Internal grip



Double acting: External grip



Single acting/ Normally closed: Internal grip



Single acting/ Normally open: External grip



#### Made to Order Click here for details

Symbol	Specifications/Description
-X4	Heat resistance (100°C)
-X5	Fluororubber seal
-X12	Opening direction spring assist
-X53	EPDM seal/Fluorine grease
-X56	Axial ported type
-X63	Fluorine grease
-X64	Finger: Side tapped mounting
-X65	Finger: Through-hole mounting
-X79	Grease for food processing machines, Fluorine grease
-X79A	Grease for food processing machines
-X81A	Anti-corrosive treatment of finger
-X81B	Anti-corrosive treatment of finger and guide



When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the IDK series in the Best Pneumatics No. 6

## Specifications



D-🗆


MHZ

MHF


# MHZA2-6/MHZAJ2-6 Series

## Construction: Standard Type MHZA2-6

## Double acting/With fingers open



## Double acting/With fingers closed



#### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	Stainless steel	
3	Lever	Stainless steel	Heat treated
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitriding
8	Holder	Brass	Electroless nickel plated
9	Holder lock	Stainless steel	
10	Сар	Aluminum alloy	Clear anodized
11	Bumper	Urethane rubber	
12	Steel balls	High carbon chrome bearing steel	
13	Needle roller	High carbon chrome bearing steel	
		° °	

### **Component Parts**

No.	Description	Material	Note
14	Type C retaining ring	Carbon steel	Phosphate coated
15	Exhaust plug	Brass	Electroless nickel plated
16	Exhaust filter	Polyvinyl formal	
17	N.O. spring	Stainless steel spring wire	
18	N.C. spring	Stainless steel spring wire	
19	N.C. holder	Brass	Electroless nickel plated
20	N.C. spacer	Stainless steel	
21	Rod seal	NBR	
22	Piston seal	NBR	
23	Gasket	NBR	
24	Gasket	NBR	

## **Replacement Parts**


Desci	ription	MHZA2-6	Main parts					
Finger assembly		Please contact SMC to replace the seal kit and finger assembly.						
	MHZA2-6□□H	MHZA-A0607						
End boss assembly	MHZA2-6□□K	MHZA-A0608	Main body of adaptor Mounting screw for adaptor					
Life boss assembly	MHZA2-6□□M	MHZA-A0609	Seal					
	MHZA2-6□□E	MHZA-A0610						

\* The end boss assembly other than type E should be mounted on the special body.


Replacement part/Grease pack part no.: GR-S-010 (10 g)

#### A 400

## Single acting/Normally open




## Single acting/Normally closed




## **Construction: With Dust Cover MHZAJ2-6**


### Double acting/With fingers open




### Double acting/With fingers closed



#### Single acting/Normally open



#### Single acting/Normally closed



MHZ

#### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	Stainless steel	
3	Lever	Stainless steel	Heat treated
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitriding
8	Holder	Brass	Electroless nickel plated
9	Holder lock	Stainless steel	
10	Сар	Aluminum alloy	Clear anodized
11	Bumper	Urethane rubber	
12	Steel balls	High carbon chrome bearing steel	
13	Needle roller	High carbon chrome bearing steel	

#### **Component Parts**

No.	Description	Material	Note
		CR	Chloroprene rubber
14	Dust cover	FKM	Fluororubber
		Silicone rubber	
15	Type C retaining ring	Carbon steel	Phosphate coated
16	Exhaust plug	Brass	Electroless nickel plated
17	Exhaust filter	Polyvinyl formal	
18	N.O. spring	Stainless steel spring wire	
19	N.C. spring	Stainless steel spring wire	
20	N.C. holder	Brass	Electroless nickel plated
21	N.C. spacer	Stainless steel	
22	Rod seal	NBR	
23	Piston seal	NBR	
24	Gasket	NBR	
25	Gasket	NBR	

#### **Replacement Parts**

Desc	riptio	n	MHZAJ2-6	Main parts				
Seal kit			Please contact SMC to re	eplace the seal kit.				
	rial	CR	MHZAJ2-J6					
Dust cover	Mater	FKM	MHZAJ2-J6F	14				
	Ξ	Silicone rubber	MHZAJ2-J6S					
Finger assembly			Please contact SMC to re	eplace the finger assembly.				
	1	MHZA2-6□□H	MHZA-A0607					
End boss assembly	1	MHZA2-6□□K	MHZA-A0608	Main body of adaptor				
Life boss assembly	I	//HZA2-6□□M	MHZA-A0609	Mounting screw for adaptor Seal				
		MHZA2-6□□E	MHZA-A0610					

\* End boss type

H = With hose nipple, K = With One-touch fitting, M = With M3 port, E = Side ported

\* The end boss assembly other than type E should be mounted on the special body.


Replacement part/Grease pack part no.: GR-S-010 (10 g)




# MHZA2-6/MHZAJ2-6 Series

## **Dimensions: Standard Type**

# MHZA2-6 Double acting/Single acting Basic type







\* For single action, the port on one side is a breathing hole.

## Parallel Type Air Gripper/Compact Series MHZA2-6/MHZAJ2-6 Series

## **Dimensions: With Dust Cover**





\* For single action, the port on one side is a breathing hole.



MHZ

MHF

MHL

MHR MHK

MHS

MHC

MHT


MHY MHW

-X🗆 MRHQ

MA D-🗆

# MHZA2-6 Series **Finger Option**


## Side Tapped Mounting [1]



\* Specifications and dimensions other than the above are the same as the basic type.


## Through-holes in Opening/Closing Direction [2]

cap bolt as its top diameter is large.



\* Specifications and dimensions other than the above are the same as the basic type.

## Flat Type Fingers [3]



**SMC** 

\* Specifications and dimensions other than the above are the same as the basic type.


# MHZA2-6/MHZAJ2-6 Series Body Option: End Boss Type

## Applicable Model

Symbol	Dising part leastion	Type of p	Applicable model			
Symbol	Piping port location	MHZA2	MHZAJ2	Double acting	Single acting	
E	Side ported	M3 >	•	•		
н		With ø4 h	ose nipple	_	•	
к	Axial ported	With ø4 One	_	•		
М	•	M3 >	—	•		

## Side Ported [E]


#### MHZA2-6 CE




\* Specifications and dimensions other than the above are the same as the basic type.

## Axial Ported (with hose nipple) [H]

## MHZA2-6°C□H




\* Specifications and dimensions other than the above are the same as the basic type.



 Specifications and dimensions other than the above are the same as the basic type or the end boss dimensions of the MHZA type.

## MHZAJ2-6°SH□

MHZAJ2-6



 Specifications and dimensions other than the above are the same as the basic type or the end boss dimensions of the MHZA type.

## Applicable Tubing

Description/	Nylon tubing	Soft nylon tubing	Polyurethane tubing	Polyurethane coil tubing	
Specifications Model	T0425	TS0425	TU0425	TCU0425B-1	
Outside diameter (mm)	4	4	4	4	
Max. operating pressure (MPa)	1.0	0.8	0.5	0.5	
Min. bending radius (mm)	13	12	10	-	
Operating temperature (°C)	-20 to 60	-20 to 60	-20 to 60	-20 to 60	
Material	Nylon 12	Nylon 12	Polyurethane	Polyurethane	

Refer to "Pneumatic Piping Equipment (CAT. E50)" regarding One-touch fittings and tubing.



MHZ

MHF

MHR

МНК

MHS

MHC

МНТ

MHY

MHW

-X□

MRHQ Ma


D-🗆

# MHZA2-6/MHZAJ2-6 Series

## Axial Ported (with One-touch fitting) [K]

## MHZA2-6 cS□K

### MHZAJ2-6<sup>s</sup><sub>c</sub>K



\* Specifications and dimensions other than the above are the same as the basic type.

\* Specifications and dimensions other than the above are the same as the basic type or the end boss dimensions of the MHZA type.


#### Applicable Tubing

Description/	Nylon tubing	Soft nylon tubing	Polyurethane tubing	Polyurethane coil tubing	
Specifications	T0425	TS0425	TU0425	TCU0425B-1	
Outside diameter (mm)	4	4	4	4	
Max. operating pressure (MPa)	1.0	0.8	0.5	0.5	
Min. bending radius (mm)	13	12	10	_	
Operating temperature (°C)	-20 to 60	-20 to 60	-20 to 60	-20 to 60	
Material	Nylon 12	Nylon 12	Polyurethane	Polyurethane	

Refer to "Pneumatic Piping Equipment (CAT. E50)" regarding One-touch fittings and tubing.

## Axial Ported (with M3 port) [M]

#### MHZA2-6<sup>s</sup>⊡M



\* Specifications and dimensions other than the above are the same as the basic type.

# 

MHZAJ2-6<sup>s</sup><sub>c</sub> M□

\* Specifications and dimensions other than the above are the same as the basic type or the end boss dimensions of the MHZA type.


## Weight

				(g)
Model		End boss ty	pe (Symbol)	
woder	E	н	к	М
MHZA2-6	28	28	28	28
MHZAJ2-6	29	29	29	29



MHZ
MHF
MHL
MHR
MHK
MHS
MHC
MHT
MHY
MHW
-X□
MRHQ
MA
D-🗆

# Parallel Type Air Gripper/Standard Type **MHZ2** Series ø6, ø10, ø16, ø20, ø25, ø32, ø40



Applicable Auto Switches/Refer to pages 797 to 850 for further information on the auto switch.

	Original	Els states el	Indicator	Marine an	Load voltage			Auto swit	ch model	Lead	d wire l	ength	(m) *						
Туре	Special function	entry	light	Wiring (Output)		Joad Volta	ye	Electrical en	0.5	1	3	5	Pre-wired connector	Applicable load					
		,		(Output)		DC	AC	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)		10	au			
				3-wire (NPN)				M9NV	M9N	٠	•	•	0	0					
						5 V. 12 V		F8N	—	٠	-	•	0	-	IC				
				3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit				
o switch		Grommet		3-wire (PNP)				F8P	—	٠	—	•	0	-					
				2-wire		12 V		M9BV	M9B	٠	•	•	0	0					
auto			Yes		24 V 5 V 12			12 V	F8B	_	•	-	•	0	-	_	Relay,		
state	Diagnosis		res	3-wire (NPN)						M9NWV	M9NW	٠	٠	•	0	0	IC	PLC	
st	(2-color			3-wire (PNP)		)	5 V, 12 V	5 V, 12 V	5 V, 12 V		M9PWV	M9PW	•	•	•	0	0	circuit	
Solid	indicator)			2-wire		12 V		M9BWV	M9BW	•	•	•	0	0	—				
0	Water resistant			3-wire (NPN)		5 V 40 V		M9NAV**	M9NA**	0	0	•	0	0	IC				
	(2-color			3-wire (PNP)	5	5 V, 12 V		M9PAV**	M9PA**	0	0	٠	0	0	circuit				
	indicator)			2-wire		12 V	12 V		M9BA**	0	0	•	0	0	-				

\*\* Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. \* Lead wire length symbols: 0.5 m ..... Nil (Example) M9NW

\* Solid state auto switches marked with O are produced upon receipt of order.

1 m ..... M (Example) M9NWM

3 m ..... L (Example) M9NWL

5 m ...... Z (Example) M9NWZ


Note 1) When using a D-F8D switch, mount it at a distance of 10 mm or more from magnetic substances such as iron, etc.

Note 2) When using the 2-color indicator type, please make the setting so that the indicator is lit in red to ensure the detection at the proper position of the air gripper.



## Parallel Type Air Gripper/Standard Type **MHZ2** Series

How to Order



	Special Electrical Indicator Wiring				oad voltad	10	Auto swit	ch model	Lead wire length (m) *				Applicable model				Dra wirad	Applicable		
Туре	function	Electrical entry	Indicator light	Wiring (Output)	Load voltage		Je	Electrical entry direction		0.5	0.5 1		5	~10	~10	ø20	~05	Pre-wired connector	load	
		Chuy	iigin	(Output)		DC	DC AC		In-line	(Nil)	(M)	(L)	.) (Z)	010	010	020	025			
								M9NV	M9N	٠	٠	٠	0	•	٠	٠	•	0		i 🗌
				3-wire (NPN)		5 V. 12 V		F8N	—	٠	—	٠	0	—	•	•	٠	-	IC	
				Quuine (DND)		5 V, 12 V		M9PV	M9P	٠	٠	٠	0	•	•	•	•	0	circuit	i l
switch				3-wire (PNP)				F8P	_	٠	—	٠	0	-	٠	٠	•	-		
				0		12 V	,	M9BV	M9B	٠	٠	٠	0	•	•	٠	٠	0		
auto		Grommet	Yes	2-wire	24 V			F8B	_	٠		٠	0	-	•	•	•	-	_	Relay,
state	Diagnosis	Circininet	ies	3-wire (NPN)		5 V. 12 V	-	M9NWV	M9NW	٠	٠	٠	0	•	٠	٠	•	0	IC	PLC
Iste	(2-color			3-wire (PNP)		5 V, 12 V		M9PWV	M9PW	٠	٠	٠	0	•	•	٠	٠	0	circuit	
Solid	indicator)			2-wire		12 V		M9BWV	M9BW	٠	٠	٠	0	•	•	•	٠	0	_	l li
l o	Water resistant			3-wire (NPN)		5 V, 12 V		M9NAV**	M9NA**	0	0	٠	0	•	•	•	•	0	IC	
	(2-color			3-wire (PNP)			5 V, 12 V	M9PAV**	M9PA**	0	0	٠	0	•	٠	•	•	0	circuit	
	indicator)			2-wire		12 V		M9BAV**	M9BA**	0	0	٠	0	•	•	٠	•	0	—	

\*\* Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot quarantee water resistance \* Solid state auto switches marked with

- \* Lead wire length symbols: 0.5 m ..... Nil (Example) M9NW 1 m ..... M (Example) M9NWM
  - 3 m······ L (Example) M9NWL

O are produced upon receipt of order.

- 5 m ..... Z (Example) M9NWZ
- Note 1) When using the 2-color indicator type, please make the setting so that the indicator is lit in red to ensure the detection at the proper position of the air gripper.
- Note 2) Through-hole mounting is not possible when using the auto switch at the square groove on the side. Note 3) When the product is ordered with auto switch, only MHZ2-10 is shipped with the auto switch mounting brackets. When the auto switch is used at the square groove on the side with MHZ2-16 to 25, mounting brackets (BMG2-012) are required. Pease order them separately. Refer to page 457 for the auto switch mounting brackets.


#### Moisture Control Tube **IDK Series**

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the IDK series in the Best Pneumatics No. 6.

MHT MHY MHW -X□ MRHO MA D-

## MHZ2 Series



#### Applicable Auto Switches/Refer to pages 797 to 850 for further information on the auto switch

							_	Auto swite	ch model	Lead	wire l	ength	(m) *				
Туре	Special function	Electrical entry	Indicator light	r Wiring (Output)	Load voltage		Electrical en	try direction	0.5	1	3	5	Pre-wired connector		Applicable		
	Turiotion	entry	iigin	(Output)	1	DC	AC	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	CONNECTOR	10	load	
switch				3-wire (NPN)			M9NV	M9N	•	•	٠	0	0				
	_							F8N	_	•	-	٠	0	-	IIC		
				3-wire (PNP)	5 V, 12 V		M9PV	M9P	•	•	٠	0	0	circuit			
				S-WIE (PINP)			F8P	_	•	-	٠	0	-				
				2-wire		24 V		M9BV	M9B	•	•	٠	0	0			
auto		0	N/	2-wire			F8B	_	•	-	٠	0	_		Relay,		
state	Diagnosis	Grommet	Yes	3-wire (NPN)			EV 10V	5 V. 12 V	EV 10V	M9NWV	M9NW	•	٠	٠	0	0	IC
l sta	(2-color			3-wire (PNP)		5 V, 12 V		M9PWV	M9PW	•	٠	٠	0	0	circuit		
Solid	indicator)			2-wire		12 V		M9BWV	M9BW	•	•	٠	0	0		1	
0	Water resistant			3-wire (NPN)		5 V, 12 V		M9NAV**	M9NA**	0	0	٠	0	0	IC	1	
(2-color	(2-color			3-wire (PNP)				M9PAV**	M9PA**	0	0	٠	0	0	circuit		
	indicator)			2-wire		12 V		M9BAV**	M9BA**	0	0	•	0	0	_	1	

\*\* Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. \* Solid state auto switches marked with O are produced upon receipt of order.

\* Lead wire length symbols: 0.5 m ..... Nil (Example) M9NW 1 m----- M (Example) M9NWM


- 3 m······ L (Example) M9NWL 5 m······ Z (Example) M9NWZ

Note 1) When using the 2-color indicator type, please make the setting so that the indicator is lit in red to ensure the detection at the proper position of the air gripper.

Note 2) Through-hole mounting is not possible when using the auto soluting solution in the too change and be determined and the proper possible when using the auto solution at the proper possible when the solution of the side. Note 3) When the auto switch is used at the square groove on the side with MHZ2-32 and 40, mounting brackets (BMG2-012) are required. Please order them separately. Refer to page 457 for the auto switch mounting brackets.

@SMC

## Parallel Type Air Gripper/Standard Type **MHZ2** Series



-X50

-X53

-X56

-X63

-X79

-X81A

Without magnet

Axial ported type

Fluorine grease

EPDM seal/Fluorine grease

-X79A Grease for food processing machines

Anti-corrosive treatment of finger -X81B Anti-corrosive treatment of finger and guide

Grease for food processing machines, Fluorine grease

## Specifications

	Fluid		Air		
			ø6: 0.15 to 0.7 MPa		
	Dou	ble acting	ø10: 0.2 to 0.7 MPa		
Operating			ø16 to ø40: 0.1 to 0.7 MPa		
pressure	Single acting	Normally open	ø6: 0.3 to 0.7 MPa		
			ø10: 0.35 to 0.7 MPa		
		Normally closed	ø16 to ø40: 0.25 to 0.7 MPa		
Ambient a	Ambient and fluid temperature		-10 to 60°C		
Repeatabi	lity		ø6 to ø25: ±0.01 mm		
переатар	iity		ø32, ø40: ±0.02 mm		
Max. oper	atina fra		ø6 to ø25: 180 c.p.m.		
max. oper	aung ne	quency	ø32, ø40: 60 c.p.m.		
Lubricatio	n		Not required		
Action			Double acting/Single acting		
Auto switch (Option) Note)			Solid state auto switch (3-wire, 2-wire)		

Note) Refer to pages 797 to 850 for further information on auto switches.

\* Use the gripper with dust cover when used in a place where there may be dust.

#### Model

Action			Bore	Gripping	force Note 1)	Opening/	Note 2)	
		Model	Model size		ce per finger value (N)	Closing stroke (Both sides)	Weight (g)	
			(mm)	External	Internal	(mm)		
		MHZ2-6D	6	3.3	6.1	4	27	
		MHZ2-10D(N)	10	11	17	4	55	
Doubl	~	MHZ2-16D(N)	16	34	45	6	115	
	-	MHZ2-20D(N)	20	42	66	10	230	
actin	y	MHZ2-25D(N)	25	65	104	14	420	
		MHZ2-32D	32	158	193	22	715	
		MHZ2-40D	40	254	318	30	1275	
		MHZ2-6S	6	1.9		4	27	
	Normally open	MHZ2-10S(N)	10	7.1		4	55	
		MHZ2-16S(N)	16	27		6	115	
		MHZ2-20S(N)	20	33	_	10	235	
	L L	MHZ2-25S(N)	25	45		14	425	
	ž	MHZ2-32S	32	131		22	760	
Single		MHZ2-40S	40	217		30	1370	
acting		MHZ2-6C	6		3.7	4	27	
	closed	MHZ2-10C(N)	10		13	4	55	
	cjo Cjo	MHZ2-16C(N)	16		38	6	115	
	È	MHZ2-20C(N)	20	_	57	10	235	
	Vormally	MHZ2-25C(N)	25		83	14	425	
:	Ñ	MHZ2-32C	32		161	22	760	
		MHZ2-40C	40		267	30	1370	

Note 2) Values excluding weight of auto switch.

## Option

#### Body Option/End Boss Type


-										
Symbol	Piping port		Type of piping port							ole model
Symbol	location	MHZ2-6	MHZ2-10	MHZ2-16	MHZ2-20	MHZ2-25	MHZ2-32	MHZ2-40	Double acting	Single acting
Nil	Basic type	M3 :	M3 x 0.5 M5 x 0.8		3		•			
E	Side ported	_	M3 x 0.5	I	M5 x 0.8	В	-	_		
w	Axial ported	_	With ø4 C	)ne-touch fi	tting for coa	axial tubing	-	_	•	—
к	Axial ported	—	With ø4 One-touch fitting			-	-	—		
М	Axial ported	—	M5 x 0.8			-	-	—		

\* For detailed body option specifications, refer to option specifications on pages 424 and 425.

	CI	
Ľ	J	VIC.

# MHZ2 Series

## **Clean Series: Air Gripper**



Applicable Auto Switches/Refer to pages 797 to 850 for further information on the auto switch.

	<b>a</b>							Auto swite	ch model	Lead	wire I	ength	(m) *								
Туре	Special function	Electrical entrv	light		Load voltage DC AC		Electrical entry direction		0.5	1	3	5	Pre-wired connector	Applicable load							
	Iuncion	entry		(Output)			Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	Connector	10	au						
					<u> </u>			M9NV	M9N	•	٠	٠	0	0							
				3-WILE (INFIN)		5 V, 12 V		F8N	_	•	—	•	0	-	IC						
÷				Quuine (DND)				M9PV	M9P	•	•	•	0	0	circuit						
switch	—			3-wire (PNP)				F8P	—	•	—	•	0	-							
				2-wiro		12 V		M9BV	M9B	•	٠	•	0	0							
auto		Grommet	Yes	-		24.V	24.V		_	F8B	_	•	—	•	0	_		Relay,			
state	Diagnosis	Citominet	163	3-wire (NPN)						EV 10 V	5 V 12 V		M9NWV	M9NW	•	٠	•	0	0	IC	PLC
	(2-color			3-wire (PNP)							J V, 12 V		M9PWV	M9PW	•	٠	•	0	0	circuit	
Solid	indicator)			2-wire		12 V		M9BWV	M9BW	•	•	•	0	0	_						
о С	Water resistant			3-wire (NPN)		5 V. 12 V		M9NAV**	M9NA**	0	0	•	0	0	IC						
	(2-color			3-wire (PNP)		5 0, 12 0	J V, 12 V		M9PAV**	M9PA**	0	0	٠	0	0	circuit					
	indicator)			2-wire		12 V		M9BAV**	M9BA**	0	0	•	0	0	—						

\*\* Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance.

\* Lead wire length symbols: 0.5 m ..... Nil (Example) M9NW

\* Solid state auto switches marked with O are produced upon receipt of order.

1 m ..... M (Example) M9NWM

3 m ..... L (Example) M9NWL

5 m······ Z (Example) M9NWZ

Note 1) When using the 2-color indicator type, please make the setting so that the indicator is lit in red to ensure the detection at the proper position of the air gripper. Note 2) When using a D-FB<sup>-</sup> switch, mount it at a distance of 10 mm or more from magnetic substances such as iron, etc.


@SMC

Note 3) For 11-MHZ2-10DD, the through-hole mounting cannot be made when using the auto switch. Note 4) Two extension fitting assemblies (P3311176A) are supplied with 11-MHZ2-10DD. Please use them if the fitting interferes with the auto switch.

## Specifications

Fluid	Air					
Operating pressure	ø10: 0.2 to 0.7 MPa ø16 to ø25: 0.1 to 0.7 MPa					
Ambient and fluid temperature	-10 to 60°C					
Repeatability	±0.01 mm					
Max. operating frequency	180 c.p.m.					
Lubrication	Not required					
Action	Double acting					
Cleanliness class (ISO class)	Class 4					
Auto switch (Option)	Solid state auto switch (3-wire, 2-wire)					






#### Vacuum port


The concentrated vacuuming of internally generated particulates prevents them from spreading into the clean room.

For details, refer to "Pneumatic Clean Series (CAT. E02-23)" catalog.


## Construction: MHZ2-6

## Double acting/With fingers open





#### Double acting/With fingers closed



### **Component Parts**


	<u> </u>		
No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	Stainless steel	
3	Lever	Stainless steel	Heat treated
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitriding
8	Magnet holder	Stainless steel	
9	Holder	Brass	Electroless nicked plated
10	Holder lock	Stainless steel	
11	Сар	Aluminum alloy	Clear anodized
12	Bumper	Urethane rubber	
13	Magnet	-	Nickel plated

## **Replacement Parts**


Desc	ription	MHZ2-6	Main parts			
Finger assembly		Please contact SMC to replace the seal kit and finger assembly.				
	MHZ2-6D	MHZ-A0603	28910121315212223			
Piston assembly	MHZ2-6S	WIHZ-A0003	2.0.9.0(2(3(32)2)2)			
	MHZ2-6C	MHZ-A0603C	289101213152021223			

Replacement part/Grease pack part no.: GR-S-010 (10 g)

#### Single acting/Normally open



## Single acting/Normally closed



# MHZ MHF MHL MHR MHR MHK MHK MHY MHW -X MRHQ D-D


## **Component Parts**

No.	Description	Material	Note
14	Steel balls	High carbon chrome bearing steel	
15	Needle roller	High carbon chrome bearing steel	
16	Type C retaining ring	Carbon steel	Phosphate coated
17	Exhaust plug	Brass	Electroless nickel plated
18	Exhaust filter	Polyvinyl formal	
19	N.O. spring	Stainless steel spring wire	
20	N.C. spring	Stainless steel spring wire	
21	Rod seal	NBR	
22	Piston seal	NBR	
23	Gasket	NBR	
24	Gasket	NBR	


## **MHZ2** Series

## Construction: MHZ2-10 to 25

#### Double acting/With fingers open




#### Double acting/With fingers closed




#### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	ø10, ø16: Stainless steel ø20, ø25: Aluminum alloy	ø20, ø25: Hard anodized
3	Lever	Stainless steel	Nitriding
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitriding
8	Seal support	Stainless steel	
9	Rod cover	Synthetic resin	
10	Сар	Synthetic resin	Single acting/Normally open only
11	Bumper	Urethane rubber	

#### Single acting/Normally open



#### Single acting/Normally closed



#### **Component Parts**

No.	Description	Material	Note
12	Rubber magnet	Synthetic rubber	
13	Steel balls	High carbon chrome bearing steel	
14	Needle roller	High carbon chrome bearing steel	
15	Type C retaining ring	Carbon steel	Phosphate coated Single acting/Normally open only
16	Exhaust plug A	Brass	Electroless nickel plated
17	Exhaust filter A	Polyvinyl formal	
18	N.O. spring	Stainless steel spring wire	
19	N.C. spring	Stainless steel spring wire	
20	Rod seal	NBR	
21	Piston seal	NBR	
22	Gasket	NBR	

#### Replacement Parts

Description		MHZ2-10	MHZ2-16	MHZ2-20	MHZ2-25	Main parts
Seal kit	MHZ2-DDD MHZ2-DDC	MHZ10-PS	MHZ16-PS	MHZ20-PS	MHZ25-PS	202122
	MHZ2-DDSD	MHZ10S-PS	MHZ16S-PS	MHZ20S-PS	MHZ25S-PS	1
	MHZ2-□□□(N)	MHZ-AA1002(N)	MHZ-AA1602(N)	MHZ-AA2002(N)	MHZ-AA2502(N)	
Firmer constants	MHZ2-□□□(N)1	MHZ-AA1002(N)-1	MHZ-AA1602(N)-1	MHZ-AA2002(N)-1	MHZ-AA2502(N)-1	45613
Finger assembly	MHZ2-□□□(N)2	MHZ-AA1002(N)-2	MHZ-AA1602(N)-2	MHZ-AA2002(N)-2	MHZ-AA2502(N)-2	Mounting screw
	MHZ2-DDD3	MHZ-AA1002-3	MHZ-AA1602-3	MHZ-AA2002-3	MHZ-AA2502-3	
	MHZ2-DDD					
Piston assembly	MHZ2-DDSD	MHZ-AA1003	MHZ-AA1603	MHZ-AA2003	MHZ-AA2503	2111214
	MHZ2-DDCD					
End boss assembly	MHZ2-DDDW	MHZ-A1007	MHZ-A1607	MHZ-A2007	MHZ-A2507	Main body of adaptor
	MHZ2-DDDDK	MHZ-A1008	MHZ-A1608	MHZ-A2008	MHZ-A2508	Mounting screw for adaptor
	MHZ2-DDDDM	MHZ-A1009	MHZ-A1609	MHZ-A2009	MHZ-A2509	
	MHZ2-DDDDE	MHZ-A1010	MHZ-A1610	MHZ-A2010	MHZ-A2510	Seal
Lever assembly		MHZ-AA1004	MHZ-AA1604	MHZ-AA2004	MHZ-AA2504	3
* Finger option	Thu 1 1 1 1 0 5			Replacement part/Gre	ease pack part no.: GR	- <b>S-010</b> (10 g)


1 = Side tapped, 2 = Through-hole, 3 = Flat type fingers

\* End boss type


W = One-touch-fitting for coaxial tubing, K = With One-touch fitting, M = With M5 port, E = Side ported \* The end boss assembly other than type E should be mounted on the special body.



## Construction: MHZ2-32 to 40



### Double acting/With fingers closed



#### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	Aluminum alloy	Hard anodized
3	Lever	Stainless steel	Heat treated
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitriding
8	Сар	Aluminum alloy	Clear anodized
9	Bumper	Urethane rubber	
10	Rubber magnet	Synthetic rubber	
11	Steel balls	High carbon chrome bearing steel	


#### **Replacement Parts**

Description Seal kit		MHZ2-32	MHZ2-40	Main parts (19202)	
		MHZ32-PS	MHZ40-PS		
Finger assembly	MHZ2-000(N)	MHZ-A3202	MHZ-A4002	4.5.61113 Mounting screw	
	MHZ2-□□□(N)1	MHZ-A3202-1	MHZ-A4002-1		
i inger assembly	MHZ2-□□□(N)2	MHZ-A3202-2	MHZ-A4002-2		
	MHZ2-DDD3	MHZ-A3202-3	MHZ-A4002-3		
	MHZ2-DDD	MHZ-A3203	MHZ-A4003		
Piston assembly	MHZ2-DDSD	MHZ-A3203S	MHZ-A4003S	291012	
-	MHZ2-DDCD	MHZ-A32035	MHZ-A40035		
Lever assembly		MHZ-A3204	MHZ-A4004	3	


\* Finger option

1 = Side tapped, 2 = Through-hole, 3 = Flat type fingers

Single acting/Normally open




Single acting/Normally closed



#### **Component Parts**

No.	Description	Material	Note
12	Needle roller	High carbon chrome bearing steel	
13	Parallel pin	Stainless steel	
14	Type C retaining ring	Carbon steel	Phosphate coated
15	Exhaust plug A	Brass	Electroless nickel plated
16	Exhaust filter A	Polyvinyl formal	
17	N.O. spring	Stainless steel spring wire	
18	N.C. spring	Stainless steel spring wire	
19	Rod seal	NBR	
20	Piston seal	NBR	
21	Gasket	NBR	



MHZ Mhf

Replacement part/Grease pack part no.: GR-S-010 (10 g)


## MHZ2 Series

### Dimensions

# MHZ2-6 Double acting/Single acting Basic type

Use the MHZJ2 series with a dust cover when used in a place where there may be dust.






Ó

17

5.5






\* For single action, the port on one side is a breathing hole.

00

2.5 5



### MHZ2-10□ Double acting/Single acting

Use the MHZJ2 series with a dust cover when used in a place where there may be dust.

-X□


### **MHZ2** Series

#### Dimensions

#### MHZ2-16 Double acting/Single acting **Basic type**

30

Use the MHZJ2 series with a dust cover when used in a place where there may be dust.




Note) Through-hole mounting is not possible when using the auto switch at the square groove.

**SMC** 

## MHZ2-20 Double acting/Single acting Basic type

Use the MHZJ2 series with a dust cover when used in a place where there may be dust.




### **MHZ2** Series

#### Dimensions

#### MHZ2-25 Double acting/Single acting Basic type


Use the MHZJ2 series with a dust cover when used in a place where there may be dust.



**SMC** 

When closed 8.8 \_

### Parallel Type Air Gripper/Standard Type MHZ2 Series



MHZ2-32 Double acting/Single acting Basic type



Note) Through-hole mounting is not possible when using the auto switch at the square groove.

mounting groove

Ø


3.3

#### **⊘**SMC

### MHZ2 Series

#### Dimensions

#### MHZ2-40 Double acting/Single acting




Note) Through-hole mounting is not possible when using the auto switch at the square groove.

3.7

# Standard Type/MHZ2 Series **Finger Option**


#### Side Tapped Mounting [1/N1]




				(mm)
Model	Α	В	С	MM
MHZ2-6 1	2.5	5	2	M2 x 0.4
MHZ2-10	3	5.7	2	M2.5 x 0.45
MHZ2-16	4	7	2.5	M3 x 0.5
MHZ2-20	5	9	4	M4 x 0.7
MHZ2-25	6	12	5	M5 x 0.8
MHZ2-32 1	7	14	6	M6 x 1
MHZ2-40 1	9	17	7	M8 x 1.25

\* Specifications and dimensions other than the above are the same as the basic type (including narrow type).


#### Flat Type Fingers [3]



#### Through-holes in Opening/ Closing Direction [2/N2]




4 x øH through



			(mm)
Model	Α	В	н
MHZ2-622	2.5	5	2.4
MHZ2-10	3	5.7	2.9
MHZ2-16	4	7	3.4
MHZ2-20	5	9	4.5
MHZ2-25	6	12	5.5
MHZ2-32 2	7	14	6.6
MHZ2-40 2	9	17	9

\* Specifications and dimensions other than the above are the same as the basic type (including narrow type).



-

-0

¢

													(mm)	MA
Model	A	в	с	D	F	G Open	Closed	J	к	мм	L	w	Weight (g)	D-□
MHZ2-6 3 (1)	2	3.5	7.2	7.5	_	5 <sup>+1.2</sup>	1 <sup>+0.2</sup>	_	_	M2 x 0.4	3	4_0.05	26	
MHZ2-1033	2.45	6	5.2	10.9	2	5.4 +2.2	1.4_0.2	4.45	2H9 <sup>+0.025</sup>	M2.5 x 0.45	5	5 <sup>0</sup> <sub>-0.05</sub>	55	
MHZ2-16 3	3.05	8	8.3	14.1	2.5		1.4_0.2	5.8	2.5H9 <sup>+0.025</sup>	M3 x 0.5	6	8_0.05	115	
MHZ2-203	3.95	10	10.5	17.9	3	11.6 <sup>+2.3</sup>	1.6_0_2	7.45	3H9 <sup>+0.025</sup>	M4 x 0.7	8	10_0.05	225 (230)	
MHZ2-2533	4.9	12	13.1	21.8	4	16 +2.5	2 _0.2	8.9	4H9 <sup>+0.030</sup>	M5 x 0.8	10	12_0.05	410 (415)	
MHZ2-32[]3[]	7.3	20	18	34.6	5	25 +2.7	3 <sup>0</sup> <sub>-0.2</sub>	14.8	5H9 <sup>+0.030</sup>	M6 x 1	12	15_0.05	740 (785)	
MHZ2-40_3_	8.7	24	22	41.4	6	33 <sup>+2.9</sup>	3 <sub>_0.2</sub>	17.7	6H9 <sup>+0.030</sup>	M8 x 1.25	16	18 <sup>0</sup> -0.05	1335 (1430)	

C

Note 1) To mount attachments, use JISB1101 type M2 round head screws. Be careful not to use commercially available M2 hexagon socket head cap bolt as its top diameter is large. Note 2) Specifications and dimensions other than the above are the same as the basic type (including narrow type).

Note 3) The overall length is the same as the MHQ(G) flat finger type. Note 4) The values inside ( ) are for the single acting type.



MHZ MHF

MHL

MHR

МНК

MHS

MHC

МНТ

MHY

MHW -X□


MRHQ

# Standard Type/*MHZ2* Series Body Option: End Boss Type

#### Applicable Model

			Type of pi	iping port	Applicable model					
Symbol	Piping port location	MHZ2-10	MHZ2-16 MHZ2-2		MHZ2-25	Double acting	Single	acting		
		WH22-10	WI122-10	WIT122-20	WI122-25	Double actility	Normally open	acting Normally closed		
E	Side ported	M3 x 0.5		M5 x 0.8		•	•	•		
w		With ø	4 One-touch fitt	ing for coaxial t	ubing	•	—	-		
к	Axial ported		With ø4 One-	-touch fitting		_	•	•		
М			M5 x	( 0.8		_	•	•		

#### Side Ported [E]




					(mm)
Model	Α	в	D1	D2	Е
MHZ2-10□□E	15	7	12f8 -0.016 -0.043	11	52.8
MHZ2-16□□E	20	10	16f8 -0.016 -0.043	15	58.7
MHZ2-20□□E	22	12	20f8 -0.020 -0.053	19	70.5
MHZ2-25	25	15	25f8 -0.020 -0.053	24	82.9

Other dimensions and specifications correspond to the standard type.

\* Refer to the dimension table.

\* When auto switches are used at the square groove on the side, side mounting with through-holes is not possible.

### Axial Ported (with One-touch fitting for coaxial tubing) [W]




\* Refer to the dimension table.

\* When auto switches are used at the square groove on the side, side mounting with through-holes is not possible.

#### **Changing from Coaxial to Single Tubing**

Changing to single tubing is possible by using a branch "Y" or branch tee fitting. In this case particularly, single tube fittings and tube for  $\sigma 3.2$  will be necessary.



								(mm)
Model	Α	в	D1	D2	Е	F	G	н
MHZ2-10D□W	15	7	12f8 -0.016 -0.043	11	52.8	18	28.3	5.5
MHZ2-16D□W	20	10	$16f8 \ _{-0.043}^{-0.016}$	15	58.7	16.2	27.7	6.5
MHZ2-20D□W	22	12	20f8 -0.020 -0.053	19	70.5	18.2	31.2	7.5
MHZ2-25D UW	25	15	25f8 -0.020 -0.053	24	82.9	19	31.8	10

Other dimensions and specifications correspond to the standard type.

#### Applicable Coaxial Tubing


Reference symbol

I/Internal nassa


	Applicable Co	axiai Tubiliy
	Model	TW04B-20
	Specifications	10040-20
	Outside diameter	4 mm
	Max. operating pressure	0.6 MPa
	Min. bending radius	10 mm
ge)	Operating temperature	-20 to 60°C
9~)	Matorial	Nylon 12

#### Branch Tee, Different Diameter Tee, Branch "Y", Male Run Tee

Please contact your SMC sales representative for details of the coaxial fittings and tubing.







#### Axial Ported (with One-touch fitting) [K]

\* Refer to the dimension table.

\* When auto switches are used at the square groove on the side, side mounting with through-holes is not possible.

Note 1) Normally open type plug position.

Note 2) Normally closed type plug position.

Axial Ported (with M5 Port) [M]

The plug is mounted on only one side for the single acting type.

								(mm)
Model	Α	в	D1	D2	Е	F	G	н
MHZ2-10 <sup>S</sup> CK	15	7	12f8 -0.016 -0.043	11	52.8	18	28.3	5.5
MHZ2-16 <sup>S</sup> CK	20	10	16f8 -0.016 -0.043	15	58.7	16.2	27.7	6.5
MHZ2-20 <sup>S</sup> □K	22	12	20f8 -0.020 -0.053	19	70.5	18.2	31.2	7.5
MHZ2-25 <sup>S</sup> CK	25	15	25f8 -0.020 -0.053	24	82.9	19	31.8	10

Other dimensions and specifications correspond to the standard type.

#### Applicable Tubing

Description/Model	Nylon tubing	Soft nylon tubing	Polyurethane tubing	Polyurethane coil tubing
Specifications	T0425	TS0425	TU0425	TCU0425B-1
Outside diameter (mm)	4	4	4	4
Max. operating pressure (MPa)	1.0	0.8	0.5	0.5
Min. bending radius (mm)	13	12	10	_
Operating temperature (°C)	-20 to 60	-20 to 60	-20 to 60	-20 to 60
Material	Nylon 12	Nylon 12	Polyurethane	Polyurethane

Refer to "Best Pneumatics No. 7" regarding One-touch fittings and tubing.

#### Auto switch mounting groove (4 locations) M5 x 0.8 Plug Piping port (Except ø10) ø10 : M-3F End boss assembly ø16 to 25: M-5F GŇ 50 Φ ф 50 4 Φ m± F Note 2) в 5 F Auto switch mounting groove (Both sides)

								(mm)
Model	Α	в	D1	D2	Е	F	G	н
MHZ2-10 <sup>S</sup> CM	15	7	12f8 -0.016 -0.043	11	52.8	18	28.3	5.5
MHZ2-16 <sup>S</sup> 🗆 M	20	10	16f8 -0.016 -0.043	15	58.7	16.2	27.7	6.5
MHZ2-20 <sup>S</sup> CM			20f8 -0.020 -0.053	19	70.5	18.2	31.2	7.5
МНZ2-25 <sup>S</sup> □М	25	15	25f8 -0.020 -0.053	24	82.9	19	31.8	10

Other dimensions and specifications correspond to the standard type.

\* Refer to the dimension table.

\* When auto switches are used at the square groove on the side, side mounting with through-holes is not possible.

Note 1) Normally open type plug position.

Note 2) Normally closed type plug position.

The plug is mounted on only one side for the single acting type.

#### Weight

,					(g)	<b>-X</b> □
	Model		End boss ty	pe (Symbol)		MDUA
	Model	E	W	к	М	MRHQ
	MHZ2-10	65	64	66	65	MA
	MHZ2-16	148	147	148	147	
	MHZ2-20	272	277	277	277	<b>D-</b> □
	MHZ2-25	485	495	496	494	

MHZ

MHF

MHL

MHR

МНК

MHS


MHC

МНТ

MHY Mhw

# Parallel Type Air Gripper/Long Stroke Type MHZL2 Series Ø10, Ø16, Ø20, Ø25

How to Order



#### Applicable Auto Switches/Refer to pages 797 to 850 for further information on the auto switch

		_						Auto swit	ch model	Lead	wire I	ength	(m) *	App	licab	le mo	odel			
Туре	Special function	Electrical entry	Indicator light	Wiring (Output)		oad voltag	je	Electrical en	try direction	0.5	1	3	5	ø10	~10	~00	~05	Pre-wired connector	Applie	ad
	lanotion	Chary	iigin	(Output)		DC	AC	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	010	010	020	025			
								M9NV	M9N	٠	•	•	0	•	٠	•	•	0		
				3-wire (NPN)		5V. 12 V		F8N	Ι	٠	-	•	0	—	٠	٠	٠	-	IC	
c	_			3-wire (PNP)		5V, 12 V		M9PV	M9P	٠	•	•	0	•	٠	٠	٠	0	circuit	
switch				3-wire (PINP)				F8P		٠	-	•	0	—	٠	•	٠	-		
AS C				2-wire		12 V		M9BV	M9B	٠	•	•	0	٠	٠	٠	٠	0		
auto		Grommet	Yes	2-wire	24 V	12 V		F8B	-	٠	-	•	0	—	٠	٠	٠	-	_	Relay,
state	Diagnosis		163	3-wire (NPN)		5 V. 12 V	_	M9NWV	M9NW	٠	•	•	0	•	٠	•	٠	0	IC	PLC
	(2-color			3-wire (PNP)		5 V, 12 V		M9PWV	M9PW	٠	•	•	0	•	٠	•	٠	0	circuit	
Solid	indicator)			2-wire		12 V		M9BWV	M9BW	٠	•	•	0	٠	٠	٠	٠	0	-	
0)	Water resistant			3-wire (NPN)		5 V. 12 V		M9NAV**	M9NA**	0	0	•	0	•	٠	•	٠	0	IC	
	(2-color			3-wire (PNP)		5 V, 12 V		M9PAV**	M9PA**	0	0	•	0	•	٠	•	٠	0	circuit	
	indicator)			2-wire		12 V		M9BAV**	M9BA**	0	0	٠	0	٠	٠	٠	٠	0	-	1

\*\* Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance.

\* Lead wire length symbols: 0.5 m······ Nil (Example) M9NW \* Solid state auto switches marked with O are produced upon receipt of order.

- 1 m ..... M (Example) M9NWM
- 3 m ..... L (Example) M9NWL
- 5 m······ Z (Example) M9NWZ

Note 1) When using the 2-color indicator type, please make the setting so that the indicator is lit in red to ensure the detection at the proper position of the air gripper. Note 2) Through-hole mounting is not possible when using the auto switch at the square groove on the side.

Note 3) When the product is ordered with auto switch, only MHZL2-10 is shipped with the auto switch mounting brackets. When the auto switch is used at the square groove on the side with MHZL2-16 to 25, mounting brackets (BMG2-012) are required. Order them separately. Refer to page 457 for the auto switch mounting brackets.





#### Symbol

Double acting: Internal grip



Double acting: External grip



Single acting/ Normally closed: Internal grip



Single acting/ Normally open: External grip



### Refer to pages 454 to 458 for the specifications with auto switch.

- Auto switch installation examples and mounting positions
- Auto switch hysteresis
- Auto switch mounting
- · Protrusion of auto switch from edge of body



Made to Order Individual Specifications (Refer to pages 436 to 439 for details.)

Symbol	
-X6110□	With dust cover

#### Made to Order

CI	icl	٢l	he	re	for	d	e	tai	ls

Symbol	Specifications/Description
-X4	Heat resistance (100°C)
-X5	Fluororubber seal
-X7	Closing direction spring assist
-X12	Opening direction spring assist
-X50	Without magnet
-X53	EPDM seal/Fluorine grease
-X56	Axial ported type
-X63	Fluorine grease
-X79	Grease for food processing machines, Fluorine grease
-X79A	Grease for food processing machines
-X81A	Anti-corrosive treatment of finger
-X81B	Anti-corrosive treatment of finger and guide

#### Specifications

	Fluid		Air				
	D. H. H.		ø10: 0.2 to 0.7 MPa				
Operating	Operating	ouble acting	ø16 to ø25: 0.1 to 0.7 MPa				
pressure		Normally open	ø10: 0.35 to 0.7 MPa				
	acting	Normally closed	ø16 to ø25: 0.25 to 0.7 MPa				
Ambient a	Ambient and fluid temperature		-10 to 60°C				
Repeatab	ility		±0.01 mm				
Max. oper	rating fr	equency	120 c.p.m.				
Lubricatio	on		Not required				
Action			Double acting/Single acting				
Auto swit	ch (Opt	ion) Note)	Solid state auto switch (3-wire, 2-wire)				

Note) Refer to pages 797 to 850 for further information on auto switches.

#### Model

Action			_	Gripping	force Note 1)	Opening/	
		Model Size		Gripping for Effective		Closing stroke (Both sides)	Weight (g)
			(mm)	External	Internal	(mm)	
		MHZL2-10D	10	11	17	8	60
Double MHZL2-16D acting MHZL2-20D MHZL2-25D		MHZL2-16D	16	34	45	12	135
		20	42	42 66		270	
		MHZL2-25D	25	65 104		22	470
	open	MHZL2-10S	10	7.1		8	70
	ly op	MHZL2-16S	16	27		12	145
	Normally	MHZL2-20S	20	33	_	18	290
Single		MHZL2-25S	25	50		22	515
acting	closed	MHZL2-10C	10		13	8	70
	Clo	MHZL2-16C	16		38	12	145
	Vormally	MHZL2-20C	20		57	18	290
No.		MHZL2-25C	25		85	22	515

Note 1) Values based on pressure of 0.5 MPa, gripping point L = 20 mm, at center of stroke. Note 2) Values excluding weight of auto switch.

#### Option

#### Body Option/End Boss Type

	Piping port Type of piping port Applicable model											
	Piping port	Piping port Type of piping port										
Symbol	location	MHZL2-10	MHZL2-10 MHZL2-16 MHZL2-20 MHZL2-29									
Nil	Basic type	M3 x 0.5		•								
Е	Side ported	M3 x 0.5		•	•							
w	Axial ported	With ø4	With ø4 One-touch fitting for coaxial tubing									
к	Axial ported		With ø4 One-touch fitting									
М	Axial ported		M5 x 0.8									

\* For detailed body option specifications, refer to option specifications on pages 434 and 435.

MHZ

MHF

MHR




When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to <u>the IDK series in the</u> Best Pneumatics No. 6.


### MHZL2 Series

#### Construction: MHZL2-10 to 25

#### Double acting/With fingers open



#### Double acting/With fingers closed




#### **Component Parts**


No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	ø10, ø16: Stainless steel ø20, ø25: Aluminum alloy	ø20, ø25: Hard anodized
3	Lever	Stainless steel	Nitriding
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitriding
8	Сар	Aluminum alloy	Clear anodized
9	Bumper	Urethane rubber	

#### **Replacement Parts**

#### Single acting/Normally open



#### Single acting/Normally closed



#### **Component Parts**

No.	Description	Material	Note
10	Rubber magnet	Synthetic rubber	
11	Steel balls	High carbon chrome bearing steel	
12	Needle roller	High carbon chrome bearing steel	
13	Type C retaining ring	Carbon steel	Phosphate coated
14	Exhaust plug A	Brass	Electroless nickel plated
15	Exhaust filter A	Polyvinyl formal	
16	Spring	Stainless steel spring wire	
17	Rod seal	NBR	
18	Piston seal	NBR	
19	Gasket	NBR	

Replacement part/Grease pack part no.: GR-S-010 (10 g)

Description		MHZL2-10	MHZL2-16	MHZL2-20	MHZL2-25	Main parts
Seal kit	Seal kit		MHZL16-PS	MHZL20-PS	MHZL25-PS	171819
Finger assembly	MHZL2-DDD	MHZL-AA1002	MHZL-AA1602	MHZL-AA2002	MHZL-AA2502	
	MHZL2-DDD1	MHZL-AA1002-1	MHZL-AA1602-1	MHZL-AA2002-1	MHZL-AA2502-1	4561
	MHZL2-DDD2	MHZL-AA1002-2	MHZL-AA1602-2	MHZL-AA2002-2	MHZL-AA2502-2	Mounting screw
	MHZL2-□□□3	MHZL-AA1002-3	MHZL-AA1602-3 MHZL-AA2002-3		MHZL-AA2502-3	
	MHZL2-DDD	MHZL-A1003	MHZL-A1603	MHZL-A2003	MHZL-A2503	
Piston assembly	MHZL2-DDSD	WINZL-AT003	WINZL-A1003	MITZL-A2003	WITZL-A2000	291012
Γ	MHZL2-DDCD	MHZL-A1003C	MHZL-A1603C	MHZL-A2003C	MHZL-A2503C	]
	MHZL2-DDDW	MHZ-A1007	MHZ-A1607	MHZ-A2007	MHZ-A2507	Main body of adaptor
End boss assembly	MHZL2-DDDDK	MHZ-A1008	MHZ-A1608	MHZ-A2008	MHZ-A2508	Mounting screw for adaptor
	MHZL2-DDDDM	MHZ-A1009	MHZ-A1609	MHZ-A2009	MHZ-A2509	Seal kit
	MHZL2-DDDDE	MHZ-A1010	MHZ-A1610	MHZ-A2010	MHZ-A2510	oodantat
Lever assembly		MHZL-A1004	MHZL-A1604	MHZL-A2004	MHZL-A2504	37

\* Finger option

1 = Side tapped, 2 = Through-hole, 3 = Flat type fingers

\* End boss type


W = One-touch-fitting for coaxial tubing, K = With One-touch fitting, M = With M5 port, E = Side ported

\* The end boss assembly other than type E should be mounted on the special body.



#### Dimensions

#### MHZL2-10 Double acting/Single acting



\* For single action, the port on one side is a breathing hole.

Note) Through-hole mounting is not possible when using the auto switch at the square groove.

6.2

Ć

5.4

0

¢

429

MHZ

MHF

MHL

MHR

MHK MHS

MHC

МНТ

MHY

MHW

-X□


MRHQ

MA D-

### MHZL2 Series

#### Dimensions

#### MHZL2-16 Double acting/Single acting



Note) Through-hole mounting is not possible when using the auto switch at the square groove.


6.2

2.1

Auto switch

mounting groove

## MHZL2-20 Double acting/Single acting Basic type



Note) Through-hole mounting is not possible when using the auto switch at the square groove.

2.1

Auto switch

mounting groove

MHZ

MHF

MHL

MHR

МНК

MHS Mhc

МНТ

MHY

MHW

-X□

MRHQ


MA

D-🗆


### MHZL2 Series


#### Dimensions

### MHZL2-25 Double acting/Single acting Basic type




The values inside ( ) are dimensions for the single acting type.





\* For single action, the port on one side is a breathing hole.


#### Auto Switch Mounting Groove Dimensions



Note) Through-hole mounting is not possible when using the auto switch at the square groove.

# Long Stroke Type/*MHZL2* Series Finger Option


#### Side Tapped Mounting [1]




				(mm)
Model	Α	В	С	MM
MHZL2-10□1□	3	5.7	2	M2.5 x 0.45
MHZL2-16□1□	4	7	2.5	M3 x 0.5
MHZL2-20□1□	5	9	4	M4 x 0.7
MHZL2-25□1□	6	12	5	M5 x 0.8


\* Specifications and dimensions other than the above are the same as the basic type.


#### Flat Type Fingers [3]





### Through-holes in Opening/ Closing Direction [2]





			(mm)
Model	Α	В	Н
MHZL2-10 2	3	5.7	2.9
MHZL2-16□2□	4	7	3.4
MHZL2-20 2	5	9	4.5
MHZL2-25 2	6	12	5.5

\* Specifications and dimensions other than the above are the same as the basic type.

MHZ

-X□

MRHQ

MA

D-□

(mm)

Madal	•		0		-	0	G		K			w	Weig	ht (g)
Model	A	в		D	F	Open	Closed	J	ĸ	ММ	L	vv	Double acting	Single acting
MHZL2-10□3□	2.45	7	5.2	11.9	2	9.4+2.2	1.4_0_2	4.95	2H9 <sup>+0.025</sup>	M2.5 x 0.45	5	5_0 -0.05	60	70
MHZL2-16□3□	3.3	9	8.3	15.7	2.5	13.4+2.2	1.4_0_	6.55	2.5H9 <sup>+0.025</sup>	M3 x 0.5	6	8_0_05	135	145
MHZL2-20 3	3.95	12	10.5	19.9	3	19.6 <sup>+2.4</sup>	1.6_0_	8.45	3H9+0.025	M4 x 0.7	8	10_0.05	270	290
MHZL2-25□3□	4.9	14	13.1	23.8	4	24 +2.6	2 _0.2	9.9	4H9 <sup>+0.030</sup>	M5 x 0.8	10	12_0.05	460	505


\* Specifications and dimensions other than the above are the same as the basic type.

# Long Stroke Type/*MHZL2* Series Body Option: End Boss Type

#### **Applicable Model**

Type of p				of piping port Applicable model		1		
Symbol	Piping port location	MHZL2-10	MHZL2-16	MHZL2-20 MHZL2-25		Double acting	Single	acting
		WHZLZ-10	WHZLZ-10	MITZEZ-20 MITZEZ-25	ZL2-25 Double acting	Normally open	Normally closed	
E	Side ported	M3 x 0.5	< 0.5 M5 x 0.8		•	•	•	
w		With a	With ø4 One-touch fitting for coaxial tubing			•	—	_
к	Axial ported		With ø4 One-touch fitting			—	•	•
М			M5 x 0.8			_	•	•

#### Side Ported [E]



						(mm)
Model	Α	в	D1	D2	E1	E2
MHZL2-10	15	7	12f8 -0.016 -0.043	11	52.8	62.8
MHZL2-16□□E	20	10	16f8 -0.016 -0.043	15	61.4	66.4
MHZL2-20	22	12	20f8 -0.020 -0.053	19	75.7	81.7
MHZL2-25	25	15	25f8 -0.020 -0.053	24	86.2	96.2


Other dimensions and specifications correspond to the standard type.

\* Refer to the dimension table.

\* When auto switches are used at the square groove on the side, side mounting with through-holes is not possible.

### Axial Ported (with One-touch fitting for coaxial tubing) [W]

Re



\* Refer to the dimension table.


\* When auto switches are used at the square groove on the side, side mounting with through-holes is not possible.

ference symbol	
1	
O (External passage)	

(Internal passage)

#### Changing from Coaxial to Single Tubing

Changing to single tubing is possible by using a branch "Y" or branch tee fitting. In this case particularly, single tube fittings and tubing for ø3.2 will be necessary.



					(mm)
Model	Α	в	D1	D2	E1
MHZL2-10D W	15	7	12f8 -0.016 -0.043	11	52.8
MHZL2-16DDW	20	10	16f8 -0.016 -0.043	15	61.4
MHZL2-20D W	22	12	20f8 -0.020 -0.053	19	75.7
MHZL2-25D W	25	15	25f8 -0.020 -0.053	24	86.2

Other dimensions and specifications correspond to the standard type.


#### Applicable Coaxial Tubing Type W

Model Specifications	TW04B-20
Outside diameter	4 mm
Max. operating pressure	0.6 MPa
Min. bending radius	10 mm
Operating temperature	-20 to 60°C
Material	Nylon 12

y	Type v	v		
		F	G	н
	ø10	17	30	5.5
	ø16	16.7	33.7	6.5
	ø20	18.2	38.2	7.5
	ø25	18.3	41.3	10


#### Branch tee, Different diameter tee, Branch "Y", Male run tee

Please contact your SMC sales representative for details of the coaxial fittings and tubing.



@SMC

#### Axial Ported (with One-touch fitting) [K]



\* Refer to the dimension table.

\* When auto switches are used at the square groove on the side, side mounting with through-holes is not possible.

Note 1) Normally open type plug position.

Note 2) Normally closed type plug position.

The plug is mounted on only one side for the single acting type.

					(mm)
Model	Α	в	D1	D2	E2
MHZL2-10 <sup>S</sup> □K	15	7	12f8 -0.016 -0.043	11	62.8
MHZL2-16 <sup>S</sup> ⊡K	20	10	16f8 -0.016 -0.043	15	66.4
MHZL2-20 <sup>S</sup> □K	22	12	20f8 -0.020 -0.053	19	81.7
MHZL2-25 <sup>S</sup> □K	25	15	25f8 -0.020 -0.053	24	96.2

Other dimensions and specifications correspond to the standard type.

#### Applicable Tubing

Description/	Nylon	Soft nylon	Polyurethane	Polyurethane
Model	tubing	tubing	tubing	coil tubing
Specifications	T0425	TS0425	TU0425	TCU0425B-1
Outside diameter (mm)	4	4	4	4
Max. operating pressure (MPa)	1.0	0.8	0.5	0.5
Min. bending radius (mm)	13	12	10	—
Operating temperature (°C)	-20 to 60	-20 to 60	-20 to 60	-20 to 60
Material	Nvlon 12	Nvlon 12	Polyurethane	Polvurethane

Refer to "Pneumatic Piping Equipment (CAT. E50)" regarding One-touch fittings and tubing.

D1

12f8 -0.016

16f8 -0.016

20f8 -0.020

25f8 -0.020

#### Type K

Model

MHZL2-10 C DM

MHZL2-16 C DM

MHZL2-20 C

MHZL2-25 C DM

F

16.7

18 2

18.3

Туре М

Ø10 17

ø16

ø**20** 

ø**25** 

.,								
	F	G	Н					
ø <b>10</b>	17	40	5.5					
ø16	16.7	38.7	6.5					
ø <b>20</b>	18.2	44.2	7.5					
ø <b>25</b>	18.3	51.3	10					

A B

15

20 10

22 | 12

25 | 15

G

40

38.7

44 2

51.3

7

Other dimensions and specifications correspond to the standard type.

н

5.5

6.5

75

10

-X□

MRHQ

MA

D-🗆

MHZ

(mm)

66.4

D2 E2


11 62.8

15

19 81.7

24 96.2

#### Axial Ported (with M5 port) [M]



\* Refer to the dimension table.

 $\ast$  When auto switches are used at the square groove on the side, side mounting with through-holes is not possible.

Note 1) Normally open type plug position.

Note 2) Normally closed type plug position

The plug is mounted on only one side for the single acting type

#### Weight


					(g)				
Model		End boss type (Symbol)							
	E								
	Double acting	Single acting	- W	к	М				
MHZL2-10-	70	80	70	80	80				
MHZL2-16-	170	180	170	180	180				
MHZL2-20-	310	330	310	330	330				
MHZL2-25-	535	580	535	580	580				



# **MHZL2** Series Made to Order Individual Specifications

Made to Order

Please contact SMC for detailed dimensions, specifications and lead times.



#### Specifications

Model	Basic type	Heat resistance	Fluororubber seal	
Ambient and fluid temperature	-10 to 60°C	-10 to 100°C	-10 to 60°C	
Specifications other than the above	Be Same as the standard type			

#### Model

			Gripping f	orce Note 1)		
Action	Model Y	Bore size (mm)	Gripping force per finger Effective value (N)		Closing stroke (Both sides)	Note 2) Weight (g)
			External	Internal	(mm)	
	MHZL2-10D-X6110	10	11	17	8	85
Double acting	MHZL2-16D-X6110	16	34	45	12	150
aoung	MHZL2-20D-X6110	20	42	66	18	385

Note 1) Values based on pressure of 0.5 MPa, gripping point L = 20 mm, at

center of stroke. Note 2) Values excluding weight of auto switch.

#### Hoto 2) failage skoldaling Holgin of

#### For heat resistance

#### A Warning

Be aware that smoking cigarettes after your hands have come into contact with the grease used for this air gripper can create a gas that is hazardous to humans.

#### ▲ Caution

- Note 1) Magnet is built-in, but when using an auto switch, the acceptable temperature range becomes -10 to 60°C.
- Note 2) For the dust cover option part number, only fluororubber (F) or silicone rubber (S) can be selected.
- Note 3) For lubrication, specialized grease GR-F is recommended.

#### For fluororubber seal

#### A Caution

- Note 1) Consult with SMC, since the type of chemical and the operating temperature may not allow the use of this product. Note 2) Since the standard-type magnet is built-in, consult with SMC
- for the product's adaptability to the operating environment. Note 3) The dust cover material is also fluororubber. Thus, enter (F)
  - for the fluororubber dust cover in the part number.




A Precautions

### Made to Order Individual Specifications MHZL2 Series

Dimensions

#### MHZL2-10D□-X6110 Basic type/Double acting




\* The dimensions of the heat resistance or fluororubber seal types are the same as those shown above.

MHF MHL MHR MHS MHS MHC MHT MHW -X MRHQ MA D-

MHZ


### MHZL2 Series

#### Dimensions



\* The dimensions of the heat resistance or fluororubber seal types are the same as those shown above.


## Made to Order Individual Specifications MHZL2 Series



\* The dimensions of the heat resistance or fluororubber seal types are the same as those shown above.

D-🗆

# Parallel Type Air Gripper with Dust Cover **MHZJ2** Series ø6, ø10, ø16, ø20, ø25, ø32, ø40



#### Applicable Auto Switches/Refer to pages 797 to 850 for further information on the auto switch.

			light				ad voltage			Lead	wire le	ength (	m) *	A	oplica	able	mod	el			
Туре	pe Special Electrical function entry	ndicator	Wiring (Output)		Load voltage		Electrical entry direction		0.5 1		3	5	<i>~</i> 6	a10	a16	ø20	a 25	Pre-wired connector	Applie	cable ad	
	lanotori	onay	ludic	(Output)		DC AC		Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	00	010	010	020	025		load	au
				2 wire (NDN)	wire (NPN)			M9NV	M9N	•	٠	٠	0	٠	٠	٠	٠	•	0		
				3-WIE (INFIN)		5 V. 12 V		F8N	—	•	—	•	0	٠	-	٠	•	•	—	IC	
				3-wire (PNP)		5 V, 12 V	V, 12 V	M9PV	M9P	•	•	٠	0	٠	٠	٠	•	•	0	circuit	
switch		o wile (i Ni )				F8P		•	-	٠	0	٠	—	٠	٠	•	-				
				2-wire	12 V	] [	M9BV	M9B	٠	٠	٠	0	٠	٠	٠	٠	•	0			
auto			V		24 V	1 1	·	F8B	-	•	—	٠	0	٠	—	٠	•	•	-	_	Relay,
state	Diagnosis	Grommet	res	3-wire (NPN)	24 V	5 V, 12 V	_	M9NWV	M9NW	•	•	٠	0	٠	٠	٠	•	•	0	IC	PLC
l sta	(2-color			3-wire (PNP)			5 V, 12 V		M9PWV	M9PW	٠	•	٠	0	٠	٠	٠	٠	•	0	circuit
Solid	indicator)			2-wire	1	12 V		M9BWV	M9BW	٠	•	٠	0	٠	٠	٠	٠	•	0	-	1
0)	Water resistant			3-wire (NPN)	N)	EV 10.V		M9NAV**	M9NA**	0	0	•	0	٠	٠	•	•	•	0	IC	]
	(2-color			3-wire (PNP)	1	5 V, 12 V		M9PAV**	M9PA**	0	0	٠	0	٠	٠	٠	٠	•	0	circuit	
	indicator)			2-wire	1	12 V		M9BAV**	M9BA**	0	0	٠	0	٠	٠	٠	٠	•	0	-	1

\* Water resistant type auto s witches can be mounted \* Solid state auto switches marked with O are produced upon receipt of order. \* Lead wire length symbols: 0.5 m ..... Nil (Example) M9NW

1 m······ M (Example) M9NWM 3 m ...... L (Example) M9NWL

5 m ...... Z (Example) M9NWZ

Note 1) When using the 2-color indicator type, please make the setting so that the indicator is lit in red to ensure the detection at the proper position of the air gripper. Note 2) When using a D-F8D switch on sizes ø6, mount it at a distance of 10 mm or more from magnetic substances such as iron, etc. 440



Symbol



Double acting: External grip

Single acting/

Normally open:

Single acting/ Normally closed: Internal grip



External grip

	Made to Order Individual Specification (Refer to pages 451 to 453 for detail						
Symbol	Specifications/Description						
VALAAT							

#### -X6100 With dust cover (ø32, ø40) Made to Order

Click here for details							
Symbol	Specifications/Description						
-X4	Heat resistance (100°C)						
-X5	Fluororubber seal						
-X7	Closing direction spring assist						
-X12	Opening direction spring assist						
-X50	Without magnet						
-X53	EPDM seal/Fluorine grease						
-X56	Axial ported type						
-X63	Fluorine grease						
-X64	Finger: Side tapped mounting						
-X65	Finger: Through-hole mounting						
-X77A	Dust cover adhesion						
-X77B	Dust cover adhesion (Finger part only)						
-X78A	Dust cover caulking						
-X78B	Dust cover caulking (Finger part only)						
-X79	Grease for food processing machines, Fluorine grease						
-X79A	Grease for food processing machines						
-X81A	Anti-corrosive treatment of finger						

#### Moisture Control Tube **IDK Series**

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the IDK series in the Best Pneumatics No. 6.

#### Specifications

	Flui	d	Air				
Operating pressure			ø6: 0.15 to 0.7 MPa				
	Do	uble acting	ø10: 0.2 to 0.7 MPa				
			ø16 to ø25: 0.1 to 0.7 MPa				
	0:	Normally open	ø6: 0.3 to 0.7 MPa				
	Single acting		ø10: 0.35 to 0.7 MPa				
		Normally closed	ø16 to ø25: 0.25 to 0.7 MPa				
Ambient a	nd fluid	d temperature	-10 to 60°C				
Repeatabi	lity		±0.01 mm				
Max. opera	ating fr	equency	180 c.p.m.				
Lubricatio	n		Not required				
Action			Double acting, Single acting				
Auto switch (option) Note)			Solid state auto switch (3-wire, 2-wire)				

Note) Refer to pages 797 to 850 for further information on auto switches.

#### Model

			Bore	Gripping f	Orce Note 1)	Opening/		
Action		Model size (mm)		Gripping for Effective	Closing stroke (Both sides)	Weight (g)		
			()	External	Internal	` (mm) ´		
		MHZJ2- 6D	6	3.3	6.1	4	28	
	MHZJ2-1		10	9.8	17	4	60	
Double acting		MHZJ2-16D	16	30	40	6	130	1
acting		MHZJ2-20D	20	42	66	10	250	
		MHZJ2-25D	25	65	104	14	460	ſ
	open	MHZJ2- 6S	6	1.9		4	28	
			10	6.3		4	60	ſ
	Normally	MHZJ2-16S	16	24		6	130	
	E	MHZJ2-20S	20	28		10	255	ſ
Single		MHZJ2-25S	25	45		14	465	L
acting	closed	MHZJ2- 6C	6		3.7	4	28	ſ
	clos	MHZJ2-10C	10		12	4	60	l
	Vormally	MHZJ2-16C	16	-	31	6	130	ſ
		MHZJ2-20C	20		56	10	255	
	ů	MHZJ2-25C	25		83	14	465	[

Note 1) Values based on pressure of 0.5 MPa, gripping point L = 20 mm, at center of stroke. Note 2) Values excluding weight of auto switch.

#### Option

#### Body Option/End Boss Type

Symbol	Piping port		Applicable mode					
Symbol	location	MHZJ2-10	MHZJ2-16	MHZJ2-20	MHZJ2-25	Double acting	Single acting	
Nil	Basic type	M3 x 0.5		•				
Е	Side ported	M3 x 0.5		•				
w	Axial ported	With ø4 0	One-touch fit	ting for coaxia	al tubing	•	—	
к	Axial ported		With ø4 One	-	•			
М	Axial ported		M5 x 0.8 — •					

\* For detailed body option specifications, refer to option specifications on pages 449 and 450.

Refer to pages 454 to 458 for the specifications with auto switch.

· Auto switch installation examples and mounting positions

· Auto switch hysteresis


· Auto switch mounting

· Protrusion of auto switch from edge of body


### MHZJ2 Series

#### Construction: MHZJ2-6

#### Double acting/With fingers open




#### Double acting/With fingers closed




#### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	Stainless steel	
3	Lever	Stainless steel	Heat treated
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitriding
8	Magnet holder	Stainless steel	
9	Holder	Brass	Eiectroless nickel plated
10	Holder lock	Stainless steel	
11	Сар	Aluminum alloy	Clear anodized
12	Bumper	Urethane rubber	
13	Magnet	-	Nickel plated
14	Steel balls	High carbon chrome bearing steel	
15	Needle roller	High carbon chrome bearing steel	
		CR	Chloroprene rubber
16	Dust cover	FKM	Fluororubber
		Silicone rubber	
17	Type C retaining ring	Carbon steel	Nickel plated
18	Exhaust plug	Brass	Electroless nickel plated
19	Exhaust filter	Polyvinyl formal	
20	N.O. spring	Stainless steel spring wire	
21	N.C. spring	Stainless steel spring wire	
22	Rod seal	NBR	
23	Piston seal	NBR	
24	Gasket	NBR	
25	Gasket	NBR	

#### Single acting/Normally open



#### Single acting/Normally closed



#### **Replacement Parts**

Descr	iptio	n	MHZJ2-6	Main parts	
Seal kit			Please contact SMC to replace the seal kit.		
	al	CR	MHZJ2-J6		
Dust cover	Material	FKM	MHZJ2-J6F	16	
	ŝ	Silicone rubber	MHZJ2-J6S		
Finger assembly	,		Please contact SMC to replace the finger assembly.		
	Μ	HZJ2-6D□	MHZJ-A0603		
Piston assembly	Μ	IHZJ2-6S□	MHZJ-A0603	2891012131522324	
rision assembly	MHZJ2-6C□		MHZJ-A0603C	289101213152122 2324	

Replacement part/Grease pack part no.: GR-S-010 (5 g)



Single acting/Normally open

Single acting/Normally closed

ΠŤ

ПП

(16

114


(17

 $\odot$ 


¢

#### Construction: MHZJ2-10□ to 25□

#### Double acting/With fingers open



#### Double acting/With fingers closed



#### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminum alloy	Hard anodized
2	Piston	ø10, ø16: Stainless steel	ø20, ø25:
-	FISION	ø20, ø25: Aluminum alloy	Hard anodized
3	Lever	Stainless steel	Nitriding
4	Guide	Stainless steel	Heat treated
5	Finger	Stainless steel	Heat treated
6	Roller stopper	Stainless steel	
7	Lever shaft	Stainless steel	Nitriding
8	Сар	Aluminum alloy	Clear anodized
9	Bumper	Urethane rubber	
10	Rubber magnet	Synthetic rubber	
11	Steel balls	High carbon chrome bearing steel	

#### No. Note Description Material 12 Needle roller High carbon chrome bearing steel 13 Type C retaining ring Carbon steel Nickel plated Electroless nickel plated 14 Exhaust plug A Brass 15 Exhaust filter A Polyvinyl formal 16 N.O. spring Stainless steel spring wire 17 N.O. spring Stainless steel spring wire NBR 18 Rod seal Piston seal 19 NBB 20 Gasket NBR CR Chloroprene rubber FKM 21 Fluororubber Dust cover Silicone rubber

#### Poplacement Ports

Description			MHZJ2-10	MHZJ2-16	MHZJ2-20	MHZJ2-25	Main parts			
Seal kit			MHZJ10-PS	MHZJ16-PS	MHZJ20-PS	MHZJ25-PS	181920			
	rial	CR	MHZJ2-J10	MHZJ2-J16	MHZJ2-J20	MHZJ2-J25				
Dust cover	Mater	FKM	MHZJ2-J10F	MHZJ2-J16F	MHZJ2-J20F	MHZJ2-J25F	20			
	Ma	Silicone rubber	MHZJ2-J10S	MHZJ2-J16S	MHZJ2-J20S	MHZJ2-J25S	]			
Finger assembly	Finger assembly		MHZJ-AA1002	MHZJ-AA1602	MHZJ-AA2002	MHZJ-AA2502	4561 Mounting thread			
Piston assembly			MHZJ-A1003	MHZJ-A1603	MHZJ-A2003	MHZJ-A2503	291012			
		MHZJ2-□□D□W	MHZ-A1007	MHZ-A1607	MHZ-A2007	MHZ-A2507	Main body of adaptor			
End boss		MHZJ2-DDDDK	MHZ-A1008	MHZ-A1608	MHZ-A2008	MHZ-A2508	Mounting screw for adaptor			
assembly		MHZJ2-DDDDM	MHZ-A1009	MHZ-A1609	MHZ-A2009	MHZ-A2509	Seal kit			
		MHZJ2-DDDDE	MHZ-A1010	MHZ-A1610	MHZ-A2010	MHZ-A2510	Searkit			
Lever assembly			MHZJ-A1004	MHZJ-A1604	MHZJ-A2004	MHZJ-A2504	3			

\* Material of packing

NBR = Nitrile rubber, FKM = Fluororubber

\* Material of dust cover

CR = Chloroprene rubber, FKM = Fluororubber, Silicone rubber

\* End boss type

W = One-touching fitting for coaxial tubing, K = With One-touch fitting, M = With M5 port, E = Side ported

\* The end boss assembly other than type E should be mounted on the special body.



Replacement part/Grease pack part no.: GR-S-010 (10 g)

MHZ

MHF

MHL MHR

MHK

MHS

MHC

MHT

MHY

MHW


-X□


MRHO MA D-🗆


### MHZJ2 Series

#### Dimensions

## MHZJ2-6 Double acting/Single acting Basic type









\* For single action, the port on one side is a breathing hole.

#### Auto Switch Mounting Groove Dimensions






**SMC** 

Note) When using auto switches, through-hole mounting is not possible.


### MHZJ2 Series

#### Dimensions

#### MHZJ2-16 Double acting/Single acting Basic type




MHZJ2-20 Double acting/Single acting Basic type



### MHZJ2 Series

Dimensions




# With Dust Cover/MHZJ2 Series Body Option: End Boss Type

#### **Applicable Model**

	Piping port location		Type of p	iping port	Applicable model			
Symbol		MHZJ2-10	MHZJ2-16	6 MHZJ2-20 MHZJ2-25		Double acting	Single acting	
			WI1232-25	Double acting	Normally open	Normally closed		
E	Side ported	M3 x 0.5	0.5 M5 x 0.8				•	•
w		With	ø4 One-touch fit	ting for coaxial tu	bing	•	—	_
к	Axial ported		With ø4 One-touch fitting				•	
М		M5 x 0.8				—	•	•


#### Side Ported [E]



\* Refer to the dimension table.

\* When auto switches are used on ø10, side mounting with through-holes is not possible.

#### Axial Ported (with One-touch fitting for coaxial tubing) [W]



ÌSMC


\* Refer to the dimension table.

\* When auto switches are used on ø10, side mounting with through-holes is not possible.

#### Changing from Coaxial to Single Tubing


Changing to single tubing is possible by using a branch "Y" or branch tee fitting.

In this case particularly, single tube fittings and tubing for ø3.2 will be necessary.



#### Branch Tee, Different Diameter Tee, Branch "Y", Male Run Tee

Please contact your SMC sales representative for details of the coaxial fittings and tubing.



MHZ

MHF

MHL


MRHO

MA

D-

### MHZJ2 Series

### Axial Ported (with One-touch fitting) [K]



\* Refer to the dimension table

\* When auto switches are used on ø10, side mounting with through-holes is not possible

Note 1) Normally open type plug position.

Note 2) Normally closed type plug position.

The plug is mounted on only one side for the single acting type.

(mm) Model A в D1 D2 Е F G н MHZJ2-10<sup>S</sup>□K 15 7 12f8 -0.016 -0.043 11 40 5.5 16 28 MHZJ2-16<sup>S</sup>□K 20 10 16f8 -0.016 15 16.2 277 43.5 6.5 MHZJ2-20<sup>S</sup>□K 22 12 20f8 19 51.7 167 31.2 75 MHZJ2-25<sup>S</sup>⊡K 25 25f8 -0.020 -0.053 15 24 61.3 17.3 32.3 10

Other dimensions and specifications correspond to the standard type.

#### Applicable Tubing

Model

MHZJ2-10<sup>S</sup>□M

MHZJ2-16<sup>S</sup>□M

MHZJ2-20<sup>S</sup>□M

MHZJ2-25<sup>S</sup>□M

Α в D1

15 7 12f8 -0.016 11 40 16 28

20 10

22 12

25 15 25f8 -0.020 24 61.3 17.3 32.3 10

Description/Model Specifications	Nylon tubing <b>T0425</b>	Soft nylon tubing TS0425	Polyurethane tubing TU0425	Polyurethane coil tubing TCU0425B-1
Outside diameter (mm)	4	4	4	4
Max. operating pressure (MPa)	1.0	0.8	0.5	0.5
Min. bending radius (mm)	13	12	10	_
Operating temperature (°C)	-20 to 60	-20 to 60	-20 to 60	-20 to 60
Material	Nylon 12	Nylon 12	Polyurethane	Polyurethane

Refer to "Pneumatic Piping Equipment (CAT, E50)" regarding One-touch fittings and tubing

16f8 -0.016

20f8 -0.020

Other dimensions and specifications correspond to the standard type.

0.043

D2 Е F G н

15 43.5 16.2 27.7 6.5


19

51.7 16.7 31.2 7.5

(mm)

5.5

# Axial Ported (with M5 port) [M]



\* Refer to the dimension table.

\* When auto switches are used on ø10, side mounting with through-holes is not possible

Note 1) Normally open type plug position.

Note 2) Normally closed type plug position.

The plug is mounted on only one side for the single acting type.

#### Weight

				(g)		
Model	End boss type (Symbol)					
Wodel	E	w	к	М		
MHZJ2-10	70	70	70	70		
MHZJ2-16	165	165	165	165		
MHZJ2-20□□	290	290	290	290		
MHZJ2-25	525	525	525	525		


**SMC** 



# **MHZJ2** series Made to Order Individual Specifications



Please contact SMC for detailed dimensions, specifications and lead times.



#### Specifications

Model		Basic type	Heat resistance	Fluororubber seal	
Fluid		Air			
Operating pressure	Double acting	0.1 to 0.7 MPa			
Ambient and flu	id temperature	-10 to 60°C -10 to 100°C -10 to 60°C			
Repeatability		±0.01 mm			
Max. operating	frequency		60 c.P.m		
Lubrication		Not required			
Action		Double acting			

#### Model

Action	Model	Bore size (mm)	Gripping force Note 1) Gripping force per finger Effective value (N)		Opening/ Closing stroke (Both sides)	Note 2) Weight (g)
			External	Internal	(mm)	
Double	MHZJ2-32D-X6100	32	158	193	22	760
acting	MHZJ2-40D-X6100	40	254	318	30	1325

Note 1) Values based on pressure of 0.5 MPa, gripping point L = 20 mm, at center of stroke.

Note 2) Values excluding weight of auto switch.

#### \land Handling Precautions

#### Heat resistance

#### A Warning

Be aware that smoking cigarettes after your hands have come into contact with the grease used for this air gripper can create a gas that is hazardous to humans.

#### ▲ Caution

- Note 1) Magnet is built-in, but when using an auto switch, the acceptable temperature range becomes -10 to 60°C.
- Note 2) With the part number for the dust cover option, only fluororubber (F) or silicone rubber (S) options may be selected.

Note 3) For lubrication, specialized grease GR-F is recommended.

#### ▲ Caution

Note 1) Please contact SMC, since the type of chemical and the operating temperature may not allow the use of this product.


Fluororubber seal

- Note 2) Since the standard-type magnet is built-in, please contact SMC for the product's adaptability to the operating environment.
- Note 3) For the air gripper with a dust cover, the dust cover material is also fluororubber. Thus, enter (F) for the fluororubber dust cover in the part number.

### MHZJ2 Series

Dimensions (Dimensions other than specified below are the same as the standard type.)


#### MHZJ2-32D□-X6100 Basic type/Double acting



\* The dimensions of the heat resistance or fluororubber seal types are the same as those shown above.

Dimensions (Dimensions other than specified below are the same as the standard type.)

#### MHZJ2-40D□-X6100 Basic type/Double acting



**SMC** 

### MHZ2/MHZ 2 Series Auto Switch Installation Examples and Mounting Position

Various auto switch applications are possible through different combinations of auto switch quantities and detecting positions. 1) Detection when Gripping Exterior of Workpiece

Detection example	1. Confirmation of fingers in reset position	2. Confirmation of workpiece held	3. Confirmation of workpiece released
Position to be detected	Position of fingers fully opened	Position when gripping workpiece	Position of fingers fully to the second seco
Operation of auto switch	Auto switch turned on when fingers return. (Light ON)	Auto switch turned on when gripping a workpiece. (Light ON)	When a workpiece is not held (Abnormal operation): Auto switch to turn ON (Light ON)
So Dre auto switch *One position, any of ①, ②, and ③ can be detected. Two positions of *Two positions of be detected. B B C C	•	•	•
Two auto switches	•	•	-
*Two positions of (1, 2, and 3 can be detected.	_	•	•
be detected.	•		•
How to determine auto switch installation position	Step 1) Fully open the fingers.	Step 1) Position fingers for workpiece.	Step 1) Fully close the fingers.
At no pressure or low	Step 2) Insert the auto switch into the sw	itch installation groove in the direction sh	own in the following drawing.0
pressure, connect the auto switch to a power supply, and follow the directions.			
directions.			
	Step 3) Slide the auto switch in the direction of the arrow until the indicator light illuminates.		ection of the arrow until the light illuminates and the direction of the arrow beyond the position
	<b></b> ⊗⊡	Position where light turns	ON
	Step 4) Slide the auto switch further in the direction of the arrow until the indicator light goes out.		<u>₩₩</u>
	_ <u></u> ®⊢	<u>0.</u>	3 to 0.5 mm
	Step 5) Move the auto switch in the opposite direction and fasten it at a position 0.3 to 0.5 mm beyond the position where the indicator light illuminates.	Position to be secured	
	Position where light turns ON		
	Position to be 0.3 to 0.5 mm		
	<b>→</b> '		

Note 1) It is recommended that gripping of a workpiece be performed close to the center of the finger stroke. Note 2) When holding a workpiece close at the end of open/close stroke of fingers, detecting performance of the combinations listed in the above table may

Note 2) When holding a workpiece close at the end of open/close stroke of fingers, detecting performance of the combinations listed in the above table may be limited, depending on the hysteresis of an auto switch, etc.



### Parallel Type Air Gripper MHZ2, MHZ 2 Series

Various auto switch applications are possible through different combinations of auto switch quantities and detecting positions. 2) Detection when Gripping Interior of Workpiece

Detection example	1. Confirmation of fingers in reset position	2. Confirmation of workpiece held	3. Confirmation of workpiece released	
Position to be detected	Position of tingers fully closed	Position when gripping workpiece	Position of ingers fully opened	
Operation of auto switch	Auto switch turned ON when fingers return. (Light ON)	Auto switch turned ON when gripping a workpiece. (Light ON)	When a workpiece is not held (Abnormal operation): Auto switch to turn ON (Light ON)	
See of the sector of	•	•	•	
Two auto switches Two positions of Two positions of (), (2), and (3) can be detected.		•	•	
be detected.	•	_	Ū.	
How to determine auto switch installation position	Step 1) Fully close the fingers.	Step 1) Position fingers for gripping a workpiece.	Step 1) Fully open the fingers.	
At no pressure or low	Step 2) Insert the auto switch into the sw	itch installation groove in the direction sh	nown in the following drawing.	MHZ
pressure, connect the auto switch to a power supply, and follow the directions.				MHI
difections.				
	Step 3) Move the auto switch in the direction of the arrow and fasten it at a position 0.3 to 0.5 mm beyond the position where the indicator light illuminates.	Step 3) Silde the auto switch in the c illuminates.	∃€	MHF MHF MHS
	Position where light turns ON	Step 4) Slide the auto switch further light goes out.	in the direction of the arrow until the indicator	MHO
	0.3 to 0.5 mm			МНУ
	Position to be secured	Step 5) Move the auto switch in direction indicated by the arrow from again.	the opposite direction 0.3 to 0.5 mm in the its location when the indicator light comes on	-X⊏ MRH
		Position where light turns ON	- <del></del>	MA D-
		· · · · ·	0.3 to 0.5 mm	
		Position to be secured		

Note 1) It is recommended that gripping of a workpiece be performed close to the center of the finger stroke.

Note 2) When holding a workpiece close at the end of open/close stroke of fingers, detecting performance of the combinations listed in the above table may be limited, depending on the hysteresis of an auto switch, etc.




### MHZ2, MHZ 2 Series

#### **Auto Switch Hysteresis**

Auto switches have hysteresis similar to micro switches.

Use the table below as a guide when adjusting auto switch positions, etc.



#### Hysteresis


Auto switch model	D-Y59A/Y59B D-Y69A/Y69B D-Y7P(V) D-Y7□W(V)	D-F8□	D-M9□(V) D-M9□W(V) D-M9□A(V)
MHZ2-6	No setting	0.5	0.5
MHZ2-10, MHZL2-10	0.5	No setting	0.5 Note)
MHZ2-16 , MHZL2-16	0.5	0.5	0.5
MHZ2-20 , MHZL2-20	0.5	0.5	0.8
MHZ2-25 , MHZL2-25	0.5	0.5	0.5
MHZ2-32□	0.5	0.5	0.7
MHZ2-40□	0.5	0.5	0.9
MHZJ2-6		0.5	0.5
MHZJ2-10		0.5	0.5
MHZJ2-16	No setting	0.5	0.5
MHZJ2-20		0.5	0.8
MHZJ2-25		0.5	0.5

Note) When mounting D-M9□(V), M9□W(V) and M9□A(V) on MHZ2-10□ and MHZL2-10, mounting brackets (BMG2-012) are required.

#### **Auto Switch Mounting**

#### Applicable models: MHZ2-6 MHZJ2 Series Round groove of the MHZ2 series Round groove of the MHZL2 series

To set the auto switch, insert the auto switch into the auto switch installation groove of the gripper from the direction indicated in the following drawing. After setting the position, tighten the attached auto switch mounting screw with a flat head watchmaker's screwdriver.



- Note) Use a watchmaker's screwdriver with a grip diameter of 5 to 6 mm to tighten the auto switch mounting screw. Also, tighten with a torque of about 0.05 to 0.15 N·m, or about 0.05 to
  - 0.10 N·m for D-M9 $\square$ A(V).


#### [Mounting of Auto Switch: Precautions]

When mounting an auto switch on the piping port surface of the MHZJ2-10□, the auto switch may not be mountable due to interference with the fitting. Use an extension fitting included with the product for the combinations in the table below.

Auto switch model	One-touch Mini Fittings (KQ2H/KQ2S/KQ2L/KQ2W) KJH/KJS/KJL/KJW	
D-M9□(V)	×	1
D-M9⊟W(V)	×	
D-F8	×	()
D-M9□A(V)	×	Ŭ




#### Mounting dimensions of extension fitting



#### Applicable models:

#### Square groove on the side of the MHZ2 series Square groove on the side of the MHZL2 series

- (1) To set the auto switch, insert the auto switch into the installation groove of the cylinder as shown below and set it roughly.
- (2) Insert the auto switch into the auto switch bracket installation groove.
- (3) After confirming the detecting position, tighten the set screws (M2.5) attached to the auto switch and set it.
- (4) Be sure to change the detecting position in the state of (2).




uto Switch Mounting Bracket: Part No.				
Auto switch part no.	Auto switch mounting bracket part no.			
D-M9□(V) D-M9□W(V) D-F8□ D-M9□A(V)	BMG2-012			


- Note) Use a watchmaker's screwdriver with a grip diameter of 5 to 6 mm to tighten the set screws (M2.5).
  - The tightening torque should be 0.05 to 0.1 N·m.
  - As a guide, it should be turned about 90° beyond the point at which tightening can be felt.

Note) D-F8□ cannot be mounted on MHZ2-10□, MHZJ2-10□ and MHZL2-10□

#### [Handling of Mounting Brackets: Precautions]

When auto switch is set on the mounting side as shown below, allow at least 2 mm run off space on mounting plate since the auto switch is protruded from the gripper edge.





## MHZ2, MHZ Series

#### Protrusion of Auto Switch from Edge of Body

The amount of auto switch protrusion from the body's end surface is as shown in the table below.

Use this as a standard when mounting, etc.

D-F8 has no protrusion from the body's end surface.

The end boss type has no protrusion either.

#### Standard Body

	Lead wire type		e type	In-line electric	cal entry type		Perpendicular electrial entry type		
	/	$\langle \rangle \rangle$	awing					Ĩ	
		HIIO SHI	an model	<u>ـــــ</u>	L	L.		L.	
		Ser !	110			+			-
		Air gripper model	, del	D-Y59□ D-Y7P D-Y7□W	D-M9□ D-M9□W	D-M9□A	D-Y69□ D-Y7PV D-Y7□WV	D-M9⊡V D-M9⊡WV	D-M9□AV
		MHZ2-6□	Open Close	No setting	11 13	13	No setting	9 11	11 13
			Open	1	3.5 Note 3)	5.5 Note 3)	_	1.5 <sup>Note 3)</sup>	3.5 <sup>Note 3)</sup>
		MHZ2-10	Close	7.5	6.5 Note 3)	8.5 Note 3)	6.5	4.5 <sup>Note 3)</sup>	6.5 <sup>Note 3)</sup>
			Open		1	3		_	
7	-	MHZ2-16□	Close	6	4	6	5	2	4
	otariuaru			6	-			<u> </u>	-
100	2	MHZ2-20□	Open	4	2	4	3	_	
4	Ø		Close	4					
0	n	MHZ2-25□	Open		-	-	-	_	-
			Close	1	-	_	_	-	-
		MHZ2-32□	Open		_	_		-	_
			Close	3	_	_	2	-	_
		MHZ2-40	Open	_	_	_	_	-	_
			Close	2	_	-	1	-	—
		MHZJ2-6□ MHZJ2-10□	Open		11	13	No setting	9	11
			Close	No setting	13	15		11	13
	ē		Open		5	7		3	5
ġ	ő		Close		7	9		5	7
-	vvitn aust cover	MHZJ2-16	Open		2	4		_	_
	Ĩ		Close		5	7		3	5
	_	MHZJ2-20	Open		_			_	_
	5		Close		3	5		1	3
2	>		Open		_	_		_	_
		MHZJ2-25	Close		2	4		_	_
			Open	0.5	1.5 Note 3)	3,5 Note 3)	_	_	_
	_	MHZL2-10D	Close	8.5	8 Note 3)	10 Note 3)	7.5	6 Note 3)	8 Note 3)
	<u>اع</u> ا		Open	-	_		7.5	_	<b>.</b>
	g	MHZL2-16D	Close	8	6	8	7	4	6
	0	5 		0	U	0	1	4	U
	q	MHZL2-20D	Open			7	_	3	
	Double acting		Close	7	5		6		5
		MHZL2-25D	Open			-		-	-
			Close	5.5	3.5	5.5	4.5	1.5	3.5
	Single acting (Normally open)	MHZL2-10S	Open	-	_	_		-	
9	ly o		Close	-	-	_			_
ð	mal	MHZL2-16S	Open	-				-	-
Long stroke	Nor		Close	3	1	3	2	-	_
g	) Bu	MHZL2-20S	Open	-	_	_	-	-	_
p.	acti		Close	1	-	—	_	—	-
	gle	MHZL2-25S	Open		_			_	_
	Sir	WITZL2-235	Close	—	_	_	—	—	_
	(je	MUZI 0 400	Open	-	_	_	_	_	—
	acting (Normally closed)	MHZL2-10C	Close	5.5	5 Note 3)	7 Note 3)	4.5	3 Note 3)	5 Note 3)
	ALC:		Open	_	_	_	_	_	_
	L L	MHZL2-16C	Close	5.5	3.5	5.5	4.5	1.5	3.5
	Z.		Open	_	_	_		_	_
	cting	MHZL2-20C	Close	3.5	1.5	3.5	2.5		_
	e ac		Open	-	-		2.5		
	Single	MHZL2-25C	Close	1.5	_	_	0.5		
	55		0058	1.0	_		0.0		

Note 1) There is no protrusion if no values are entered in the table. Note 2) The actual mounting position should be adjusted after confirming the auto switch operating conditions. Note 3) When mounting D-MB(U/N, MB(WU/N) and MB\_DA(V) on MH22-10[] and MH2L2-10, mounting brackets (BMG2-012) are required.

# *MHZ2 Series* Made to Order: Individual Specifications 1

Ī


Ì



#### 1 Built-in needle valve for finger speed control

Symbol -X46


Installation of a variable throttle allows adjustment of the finger opening/closing speed.



Bore size (mm)	10, 16, 20, 25			
Action	Double acting			
Needle position	Refer to the dimensions and figures below.			
Specifications/dimensions other than the above	Same as the standard type			
Note) Net sweileble for all all and all				

Note) Not available for ø6, ø32 and ø40.

Dimensions (Dimensions other than specified below are the same as the standard type.)



Adjust so that the finger opening/closing speed will be no greater than necessary. If the finger opening/closing speed is greater than necessary, impact forces acting on the fingers and other parts will increase. This can cause a loss of repeatability when gripping workpieces and have an adverse effect on the life of the unit.

This needle is used to adjust the finger closing speed. When adjusting the opening speed (attenuating impact during operation, etc.), use a meter-out control speed controller AS series.

#### Guide for Internal Needle Adjustment

Model	Number of rotations from fully closed needle condition Note)
MHZ2-10D -X46	1/4 to 1/2
MHZ2-16D -X46	1/2 to 1
MHZ2-20D -X46	1 to 1 <sup>1</sup> /2
MHZ2-25D -X46	11/2 to 2

Note) The condition in which the needle is tightened gently until it stops.

				(mm)	MHF
Model	Α	В	С	D *	
MHZ2-10DDD-X46	9	11	4.5	5.2	MHL
MHZ2-16D -X46	7.5	13	7	5.8	<u> </u>
MHZ2-20D -X46	10	15	7	6	MHR
MH72-25D	10.7	20	7	62	

Dimensions other than the above are identical to the standard type; refer to pages 417 to 420.

\* Reference values to establish criteria for needle adjustment.

MHZ
MHF
MHL
MHR
MHK
MHS
MHC
MHT
MHY
MHW
-X□
MRHQ
MA
D-🗆


# MHZ2 Series Made to Order: Individual Specifications 2



#### 2 MHQ2/MHQG2 Compatible Flat Type Fingers

Symbol -X51

Previous MHQ2/MHQG2 series compatible flat type finger is selectable for the MHZ2 series.




Bore size (mm)	10, 16, 20, 25
Action	Double acting, Single acting (normally open, normally closed)
Finger dimensions	Refer to the dimensions and figures below.
Specifications/dimensions other than the above	Same as the standard type

Note 1) Not available for ø6, ø32 and ø40.

Note 2) An option symbol (3) for the flat finger type is not specified.

Dimensions (Dimensions other than specified below are the same as the standard type.)



(mm)										
Model		АВ			D	G		мм		w
		A   E		вС	5	Open	Closed	IVIIVI	- L	vv
MHZ2-10□□-X51	MHQG2 compatible	3	6	5.2	12	9.7 +2.2	5.7 _0.4	M2 x 0.4	3.6	5 _0.05
	MHQ2 compatible	2	5	5.2	9	9.7 0 2.2	5.7 -0.4	M2 x 0.4	3.6	5-0.05
MHZ2-16□□-X51	MHQG2 compatible	4	8	8.3	16	12.6 +2.2	6.6 _0.4	M3 x 0.5	6	8 _0.05
	MHQ2 compatible	2.5	7	8.3	12	12.6 +2.2	6.6-0.4	M3 x 0.5	6	8 -0.05
MHZ2-20	MHQG2 compatible	5	10	10.5	20.8	17.2 +2.2	7.2 -0.4	M4 x 0.7	8	10-0.05
	MHQ2 compatible	3.3	9	10.5	15.5	17.2 +2.2	7.2 _0.4	M4 x 0.7	8	10_0.05
MHZ2-25□□□-X51	MHQG2 compatible	6.5	12	13.1	25	22.8 +2.5	8.8 -0.4	M5 x 0.8	10	12-0.05
WITIZ2-2000-X51	MHQ2 compatible	3.5	12	13.1	19	22.8 <sup>+2.5</sup>	8.8 0	M5 x 0.8	10	12_0.05





### MHZ Series Specific Product Precautions


Be sure to read this before handling the products.

#### Mounting Air Grippers/MHZ 2 Series

Possible to mount from 3 directions.

#### How to mount air grippers

#### Axial mounting (Body tapped)




Model	Applicable bolts	Max. tightening torque (N·m)	Max. screw-in depth (L mm)	
MHZ_2-6 <sup>Note)</sup>	M2 x 0.4	0.15	4.5	
MHZ_2-10	M3 x 0.5	0.88	6	
MHZ_2-16	M4 x 0.7	2.1	8	
MHZ_2-20	M5 x 0.8	4.3	10	
MHZ_2-25	M6 x 1	7.3	12	
MHZ_2-32	M6 x 1	7.9	13	
MHZ_2-40	M8 x 1.25	17.7	17	

Note) Axial mounting type is not available for MHZ2-6 and MHZJ2-6.

Model	Hole diameter (mm)	Hole depth (mm)
MHZ_2- 6	ø7H8 <sup>+0.022</sup>	1.5
MHZ_2-10	ø11H9 <sup>+0.043</sup>	2
MHZ_2-16	ø17H9 <sup>+0.043</sup>	2
MHZ_2-20	ø21H9 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	3
MHZ_2-25	ø26H9 <sup>+0.052</sup>	3.5
MHZ_2-32	ø34H9 <sup>+0.062</sup>	4
MHZ2-40	ø42H9 <sup>+0.062</sup>	4

#### Perpendicular mounting (Body tapping)




Model	Applicable bolts	Max. tightening torque (N·m)	Max. screw-in depth (L mm)		
MHZ 2-6Note	M2 x 0.4	0.15	4		
MHZ_2-10	M3 x 0.5	0.9	6		
MHZ_2-16	M4 x 0.7	1.6	4.5		
MHZ_2-20	M5 x 0.8	3.3	8		
MHZ_2-25	M6 x 1	5.9	10		
MHZ_2-32	M6 x 1	5.9	10		
MHZ_2-40	M8 x 1.25	13.7	13		
Nists) Everyth MUZO O surd MUZIO O					

Note) Except MHZ2-6 and MHZJ2-6.


#### How to mount air grippers

Lateral mounting (Body tapped and through-hole) •Body tapped



Model	Applicable bolts	Max. tightening torque (N·m)	Max. screw-in depth (L mm)	
MHZ_2-6	M3 x 0.5	0.88	10	
MHZ_2-10	M3 x 0.5	0.69	5	
MHZ_2-16	M4 x 0.7	2.1	8	
MHZ_2-20	M5 x 0.8	4.3	10	
MHZ_2-25	M6 x 1	7.3	12	
MHZ_2-32	M6 x 1	7.9	13	
MHZ_2-40	M8 x 1.25	17.7	16	

#### Body through-holes




Model	Applicable bolts	Max. tightening torque (N·m)			
MHZ[]2- 6	M2.5 x 0.45	0.49			
MHZ_2-10	M2.5 x 0.45	0.49			
MHZ_2-16	M3 x 0.5	0.88			
MHZ_2-20	M4 x 0.7	2.1			
MHZ_2-25	M5 x 0.8	4.3			
MHZ_2-32	M5 x 0.8	4.3			
MHZ[2-40	M6 x 1	7.3			

Note) Use body tapped for D-Y59, D-Y69, D-Y7P with auto switch types. Make sure that the bolt's screw-in depth is less than those shown in the table below to prevent the tip of the bolt from pressing the switch body.

Model	Max. screw-in depth (L mm)
MHZ_2- 6	_
MHZ_2-10	5
MHZ_2-16	8
MHZ_2-20	10
MHZ_2-25	12
MHZ_2-32	13
MHZ_2-40	16

#### How to mount the attachment to the finger

The attachment must be mounted on fingers using bolts such as finger mounting female threads, etc., which should be tightened with the tightening torque in the table below.



Model	Applicable bolts	Max. tightening torque (N·m)	MHZ
MHZ[]2- 6		0.15	MULE
MHZ_2-10	M2.5 x 0.45	0.31	MHF
MHZ_2-16	M3 x 0.5	0.59	
MHZ_2-20	M4 x 0.7	1.4	MHL
MHZ2-25	M5 x 0.8	2.8	
MHZ2-32	M6 x 1	4.9	MHR
MHZ2-40	M8 x 1.25	11.8	
			MHK
			MHS
			MHC
			MHT
			MHY
			MHW
			-X□
			MRHQ
			MA
			<b>D</b> -□

**Operating Environment** 

### A Caution

#### Use caution for the anti-corrosiveness of linear guide section.

Martensitic stainless steel is used for the finger guide. But, use caution that anti-corrosiveness is inferior to the austenitic stainless steel. Especially, in an environment where waterdrops are adhered by condensation, etc., rust might be generated.



# High Rigidity MHQG2 Series Ø32, Ø40

#### With guide holder

Possible to mount the solid state auto switch with indicator light.



#### Specifications

Fluid			Air	
		e acting	0.1 to 0.6 MPa	
Operating pressure Single acting	Normally open			
	acting	Normally closed	0.25 to 0.6 MPa	
Ambient and fluid temperature		perature	-10 to 60°C	
Repeatabilit	Repeatability		ø32, 40: ±0.02 mm	
Max. operating frequency		су	ø32, 40: 60 c.p.m	
Lubrication			Not required	
Operating s	ystem		Double acting, Single acting	
Auto switch (Option) *		uto switch (Option) * Solid state auto switch: D-M9N(V), D-Y59 <sup>°</sup> <sub>6</sub> , C		

\* Refer to pages 797 to 850 for the detailed specifications of auto switches.

#### Model

Operati	ng system	Model	Cylinder bore (mm)	Gripping force Note 1) (Effective value) N	Opening/Closing stroke (mm)	Weight (g)
Daubl		MHQG2-32D	32	External grip: 88 Internal grip: 139	20	1100
Doubi	Double acting MHQG2-40D		40	External grip: 158 Internal grip: 247	28	1940
	Normally	MHQG2-32S	32	69	20	1110
Single	open	MHQG2-40S	40	130	28	1960
acting	Normally	MHQG2-32C	32	127	20	1110
	closed MHQG2-40C		40	227	28	1960

Note 1) Values at the pressure of 0.5 MPa. Double acting is compatible with both external and internal gripping forces, while single acting and normally open external gripping force, and single acting and normally closed internal gripping force.

Note 2) Values excluding weight of auto switch.

#### Symbol Double

Double acting: Internal grip

Double acting: External grip

Single acting/Normally closed: Internal grip



Single acting/Normally open: External grip



# With Dust Cover **MHQJ2** Series Ø10, Ø16, Ø20, Ø25

Air gripper with dustproof and dripproof construction

Enclosure to prevent accumulation of dust.

Sealed construction with a dust cover

Possible to mount the solid state auto switch with indicator light.

# Three-type dust cover variations for diversified applications



#### Symbol

Double acting: Internal grip



Double acting: External grip

Single acting/Normally closed: Internal grip



Single acting/Normally open: External grip



#### Specifications

Fluid			Air		
	Double acting		0.1 to 0.6 MPa		
Operating pressure	Single acting	Normally open	0.25 to 0.6 MPa		
		Normally closed			
Ambient and fluid temperature			-10 to 60°C		
Repeatability			±0.01 mm		
Max. operating frequency			180 c.p.m		
Lubrication			Not required		
Operating system			Double acting, Single acting		
Auto switch (Option) *			Solid state auto switch: D-M9N(V), D-M9P(V), D-M9B(V)		

\* Refer to pages 797 to 850 for the detailed specifications of auto switches.

#### Model

			Cylinder	Note 1) Gripping force	Opening/Closing	Note 2)	MHZ
Operati	ng system	Model	bore (mm)	(Effective value) N	stroke (mm)	Weight (g)	MHF
		MHQJ2-10D	10	11	4	90	
Double acting		MHQJ2-16D	16	34	6	180	MHL
		MHQJ2-20D	20	42	10	340	
		MHQJ2-25D	25	63	14	640	MHR
Single acting	Normally open	MHQJ2-10S	10	7.8	4	90	MHK Mhs
		MHQJ2-16S	16	26	6	181	
		MHQJ2-20S	20	33	10	342	
		MHQJ2-25S	25	49	14	643	
	Normally closed	MHQJ2-10C	10	7.8	4	90	MHC Mht
		MHQJ2-16C	16	26	6	181	
		MHQJ2-20C	20	33	10	342	
		MHQJ2-25C	25	49	14	643	
Note 1) Values at the pressure of 0.5 MPa. Double acting is compatible with both external and							MHY

Note 1) Values at the pressure of 0.5 MPa. Double acting is compatible with both external and internal gripping forces, while single acting and normally open external gripping force, and single acting and normally closed internal gripping force.
Note 2) Values excluding weight of auto switch.

MHS
MHC
MHT
MHY
MHW
X
WRHQ
MA
D-🗆