
# 2-Color Display High-Precision Digital Pressure Switch Series ZSE30A(F)/ISE30A




### Mounting

#### Bracket configuration allows mounting in four orientations.


### Replaceable One-touch fittings

The clip type allows easy removal of fittings. Fitting's type and size can be changed.



**SMC** 

# 2-Color Display High-Precision Digital Pressure Switch Series ZSE30A(F)/ISE30A



**SMC** 

#### Specifications

For details about the Pressure Switch Precautions, refer to pages 763 and 764. For details about the Specific Product Precautions, refer to the Operation Manual at SMC website.

	М	odel	ZSE30A (Vacuum pressure)	ZSE30	AF (Compound pressure)	ISE30A (Positive pressure)			
Rated pre	ssure rang	ge	0.0 to -101.0 kPa		-100.0 to 100.0 kPa	-0.100 to 1.000 MPa			
Display/S	et pressur	e range	10.0 to -105.0 kPa		-105.0 to 105.0 kPa	-0.105 to 1.050 MPa			
Withstand	d pressure	-	500 kPa		500 kPa	1.5 MPa			
Display/Minimum unit setting			0.1 kPa		0.1 kPa	0.001 MPa			
Applicabl	e fluid		Air, Non-corrosive gas, Non-flammable gas						
Power supply voltage			12 to 24 VDC ±10%, Ripple (p-p) 10% or less (with power supply polarity protection)						
Current consumption					40 mA or less				
Switch ou	ıtput		NPN or PNP op	en collecto	r 1 output, NPN or PNP open o	collector 2 outputs			
	Maximum	load current			80 mA				
	Maximum	applied voltage			28 V (at NPN output)				
	Residual	voltage		1 V or les	ss (with load current of 80 mA)				
Response time			2.5 ms or less (	with anti-ch	nattering function: 20, 100, 500	, 1000, 2000 ms)			
Short circuit protection					Yes				
Repeatability					±0.2% F.S. ±1 digit				
Hystere- Hysteresis mode		s mode	Variable (0 or above) Note 1)						
sis Window comparator mode		comparator mode							
	Note 2)	Output voltage (Rated pressure range)	1 to 5V ±2.5% F.S. 0.6 to 5 V ±2 ±1% F.S.						
	Voltage	Linearity							
Analog	output	Output impedance			Approx. 1 kΩ				
output	Note 3)	Output current (Rated pressure range)	4 to 20 mA	±2.5% F.8	2.4 to 20 mA ±2.5% F.S.				
	Current	Linearity							
	output	Load impedance	Maximum load impedance: Power supply voltage 12 V: 300 $\Omega,$ Power supply voltage 24 V: 600 $\Omega$ Minimum load impedance: 50 $\Omega$						
Display			4-digit, 7-segment, 2-color LCD (Red/Green)						
Display a	ccuracy		±2%	F.S. ±1 dig	git (Ambient temperature of 25	±3°C)			
ndicator	light		Lights up when switch output is turned ON. OUT1: Green, OUT2: Red						
	Enclosu	ire	IP40						
Environ-	Operati	ng temperature range	Operating: 0 to	50°C, Sto	red: -10 to 60°C (No freezing of	or condensation)			
nent	Operati	ng humidity range	Operating/Stored: 35 to 85% RH (No condensation)						
		nd voltage	1000 VAC for 1 minute between terminals and housing						
Insulation resistance			50 M $\Omega$ or more (500 VDC measured via megohmmeter) between terminals and housing						
<b>Femperat</b>	ure charac	teristics		±2	% F.S. (25°C reference)				
Lead wire	with conr	nector	Oilproof heavy-duty vinyl cable, 3 cores ø3.5, 2 m 4 cores Conductor area: 0.15 mm <sup>2</sup> (AWG26), Insulator O.D.: 1.0 mm						
Standards	s			CE, U	JL/CSA (E216656), RoHS				
			value, set the hysteresis above the fluctus						

Note 1) If applied pressure fluctuates near the set value, set the hysteresis above the fluctuation range to prevent chattering. Note 2) When analog voltage output is selected, analog current output cannot be used together.

Note 3) When analog current output is selected, analog voltage output cannot be used together.

### **Piping Specifications**

	Model	01	N01	C4H	C6H	N7H	C4L	C6L	N7L	
Port size		R1/8 M5 x 0.8	NPT1/8 M5 x 0.8	_	_	_	—	_	—	
	One-touch fitting, Straight type	_	-	ø4 mm ø5/32 inch	ø6 mm	ø1/4 inch	—	_	—	
	One-touch fitting, Elbow type	—	-	—	—	-	ø4 mm ø5/32 inch	ø6 mm	ø1/4 inch	
Wetted	Wetted Sensor pressure receiving area		Sensor pressure receiving area: Silicon							
parts material Piping port			C3602 (electroless nickel plating) O-ring: HNBR PBT, POM, Stainless steel 304, C3604 (electroless nickel plating) O-ring: NBR					ng)		
	Including lead wire with connector (3 cores, 2 m)	81	g	70 g	71 g	73 g	75 g	73 g	75 g	
Weight	Including lead wire with connector (4 cores, 2 m)	85 g		74 g	75 g	77 g	79 g	77 g	79 g	
	Excluding lead wire with connector	43 g		32 g	33 g	35 g	37 g	35 g	37 g	

#### **Option/Part No.**

When optional parts are required separately, use the following part numbers to place an order.

Part no.	Option	Note	Part no.	Option	Note
ZS-38-A1	Bracket A	Mounting screw (with 2 pcs. of M3 x 5L)	ZS-38-4G	Lead wire with connector (with connector cover)	4 cores, for 2 outputs, 2 m
ZS-38-A2	Bracket B	Mounting screw (with 2 pcs. of M3 x 5L)	ZS-38-5L	Lead wire with a connector for copying	3 cores, copy function, 1 m
ZS-38-A3	Bracket C	Mounting screw (with 2 pcs. of M3 x 5L)	ZS-38-U	Lead wire unit with a connector for copying	Copy function (up to 10 slaves)
ZS-27-C	Panel mount adapter	Mounting screw (with 2 pcs. of M3 x 8L)	ZS-38-C4H	One-touch fittings ø4 mm straight	O-ring, one-touch clip included
ZS-27-D	Panel mount adapter + Front protection cover	Mounting screw (with 2 pcs. of M3 x 8L)	ZS-38-C6H	One-touch fittings ø6 mm straight	O-ring, one-touch clip included
ZS-27-01	Front protection cover		ZS-38-N7H	One-touch fittings ø1/4 inch straight	O-ring, one-touch clip included
ZS-38-3L	Lead wire with connector	3 cores, for 1 output, 2 m	ZS-38-C4L	One-touch fittings ø4 mm elbow	O-ring, one-touch clip included
ZS-38-4L	Lead wire with connector	4 cores, for 2 outputs, 2 m	ZS-38-C6L	One-touch fittings ø6 mm elbow	O-ring, one-touch clip included
ZS-38-3G	Lead wire with connector (with connector cover)	3 cores, for 1 output, 2 m	ZS-38-N7L	One-touch fittings ø1/4 inch elbow	O-ring, one-touch clip included
			-		



#### 2-Color Display High-Precision Digital Pressure Switch Series ZSE30A(F)/ISE30A

#### Set Pressure Range and Rated Pressure Range

#### Set the pressure within the rated pressure range.


The set pressure range is the range of pressure that is possible in setting.

The rated pressure range is the range of pressure that satisfies the specifications (accuracy, linearity, etc.) on the switch.

Although it is possible to set a value outside the rated pressure range, the specifications will not be guaranteed even if the value stays within the set pressure range.

0				Pressure range	Э		ZSE40
51	witch	–100 kPa	ı 0 10	0 kPa	500 kPa	1 MPa	ISE40
For vacuum	ZSE30A	–101 kPa	0 10 kPa				ZSE10 ISE10
pressure For		-105 KFa	IU KFa				ISE70
com- pound pressure	ZSE30AF	–100 kPa –105 kPa		100 kPa 105 kPa			ZSE80 ISE80
For		-100 kPa				1 MPa	ZSE□ ISE□
positive pressure	ISE30A	-105 kPa (-0.105 MPa)				1.05 MPa	ZSP
				Rated pr	essure range of switch	Set pressure range of switch	DC

#### Analog Output



					PSE
Range	Rated pressure range	Α	В	С	<u> </u>
For vacuum pressure	0.0 to –101.0 kPa	_	0	–101 kPa	IS
For compound pressure	-100.0 to 100.0 kPa	_	–100 kPa	100 kPa	ISG
For positive pressure	-0.100 to 1.000 MPa	–0.1 MPa	0	1 MPa	ZSM1

#### Functions (Refer to pages 776 and 777 for details.)


O	
Copy function	Copies the settings of the master sensor to the slave sensors.
Auto-preset function	This function is to calculate a rough set-value automatically based on the on-going operation.
Display calibration function	Evens out deviations in the displayed value.
Peak display function	Can retain the maximum pressure value displayed during measurement.
Bottom display function	Can retain the minimum pressure value displayed during measurement.
Keylock function (Selectable secret code)	The key board can be locked to prevent any incorrect function of the operation switch.
Zero-clear function	The pressure display can be set at zero when the pressure is open to the atmosphere.
Anti-chattering function	Prevents possible malfunction due to sudden fluctuations in the primary pressure by adjusting the response time.
Unit display switching function	Can convert the display value.
Power-saving mode	Reduces power consumption.
Display resolution-switch function	Converts display resolution from the normal value of 1/1000 to 1/100. It reduces the monitor to flicker.
$\textbf{kPa} \leftrightarrow \textbf{MPa} \text{ switch function}$	Converts the unit between kPa and MPa.

ZSE30 ISE30


PS ISA2

**⊘**SMC

#### Internal Circuits and Wiring Examples




Main circuit




### -C

NPN (1 output) + Analog voltage output




#### -E PNP (1 output) + Analog voltage output



\* The FUNC terminal is connected when using the copy function. (Refer to "Copy function" on page 776.)

## -D NPN (1 output) + Analog current output

本 本



Brown DC (+)

Black OUT1

White OUT2

Blue DC (-)

FUNC

Ц ра


d d

+

12 to 24

VDC

#### -F PNP (1 output) + Analog current output



ZSP

PS

ISA2


PSE

IS


ISG ZSM1





Dimensions













C4H

One-touch fitting Ø4 mm Ø5/32 inch straight






One-touch fitting ø6 mm straight




N7H

One-touch fitting ø1/4 inch straight




C4L

One-touch fitting ø4 mm ø5/32 inch elbow







One-touch fitting Ø6 mm elbow






One-touch fitting Ø1/4 inch elbow






\* When using the bracket B or C, install it by taking the dimensions of the piping part into consideration.

#### Dimensions




## D

Panel mount adapter + Front protection cover (Option unit part no.: ZS-27-D)



Lead wire with connector (Option unit part no.: ZS-38-3L)


(Option unit part no.: ZS-38-4L)




A 774


#### 2-Color Display High-Precision Digital Pressure Switch Series ZSE30A(F)/ISE30A

#### Panel fitting dimensions



#### Multiple (2 pcs. or more) vertical mounting






#### **Function Details**

#### A Copy function (F97)


The settings of the master sensor can be copied to the slave sensors, reducing setting labor and minimizing risk of mistakes in setting. Can copy to up to 10 switches simultaneously. (Maximum transmission distance 4 m)



#### B Auto-preset function (F5)

Auto-preset function, when selected in the initial setting, calculates and stores the set-value from the measured pressure. The optimum set-value is determined automatically by repeating vacuum and break with the target workpiece several times.


#### Suction Verification



#### C Display calibration function (F6)

Fine adjustment of the indicated value of the pressure sensor can be made within the range of ±5% of the read value.


(The scattering of the indicated value can be eliminated.)



Note) When the display calibration function is used, the set pressure value may change ±1 digit.

- 1) The sensors are connected by a dedicated lead wire (ZS-38-5L (for master and one slave) or ZS-38-U (for master and up to 10 slaves)). Copying is performed through a dedicated communication line.
- 2) Select the slave switch which is to be the master, and change it into a master using the buttons. (In the default setting, all switches are set as slaves.)
- 3) Press the S button of the master switch to start copying.

Wiring example when using ZS-38-U



#### Formula for Obtaining the Set-Value

P_1 or P_2	H_1 or H_2
P_1 (P_2) = A - (A-B)/4 n_1 (n_2) = B + (A-B)/4	H_1 (H_2) =   (A-B)/2

#### D Peak/Bottom value indication

This function constantly detects and updates the maximum (minimum) value and allows to hold the maximum (minimum) pressure value

When the  $(\Delta)$   $(\nabla)$  buttons are simultaneously pressed for 1 second or longer, while "holding", the held value will be reset.

#### E Keylock function

Prevents operation errors such as accidentally changing setting values

#### F Zero-clear function

This function clears and resets the zero value on the display of measured pressure

For the pressure switch with analog output, the analog output shifts according to the indication. The indicated value can be adjusted within ±7% F.S. of the pressure when ex-factory. (ZSE30AF (for compound pressure) ±3.5% F.S.)



The  $F\Box$  in () shows the function code number. Refer to the Operation Manual for the details of operation procedures and function codes.

Error name	Error code	Description	Action
Overcurrent	Erl	Load current of 80 mA or more is applied to the switch output (OUT1).	Eliminate the cause of the over current by turning
error	Erd	Load current of 80 mA or more is applied to the switch output (OUT2).	off the power supply, and then turn on it again.
Residual pressure error	Er 3	During zero-clear operation, pressure over $\pm 7\%$ F.S. is applied. (ZSE30AF (compound) $\pm 3.5\%$ F.S.) After 1 second, the mode will reset to measurement mode, $\pm 1\%$ F.S. of the zero-clear range varies between individual products.	Perform zero-clear operation again after restoring the applied pressure to an atmospheric pressure condition.
Applied	ннн	Supply pressure exceeds the maximum set pressure.	Reset applied pressure to a level within the set
pressure error	LLL	Supply pressure is below the minimum set pressure.	pressure range.
	ErO		
	Er4		
System error	Erb	Internal data error	Turn off the power supply and then turn on it again. If the failure cannot be solved, please contact SMC
oystem enter	Erl		for investigation.
	Er8		
	Er 9		

If the failure cannot be solved after the above instructions are performed, please contact SMC for investigation.


#### H Anti-chattering function (F3)

G Error indication function

A large bore cylinder or ejector consumes a large volume of air in operation and may experience a temporary drop in the supply pressure. This function prevents detection of such temporary drops in the supply pressure as an error.

#### <Principle>

This function averages pressure values measured during the response time set by the user and then compares the average pressure value with the pressure set point value to output the result on the switch.



#### Display unit switching function (F0)

Display units can be switched with this function.

Display unit	PA		GF	bAr	PSi	inH	mmH
Min. unit setting	kPa	MPa*	kgf/cm <sup>2</sup>	bar	psi	inHg	mmHg
ZSE30A (Vacuum pressure)	0.1	0.001	0.001	0.001	0.01	0.1	1
ZSE30AF (Compound pressure)	0.1	0.001	0.001	0.001	0.01	0.1	1
ISE30A (Positive pressure)	1	0.001	0.01	0.01	0.1		

\* The ZSE30A (vacuum pressure) and ZSE30AF (compound pressure) will have different setting and display resolution when the unit is set to MPa.

#### J Power-saving mode (F7)

Power-saving mode can be selected.

It shifts to the power-saving mode without button operation for 30 seconds. It is set to the normal mode (Power-saving mode is OFF.) when ex-factory. (Decimal points and operation indicator light (only when the switch output is turned ON.) blink in the power-saving mode.)

Available response time settings

20 ms, 100 ms, 500 ms, 1000 ms, 2000 ms

#### K Setting of secret code (F8)

Users can select whether a secret code must be entered to release key lock. At the time of shipment from the factory, it is set such that the secret code is not required.

PSE IS

ISG

ZSM1




Please contact SMC for detailed dimensions, specifications, and lead times.


## 1 M12 4-pin Pre-wired Connector (Lead wire length 100 mm)



Made t Order



Option cable ZS-38-4GM12



# 2 White 1 Brown

3 4

4 Black

Pin no.	Pin description
1	DC (+)
2	OUT (2)
3	DC (-)
4	OUT (1)

3 Blue