



E/P Pressure Regulator

PROFINET Communication

Electro-Pneumatic Regulator

Electronic Vacuum Regulator



Features

- DIP switch for default device name
- Integrated web server
- Fast Startup
- Setpoint and feedback in engineering units
- Integrated 2-port ethernet switch
- Adjustable gain & sensitivity
- Diagnostic Alarms
- Over and under voltage indication
- Daisy chain/PoE (up to 5 units)
- Hold set pressure on lost connection
- Shared Device I/O
- I & M 0-3 Data Supported

How to Order

ITV 2030-SPN- 2-DUX02357-

○ Body Size

1010	2010	3010
1030	2030	3030
1050	2050	3050
	2090	

○ Port Size

1	1/8 (1000)
2	1/4 (1000, 2000) *
3	3/8 (2000, 3000) *
4	1/2 (3000)

* Note: 2090 available with 1/4 port only.

○ Protocol

SPN	PROFINET
-----	----------

○ Thread Type

Nil	Rc
N	NPT

○ Made to Order

Nil	Standard Mounting
X26	Manifold Mounting *
X400	Gage Port **

* Note: -X26 is available only for 2010, 2030, and 2050 sizes with 1/4 Rc only.

** Note: 2030, 2050 with 3/8 Rc port only.




Specifications

Model	1010	1030	1050	2090
	2010	2030	2050	
	3010	3030	3050	
Min. Supply Pressure (psi)	Set Pressure +14.5			-1.9
Max. supply pressure (psi)	29	145		-14.6
Set Pressure Range (psi)	0.7 to 14.5	0.7 to 72.5	0.7 to 130.5	-0.2 to -11.6
Power Supply Voltage	24VDC ± 10%			
Current Consumption	0.15A or less			
Input & Output Signal	12 bit resolution			
Linearity	Within ± 1% (Full Span)			
Hysteresis	Within ± 0.5% (Full Span)			
Repeatability	Within ± 0.5% (Full Span)			
Sensitivity	Within ± 0.2% (Full Span)			
Temperature Characteristics	Within ± 0.12% (Full Span) / °C			
Ambient & Fluid Temperature	0 to 50°C (32 to 122 °F) (No condensation)			
Enclosure Rating	IP65			
Weight	Size 1000	12.3 oz.		
	Size 2000	15.9 oz.		
	Size 3000	26.5 oz.		
Compliance	CE, UL, PROFINET Conformance Class C, Netload Class III			

How to Order

IITV20-N 2-3-2050-SPN-DUX02357

Port size	Number of Stations	Pressure	Protocol
2 1/4 (1000, 2000)	2 Station	1 0.1 MPa	SPN PROFINET
3 3/8 (2000, 3000)	3 Station	3 0.5 MPa	
	4 Station	5 0.9 MPa	
Thread Type	5 Station		
Nil Rc(PT)	6 Station		
N NPT	7 Station		
F G	8 Station		



Porting


- Supply: 1/2
- Out: 1/4 or 3/8 (per order)
- Thread Type: Rc, NPT or NPTF (per order)
- Solenoid Valve Exhaust: M5x0.8 port

Dimensions

- L** Length (mm): 52N + 36 (N = # of stations)
- H** Height (mm): 173.2
- W** Width (mm): 70

Mounting Screws


- 4X M5x0.8 SHCS



Specifications

Voltage	24 VDC ± 10%
Input Signal (Digital)	12 bit
Output Signal (Digital)	12 bit
Linearity	Within ± 1% Full Span
Hysteresis	Within ± 0.5% Full Span
Repeatability	Within ± 0.5% Full Span
Sensitivity	Within ± 0.2% Full Span
Enclosure	IP 65*

* Note: To meet IP rating, liquids must not have access to solenoid valve exhaust port



ZR-POD