



Pneumatics for Outdoor Applications

UV Resistant Components



Water Removal Units



*All Metal or SUS 316
Filter/Regulator
Combo Unit*



*Tie Rod Cylinders
with Viton™ Seals*



*SUS 2-way
Solenoid Valve*



*Jet Pulse
Dust Collector Valves*



*SUS Floating Joint
with Silicone Cover*



Fittings & Tubing



*SUS Lockout-
Tagout (LOTO)*




*All Metal
Speed Controller*

www.smcusa.com
sales@smcusa.com



Air Shocker Series XT316



Specifications

Model	XT316-30B	XT316-40B	XT316-63B	XT316-80B	XT316-100B
Bore size	Ø30	Ø40	Ø63	Ø80	Ø100
Operating pressure MPa (kgf/cm ²)	0.4 - 0.6 (4.1 - 6.1)				
Impact cycle (cycles/min)	MAX. 15				
Air consumption (ℓ/cycles)	0.33	0.75	1.29	1.91	4
(Note 1) Impact energy (kgm)	0.05 - 0.07	0.17 - 0.31	0.45 - 0.75	1.0 - 1.8	2.2 - 4.0
(Note 2) Weight (kg)	2.5	4.4	11.2	15	33.5
Ambient and fluid temperature	32 - 140 °F (0 - 60 °C)				
Port size (PT)	1/8				3/8
Lubrication	Not lubricated				

(Note 1) Change in potential energy applied to a pendulum
(Note 2) Total weight including the mounting base and bolts

U.S. & Canadian Sales Offices

WEST

Austin
Dallas
Denver
Los Angeles
Phoenix
Portland
San Jose

CENTRAL


Chicago
Cincinnati
Cleveland
Detroit
Des Moines
Grand Rapids
Indianapolis
Kansas City
Milwaukee
Minneapolis
St. Louis

EAST

Albany
Atlanta
Birmingham
Boston
Charlotte
Knoxville
Nashville
New Jersey
Rochester
Tampa

CANADA

Vancouver
Toronto
Windsor
Montreal



- Sales Branches
- Regional Distribution Centers
- Central warehouse

ZR-RRD-3M