


Linear Low Density Industrial Polyethylene Tubing



Construction:

- Linear low density polyethylene tubing

Applications:

- Transfer of air and liquids in industrial applications
- Chemical transfer lines
- Humidifier fill lines
- Drain lines
- Instrument air lines

Features:

- Economical and lightweight
- LLDPE resin provides excellent environmental stress crack resistance
- Six colors
- Excellent resistance to solvents
- Excellent chemical resistance
- Resistant to sunlight and other forms of ultra-violet radiation (black only)
- FDA Type 1, Class A, category 4 polyethylene resin (complies with FDA 21 CFR 177.1520 for olefin polymers (par (c) 3.2a)). Not NSF Certified

Weight

Inch Sizes			Metric Sizes		
OD	Package Length (in)	Package Weight (lbs)	OD	Package Length (in)	Package Weight (lbs)
1/4"	100 <input type="radio"/>	1.2	4mm	100 <input type="radio"/>	0.6
	500 <input type="radio"/>	6		500 <input type="radio"/>	3
	1,000 <input type="radio"/>	12		1,000 <input type="radio"/>	6
3/8"	100 <input type="radio"/>	2.3	6mm	100 <input type="radio"/>	1.1
	500 <input type="radio"/>	11.5		500 <input type="radio"/>	5.5
	1,000 <input type="radio"/>	23		1,000 <input type="radio"/>	11
1/2"	100 <input type="radio"/>	3.4	8mm	100 <input type="radio"/>	1.5
	500 <input type="radio"/>	17		500 <input type="radio"/>	7.5
	1,000 <input type="radio"/>	34		1,000 <input type="radio"/>	15
5/8"	100 <input type="radio"/>	5	10mm	100 <input type="radio"/>	2.1
	500 <input type="radio"/>	25		500 <input type="radio"/>	10.5
				1,000 <input type="radio"/>	21
			12mm	100 <input type="radio"/>	2.5
				500 <input type="radio"/>	13

Bagged Reel

Specifications - Inch

Nominal OD (in)	Nominal ID (in)	Nominal Wall (in)	Bend Radius (in)	Working Pressure @ 70°F (20°C) (in)	Bend Radius (in)	Service Temp Range	Hardness
0.25	0.17	0.04	1.25	150	450	-50°~ +140°F (-45°~ 60°C)	Shore A 98A, Shore D 55D
0.375	0.25	0.063	2	150	450		
0.5	0.375	0.063	2.5	125	375		
0.625	0.5	0.063	3	100	300		

Applicable SMC Fitting Series: KQ2, KQG2, KQB2, KG, KB, KS, KX, DMK, KDM
Note: Fittings are not FDA/NSF compliant

Specifications - Metric

Nominal OD (mm)	Nominal ID (mm)	Nominal Wall (mm)	Bend Radius (mm)	Working Pressure @ 70°F (20°C) (psi)	3:1 Burst Pressure (psi)*	Service Temp Range	Hardness
4	2.5	0.75	25.4	180	540	-50°~ +140°F (-45°~ 60°C)	Shore A 98A, Shore D 55D
6	4	1	31.8	150	450		
8	6	1	38	150	450		
10	8	1	51	125	375		
12	9	1.5	63.5	100	300		


Applicable SMC Fitting Series: KQ2, KQG2, KQB2, KG, KB, KS, KX, DMK, KDM
Note: Fittings are not FDA/NSF compliant

General Specifications

Operating Fluid	Air, Water, Compatible chemicals
Operating Temperature	-50 to +140°F (-45 to +60°C)
Material	Linear Low density polyethylene
Hardness	Shore A 98A, Shore D 55D

Note: Working pressure decreases as temperature increases. Pressure ratings can only be obtained with proper coupling procedures. Because we continually examine ways to improve our products, we reserve the right to alter specifications without prior notice.

How To Order



Note: 4mm tubing is suitable for use with 5/32" SMC One-touch fittings as is 8mm tubing and 5/16" fittings. 4, 6, 8, 10 and 12mm are commonly available in black, blue and natural only, other colors are special order.

PEAPP Series

www.smcusa.com

www.smcworld.com

NF417B
(NF-36-03-C02-11)



Automation - Controls - Process



Leading global pneumatics and industrial automation components manufacturer dedicated to sustainable factory automation.

Serving the industries of semiconductor, food & packaging, life science, automotive, machine tool, process, natural resource, and general needs for automation, controls, and process.

Global Presence

- 532 Sales Offices in 83 Countries
- Production Facilities in 29 Countries & Regions
- Technical Centers in Japan, the U.S., Europe, & China

Extensive Product Line

- 12,000 Basic Models with over 700,000 Variations
 - Actuators
 - Sensors & Switches
 - Connectors
 - Process Gas
 - Electrical Products
 - Temperature Control
 - Vacuum
 - Valves
 - Air Preparation
 - Static Control
 - Chemical Handling
 - Specialty Products

North American Support

- 30 North American Locations
- Configure, Validate, & Download 3D & 2D Models from www.smcusa.com/products
- 2.6 Million sqft North American Headquarters of Engineering, Production, Central Distribution & Administration

Sales Offices

WEST


- Austin
- Dallas
- Denver
- El Paso
- Los Angeles
- Phoenix
- Portland
- San Jose

CENTRAL

- Chicago
- Cincinnati
- Cleveland
- Detroit
- Des Moines
- Grand Rapids
- Indianapolis
- Kansas City
- Milwaukee
- Minneapolis
- St. Louis

EAST

- Atlanta
- Birmingham
- Boston
- Charlotte
- Knoxville
- Nashville
- New Jersey
- Rochester
- Tampa



● Sales Offices
 Production/Distribution Center



SMC Corporation of America
 10100 SMC Blvd., Noblesville, IN 46060
www.smcusa.com

International inquiries: www.smcworld.com

(800) SMC.SMC1 (762-7621)
 email: sales@smcusa.com

SMC Automation (Canada) Ltd.
www.smcautomation.ca

© 2023 SMC Corporation of America, All Rights Reserved.
 All reasonable efforts to ensure the accuracy of the information detailed in this catalog were made at the time of publishing. However, SMC can in no way warrant the information herein contained as specifications are subject to change without notice.