
3 Port Solenoid Valve Rubber Seal

Series SY100

Low power consumption: 0.5W (Standard, Without light)

(Current draw: 21mA at 24V DC)

*Large flow capacity style:0.75W (Current draw: 31mA at 24V DC)




Body width: 10mm

7.85 Ndmin (Standard style)
11.78 Ndmin (Large flow capacity style)

Exceedingly long life

100 million cycles (By SMC life test data)



Vacuum Applications Possible

Can be used up to -100kPa


Copper free

No copper used for sections in contact with fluids.

Bright colour tone and "state of the art" design

A bright grey concept has been adopted for this product to complement the surrounding operational environment.

SY100/ Application example (Pneumatic symbols shown are typical examples.)



Characteristics values indicated in this catalog are not guaranteed values but typical ones.



⚠Precautions


⚠ Warning


Operation of Manual Override

Make sure that there is no danger, since manual override operation can make any connected equipment operate.


■Non-locking push style [Standard style] ■Locking slotted style [B] Turn in the direction of arrow.


Press in the direction of the arrow.





■Push-locking slotted style [D] ■Push-locking lever style [E]





Pressing makes the valve operate. The valve can be locked in the manual override position by turning it to the direction that the arrow shows while keeping it pressed. If it is not turned, it can be used as a non-locking push style.

⚠ Caution


Gently operate locking manual override styles B, D using small screwdriver. [Torque: 0.1Nm or less]

⚠ Caution

How to Use Plug Connector


①Connection/Disconnection of connector

- •Connection: Push the connector straight onto the pins of the solenoid, making sure the lip of the lever securely "locks" into the groove of the solenoid cover.
- Disconnecton: Press the lever against the connector housing and pull it outward from the solenoid.



2 Crimping connection of lead wire and socket

Strip 3.2 to 3.7mm of the lead wire ends, insert each stripped wire into a socket and crimp contact it using special crimping tool. Be careful that the outer insulation of the lead wires does not interfere with the socket contact part. Use exclusive crimping tool for crimping. (Contact SMC for special crimping tool.)




3 Connection/Disconnection of socket with lead wire

Connection

Insert lead wire and crimped socket into square holes (indicated as A, B, COM) of connector. Press the socket in fully until the hook of the socket locks into the groove of the connector housing. Confirm the locked position by lightly pulling on the lead wire.

Disconnection


To remove the socket from the connector, pull out lead wire while depressing the hook of the socket with a fine screw driver (≅1mm). If the socket is to be re-used, reposition the hook again.



Plug Connector Lead Wire Length

Standard length is 300mm, but the following lengths are also available.

How to Order Connector Assembly



How to Order

To order a valve with lead wire length of other than 300mm, indicate part numbers of the valve without connector and the required connector ass'y separately. Example: 2000mm lead wire length

For DC SY114-5LO SY100-30-4A-20

| Lead wire lengtl | | | | | | | | | |
|-------------------------|--------|--|--|--|--|--|--|--|--|
| _ | 300mm | | | | | | | | |
| 6 | 600mm | | | | | | | | |
| 10 | 1000mm | | | | | | | | |
| 15 | 1500mm | | | | | | | | |
| 20 | 2000mm | | | | | | | | |
| 25 | 2500mm | | | | | | | | |
| 30 | 3000mm | | | | | | | | |
| 50 | 5000mm | | | | | | | | |


Surge Voltage Suppressor

<DC>

Grommet, L and M plug connector


■Standard style (With polarity) With surge voltage suppressor






Indicator light and surge voltage suppressor (□Z)







■Non-polar style







■Indicator light and surge voltage suppressor ("□U")



 Please connect correctly the lead wires to ⊕ (positive) and ⊕ (negative) indications on the connector.

For non-polar style, the lead wires can be connected to either one.

- · For DC voltages other than 12, 24V DC, incorrect wiring will cause damage to the surge voltage suppressor circuit. (Wrong polarity will cause trouble.)
- Solenoids, whose lead wires have been pre-wired: positive side red and negative side black.

⚠ Caution


Since there is some residual voltage according to the protection device and rated voltage in case of voltage surge suppressor by zener diode, pay attention to the surge protection on the controller side. (Diode residual voltage: 1V)

Connector Assembly with Protective Cover


Connector assembly with protective cover enhances dust protection.

- Effective in preventing possible short circuit problems due to contaminants in contact with connector section.
- Cover material is chloroprene rubber which has excellent weatherability and electric insulation properties. However, be careful not to allow contact with cutting oil.
- •Round cord provides neat appearance.

How to Order



Connector Assembly with Cover/Dimension



●How to Order

Indicate part number of connector assembly with cover in addition to the solenoid valve part number without connector of the plug connector.

<Example 1> Lead wire length: 2000mm

SY114-5LOZ-M3-Q SY100-68-A-20

<Example 2> Lead wire length: 300mm (Standard)

SY114-5LPZ-M3-Q

Symbol of connector assembly with cover

No part numbers of connector assembly with cover are needed to be indicated in this case.

3 Port Direct Operated Rubber Seal

Series SY100

Model




Body ported



Base mounted

JIS Symbol





| | | | Operating | Vacuum appl | ication (MPa) | | Weigh | t (g) (2) |
|-----------|----------------------|---------------------------|-------------------------|----------------|----------------|----------------------------------|--------------------------------|--------------------------------|
| Actuation | Model | Style | pressure range (MPa) | P port | R port | Effective area (mm²) (Nt/min) | Grommet style | L, M Plug connector |
| N.C. | SY11 ³ | Standard | 0 to 0.7 | -100kPa to 0.6 | -100kPa to 0 | 0.14 (7.85) | | |
| N.C. | SY11 ³ A | Large flow capacity | 0 to 0.7 | -100kPa to 0.6 | -100kPa to 0 | | SY1□3 (A): 13 SY1□4 (A): 24 | SY1□3 (A): 15 SY1□4 (A): 26 |
| N.O. | SY123 ⁽¹⁾ | Standard | 0 to 0.7 | -100kPa to 0 | -100kPa to 0.6 | 0.14 (7.85) | (Without sub-plate 12) | (Without sub-plate 14) |
| N.O. | SY12 ³ A | Large flow capacity | 0 to 0.7 | -100kPa to 0 | -100kPa to 0.6 | 0.22 (11.78) | | |

Note 1) SY123/SY124 and SY123/SY124 A: Supply pressure to 1(R) port and exhaust air from 3(P) port. Note 2) Value for DC.

Specifications

| Fluid | Air | | | |
|--|---|--|--|--|
| Ambient and fluid temperature (°C) | Max. 50°C | | | |
| Response time (ms) (1) | 10ms or less | | | |
| Max. operating frequency (Hz) | 20 | | | |
| Manual override | Non-locking push, Locking slotted, Push-locking slotted, Push-locking lever | | | |
| Lubrication | Not requited | | | |
| Mounting position | Free | | | |
| Impact/Vibration resistance (m/s2) (2) | 150/30 | | | |
| Enclosure | Dust-proof | | | |

Note 1) According to dynamic performance test JIS B8374-1981 (Coil temperature 20°C, at rated voltage, without surge suppressor.)

Note 2) Impact resistance: No malfunction from tests using drop impact tester, to axis and right angle direction of main valve and armature, each one time when energized and de-energized. (Value in the inital stage)

Vibration resistance: No malfunction from tests with 8.3~2000Hz 1 sweep, to axis and right angle direction of main valve and armature, each one time when energized and de-enegized. (Value in the initial stage.)


Solenoid Specifications

| Series | | SY1 13 24 | SY1 ¹³ A | | | |
|------------------------|------------------------------|---|--------------------------|--|--|--|
| Electrical entry | | Grommet (G), (H), L plug connector (L), M plug connector (M) | | | | |
| Coil rated voltage (V) | DC | 24, 12, 6, 5, 3 | | | | |
| Allowable voltage | | −10 to +10% | | | | |
| Power consumption (W) | Power consumption (W) (1) DC | | 0.75W (With light: 0.8W) | | | |
| Surge voltage suppres | sor | Diode | | | | |
| Indicator light | · | LED | | | | |


⁽¹⁾ At rated voltage



How to Order





How to Order



Construction

SY114, SY114A






Component Parts

| No. | Description | Material | Notes |
|-----|----------------|---------------------|-------|
| 1 | Body | Resin | Gray |
| 2 | Cover | Resin | Gray |
| 3 | Push rod | Resin | _ |
| 4 | Armature ass'y | NBR/Stainless steel | _ |
| (5) | Core | Stainless steel | _ |
| 6 | Exhaust poppet | NBR | _ |
| 7 | Return spring | Stainless steel | _ |
| 8 | Poppet spring | Stainless steel | _ |
| 9 | Coil ass'y | _ | _ |

Replacement Parts


| Ī | No. | Description | Part No. | Material |
|---|-----|-------------|------------|---------------|
| | 10 | Sub-plate | SY100-74-1 | Zinc die cast |
| | 11) | Gasket | VJ100-6-8 | NBR |


How to Order Connector Assembly





Body Ported

Grommet (G), (H): SY1 1/2 (A)-□ H □ □-PM3 (-F) -Q










Other dimensions are same as grommet style.


M plug connector (M): SY1¹₂3 (A)-□M□□-PM3 (-F)-Q




Other dimensions are same as grommet style.

Base Mounted (With Sub-plate)

Grommet (G), (H): SY1 ¹₂4 (A)-□ ^G_H□□-M3-Q





Series **SY100 Manifold**



Specifications

| Туре | | 30 ⁽⁴⁾ | S41 | | | |
|------------------------------------|--------------------------------|----------------------------|------------------|-------------|--|--|
| Manifold style | | Single base style, B mount | | | | |
| P (SUP)/R (EXH) | style | Comr | non SUP/Common E | XH | | |
| Valve stations | alve stations 2 to 10 stations | | | | | |
| A porting | Location | Va | Base | | | |
| A porting | Direction | To | Top Side | | | |
| Port size | P, R port | | | | | |
| Port Size | A port | М | M3 , M5 | | | |
| | SY1□3 | 0.14 (| (7.85) | _ | | |
| Valve effective | SY1□3A | 0.21 (| 11.78) | _ | | |
| area mm² (N∉min) ⁽¹⁾ | SY1□4 | _ | - | 0.13 (6.87) | | |
| | SY1□4A | _ | 0.2 (10.8) | | | |



Note 1) When mounted on manifold base


Note 2) SY114 (A) and SY124 (A) can not be mounted on the same manifold.

Note 3) Supply to R port and exhaust from P port for SY124 (A).

Note 4) 30 Type is applicable only for SY113 and SY113A. Piping to exhaust port is not possible.

How to Order Manifold Base (Ordering Example)

Example




SS3Y1-S41-05-M5-Q.....1set (S41 type 5-station manifold part number)

SY100-77-1A······1set (Blank plate assembly part number)

SY114-5GZ-Q······4set (Valve)


List part numbers of the installed valve and option in required station location separately under manifold part number.






Common SUP/Common EXH

30 Type




How to Order



Applicable solenoid valve (1) SY113-□□□-M3-Q


SY113A-□□□□-M3-Q Applicable blank plate

assembly SY100-77-1A



31 Type R port P port

How to Order



Applicable solenoid valve (1)

SY113-□□□-M3-Q

SY113A-□□□□-M3-Q

SY123-□□□-M3-Q SY123A-□□□□-M3-Q


Applicable blank plate

assembly


SY100-77-1A



S41 Type



How to Order



Applicable solenoid valve (1)

SY114-□□□□-Q

SY114A-□□□□-Q

SY124-□□□□-Q SY124A-□□□□-Q

Applicable blank plate assenbly

SY100-77-1A







Protective class class III (Mark: 1)

Combination with Solenoid Valve and Gasket Manifold Base

Body ported




Base mounted



Parts No.: SY100-77-1A

Blank Plate Assembly



Applicable base

Sub-plate (For body ported style) SS3Y1-30 type | Manifold base SS3Y1-31 type

Applicable base

Sub-plate

SS3Y1-S41 type manifold base

Applicable base


Sub-plate SS3Y1-30 type


SS3Y1-31 type Manifold base

SS3Y1-S41 type

30 Type Manifold: Top Ported/SS3Y1-30-Station -F-Q

Grommet (G), (H)









No bracket is assembled prior to delivery. Mount one to the appropriate position. (Attach two brackets if more than five stations.)


L plug connector (L)





| Station | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 |
|---------|------|----|------|----|------|----|------|----|-------|
| | 20.5 | 31 | 41.5 | 52 | 62.5 | 73 | 83.5 | 94 | 104.5 |

M plug connector (M)







Other dimensions are same as grommet style.




31 Type Manifold: Top Ported/SS3Y1-31-Station-Q


Grommet (G), (H)








L plug connector (L)






Other dimensions are same as grommet style.

M plug connector (M)






| Station | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 |
|----------------|------|----|------|----|------|----|------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| L ₁ | 33.5 | 44 | 54.5 | 65 | 75.5 | 86 | 96.5 | 107 | 117.5 | 128 | 138.5 | 149 | 159.5 | 170 | 180.5 | 191 | 201.5 | 212 | 222.5 |
| 12 | 27.5 | 38 | 48.5 | 59 | 69.5 | 80 | 90.5 | 101 | 111.5 | 122 | 132.5 | 143 | 153.5 | 164 | 174.5 | 185 | 195.5 | 206 | 216.5 |




S41 Type Manifold: Side Ported/SS3Y1-S41-Station - M3/M5-Q


Grommet (G), (H)


In case of M5






In case of M3






L plug connector (L)




Other dimensions are same as grommet style.

M plug connector (M)



Other dimensions are same as grommet style.





Series SY Made to Order

(Contact SMC for further specifications, dimensions and delivery lead time.)



Power Saver


Power consumption is decreased by 1/3 of standard product by reducing electrical power at holding. (This is effective when energizing time exceeds 62ms at rated voltage of 24V DC.)

Specifications

| Series | | SY1 ¹³ ₄ T | SY1 ¹³ AT | | | |
|--------------------|---------|----------------------------------|----------------------|--|--|--|
| Coil rated voltage | e (V) | 24, 12V DC | | | | |
| Power | Inrush | 0.55 | 0.8 | | | |
| consumption (W) | Holding | 0.22 | 0.3 | | | |


Specifications except those mentioned above are same at standard.

How to Order




Operating principle

Power consumption at holding is decreased with the below indicated circuit, for energy savings. Refer to electrical power wave form shown below.



<Electrical wave form of power saving style, SY1¹³₂₄T>



<Electrical wave from of power saving style, SY1¹³₂₄AT>

