Electro-pneumatic Proportional Valve

Series VEF/VEP

Electro-pneumatic proportional valve: Flow type (VEF)

Controls the flow rate steplessly according to current. (It is a 2/3 port valve that has an electrical throttle valve function.) A model that is suitable for operating conditions, such as the number of ports or maximum effective area, can be selected.

Electro-pneumatic proportional valve: Pressure type (VEP)

Controls the pressure steplessly according to current. Also, because the effective fully opened area of the exhaust side is identical due to its construction, this valve provides a large exhaust capacity and can be used as a relief valve. (It is a 3 port valve that has an electrical pressure reducing valve function.)




Specifications

Model		Flow type		Pressu	ire type
Item	VEF2121 VEF3121	VEF2121	VEF2141 VEF3141	VEP3121	VEP3141
Port size Rc	1/4, 3/8	1/4, 3/8, 1/2	3/8, 1/2, 3/4	1/4, 3/8	3/8, 1/2, 3/4
Fluid			Air (Inert gas)	
Proof pressure			1.5 MPa		
Maximum operating pressure			1.0 MPa		
Ambient and fluid temperature		0 to 50°C	(With no cor	ndensation)	
Response time	0.03 s	or less	0.05 s or less	0.03 s or less	0.05 s or less
Hysteresis			3% F.S.		
Repeatability			3% F.S.		
Sensitivity			0.5% F.S.		
Linearity				3% F.S.	or less
Lubrication	Not require	d (Use turbin	e oil Class 1,	ISO VG32, if	lubricated.)
Weight (kg)	0.9	1.0	1.4	0.9	1.4

Proportional Solenoid Specifications

Proportional solenoid recognition symbol	1 (Applicable power amplifier: VEA25□)		
Applicable power amplifier	VEA25□		
Max. current	1 A		
Coil resistance	13 Ω (20°C)		
Rated power consumption	13 W (20°C, with maximum current)		
Coil insulation type	Class H or equivalent (180°C)		
Max. temperature	140°C (With maximum current)		
Electrical entry	DIN terminal		

How to Order



2.5

25

4

1

4

<f< th=""><th>ressure</th><th>e type:</th><th>></th><th></th><th></th><th></th><th></th><th></th></f<>	ressure	e type:	>					
V	EP31	4	1-1	0	3			
			J		+	Threa	d type	
		cable p	ower			Nil	Rc	
	ampli	fier		٦		F	G	
	Symbol	Power	amplifier			N	NPT	
	1	VE	\25 □			T	NPTF	
							٦	
			O4ll	.				
, 	Body si		Standard characte				Port size	ze
	Body size Standard characteristics			cs	Symbol	Port size		
	Symbol	Symbol	Set pressu	ire rang	e (MPa)	Symbol	FUIT SI	Z U
		1	0.05 to 0.65 MPa		Nil	Withou		
_	2					02	sub-pla	
		_						
		2	0.1 to 0	.9 MPa		03	Rc 3/	
_		2	0.1 to 0	.9 MPa		03	Rc 3/	8
-	4	1		.9 MPa o 0.15 M	Pa		Rc 3/ Rc 1/	8 8 2
-	4	_			Pa	03	Rc 3/	8 8 2

JIS Symbol Flow

F.R.L.

AV

AU

AF

AR

IR

VEX

AMR

ITV

IC

VBA

VE□

VY1

PPA


AL

G

Series VEF/VEP


Application Example

Controlling pressure for die press cushion



(Imagine air type shock absorber)

Controlling welding pressure of welding machine electrode



Controlling rotation of air motor

Electro-pneumatic proportional valve

Flow type (3 port)

Controlling multispeed of cylinder


Surge absorber

Power


amplifier

Control

circuit



Controlling pressure of low pressure die-casting



Previous Type VE^P □□□0, VEA1□□

⚠ Caution

 $VE_E^P \square \square \square 0$ must be used in conjunction with the power amplifier $VEA1 \square \square$.

An old VEA1 \square cannot be used in combination with the current VE $_{E}^{P}\square\square\square$ 1.

How to Use DIN Terminal

⚠ Caution

Wiring procedure

- 1. Loosen the retaining screw and pull the connector from the pin plug.
- Make sure to remove the retaining screw, insert the tip of a flat head screwdriver into the groove below the terminal block and pry it up to separate the terminal cover from the terminal block.
- Securely connect the wires to the specified terminals in accordance with the wiring procedure.

Wiring



Terminal block Connection 3 is not used for terminal 1 and 2. * Coil has no polarity.

Pin plug shape

Applicable cable (Heavy-duty cable)

0.75 mm², 1.25 mm²/2 core, 3 core (O.D. \emptyset 6.8 to \emptyset 11.5) based on JIS C 3312 and C 3322

Outlet changing procedure

To change the wire outlet, first separate the terminal cover from the terminal block.

Then, reinstall the terminal cover in the desired direction (in 90° increments).

⚠ Precautions

Be sure to read before handling.
Refer to pages 14-21-3 to 14-21-4
for Safety Instructions and
Common Precautions.

⚠ Caution

1. Air supply

Poor quality air could increase the spool's sliding resistance, while preventing it from attaining its specified characteristics. Use compressor oil with a minimal generation of oxidants and install a mist separator (SMC's AM series). Refer to page 14-14-2.

2. Mounting

- Vibrations are transmitted to the valve by the proportional solenoid's dither. If it is necessary to prevent the transmission of vibrations, insert vibration isolating rubber material.
- Thoroughly flush the pipe to completely eliminate any dust or scales from the pipe inside.
- Install a silencer (AN series) on the exhaust port.
- Be careful with the molded coil because it generates heat while current is applied to it

3. Lubrication

This product can be used without lubrication. But if lubricated, use turbin oil Class 1, ISO VG32 (with no additive). It is impossible to use spindle oil, machine oil, or grease.

4. Manual operation


To check the operation of the valve without applying a current, remove the lock nut and use a screwdriver or the like to press the tip of the core. After checking the operation, reinstall the rubber cap in its original position.





Electro-pneumatic Proportional Valve Series VEF/VEP


Diagram of Working Principle


The spool controls the sleeve's opening through the balance between the proportional solenoid's pulling force (F1) and the spring's reaction force (F2). The spool moves in accordance with the amperage that is applied to the proportional solenoid, thus controlling the flow rate.




















F.R.L.

AV

AU

AF

AR

IR

VEX

AMR

ITV

IC

VBA

 $\mathsf{VE}\square$

VY1

G

PPA


AL


Series VEF/VEP


Pressure Type: VEP

Diagram of Working Principle

The control opening becomes closed when the solenoid's pulling force (F1) balances with the force (F2), which is created by the outlet pressure (P2) that passes through the feedback passage and acts on the spool surface. As a result, the outlet pressure (P2) is established.









Current-Pressure Characteristics

The horizontal axis of the characteristics represents the output amperage of the power amplifier VEA25□. (If NULL and GAIN are in the shipping condition, 0 to 1 A can be viewed by substituting them with command signals 0 to 5 V.)




Pressure Characteristics JIS B 8372 (In accordance with air regulator)


VEP3121-1




VEP3121-2





VEP3141-1



Flow Characteristics









Electro-pneumatic Proportional Valve Series VEF/VEP

Construction


Flow type: VEF2121 (2 port) VEF3121 (3 port) Pressure type: VEP3121 (3 port)



Flow type: VEF2131 (2 port)



Flow type: VEF2141 (2 port) VEF3141 (3 port) Pressure type: VEP3141 (3 port)



Component Parts

	inpondit i aito						
No.	Description	Material	Note	No.	Description	Material	Note
1	Body	Aluminum alloy	Metallic painted	11)	Gasket	NBR	_
2	Sub-plate	Aluminum alloy	Metallic painted	12	Spring	Stainless steel/Piano wire	_
3	Spool	Special stainless steel	_	13	Spring seat	Brass	_
4	Sleeve	Special stainless steel	_	14)	O-ring	NBR	_
5	Mold coil	_	_	15	O-ring	NBR	_
6	Solenoid cap assembly	Aluminum alloy	Metallic painted	16	O-ring	NBR	_
7	Movable core assembly	_	_	17)	Hex. socket head cap screw	Chromium-molybdenum	_
8	End cover	Aluminum alloy	_	18	Hex. socket head cap screw	Chromium-molybdenum	_
9	Bush	Resin	_	19	Hex. socket head cap screw	Chromium-molybdenum	_
(10)	Set bushing	Brass	_	20	Lock nut	NBR	_

F.R.L.

ΑV AU

AF

AR

IR

VEX

AMR

ITV

IC

VBA $\mathsf{VE}\square$

VY1

G

PPA

AL

Series VEF/VEP

