

# **5 Port Pilot Operated Solenoid Valve** Metal Seal, Body Ported Series VFS1000

#### Model

		Mc	del				Flow char			(1)				
Τv	ype of ctuation			Dentaling	1 —	$\rightarrow$ 4/2 (P $\rightarrow$ A/	/B)	4/2 →	5/3 (A/B $\rightarrow$ F	R1/R2)	operating	Response	Weight (3)	•
acti		Plug-in	Non plug-in	Port size	C [dm³/(s·bar)]	b	Cv	C [dm³/(s·bar)]	b	Cv	cycle (cpm)	time (ms)	(kg)	
sition	Single	VFS1120	VFS1130	1⁄8	1.7	0.22	0.38	1.8	0.19	0.40	1200	15 or less	0.18	
2 pos	Double	VFS1220	VFS1230	1⁄8	1.7	0.22	0.39	1.8	0.19	0.40	1200	13 or less	0.26	1
Ľ	Closed center	VFS1320	VFS1330	1⁄8	1.6	0.20	0.37	1.8	0.20	0.41	600	20 or less	0.27	١
3 positio	Exhaust center	VFS1420	VFS1430	1⁄8	1.7	0.18	0.38	1.9	0.19	0.44	600	20 or less	0.27	١
	Pressure center	VFS1520	VFS1530	1⁄8	1.7	0.24	0.40	1.6	0.18	0.37	600	20 or less	0.27	

Note 1) Based on JIS B 8375 (once per 30 days) for the minimum operating frequency.

Note 2) According to JIS B 8375-1981. (The value at supply pressure 0.5 MPa.)

Note 3) In the case of grommet type

Note 4) "Note 1)" and "Note 2)" are with controlled clean air.

### Compact yet provides a large flow capacity C: 1.8 dm<sup>3</sup>/(s·bar)

Low power consumption: 1.8 W DC



JIS Symbol



### Sta

ano	dard Specifications	5			
	Fluid		Air/Inert gas		
	Maximum operating pressu	ıre	1.0 MPa		
	Min operating prossure	2 position	0.1 MPa		
	Min. Operating pressure	3 position	0.15 MPa		
5	Proof pressure		1.5 MPa		
עמועם אחמי	Ambient and fluid tempera	ture	-10 to 60°C <sup>(1)</sup>		
	Lubrication		Non-lube (2)		
	Pilot valve manual override	)	Non-locking push type (Flush)		
	Shock/Vibration resistance		150/50 m/s <sup>2 (3)</sup>		
	Enclosure		Dustproof (Degrees of protection 0) (4)		
2	Coil rated voltage		100, 200 VAC, 50/60 Hz; 24 VDC		
all	Allowable voltage fluctuation	on	-15 to +10% of rated voltage		
د !	Coil insulation type		Class B or equivalent (130°C) (5)		
ining speed	Apparent power	Inrush	5.6 VA (50 Hz), 5.0 VA (60 Hz)		
	(Power consumption) AC	Holding	3.4 VA (2.1 W)/50 Hz, 2.3 VA (1.5 W)/60 Hz		
	Power consumption (DC)		1.8 W (2.04 W: With light/surge voltage suppressor)		
	Electrical entry		Grommet, Grommet terminal, Conduit terminal, DIN terminal		

Note 1) Use dry air at low temperatures. Note 2) Use turbine oil Class 1 (ISO VG32), if lubricated. Note 3) Impact resistance: No malfunction occurred when it is tested with a drop tester in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the initial period)

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. Test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature. (Values at the initial period) Note 4) Based on JIS C 0920. Note 5) Based on JIS C 4003.

#### **Option Specifications**

Pilot valve manual override	Non-locking push type (Extended), Locking type (Tool required), Locking type (Lever)
O all material conditions	110 to 120, 220, 240 VAC (50/60 Hz)
Coll rated voltage	12, 100 VDC
Option	With light/surge voltage suppressor Note)
Foot bracket (With screw)	Part No.: AXT626-10A, VFS1120 (single) only
THE CASE IN CONTRACTOR OF	

Note) Grommet type is available only w/ surge voltage suppressor (which is directly connected with lead wire)

#### Manifold

Body type	Applicable manifold base (Pilot EXH)
VFS1□20	Bar manifold (Individual EXH)
VFS1□30	Bar manifold (Common EXH base side)
CARLES AND A CONTRACT OF A CONTRACT	

Note) VFS1D30: Manifold only. Cannot be used as a single unit.



# Series VFS1000



		DL				
Cail				• Ap	plicable mod	lel
1	100 VAC, 50/60 Hz	Elec	strical entry, Light/Surge voltage suppressor	21	For VFS1□20	Individual pilot exhaust
2 3*	200 VAC, 50/60 Hz 110 to 120 VAC (50/60 Hz)	G GS	Grommet Grommet with surge voltage suppressor	22	For VFS1□30	Common pilot exhaust
4* 5	220 VAC, 50/60 Hz 24 VDC	D DZ	DIN terminal DIN terminal with light/surge voltage suppressor	- ■ Ma	nual override	9
6* 7*	12 VDC 240 VAC, 50/60 Hz	DO DOZ	DIN terminal ** DIN terminal with light/surge voltage suppressor **	- Nil A*	Non-locking pu Non-locking pus	ush type (Flush) n type (Extended)
9*	Other	Υ* \\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	DIN terminal	B*	Locking type	(Tool required)
* Opt	ion	YO*	DIN terminal **	- <u>C*</u> * Opt	Locking ty	/pe (Lever)
		YOZ*	DIN terminal with light/surge voltage suppressor **	-		
		TZ	Conduit terminal Conduit terminal with light/surge voltage suppressor	-		
		E EZ	Grommet terminal Grommet terminal with light/surge voltage suppressor	-		
		Q	* Y: Conforming to DIN43650B standard ** DIN connector is not attached.	-		



### 5 Port Pilot Operated Solenoid Valve Metal Seal, Body Ported Series VFS1000

# **Cylinder Speed Chart**

Detent assembly

 $\bigcirc$ 





AXT624-11A

# Series VFS1000



## 5 Port Pilot Operated Solenoid Valve Metal Seal, Body Ported Series VFS1000



# Series VFS1000 Manifold Specifications Single Base Type

### Compact and lightweight

Compact due to manifolding on a single base for mounting in small spaces.

### Keeps environmental air clean from pilot exhaust Use of the VV5FS1-30 manifold can exhaust

Use of the VV5FS1-30 manifold can exhaust intensively the pilot exhaust gas to the base side, and can prevent environmental aggravation due to noise and oil mist.



VV5FS1-20



VV5FS1-30

Part no. for mounting bolt and gasket BG-VFS1030

### Specifications

Manifold base type Bar manifold, Body ported		
	Manifold base type	Bar manifold, Body ported
Stations Max. 15 stations	Stations	Max. 15 stations

### **Port Specifications**

	Dee		Porting specific	ations: Rc (Conne	ecting port size)
Symbol	r do:	saye	Base	Valve	Base
	1(P)	5(R1), 3(R2)	1(P)	4(A), 2(B)	5(R1), 3(R2)
1	Common Common		Side/Rc 1/8	Top/Rc 1/8	Side/Rc 1/8

### Option

Blanking plate VVFS1000-10A-1 With gasket, screw

### How to Order Manifold Base



\*VFS1□20-□□-01 mountable

### How to Order Manifold Assembly

Instruct by mounted on	spec the	ifying manifo	the Id a	valv long	es with	and 1 the	blanking manifold	plate base	to mo	be del
no.				0						
<examble></examble>										
	``									

30

Manifold base)	VV5FS1-20-061-01 ······1
2 position single)	VFS1120-1D-01 ······ 3
2 position double)	VFS1220-1D-01 ····· 2
Blanking plate)	VVFS1000-10A-1 ····· 1



## 5 Port Pilot Operated Solenoid Valve Metal Seal, Body Ported Series VFS1000



**SMC** 

# Series VFS1000

