

5 Port Pilot Operated Solenoid Valve Metal Seal, Plug-in/Non Plug-in Series **VFS4000**

Model

Type of actuation		Model		Port size	Flow characteristics ⁽¹⁾						Max. operating cycle (cpm) ⁽¹⁾	Response time (ms) ⁽²⁾	Weight (kg) ⁽³⁾⁽⁴⁾
		Plug-in	Non plug-in		1 → 4/2 (P → A/B)			4/2 → 5/3 (A/B → R1/R2)					
					C [dm ³ /(s·bar)]	b	Cv	C [dm ³ /(s·bar)]	b	Cv			
2 position	Single	VFS4100	VFS4110	3/8	11	0.18	2.6	12	0.20	2.8	1,000	40 or less	0.63
				1/2	12	0.15	2.8	12	0.22	3.1			
	Double	VFS4200	VFS4210	3/8	11	0.18	2.6	12	0.20	2.8	1,200	15 or less	0.75
				1/2	12	0.15	2.8	12	0.22	3.1			
3 position	Closed center	VFS4300	VFS4310	3/8	10	0.18	2.5	10	0.14	2.3	600	50 or less	0.82
				1/2	11	0.18	2.7	11	0.22	2.6			
	Exhaust center	VFS4400	VFS4410	3/8	11	0.16	2.6	10	0.15	2.3	600	50 or less	0.82
				1/2	12	0.15	2.9	10	0.15	2.4			
	Pressure center	VFS4500	VFS4510	3/8	11	0.22	2.7	11	0.22	2.7	600	50 or less	0.82
				1/2	11	0.22	2.9	11	0.22	2.8			
	Double check	VFS4600	VFS4610	3/8	6.3	—	—	6.5	—	—	200	55 or less	1.71
				1/2	6.8	—	—	6.8	—	—			


Note 1) Based on JIS B 8375 (once per 30 days) for the minimum operating frequency. Note 2) Based on JIS B 8375-1981 (The value at supply press. 0.5 MPa).
 Note 3) The figures in the above list are for without sub-plate. In the case of with plug-in sub-plate and with non plug-in sub-plate, add 0.50 kg and 0.43 kg respectively. Note 4) "Note 1)" and "Note 2)" are with controlled clean air.

Compact yet provides a large flow capacity
 1/2: C: 12 dm³/(s·bar)


Low power consumption: 1.8 W DC

Easy maintenance

2 types of sub-plates:
 Plug-in and non plug-in



JIS Symbol



Standard Specifications

Valve specifications		Electricity specifications	
Fluid	Air/Inert gas		
Maximum operating pressure	1.0 MPa		
Minimum operating pressure	2 position	0.1 MPa	
	3 position	0.15 MPa	
Proof pressure	1.5 MPa		
Ambient and fluid temperature	-10 to 60°C ⁽¹⁾		
Lubrication	Non-lube ⁽²⁾		
Pilot valve manual override	Non-locking push type (Flush)		
Shock/Vibration resistance	150/50 m/s ² ⁽³⁾		
Enclosure	Type E: Dustproof (level 0), Type F: Dripproof (level 2), Type D: Splashproof (level 4) ⁽⁴⁾		
Coil rated voltage	100, 200 VAC, 50/60 Hz; 24 VDC		
Allowable voltage fluctuation	-15 to +10% of rated voltage		
Coil insulation type	Class B or equivalent (130°C) ⁽⁵⁾		
Apparent power (Power consumption)	AC	Inrush	5.6 VA/50 Hz, 5.0 VA/60 Hz
		Holding	3.4 VA (2.1 W)/50 Hz, 2.3 VA (1.5 W)/60 Hz
Power consumption DC	1.8 W (2.04 W: With light/surge voltage suppressor)		
Electrical entry	Plug-in type		Conduit terminal
	Non plug-in type		Grommet terminal, DIN terminal

Note 1) Use dry air at low temperatures.
 Note 2) Use turbine oil Class 1 (ISO VG32), if lubricated.
 Note 3) Impact resistance: No malfunction occurred when it is tested with a drop tester in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the initial period)
 Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. Test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature. (Values at the initial period)

Note 4) Based on JIS C 0920.
 Note 5) Based on JIS C 4003.

Option Specifications

Pilot type	External pilot ^{Note)}	
Manual override	Main valve	Direct manual override
	Pilot valve	Non-locking push type (Extended), Locking type (Tool required), Locking type (Lever)
Coil rated voltage	110 to 120, 220, 240 VAC, 50/60 Hz	
	12, 100 VDC	
Porting specifications	Bottom ported	
Option	With light/surge voltage suppressor, Non-rotating DIN terminal	

Note) Operating pressure: 0 to 1.0 MPa
 Pilot pressure 2 position: 0.1 to 1.0 MPa, 3 position: 0.15 to 1.0 MPa

VK

VZ

VF

VFR

VP4

VZS

VFS

VS4

VQ7


EVS

VFN


How to Order

Body type

O: Plug-in type sub-plate



F: Plug-in type conduit terminal



Porting specifications

Nil	Side ported
B*	Bottom ported

* In the case of external pilot (Option), bottom piping is not available.

Port size

Nil	Without sub-plate
03	Rc 3/8
04*	Rc 1/2

* EA, EB: Rc 3/8

Thread type

Nil	Rc
N*	NPT
T*	NPTF
F*	G

* Option







Plug-in

VFS4 2 0 0 [] 5 F [] [] [] 03 []

Non plug-in

VFS4 2 1 0 [] 1 E [] [] [] 03 []

Symbol

1	2 position single 	5	3 position pressure center 
2	2 position double 	6	3 position double check 
3	3 position closed center 		
4	3 position exhaust center 		

* Reverse pressure: Can be used by external pilot specifications.



Option

Nil	None
Z	With light/surge voltage suppressor
P*	Non-rotating DIN terminal

* In the case of w/ "Z", enter "ZP".
* Type "P" is available for DIN type only.


Electrical entry

E:	Grommet terminal
D:	DIN terminal





Pilot valve Manual override


Nil: Non-locking push type (Flush)




A*: Non-locking push type (Extended)



B*: Locking type (Tool required)




C*: Locking type (Lever)



* Option

Body type

1: Non plug-in type sub-plate



Coil rated voltage

1	100 VAC, 50/60 Hz
2	200 VAC, 50/60 Hz
3*	110 to 120 VAC, 50/60 Hz
4*	220 VAC, 50/60 Hz
5	24 VDC
6*	12 VDC
7*	240 VAC, 50/60 Hz
9*	Other

* Option

Pilot type

Nil	Internal pilot
R*	External pilot

* Option

Body option

0	Standard
1*	Direct manual override

* Option

How to Order Pilot Valve Assembly

SF4 - 1 F [] - 30

Coil rated voltage	
1	100 VAC, 50/60 Hz
2	200 VAC, 50/60 Hz
3*	110 to 120 VAC, 50/60 Hz
4*	220 VAC, 50/60 Hz
5	24 VDC
6*	12 VDC
7*	240 VAC, 50/60 Hz
9*	Other

* Option

Manual override	
Nil	Non-locking push type (Flush)
A*	Non-locking push type (Extended)
B*	Locking type (Tool required)
C*	Locking type (Lever)


* Option

* Refer to page 3-8-5 for voltage conversion.

5 Port Pilot Operated Solenoid Valve Metal Seal, Plug-in/Non Plug-in Series VFS4000

Cylinder Speed Chart

Use as a guide for selection.
Please confirm the actual conditions with SMC
Sizing Program.



System Components

System	Solenoid valve	Speed controller	Silencer	SGP (Steel pipe) Port size x Length
A	Series VFS4000 Rc 3/8	AS420-03 (S = 73 mm ²)	AN300-03 (S = 60 mm ²)	10A x 1
B	Series VFS4000 Rc 1/2	AS420-04 (S = 97 mm ²)	AN400-04 (S = 90 mm ²)	15A x 1




* It is when the cylinder is extending that is meter-out controlled by speed controller which is directly connected with cylinder, and its needle valve with being fully open.
 * The average velocity of the cylinder is what the stroke is divided by the total stroke time.
 * Load factor: ((Load weight x 9.8)/Theoretical force) x 100%

- VK
- VZ
- VF
- VFR
- VP4
- VZS
- VFS**
- VS4
- VQ7
- EVS
- VFN

Double Check Spacer/Specifications

Can hold an intermediate cylinder position for an extended time

If the double check spacer with a built-in double check valve is combined, it will enable the cylinder to stop in the intermediate stroke and maintain its position for a long time without being affected by the leakage between the spools.



Specifications


Double check spacer part no.	Plug-in type	Non plug-in type	
	VVFS4000-22A-1	VVFS4000-22A-2	
Applicable valve model	VFS4400-□F	VFS4410-□D VFS4410-□E	
Leakage * (cm ³ /min)	Solenoid one side energized	P	EA 230 EB or less
		P	EA 230 EB or less
	Solenoid both sides de-energized	A	EA 0
		B	EB 0

* Supply pressure: 0.5 MPa

⚠ Caution

- In the case of 3 position double check valve (VFS46□0), check the leakage from piping and fittings in between valve and cylinder by means of synthetic detergent solutions, and ensure that there is no such leakage found there. Also check the leakage from cylinder seal and piston seal. If there is any leakage, sometimes the cylinder, when valve is de-energized, can move without stopping at intermediate position.
- Be aware that if the exhaust side is restricted excessively, the intermediate stopping accuracy will decrease and will lead to improper intermediate stops.


Check Valve Operation



- The combination of VFS41□0, VFS42□0 and Double check spacer for prevention of falling at the stroke end but cannot hold the intermediate position of the cylinder.

Series VFS4000

Construction




Component Parts

No.	Description	Material	Note
①	Body	Aluminum die-casted	Platinum silver
②	Sub-plate	Aluminum die-casted	Platinum silver
③	Spool/Sleeve	Stainless steel	—
④	Adapter plate	Aluminum die-casted	Black
⑤	End plate	Aluminum die-casted	Black
⑥	Piston	Resin	—
⑦	Junction cover	Resin	—
⑧	Light cover	Resin	—

Sub-plate Assembly Part No.

Plug-in	VFS4000-P- ⁰³ / ₀₄
Non plug-in	VFS4000-S- ⁰³ / ₀₄

 * Mounting bolt and gasket are not included.

Part no. for mounting bolt and gasket
BG-VFS4000


Replacement Parts

No.	Description	Material	Part no.		
			VFS41□□	VFS42□□	VFS43□□/44□□/45□□
⑨	Return spring	Stainless steel	VF4000-18-1	—	VF4000-18-2A
⑩	Gasket	NBR	VF4000-20-1	VF4000-20-1	VF4000-20-1
⑪	Hexagon socket head screw	Steel	M4 x 40	M4 x 40	M4 x 40
⑫	Detent assembly	—	—	VF4000-12A	—
⑬	Pilot valve assembly	—	Refer to "How to Order Pilot Valve Assembly" on page 3-8-70.		

5 Port Pilot Operated Solenoid Valve Metal Seal, Plug-in/Non Plug-in Series VFS4000

Plug-in 2 position single/double, 3 position closed center/exhaust center/pressure center/double check



2 position single: VFS4100-□F



- VK
- VZ
- VF
- VFR
- VP4
- VZS
- VFS**
- VS4
- VQ7
- EVS
- VFN

- 2 position double: VFS4200-□F
- 3 position closed center: VFS4300-□F
- 3 position exhaust center: VFS4400-□F
- 3 position pressure center: VFS4500-□F


3 position double check: VFS4600-□F



Series VFS4000

Non Plug-in 2 position single/double, 3 position closed center/exhaust center/pressure center/double check

2 position single: VFS4110-□E, VFS4110-□D



2 position double: VFS4210-□E, VFS4210-□D
3 position closed center: VFS4310-□E, VFS4310-□D
3 position exhaust center: VFS4410-□E, VFS4410-□D
3 position pressure center: VFS4510-□E, VFS4510-□D

3 position double check: VFS4610-□E, VFS4610-□D

