VK

VZ

VF

VFR

VP4

VZS

VFS

VS4

VQ7

EVS

 VFN

5 Port Pilot Operated Solenoid Valve Metal Seal, Plug-in/Non Plug-in Series VZS3000

Model

Flow characteristics							(1)	(2)	(3)			
Type of actuation		Model	Port size Rc	$1 \rightarrow 4/2 \ (P \rightarrow A/B)$		4/2 → 5/3 (A/B → R1/R2)			Max. operating cycle (CPM)	Response time (ms)	Weight	
				C [dm ³ /(s·bar)]	b	Cv	C [dm3/(s-bar)]	b	Cv	Cycle (CPIVI)	ume (ms)	(kg)
position	Single	VZS3150	1/4	2.6	0.17	0.58	2.4	0.09	0.53	1200	18 or less	0.22
2 pos	Double	VZS3250	1/4	2.6	0.17	0.58	2.4	0.09	0.53	1200	13 or less	0.27
3 position	Closed center	VZS3350	1/4	2.5	0.17	0.56	2.4	0.11	0.52	500	26 or less	0.28
	Exhaust center	VZS3450	1/4	2.5	0.17	0.56	2.4	0.11	0.49	500	26 or less	0.28
	Pressure center	VZS3550	1/4	2.8	0.12	0.60	2.4	0.16	0.53	500	26 or less	0.28
	Double check	VZS3650	1/4	1.1	_	_	1.2	_	_	420	32 or less	0.43

 \bigcirc

Note 1) Min. operating cycle is based on JIS B 8375 (One time per 30 days).

Note 2) Response time is based on JIS B 8375-1981. (0.5 MPa, without light/surge voltage suppressor)

Note 3) For VZS3□50-□FZ-01 Note 4) "Note 1" and "Note 2" are with controlled clean air.

Reduction of wiring cost MIL standard D-sub connector with one-touch connection (Plug-in type)

Compact and large valve capacity: Width 18 mm
Flexible to increase and decrease manifold stations
(Stacking type manifold base)

High frequency/Long service life (more than 30 mil. times) Possible to use in nonlubrication and dry air (Metal seal structure)

Different variations for connection Grommet type

L, M plug connector type: Individual take out of A and B sides

K plug connector type: Common take out of A and B sides

DIN terminal type: Individual take out of A and B sides

A little power consumption: 1.8 W DC

For serial transmission





Non plug-in type

Standard Specifications

Jian	Standard Opecinications						
Valve specifications	Fluid		Air/Inert gas				
	Maximum operating pressure		1.0 MPa				
	Minimum operating pressure		0.1 MPa				
<u>i2</u>	Proof pressure		1.5 MPa				
əcit	Ambient and fluid temperature		-10 to 50°C ⁽¹⁾				
ds	Lubrication		Non-lube (2)				
<u>8</u>	Pilot valve manual override		Non-locking push type (Flush)				
\ 	Shock/Vibration resistance (m/s	S ²)	150/50 ⁽³⁾				
	Enclosure		Dustproof (Degrees of protection 0) (4)				
	Coil rated voltage		100, 200 VAC, 50/60 Hz; 24 VDC				
Suc	Allowable voltage fluctuation		-15 to +10% of rated voltage				
aţic	Coil insulation type		Class E or equivalent (120°C) (5)				
ij	Apparent power (AC)	Inrush	4.5 VA/50 Hz, 4.2 VA/60 Hz				
Electricity specifications		Holding	3.5 VA/50 Hz, 3 VA/60 Hz				
	Power consumption (DC)		1.8 W				
			Plug-in type (FZ)				
	Floatrical antru		Non plug-in type				
E	Electrical entry		Grommet (G), Plug connector (L, M, KZ)				
			DIN terminal (D)				

Note 1) Use dry air at low temperatures.

Note 2) Use turbine oil Class 1 (ISO VG32), if lubricated.

Note 3) Impact resistance: No malfunction occurred when it is tested with a drop tester in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the initial period)

Vibration resistance: No malfunction occurred in a one-sweep test between 8.3 and 2000 Hz.

Test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature.

(Values at the initial period)

Note 4) Based on JIS C 0920. Note 5) Based on JIS C 4003.


Option Specifications

<u>- - - - - - - - - - </u>				
Coil rated voltage	24, 48, 110, 220 VAC (50/60 Hz)			
Con rated voltage	6, 12, 48 VDC			
Manual override	Locking type (Tool required)			
Option	With light/surge voltage suppressor Note)			

Note) Plug-in, K plug connector type is standard with light/surge voltage suppressor.



How to Order




arranged separately.

5 Port Pilot Operated Solenoid Valve Metal Seal, Plug-in/Non Plug-in Series VZS3000

Cylinder Speed Chart

Use as a guide for selection. Please confirm the actual conditions with SMC Sizing Program.



- * It is when the cylinder is extending that is meter-out controlled by speed controller which is directly connected with cylinder, and its needle valve with being fully open.
- * The average velocity of the cylinder is what the stroke is divided by the total stroke time.
- * Load factor: ((Load weight x 9.8)/Theoretical force) x 100%

Conditions

		Series CJ2	Series CM2	Series MB
	Tube bore x Length	T0604 x 1 m	(1 m T0806 x 1 m	
VZS3150-02	Speed controller	AS3001F-06	AS3001F-08	
	Silencer		AN101-01	

Double Check Spacer/Specifications

Can hold an intermediate cylinder position for an extended time

If the double check spacer with a built-in double check valve is combined, it will enable the cylinder to stop in the intermediate stroke and maintain its position for a long time without being affected by the leakage between the spools.





Non plug-in type


Specifications

Plug-in t	ype	Non plug-in type		
VVZS3000-	22A-1	VVZS3000-22A-2		
VZS3450-	⊐FZ	VZS3450-□ M KZ		
Solenoid one side energized	1(P)	5(R1) 3(R2)	210 Ncm³/ min or less	
Solenoid both sides	1(P)	5(R1)	210 Ncm ³ /	
		3(R2)	min or less	
	4(A)	5(R1)	0	
g	2(B)	3(R2)		
	VZS3450-I Solenoid one side energized Solenoid	Solenoid both sides energized 1(P) 4(A)	VVZS3000-22A-1 VVZS3000-22A-1 VZS3450-□FZ VZS3450-□FZ Solenoid one side energized both sides energized 1(P) 5(R1) 3(R2) 5(R1) 3(R2) 4(A) 5(R1)	

⚠ Caution

In the case of 3 position double check (VZS3650), check the leakage from piping and fittings in between valve and cylinder by means of synthetic detergent solutions, and ensure that there is no such leakage found there. Also check the leakage from cylinder seal and piston seal. If there is any leakage, sometimes the cylinder, when valve is de-energized, can move without stopping at intermediate position.

Check Valve Operating Pressure/Characteristics



• The combination of VZS3150, VZS3250 and a double check spacer can be used as prevention of falling at the stroke end but cannot hold the intermediate position of the cylinder.

٧Z

٧K

VF

VFR

VP4

VZS

VFS

VS4


VQ7

EVS


VFN

Series VZS3000

Construction



3 position closed center/exhaust center/pressure center



Component Parts

	•			
No.	Description	Material	Note	
1	Body	Aluminum die-casted	Platinum silver	
2	Sub-plate	Aluminum die-casted	Platinum silver	
3	Spool/Sleeve	Stainless steel	_	
4	Adapter plate	Resin	Black	
(5)	End plate	Resin	Black	
6	Piston	Resin	_	

Sub-plate Assembly

Plug-in		VZS3000-P-01 □				
Non plug-in		VZS3000-S-01 □				
* Mounting bolt and gasket are not attached. : Thread type Thread Type						
Standard	Standard Nil Rc					
	N	NPT				
Ontion	т	NIDTE				


Replacement Parts

No.	Description	Material	Part no.			
7	Gasket	NBR	BG-VZS3000-1 (Groove gasket 1 pc. Round head combination screw 2 pcs.)			
8	Round head combination screw	Carbon steel	BG-VZS3000 (Gasket 1 pc., Round head combination screw 3 pcs.) Note			
9	Pilot valve assembly	_	Refer to "How to Order Pilot Valve Assembly" on page 3-7-24.			
10	Light cover assembly	_	Refer to "How to Order Light Cover Assembly" on page 3-7-24.			


Note) Refer to page 3-7-6.



5 Port Pilot Operated Solenoid Valve Metal Seal, Plug-in/Non Plug-in Series VZS3000




Series VZS3000



Non Plug-in 2 position double, 3 position closed center/exhaust center/pressure center Grommet 2 position double: VZS3250-□ ^G_H(S)-⁰¹₀₂ 3 position closed center: VZS3350-□ ^G_H(S)-⁰¹₀₂ 3 position exhaust center: VZS3450-□ ^G_H(S)-⁰¹₀₂ 3 position pressure center: VZS3550-□ G(S)-01 2-ø4.5 mounting hole Pilot EXH port M5×0.8 (External pilot port) (M5×0.8)Not machined 3-Rc 1/8 1/4 2-Rc1/8 L plug connector K plug connector 2 position double: VZS3250-□L(Z)-01 2 position double: VZS3250-□KZ-01

3 position closed center: VZS3350-□L(Z)-01/02


3 position pressure center: VZS3550-□L(Z)-01



3 position closed center: VZS3350-□KZ-01

3 position exhaust center: VZS3450-□KZ-012

3 position pressure center: VZS3550-□KZ-01




M plug connector

2 position double: VZS3250-□M(Z)-01/02

3 position closed center: VZS3350-□M(Z)-01

3 position exhaust center: VZS3450-□M(Z)-01



DIN terminal

2 position double: VZS3250-□D(Z)-01/02

3 position closed center: VZS3350-□D(Z)-01

3 position pressure center: VZS3550-□D(Z)-01

164 (3 position: 171.5) MAX.10 Applicable cable O.D. With light/surge voltage suppressor Ø3.5 to Ø7 7.9 85.5 * Other dimensions are the same as the grommet type.

VK

VZ

VFR

VP4

VS4

VQ7

EVS

VFN

Series VZS3000

