
Series XLF



to the left side when the flange surface is viewed from the front.

XLF

Option specifications/Combination table

Option specifications		Symbol	Model						
		Symbol	XLF-16	XLF-25	XLF-40	XLF-50	XLF-63	XLF-80	
	Indicator	Α	•	•	•	•	•	•	
n temp. type	Without heater	H0	•	•	•	•	•	•	
	With heater for 80°C (176°F)	H1	_	•	•	•	•	•	
	With heater for 100°C (212°F)	H2	_	_	•	•	•	•	
High	With heater for 120°C (248°F)	H3	_	•	•	•	•	•	

5 to 150°C

(41 to 302°F)

With heater for 100°C (212°F)

With heater for 120°C (248°F)

H2


H3

Note) Auto switches cannot be mounted in the case of high temperature types.

13

SMC

How to Order



Note 2) Solenoid valves

XLFV-16, 25, 40: SYJ319 XLFV-50, 63, 80: SYJ519 Example) SYJ319-1GS

For further details on solenoid valves, refer to the SMC solenoid valve catalog "SYJ300, 500, 700" (N220).

Note 3) Solenoid valves are shipped facing downward (flange side), but can be rotated to face upward.

XLFV

Series XLF, XLFV

Specifications


Model	XLF(V)-16	XLF(V)-25	XLF(V)-40	XLF(V)-50	XLF(V)-63	XLF(V)-80				
Valve type	Normally closed (pressurize to open, spring seal)									
Fluid	Non-corrosive gas for aluminum alloy (A6063) and SUS304/316									
Operating temperature °C	XLF	5 to 60°C (41 to 140°F) [high temperature type: 5 to 150°C (41 to 302°F)]								
Operating temperature C	XLFV	5 to 50°C (41 to 122°F)								
Operating pressure Pa {Torr}		Atmospheric pressure to 1 x 10^{-6} {760 to 7.5 x 10^{-9} }								
Conductance <i>d</i> 's Note 1)		5	14	45	80	160	200			
Leakage Pa m ³ /s	Internal	1.3 x 10 ⁻¹⁰ {1 x 10 ⁻⁹ } at ordinary temperatures, excluding gas transmission								
{Torr d/s}	External	1.3 x 10 ⁻¹¹ {1 x 10 ⁻¹⁰ } at ordinary temperatures, excluding gas transmission								
Operating time ms Note 2)	XLF	30	35	40	45	65	85			
Operating time ins the p	XLFV	30	35	60	60	100	130			
Flange type	KF (NW) KF (NW), K (DN)									
Principle materials	Body: Aluminum alloy Bellows: Stainless steel Seal: FKM (fluoro rubber)									
Surface treatment	Exterior: Hard anodized Interior: Machined for clean environment									
Actuation pressure MPa	0.4 to 0.7 (58 to 101psi)									
Actuation port size XLF		M5 (10-32 nominal) Rc(PT) 1/8								
Actuation port size	XLFV		M5 (10-32 nom	inal) Ports P, R	Rc(PT) 1/8(Port P): M5(10-32 nominal) (Port)					
Actuating solenoid valve recommended C	0.06≤	0.09≤	0.11≤	0.15≤	0.4≤	0.5≤				
Service life (Million cycles)	3			2						
Weight kg (lb)	XLF	0.25 (0.55)	0.45 (0.99)	1.1 (2.43)	1.6 (3.52)	3.0 (6.61)	4.8 (10.58)			
	XLFV	0.29 (0.64)	0.49 (1.08)	1.14 (2.51)	1.66 (3.65)	3.06 (6.75)	4.86 (10.72)			

Note 1) Conductance is represented by the value of an elbow with the same dimensions.

Note 2) The operating time with no solenoid valve (XLF) is the same value as the case of the solenoid valve piped directly to the bonnet, where the actuation pressure is 0.5MPa (72psi). The operating time becomes faster under high pressure.

Note 3) For valve heater specifications, refer to "Common Option Specifications, [1] Heaters" on page 37.

Construction/Operation



Options

which is sealed by the shaft seal (11) and the piston seal (9), overcomes the force of the spring (13), and the valve (15) opens.

With the exhaust of air pressure, the valve (15) is closed by the force of the spring (13) and is sealed by the valve seal (14).

In the case of the XLFV, port P (19) is normally pressurized, and the valve (15) opens when the solenoid valve (18) is turned ON, and closes when it is turned OFF. Operation is the same as that of the XLF.

Valve side exhaust

For selections, refer to item 3, model number and option symbol table.

④ Auto switch: The magnet (10) actuates the auto switch (4) indicating the position of the integrated valve (15) and piston (8). With 2 auto switches, the open and closed positions are detected, and with 1 auto switch, either the open or closed position is detected. Auto switches are applicable at ordinary temperatures only 5 to 60°C (41 to 140°F).
⑤ Heater: Simple heating is performed using thermistors. The valve body can be heated to

Simple heating is performed using thermistors. The valve body can be heated to approximately 80, 100 or 120°C (176, 212, or 248°F), depending on the heater option and the valve size. The type and number of thermistors to be used will vary depending upon size and setting temperature. In the case of high temperature specifications, the bonnet assembly (1) is a heat resistant structure. This is not available with solenoid valve.


(6) Indicator: When the valve is open, an orange marker about 1mm in height appears in the center of the name plate (16).



Dimensions (mm)

1in=25.4mm


XLF/Air operated type




									(mm)
Model	Α	В	С	D	E Note 1)	Fn	Fd	G	Н
XLF-16	40	103	38	1	-	30	-	17	40
XLF-25	50	113	48	1	12	40	-	26	39
XLF-40	65	158	66	2	11	55	-	41	63
XLF-50	70	170	79	2	11	75	-	52	68
XLF-63	88	196	100	3	11	87	95	70	69
XLF-80	90	235	117	3	11	114	110	83	96

Note 1) Dimension E applies when heater option is included. (lead wire length: approx. 1m) Note 2) (a), (b) and (c) in the above drawing indicate heater mounting positions. Moreover, heater mounting positions will differ depending on the type of heater. For further details, refer to mounting positions under Replacement heaters/Part Nos. on page 46.

XLFV/With solenoid valve





					(mm)			
Model	J	K	L	М	Ν			
XLFV-16	16.5	13	8.5	3	3			
XLFV-25	16.5	14	8.5	3	3			
XLFV-40	17.5	23	8.5	3	3			
XLFV-50	28	23	12	4	2			
XLFV-63	29	29	12	4	2			
XLFV-80	29	39	12	4	2			

* Other dimensions are the same as XLF.

