

Vacuum Ejector Box Style (Built-in Silencer)/Body Ported Style

Series ZH

Nozzle diameter— Ø0.5, Ø0.7, Ø1.0, Ø1.3, Ø1.5, Ø1.8, Ø2.0

L: Large Flow Capacity

Compact and Lightweight

The nozzle and the body, which have been made into a composite resin construction, are compact and lightweight.

ZX

ZR

ZΜ

ZY

ZΗ

ZU

ZL

ZF


ZP

ZCU

CYV

Vacuum related

Nozzle diameter ø0.5...28g





Box style (built-in silencer) and body ported style


Two styles are available in the series: the box style with a silencer exhaust and the body ported style with an individual exhaust.

One-touch and screwin connections can be combined.

To suit the operating conditions, port connections can be combined with a choice of One-touch and screw-in connections.








Body can be mounted and secured.

The body ported style is also provided with mounting holes for securing the body.







How to Order







Note Refer to table 1\&2 below for combination of connection and port size.

Box style (Built-in silencer)

Body ported style (Without silencer)



ZH | 07 | B | S | 06 ZH 07 D S 01 01 01

Nozzle diameter **05** 0.5mmø 07 0.7mmø 1.0mmø 1.3mmø 13 15 1.5mmø 1.8mmø 18 20 2.0mmø

> Max. vacuum pressure **s** –88kPa{–660mmHg} -48kPa{-360mmHg}

> > SUP port size Note)

Symbol	Size	Style
06	ø6	One-touch
08	ø8	One-touch
10	ø10	One-touch
12	ø12	One-touch
01	Rc¹∕8	Screw-in
02	Rc1/4	Screw-in
03	Rc3/8	Screw-in

↓ EX	(H port size	Note)
Symbol	Size	Style
06	ø6	One-touch
08	ø8	One-touch
10	ø10	One-touch
12	ø12	One-touch
16	ø16	One-touch
01	Rc1/8	Screw-in
02	Rc1/4	Screw-in
03	Rc3/8	Screw-in
04	Rc1/2	Screw-in

Screw-in

Size Style 06 ø6 One-touch ø10 10 One-touch 12 ø12 One-touch 16 ø16 One-touch 01 Rc1/8 Screw-in Rc 1/4 Screw-in 02 03 Rc3/8 Screw-in Rc1/2

VAC port size Note)

04

Table 1 Combination of connection									
Body		SUP	VAC	EXH					
Box style (Built-in silencer)	1	One-touch	One-touch	_					
	2	One-touch	Screw-in	_					
(=====,	3	Screw-in	Screw-in	_					
	1	One-touch	One-touch	One-touch					
Body ported style		One-touch	Screw-in	One-touch					
(Without silencer)	3	Screw-in	Screw-in	Screw-in					

	Table②Port size											
Model	Connectio	n (One-touch	/Screw-in)									
Model	SUP	VAC	EXH									
ZH05B												
ZH07B	ø6/Rc1/8	ø6Rc 1/8	_									
ZH10B												
ZH13B	ø8/Rc1/8	ø10/Rc1/4										
ZH05D	ø6/Rc1/8	ø6/Rc1/8	ø6/Rc1/8									
ZH07D	50/110 /8	20/110 /6	90/110-/8									
ZH10D	ø6/Rc1/8	ø6/Rc1/8	ø8/Rc1/8									
ZH13D	ø8/Rc1/ ₈	ø10/Rc1/4	ø10/Rc1/4									
ZH15D	ø10/Rc1/4	ø12/Rc3/8	ø12/Rc3/8									
ZH18D	ø12/Rc3/8	912/110-78	Ø12/11078									
ZH20D	ø12/Rc3/8	ø16/Rc1/2	ø16/Rc1/2									

Vacuum Ejector/Series ZH







Ejector symbol



Box style (Built-in silencer) ZH□□B

ZX

ZR

ZM

ZY

ZH

ZU

ZL

ZF

ZΡ

ZCU

CYV


Vacuum related


Model

Model	Nozzle dia.	Body style	Max. vacuum pressure (kPa)		Max. suction flow (c/min(ANR))		Air consumption (ℓ/min(ANR))	Connection (One-touch/Scre		w-in)	Weight (g)													
	(111111)		S type	L type	S type	L type	S type/L type	SUP	VAC	EXH	(9)													
ZH05B□	0.5				5	8	13				28													
ZH07B□	0.7	Box style	40	40	12	20	23	ø6/Rc1/8	ø6/Rc1/8		28													
ZH10B□	1.0	(Built-in silencer)	-48	-48	24	34	46			_	33													
ZH13B□	1.3				40	70	78	ø8/Rc1/ ₈	ø10/Rc1/4		66													
ZH05D□	0.5			40	5	8	13	ø6/Rc1/8	/8 ø6/Rc ¹ /8	ø6/Rc ¹ /8	11													
ZH07D□	0.7	Body ported style	-88		12	20	23	00/nc/8	Ø6/nc //8		12													
ZH10D□	1.0	(Without silencer)	-88	-48	24	34	46	ø6/Rc1/8	ø6/Rc1/8	ø8/Rc1/ ₈	16													
ZH13D□	1.3				40	70	78	ø8/Rc1/ ₈	ø10/Rc1/4	ø10/Rc1/4	27													
ZH15D□	1.5	D - d d - d - d - d	Dady named about	Pady parted style	Pady parted style	Pady parted style	Pady parted style	Pady parted style	Pady parted style	Dady samed at the	Dady named at da	Pady parted style	Pady parted atula	Dady parted at de	Dady parted at de			55	75	95	ø10/Rc ¹ / ₄	ø12/Rc3/8	ø12/Rc3/8	43
ZH18D□	1.8	Body ported style (Without silencer)	-88	- 53	65	110	150	ø12/Rc3/8	Ø12/HC%8	Ø 12/RC 9/8	55													
ZH20D□	2.0	(Without Shericer)			85	135	185	ø12/Rc ³ /8	ø16/Rc1/2	ø16/Rc1/2	95													

*Supply pressure: 0.45MPa.

Construction





⚠ Precautions

Be sure to read before handling. Refer to p.0-20 and 0-21 for Safety Instructions and common precautions on the products mentioned in this catalogue, and refer to p.3.0-2 for precautions on every series.

⚠ Caution

Installation

Make sure that an excessive amount of load or moment is not applied to the ejector body due to pipe connections or installation.

Exhaust piping


On the ZHUDBDmodels, keep exhaust ports open on at least one side. Make sure that the back pressure of the exhaust pipe on the ZHDDDmodels is 0.005MPa max. (Reference: Using a tube with the applicable diameter, its length must be 0.5m max.) (Port indication: P: supply port; V: vacuum port; E: exhaust port.)


Matching of the ejector to the vacuum circuit:


For precautions associated with the matching of the ejector to the vacuum circuit, refer to the technical data in "Best Pneumatics 3"




Exhaust Characteristics/Flow Characteristics Flow characteristics: at 0.45MPa supply pressure ZH05□S Max. vacuum pressure: -88kPa ZH05□L Max. vacuum pressure: -48kPa **Exhaust characteristics** Flow characteristics **Exhaust characteristics** Flow characteristics -100 -100(kPa) (kPa) (kPa) (kPa) e (d/min(ANR)) (d/min(ANR)) (dmin(ANR)) Air consumption (d/min(ANR)) Vacuum pressure Vacuum pressure /acuum pressure -60 Air Suction flow rate Suction flow rate Air consumption 0 /acuum Suction floy 5 5 0 0 0.1 0.2 0.3 0.4 0.5 0.6 0.1 0.2 0.3 0.4 0.5 0.6 8 10 2 4 6 8 10 6 Supply air pressure (MPa) Suction flow rate (\ell/min(ANR)) Supply air pressure (MPa) Suction flow rate (\ell/min(ANR)) ZH07□S Max. vacuum pressure: -88kPa ZH07□L Max. vacuum pressure: -48kPa **Exhaust characteristics** Flow characteristics **Exhaust characteristics** Flow characteristics 25 -100 -100 20 (kPa) (kPa) (kPa) (kPa) Air consumption ("min(ANR) Air consumption ("min(ANR) /acuum pressure /acuum pressure pressure pressure Suction flow Suction flow rate flow rate Vacuum Vacuum Suction 5 0 0.2 0.3 0.4 0.5 0.6 0.1 0.1 0.2 0.3 0.4 0.5 0.6 10 20 5 10 15 20 25 Suction flow rate (\ell/min(ANR)) Supply air pressure (MPa) Suction flow rate (\ell/min(ANR)) Supply air pressure (MPa) ZH10□S ZH10□L Max. vacuum pressure: -88kPa Max. vacuum pressure: -48kPa **Exhaust characteristics Exhaust characteristics** Flow characteristics Flow characteristics -100 -100-100 (kPa) (kPa) (kPa) (kPa) ((/min(ANR)) (/wmin(ANR) pressure pressure Vacuum pressure pressure rate Air consumption 40 consumption -Mog ₩ /acuum /acuum uction flow /acuum Suction 1 Suction 0.1 0.2 0.3 0.4 0.5 0.6 0.2 0.3 0.4 0.5 0.6 30 40 50 10 20 5 10 15 2025 Supply air pressure (MPa) Supply air pressure (MPa) Suction flow rate (#min(ANR)) Suction flow rate (\ell/min(ANR)) ZH13□S ZH13□L Max. vacuum pressure: -88kPa Max. vacuum pressure: -48kPa **Exhaust characteristics** Flow characteristics **Exhaust characteristics** Flow characteristics 125 125 -100 -100(KPa) (kPa) (kPa) (kPa) Air consumtion









Vacuum Ejector/Series

Exhaust Characteristics/Flow Characteristics

/acuum pressure (kPa)


-20

Flow characteristics: at 0.45MPa supply pressure

ZH15□S **Exhaust characteristics** 125 Vacuum Press (#/min(ANR)) (#/min(ANR)) Air consumption Vacuum pressure Suction flow rate 50 ⋛ consumption 40 Suction f -20 0 0.1 0.2 0.3 0.4 0.5 0.6 Supply air pressure (MPa)

Max. vacuum pressure: -88kPa Flow characteristics

ZH15□L



Flow characteristics -100(kPa) pressure Vacuum 20 40 60 80100 Suction flow rate (&/min(ANR))

Max. vacuum pressure: -53kPa

ZH18□S

Suction flow rate (/min(ANR) Max. vacuum pressure: -88kPa

20 40 60 80 100

ZH18□L

Max. vacuum pressure: -53kPa

ZH ZU

ZX

ZR

ZM

ZY

ZL


ZF


ZP


ZCU


CYV

Vacuum related











ZH20□S


Max. vacuum pressure: -88kPa


ZH20□L

Max. vacuum pressure: -53kPa










How to Read Graphs



Flow characteristics are expressed in ejector vacuum pressure and suction flow. If suction flow rate changes a change in vacuum pressure will also be expressed. Normally this relationship is expressed in ejector standard use. In graph, Pmax is max. vacuum pressure and Qmax is max. suction flow. The values are specified according to catalogue use. Changes in vacuum pressure are expressed in the below order.

1)When ejector suction port is covered and made airtight, suction flow becomes 0 and vacuum pressure is at maximum value (Pmax).

2When suction port is opened gradually, air can flow through, (air leakage), suction flow increases, but vacuum pressure decreases. (condition P1 and Q1)

3When suction port is opened further, suction flow moves to maximum value (Qmax), but vacuum pressure is near 0. (atmospheric pressure).


When vacuum port (vacuum piping) has no leakage, vacuum pressure becomes maximum, and vacuum pressure decreases as leakage increases when leakage value is the same as max, suction flow, vacuum pressure is near 0. In the case when ventirative or leaky work should be absorbed, please note that vacuum pressure will not be high.



Series ZH

Box Style (Built-in silencer)/ZH□B: -□-□


One-touch connection



Model	Α	øΒ	С	D	E	F	G	Н
ZH05BS-06-06	60	6	22	16	17	28	5	47
ZH05BL-06-06	60	6	22	16	17	28	5	47
ZH07BS-06-06	60	6	22	16	17	28	5	47
ZH07BL-06-06	60	6	22	16	17	28	5	47
ZH10BS-06-06	63	6	23	18	17	29	5	50
ZH10BL-06-06	63	6	23	18	17	29	5	50
ZH13BS-08-10	78	8	27.5	23	18.5	35	7	61
ZH13BL-08-10	78	8	27.5	23	18.5	35	7	61

Model	ı	J	øK	L	øΜ	øΝ	0	Р
ZH05BS-06-06	57	17	3.2	24	6	5.8	2	31
ZH05BL-06-06	57	17	3.2	24	6	5.8	2	31
ZH07BS-06-06	57	17	3.2	24	6	5.8	2	31
ZH07BL-06-06	57	17	3.2	24	6	5.8	2	31
ZH10BS-06-06	60	17	3.2	26	6	5.8	2	32
ZH10BL-06-06	60	17	3.2	26	6	5.8	2	32
ZH13BS-08-10	75	21	4.2	28	10	7.5	3	38.5
ZH13BL-08-10	75	21	4.2	28	10	7.5	3	38.5


One-touch and Screw-in connection



Model	Α	øΒ	С	D	Е	F	G	Н
ZH05BS-06-01	60	6	29.5	16	17	28	5	47
ZH05BL-06-01	60	6	29.5	16	17	28	5	47
ZH07BS-06-01	60	6	29.5	16	17	28	5	47
ZH07BL-06-01	60	6	29.5	16	17	28	5	47
ZH10BS-06-01	63	6	30.5	18	17	29	5	50
ZH10BL-06-01	63	6	30.5	18	17	29	5	50
ZH13BS-08-02	78	8	39	23	18.5	35	7	61
ZH13BL-08-02	78	8	39	23	18.5	35	7	61

Model	ı	J	øΚ	L	M	øΝ	0	Р
ZH05BS-06-01	57	12	3.2	24	Rc1/8	5.8	2	31
ZH05BL-06-01	57	12	3.2	24	Rc1/8	5.8	2	31
ZH07BS-06-01	57	12	3.2	24	Rc1/8	5.8	2	31
ZH07BL-06-01	57	12	3.2	24	Rc1/8	5.8	2	31
ZH10BS-06-01	60	12	3.2	26	Rc1/8	5.8	2	32
ZH10BL-06-01	60	12	3.2	26	Rc1/8	5.8	2	32
ZH13BS-08-02	75	17	4.2	28	Rc1/4	7.5	3	38.5
ZH13BL-08-02	75	17	4.2	28	Rc1/4	7.5	3	38.5

Screw-in connection




Model	Α	В	С	D	Е	F	G	Н
ZH05BS-01-01	67.5	Rc1/8	29.5	16	12	28	5	47
ZH05BL-01-01	67.5	Rc1/8	29.5	16	12	28	5	47
ZH07BS-01-01	67.5	Rc1/8	29.5	16	12	28	5	47
ZH07BL-01-01	67.5	Rc1/8	29.5	16	12	28	5	47
ZH10BS-01-01	70.5	Rc1/8	30.5	18	12	29	5	50
ZH10BL-01-01	70.5	Rc1/8	30.5	18	12	29	5	50
ZH13BS-01-02	86.5	Rc1/8	39	18	14	35	7	61
ZH13BL-01-02	86.5	Rc1/8	39	18	14	35	7	61


Model	ı	J	øΚ	L	М	øΝ	0	Р
ZH05BS-01-01	57	12	3.2	31.5	Rc1/8	5.8	2	38.5
ZH05BL-01-01	57	12	3.2	31.5	Rc1/8	5.8	2	38.5
ZH07BS-01-01	57	12	3.2	31.5	Rc1/8	5.8	2	38.5
ZH07BL-01-01	57	12	3.2	31.5	Rc1/8	5.8	2	38.5
ZH10BS-01-01	60	12	3.2	33.5	Rc1/8	5.8	2	39.5
ZH10BL-01-01	60	12	3.2	33.5	Rc1/8	5.8	2	39.5
ZH13BS-01-02	75	17	4.2	36.5	Rc1/4	7.5	3	50
ZH13BL-01-02	75	17	4.2	36.5	Rc1/4	7.5	3	50

Vacuum Ejector/Series

Body Ported Style (Without silencer) /ZH05D^S₋□-□-□ to ZH15D^S₋□-□-□

One-touch connection





Model	Α	В	С	D	øΕ	F	øG	Н
ZH05DS-06-06-06	58	14.2	34	22	6	17	3.2	17
ZH05DL-06-06-06	58	14.2	34	22	6	17	3.2	17
ZH07DS-06-06-06	61	14.2	34	22	6	17	3.2	17
ZH07DL-06-06-06	61	14.2	34	22	6	17	3.2	17
ZH10DS-06-06-08	66	17.2	37	23	6	17	4.2	17
ZH10DL-06-06-08	70	17.2	37	23	6	17	4.2	17
ZH13DS-08-10-10	74	20	42	27	8	18.5	4.2	21
ZH13DL-08-10-10	79	20	42	27	8	18.5	4.2	21
ZH15DS-10-12-12	93.3	22.45	47	29.5	10	21	4.2	22
ZH15DL-10-12-12	93.3	22.45	47	29.5	10	21	4.2	22

7	
1_	ZX
1	
2	ZR
,	ZM
4	

ZY

ZΗ

ZU

ZL

ZF

Model	ı	øJ	K	L	М	øΝ	0	Р
ZH05DS-06-06-06	17	6	24	21	7.8	6	17	24
ZH05DL-06-06-06	17	6	24	21	7.8	6	17	24
ZH07DS-06-06-06	17	6	24	22	7.8	6	17	24
ZH07DL-06-06-06	17	6	24	22	7.8	6	17	24
ZH10DS-06-06-08	18.5	6	26	24.5	9.6	8	20	28
ZH10DL-06-06-08	18.5	6	26	24.5	9.6	8	20	28
ZH13DS-08-10-10	21	10	28	26.5	10.7	10	22	30
ZH13DL-08-10-10	21	10	28	26.5	10.7	10	22	30
ZH15DS-10-12-12	22	12	31.5	32.8	12	12	27	35
ZH15DL-10-12-12	22	12	31.5	32.8	12	12	27	35
Model	Α	В	С	D	øΕ	F	øG	Н
ZH05DS-06-01-06	58	14.5	41.5	29.5	6	17	3.2	12


2111303-00-10-10	~ '	10	20	20.5	10.7	10	~~	- 00
ZH13DL-08-10-10	21	10	28	26.5	10.7	10	22	30
ZH15DS-10-12-12	22	12	31.5	32.8	12	12	27	35
ZH15DL-10-12-12	22	12	31.5	32.8	12	12	27	35
Model	Α	В	С	D	øΕ	F	øG	Н
ZH05DS-06-01-06	58	14.5	41.5	29.5	6	17	3.2	12
ZH05DL-06-01-06	58	14.5	41.5	29.5	6	17	3.2	12
ZH07DS-06-01-06	61	14.5	41.5	29.5	6	17	3.2	12
ZH07DL-06-01-06	61	14.5	41.5	29.5	6	17	3.2	12
ZH10DS-06-01-08	66	17.4	44.5	30.5	6	17	4.2	12
ZH10DL-06-01-08	70	17.4	44.5	30.5	6	17	4.2	12
ZH13DS-08-02-10	74	20.2	54	39	8	18.5	4.2	17
ZH13DL-08-02-10	79	20.2	54	39	8	18.5	4.2	17
ZH15DS-10-03-12	93.3	22.45	58.5	41	10	21	4.2	19
ZH15DL-10-03-12	93.3	22.45	58.5	41	10	21	4.2	19

ZCU

CYV

Vacuum related

One-touch and Screw-in connection




Model		J	ĸ	L	IVI	ØN	5	۲
ZH05DS-06-01-06	17	Rc1/8	24	21	7.8	6	17	24
ZH05DL-06-01-06	17	Rc1/8	24	21	7.8	6	17	24
ZH07DS-06-01-06	17	Rc1/8	24	22	7.8	6	17	24
ZH07DL-06-01-06	17	Rc1/8	24	22	7.8	6	17	24
ZH10DS-06-01-08	17	Rc1/8	26	24.5	9.6	6	20	28
ZH10DL-06-01-08	17	Rc1/8	26	24.5	9.6	6	20	28
ZH13DS-08-02-10	21	Rc1/4	28	26.5	10.7	10	22	30
ZH13DL-08-02-10	21	Rc1/4	28	26.5	10.7	10	22	30
ZH15DS-10-03-12	22	Rc3/8	31.5	32.8	12	12	27	35
ZH15DL-10-03-12	22	Rc3/8	31.5	32.8	12	12	27	35

Model	Α	В	С	D	Е	F	øG	Η
ZH05DS-01-01-01	73.5	14.5	41.5	29.5	Rc1/8	12	3.2	12
ZH05DL-01-01-01	73.5	14.5	41.5	29.5	Rc1/8	12	3.2	12
ZH07DS-01-01-01	76	14.5	41.5	29.5	Rc1/8	12	3.2	12
ZH07DL-01-01-01	76	14.5	41.5	29.5	Rc1/8	12	3.2	12
ZH10DS-01-01-01	82	17.4	44.5	30.5	Rc1/8	12	4.2	12
ZH10DL-01-01-01	86	17.4	44.5	30.5	Rc1/8	12	4.2	12
ZH13DS-01-02-02	94.5	20.2	54	39	Rc1/8	14	4.2	17
ZH13DL-01-02-02	99.5	20.2	54	39	Rc1/8	14	4.2	17
ZH15DS-02-03-03	116.5	22.45	58.5	41	Rc1/4	17	4.2	19
ZH15DL-02-03-03	116.5	22.45	58.5	41	Rc1/4	17	4.2	19

Model	- 1	J	K	L	М	N	0	Р
ZH05DS-01-01-01	12	Rc1/8	31.5	28.5	7.8	Rc1/8	17	24
ZH05DL-01-01-01	12	Rc1/8	31.5	28.5	7.8	Rc1/8	17	24
ZH07DS-01-01-01	12	Rc1/8	31.5	29.5	7.8	Rc1/8	17	24
ZH07DL-01-01-01	12	Rc1/8	31.5	29.5	7.8	Rc1/8	17	24
ZH10DS-01-01-01	14	Rc1/8	33.5	33	9.6	Rc1/8	20	28
ZH10DL-01-01-01	14	Rc1/8	33.5	33	9.6	Rc1/8	20	28
ZH13DS-01-02-02	17	Rc1/4	36.5	38.5	10.7	Rc1/4	22	30
ZH13DL-01-02-02	17	Rc1/4	36.5	38.5	10.7	Rc1/4	22	30
ZH15DS-02-03-03	19	Rc3/8	43	44.5	12	Rc3/8	27	35
ZH15DL-02-03-03	19	Rc3/8	43	44 5	12	Rc3/6	27	35


Screw-in connection



Series ZH

Body Ported Style (Without silencer)/ZH18D^S₂-□-□-□, ZH20D^S₂-□-□-□


One-touch connection



Model	Α	В	С	D	øΕ	F	øG	Н
ZH18DS-12-12-12	114	20.95	40.95	30.5	ø12	22	ø3.5	22
ZH18DL-12-12-12	114	20.95	40.95	30.5	ø12	22	ø3.5	22
ZH20DS-12-16-16	124.6	26.5	48.75	35.5	ø12	22	ø3.5	24
ZH20DL-12-16-16	124.6	26.5	48.75	35.5	ø12	22	ø3.5	24

Model	ı	øJ	K	L	M	øΝ	0
ZH18DS-12-12-12	22	ø12	35.5	50	17	ø12	10
ZH18DL-12-12-12	22	ø12	35.5	50	17	ø12	10
ZH20DS-12-16-16	24	ø16	38.5	54.3	21.7	ø16	12
ZH20DL-12-16-16	24	ø16	38.5	54.3	21.7	ø16	12


One-touch and Screw-in connection



Model	Α	В	С	D	øΕ	F	øG	Н
ZH18DS-12-03-12	114	20.95	52.45	42	ø12	22	ø3.5	19
ZH18DL-12-03-12	114	20.95	52.45	42	ø12	22	ø3.5	19
ZH20DS-12-04-16	124.6	26.5	63.75	50.5	ø12	22	ø3.5	24
ZH20DL-12-04-16	124.6	26.5	63.75	50.5	ø12	22	ø3.5	24

Model	ı	J	K	L	M	øΝ	0
ZH18DS-12-03-12	22	Rc3/8	35.5	50	17	ø12	10
ZH18DL-12-03-12	22	Rc3/8	35.5	50	17	ø12	10
ZH20DS-12-04-16	24	Rc1/2	38.5	54.3	21.7	ø16	12
ZH20DL-12-04-16	24	Rc1/2	38.5	54.3	21.7	ø16	12

Screw-in connection





Model	Α	В	С	D	Е	F	øG	Н
ZH18DS-03-03-03	137	20.95	52.45	42	Rc3/8	19	ø3.5	19
ZH18DL-03-03-03	137	20.95	52.45	42	Rc3/8	19	ø3.5	19
ZH20DS-03-04-04	151.1	26.5	63.75	50.5	Rc3/8	19	ø3.5	24
ZH20DL-03-04-04	151.1	26.5	63.75	50.5	Rc3/8	19	ø3.5	24

Model	ı	J	K	L	М	N	0
ZH18DS-03-03-03	19	Rc3/8	47	61.5	17	Rc3/8	10
ZH18DL-03-03-03	19	Rc3/8	47	61.5	17	Rc3/8	10
ZH20DS-03-04-04	24	Rc1/2	50	69.3	21.7	Rc1/2	12
ZH20DL-03-04-04	24	Rc1/2	50	69.3	21.7	Rc1/2	12

Vacuum Ejector/Series

Application Circuit Example





Diagrams a to d show the combination with peripherals.

⚠ Caution

Handling of application circuits

①Countermeasures for power outages

Select a supply valve for the ejector that is normally open or one that is equipped with a self-holding function.

②Using a small-diameter picking nozzle

For picking electronic parts or small precision parts, if the picking nozzle is approximately ø1mm in diameter, the vacuum remains high by being restricted by the nozzle. As a result, it will not be possible to verify it with the vacuum switch. In such a case, it is necessary to use an ejector that is suited to the nozzle and to select a vacuum switch with a favourable hysteresis and precision.

3Considerable leakage from the suction surface

If the workpiece is made of porous material or if there is air leakage from the area between the pad and the workpiece, use a nozzle with a large diameter and a large suction flow volume. If the amount of leakage is known based on the effective sectional area of the side with the leakage, the vacuum pressure can be estimated in accordance with the ejector's flow volume characteristics.

4 Suction filter

To protect the ejectors and valves from dust, the use of a suction filter (ZFA, ZFB series) is recommended.

5Use of a vacuum switch

It is recommended that verification be made with a vacuum switch as much as possible.

6 Vacuum release valve

To serve as a vacuum release valve, use a 2 port or 3 port valve. As for the performance of the valve, select a valve for a low vacuum. In addition, add a needle valve that can regulate the flow volume of the vacuum releasing air. Use the atmospheric pressure or a positive pressure for the vacuum releasing pressure.

ZX

ZR

ZΜ

ZY

ZH

ZU ZL

ZF

ZP

ZCU

CYV

Vacuum related