
3-Screen Display

High-Precision Digital Pressure Switch





RoHS

Setting is possible while checking

Main screen

Measured value (Current pressure value)

the measured value.


Sub screen

Label (Display item), Set value (Threshold value)



settings





e l							Piping	
Applicable fluid	Series	Output type	Enclosure	Copy function	M5 female thread	1/8 (R, NPT)	One-touch fittings (Ø 4 mm, Ø 6 mm, Ø 1/4 inch)	1/4 (R, NPT, G) (URJ*1/TSJ*2)
	ZSE20(F)/ ISE20 p. 9	1 output	IP40	_	•	•	•	_
Air	ZSE20A(F)/ ISE20A p.11	2 outputs Analogue output (Voltage/Current)	IP40	•	•	•	•	_
	ZSE20B(F)-(L)/ ISE20B-(L)	2 outputs Analogue output (Voltage/Current)	IP65	•			*5	_
	p. 13, 15	IO-Link/ Switch: 1 output		*4			_	
General	ZSE20C(F)/ ISE20C(H) p. 24	2 outputs Analogue output (Voltage/Current)	IP65	•	*3	(Rc thread only)	_	•


- *1 Face seal fitting *2 Compression fitting *3 With 1/4 (R, NPT, G) M5 female threaded
- *4 A block parameter or data storage function is provided with the IO-Link compatible type.
- *5 Only the Ø 4 mm or Ø 6 mm elbow type One-touch fitting is applicable.





Improved Operability


Visualization of Settings The sub screen (label) shows the item to be set. ZSE20 (F)/ISE20 Current model Switches between displays




Simple 3-Step Setting

Always lisplaye on one screen


When the S button is pressed and the set value (P_1) is being displayed, the set value (threshold value) can be set. When the S button is pressed and the hysteresis (H_1) is being displayed, the hysteresis value can be set.






Easy Screen Switching


It is possible to change the settings while checking the measured value.





- st One additional arbitrary display mode can be added via the function settings. (Refer to p. 3.)
- * Example for 1 output







Improved Operability

Other Sub Screen Display

The peak value or bottom value, or both values can be displayed on one screen!

* Peak and bottom values are maintained even if the power supply is cut.





* A combination of the displays shown above and the set values can be displayed on the 2 sub screens.

Delay Time 1.5 ms or less

*1 Select from 1.5 ms or less, 20 ms, 100 ms, 500 ms, 1000 ms, 2000 ms, or 5000 ms.

Convenient Functions

p. **17, 26**

Functions	Copy function	Auto-shift function	Security code	Power saving mode	Resolution switch function	MPa/kPa switch function
20	_	_	•	•	•	•
20A	•	•	•	•	•	•
20B	•	•	•	•	•	•
20B-L	_	_	•	•	•	•
20C	•	•	•	•	•	•

Copy function

The settings of the master sensor can be copied to the slave sensors.



Auto-shift function

This measures the pressure at the time of external input and uses it as a reference to correct the on-off point of the switch.

Security code

The key locking function keeps unauthorized persons from tampering with the settings.

Power saving mode

Power consumption is reduced by turning off the monitor.

Series	Current consumption	Reduction rate*1		
20	25 mA or less	Approx. 60 % reduction		
20A		40.0/		
20B(-L)	35 mA or less	Approx. 40 % reduction		
20C		reduction		

*1 In power saving mode

Display resolution switch function

Reduces monitor flickering



(Only the displayed values are changed; the accuracy remains the same.)

MPa/kPa switch function

Vacuum, compound, and/or positive pressure can be displayed in MPa or kPa.













Compact & Lightweight






Improved Installability




Enclosure



Mounting


Available Mounting Options

	0 1			
Series	Bracket A	Bracket B	Bracket C	Panel mount
20	•	•	_	•
20A	•	•	_	•
20B(-L)	•	•	_	•
20C	•	_	•	•



IO-Link Compatible ZSE20B(F)-L/ISE20B-L 5.15

Visualization of operation/equipment status/Remote monitoring and control by communication



Configuration File (IODD File*1)

•Manufacturer •Product part no. •Set value

*1 IODD File:

IODD is an abbreviation of IO Device Description. This file is necessary for setting the device and connecting it to a master. Save the IODD file on the PC to be used to set the device prior to use.



IO-Link is an open communication interface technology between the sensor/actuator and the I/O terminal that is an international standard, IEC61131-9.



IO-Link Compatible Device ZSE20B(F)-L/ISE20B-L

Diagnosis items

· Internal product malfunction

· Outside of zero-clear range

Outside of rated pressure range
 Upper temperature limit

exceeded inside the product

Read the device data.

- Switch ON/OFF signal and analogue value
- Device information:
- Manufacturer, Product part number, Serial number, etc.
- Normal or abnormal device status
- Cable breakage



IO-Link Master

0-0

0-0

Implement diagnostic bits in the process data.

The diagnostic bit in the cyclic process data makes it easy to find problems with the equipment.

Device settings

master.

etc.

•Threshold value

Operation mode,

can be set by the

It is possible to find problems with the equipment in real time using the cyclic (cycle) data and to monitor such problems in detail with the noncyclic (aperiodic) data.

Process Data

Bit offset	Item	Note
0	OUT1 output	0: OFF 1: ON
1	OUT2 output	0: OFF 1: ON
2	Diagnosis	0: Normal 1: Abnormal
3 to 15	Measured pressure value	Unsigned 13 bit

Bit offset	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Item		Measured pressure value										Diagnosis	OUT2	OUT1		

Display function

Displays the output communication status and indicates the presence of communication data









Operation and Display

Communication with master		status or light	Status		us	Screen display*3	Description	
		*2		- E	Operate	ModE oPE	Normal communication status (readout of measured value)	
				Normal	Start up	ModE Strt	At the start of communication	
	0.015			_	Preoperate		At the start of communication	
Yes	*2 IO-Link mode	Version does not match	Er 15	IO-Link version does not match that of the master. The master uses version 1.0. * The applicable IO-Link version is 1.1.				
		(Flashing)		Abnormal	Lock	ModE LoC	Back-up and re-store required due to data storage lock	
No	OFF			Abn	Communication disconnection	ModE oPE ModE Strt ModE PrE	Normal communication was not received for 1 second or longer.	
		OFF	S	IO n	node	ModE 5 io	General switch output	

^{*1} The COM indicator is ON when communication with the master is established. *2 In IO-Link mode, the IO-Link indicator is ON or flashes. *3 When the sub screen is set to Mode

For General Fluids ZSE20C(F)/ISE20C(H) p.24

Stainless Diaphragm

Oil-free (Single-layer diaphragm structure)

Sensor unit: Stainless steel 630 Fitting parts: Stainless steel 304

A stainless steel 316L option is also available for the sensor unit and fitting parts.



Enclosure: IP65

Leakage

1 x 10⁻¹⁰ Pa·m³/s

<Face seal and compression fitting>

1 x 10⁻⁵ Pa·m³/s

<Threaded type (R, Rc, NPT, G)>

Select from 2 Piping Directions.





Welded structure for sensor units and fitting parts


Select from a face seal or compression fitting.

Face seal






Confirmation of the atmospheric pressure of a load lock chamber



Applicable Fluid Examples

- Hydraulic fluid (JIS-K2213)
- Silicone oil (JIS-K2213)
- Lubricant (JIS-K6301)
- Fluorocarbon
- Argon
- Carbon dioxide
- Air-containing drainage
- Nitrogen

Applications








Made to Order

Parts in Contact with Fluid: Stainless Steel 316L


This pressure switch has increased corrosion resistance due to the use of stainless steel 316L for the parts in contact with fluid (pressure sensor and fitting).

Restrictor-installed Fitting (-X510)

A pressure switch that has a restrictor installed in the fitting is available to prevent the sensor from being damaged by water hammer or fluid inertia. (Refer to p. 38 for details.)



Introduction of Series




CONTENTS

3-Screen Display High-Precision Digital Pressure Switch ZSE20(F)/ISE20 Series

3-Screen Display High-Precision Digital Pressure Switch ZSE20A(F)/ISE20A Series

How to Order ·····	p.	11
Specifications ·····	p.	12
Set Pressure Range and Rated Pressure Range	p.	17
Analogue Output ······	p.	17
IO-Link: Process Data ·····	p.	17
Functions ·····	p.	17
Internal Circuits and Wiring Examples	p.	18
Dimensions	n	20



^{*4 1} output in SIO mode (NPN or PNP switching type)

3-Screen Display High-Precision Digital Pressure Switch ZSE20B(F)/ISE20B Series

How to Order ·····	p.	1	3
Specifications	p.	1	4

3-Screen Display High-Precision Digital Pressure Switch/ **IO-Link Compatible**

ZSE20B(F)-L/ISE20B-L Series

How to Order ·····	p. 1	15
Specifications ·····	p. 1	16
Set Pressure Range and Rated Pressure Range	p. 1	17
Analogue Output ······	p. 1	17
IO-Link: Process Data ·····	p. 1	17
Functions ·····	p. 1	17
Internal Circuits and Wiring Examples		
Dimensions ·····	p. 2	20

3-Screen Display High-Precision Digital Pressure Switch for General Fluids

ZSE20C(F)/ISE20C(H) Series

How to Order ·····	p. 24
Specifications ·····	p. 25
Set Pressure Range and Rated Pressure Rang	e p. 26
Analogue Output	p. 26
Functions	p. 26
Internal Circuits and Wiring Examples	p. 27
Dimensions	p. 28
	·
unction Details	p. 34
Made to Order	p. 38
Safety Instructions	Back cover




^{*5} This function is not provided with the IO-Link compatible type.

1 Output

3-Screen Display High-Precision Digital Pressure Switch

ZSE20(F)/ISE20 Series



Rated pressure range

For positive pressure

For vacuum/

compound pressure

ZSE20	0 to -101 kPa
ZSE20F	-100 to 100 kPa

2 Output specification

Symbol	Description			
N	NPN open collector 1 output			
Р	PNP open collector 1 output			

3 Unit specification

Symbol	Description			
 Units selection function 				
M SI unit only*1				
Р	Units selection function (Initial value psi)			

*1 Fixed unit: kPa, MPa

4 Piping specification

<u> </u>	i iping specification						
Symbol	Description	Symbol	Description				
	M5 female thread	C4H	One-touch fitting Ø 4 mm	Straight type			
M5		С6Н	One-touch fitting Ø 6 mm				
	Piping port	N7H	One-touch fitting Ø 1/4 inch				
01	R1/8	C4L	One-touch fitting Ø 4 mm	Elbow type			
		C6L	One-touch fitting Ø 6 mm				
	R1/8 Piping adapter ZS-46-N1	N7L	One-touch fitting Ø 1/4 inch				
	NPT1/8	* One-touch fitting is shipped together with the					
	A	product.					

5 Option 1

Symbol	Description					
_	Without lead	Without lead wire				
L	Lead wire with connector (3-core, 2 m lead wire)	ZS-46-3L Without waterproof cover				

* For the lead wire with M12 connector, refer to p. 38.

7 Option 3

Symbol	Operation manual*1	Calibration certificate*1
_	0	_
Υ	_	_
K	0	0
T	_	0

(RoHS)

*1 All texts are in both English and Japanese.

6 Option 2

Symbol	Description						
_	None						
A1	Bracket A (Vertical mounting)	ZS-46-A1					
A2	Bracket B (Horizontal mounting)	ZS-46-A2					
В	Panel mount adapter	ZS-46-B					
D	Panel mount adapter + Front protection cover	ZS-46-D					

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Description	Part no.	Note
Bracket A	ZS-46-A1	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
Bracket B	ZS-46-A2	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
Panel mount adapter	ZS-46-B	_
Panel mount adapter + Front protection cover	ZS-46-D	_
Lead wire with connector	ZS-46-3L	3-core, 2 m, Non-waterproof (Without waterproof cover)
Lead wire with M12 connector (Made to Order)	ZS-46-5LM12	
Front protection cover	ZS-27-01	_
R1/8 Piping adapter	ZS-46-N1	R1/8 NPT1/8
NPT1/8 Piping adapter	ZS-46-N2	
One-touch fitting Ø 4 mm straight	ZS-46-C4H	_
One-touch fitting Ø 6 mm straight	ZS-46-C6H	_
One-touch fitting Ø 1/4 inch straight	ZS-46-N7H	_
One-touch fitting Ø 4 mm elbow	ZS-46-C4L	_
One-touch fitting Ø 6 mm elbow	ZS-46-C6L	_
One-touch fitting Ø 1/4 inch elbow	ZS-46-N7L	_

3-Screen Display High-Precision Digital Pressure Switch ZSE20(F)/ISE20 Series

Specifications

For details on the specific product precautions, refer to the "Operation Manual" on the SMC website.

	Mo	odel	ZSE20 (Vacuum pressure)	ZSE20F (Compound pressure)	ISE20 (Positive pressure)		
Applicable fluid			Air, Non-corrosive gas, Non-flammable gas				
	Rated pre	ssure range	0.0 to -101.0 kPa	-100.0 to 100.0 kPa	-0.100 to 1.000 MPa		
Pressure	Display/Se	et pressure range	10.0 to -105.0 kPa	-105.0 to 105.0 kPa	-0.105 to 1.050 MPa		
Pressure	Display/Smallest settable increment		0.1	kPa	0.001 MPa		
	Withstand	l pressure	500	kPa	1.5 MPa		
	Power sup	oply voltage	12 to 2	4 VDC ±10 %, Ripple (p-p) 10 %	or less		
Power supply	Current co	onsumption		25 mA or less			
	Protection	1		Polarity protection			
	Display ac	ccuracy	±2 % F.S.	±1 digit (Ambient temperature of	25 ±3 °C)		
Accuracy	Repeatabi	ility		±0.2 % F.S. ±1 digit			
	Temperatu	ure characteristics		±2 % F.S. (25 °C standard)			
	Output typ	·		PN or PNP open collector 1 outp			
	Output mo	ode	Hysteresis mode, V	Vindow comparator mode, Error o	output, Output OFF		
	Switch op	eration		Normal output, Reversed output			
	Max. load			80 mA			
Switch output		ied voltage (NPN only)	28 V				
Switch output		Itage drop (Residual voltage)	1 V or less (at load current of 80 mA)				
	Delay time		1.5 ms or less (with anti-chattering function: 20, 100, 500, 1000, 2000, 5000 ms)				
	Hysteresis mode Window comparator mode			Variable from 0*2			
		uit protection	Yes				
	Unit*3		MPa, kPa, kgf/cm², l	oar, psi, inHg, mmHg	MPa, kPa, kgf/cm², bar, psi		
	Display ty	•		LCD			
	Number o	f screens	3-screen display (Main screen, Sub screen x 2)				
Display	Display co	olour		 Main screen: Red/Green Sub screen: Orange 			
	Number o	f display digits	Main screen: 4 digits (7 segments) Sub screen: 4 digits (Upper 1 digit 11 segments, 7 segments for other)				
	Indicator I	light	Lights up wh	en switch output is turned ON. O	UT1: Orange		
Digital filter*4				, 10, 50, 100, 500, 1000, 5000 m			
	Enclosure)		IP40			
	Withstand	l voltage	1000 VAC for 1 minute between terminals and housing				
Environment	Insulation	resistance	50 MΩ or more (500 VDC n	neasured via megohmmeter) betw	ween terminals and housing		
	Operating	temperature range	Operating: -5 to 50 °	C, Stored: -10 to 60 °C (No conde	ensation or freezing)		
	Operating	humidity range		ensation)			
Standards			UL/CSA (E216656), CE marking (EMC directive/RoHS directive)				
Length of lead	wire with c	onnector	2 m				
. 4. Malura militarus	E 2 1 CD	(1 0)					

- *1 Value without digital filter (at 0 ms)
- *2 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value greater than the amount of fluctuation, or chattering will occur.
- *3 Setting is only possible for models with the units selection function. Only MPa or kPa is available for models without this function.
- *4 The response time indicates when the set value is 90 % in relation to the step input.
- * Products with tiny scratches, marks, or display colour or brightness variations which do not affect the performance of the product are verified as conforming products.

Piping Specifications and Weights

		9								
	Model	M5	01	N01	C4H	C6H	N7H	C4L	C6L	N7L
Port size		M5 x 0.8	R1/8	NPT1/8	_	_	_	_		_
	One-touch fitting Straight type	_	_	_	Ø 4 mm Ø 5/32 inch	Ø 6 mm	Ø 1/4 inch		_	
	One-touch fitting Elbow type	_	_	_	_	_	_	Ø 4 mm Ø 5/32 inch	Ø 6 mm	Ø 1/4 inch
	Sensor pressure receiving area		Silicon							
Materials of	Piping port (Common)		PBT, CB156, Heat-resistant PPS, O-ring: HNBR							
parts in contact with fluid	Piping port		C3604 (Electroless nickel plating), Stainless steel POM, Stainless steel 304, NBR, C3604 304, NBR							
Weight	Body	22 g	32 g	34 g	25 g	26 g	27 g	28 g	28 g	34 g
weignt	Lead wire with connector					+35 g				·

Cable Specifications

Conductor area		0.15 mm² (AWG26)		
Insulator	O.D.	1.0 mm		
	Colour	Brown, Blue, Black (3-core)		
Sheath	Finished O.D.	Ø 3.4		

"Set Pressure Range and Rated Pressure Range," "Functions" ⇒ p. 17
"Internal Circuits and Wiring Examples" ⇒ p. 18 "Dimensions" ⇒ From p. 20



2 Outputs + Analogue Output (Voltage/Current)

3-Screen Display High-Precision Digital Pressure Switch

ZSE20A(F)/ISE20A Series







RoHS)

For positive pressure **SE**

ISE20A - X - M - M5 - X - M - M

Made to Order

(p. 39)

Description

Conversion cable for the Z/ISE30A lead wire with connector

Rated pressure range

For vacuum/

compound pressure

	<u>. </u>
ZSE20A	0 to -101 kPa
ZSE20AF	-100 to 100 kPa

2 Output specification

Rated pressure range ISE20A -0.1 to 1 MPa

Symbol	Description
R	NPN open collector 2 outputs + Analogue voltage output *1
S	NPN open collector 2 outputs + Analogue current output *1
Т	PNP open collector 2 outputs + Analogue voltage output*1
V	PNP open collector 2 outputs + Analogue current output *1
X	NPN open collector 2 outputs + Copy function
Υ	PNP open collector 2 outputs + Copy function

*1 Can be switched to auto-shift or copy function

3 Unit specification

Symbol	Description			
_	Units selection function			
M	SI unit only*1			
Р	Units selection function (Initial value psi)			

*1 Fixed unit: kPa, MPa

4 Piping specification

IPT1/8 Piping adapte

<u> </u>	or iping opeomounen						
Symbol	Description	Symbol	Description	า			
	M5 female thread	C4H	One-touch fitting Ø 4 mm	Straight type			
M5		С6Н	One-touch fitting Ø 6 mm				
	Piping port	N7H	One-touch fitting Ø 1/4 inch				
	R1/8	C4L	One-touch fitting Ø 4 mm	Elbow type			
01		C6L	One-touch fitting Ø 6 mm				
	R1/8 Piping adapter ZS-46-N1	N7L	One-touch fitting Ø 1/4 inch				
	NPT1/8		ne-touch fitting is shipped to oduct.	ogether with the			

5 Option 1

Symbol	Description				
_	Without lead	l wire			
L	Lead wire with connector (3-core, 2 m lead wire)	ZS-46-3L Without waterproof cover			

 For the lead wire with M12 connector, refer to p. 38.

Option 3

Symbol	Operation manual*1	Calibration certificate*1
_	0	_
Υ	_	_
K	0	0
T	_	0

*1 All texts are in both English and Japanese.

6 Option 2

Symbol	[Description
	None	·
A1	Bracket A (Vertical mounting)	ZS-46-A1
A2	Bracket B (Horizontal mounting)	ZS-46-A2
В	Panel mount adapter	ZS-46-B
D	Panel mount adapter + Front protection cover	ZS-46-D

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

		-
Description	Part no.	Note
Bracket A	ZS-46-A1	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
Bracket B	ZS-46-A2	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
Panel mount adapter	ZS-46-B	_
Panel mount adapter + Front protection cover	ZS-46-D	_
Lead wire with connector	ZS-46-5L	5-core, 2 m, Non-waterproof (Without waterproof cover)
Lead wire with M12 connector (Made to Order)	ZS-46-5LM12	
Front protection cover	ZS-27-01	_
R1/8 Piping adapter	ZS-46-N1	R1/8 NPT1/8
NPT1/8 Piping adapter	ZS-46-N2	
One-touch fitting Ø 4 mm straight	ZS-46-C4H	_
One-touch fitting Ø 6 mm straight	ZS-46-C6H	_
One-touch fitting Ø 1/4 inch straight	ZS-46-N7H	_
One-touch fitting Ø 4 mm elbow	ZS-46-C4L	_
One-touch fitting Ø 6 mm elbow	ZS-46-C6L	_
One-touch fitting Ø 1/4 inch elbow	ZS-46-N7L	_

3-Screen Display High-Precision Digital Pressure Switch ZSE20A(F)/ISE20A Series

Specifications

For details on the specific product precautions, refer to the "Operation Manual" on the SMC website.

	Mo	odel	ZSE20A (Vacuum pressure)	ZSE20AF (Compound pressure)	ISE20A (Positive pressure)	
Applicable fluid	d			lon-corrosive gas, Non-flammabl		
11		essure range	0.0 to -101.0 kPa	-100.0 to 100.0 kPa	-0.100 to 1.000 MPa	
_		et pressure range	10.0 to -105.0 kPa	-105.0 to 105.0 kPa	-0.105 to 1.050 MPa	
Pressure	Display/Smallest settable increment		0.1	kPa	0.001 MPa	
	Withstand pressure		500	500 kPa 1.5 MP		
	Power su	pply voltage	12 to 2	4 VDC ±10 %, Ripple (p-p) 10 %	or less	
Power supply		onsumption	35 mA or less			
	Protection	n .	Polarity protection			
	Display accuracy		±2 % F.S.	±1 digit (Ambient temperature of	25 ±3 °C)	
	Repeatab			±0.2 % F.S. ±1 digit	,	
Accuracy		output accuracy	±2.5 %	F.S. (Ambient temperature of 25	i ±3 °C)	
•		output linearity		±1 % F.S.	,	
	Temperat	ure characteristics		±2 % F.S. (25 °C standard)		
	Output ty		NF	PN or PNP open collector 2 output	uts	
	Output m			Vindow comparator mode, Error		
	Switch op			Normal output, Reversed output		
	Max. load			80 mA		
Outlieb :		ied voltage (NPN only)		28 V		
Switch output		oltage drop (Residual voltage)	1	V or less (at load current of 80 m	A)	
	Dolay time	o*1	1.5 ms or less (with anti	-chattering function: 20, 100, 500	0. 1000. 2000. 5000 ms)	
	Hysteresis mode Window comparator mod		·			
	Hysteresis Window comparator mode		Variable from 0*2			
	Short circuit protection		Yes			
	Voltage Output type		Voltage out	out: 1 to 5 V	Voltage output: 0.6 to 5 V	
	output	Output impedance		Approx. 1 kΩ		
Analogue		Output type	Current output: 4 to 20 mA Currer		Current output: 2.4 to 20 mA	
output	Current		Maximum load impedance at power supply voltage of 12 V: 300 Ω			
•	output	Load impedance	at power supply voltage of 24 V: 600 Ω			
	-	•	Minimum load impedance: 50 Ω			
	Input type			Non-voltage input: 0.4 V or less		
Auto-shift	Input mod		Select from Auto-shift or Auto-shift zero.			
input	Input time	•	5 ms or more			
	Unit*3		MPa, kPa, kgf/cm², k	par, psi, inHg, mmHg	MPa, kPa, kgf/cm2, bar, psi	
	Display ty	/pe	LCD			
	Number o	of screens	3-screen display (Main screen, Sub screen x 2)			
Diamlau	Dianles	alour .	1) Main screen: Red/Green			
Display	Display co	biour	2) Sub screen: Orange			
	Managhan	d diamin, dinit-	1) Main screen: 4 di	gits (7 segments)		
	Number o	of display digits	2) Sub screen: 4 digits (Upper 1 digit 11 segments, 7 segments for other)			
Indicator light		Lights up when switch output is turned ON. OUT1, OUT2: Orange				
Digital filter*4		0, 10, 50, 100, 500, 1000, 5000 ms				
_	Enclosure	9		IP40		
	Withstand	d voltage	1000 VAC for 1 minute between terminals and housing			
Environment		n resistance	$50 \text{ M}\Omega$ or more (500 VDC measured via megohmmeter) between terminals and housing			
		temperature range	Operating: -5 to 50 °C, Stored: -10 to 60 °C (No condensation or freezing)			
		humidity range	Operating/Stored: 35 to 85 %RH (No condensation)			
Standards		, , , , , , , , , , , , , , , , , , ,	UL/CSA (E216656), CE marking (EMC directive/RoHS directive)			
Length of lead	wire with c	connector		2 m	,	
4 1/ 1 '11 1			L			

*1 Value without digital filter (at 0 ms)

*2 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value greater than the amount of fluctuation, or chattering will occur.

*3 Setting is only possible for models with the units selection function. Only MPa or kPa is available for models without this function.
*4 The response time indicates when the set value is 90 % in relation to the step input.

Piping Specifications and Weights

<u> </u>										
	Model	M5	01	N01	C4H	C6H	N7H	C4L	C6L	N7L
Port size		M5 x 0.8	R1/8	NPT1/8	_	_	_	_	_	_
	One-touch fitting Straight type	1	1	_	Ø 4 mm Ø 5/32 inch	Ø 6 mm	Ø 1/4 inch	_	-	-
	One-touch fitting Elbow type	-	_	_	_	_	_	Ø 4 mm Ø 5/32 inch	Ø 6 mm	Ø 1/4 inch
Matariala af	Sensor pressure receiving area		Silicon							
Materials of	Piping port (Common)		PBT, CB156, Heat-resistant PPS, O-ring: HNBR							
parts in contact with fluid	Piping port	_	C3604 (Electroless nickel plating), Stainless steel 304, NBR, C3604 304, NBR							
Waight	Body	24 g	34 g	36 g	27 g	28 g	29 g	30 g	30 g	36 g
Weight	Lead wire with connector		+39 g							

Cable Specifications

Conductor area		0.15 mm ² (AWG26)
Insulator	O.D.	1.0 mm
	Colour	Brown, Blue, Black, White, Grey (5-core)
Sheath	Finished O.D.	Ø 3.5

"Set Pressure Range and Rated Pressure Range," "Functions" ⇒ p. 17 "Internal Circuits and Wiring Examples" → From p. 18 "Dimensions" → From p. 20



^{*} Products with tiny scratches, marks, or display colour or brightness variations which do not affect the performance of the product are verified as conforming products.

2 Outputs + Analogue Output (Voltage/Current)

3-Screen Display High-Precision **Digital Pressure Switch**

ZSE20B(F)/ISE20B Series



How to Order





RoHS)

For positive pressure

For vacuum/

compound pressure

Rated pressure range

ZSE20B	0 to -101 kPa
ZSE20BF	-100 to 100 kPa

2 Output specification

Rated pressure range **ISE20B** -0.1 to 1 MPa

Symbol	Description
R	NPN open collector 2 outputs + Analogue voltage output *1
S	NPN open collector 2 outputs + Analogue current output *1
Т	PNP open collector 2 outputs + Analogue voltage output *1
V	PNP open collector 2 outputs + Analogue current output *1
X	NPN open collector 2 outputs + Copy function
Υ	PNP open collector 2 outputs + Copy function

*1 Can be switched to auto-shift or copy function

Elbow type

Unit specification

Symbol	bol Description		
_	 Units selection function 		
M	SI unit only*1		
Р	Units selection function (Initial value psi)		

^{*1} Fixed unit: kPa, MPa

Piping specification

Symbol	Description	Syr	nbol
M5	M5 female thread	Ċ	4L
IVIO	Piping port	С	6L
	R1/8	*	Or
01	R1/8 Piping adapter ZS-46-N1		pro
	NPT1/8		
N01	NPT1/8 Piping adapter ZS-46-N2		

 One-touch fitting is shipped together with the product.

One-touch fitting Ø 4 mm

One-touch fitting Ø 6 mm

Description

Ontion 1

Option i				
Symbol		Description		
_	Without lead	l wire		
L	Lead wire with connector (3-core, 2 m lead wire)	ZS-46-3L Without waterproof cover		

For the lead wire with M12 connector, refer to p. 38.

Option 3

Symbol	Operation manual*1	Calibration certificate*1	
_	0	_	
Υ	_	_	
K	0	0	
Т	_	0	

All texts are in both English and Japanese.

Option 2					
Symbol	Description				
_	None				
A 1	Bracket A (Vertical mounting)	ZS-46-A1			
A2	Bracket B (Horizontal mounting)	ZS-46-A2			
В	Panel mount adapter	ZS-46-B			
D	Panel mount adapter + Front protection cover	ZS-46-D			

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Description	Part no.	Note
Bracket A	ZS-46-A1	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
Bracket B	ZS-46-A2	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
Panel mount adapter	ZS-46-B	_
Panel mount adapter + Front protection cover	ZS-46-D	_
Lead wire with connector	ZS-46-5F	5-core, 2 m, Waterproof (With waterproof cover)
Lead wire with M12 connector (Made to Order)	ZS-46-5LM12	
Front protection cover	ZS-27-01	_
R1/8 Piping adapter	ZS-46-N1	R1/8 NPT1/8
NPT1/8 Piping adapter	ZS-46-N2	
One-touch fitting Ø 4 mm elbow	ZS-46-C4L	_
One-touch fitting Ø 6 mm elbow	ZS-46-C6L	_

3-Screen Display High-Precision Digital Pressure Switch ZSE20B(F)/ISE20B Series

Specifications

For details on the specific product precautions, refer to the "Operation Manual" on the SMC website.

	Mo	odel	ZSE20B (Vacuum pressure)	ZSE20BF (Compound pressure)	ISE20B (Positive pressure)	
Applicable fluid			on-corrosive gas, Non-flammabl			
••	Rated pressure range		0.0 to -101.0 kPa	-100.0 to 100.0 kPa	-0.100 to 1.000 MPa	
_	Display/Set pressure range		10.0 to -105.0 kPa	-105.0 to 105.0 kPa	-0.105 to 1.050 MPa	
Pressure	Display/Smallest settable increment		0.1	kPa	0.001 MPa	
	Withstand	d pressure	500	kPa	1.5 MPa	
	Power su	pply voltage	12 to 2	4 VDC ±10 %, Ripple (p-p) 10 %	or less	
Power supply	Current consumption		35 mA or less			
	Protection	n .	Polarity protection			
	Display accuracy		±2 % F.S. ±1 digit (Ambient temperature of 25 ±3 °C)			
	Repeatab	ility		±0.2 % F.S. ±1 digit	•	
Accuracy	Analogue	output accuracy	±2.5 %	F.S. (Ambient temperature of 25	i ±3 °C)	
	Analogue	output linearity		±1 % F.S.		
	Temperat	ure characteristics		±2 % F.S. (25 °C standard)		
	Output ty	ре	NF	PN or PNP open collector 2 outp	uts	
	Output m	ode	Hysteresis mode, V	Vindow comparator mode, Error	output, Output OFF	
	Switch op	eration		Normal output, Reversed output		
	Max. load	current		80 mA		
Outlieb 1	Max. appl	ied voltage (NPN only)		28 V		
Switch output	Internal vo	Itage drop (Residual voltage)	1'	V or less (at load current of 80 m	A)	
	Delay time	e*1	1.5 ms or less (with anti	-chattering function: 20, 100, 500	0, 1000, 2000, 5000 ms)	
		Hysteresis mode	,	24 1 1 1 4 200	,	
	Hysteresis Hode Window comparator mode		Variable from 0*2			
	Short circuit protection			Yes		
	Voltage Output type		Voltage out	out: 1 to 5 V	Voltage output: 0.6 to 5 V	
	output	Output impedance		Approx. 1 kΩ	, .	
Analogue	·	Output type	Current outpu	ıt: 4 to 20 mA	Current output: 2.4 to 20 mA	
output	Current output	Load impedance	Maximum load impedance at power supply voltage of 12 V: 300 Ω at power supply voltage of 24 V: 600 Ω Minimum load impedance: 50 Ω			
	Input type			Non-voltage input: 0.4 V or less		
Auto-shift	Input mod		Select from Auto-shift or Auto-shift zero.			
input	Input time	9		5 ms or more		
	Unit*3		MPa, kPa, kgf/cm², b	par, psi, inHg, mmHg	MPa, kPa, kgf/cm ² , bar, psi	
	Display type			LCD		
	Number of screens		3-screen display (Main screen, Sub screen x 2)			
Display	Display co	olour	1) Main screen: Red/Green 2) Sub screen: Orange			
	Number of display digits		Main screen: 4 digits (7 segments) Sub screen: 4 digits (Upper 1 digit 11 segments, 7 segments for other)			
Indicator light		Lights up when switch output is turned ON. OUT1, OUT2: Orange				
Digital filter*4		0, 10, 50, 100, 500, 1000, 5000 ms				
Enclosure		9		IP65		
	Withstand	d voltage	1000 VAC for 1 minute between terminals and housing			
Environment	Insulation resistance		50 M Ω or more (500 VDC measured via megohmmeter) between terminals and housing			
	Operating	temperature range	Operating: –5 to 50 °C, Stored: -10 to 60 °C (No condensation or freezing)			
	Operating humidity range		Operating/Stored: 35 to 85 %RH (No condensation)			
Standards			UL/CSA (E216656), CE marking (EMC directive/RoHS directive)			
Length of lead	wire with c	onnector	`	2 m	,	
1 Value without	digital filter	(at 0 ms)				

- *1 Value without digital filter (at 0 ms)
- *2 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value greater than the amount of fluctuation, or chattering will occur.
- *3 Setting is only possible for models with the units selection function. Only MPa or kPa is available for models without this function.
- *4 The response time indicates when the set value is 90 % in relation to the step input.
- * Products with tiny scratches, marks, or display colour or brightness variations which do not affect the performance of the product are verified as conforming products.

Piping Specifications and Weights

	Model	M5	01	N01	C4L	C6L
Port size		M5 x 0.8	R1/8	NPT1/8	_	_
	One-touch fitting Straight type				_	
	One-touch fitting Elbow type	1	1	1	Ø 4 mm Ø 5/32 inch	Ø 6 mm
	Sensor pressure receiving area	Silicon				
Materials of	Piping port (Common)	PBT, CB156, Heat-resistant PPS, O-ring: HNBR				
parts in contact with fluid	Piping port		nickel platin	lectroless g), Stainless 4, NBR		nless steel R, C3604
Weight	Body	24 g	34 g	36 g	30 g	30 g
weight	Lead wire with connector			+39 g		

Cable Specifications

Conductor area		0.15 mm² (AWG26)
Insulator	O.D.	1.0 mm
	Colour	Brown, Blue, Black, White, Grey (5-core)
Sheath	Finished O.D.	Ø 3.5


"Set Pressure Range and Rated Pressure Range," "Functions" ⇒ p. 17 "Internal Circuits and Wiring Examples" → From p. 18 "Dimensions" → From p. 20




3-Screen Display High-Precision **Digital Pressure Switch**



ZSE20B(F)-L/ISE20B-L Series



How to Order



Rated pressure range

ZSE20B	0 to -101 kPa
ZSE20BF	-100 to 100 kPa

2	Output	specification
---	--------	---------------

Symbol	Description
L	IO-Link/Switch: 1 output ← (PNP or NPN switching type for switch output)

4 Piping specification

Symbol	Description			
M5	M5 female thread Piping port			
01	R1/8 R1/8 R1/8 Piping adapter ZS-46-N1			
N01	NPT1/8 NPT1/8 Piping adapter ZS-46-N2			

6 Option 1

Symbol		Description
_	Without lead	wire
W	Lead wire with connector (5-core, 2 m lead wire, With waterproof cover)	ZS-46-5F With waterproof cover

* For the lead wire with M12 connector, refer to p. 38.

Option 3

Symbol	Operation manual*1	Calibration certificate*1
_	0	
Υ	_	_
K	0	0
Т	_	0

*1 All texts are in both English and Japanese.

Options/Part Nos.

When only ontional parts are required order with the part numbers listed below

when only optional parts are required, order with the part humbers listed be				
Description	Part no.	Note		
Bracket A	ZS-46-A1	Tapping screw: Nominal size 3 x 8 L (2 pcs.)		
Bracket B	ZS-46-A2	Tapping screw: Nominal size 3 x 8 L (2 pcs.)		
Panel mount adapter	ZS-46-B	_		
Panel mount adapter + Front protection cover	ZS-46-D	_		
Lead wire with connector	ZS-46-5F	5-core, 2 m, Waterproof (With waterproof cover)		
Lead wire with M12 connector (Made to Order)	ZS-46-5LM12			
Front protection cover	ZS-27-01	_		
R1/8 Piping adapter	ZS-46-N1	R1/8 NPT1/8		
NPT1/8 Piping adapter	ZS-46-N2			

6 Option 2

	lion Z	
Symbol		Description
_	None	
A1	Bracket A (Vertical mounting)	ZS-46-A1
A2	Bracket B (Horizontal mounting)	ZS-46-A2
В	Panel mount adapter	ZS-46-B
D	Panel mount adapter + Front protection cover	ZS-46-D

Specifications/IO-Link Compatible

For details on the specific product precautions, refer to the "Operation Manual" on the SMC website.

	Model		ZSE20B-L (Vacuum pressure)	ZSE20BF-L (Compound pressure)	ISE20B-L (Positive pressure)
Applicable fluid		Air, Non-corrosive gas, Non-flammable gas			
Rated pressure range			0.0 to -101.0 kPa -100.0 to 100.0 kPa -0.100 to 1		
_	Display/Set pressure range		10.0 to -105.0 kPa	-105.0 to 105.0 kPa	-0.105 to 1.050 MPa
Pressure		lest settable increment	0.1	kPa	0.001 MPa
	Withstand pre		500	kPa	1.5 MPa
	•	When used as a switch output device			
	Power supply	(When not used as an IO-Link device)	12 to 24 VDC ± 10 % with 10 % voltage ripple or less		
Power supply	voltage	When used as an IO-Link device	18 to 30 VDC, including ripple (p-p) 10 %		
	Current cons	umption		35 mA or less	
	Protection			Polarity protection	
	Display accur	racv	+2 % F.S.	±1 digit (Ambient temperature of	25 +3 °C)
Accuracy	Repeatability			±0.2 % F.S. ±1 digit	
,		characteristics		±2 % F.S. (25 °C standard)	
	Output type		Select	from NPN or PNP open collector	output.
	Output mode			Vindow comparator, Error output	
	Switch operate			Normal output, Reversed output	
	Max. load cur			80 mA	
Switch output	Max. applied	voltage		30 V (NPN output)	
(SIO mode)	Internal voltage	e drop (Residual voltage)	1.5	V or less (at load current of 80 r	nA)
,	Delay time*1	1 (1.5 ms or le	ss, variable from 0 to 60 s/0.01 s	increments
	Hys	steresis mode		Variable from 0*2	
	Window comparator mode Short circuit protection		variable from 0°2		
			Yes		
	Unit*3		MPa, kPa, kgf/cm², bar, psi, inHg, mmHg MPa, kPa, kgf/cm²		MPa, kPa, kgf/cm², bar, psi
	Display type		LCD		
Display	Number of sc		3-screen display (Main screen, Sub screen x 2)		
Diopiay	Display colou		Main screen: Red/Green, Sub screen: Orange		
	Number of dis	. , ,	Main screen: 4 digits (7 segments), Sub screen: 4 digits (Upper 1 digit 11 segments, 7 segments for other)		
	Indicator light	t	Lights up when switch output is turned ON (OUT1, OUT2: Orange)		
Digital filter*4			Variable from 0 to 30 s/0.01 s increments		
Length of lead		ector		2 m	
	Enclosure			IP65	
	Withstand vo		1000 VAC for 1 minute between terminals and housing		
Environment	Insulation res		$50~\text{M}\Omega$ or more (500 VDC measured via megohmmeter) between terminals and housing		
		nperature range		C, Stored: -10 to 60 °C (No cond	
	Operating hu	midity range	Operating	/Stored: 35 to 85 %RH (No cond	densation)
Standards	I			CE, RoHS	
	IO-Link type			Device	
	IO-Link version Communication speed Configuration file		V1.1		
			COM2 (38.4 kbps)		
			IODD file*5		
Communication			2.3 ms		
(IO-Link mode)	Process data		Input data: 2 bytes, Output data: 0 bytes		
		ata communication		Yes	
	Data storage		Yes		
	Event functio	n	Yes		
	Vendor ID		131 (0 x 0083)		

- *1 Value without digital filter (at 0 ms)
- *2 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value greater than the amount of fluctuation, or chattering will occur.
- *3 Setting is only possible for models with the units selection function. Only MPa or kPa is available for models without this function.
- *4 The response time indicates when the set value is 90 % in relation to the step input.
- *5 The configuration file can be downloaded from the SMC website, http://www.smcworld.com
- * Products with tiny scratches, marks, or display colour or brightness variations which do not affect the performance of the product are verified as conforming products.

Piping Specifications and Weights

Model		M5	01	N01
Port size		M5 x 0.8	R1/8	NPT1/8
Materials of nexts in	Sensor pressure receiving area	Silicon		
Materials of parts in contact with fluid	Piping port (Common)	PBT, CB156, Heat-resistant PPS, O-ring: HNBR		
Contact with hulu	Piping port	 C3604 (Electroless nickel plating), Stainless steel 304, No. 		
Weight	Body	24 g	34 g 36 g	
weignt	Lead wire with connector	+39 g		

Cable Specifications

Conductor area		0.15 mm ² (AWG26)	
Insulator	O.D.	1.0 mm	
insulator	Colour	Brown, Blue, Black, White, Grey (5-core)	
Sheath	Finished O.D.	Ø 3.5	

"Set Pressure Range and Rated Pressure Range," "Functions" ⇒ p. 17 "Internal Circuits and Wiring Examples"

p. 19 "Dimensions"

From p. 20




ZSE20□(F)/ISE20□ Series


Set Pressure Range and Rated Pressure Range


Set the pressure within the rated pressure range.


The set pressure range is the range of pressure within which setting is possible. The rated pressure range is the range of pressure that satisfies the specifications (accuracy, linearity, etc.) of the switch. Although it is possible to set a value outside the rated pressure range, the specifications cannot be guaranteed even if the value stays within the set pressure range



Analogue Output*1










*1 Excluding the 20/20B(F)-L

IO-Link: Process Data

Relationship between the process data and pressure value







Functions


Sub screen setting function	The display of the sub screen can be selected.
Auto-preset function	This function calculates a rough set value automatically based on the on-going operation.
Display value fine adjustment function	Evens out deviations in the displayed value
Peak value indication function	Can retain the maximum pressure value displayed during measurement
Bottom value indication function	Can retain the minimum pressure value displayed during measurement
Keylock function (Selectable security code)	The keyboard can be locked to prevent the accidental operation of the operation switch.
Zero-clear function	The pressure display can be set to zero when the pressure is open to the atmosphere.
Error indication function	This function displays the error location and content when a problem or error has occurred.
Anti-chattering function	Prevents possible malfunctions due to sudden fluctuations in the primary pressure by adjusting the delay time
Units selection function	Can convert the display value
Power saving mode	Reduces power consumption
Display resolution switch function	Converts the display resolution from the normal value of 1/1000 to 1/100 Can reduce flickering of the monitor
kPa ↔ MPa switch function	Converts the unit between kPa and MPa
Copy function*1	The settings of the master sensor can be copied to the slave sensors.
Auto-shift function*1	Measures the pressure at the time of external input and uses it as a reference to correct the set value of the switch

^{*1} Not available for the 20/20B-L




Made to Order


Internal Circuits and Wiring Examples




-P PNP (1 output)




-N NPN (1 output)







-X NPN (2 outputs) + Copy function




-Y PNP (2 outputs) + Copy function



-R: NPN (2 outputs) + Analogue voltage output -S: NPN (2 outputs) + Analogue current output




-T: PNP (2 outputs) + Analogue voltage output -V: PNP (2 outputs) + Analogue current output




*1 Refer to p. 37.

ZSE20□(**F**)/**ISE20**□ Series


Internal Circuits and Wiring Examples



- -R: NPN (2 outputs) + Auto-shift input
- -S: NPN (2 outputs) + Auto-shift input




-R: NPN (2 outputs) + Copy function -S: NPN (2 outputs) + Copy function




*1 Refer to p. 37.

-T: PNP (2 outputs) + Auto-shift input -V: PNP (2 outputs) + Auto-shift input



-T: PNP (2 outputs) + Copy function -V: PNP (2 outputs) + Copy function





-L: (IO-Link/Switch: 1 output)

When used as a switch output device (When not used as an IO-Link device = When in SIO mode)

NPN open collector 1 output setting

PNP open collector 1 output setting






When used as an IO-Link device



Made to Order

Dimensions




M5

M5 female thread


If there is a possibility that the atmospheric vent port of the switch will be exposed to water or dust, insert a tube into the atmospheric vent port and route the other end of the tube to a safe place away from water or dust. (Z/ISE20B)

* For tubing, please use the SMC TU 0 4 2 5 (polyurethane, O.D. Ø 4, I.D. Ø 2.5) for the pressure switch.



3-Screen Display High-Precision Digital Pressure Switch $ZSE20 \square (F)/ISE20 \square Series$

Atmospheric vent port 20 4 x Ø 2.6 Depth 7 or less M5 x 0.8 Thread depth 3.5







NPT1/8

Piping specification	Port size	Α
01	R1/8	Width across flats 10
N01	NPT1/8	Width across flats 12

C4H, C6H, N7H


One-touch fitting Straight type \emptyset 4 mm, \emptyset 6 mm, \emptyset 1/4 inch


Piping specification	Α	В
C4H	15.6	Ø8
C6H	16.5	Ø 10
N7H	16	Ø 10.3


C4L, C6L, N7L


One-touch fitting Elbow type \emptyset 4 mm, \emptyset 6 mm, \emptyset 1/4 inch

Piping specification	Α	В	С	D
C4L	15.2	17.5	4	Ø 8.2
C6L	15.2	18.3	4	Ø 10.4
N7L	20.9	20.6	6	Ø 11.1










 \Box

15.2




SMC

$ZSE20\square(F)/ISE20\square$ Series

Dimensions


With bracket





A1


Bracket A

(Part no.: ZS-46-A1)











 The bracket configuration allows for mounting in four orientations.





Bracket B


(Part no.: ZS-46-A2)












 The bracket configuration allows for mounting in four orientations.

3-Screen Display High-Precision Digital Pressure Switch $ZSE20 \square (F)/ISE20 \square Series$


Dimensions


Panel mount adapter






Panel mount adapter (Part no.: ZS-46-B)













Panel mount adapter + Front protection cover (Part no.: ZS-46-D)







SMC








Lead wire with connector












(2000)

$ZSE20\square(F)/ISE20\square$ Series


Dimensions

Panel fitting dimensions


Individual mounting




Multiple (2 pcs. or more) secure mounting <Horizontal>




Panel mount example <Horizontal>



<Vertical>



Panel mount example <Vertical>



RoHS


Made to Order

2 Outputs + Analogue Output (Voltage/Current)

3-Screen Display High-Precision Digital Pressure Switch for General Fluids

ZSE20C(F)/ISE20C(H)

How to Order



Rated pressure range

For positive pressure

For vacuum/ compound pressure

ZSE20C	0 to -101 kPa
ZSE20CF	-100 to 100 kPa

Output specification

Symbol	Description				
R	NPN open collector 2 outputs + Analogue voltage output*1				
S	NPN open collector 2 outputs + Analogue current output*1				
Т	PNP open collector 2 outputs + Analogue voltage output*1				
V	PNP open collector 2 outputs + Analogue current output*1				
X	NPN open collector 2 outputs + Copy function				
Υ	PNP open collector 2 outputs + Copy function				

*1 Can be switched to auto-shift or copy function

4 Piping specification

Symbol	Description					
02	02 R1/4 (M5 female threaded)					
N02	NO2 NPT1/4 (M5 female threaded)					
F02	G1/4 (M5 female threaded)					
C01	Rc1/8					
A2	URJ1/4 (Face seal fitting)					
B2	TSJ1/4 (Compression fitting)					

*2 Fixed unit: kPa, MPa

5 Piping direction

L

3 Unit specification

SI unit only*2

Description Units selection function

Units selection function (Initial value psi)*

Bottom ported

6 Ontion 1

Symbol	Description
	Without lead wire
	Lead wire with connector, 5-core (2 m lead wire, With waterproof cover)
W	With waterproof cover
	ZS-46-5F

^{*} For the lead wire with M12 connector, refer to p. 38.

Options/Part Nos.

when only optional parts are required, order with the part numbers listed below.					
Description	Part no.	Note			
Bracket A	ZS-46-A1	For rear ported/Tapping screw: Nominal size 3 x 8 L (2 pcs.)			
Bracket C	ZS-46-E	For bottom ported/Tapping screw: Nominal size 3 x 10 L (2 pcs.)			
Panel mount adapter	ZS-46-B	Rear ported			
Pariei mount adapter	ZS-35-B	Bottom ported			
Panel mount adapter +	ZS-46-D	Rear ported			
Front protection cover	ZS-35-E	Bottom ported			
Lead wire with connector	ZS-46-5F	5-core, 2 m, Waterproof (With waterproof cover)			
Lead wire with M12 connector (Made to Order)	ZS-46- 5LM12				
Front protection cover	ZS-27-01	Rear ported			
From protection cover	ZS-35-01	Bottom ported			

Option 2

Symbol	
_	None

Poor ported (Dining direction: -

Ų	nea	ar ported (Piping direction: —)							
ı	Symbol	Description		Symbol	Description				
	A 1	Bracket A	ZS-46-A1	В	Panel mount adapter		ZS-46-B		
	D	Panel mount adapter + Front protection cover					ZS-46-D		

Bottom ported (6) Piping direction: L)

		ted (Fibility direction. L)	
Symbo		Description	
А3	Bracket C		ZS-46-E
E	Panel mount adapter		ZS-35-B
F	Panel mount adapter + Front protection cover		ZS-35-E

8 Option 3

Symbol	Operation manual*4	Calibration certificate*4		
_	0	_		
Υ	_	_		
K	0	0		
Т	_	0		

*4 All texts are in both English and Japanese.

9 Made to Order (= n 38)

(-7 p. 50)				
X500	Parts in contact with fluid: Stainless steel 316L			
X510	Restrictor-installed fitting			

ZSE20C(F)/ISE20C(H) Series

Specifications

For details on the specific product precautions, refer to the "Operation Manual" on the SMC website.

	М	odel	ZSE20C (Vacuum pressure)	ZSE20CF (Compound pressure)	ISE20C (Positive pressure)	ISE20CH (Positive pressure)		
Applicable fluid	t		Liquids a	and gases that do not co	rrode stainless steel 630	and 304		
	Rated pressure range		0.0 to -101.0 kPa	-100.0 to 100.0 kPa	-0.100 to 1.000 MPa	-0.100 to 2.000 MPa		
Pressure	Display/S	et pressure range	10.0 to -105.0 kPa	-105.0 to 105.0 kPa	-0.105 to 1.050 MPa	-0.105 to 2.100 MPa		
riessuie	Display/S	mallest settable increment	0.1	kPa	0.001	MPa		
	Withstand	l pressure	500	500 kPa 2 MPa 4 MPa				
	Power su	oply voltage	1.	2 to 24 VDC ±10 % with	10 % voltage ripple or les	SS		
Power supply	Current c	onsumption		35 mA	or less			
	Protection	ı		Polarity p	protection			
	Display a	ccuracy	土	2 % F.S. ±1 digit (Ambier	It temperature of 25 \pm 3 $^{\circ}$ 0	C)		
	Repeatab	ility		±0.2 % F.	S. ±1 digit			
Accuracy	Analogue	output accuracy		±2.5 % F.S. (Ambient to	emperature of 25 ±3 °C)			
	Analogue	output linearity		±1 %	F.S.			
	Temperat	ure characteristics		±3 % F.S. (25	°C standard)			
	Output ty	ре		NPN or PNP open	collector 2 outputs			
	Output m	ode	Hysteresis	mode, Window compara		Output OFF		
	Switch op			Normal output,	Reversed output			
	Max. load				mA			
Switch output		ied voltage (NPN only)		28	3 V			
omiton output		Itage drop (Residual voltage)		1 V or less (at load	d current of 80 mA)			
	Delay time	e*1	1.5 ms or less (with anti-chattering funct	tion: 20, 100, 500, 1000,	2000, 5000 ms)		
	Hysteresis	Hysteresis mode	Variable from 0*2					
	_	Window comparator mode						
	Short circuit protection		Yes					
	Voltage Output type		Voltage out	put: 1 to 5 V	Voltage output: 0.6 to 5 V	Voltage output: 0.8 to 5 V		
	output	Output impedance	Approx. 1 kΩ					
Analogue		Output type	Current outp	ut: 4 to 20 mA	Current output: 2.4 to 20 mA	Current output: 3.2 to 20 mA		
output	Current output	Load impedance	Maximum load impedance at power supply voltage of 12 V: 300 Ω at power supply voltage of 24 V: 600 Ω Minimum load impedance: 50 Ω					
	Input type)		Non-voltage inp	out: 0.4 V or less			
Auto-shift	Input mod	le	Select from Auto-shift or Auto-shift zero.					
input	Input time)		5 ms c	or more			
	Unit*3		MPa, kPa, kgf/cm², l	m², bar, psi, inHg, mmHg MPa, kPa, kgf/cm², bar, psi				
	Display ty	ре	LCD					
	Number o	f screens		3-screen display (Main	screen, Sub screen x 2)			
Display	Display color		Main screen: Red/Green Sub screen: Orange					
	Number of display digits		1) Main screen: 4 digits (7 segments) 2) Sub screen: 4 digits (Upper 1 digit 11 segments, 7 segments for other)					
Indicator light		Lights up when switch output is turned ON (OUT1, OUT2: Orange)						
Digital filter*4				0, 10, 50, 100, 50	0, 1000, 5000 ms			
	Enclosure)	IP65					
	Withstand	l voltage	250 VAC for 1 minute between terminals and housing					
Environment	Insulation	resistance	$2~\text{M}\Omega$ or more (50 VDC measured via megohmmeter) between terminals and housing					
	Operating	temperature range	Operating: -5 to 50 °C, Stored: -10 to 60 °C (No condensation or freezing)					
	Operating	humidity range	Operating/Stored: 35 to 85 %RH (No condensation)					
Standards			UL/CSA (E216656), CE marking (EMC directive/RoHS directive)					
Length of lead wire with connector		onnector	2 m					

- *1 Value without digital filter (at 0 ms)
- *2 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value greater than the amount of fluctuation, or chattering will occur.
- *3 Setting is only possible for models with the units selection function. Only MPa or kPa is available for models without this function.
- $*4\,$ The response time indicates when the set value is 90 % in relation to the step input.
- * Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

Piping Specifications and Weights

ı ıbııış	iping opcomoditions and weights							
Model		02	N02	F02	C01	A2	B2	
Port siz	Port size		NPT1/4	G1/4	Rc1/8	URJ1/4	TSJ1/4	
Materials of parts in contact with fluid		Pressure	sensor: Sta	inless steel	630, Fittin	g: Stainless	steel 304	
	Body (Rear ported)	51 g	51 g	48 g	47 g	54 g	46 g	
Weight	Body (Bottom ported)	77 g	78 g	74 g	65 g	81 g	72 g	
	Lead wire with connector	+39 g						

Cable Specifications

Conductor area		0.15 mm ² (AWG26)		
Inquilator	O.D.	1.0 mm		
insulator	O.D. Colour	Brown, Blue, Black, White, Grey (5-core)		
	Finished O.D.	Ø 3.5		



-101.0 kPa

100.0 kPa


1.000 MPa

2.00 MPa

Set Pressure Range and Rated Pressure Range

Set the pressure within the rated pressure range.

The set pressure range is the range of pressure within which setting is possible. The rated pressure range is the range of pressure that satisfies the specifications (accuracy, linearity, etc.) of the switch. Although it is possible to set a value outside the rated pressure range, the specifications cannot be guaranteed even if the value stays within the set pressure range.



Analogue Output

0.6

C

Pressure

В

Voltage output **Current output** Rated pressure range В For vacuum Analogue output [mA] 0.0 to -101.0 kPa 10.1 kPa 0 Analogue output [V] 20 pressure For compound -100.0 to 100.0 kPa -100.0 kPa -0.100 to 1.000 MPa | -0.100 MPa For positive -0.100 to 2.00 MPa -0.100 MPa*1 *1 Analogue output is 0.8 [V] or 3.2 [mA] at the pressure A.

В


Functions

Sub screen setting function	The display of the sub screen can be selected.	
Auto-preset function	This function calculates a rough set value automatically based on the on-going operation.	
Display value fine adjustment function	Evens out deviations in the displayed value	
Peak value indication function	Can retain the maximum pressure value displayed during measurement	
Bottom value indication function	Can retain the minimum pressure value displayed during measurement	
Key lock function (Selectable security code)	The keyboard can be locked to prevent the accidental operation of the operation switch.	
Zero-clear function	The pressure display can be set to zero when the pressure is open to the atmosphere.	
Error indication function	This function displays the error location and content when a problem or error has occurred.	
Anti-chattering function	Prevents possible malfunctions due to sudden fluctuations in the primary pressure by adjusting the delay time	
Units selection function	Can convert the display value	
Power saving mode	Reduces power consumption	
Display resolution switch function	Converts the display resolution from the normal value of 1/1000 to 1/100	
Display resolution switch function	Can reduce flickering of the monitor	
kPa ↔ MPa switch function	Converts the unit between kPa and MPa	
Copy function	The settings of the master sensor can be copied to the slave sensors.	
Auto-shift function	Measures the pressure at the time of external input and uses it as a reference to correct the set value of the switch	


Pressure

ZSE20C(F)/ISE20C(H) Series


Internal Circuits and Wiring Examples




NPN (2 outputs) + Copy function




-Y PNP (2 outputs) + Copy function




-R: NPN (2 outputs) + Analogue voltage output -S: NPN (2 outputs) + Analogue current output




-T: PNP (2 outputs) + Analogue voltage output -V: PNP (2 outputs) + Analogue current output




-R: NPN (2 outputs) + Auto-shift input -S: NPN (2 outputs) + Auto-shift input




-T: PNP (2 outputs) + Auto-shift input -V: PNP (2 outputs) + Auto-shift input



-R: NPN (2 outputs) + Copy function -S: NPN (2 outputs) + Copy function



-T: PNP (2 outputs) + Copy function -V: PNP (2 outputs) + Copy function



ZSE20(F)/ISE20

Made to Order





If there is a possibility that the atmospheric vent port of the switch will be exposed to water or dust, insert a tube into the atmospheric vent port and route the other end of the tube to a safe place away from water or dust.


* For tubing, please use the SMC TU0425 (polyurethane, O.D. Ø 4, I.D. Ø 2.5) for the pressure switch.

N02 NPT1/4

* If it is expected that the pressure, such as water hammer or surge pressure, will fluctuate rapidly, refer to the precautions in the Operation Manual on the SMC website (http://www.smcworld.com).












F02 G1/4















ZSE20C(F)/ISE20C(H) Series

Dimensions



R1/4


N021 **NPT1/4**


If there is a possibility that the atmospheric vent port of the switch will be exposed to water or dust, insert a tube into the atmospheric vent port and route the other end of the tube to a safe place away from water or dust.

* For tubing, please use the SMC TU0425 (polyurethane, O.D. Ø 4, I.D. Ø 2.5)

for the pressure switch.


* If it is expected that the pressure, such as water hammer or surge pressure, will fluctuate rapidly, refer to the precautions in the Operation Manual on the SMC website (http://www.smcworld.com).


















URJ1/4









Made to Order










Bracket A (Rear ported) (Part no.: ZS-46-A1)












A3


Bracket C (Bottom ported)

(Part no.: ZS-46-E)









ZSE20C(F)/ISE20C(H) Series

Dimensions


Panel mount adapter







Panel mount adapter (Rear ported)

(Part no.: ZS-46-B)













Panel mount adapter (Bottom ported)

(Part no.: ZS-35-B)








32

For the lead wire with M12

connector, refer to p. 38.



(2000)


SMC

ZSE20C(F)/ISE20C(H) Series


Dimensions

<Vertical>

Panel fitting dimensions (Rear ported)




Multiple (2 pcs. or more) secure mounting <Horizontal>




24 or more

Panel mount example <Horizontal>




31 x n pcs. + 3.5 x (n pcs. -1)


Panel mount example <Vertical>




Panel fitting dimensions (Bottom ported)

Multiple (2 pcs. or more) secure mounting <Horizontal>











ZSE20□(F)/ISE20□ Series Function Details

Display examples of the main and sub (set value) screens of each mode. (For ISE20□ (for Positive pressure))









ZSE20 ☐ (F)/ISE20 ☐ Series


Function Details

The $F\Box$ in () shows the function code number. Refer to the operation manual for details about operation procedures and function codes.

A Auto-preset function (F4)

Auto-preset function, when selected in the initial setting, calculates and stores the set value from the measured pressure. For example, if this function is used for suction verification, the optimum set value is determined automatically by performing suction and release of several workpieces.

Suction Verification




 When using with IO-Link, the set values cannot be changed by communication.

Formula for Obtaining the Set Value

P_1 or n_1	H_1
P_1=A-(A-B)/4 n_1=B+(A-B)/4	H_1= (A-B)/2

B Display value fine adjustment function (F6)

Fine adjustment of the indicated value of the pressure sensor can be made within the range of ± 5 % of the read value. (The scattering of the indicated value can be eliminated.)



Indicated value at the time of shipment
 Adjustable range of display value fine adjustment function

When the display value fine adjustment function is used, the set pressure value may change ±1 digit.

C Peak/Bottom value display

This function constantly detects and updates the maximum (minimum) pressure when the power is supplied, and allows to hold the maximum (minimum) pressure value.

The held value is maintained even if the power supply is cut.

When the s and v buttons are simultaneously pressed for 1 second or longer, while "holding", the held value will be reset.

D Key lock function

Prevents operation errors such as accidentally changing setting values

E Zero-clear function

This function clears and resets the zero value on the display of measured pressure.

The indicated value can be adjusted within ± 7 % F.S. of the pressure when ex-factory. (ZSE20 \Box F (for compound pressure): ± 3.5 % F.S.)

F Error display function

When an error or abnormality arises, the location and contents are displayed

Error name	Error code	Description	Action
Over current error	Er 1 Er 2	Load current of 80 mA or more is applied to the switch output.	Turn the power off and remove the cause of the over current. Then supply the power again.
Residual pressure error	[r]	During zero-clear operation, pressure over $\pm 7\%$ F.S. ($\pm 3.5\%$ F.S. for compound pressure) is present. Note that the mode is returned to measurement mode automatically 1 second later. The zero clear range varies by $\pm 1\%$ F.S. due to variation between individual products.	Perform zero-clear operation again after restoring the applied pressure to an atmospheric pressure condition.
Applied	XXX	Supply pressure exceeds the maximum set pressure.	Reset applied pressure to a level
pressure error		Supply pressure is below the minimum set pressure.	within the set pressure range
System error	Er 0 Er 7 Er 4 Er 8 Er 6 Er 9	Internal data error	Turn the power off and then on again. If the failure cannot be solved, please contact SMC for investigation.
Copy error	Er 13	The copy function does not operate properly.	After clearing the error by pressing the and buttons simultaneously for a minimum of 1 second, check the wiring and the model, and then attempt to copy again.
IO-Link master version error	Er 15	IO-Link version does not match that of the master.	Ensure that the master IO-Link version matches the device version.

SMC

Function Details **ZSE20** (F)/ISE20 Series

Function Details

The $F\square$ in () shows the function code number. Refer to the operation manual for details about operation procedures and function codes.


G Anti-chattering function (Simple setting mode or F1)

A large bore cylinder or ejector consumes a large volume of air in operation and may experience a temporary drop in the supply pressure. This function prevents detection of such temporary drops in the supply pressure as an error by changing the delay time setting.

Available delay time settings			
1.5 ms or less, 20 ms, 100 ms, 500 ms, 1000 ms, 2000 ms, 5000 ms			

<Principle>

This function averages pressure values measured during the response time set by the user and then compares the average pressure value with the pressure set point value to output the result on the switch.



H Units selection function (F0)

Display units can be switched with this function.

Display unit	MPA	kPA	kGF	bAr	PSi	inCH	mmHG
Smallest settable increment	MPa*1	kPa	kgf/cm ²	bar	psi	inHg	mmHg
ZSE20□ (Vacuum pressure)	0.001	0.1	0.001	0.001	0.01	0.1	1
ZSE20□F (Compound pressure)	0.001	0.1	0.001	0.001	0.02	0.1	1
ISE20□ (Positive pressure)	0.001	1	0.01	0.01	0.1		
ISE20□H (Positive pressure)	0.001	1	0.01	0.01	0.2		

^{*1} The ZSE20 (vacuum pressure) and ZSE20 F (compound pressure) will have different setting and display resolution when the unit is set to MPa.

Selection of power saving mode (F80)

The power saving mode can be selected.

It shifts to the power saving mode without button operation for 30 seconds.

It is set to the normal mode (Power saving mode is OFF.) at a time of shipment from the factory.

(During power saving mode, [ECo] will flash in the sub screen and the operation light will be ON (only when the switch is ON).)

J Setting of security code (F81)

The user can select whether a security code must be entered to release the key lock.

At a time of shipment from the factory, it is set such that a security code is not required.

ZSE20 ☐ (F)/ISE20 ☐ Series

Function Details

The $F\Box$ in () shows the function code number. Refer to the operation manual for details about operation procedures and function codes.

K Copy function (F97) (Z/ISE20A, 20B, 20C series only)

The settings of the master sensor can be copied to the slave sensors, reducing setting labour and minimizing the risk of setting mistakes.

The set value can be copied to up to 10 switches simultaneously. (Maximum transmission distance: 4 m)

(Max. 10 units)

1 unit 2 units 10 units

1 unit 2 units

10 units


P 1 0050

P 1 0050

Master

Slaves

* This function is not provided with the IO-Link compatible type.




- 1) Wire as shown in the figure on the left.
- Select the slave sensor which is to be the master, and change it into a master using the buttons. (In the default setting, all sensors are set as slaves.)
- 3) Press the sutton on the master sensor to start copying.

L Auto-shift function (F5) (Z/ISE20A, 20B, 20C series only)

When there are large fluctuations in the supply pressure, the switch may fail to operate correctly. The auto-shift function compensates for such supply pressure fluctuations. It measures the pressure at the time of auto-shift signal input and uses it as the reference pressure to correct the set value on the switch.

Set value correction by auto-shift function



*1 When delay time is 1.5 ms or less

When the auto-shift function is selected, " $\Re S_{\text{in}=000}$ " will be displayed on the sub screen for about 1 second, and the pressure value at that point will be saved as reference value " $\Gamma_- S$." Based on the saved reference value, output on-off points controlled by set values*2 such as " $P_- I$," " $P_- I$," " $P_- I$," and " $P_- I$," will also be rectified.

*2 When an output is reversed, output on-off points displayed at "n_ !," "H_ !," "n_ ?," and "H_ ?" will be rectified.

The above is an example in hysteresis mode. On-off points are similarly rectified in window comparator mode. Outputs that enable the auto-shift function can be changed via the settings.

* This function is not provided with the IO-Link compatible type.

Settable Range for Auto-Shift Input

	Set pressure range	Settable range
Compound pressure	-105.0 to 105.0 kPa	-210 to 210 kPa
Vacuum pressure	10.0 to -105.0 kPa	115.0 to -115.0 kPa
Positive pressure	-0.105 to 1.050 MPa	-1.155 to 1.155 MPa
Positive pressure*3	-0.105 to 2.100 MPa	-2.20 to 2.205 MPa

*3 Z/ISE20C series only

Auto-shift zero

The basic function of auto-shift zero is the same as that of auto-shift. However, it corrects values on the display based on a pressure value of "j", which is set as the reference value when auto-shift function is selected.



Connector pin assignment

1 2

1 Brown

2 White

 $ZSE20\square(F)/ISE20\square$ Series **Made to Order**


Please contact SMC for detailed dimensions, specifications, and delivery times.



Parts in Contact with Fluid: Stainless Steel 316L

This pressure switch has better corrosion resistance because it uses stainless steel 316L for the parts in contact with fluid (pressure sensor and fitting).

How to Order



- * Not applicable to the rated pressure -0.1 to 2 MPa specifications (ISE20CH).
- * A restrictor (equivalent to -X510) is installed inside the fitting. (Piping specifications A2(L) and B2(L) are excluded.)

Specifications


Model	ZSE20C(F)	ISE20C	
Withstand pressure	500 kPa	1.5 MPa	
Applicable fluid	Liquids and gases do not corrode stainless steel 316L.		


Models other than those above have the same specifications as the standard product.

Restrictor-installed Fitting

A restrictor is installed inside the fitting in order to reduce the effects of water collision with inertia force in the piping when adsorption is broken.

How to Order





Made to Order: "-X510"

Standard

- Not applicable for piping specifications A2(L) and B2(L).
- There are cases in which this product will not effectively suppress of the effects of water hammer. It is advised that other measures be taken in such cases

Lead Wire with M12 Connector


A lead wire applicable to the M12 4-pin pre-wired connector The lead wire length is 100 mm.


Series	20	20A	20B(-L)	20C
ZS-46-5LM12 (Non-waterproof)	0	0	_	_
ZS-46-5FM12 (Waterproof)	_	_	0	0

* If you wish for the sensor (switch body) and the lead wire to be shipped together, please contact SMC.

Во	dy side pin no.	Pin name	Lead wire color	M12 pin no.
	1	DC (-)	Blue	3
	2	Function	Gray	_
	3	OUT (2)	White	2
	4	OUT (1)	Black	4
	5	DC (+)	Brown	1

If you intend to make a connection to "Function," please contact SMC






ZSE20□(F)/ISE20□ Series Made to Order



Please contact SMC for detailed dimensions, specifications, and delivery times.

4 Conversion Cable for the Z/ISE30A Lead Wire with Connector

The conversion cable allows for connection between the existing Z/ISE30A lead wire with connector and the Z/ISE20.




The output specification signal may vary from that of the existing pressure switch.

 $Z/ISE30A \rightarrow Z/ISE20 + Conversion cable correspondence table$

Existing digital pressure switch model	Output specification	①Pressure switch part no.	②Conversion cable part no.
Z/ISE30A-□-N-□□□□	NPN open collector 1 output	Z/ISE20- N -□-□-□□□	
Z/ISE30A-□- P -□□□□	PNP open collector 1 output	Z/ISE20- P -□-□-□□□	ZS-46-5L A -X424*1
Z/ISE30A-□- A -□□□□	NPN open collector 2 outputs	Z/ISE20A- X -□-□-□□□	25-40-3L A -7424
Z/ISE30A-□- B -□□□□	E30A-□-B-□□□□ PNP open collector 2 outputs		
Z/ISE30A-□- C -□□□□	NPN open collector 1 output + Analogue voltage output	Z/ISE20A- R -□-□-□□□	
Z/ISE30A- D -□□□□	NPN open collector 1 output + Analogue current output	Z/ISE20A- S -□-□-□□□	ZS-46-5L B -X424*1
Z/ISE30A-E-□□□□ PNP open collector 1 output + Analogue voltage output		Z/ISE20A- T -□-□-□□□	23-40-3L D -7424
Z/ISE30A- F -□□□□	PNP open collector 1 output + Analogue current output	Z/ISE20A- V -□-□-□□□	

^{*} While this conversion cable allows for use of the existing wiring, output and functions other than that of the Z/ISE30A will be invalid (not wired).



⚠ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of **"Caution," "Warning"** or **"Danger."** They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC) ¹⁾, and other safety regulations.

Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate

injury.

Warning indicates a hazard with a medium level of risk★ Warning: which, if not avoided, could result in death or serious

njury.

Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious

njury.

ISO 4414: Pneumatic fluid power – General rules relating to systems.
 ISO 4413: Hydraulic fluid power – General rules relating to systems.
 IEC 60204-1: Safety of machinery – Electrical equipment of machines.
 (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots - Safety.

The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalogue information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.

- The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
- When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
- 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions

- Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
- 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalogue.
- An application which could have negative effects on people, property, or animals requiring special safety analysis.
- 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

⚠ Caution

1. The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing industries.

If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary. If anything is unclear, contact your nearest sales branch.

Limited warranty and Disclaimer/Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements". Read and accept them before using the product.

Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first. ²⁾ Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalogue for the particular products.
- 2) Vacuum pads are excluded from this 1 year warranty. A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements


- The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

↑ Caution

SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country.

Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.



SMC Cor	poration (E	urope)	
Austria	+43 (0)2262622800	www.smc.at	office@smc.at
Belgium	+32 (0)33551464	www.smc.be	info@smc.be
Bulgaria	+359 (0)2807670	www.smc.bg	office@smc.bg
Croatia	+385 (0)13707288	www.smc.hr	office@smc.hr
Czech Republic	+420 541424611	www.smc.cz	office@smc.cz
Denmark	+45 70252900	www.smcdk.com	smc@smcdk.com
Estonia	+372 6510370	www.smcpneumatics.ee	info@smcee.ee
Finland	+358 207513513	www.smc.fi	smcfi@smc.fi
France	+33 (0)164761000	www.smc-france.fr	info@smc-france.fr
Germany	+49 (0)61034020	www.smc.de	info@smc.de
Greece	+30 210 2717265	www.smchellas.gr	sales@smchellas.gr
Hungary	+36 23513000	www.smc.hu	office@smc.hu
Ireland	+353 (0)14039000	www.smcautomation.ie	sales@smcautomation.ie
Italy	+39 03990691	www.smcitalia.it	mailbox@smcitalia.it
Latvia	+371 67817700	www.smc.lv	info@smc.lv

Lithuania	+370 5 2308118	www.smclt.lt	info@smclt.lt
Netherlands	+31 (0)205318888	www.smc.nl	info@smc.nl
Norway	+47 67129020	www.smc-norge.no	post@smc-norge.no
Poland	+48 222119600	www.smc.pl	office@smc.pl
Portugal	+351 214724500	www.smc.eu	apoioclientept@smc.smces.es
Romania	+40 213205111	www.smcromania.ro	smcromania@smcromania.ro
Russia	+7 8123036600	www.smc.eu	sales@smcru.com
Slovakia	+421 (0)413213212	www.smc.sk	office@smc.sk
Slovenia	+386 (0)73885412	www.smc.si	office@smc.si
Spain	+34 945184100	www.smc.eu	post@smc.smces.es
Sweden	+46 (0)86031200	www.smc.nu	smc@smc.nu
Switzerland	+41 (0)523963131	www.smc.ch	helpcenter@smc.ch
Turkey	+90 212 489 0 440	www.smcpnomatik.com.tr	info@smcpnomatik.com.tr
UK	+44 (0)845 121 5122	www.smc.uk	sales@smc.uk