Aluminum One-touch Connection and Release High Vacuum Angle Valve

XLAQ/XLDQ Series



Lightweight, Compact

Large conductance. Small body.



XLAQ Series Case

 Model	A* (mm)	B (mm)	Weight (kg)	Conductance* (L/s)
XLAQ-16	40	120	0.33	5
XLAQ-25	50	133	0.6	14
XLAQ-40	65	178	1.3	45
XLAQ-50	70	190	2.0	80

*: Common to the XLAQ/XLDQ series





2-step control, Single acting/XLDC

Bellows seal, Single acting/XLAC

- Bellows type is particulate free and completely cleaned.
- Pressure balancing mechanism.

• Initial stage exhaust valve and main exhaust valve are combined. (flow rate 2-step control valve)

- Designed with a compact system and reduced piping.
- Prevents particulate turbulence inside the chamber during exhaustion.
- Prevents pumps from running while overloaded.

Actua-	Applications	Shaft seal	Model	Valve	Operating pressure		Flang	e size			Options	
tion		system	Model	type	Pa	16	25	40	50	Switch	Indicator	High tem- perature spec.
	Particle free		XLAQ									
Air operated		Bellows seal		Single		•	•	•	•	•	•	•
	Prevents turbulence of particulates. Prevents a pump from running overloaded.	Bellows seal O-ring seal	XLDQ	acting (N.C.)	pressure to 1 x 10 ⁻⁶			•	•	•	Standard	•

Variations

Aluminum One-touch Connection and Release **High Vacuum Angle Valve** Normally Closed/Bellows Seal XLAQ Series

How to Order





1) Flange siz	e
Size	
16	
25	
40	
50	

(2) Indicator/Actuator port direction

Indiduced/Hotduced point direct										
Symbol	Indicator	Actuator port direction								
Nil	Without indicator	Flange side								
Α		Flange side								
F	With	Left flange surface								
G	indicator	Rear flange surface								
J		Right flange surface								
K	Without	Left flange surface								
L	indicator	Rear flange surface								
M	Indicator	Right flange surface								



4 Auto switch type

Symbol	Auto switch part no.	Remarks				
Nil	—	Without auto switch (Without built-in magnet)				
M9N(M)(L)(Z)	D-M9N(M)(L)(Z)					
M9P(M)(L)(Z)	D-M9P(M)(L)(Z)	Solid state auto switch				
M9B(M)(L)(Z)	D-M9B(M)(L)(Z)					
A90(L)	D-A90(L)	Reed auto switch (Not applicable				
A93(M)(L)(Z)	D-A93(M)(L)(Z)	to flange size 16)				
M9//	_	Without auto switch (With built-in magnet)				

Note 1) Auto switches are not applicable for high-temperature specifications (Temperature specifications H0, H4, H5). Standard lead wire length is 0.5 m. Add "L" to the end of the part number when 3 m is desired, "M"

when 1 m, and "Z" when 5 m. Fxample) -M9NL Note 2) A type with a pre-wired connector is also selectable. Example) -M9NSAPC

Note 3) Refer to the Auto Switch Catalog for further information on auto switches.

XL
XL¤Q
XM⊡ XY⊡
D-🗆
XSA
XVD
XGT
CYV

XLA

Part numbers indicating changed seal material and leakage . Note 2) Leakage Pa·m³/s or less Note 1)

Svm		Chanded								
Synn		part	Internal	External						
Ni	il	None	1.3 x 10 ⁻¹⁰ (FKM)	1.3 x 10 ⁻¹⁰ (FKM)						
Α		2,3	1.3 x 10 ⁻⁸	1.3 x 10 ⁻⁸						
В	B (2)		1.3 x 10 ⁻⁸	1.3 x 10 ⁻¹⁰ (FKM)						
С	;	3	1.3 x 10 ⁻¹⁰ (FKM)	1.3 x 10 ⁻⁸						
Note	Note 1) Values at ambient temperatures, excluding gas permeation.									
Note 2) Refer to parts number of "Construction" on the page 470 for changed										
	part. Number indicates parts number of "Construction" accordingly.									

Note 3) For option "F1," only "A" can be selected. The leakage amount is the same as that of "Nil" (standard FKM type).

To order something else "Nil" (standard), list the symbols starting with "X", followed by each symbol for "body surface treatment", "seal material" and then "changed parts" at last.

Example) XLAQ-25-M9NA-XAN1A

③ Temperature specifications/Heater

O: make al	T	Lington	Applicable flange size				
Symbol	Temperature	Heater	16	25	40	50	
Nil	5 to 60°C	None	۲	٠	•	•	
HO		None	•	•	•	•	
H4	5 to 150°C	With 100°C heater	-	_	•	•	
H5		With 120°C heater	—	•	•		

Note 1) Size 16 is not applicable for H4, H5, Size 25 not for H4. Note 2) Heater cannot be retrofitted for the H0 type.

(5) Number of auto switches/Mounting position

g									
Symbol	Quantity	Mounting position							
Nil	Without auto switch								
Α	2 pcs.	Valve open/closed							
В	1 pc.	Valve open							
С	1 pc.	Valve closed							

6 Body surface treatment/Seal material and its changed part

 Body surface 	ce treatment								
Symbol	Surface	Surface treatment							
Nil	External: Hard anodized Internal: Raw material								
Α	External: Hard anodized Internal: Oxalic acid anodized								
Seal material									
Symbol	Seal material	Compound no.							
Nil	FKM	1349-80* 2101-80*							
N1	EPDM								
P1	Barrel Perfluoro®	70W							
Q1	Kalrez®	4079							
R1		SS592							
R2	Chemraz®	SS630							
R3		SSE38							
S1	VMQ	1232-70*							
T1	EKM for Plasma	3310-75*							

-KIM for Plasi U1 ULTIC ARMOR UA4640 F1 FKM Produced by Mitsubishi Cable Industries, Ltd

** Same specifications as the standard FKM type

Barrel Perfluoro® is a registered trademark of Matsumura Oil Co.,Ltd. Kalrez® is a registered trademark of E. I. du Pont de Nemours and Company or its affiliates.

Chemraz[®] is a registered trademark of Greene, Tweed Technologies, Inc. ULTIC ARMOR[®] is a registered trademark of VALQUA, LTD.



XLAQ Series

Specifications

Model		XLAQ-16	XLAQ-25	XLAQ-40	XLAQ-50				
Flange (valve) size		16	25	40	50				
Valve type		Normally closed (Pressurize to open, Spring seal)							
Fluid			Inert gas un	der vacuum					
Operating temperature (°C)			5 to 60 (High-temper	rature type: 5 to 150)					
Operating pressure (Pa) (ab	s)		Atmospheric pre	ssure to 1 x 10 ⁻⁶					
Conductance (L/s) Note 1)		5	14	45	80				
Leakage (Pa·m³/s)	Internal								
Leakage (Pa·III7S)	External	1.3 x 10 ⁻¹⁰ at normal temperatures (in case of standard material, FKM), excluding gas permeation							
Flange type		KF (NW)							
Principal materials		Body: Aluminum alloy, Bellows: Stainless steel 316L, Bellows holder: Stainless steel 304, FKM (Standard seal material) ^{Note 2)}							
Surface treatment		External: Hard anodized Internal: Raw material							
Pilot pressure (MPa) (G)		0.4 to 0.7							
Pilot port size		M5 Rc 1/8							
Weight (kg)		0.33	0.6	1.3	2.0				

Note 1) Conductance is the value for the "molecular flow" of an elbow with the same dimensions.

Note 2) Vacuum grease (Fluorine-based, Y-VAC2) is applied to the external seal of the vacuum components.

Construction



* Refer to page 478 for the maintenance parts.

Aluminum Aluminum One-touch Connection and Release High Vacuum Angle Valve XLAQ Series

Dimensions



									(11111)
Model	Α	В	С	D	Е	F	G	Н	J
XLAQ-16	40	120	38	1	—	30	17	40	87
XLAQ-25	50	133	48	1	12	40	26	39	91
XLAQ-40	65	178	66	2	11	55	41	63	129
XLAQ-50	70	190	79	2	11	75	52	68	142

Note) The heater (Option) is not available with XLAQ-16.

Aluminum One-touch Connection and Release High Vacuum Angle Valve 2-step Control, Single Acting/Bellows Seal, O-ring Seal XLDQ Series

How to Order





1) Flange siz	e
Size	
40	
50	

2 Actuator port direction

Symbol	Actuator port direction		
Nil	Flange side		
K	Left flange surface		
L Rear flange surface			
M	Right flange surface		



3 Temperature specifications/Heater

Symbol	Temperature	Heater
Nil	5 to 60°C	None
HO		None
H4	5 to 150°C	With 100°C heater
H5		With 120°C heater

Note) Heater cannot be retrofitted for the H0 type

(5) Number of auto switches/Mounting position

Symbol	Quantity	Mounting position			
Nil	Without auto switch				
Α	2 pcs.	Valve open/closed			
В	1 pc.	Valve open			
С	1 pc.	Valve closed			

6 Body surface treatment/Seal material and its changed part

Body surface treatment

Symbol	Surface treatment						
Nil	External: Hard anodized Internal: Raw material						
Α	External: Hard anodized Ir	ternal: Oxalic acid anodized					
 Seal materia 	al						
Symbol	Seal material	Compound no.					
Nil	FKM	1349-80*					
N1	EPDM	2101-80*					
P1	Barrel Perfluoro®	70W					
Q1	Kalrez®	4079					
R1		SS592					
R2	Chemraz®	SS630					
R3		SSE38					
S1	VMQ	1232-70*					
T1	FKM for Plasma	3310-75*					
U1	ULTIC ARMOR [®]	UA4640					
F1	FKM	-**					

The material for the sliding parts of the S valve is FKM

* Produced by Mitsubishi Cable Industries, Ltd.

** Same specifications as the standard FKM type

4 Auto switch type

Symbol	Auto switch part no.	Remarks			
Nil	—	Without auto switch (Without built-in magnet)			
M9N(M)(L)(Z)	D-M9N(M)(L)(Z)				
M9P(M)(L)(Z)	D-M9P(M)(L)(Z)	Solid state auto switch			
M9B(M)(L)(Z)	D-M9B(M)(L)(Z)				
A90(L)	D-A90(L)	Desite the high			
A93(M)(L)(Z)	D-A93(M)(L)(Z)	Reed auto switch			
M9//		Without auto switch (With built-in magnet)			

Note 1) Auto switches are not applicable for high-temperature specifications (Temperature specifications H0, H4, H5). Standard lead wire length is 0.5 m. Add "L" to the end of the part number when 3 m is desired, "M" when 1 m, and "Z" when 5 m.

Example) -M9NL Note 2) A type with a pre-wired connector is also selectable. Example) -M9NSAPC Note 3) Refer to the Auto Switch Catalog for further information on auto switches.

Part numbers indicating changed seal material and leakage

r art nambere maleating enanged bear material and leakage							
Symbol	Note 2) Changed	Leakage Pa·m ³ /s or less Note 1)					
0,	part	Internal	External				
Nil	None	1.3 x 10 ⁻¹⁰ (FKM) 1.3 x 10 ⁻¹⁰ (FKM)					
Α	2, 3, 4, 5	1.3 x 10 ⁻⁸ 1.3 x 10 ⁻⁸					
В	2, 4, 5	1.3 x 10 ⁻⁸	1.3 x 10 ⁻¹⁰ (FKM)				
С	3	1.3 x 10 ⁻¹⁰ (FKM) 1.3 x 10 ⁻⁸					
Note 1) V	Note 1) Values at ambient temperatures, excluding gas permeation						

 Note 1) Values at ambient temperatures, excluding gas permeation.
 Note 2) Refer to parts number of "Construction" on the page 473 for changed part. Number indicates parts number of "Construction" accordingly.
 Note 3) For option "F1," only "A" can be selected. The leakage amount is the same as that of "Nii" (standard FKM type).

To order something else "Nil" (standard), list the symbols starting with "X", followed by each symbol for "body surface treatment", "seal material" and then "changed parts" at last.

Example) XLDQ-40K-M9NA-XAN1A

Barrel Perfluoro® is a registered trademark of Matsumura Oil Co., Ltd. Kalrez® is a registered trademark of E. I. du Pont de Nemours and Company or its affiliates.

Chemraz[®] is a registered trademark of Greene, Tweed Technologies, Inc. ULTIC ARMOR[®] is a registered trademark of VALQUA, LTD.



Specifications

Moc	lel	XLDQ-40	XLDQ-50		
Flange (valve) size		40	50		
Valve type		Normally closed (Pressurize to open, Sprin	ng seal) [both main & initial exhaust valves)		
Fluid		Inert gas un	der vacuum		
Operating temperatu	ıre (°C)	5 to 60 (High-temper	rature type: 5 to 150)		
Operating pressure	(Pa) (abs)	Atmospheric pressure to 1 x 10 ⁻⁶			
Conductance Note 1)	Main exhaust valve	45	80		
(L/s)	Initial exhaust valve	8	11		
	Internal	1.3 x 10 ⁻¹⁰ at ordinary temperature (in case of standard material, FKM), excluding gas permeation			
Leakage (Pa·m³/s)	External				
Flange type		KF (NW)		
Principal materials		Body: Aluminum alloy, Bellows: Stainless steel 316L, Bellows holder: Stainless steel 304, FKM (Standard seal material) Note 2)			
Pilot pressure (MPa)	(G)	0.4 to 0.7 [both main & initial exhaust valves]			
Pilot port size Rc 1/8			1/8		
Weight (kg)		1.5	2.2		

Note 1) The main exhaust valve conductance is the valve for the "molecular flow" of an elbow with the same dimensions. The initial exhaust valve conductance is the value for the "viscous flow". Flow adjustment is not available for the initial exhaust valve.

Note 2) Vacuum grease (Fluorine-based, Y-VAC2) is applied to the external seal of the vacuum components.

Construction



* Refer to page 478 for the maintenance parts.

XLA

XL

XL⊡Q Xm⊡

XY□

D-🗆 XSA

XVD

XGT

CYV

XLDQ Series

Dimensions



											(mm)
Model	Α	в	С	D	E	F	G	н	J	K	L
XLDQ-40	65	189	66	2	11	55	41	63	20	Max. 5	143
XLDQ-50	70	198	79	2	11	75	52	68	20	Max. 5	153

XLAQ/XLDQ Series Glossary of Terms

1 Seal Materials

Please note that the following are general features and subject to change depending on a processing condition. For details, please contact sealing component manufacturerers.

FKM (Fluororubber)

With low outgassing, low permanent-setting and low gas permeation rates, this is the most popular seal material for high vacuums. Standard material used by SMC's high vacuum angle valve is Mitsubishi Cable Industries, Ltd. (Compound No. 1349-80).

It is advisable to choose a model depending on its application, because an improved material compound (3310-75) which reduces the weight reduction ratio with O_2 plasma is also available.

Kalrez[®] • Kalrez[®] is a registered trademark of E.I. du Pont de Nemours and Company or its affiliates. This material, perfluoroelastomer (FFKM), has excellent heat and chemical resistance, but its permanent-setting is large, and special caution is required. Variations are available with improved plasma (O₂, CF4) and particulate resistance; therefore it is advisable to select types based upon the application.

Compound No. 4079: Standard Kalrez[®], excellent in gas and heat resistance.

Chemra2® * Chemra2® is a registered trademark of Greene, Tweed Technologies, Inc. This material, perfluoroelastomer (FFKM), has excellent chemical and plasma resistance and has slightly higher heat resistance than FKM. Several variations of Chemra2® are available and it is advisable to choose based upon the particular plasma being used and other conditions, etc.

- Compound No. SS592: Excellent physical properties and especially effective for moving parts.
- Compound No. SS630: Applicable to both fixed and moving parts and compatible with a wide variety of applications.
- Compound No. SSE38: The cleanest material among Chemraz[®], developed for high-density plasma instruments and its permanent-setting is relatively low.

Barrel Perfluoro[®] • Barrel Perfluoro[®] is a registered trademark of Matsumura Oil Co.,Ltd. Compound No. 70W: Perfluoroelastomer (FFKM) which does not contain a metal filler. Resistant against NF₃, NH₃. Low particle generation under dry process conditions.

ULTIC ARMOR® + ULTIC ARMOR® is a registered trademark of Nippon Valqua Industries, Ltd. Fluoro-based rubber which does not contain a metal filler. Seal material which is plasma-resistant and has low gas emittance and heat resistance.

Silicone (Silicone rubber, VMQ)

This material is relatively inexpensive, has good plasma resistance, but its gas permeation rate is high.

Optional seal material used by SMC's high vacuum angle valve is Mitsubishi Cable Industries, Ltd. (Compound No. 1232-70, White) It has a low weight-reduction ratio and low particle generation within O_2 plasma and NHs gas environments.

EPDM (Ethylenepropylene rubber)

Relatively lower priced and excellent in weatherability, chemical and heat resistance, but with no resistance at all to general mineral oil. Optional seal material used by SMC's high vacuum angle valve is Mitsubishi Cable Industries, Ltd. (Compound No. 2101-80) Resistant to NHs gas, etc.

2 Shaft Sealing Method

Bellows

Bellows offer cleaner sealing with reduced particle generation and less outgassing. The two major bellow types are: Formed-bellows and Welded-bellows. Formed-bellows produce less dusts and offer higher dust resistance. Welded-bellows allow longer strokes, but generate more dust particles and offer less dust resistance. Please note, the endurance depends on length and speed of the strokes.

3 Response Time/Operation Time

Valve opening

The time from the application of voltage to the actuation solenoid valve until 90% of the valve stroke has been completed is the valve opening response time. Valve opening operation time indicates the time from the start of the stroke until 90% of movement has been completed. Both of these become faster as the operating pressure is increased.

Valve closing

The time from the cut off of power to the actuation solenoid valve until 90% of the valve return stroke has been completed is the valve closing response time. Valve closing operation time indicates the time from valve opening until 90% of return movement has been completed. Both of these become slower as the operating pressure is increased.





XLAQ/XLDQ Series Specific Product Precautions 1

Be sure to read this before handling the products.

Caution on Design

∆ Warning

All models

- The body material is A6063, the bellows are stainless steel 316L, and other metal seal material is stainless steel 304. Standard seal material in the vacuum section is FKM that can be changed to the other materials (please refer to "How to Order"). Use fluids which are compatible with materials after confirming.
- Select materials for the actuation pressure piping, and heat resistance for fittings that are suitable for the applicable operating temperatures.

· Model with auto switch

1. The switch section should be kept at a temperature no greater than $60^\circ\text{C}.$

Model with heater

- 1. When using a model with a heater (thermistor), a device should be installed to prevent overheating.
- 2. Refer to the XL□ series common option specifications on page 459 for heater specifications.

Selection

ACaution

All models

- When controlling valve responsiveness, take note of the size and length of piping, as well as the flow rate characteristics of the actuating solenoid valve.
- 2. Actuating pressure should be kept within the specified range. 0.4 to 0.5 MPa is recommended.
- 3. Use within the limits of the operating pressure range.
- The piston chamber and bellows chamber are directly connected to the atmosphere. Use in an environment where particulate discharge will not present a problem.
- High temperature type
- 1. In the case of gases which cause a large amount of deposits, heat the valve body to prevent deposits in the valve.

Mounting

▲ Caution

All models

- 1. In high humidity environments, keep valves packaged until the time of installation.
- In case with switches, secure the lead wires so that they have sufficient slack, without any unreasonable force applied to them.
- Perform piping so that excessive force is not applied to the flange sections. In case there is vibration of heavy objects or attachments, etc., secure them so that torque is not applied directly to the flanges.
- Vibration resistance allows for normal operation up to 30 m/s² (45 to 250 Hz), but continuous vibration may cause a decline in durability. Arrange piping to avoid excessive vibrations or shocks.

Mounting

ACaution

- High-temperature type (Temperature specifications/ H0, H4, H5)
- In models with heater (thermistor), take care not to damage the insulation components of the lead wires and connector section.
- The setting temperature for models with heater should be established without a draft or heat insulation. It will change depending on conditions such as heat retaining measures and the heating of other piping. Fine adjustment is not possible.
- When installing heater accessories or mounting a heater, check insulation resistance at the actual operating temperature. A short circuit breaker or fuse should be installed.
- When a valve is to be heated, only the body section should be heated, excluding the bonnet (handle) section.
- 5. When a heater is in operation, the entire valve becomes hot. Be careful not to touch it with bare hands, as burns will result.

Piping

A Caution

- 1. Before mounting, clean the surface of the flange seal and the O-ring with ethanol, etc.
- There is an indentation of 0.1 to 0.2 mm in order to protect the flange seal surface, and it should be handled so that the seal surface is not damaged in any way.

3. Exhaust direction

ÌSMC

During operation, the direction of the exhaust may be determined freely, but in cases where a flow is generated by the exhaust, a decline in durability may result.

The exhaust direction shown in the figure below (bellows side exhaust) is recommended.

Please take all available precautions, as the life of the equipment is affected by conditions of usage.



Recommended exhaust direction [Vacuum pump connected on bellows side]



XLAQ/XLDQ Series Specific Product Precautions 2

Be sure to read this before handling the products.

Maintenance

ACaution

- 1. Observe the caution plate during maintenance.
- When removing deposits from a valve, take care not to damage any of its parts.
- 3. SMC specified parts should be used for service. Refer to "Construction" or "Maintenance Parts."
- When removing valve or exterior seals, take care not to damage the sealing surfaces. When installing the valve seal, be sure that the O-ring is not twisted.
- 5. Refer to the operation manual for replacement instructions.



XLA
XL
XL□Q
XM□ XY□
D-🗆
XSA
XVD
XGT
CYV





XLAQ/XLDQ Series Specific Product Precautions 3

Be sure to read this before handling the products.

Maintenance Parts

ACaution

 Replace the bonnet assembly when changing the seal material. It may not be applicable when a seal material different from the current one has been chosen.



Bonnet assembly

-XU1

ARMOR®

UA4640

-XF1

FKM

**

Bonnet Assembly: Component Part No.: 1)

Model	Temperature	Indicator		Flange (Valve) size					
woder	specifications	Indicator	16	25	40	50			
	General	-	XLAQ16-30-1	XLAQ25-30-1	XLAQ40-30-1	XLAQ50-30-1			
XLAQ	use	0	XLAQ16A-30-1	XLAQ25A-30-1	XLAQ40A-30-1	XLAQ50A-30-1			
ALAG	High	-	XLAQ16-30-1H	XLAQ25-30-1H	XLAQ40-30-1H	XLAQ50-30-1H			
	temperature	0	XLAQ16A-30-1H	XLAQ25A-30-1H	XLAQ40A-30-1H	XLAQ50A-30-1H			
XLDQ	General use	0:	_	_	XLDQ40-30-1	XLDQ50-30-1			
ALDQ	High temperature	Standard	-	—	XLDQ40-30-1H	XLDQ50-30-1H			

Note 1) Add a suffix for the seal material (below Table 1) to the end of the part number when valve seal materials other than the standard (FKM: Compound No. 1349-80: Mitsubishi Cable Industries, Ltd.) are desired.

Note 2) An auto switch magnet is not attached. In cases where an auto switch magnet is attached, please add "-M9//" at the end of the part number. (Not available for high temperature models)

Note 3) Auto switch and solenoid valve are not attached. When a set including auto switch and solenoid valve is required, please add the symbols after the auto switch in "How to Order" at the end of the part number.

External Seal/Valve Seal/S Valve Seal Assembly

Model	Description	Material		Flange (Valve) size										
Iviodei	construction no.	Material	16	25	40	50								
	External seal	Standard	AS568-122V	AS568-129V	AS568-140V	AS568-231V								
XLAQ	3	Special	AS568-122□	AS568-129□	AS568-140□	AS568-231□								
XLDQ	Valve seal	Standard	B2401-V15V	B2401-V24V	B2401-P42V	AS568-227V								
	(2)	2	2	2	2	2	2	2	2	Special	B2401-V15	B2401-V24□	B2401-P42□	AS568-227□
XLDQ	S valve seal assembly	Standard	_	AS568-009V	XLD40-2-9-1A AS568-016V	XLD50-2-9-1A AS568-016V								
ALDQ.	(4)	Special	_	AS568-009□	XLD40-2-9-1A□ AS568-016□	XLD50-2-9-1A□ AS568-016□								

Note 1) Add a suffix for the seal material (below Table 1) to the end of the part number (blank box) when valve seal materials other than the standard (FKM: Compound No. 1349-80: Mitsubishi Cable Industries, Ltd.) are desired.

Note 2) Refer to "Construction" of each series for the construction numbers.

Table 1 Optional Seal Material										
	Symbol	-XN1	-XP1	-XQ1	-XR1	-XR2	-XR3	-XS1	-XT1	Γ
	Seal material	EPDM	Barrel Perfluoro®	Kalrez®	Chemraz®			VMQ	FKM for Plasma	

 Compound no.
 2101-80*
 70W
 4079
 SS592
 SS630
 SSE38
 1232-70*
 3310-75*

 Note) It may not be appplicable when a seal material different from the current one has been chosen.
 3310-75*
 3310-75*

* Produced by Mitsubishi Cable Industries, Ltd. ** Same specifications as the standard FKM type

Barrel Perfluoro® is a registered trademark of Matsumura Oil Co., Ltd.

Kalrez® is a registered trademark of E. I. du Pont de Nemours and Company or its affiliates.

Chemraz® is a registered trademark of Greene, Tweed Technologies, Inc.

ULTIC ARMOR® is a registered trademark of VALQUA, LTD.