Doc. No. AMX-OM-Q018-B



# **Operation Manual**

### **PRODUCT NAME**

# Membrane Air Dryer

MODEL / Series / Product Number



# **SMC** Corporation

Contents	
1. Safety Instructions	1
2. Installations and Operations	3
3. Maintenance and Checks	5
4. Specifications	6

# Membrane Air Dryer Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger."

They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)<sup>\*1)</sup>, and other safety regulations.

\*1) ISO 4414: Pneumatic fluid power -- General rules relating to systems.

ISO 4413: Hydraulic fluid power -- General rules relating to systems.

IEC 60204-1: Safety of machinery -- Electrical equipment of machines .(Part 1: General requirements) ISO 10218-1992: Manipulating industrial robots -Safety.



**Caution** indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

**Warning** indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

**Danger** indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

# Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results.

The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product.

This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

### 2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

3. Do not service or attempt to remove product and machinery/equipment until safety is confirmed.

1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.

2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.

Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.
 Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.

1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.

2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalog.

3. An application which could have negative effects on people, property, or animals requiring special safety analysis.

4.Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.



# Membrane Air Dryer Safety Instructions

# 

#### 1. The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing industries. If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary. If anything is unclear, contact your nearest sales branch.

### Limited warranty and Disclaimer/Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements". Read and accept them before using the product.

### Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.<sup>\*2)</sup> Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.
  - \*2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered.Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

### **Compliance Requirements**

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

# Caution

1. SMC products are not intended for use as instruments for legal metrology. Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (Measurement) laws of each country.

## 2. Installations and Operations:

#### Design

### ▲ Caution

a. Depending on the model and operating conditions, the oxygen ratio of the outlet air may drop below the prescribed standard.

Do not use standard dew point  $-40^{\circ}$ C (symbol L) type, standard dew point  $-60^{\circ}$ C (symbol S) type and IDG30A, 50A, 30HA, 50HA for dehumidifying breathing air. Do not use only outlet air (dry air ) in a closed room.

# b. Devise a layout which considers the position of the purge air discharge ports.

Purge air is humid air. Devise a layout in which the humid purge air will not cause corrosion or malfunction of peripheral equipment.

#### c. When very clean air is required

(Supplying clean air to air bearings, blowing of semiconductor parts, etc.) Install a micro mist separator or Super Mist Separator on the outlet side of this equipment. Grease is applied inside of the Regulator used in the V type unit. When air with high purity is required, please either mount the Super Mist Separator on the outlet side or use a made-to-order product, which is provided with a Micro Mist Separator (Series AWD) instead of a Regulator.

#### d. Time to reach the rated dew point

A certain amount of time is required to achieve the rated dew point after the air begins flowing into the membrane air dryer. Use the times below as a guide, and begin operating the outlet side equipment after the rated dew point is achieved.

\* This time can be shortened as described below.

- 1) Provide a valve on the outlet side of the membrane air dryer.
- 2) Supply air with the valve closed so that only purge air flows through the membrane air dryer.
- 3) After 15 minutes or more, open the valve and let air flow to the outlet side equipment.

### Selection

### ▲ Caution

a. Consider the purge air flow rate in total flow rate requirements.

Find the purge air flow rate from the charts and calculate the "required outlet air flow rate + purge air flow rate". The air supply capacity must be at lease equal to the calculated flow or the required outlet air flow rate cannot be obtained.

#### Mounting

### ▲ Caution

- a. Do not obstruct the purge air discharge ports. Dehumidification performance will decrease or may become impossible if purge air back pressure becomes too high or purge air stops flowing.
- **b.** Remove water droplets from the inlet air Water droplets in the air can lower performance and cause malfunction.
- c. Large quantities of dust (solid foreign matter) are contained in the supply air. When there are large quantities of dust (solid foreign

matter), install an air filter or main line filter to the inlet side of the mist separator.

d. Ensure that intermittent pressure is not applied to the product.

Do not frequently operate a solenoid valve on the inlet side. The membrane dryer can be damaged if inlet pressure is applied intermittently.



# 2. Installations and Operations:

#### Piping

## **Marning**

#### a. Confirm locking of case and body

When using in a unit, be sure to set the air pressure to zero before using a Mist Separator or Micro Mist Separator with modular connections. Also, confirm that the body and case are locked together with a click before starting the flow of compressed air.

#### b. Confirm tightening of the holder.

Before starting the flow of compressed air, turn the Membrane air dryer's holder in its tightening direction, confirming that it is completely tightened and that the case will not come off.

# **▲** Caution

#### a. Use of tools

Hold the upper portion of the body (aluminum die-casted section) with a spanner or adjustable angle wrench. Do not turn it while holding the case section.

#### b. Drain piping for separators

Use a tube of the prescribed size and keep the length within 5 meters or less when installing drain piping for Mist Separators or Micro Mist Separators. Be sure that the tube does not rise up or become folded over.

#### c. Flush pipes before installation.

Use an air blower to flush the piping to thoroughly remove any cutting chips, cutting oil, or debris from the piping inside, before connecting them. If they enter the inside of products, they could cause products to malfunction, lower performance or damage the element.

#### d. Piping materials for low dew point air

Do not use nylon tube piping and resin fittings (except fluoropolymer) for the outlet side of the membrane air dryer if air of a low dew point (40 °C or less) is required, Due to the nature of the nylon tube, it could be affected by the ambient air, and it might not be possible to achieve the prescribed low dew point at the end of the tube. For low dew point air, use stainless steel or fluoropolymer piping.

#### e. Installation of Differential Pressure Gauge Please attach by a customer.

Connection thread size	Proper tightening torque (N • m)		
1/8	7 to 9		
1/4	12 to 14		

#### Air Supply

### ▲ Caution

#### a. Compressed air supply capacity

An air source that has a supply capacity that is larger than the "necessary outlet air flow rate (dry air flow rate) + purge air flow rate" is required. See the purge air flow rate diagram in the catalog for the purge air flow rate.

# b. Avoid chemical substances which have an adverse effect on the product

The chemical substances stated in the table below can reduce the performance or damage the membrane element. Do not use the membrane dryer in an environment containing these chemicals substances.

Туре	Harmful Substances
Solvent	Acetone, Benzene, Phenol, Toluene,
	Trichloroethylene, Xylene, Cresol, Thinner,
	Aniline, Chloroform, Ethyl Alcohol, Methyl
	Alcohol, Chlorobenzene, Trichloroethane,
	Ethylbenzene, Isopropyl Alcohol, Dioxane,
	Tetrahydrofuran, Methyl Chloride,
	Cyclohexanone, Carbon Tetrachloride, Methyl
	Ketone, Ethyl Ketone, etc.
Acid	Sulfuric Acid, Nitric Acid, Hydrochloric Acid,
	Acetic Acid, Lactic Acid, Chromic Acid, etc.
Gas	Chlorine, Sulfurous Acid, Hydrogen Sulfide,
	Bromine, Ozone, Ammonia, etc.
Oil	Hydraulic Fluid (Phosphoric Ester), Fuel Oil,
	Water Soluble Cutting Fluid (Alkaline),
	Kerosene, etc.
Strong	Lithium hydroxide, Sodium hydroxide,
Bases	Potassium hydroxide, Calcium hydroxide, etc.
Others	Anaerobic thread lockers

#### **Operating Environment**

### ▲ Caution

a. Do not use at temperatures (fluid or ambient temperatures) higher than the prescribed operating conditions.

Resin is used in the membrane module (element), and it can be damaged by operation at high temperatures. confirm that the fluid temperature does not exceed the membrane dryer's range of operating conditions during use, especially when installed immediately after a reciprocating type air compressor.

# b. Keep the inlet air temperature lower than the ambient temperature.

Condensation and water drops may accumulate inside of the membrane dryer's body and reduce its dehumidification capacity if the membrane air dryer's body is cooled by the ambient air.

# 3. Maintenance and Checks

- a. <u>Do not remove the parts and piping when the</u> product is pressurized. Always confirm that there is no residual pressure present before removal of unit. <u>Replacement while residual pressure is present in</u> the product may cause injury or damage of the product.
- b. <u>Precautions for membrane module removal</u> When the filter and membrane air dryer is connected by spacer (modular connection), be sure to remove the membrane dryer before replacement.

#### c. Color of the dew point indicator

The color of the dew point indicator shows the condition of the outlet air from the membrane air dryer.

- Dew point indicator color and humidity of air
- (1) Bluish ←→ Pinkish
   Bluish --- Relative humidity approx. 10% or less
- Pinkish --- Relative humidity approx. 50% or higher
- (2) Greenish  $\leftarrow \rightarrow$  Yellowish

Greenish --- Relative humidity approx. 10% or less Yellowish --- Relative humidity approx. 50% or higher

- \*1. It takes time for the color of the dew point indicator changes.
- \*2. Use a dew point meter for confirming the correct dew point.
- -Discoloration other than above

Absorbent is used for the dew point indicator. The absorbent absorbs vaporized oil or other gas components which cannot be eliminated by micro mist separator and the dew point indicator may turn colors other than specified above.

In this case, it is difficult to check the humidity of the outlet air. Please replace the dew point indicator regularly.

It is possible to avoid discoloration by installing a super mist separator which absorbs vaporized oil and an odor removal filter. It is recommended to add the super mist separator and an odor removal filter after replacing the dew point indicator.

#### **Service Parts**

Table 3-1. Membrane module kit (Element) and Dew point indicator Klt

Name	Membrane module	Dew point Checker set	
Model	set	Checker set	
IDG3 (Option : S)	IDG-EL3		
IDG3H (Option : S)	IDG-EL3H		
IDG5 (Option : S)	IDG-EL5		
IDG5H (Option : S)	IDG-EL5H		
IDG10	IDG-EL10	IDG-DP01	
IDG10H	IDG-EL10H		
IDG20	IDG-EL20		
IDG20H	IDG-EL20H		
IDG30□A	IDG-EL30A		
IDG50□A	IDG-EL50A		
IDG60LA, 60SA	IDG-EL60LA		
IDG75LA, 75SA	IDG-EL75LA		
IDG100LA, 100SA	IDG-EL100LA		

## 4. Specifications

#### 1) Standard dew point: -20°C, -15°C

Model			Specifications										
	Woder	IDG3V4	IDG5V4	IDG10V4	IDG20V4	IDG30AV4	IDG50AV4	IDG3HV4	IDG5HV4	IDG10HV4	IDG20HV4	IDG30HAV4	IDG50HAV4
Component equipment	Mist separator	AFN	120-A	AFM	30-A	AFM40-A		AFM20-A		AFM30-A		AFM40-A	
	Micro mist separator	AFD	20-A	AFD30-A		AFD40-A		AFD20-A		AFD30-A		AFD40-A	
	Regulator	AR:	20-B	AR25-B		AR40-B		AR20-B		AR25-B		AR40-B	
	Differential pressure gauge		GD40-2-01-X29										
	Spacer	Y2□	0(T)-A	Y3□0(T)-A		Y4□0(T)-A		Y2□0(T)-A		Y3□	Y3□0(T)-A		Y4□0(T)-A
Range of operating conditions	Fluid		Compressed Air										
	Inlet air pressure MPa		0.3 to 0.85				0.3 to 1.0		0.3 to 0.85			0.3 to 1.0	
	Inlet air temperature °C *Not	=1	-5 to 55				-5 to 50		-5 to 55			-5 to 50	
œ ₀ 8	Ambient temperature °C *Not	=1	-5 to 55				o 50		-5 1	to 55		-5 to 50	
Standard Performance	Outlet air atmospheric pressure dew point °C *Note	2	-20					-15					
	Inlet air flow rate L/min(ANR)	31	62	125	250	360	586	28	56	111	222	329	550
Performance Iditions	Outlet air flow rate L/min(ANR)	25	50	100	200	300	500	25	50	100	200	300	500
forn	Purge air flow rate L/min(ANR) *Not	3 6	12	25	50	60	86	3	6	11	22	29	50
trd Perforn conditions	Inlet air pressure MPa		0.7										
	Inlet air temperature °C							25					
Standard cor	Inlet air saturation temperature °C							25					
Sta	Ambient temperature °C							25					
Dew point ind	icator purge air flow rate *Note	4	1 L/min (ANR) {In the case of inlet air pressure 0.7MPa}										
Regulator con	struction (about Type V)		Relief type										
Portsize			1/8 · 1/4 1/4 · 3/8 1/8 · 1/4 1/4 · 3/8										
	Mass kg	1.4	1.4	1.9	2.1	3.0	3.1	1.4	1.4	1.9	2.1	3.0	3.1

#### 2) Standard dew point: -40°C, -60°C

Model		Specifications									
	Woder	IDG30LAV4	IDG50LAV4	IDG60LAV4	IDG75LAV4	IDG100LAV4	IDG60SAV4	IDG75SAV4	IDG100SAV4		
Component equipment	Mist separator	AFM40-A									
	Micro mist separator	AFD40-A									
	Regulator	AR40-B									
	Differential pressure gauge	GD40-2-01-X29									
	Spacer	Y4□0(T)-A									
Range of operating conditions	Fluid	Compressed Air									
	Inlet air pressure MPa	0.3 to 1.0									
	Inlet air temperature °C *Note1	-5 to 50									
<u>∞ -</u> S	Ambient temperature °C *Note1	-5 to 50									
Standard	Outlet air atmospheric *Note2			-40				-60			
Performance	pressure dew point °C					-00					
	Inlet air flow rate L/min(ANR)	93	135	224	308	400	75	140	230		
9	Outlet air flow rate L/min(ANR)	75	110	170	240	300	50	100	150		
ard anc ons	Purge air flow rate L/min(ANR)*Note3	18	25	54	68	100	25	40	80		
Standard erformanc conditions	Inlet air pressure MPa	0.7									
Standard Performance conditions	Inlet air temperature °C	25									
<u>م</u>	Inlet air saturation temperature °C	25									
	Ambient temperature °C	25									
Dew point ind	icator purge air flow rate	1 L/min (ANR) {In the case of inlet air pressure 0.7MPa}									
Regulator con	struction (about Type V)	Relief type									
Port size		1/4 · 3/8 3/8 · 1/2									
	Mass kg	3.0	3.1	3.8	3.9	4.0	3.8	3.9	4.0		

\* Note 1. When using the product in the temperature range between -5 and 5 deg. C, prevent water droplets from entering the inlet port. (No freezing of the fluid)
\* Note 2. "ANR" indicates the flow rate converted to the value at 20 deg. C, under the atmospheric pressure and the state of relative humidity 65%.
\* Note 3. Includes 1 L/min [ANR] of purge air flow (at 0.7 MPa inlet air pressure) for the dew point indicator (except IDG3, 3H, 5, 5H).
\* Note 4. Option: S (for IDG3, 3H, 5, 5H)

#### Revision history

- A: Changes to Maintenance and Checks
- B: Correction of specification column

# **SMC** Corporation

4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021 JAPAN Tel: + 81 3 5207 8249 Fax: +81 3 5298 5362

URL http://www.smcworld.com Note: Specifications are subject to change without prior notice and any obligation on the part of the manufacturer. © 2018 SMC Corporation All Rights Reserved