

Certificate of Compliance

Certificate Number:

UL-CA-L216656-41-
71406002-8

Report Reference:

E216656-20060417

Issue Date:

2024-11-27

Issued to:

**SMC CORP
4-14-1 SOTO-KANDA CHIYODA-KU, Tokyo 101-0021
Japan**

This certificate confirms that representative samples of:

**NKPZ8 - Motor Controllers, Float- and Pressure-operated
Certified for Canada - Component**

See Addendum Page for Product Designation(s).

Have been evaluated by UL in accordance with the component requirements in the Standard(s) indicated on this Certificate. UL Recognized components are incomplete in certain constructional features or restricted in performance capabilities and are intended for installation in complete equipment submitted for investigation to UL LLC.

CSA C22.2 No. 14, Edition 13, Issue Date 2018-03, Revision Date 2022-06

Additional Information:

See UL Product iQ® at <https://iq.ulprospector.com> for additional information.

This Certificate of Compliance indicates that representative samples of the product described in the certification report have met the requirements for UL certification. It does not provide authorization to apply the UL Recognized Component Mark. Only the Authorization Page that references the Follow-Up Services Procedure for ongoing surveillance provides authorization to apply the UL Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



David Piecuch
UL Mark Certification Program Owner

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.



CERTIFICATE OF COMPLIANCE

Certificate number UL-CA-L216656-41-71406002-8
Report reference E216656-20060417
Date 2024-11-27

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Model	Product Description
IZEII Series, IZEII, , followed by 1, followed by 1, followed by 0, 1, 2 or 3, may be followed by additional suffix(es).	Digital Flow Switch
PF2M7, , may be prefixed by up to 3 alphanumeric characters, followed by 01, 02, 05, 10, 11, 21, 25 or 50, may be followed by L, S or W, followed by 01, 02, C4, C6, C8, F1, F2, N1, N2 or N7, followed by A, B, C, D, E, F, L, L2, L3 or L4, may be followed by N, Q or W, may be followed by -, may be followed by M, may be followed by R, S, T or V, may be followed by A, may be followed by additional suffixes.	Digital Flow Switch, Class 2
PF2MC7, , may be prefixed by up to 3 alphanumeric characters, followed by 102-, 202- or 501-, may be followed by F or N, followed by 00, followed by A, B, C, D, E or F, may be followed by N, may be followed by M, may be followed by R, may be followed by A, may be followed by additional suffixes.	Float and Pressure Operated Motor Controllers
PF2MC7 series, Model PF2MC7, may be prefixed by up to 3 alphanumeric characters, followed by 102- or 501-, , may be followed by F or N, followed by 04, followed by A, B, C, D, E or F, may be followed by N, may be followed by M, may be followed by R, may be followed by A, may be followed by additional suffixes.	Float and Pressure Operated Motor Controllers
PF2MC7, may be prefixed by up to 3 alphanumeric characters, followed by 102- or 501-, may be followed by F or N, , followed by 04, followed by L, L2, L3 or L4, may be followed by N or Q, may be followed by M, may be followed by R, may be followed by A, may be followed by additional suffixes.	Float and Pressure Operated Motor Controllers
PF2MC7, may be prefixed by up to 3 alphanumeric characters, followed by 102-, 202- or 501-, may be followed by F or N, , followed by 00, followed by L, L2, L3 or L4, may be followed by N or Q, may be followed by M, may be followed by R, may be followed by A, may be followed by additional suffixes.	Float and Pressure Operated Motor Controllers
PF2MC7202-, , may be prefixed by up to 3 alphanumeric characters, may be followed by F or N, followed by 06, followed by A, B, C, D, E or F, may be followed by N, may be followed by M, may be followed by R, may be followed by A, may be followed by additional suffixes.	Float and Pressure Operated Motor Controllers
PF2MC7202-, may be prefixed by up to 3 alphanumeric characters, may be followed by F or N, followed by 06, , followed by L, L2, L3 or L4, may be followed by N, may be	Float and Pressure Operated Motor Controllers

CERTIFICATE OF COMPLIANCE

Certificate number UL-CA-L216656-41-71406002-8
Report reference E216656-20060417
Date 2024-11-27

followed by M, may be followed by R, may be followed by A, may be followed by additional suffixes.	
PF3W3, , followed by 0, followed by A, B, C, D, E, F, G, H, J, or K, followed by N, followed by M, G, F, or J, may be followed by T or V, may be followed by C, may be followed by A, may be followed by additional suffix(es).	Digital Flow Switch Display, Class 2
PF3W5-Z , PF3W5, , may be prefixed by up to 3 alphanumeric characters, followed by 04, 20, 40, 11, or 21, may be followed by S, may be followed by N, F, or U, followed by 00, 03, 04, 06, 10, 12, 14, 25, 30 or 32, followed by 1, 2, 1T, or 2T, may be followed by N, may be followed by G, F, or J, may be followed by R, may be followed by C, may be followed by A, may be followed by additional suffix(es) except Z.	Float and Pressure Operated Motor Controllers
PF3W5-Z series , PF3W5, , may be prefixed by up to 3 alphanumeric characters, followed by 04, 11, 20 or 40, may be followed by S, may be followed by F or N, followed by 00, 03, 04, 06 or 10, followed by 1, 2, 1T or 2T, may be followed by N, may be followed by G, may be followed by R, may be followed by A, followed by Z, may be followed by additional suffix(es).	Digital Flow Switch Remote Unit, Class 2
PF3W5, , may be prefixed by up to 3 alphanumeric characters, followed by 04, 20, 40, 11, or 21, may be followed by S, may be followed by N, F, or U, followed by 00, 03, 04, 06, 10, 12, 14, 25, 30 or 32, followed by 1, 2, 1T, or 2T, may be followed by N, may be followed by G, F, or J, may be followed by R, may be followed by C, may be followed by A, may be followed by additional suffix(es) except Z.	Digital Flow Switch Remote Unit, Class 2
PF3W7-Z series , PF3W7, , may be prefixed by up to 3 alphanumeric characters, followed by 04, 11, 20, 40, may be followed by S, may be followed by F or N, followed by 00, 03, 04, 06 or 10, followed by A, B, C, D, E, F, G, H, AT, BT, CT, DT, ET, FT, JT or KT, may be followed by N, followed by F, G, J or M, may be followed by R, may be followed by A, followed by Z, may be followed by additional suffix(es).	Float and Pressure Operated Motor Controllers
PF3W7-L series , PF3W7, may be prefixed by up to 3 alphanumeric characters, followed by 04, 11, 20 or 40, may be followed by S, may be followed by F or N, followed by 00, 03, 04, 06, 10, 12 or 14, followed by L, L2, LT or L2T, may be followed by N or Q, may be followed by M, may be followed by R, may be followed by A, followed by Z, may be followed by additional suffix(es).	Float and Pressure Operated Motor Controllers
PF3W7 , PF3W7, , may be prefixed by up to 3 alphanumeric characters, followed by 04, 20, 40, 11, 21, may be followed by S, may be followed by F, N or U, followed by 00, 03, 04, 06, 10, 12, 14, 25, 30, or 32,	Digital Flow Switch with Integrated Display, Class 2

CERTIFICATE OF COMPLIANCE

Certificate number UL-CA-L216656-41-71406002-8
Report reference E216656-20060417
Date 2024-11-27

followed by A, B, C, D, E, F, G, H, AT, BT, CT, DT, ET, FT, JT or KT, may be followed by N, followed by M, G, F, or J, may be followed R, may be followed by A, may be followed by additional suffix(es) except Z.	
PF3W7-L series , PF3W721, , may be prefixed by up to 3 alphanumeric characters, may be followed by F or N, followed by 00, 03, 04, 06, 10, 12 or 14, followed by L, L2, LT or L2T, may be followed by N or Q, may be followed by M, may be followed by R, may be followed by A, may be followed by additional suffix(es).	Float and Pressure Operated Motor Controllers
PFM3, , followed by 0 or 1, followed by 0, 1, 2, 3, 4, or 5, followed by -M or blank, followed by L or blank, followed by B, D, E, or blank, followed by F or blank, followed by -N or blank, followed by A or blank, may be followed by additional suffix(es).	Digital Flow Switch, Class 2
PFMB7 or PFMC7, , followed by 501, 102, or 202, followed by 04, N04, F04, 06, N06, or F06, followed by A, B, C, D, E, F, G, or H, may be followed by N, may be followed by M, may be followed by R, may be followed by A, may be followed by -X101, -X107 or -X110, may be followed by additional suffix(es).	Digital Flow Switch, Class 2
PFMB7201, , may be followed by S, followed by 02, N02, F02, C6, C8, N7, may be followed by L, followed by A, B, C, D, E, F, G, or H, may be followed by W or N, may be followed by M, may be followed by R, S, T, V, may be followed by A, may be followed by additional suffix(es).	Digital Flow Switch, Class 2
PFMV3, , followed by 0, followed by 0, 1, 2, 3, 4 or 5, followed by -M or blank, followed by L or blank followed by E, B, D or blank, followed by G or blank, followed by -N or blank, followed by A or blank, may be followed by additional suffix(es).	Digital Flow Switch, Class 2