

EQYG Certification: UL 2011 and CSA C22.2 No.14



Certification Mark

Certified Options

EQYG	Size	Bearing Type	Motor Mounting	H	Lead	-	Stroke	Motor Option	-	B	I/O Communication
	16	M	Nil		H		30	Without Option			5
	25	L	D		A		50	B			6
	32		D1		B		100				LA
			D2		C		150				LB
			D3				200				
			D4				250				
							300				