

# Rotary Actuator

## Series CRA1

Rack Pinion Style/Size: 30, 50, 63, 80, 100

**Models with cushion or with solenoid valve available.**

(Only sizes  $\geq 50$  are available.)

**Angle adjustement is possible.**

Size 30..... Fine angle adjuster is standard equipment.

Size 50 or larger..... Angle adjustable style

**Auto switch is mountable.**

Adjustment of switch location is easy with rail mounting.



### Series Variations

Fluid		Air					Hydraulic oil				Page
Size		30	50	63	80	100	50	63	80	100	
<b>Rotation angle</b>	90°	●	●	●	●	●	●	●	●	●	
	100°	●	●	●	●	●	●	●	●	●	
	180°	●	●	●	●	●	●	●	●	●	
	190°	●	●	●	●	●	●	●	●	●	
<b>Shaft style</b>	Single shaft	●	●	●	●	●	●	●	●	●	
	Double shaft	●	●	●	●	●	●	●	●	●	
	Single shaft with four chamfers	●	●	●	●	●	●	●	●	●	
	Double shaft key	●	●	●	●	●	●	●	●	●	
	Double shaft with four chamfers	●	●	●	●	●	●	●	●	●	
<b>Cushion</b>	Without air cushion	●	●	●	●	●	●	●	●	●	4-176 to 4-196
	With air cushion	●	●	●	●	●	●	●	●	●	
<b>Variations</b>	With auto switch	●	●	●	●	●	●	●	●	●	
	Angle adjustable style	●	●	●	●	●	●	●	●	●	
	Clean specification 11-	●	●	●	●	●	●	●	●	●	
	Copper free (standard)	●	●	●	●	●	●	●	●	●	
	Built-in one-touch fittings	●	●	●	●	●	●	●	●	●	
	Flange	●	●	●	●	●	●	●	●	●	
		●	●	●	●	●	●	●	●	●	
<b>Option</b>	<b>Mounting bracket</b>	●	●	●	●	●	●	●	●	●	
	Foot	●	●	●	●	●	●	●	●	●	
<b>Made to Order</b>	<b>Material of main part</b>	●	●	●	●	●	●	●	●	●	4-197 to 4-214
	Stainless steel -X6	●	●	●	●	●	●	●	●	●	
	<b>Shaft style</b>	Single shaft	●	●	●	●	●	●	●	●	
		Single shaft with four chamfers	●	●	●	●	●	●	●	●	
		Double shaft key	●	●	●	●	●	●	●	●	
		Double shaft with four chamfers	●	●	●	●	●	●	●	●	
		Single round shaft	●	●	●	●	●	●	●	●	
		Double shaft (Round, With four chamfers)	●	●	●	●	●	●	●	●	
		Double round shaft	●	●	●	●	●	●	●	●	
	<b>Operating temp.</b>	●	●	●	●	●	●	●	●	●	
	100°C at maximum	●	●	●	●	●	●	●	●	●	
	<b>Patterns</b>	Shaft end shape	●	●	●	●	●	●	●	●	
		Rotation range	●	●	●	●	●	●	●	●	
		Port location	●	●	●	●	●	●	●	●	
	Both sides angle adjustable	●	●	●	●	●	●	●	●	●	
	One side angle adjustable, One side with cushion	●	●	●	●	●	●	●	●	●	
	Fluorine rubber as seal material	●	●	●	●	●	●	●	●	●	




# Rotary Actuator


## Series *CRA1*

Rack Pinion Style/Size: 30, 50, 63, 80, 100

### How to Order



### Foot Brackets Part No.



Size	Foot bracket	Mounting screws included in foot bracket
30	CRA1L30-Y-1	M5 X 25
50	CRA1L50-Y-1	M8 X 35
63	CRA1L63-Y-1	M10 X 40
80	CRA1L80-Y-1	M12 X 50
100	CRA1L100-Y-1	M12 X 50



Notes) The part numbers shown above include mounting screw.  
As ordering foot bracket, write "1 piece" for the bracket for one rotary actuator.



# Rotary Actuator Rack Pinion Style **Series CRA1**

## Specifications



Style	Pneumatic					Air-hydro			
Size	30	50	63	80	100	50	63	80	100
Fluid	Air (Non-lube)					Hydraulic oil			
Max. operating pressure	1MPa								
Min. operating pressure	0.1MPa								
Ambient and fluid temperature	0° to 60°C (No freezing)								
Cushion	None	With or without air cushion				None			
Output <sup>(1)</sup> (Nm)	1.9	9.3	17	32	74	9.3	17	32	74
Allowable surge pressure	—————					1.5MPa			
Backlash	(2)	Within 1°							
Tolerance in rotating angle	—	+4° 0							



Note 1) Output under the operating pressure of 0.5MPa.

Note 2) Since CRA1□30 has a stopper installed, there is no backlash produced under pressure.

## Allowable Kinetic Energy/Safe Range of Rotation Time


Model	Allowable kinetic energy			Safe range of rotation time
	Allowable kinetic energy (J)		Cushion angle	
	Without cushion	With cushion <sup>(1)</sup>		Rotation time (s/90°)
CRA1□W30	0.01	—	—	0.2 to 1
CRA1□□50	0.05	0.98	35°	0.2 to 2
CRA1□□63	0.12	1.5	35°	0.2 to 3
CRA1□□80	0.16	2.0	35°	0.2 to 4
CRA1□□100	0.54	2.9	35°	0.2 to 5



Note 1) Allowable kinetic energy of the bumpers equipped model

The maximum absorbed energy under proper adjustment of the cushion needle.

JIS symbol



P.4-197 to 4-214

## Weight/Standard

(kg)

Model	Standard weight		Additional weight	
	90°	180°	Foot bracket	Flange bracket
<b>CRA1BW30</b>	0.3	0.4	0.1	—
<b>CRA1BW50</b>	1.5	1.7	0.3	0.5
<b>CRA1BW63</b>	2.5	3	0.5	0.9
<b>CRA1BW80</b>	4.3	5	0.9	1.5
<b>CRA1BW100</b>	8.5	9.5	1.2	2

## Weight/With Auto Switches and Solenoid Valves

(kg)

Size	Additional weight	
	With 2 auto switches	With solenoid valve*
<b>30</b>	0.1	—
<b>50</b>	0.2	0.2
<b>63</b>	0.4	0.2
<b>80</b>	0.6	0.2
<b>100</b>	0.9	0.2




\* Weight of the solenoid valve is not included. Refer to p.1.4-17 concerning weight of the solenoid valve.



# Series CRA1

## Rotary Actuator with Built-in One-touch Fittings

CRA1 Mounting Shaft style Size **F** Rotation Additional symbol  
 ↓  
 With built-in one-touch fittings



Piping steps and installation space are saved.

### Specifications

Style	Pneumatic
Applicable size	<b>30, 50, 63</b>
Max. operating pressure	1MPa
Min. operating pressure	0.1MPa
Auto switch	Mountable

### Applicable Tube Specification

Size	30	50	63
Applicable tube O.D.	ø4	ø6	
Applicable tube materials	Nylon, Soft nylon, Polyurethane		

Refer to p.4-182 to 4-184 for dimensions.

## Clean Series Rotary Actuator

11—CRA1 Mounting Shaft type Size Rotation Additional symbol  
 ↓  
 Clean series

Vacuum ports are equipped to prevent dust from being produced from the rod part of the rotary actuators.

### Specifications

Style	Pneumatic
Applicable size	<b>30, 50</b>
Max. operating pressure	1MPa
Min. operating pressure	0.1MPa
Auto switch	Mountable

## Copper Free Rotary Actuator

No influence on cathode ray tubes by copper ion and fluorine resin. As standard models are already made applicable to copper free styles, they can be applied as they are.

### Specifications


Style	Pneumatic
Applicable size	<b>30, 50, 63, 80, 100</b>
Max. operating pressure	1MPa
Min. operating pressure	0.1MPa
Auto switch	Mountable




## Rotation Range of Key Grooves

If air pressure is applied from the A side of the direction indication label, the shaft rotates clockwise. If air pressure is applied from the B side, the shaft rotates counterclockwise.

### Size: 30



### Size: 50 to 100



Stopper screw A: For end adjustment in clockwise direction  
Stopper screw B: For end adjustment in counter clockwise direction.

## How to Set The Rotation Time



Even if the torque that is generated by the rotary actuator is small, the parts could become damaged depending on the inertia of the load. Therefore, the rotation time should be determined by calculating the load's inertial moment and kinetic energy.





# Series CRA1

## Construction

Without air cushion  
Size: 30



Without air cushion  
Size: 50 to 100



### Component Parts

No.	Description	Material	Note
①	Body	Aluminum alloy	Hard anodized
②	Cover (Right)	Aluminum alloy	Black anodized
③	Cover (Left)	Aluminum alloy	Black anodized
④	Piston	Aluminum alloy	Chromated
⑤	Shaft	Chromium-molybdenum steel	
⑥	Rack	Carbon steel	Nitrided
⑦	Stopper	Chromium-molybdenum steel	
⑧	Stopper screw	Chromium-molybdenum steel	Black dyed
⑨	Slider	Resin	
⑩	Bearing retainer	Zinc alloy <sup>(1)</sup>	Black painted
⑪	Tube gasket	NBR	



Note 1) Size 50 to 100: Aluminum alloy (Black alumite)


### Component Parts

No.	Description	Material	Note
⑫	Piston packing	NBR	
⑬	O ring	NBR	
⑭	Bearing	Carbon steel	
⑮	Hexagon socket head cap screw spring washer	Chromium-molybdenum steel	Black zinc chromated
⑯	Hexagon socket head cap flange screw	Chromium-molybdenum steel	Zinc chromated
⑰	Cross-recessed countersunk head screw	Steel wire	Black dyed
⑱	Hexagon nut	Steel wire	Black dyed
⑲	Spring pin	Steel wire	
⑳	Parallel key	Carbon steel	
㉑	Parallel key	Carbon steel	
㉒	Connecting screw	Carbon steel	Zinc chromated
㉓	Cross-recessed round head screw	Steel wire	Black zinc chromated





# Rotary Actuator Rack Pinion Style **Series CRA1**


## With air cushion



## With auto switch Size: 30



## Size: 50 to 100



## Component Parts

No.	Description	Material	Note
24	Auto switch mounting rail	Aluminum alloy	
25	Auto switch	—	
26	Plastic magnet	Magnetic substance	
27	Cross-recessed head cap screw	Steel wire	Nickel plated
28	Hexagon nut	Steel wire	Nickel plated
29	Needle valve	Steel wire	Nickel plated
30	Lock nut	Steel wire	Nickel plated
31	Cushion packing	NBR	
32	O ring	NBR	
33	Cross-recessed head cap screw	Steel wire	Nickel plated

## Replacement Parts (Corresponding parts shown below are set.)

Size	Replacement parts			
	Standard	With air cushion	With auto switch	Air-hydro
<b>CRA1□W30-90</b>	P294010-20	—	P294010-20	—
<b>CRA1□W30-180</b>	P294010-21	—	P294010-21	—
<b>CRA1□□50</b>	P294020-20A	P294020-20A	P294020-20A	P294020-23A
<b>CRA1□□63</b>	P294030-20A	P294030-20A	P294030-20A	P294030-23A
<b>CRA1□□80</b>	P294040-20	P294040-20	P294040-20	P294040-23
<b>CRA1□□100</b>	P294050-20A	P294050-20A	P294050-20A	P294050-23A
Corresponding parts	⑨, ⑪, ⑫, and ⑰ are set.			




Note) When ordering spare parts, write "1 piece" for 1 set of the parts for one actuator.




# Series CRA1

Size **30**/Standard: CRA1BW, Foot Style: CRA1LW

Standard/CRA1BW30



Foot style/CRA1LW30



\* The dimensions above show pressurization to B port.  
\* ( ) are the dimensions for rotation of 180°




# Rotary Actuator Rack Pinion Style **Series CRA1**

Size **50, 63, 80, 100**/Standard: CRA1B□

Size: 50 to 100

Single shaft style/CRA1BS


Single shaft



\*The dimensions above show pressurization to B port.

\*( ) are the dimensions for rotations of 180° and 190°.

Double shaft style/CRA1BW  
Double shaft




Note) Other dimensions are the same as the single shaft.

Models	Port size	A	B	C	D (g6)	DD (h9)	F	H	J	K	S	U	W	BA	BB	CA*	CB*	Key dimensions	
CRA1BS50	1/8	62	48	46	15	25	2.5	36	M8 Depth 8	5	144 (177)	98	17	17	8.5	8.5	13	5 <sup>0</sup> <sub>0.030</sub>	25
CRA1BS63	1/8	76	60	57	17	30	2.5	41	M10 Depth 12	5	163 (201.5)	117	19.5	20	10	10	14	6 <sup>0</sup> <sub>0.030</sub>	30
CRA1BS80	1/4	92	72	70	20	35	3	50	M12 Depth 13	5	186 (230)	142	22.5	23.5	12	12	18	6 <sup>0</sup> <sub>0.030</sub>	40
CRA1BS100	3/8	112	85	85	25	40	4	60	M12 Depth 14	5	245 (311)	172	28	25	12.5	12.5	18	8 <sup>0</sup> <sub>0.036</sub>	45

Models	D (g6)	G	M	N	UU	L
CRA1BW50	15	11	20	15	118	14
CRA1BW63	17	13	22	17	139	16
CRA1BW80	20	15	25	20	167	19
CRA1BW100	25	19	30	25	202	24


Single shaft with four  
chamfers/CRA1BX



Note) Other dimensions are the same as the single shaft.

Models	G	H	N	U	L
CRA1BX50	11	27	15	89	14
CRA1BX63	13	29	17	105	16
CRA1BX80	15	38	20	130	19
CRA1BX100	19	44	25	156	24


Double shaft key/CRA1BY



Note) Other dimensions are the same as the single shaft.

Models	H	K	UU	L
CRA1BY50	36	5	134	25
CRA1BY63	41	5	158	30
CRA1BY80	50	5	192	40
CRA1BY100	60	5	232	45

Double shaft with four  
chamfers/CRA1BZ



Note) Other dimensions are the same as the single shaft.


Models	G	H	M	N	UU	L
CRA1BZ50	11	27	20	15	109	14
CRA1BZ63	13	29	22	17	127	16
CRA1BZ80	15	38	25	20	155	19
CRA1BZ100	19	44	30	25	186	24



# Series CRA1

Size **50, 63, 80, 100**/Foot Style: CRA1L□, Flange Style: CRA1F□

Foot style/CRA1L□




\*Dimensions above show pressurization to B port.

\*( ) are the dimensions for rotation of 180° and 190°

Models	LA	LB	LC	LD	LE	LF	LH	LT
CRA1L□50	62	9	44	200 (233)	224 (257)	41	108	4.5
CRA1L□63	76	11	55	235 (273.5)	263 (301.5)	48	127	5
CRA1L□80	92	13	67	274 (318)	316 (360)	58	154	6
CRA1L□100	112	13	87	333 (399)	375 (441)	73.5	189.5	6


Flange style  
Single shaft/CRA1FS



Other dimensions are the same as standard.

Models	F	H	MM	U	FD	FT	FX	FY	ZX	ZY
CRA1F□50	4	39	M6 Depth12	114	9	13	90	50	110	81
CRA1F□63	5	45	M6 Depth12	136	11.5	15	105	59	130	101
CRA1F□80	5	55	M8 Depth16	165	13.5	18	130	76	160	119
CRA1F□100	5	60	M10 Depth20	190	13.5	18	150	92	180	133


Flange style  
Double shaft/CRA1FW



Other dimensions are the same as the single shaft.

Models	H	N	U	UU
CRA1FW□50	39	15	114	134
CRA1FW□63	45	17	136	158
CRA1FW□80	55	20	165	190
CRA1FW□100	60	25	190	220


Flange style  
Single shaft with four chamfers/  
CRA1FX



Other dimensions are the same as the single shaft.

Models	H	N	U
CRA1FX□50	30	15	105
CRA1FX□63	33	17	124
CRA1FX□80	43	20	153
CRA1FX□100	44	25	174


Flange style  
Double shaft key/  
CRA1FY



Other dimensions are the same as the single shaft.

Models	H	U	UU
CRA1FY□50	39	114	150
CRA1FY□63	45	136	177
CRA1FY□80	55	165	215
CRA1FY□100	60	190	250

Flange style  
Double shaft with four chamfers/  
CRA1FZ



Other dimensions are the same as the single shaft.

Models	H	N	U	UU
CRA1FZ□50	30	15	105	125
CRA1FZ□63	33	17	124	146
CRA1FZ□80	43	20	153	178
CRA1FZ□100	44	25	174	204



# Rotary Actuator with Auto Switch

## Series *CDRA1*

Rack Pinion Style/Size: 30, 50, 63, 80, 100



### How to Order

**Size 30**

**Size 50 to 100**

**Thread Port**

—	Rc(PT)
E	G(PF)

**Built-in magnet**

**Mounting**

B	Basic
L	Foot

**Shaft styles**

Std.	S	Single shaft
Option	W	Double shaft
Option	X	Single shaft with four chamfers
Option	Y	Double shaft key
Option	Z	Double shaft with four chamfers

**Style**

—	Pneumatic
H	Air-hydro

**Rotation angle**

90	90°
180	180°

**No. of auto switches mounted**

S	1
—	2

Note) Max. no. auto switches mountable is two.

**Auto switch**

\* Refer to the table below for part numbers of applicable auto switch.

**Rotation angle**

Std.	90	90°
Option	180	180°
Option	100	100°
Option	190	190°

**Cushion**

—	Without cushion
C	With cushion

**Size**

50
63
80
100

**Ordering Example**

Size 30: CDRA1 B W30 90 A72 S

Size 50 to 100: E CDRA1 B W 50 90 A53 S

### Auto Switch Specifications

Style	Special function	Electrical entry	Indicator	Wiring (Output)	Load voltage		Auto switch part No.			Lead wire length <sup>(1)</sup> (m)				Applicable load				
					DC	AC	Size 30		Size 50 to 100	0.5 (—)	3 (L)	5 (Z)	— (N)					
							Perpendicular	In-line						In-line				
Reed switch	—	Grommet	Yes	3 wire (Equivalent to NPN)	—	5V	—	—	A76H	A56	●	●	—	—	IC	—		
					—	—	200V	A72	A72H	—	●	●	—	—	—		Relay PLC	
					12V	100V	A73	A73H	—	●	●	●	—	—	IC			
		Connector Grommet	Yes	2 wire	24V	5V,12V	≤ 100V	A80	A80H	—	●	●	—	—		IC	—	
						12V	—	A73C	—	—	●	●	●	●	—	PLC		
		Connector	No			12V	—	—	—	A53	●	●	●	—	—		Relay PLC	
						5V,12V	≤ 24V	A80C	—	—	●	●	●	●	IC	Relay PLC		
		Grommet	Yes			—	100V,200V	—	—	A54	●	●	●	—	—		—	IC
						—	—	—	—	A67	●	●	—	—	IC	Relay PLC		
	—			100V,200V	—	—	A64	●	●	—	—	IC	Relay PLC					
Diagnostic indicator (2 colour)	Yes	—	—	A79W	—	A59W	●	●	—	—	—	—		—	—			
Solid state switch	—	Grommet	Yes	2 wire	—	—	100V,200V	—	—	J51	●	●	○	—	—	Relay PLC		
				3wire(NPN)	5V,12V	—	F7NV	F79	F59	●	●	○	—	IC				
				3wire(PNP)			F7PV	F7P	F5P	●	●	○	—		—			
		Connector	2 wire	12V	—	F7BV	J79	J59	●	●	○	—	—	—				
			—	—	—	J79C	—	—	●	●	●	●	—	—				
		Grommet	3wire(PNP)	24V	5V,12V	—	—	F7PW	F5PW	●	●	○	—	IC	—			
			3wire(NPN)				—	F79W	F59W	●	●	○	—	—				
			Grommet	2 wire	—	—	—	J79W	J59W	●	●	○	—	—	—			
		Water resistant (2 colour) <sup>(2)</sup>		—	—	—	F7BA <sup>(2)</sup>	F5BA <sup>(2)</sup>	—	●	○	—	—	—				
	Timer	—		—	—	F7NT	F5NT	—	●	○	—	IC						
Diagnostic output (2 colour)	—	—		—	F59F	●	●	○	—	—								

Note 1) Symbols for wire lengths 0.5m..... (—) Ex.) A80C 3m..... L Ex.) A80CL 5m..... Z Ex.) A80CZ — .....N Ex.) A80CN

Auto switches marked with "○" in the table are made to order specification.


Note 2) This rotary actuator is not a improved product in water proof.

• Consult SMC when using F7BA\* and F5BA\*.




# Series CDRA1

## Rotation Range of Key Grooves/Switch Mounting Positions





## Operation Principles

In the diagram below, switch B is ON. When pressure is applied from A, the piston moves to B, causing the shaft to rotate clockwise. At this time, magnet B goes out of the movement range of switch B, causing switch B to turn OFF. Furthermore, the piston moves to the right, causing magnet A to enter the movement range of switch A. As a result, switch A turns ON.



## Proper Mounting Positions for Auto Switches



Operating angle  $\theta_m$ : Converts the operating range (Lm) of the auto switch into the rotation angle  
(1) Angle of hysteresis: The hysteresis of the auto switch is converted to degrees.

Model	A (mm)	Operating angle $\theta_m$	Angle of hysteresis (1)
CDRA1□W30-90	9 (19)	95°	20°
CDRA1□□50-90	9 (26)	65°	20°
CDRA1□□63-90	11 (30)	60°	10°
CDRA1□□80-90	15 (37)	45°	7°
CDRA1□□100-90	27 (60)	35°	5°

\* The dimensions inside "( )" are for 180°. \*\* Up to 2 auto switches can be mounted per actuator.  
The dimensions in the table are the values that represent the most sensitive positions of the auto switches. Thus, they are not the dimensions that represent the mounting position at the time of shipment.  
\* Consult SMC concerning the angles for the auto switches other than the models D-A73 and D-A53.

## ⚠ Caution

- Be sure to read before handling.
- Refer to p. 6-15 before handling auto switches.


Sets of mounting screws for auto switch (Round head Phillips screw, Hexagon nut)

Model	Part No.
CDRA1□W30	P294010-24
CDRA1□□50 to 100	P294020-24




- Note 1) The above part numbers include 2 pieces of mounting screws and 2 pieces of nuts.  
Note 2) To order a set for 1 unit, the ordering quantity should be "1".





Size **30**/Standard: CDRA1BW, Foot Style: CDRA1LW



With auto switch  
Standard/CDRA1BW30



Foot style/CDRA1LW30



\* The dimensions above show pressurization to B port.  
\* ( ) are the dimensions for rotation of 180°







# Series CDRA1


Size **50, 63, 80, 100**/Standard: CDRA1B□

With auto switch

Single shaft/CDRA1BS



Double shaft/CDRA1BW  
Double shaft



Double shaft

Model	D(g6)	G	M	N	UU	L
CDRA1BW50	15	11	20	15	118	14
CDRA1BW63	17	13	22	17	139	16
CDRA1BW80	20	15	25	20	167	19
CDRA1BW100	25	19	30	25	202	24


\*The dimensions below show pressurization to B port.

\*( ) are the dimensions for rotation of 180° and 190°.

Single shaft

Model	Port size	A	B	C	D (g6)	DD (h9)	F	H	J	K	S	U	W	BA	BB	CA	CB	SA	SB	SC	SD	SE	Key dimensions	
CDRA1BS50	1/8	62	48	46	15	25	2.5	36	M8 X 1.25 X 8	5	156(189)	98	17	17	8.5	8.5	13	33	13.5	12	14	34	5 <sup>0</sup> <sub>-0.030</sub>	25
CDRA1BS63	1/8	76	60	57	17	30	2.5	41	M10 X 1.5 X 12	5	175(213.5)	117	19.5	20	10	10	14	33	14.5	12	21	34	6 <sup>0</sup> <sub>-0.030</sub>	30
CDRA1BS80	1/4	92	72	70	20	35	3	50	M12 X 1.75 X 13	5	199(243)	142	22.5	23.5	12	12	18	33	15.5	12	29	34	6 <sup>0</sup> <sub>-0.030</sub>	40
CDRA1BS100	3/8	112	85	85	25	40	4	60	M12 X 1.75 X 14	5	259(325)	172	28	25	12.5	12.5	18	33	16	12	39	34	8 <sup>0</sup> <sub>-0.036</sub>	45


Single shaft with four chamfers/  
CDRA1BX□



Other dimensions are the same as the single shaft.

Model	G	H	N	U	L
CDRA1BX□50	11	27	15	89	14
CDRA1BX□63	13	29	17	105	16
CDRA1BX□80	15	38	20	130	19
CDRA1BX□100	19	44	25	156	24


Double shaft key/CDRA1BY□



Other dimensions are the same as the single shaft.

Model	H	K	UU	L
CDRA1BY□50	36	5	134	25
CDRA1BY□63	41	5	158	30
CDRA1BY□80	50	5	192	40
CDRA1BY□100	60	5	232	45

Double shaft with four chamfers/  
CDRA1BZ□




Other dimensions are the same as the single shaft.

Model	G	H	M	N	U	UU	L
CDRA1BZ□50	11	27	20	15	89	109	14
CDRA1BZ□63	13	29	22	17	105	127	16
CDRA1BZ□80	15	38	25	20	130	155	19
CDRA1BZ□100	19	44	30	25	156	186	24



Size **50, 63, 80, 100**/Foot Style: CDRA1L, Flange Style: CDRA1F


Foot style/CDRA1L□



\*Dimensions above show pressurization to B port.  
\*( ) are the dimensions for rotation of 180° and 190°.

Model	LA	LB	LC	LD	LE	LF	LH	LT
CDRA1L□□50	62	9	44	212 (245)	236 (269)	41	108	4.5
CDRA1L□□63	76	11	55	247 (285.5)	275 (313.5)	48	127	5
CDRA1L□□80	92	13	67	287 (331)	329 (373)	58	154	6
CDRA1L□□100	112	13	87	347 (413)	389 (455)	73.5	189.5	6


Flange style  
Single shaft/CRA1FS



Other dimensions are the same as standard.

Model	F	H	MM	U	FD	FT	FX	FY	ZX	ZY
CDRA1F□□50	4	39	M6 Depth 12	114	9	13	90	50	110	81
CDRA1F□□63	5	45	M6 Depth 12	136	11.5	15	105	59	130	101
CDRA1F□□80	5	55	M8 Depth 16	165	13.5	18	130	76	160	119
CDRA1F□□100	5	60	M10 Depth 20	190	13.5	18	150	92	180	133


Flange style



Other dimensions are the same as the single shaft.

Model	H	N	U	UU
CDRA1FW□50	39	15	114	134
CDRA1FW□63	45	17	136	158
CDRA1FW□80	55	20	165	190
CDRA1FW□100	60	25	190	220


Flange style  
Single shaft with four  
chamfers  
/CDRA1FX



Other dimensions are the same as the single shaft.

Model	H	N	U
CDRA1FX□50	30	15	105
CDRA1FX□63	33	17	124
CDRA1FX□80	43	20	153
CDRA1FX□100	44	25	174


Flange style  
Double shaft key  
/CDRA1FY



Other dimensions are the same as the single shaft.

Model	H	U	UU
CDRA1FY□50	39	114	150
CDRA1FY□63	45	136	177
CDRA1FY□80	55	165	215
CDRA1FY□100	60	190	250

Flange style  
Double shaft with  
four chamfers  
/CDRA1FZ



Other dimensions are the same as the single shaft.

Model	H	N	U	UU
CDRA1FZ□50	30	15	105	125
CDRA1FZ□63	33	17	124	146
CDRA1FZ□80	43	20	153	178
CDRA1FZ□100	44	25	174	204




# Angle Adjustable Style Rotary Actuator

(Angle adjusting ability for standard equipment.)

## Series **CRA1**     **U**

Rack Pinion Style/Size: 50, 63, 80, 100

### How to Order



### Auto Switch Specifications

Style	Special function	Electrical entry	Indicator	Wiring (out put)	Load voltage		Auto switch part No.	Lead wire length* (m)			Applicable load		
					DC	AC		0.5 (—)	3 (L)	5 (Z)			
Reed switch	—	Grommet	Yes	3 wire (Equiv. to NPN)	—	5V	—	A56	●	●	—	IC	—
				2 wire		12V	—	A53	●	●	●	—	PLC
			24V		—	100V,200V	A54	●	●	●	—	Relay, PLC	
					—	—	A67	●	●	—	IC	PLC	
					—	100V,200V	A64	●	●	—	IC	Relay, PLC	
	Yes		—	—	A59W	●	●	—	—				
Solid state switch	—	Grommet	Yes	3 wire (NPN)	24V	5V,12V	—	F59	●	●	○	IC	Relay, PLC
				3 wire (PNP)				F5P	●	●	○		
	2 wire			—	100V,200V	J51	●	●	○	—			
						12V	J59	●	●		○		
						5V,12V	F5PW	●	●		○	IC	
	24V			—	—		F59W	●	●	○	—		
						J59W	●	●	○	IC			
	2 wire			5V,12V	F5BA	—	●	○					
	3 wire (NPN)				F5NT	—	●	○					
	4 wire (NPN)				F59F	●	●	○					
	Diagnostic indicator (2 colour)												

\*Symbols for lead wire length 0.5m..... — Ex.) A53  
 3m..... L Ex.) A53L  
 5m..... Z Ex.) 53Z

\*Auto switches without contact point marked with "○" are made to order specifications.

#### Foot Brackets/Part No.

Size	Foot bracket
<b>50</b>	P294020-25
<b>63</b>	P294030-25
<b>80</b>	P294040-25
<b>100</b>	P294050-25



The part numbers of bracket in the table above are for foot fittings including mounting screws.





### Specifications


Fluid	Air (Non-lube)
Cushion	Without cushion
Mounting	Basic, Foot, Flange style
Angle adjustable range	0° to 90°
Backlash	Within 1°

### Weight


Model	Standard weight		Additional weight
	90°	180°	
<b>CRA1 □□U 50</b>	1.5	1.7	0.5
<b>CRA1 □□U 63</b>	2.5	3.0	0.8
<b>CRA1 □□U 80</b>	4.3	5.0	1.5
<b>CRA1 □□U 100</b>	8.5	9.5	2.0

### Rotation Range of Key Groove

Adjusting direction is in the direction the arrows show.  
Adjusting angle at 90° at maximum.  
90° Type: 90° to 0°, 180° type: 180° to 90°



### How to Adjust Angle



Rotation angle becomes smaller by tightening the angle adjusting screw to the right.

### Adjusting angle per one rotation of angle adjusting screw



Size	50	63	80	100
Adjusting angle	8.2°	7.0°	6.1°	4.1°





# Series CRA1□□U

## Construction

Standard/CRA1□□U



With auto switch/CDRA1□□U



### Component Parts

No.	Description	Material	Note
①	Body	Aluminum alloy	Hard anodized
②	Right cover	Carbon steel	Black zinc anodized
③	Left cover	Aluminum alloy	Black anodized
④	Piston	Aluminum alloy	Chromated
⑤	Shaft	Chromium-molybdenum steel	
⑥	Parallel key	Carbon steel	
⑦	Slider	Delrin	
⑧	Connecting screw	Carbon steel	Zinc chromated
⑨	Bearing retainer	Aluminum alloy	Black anodized
⑩	Hexagon socket head cap screw with spring washer	Chromium-molybdenum steel	Black zinc anodized
⑪	Tube gasket	NBR	
⑫	Piston seal	NBR	
⑬	Bearing	Carbon steel	
⑭	Cross-recessed head cap screw	Steel wire	Black zinc anodized

### Component Parts

No.	Description	Material	Note
⑮	Spring pin	Steel wire	
⑯	Rack	Carbon steel	Nitrided
⑰	Stopper	Carbon steel	Zinc chromated
⑱	Stopper screw	Carbon steel	Black zinc anodized
⑲	O ring	NBR	
⑳	Seal washer	NBR	
㉑	E type stopper ring	Steel wire	Chromated
㉒	Hexagon nut	Steel wire	Nickel plated
㉓	Switch mounting rail	Aluminum alloy	
㉔	Auto switch		
㉕	Plastic magnet	Magnetic substance	
㉖	Cross-recessed head cap screw	Steel wire	Nickel plated
㉗	Cross-recessed head cap screw	Steel wire	Nickel plated
㉘	Hexagon nut	Steel wire	Nickel plated

### Replacement Parts (The corresponding parts shown below are set.)

Size (Type)	With angle adjuster, With angle adjuster and auto switch
CRA1□□U50	P294020-22A
CRA1□□U63	P294030-22A
CRA1□□U80	P294040-22
CRA1□□U100	P294050-22A
Corresponding parts	⑦, ⑪, ⑫, ⑮ and ㉔ are set.




Angle Adjustable Rotary  
Actuator Rack Pinion Style

Series **CRA1□□U**


Size **50, 63, 80, 100**/Standard: CRA1□□U

Single shaft style/CRA1BSU



Double shaft style/CRA1BWU

Model	D(g6)	G	L	M	N	UU
CRA1BWU50	15	11	14	20	15	118
CRA1BWU63	17	13	16	22	17	139
CRA1BWU80	20	15	19	25	20	167
CRA1BWU100	25	19	24	30	25	202



\*The dimensions below show pressurization to B port.

\*( ) are the dimensions for rotation of 180° and 190°.

Single shaft style


Model	Port size Rc(PT)	A	AU	B	BA	BB	BU	C	CU	D (g6)	DD (h9)	DU	EU	F	H	J	K	MU	S	SU	U	W	Key dimensions	
																							b	$\ell$
CRA1BSU50	1/8	62	15	48	17	8.5	11	46	9	15	25	14	12	2.5	36	M8 Depth 8	5	M16 X 1.5	144 (177)	45	98	17	5 $_{-0.030}^0$	25
CRA1BSU63	1/8	76	19	60	20	10	13	57	11	17	30	18	14	2.5	41	M10 Depth 12	5	M20 X 1.5	163 (201.5)	54.5	117	19.5	6 $_{-0.030}^0$	30
CRA1BSU80	1/4	92	22	72	23.5	12	16	70	13	20	35	22	19	3	50	M12 Depth 13	5	M24 X 1.5	186 (230)	62.5	142	22.5	6 $_{-0.030}^0$	40
CRA1BSU100	3/8	112	22	85	25	12.5	16	85	13	25	40	22	19	4	60	M12 Depth 14	5	M24 X 1.5	245 (311)	73.5	172	28	8 $_{-0.036}^0$	45



# Series **CRA1□□U**

## Size **50,63,80,100**


Single shaft with four chamfers/  
**CRA1BXU□**



Model	G	H	L	N	U
<b>CRA1BXU□50</b>	11	27	14	15	89
<b>CRA1BXU□63</b>	13	29	16	17	105
<b>CRA1BXU□80</b>	15	38	19	20	130
<b>CRA1BXU□100</b>	19	44	24	25	156

Other dimensions are the same as the single shaft.


Double shaft/CRA1BYU□



Model	l	H	K	UU
<b>CRA1BYU□50</b>	25	36	5	134
<b>CRA1BYU□63</b>	30	41	5	158
<b>CRA1BYU□80</b>	40	50	5	192
<b>CRA1BYU□100</b>	45	60	5	232

Other dimensions are the same as the single shaft.



Double shaft with four chamfers/  
**CRA1BZU□**



Model	G	H	L	M	N	U	UU
<b>CRA1BZU□50</b>	11	27	14	20	15	89	109
<b>CRA1BZU□63</b>	13	29	16	22	17	105	127
<b>CRA1BZU□80</b>	15	38	19	25	20	130	155
<b>CRA1BZU□100</b>	19	44	24	30	25	156	186

Other dimensions are the same as the single shaft.

**Foot style/CRA1L□U**



\*The dimensions below show pressurization to B port.

\*( ) are the dimensions for rotation of 180° and 190°.


Other dimensions are the same as the single shaft.

Model	LA	LB	LC	LD	LE	LF	LH	LT
<b>CRA1L□U50</b>	62	9	44	200 (233)	224 (257)	41	108	4.5
<b>CRA1L□U63</b>	76	11	55	235 (273.5)	263 (301.5)	48	127	5
<b>CRA1L□U80</b>	92	13	67	274 (318)	316 (360)	58	154	6
<b>CRA1L□U100</b>	112	13	87	333 (399)	375 (441)	73.5	189.5	6




Size **50, 63, 80, 100**

Single shaft flange style/CRA1FSU




Model	F	FD	FT	FX	FY	H	MM	U	ZX	ZY
CRA1F□U50	4	9	13	90	50	39	M6 X 12	114	110	81
CRA1F□U63	5	11.5	15	105	59	45	M6 X 12	136	130	101
CRA1F□U80	5	13.5	18	130	76	55	M8 X 16	165	160	119
CRA1F□U100	5	13.5	18	150	92	60	M10 X 20	190	180	133

Flange style  
Double shaft/  
CRA1FWU




Model	H	N	U	UU
CRA1FWU50	39	15	114	134
CRA1FWU63	45	17	136	158
CRA1FWU80	55	20	165	190
CRA1FWU100	60	25	190	220

Flange style  
Single shaft with  
four chamfers/  
CRA1FXU




Model	H	N	U
CRA1FXU50	30	15	105
CRA1FXU63	33	17	124
CRA1FXU80	43	20	153
CRA1FXU100	44	25	174

Flange style  
Double shaft key/  
CRA1FYU



Model	H	U	UU
CRA1FYU50	39	114	150
CRA1FYU63	45	136	177
CRA1FYU80	55	165	215
CRA1FYU100	60	190	250

Flange style  
Double shaft with  
four chamfers/  
CRA1FZU




Model	H	N	U	UU
CRA1FZU50	30	15	105	125
CRA1FZU63	33	17	124	146
CRA1FZU80	43	20	153	178
CRA1FZU100	44	25	174	204



# Series CRA1□□U

## Size 50,63,80,100

### Single shaft style/CDRA1BSU




\*The dimensions above show pressurization to B port.

\*( ) are the dimensions for rotation of 180° and 190°


Model	Port size Rc(PT)	□A	□B	□C	øD (g6)	øDD (h9)	F	H	J	K	S	U	W	BA	BB	SA	SB	SC	SD	SE	Key dimensions		AU	BU	CU	DU	EU	SU	MU
																					b	ℓ							
CDRA1BSU50	1/8	62	48	46	15	25	2.5	36	M8 Depth8	5	156 (189)	98	17	17	8.5	33	13.5	12	14	34	5 <sup>0</sup> <sub>-0.030</sub>	25	15	11	9	14	12	45	M16 X 1.5
CDRA1BSU63	1/8	76	60	57	17	30	2.5	41	M10 Depth12	5	175 (213.5)	117	19.5	20	10	33	14.5	12	21	34	6 <sup>0</sup> <sub>-0.030</sub>	30	19	13	11	18	14	54.5	M20 X 1.5
CDRA1BSU80	1/4	92	72	70	20	35	3	50	M12 Depth13	5	199 (243)	142	22.5	23.5	12	33	15.5	12	29	34	6 <sup>0</sup> <sub>-0.030</sub>	40	22	16	13	22	19	62.5	M24 X 1.5
CDRA1BSU100	3/8	112	85	85	25	40	4	60	M12 Depth14	5	259 (325)	172	28	25	12.5	33	16	12	39	34	8 <sup>0</sup> <sub>-0.036</sub>	45	22	16	13	22	19	73.5	M24 X 1.5

### Double shaft style/CDRA1BWU



Model	øD (g6)	□G	M	N	UU	øL
CDRA1BWU50	15	11	20	15	118	14
CDRA1BWU63	17	13	22	17	139	16
CDRA1BWU80	20	15	25	20	167	19
CDRA1BWU100	25	19	30	25	202	24

### Foot style/CDRA1LSU




\*The dimensions above show pressurization to B port.

\*( ) are the dimensions for rotation of 180° and 190°

Note) Other dimensions are the same as the single shaft.

Model	LA	øLB	LC	LD	LE	LF	LH	LT
CDRA1LSU50	62	9	44	212 (245)	236 (269)	41	108	4.5
CDRA1LSU63	76	11	55	247 (285.5)	275 (313.5)	48	127	5
CDRA1LSU80	92	13	67	287 (331)	329 (373)	58	154	6
CDRA1LSU100	112	13	87	347 (413)	389 (455)	73.5	189.5	6

### Single shaft flange style/CDRA1FSU



Model	F	H	MM	U	øFD	FT	FX	FY	ZX	ZY
CDRA1FSU50	4	39	M6 Depth12	114	9	13	90	50	110	81
CDRA1FSU63	5	45	M6 Depth12	136	11.5	15	105	59	130	101
CDRA1FSU80	5	55	M8 Depth16	165	13.5	18	130	76	160	119
CDRA1FSU100	5	60	M10 Depth20	190	13.5	18	150	92	180	133



# Series CRA1 Made to Order Specifications

## Change of Shaft End Shape/-XA1 to XA46



Consult SMC for further information on specifications, dimensions and delivery.

### Symbols

### -XA1 to XA46

1

## Change of shaft end shape

A wide selection of models is now available, as non-standard shaft configurations for the CRA1 series rotary actuators are provided in 60 styles.


### Applicable patterns

Size	30, 50, 63, 80, 100
Pattern	XA1 to XA24, XA33 to XA46, XC7 to XC11, XC30 to XC64

### Additional reminders

- Enter the dimensions within a range that allows for additional machining.
- SMC will make appropriate arrangements if no dimensions, tolerance, or finish instructions are given in the diagram.
- The length of the unthreaded portion is 2 to 3 pitches.
- Unless specified otherwise, the thread pitch is based on coarse metric threads.  
P = thread pitch  
M3, M4, M5,  
M6, M8, M10
- Enter the desired values in the  portion of the diagram.
- Consult SMC for made to order specifications other than those mentioned in "How to Order".
- Individual drawings for specific made to order models may not be available.  
Consult SMC separately if drawings are needed.

## How to Order



### How to order model with auto switches

Refer to p.4-185 concerning how to order for the auto switch equipped type.

### How to order angle adjustable style

Refer to p.4-190 concerning how to order for the angle adjustable type.



# Series CRA1

## Made to Order Specifications

### Change of Shaft End Shape/-XA1 to XA46

Consult SMC for further information on specifications, dimensions and delivery.

Symbols

-XA1 to XA46

1

## Change of shaft end shape

### Applicable shaft style/Pattern combination table (Size: 30, 50, 63, 80, 100)

Shaft style/S (Single shaft), W (Double shaft), Y (Double shaft key)

Symbol	Description	Shaft direction		Applicable size
		Upper	Lower	
-XA1	Female thread at the shaft end	●	—	30
-XA2	Female thread at the shaft end	—	●	
-XA13	Shaft through-hole	●	●	50
-XA14	Shaft through-hole and female thread	●	—	63
-XA15	Shaft through-hole and female thread	—	●	80
-XA16	Shaft through-hole and female thread	●	●	100
-XA24	Double key	●	—	

#### Shaft style

Symbol	Description	Shaft direction		Shaft style								Applicable size
		Upper	Lower	J	K	S	T	Y	X	Z		
-XA33	Female thread at the shaft end	●	—	●	●	—	●	—	—	—	30	
-XA34	Female thread at the shaft end	—	●	●	●	—	●	—	—	—		
-XA35	Female thread at the shaft end	●	—	—	—	—	—	—	●	●	50	
-XA36	Female thread at the shaft end	—	●	—	—	—	—	—	●	●		
-XA37	Round shaft with steps	●	—	●	●	—	●	—	—	—	63	
-XA38	Round shaft with steps	—	●	—	●	—	—	—	—	—	80	
-XA40	Shaft through-hole	●	●	—	●	—	●	—	—	—		
-XA41	Shaft through-hole	●	●	●	—	—	—	—	●	●	100	
-XA43	Shaft through-hole with female	●	●	—	●	—	●	—	—	—		
-XA44	Shaft through-hole with female	●	●	●	—	—	—	—	●	●		
-XA45	Intermediate chamfer	●	—	●	●	—	●	—	—	—		
-XA46	Intermediate chamfer	—	●	—	●	—	—	—	—	—		

#### Shaft style

Symbol	Description	Shaft style								Applicable size
		S	W	X	Y	Z	T	J	K	
-XC7	Reverse mounting of rotation shaft	●	●	●	—	—	●	●	—	50
-XC8	Change of rotation range	●	●	—	●	—	—	—	—	
-XC9		●	●	—	●	—	—	—	—	63
-XC10		●	●	—	●	—	—	—	—	80
-XC11		●	●	—	●	—	—	—	—	100
-XC30	Fluorine grease	●	●	●	●	●	●	●	●	30 to 100
-XC31	Change of rotation range and shaft rotation direction	●	●	—	●	—	—	—	—	
-XC32		●	●	—	●	—	—	—	—	50
-XC33		●	●	—	●	—	—	—	—	
-XC34		●	●	—	●	—	—	—	—	63
-XC35	Change of rotation range and angle adjusting direction	●	●	—	●	—	—	—	—	80
-XC36		●	●	—	●	—	—	—	—	
-XC37		●	●	—	●	—	—	—	—	100
-XC38		●	●	—	●	—	—	—	—	
-XC39	Change of rotation range and angle adjusting direction	●	●	—	●	—	—	—	—	50
-XC40		●	●	—	●	—	—	—	—	
-XC41		●	●	—	●	—	—	—	—	63
-XC42		●	●	—	●	—	—	—	—	80
-XC43	Change of rotation range and angle adjusting direction (Angle adjusting screw is equipped on the left.)	●	●	—	●	—	—	—	—	100
-XC44		●	●	—	●	—	—	—	—	
-XC45		●	●	—	●	—	—	—	—	100
-XC46		●	●	—	●	—	—	—	—	
-XC47	Change of rotation range and angle adjusting direction	●	●	—	●	—	—	—	—	30
-XC48		●	●	—	●	—	—	—	—	
-XC49		●	●	—	●	—	—	—	—	50
-XC50		●	●	—	●	—	—	—	—	
-XC51	Change of rotation range and angle adjusting direction (Angle adjusting screw is equipped on the left.)	●	●	—	●	—	—	—	—	63
-XC52		●	●	—	●	—	—	—	—	
-XC53		●	●	—	●	—	—	—	—	80
-XC54		●	●	—	●	—	—	—	—	
-XC55	Change of rotation range and angle adjusting direction	●	●	—	●	—	—	—	—	100
-XC56		●	●	—	●	—	—	—	—	
-XC57		●	●	—	●	—	—	—	—	30
-XC58		●	●	—	●	—	—	—	—	
-XC59	Change of port direction	●	●	●	●	●	●	●	●	50
-XC60		●	●	●	●	●	●	●	●	
-XC61		●	●	●	●	●	●	●	●	63
-XC62		●	●	●	●	●	●	●	●	
-XC63	Reverse mounting of auto switch	●	●	●	●	●	●	●	●	80
-XC64	One side hydro, One side air	●	●	●	●	●	●	●	●	100



# Series CRA1

## Made to Order Specifications

### Change of Shaft End Shape/-XA1 to XA33

Consult SMC for further information on specifications, dimensions and delivery.

## 1 Change of shaft end shape


### Symbols -XA1 to XA33

#### Additional reminders

- Enter the dimensions within a range that allows for additional machining.
- SMC will make appropriate arrangements if no dimensional, tolerance, or finish instructions are given in the diagram.
- The length of the unthreaded portion is 2 to 3 pitches.
- Unless specified otherwise, the thread pitch is based on coarse metric threads.  
P = thread pitch  
M3, M4, M5  
M6, M8, M10
- Enter the desired figures in the  portion of the diagram.
- If not specified, the chamfer "C" is 0.5.

#### Symbol: A1


Note) Except for the flange style. Machine female threads into the long end of the shaft. (Shafts S, W and Y are additionally machined.) The L dimension (maximum) is, as a rule, twice the size of the bolt.



Size	Q
30	M3
50	M4, M5, M6
63	M4, M5, M6
80	M4, M5, M6, M8
100	M5, M6, M8, M10

#### Symbol: A2


Note) Except for the flange style. Machine female threads into the short end of the shaft. (Shafts S, W and Y are additionally machined.) The L dimension (maximum) is, as a rule, twice the size of the bolt.



Size	Q
30	M3, M4
50	M4, M5, M6
63	M4, M5, M6
80	M4, M5, M6, M8
100	M5, M6, M8, M10

#### Symbol: A13


Note) Except for the flange style. Shaft through-hole (Shafts S, W, Y are additionally machined). Note) The minimum range of the machinable dimension for the  $\phi d$  area is 0.1mm.



Size	d
30	$\phi 2.5$
50	$\phi 4$ to $\phi 7$
63	$\phi 4$ to $\phi 8$
80	$\phi 6.8$ to $\phi 11$
100	$\phi 6.8$ to $\phi 13$

#### Symbol: A14


Note) Except for the flange style. Machine a special end (at the long end of the shaft), and machine female threads in the through-hole at the long end of the shaft, thus creating a through-hole to serve as the pilot hole. (Shafts S, W, Y are additionally machined.) The L dimension (maximum) is, as a rule, twice the size of the bolt. (Example: For M5 bolt: L max. = 10mm)



Size	30	50	63	80	100
Thread					
M3	$\phi 2.5$	—	—	—	—
M5	—	$\phi 4$	$\phi 4$	—	—
M6	—	$\phi 5$	$\phi 5$	—	—
M8	—	—	$\phi 6.8$	$\phi 6.8$	$\phi 6.8$
M10	—	—	—	$\phi 8.5$	$\phi 8.5$
M12	—	—	—	$\phi 10.3$	$\phi 10.3$
Rc X PT $1/8$	—	—	—	$\phi 8$	$\phi 8$
Rc X PT $1/4$	—	—	—	—	$\phi 11$

#### Symbol: A15


Note) Except for the flange style. Machine a special end (at the short end of the shaft), and machine female threads in the through-hole at the short end of the shaft, thus creating a through-hole to serve as the pilot hole. (Shafts S, W, Y are additionally machined.) The L dimension (maximum) is, as a rule, twice the size of the bolt. (Example: For M4 bolt: L max. = 8mm)



Size	30	50	63	80	100
Thread					
M3	$\phi 2.5$	—	—	—	—
M5	—	$\phi 4$	$\phi 4$	—	—
M6	—	$\phi 5$	$\phi 5$	—	—
M8	—	—	$\phi 6.8$	$\phi 6.8$	$\phi 6.8$
M10	—	—	—	$\phi 8.5$	$\phi 8.5$
M12	—	—	—	$\phi 10.3$	$\phi 10.3$
Rc (PT) $1/8$	—	—	—	$\phi 8$	$\phi 8$
Rc (PT) $1/4$	—	—	—	—	$\phi 11$

#### Symbol: A16


Note) Except for the flange style. Machine special ends (at both the long and short ends of the shaft), and machine female threads in the through-hole at both the long and short ends of the shaft, thus creating through holes to serve as pilot holes. (Shafts S, W, Y are additionally machined.) The L dimension (maximum) is basically twice the size of the bolt. (Example: For M5 bolt: L max. = 10mm)



Size	30	50	63	80	100
Thread					
M3	$\phi 2.5$	—	—	—	—
M5	—	$\phi 4$	$\phi 4$	—	—
M6	—	$\phi 5$	$\phi 5$	—	—
M8	—	—	$\phi 6.8$	$\phi 6.8$	$\phi 6.8$
M10	—	—	—	$\phi 8.5$	$\phi 8.5$
M12	—	—	—	$\phi 10.3$	$\phi 10.3$
Rc (PT) $1/8$	—	—	—	$\phi 8$	$\phi 8$
Rc (PT) $1/4$	—	—	—	—	$\phi 11$

#### Symbol: A24


Double keys. Additionally machine a key groove at 180° from the standard key position. (Shafts S, W, Y are additionally machined.)



Size	Key groove dimension	L1
30	3 X 3 X 14	3
50	5 X 5 X 25	5
63	6 X 6 X 30	5
80	6 X 6 X 40	5
100	8 X 7 X 45	5

#### Symbol: A33

Note) Except for the flange style. Machine female threads into the long end of the shaft. (Shafts J, K and T are additionally machined.) The L dimension (maximum) is, as a rule, twice the size of the bolt. (Example: For M3 bolt: L max. = 6mm)



Size	Q
30	M3
50	M4, M5, M6, M8
63	M4, M5, M6, M8, M10
80	M4, M5, M6, M8, M10, M12
100	M5, M6, M8, M10, M12



# Series CRA1


## Made to Order Specifications

### Change of Shaft End Shape/-XA34 to XA44

Consult SMC for further information on specifications, dimensions and delivery.


## 1 Change of shaft end shape Symbols -XA34 to XA44

**Symbol: A34** Note) Except for flange style  
Machine female threads into the short end of the shaft.  
(Shafts J, K and T additionally machined)  
The L dimension (maximum) is, as a rule, twice the size of the bolt.  
(Example: For M3 bolt: L = 6)




Size	Q
30	M3
50	M4, M5, M6, M8
63	M4, M5, M6, M8, M10
80	M4, M5, M6, M8, M10, M12
100	M5, M6, M8, M10, M12

**Symbol: A35** Note) Except for flange style  
Machine female threads into the long end of the shaft.  
(Shafts X and Z additionally machined)  
The L dimension (maximum) is, as a rule, twice the size of the bolt.  
(Example: For M3 bolt: L = 6)




Size	Q
30	M3
50	M4, M5, M6, M8
63	M4, M5, M6, M8, M10
80	M4, M5, M6, M8, M10, M12
100	M5, M6, M8, M10, M12

**Symbol: A36** Note) Except for flange style  
Machine threads into the short end of the shaft.  
(Shafts X and Z additionally machined)  
The L dimension (maximum) is, as a rule, twice the size of the bolt.  
(Example: For M3 bolt: L = 6)




Size	Q
30	M3
50	M4, M5, M6, M8
63	M4, M5, M6, M8, M10
80	M4, M5, M6, M8, M10, M12
100	M5, M6, M8, M10, M12

**Symbol: A37** Note) Except for flange style  
The shaft can be further shortened by machining a round shaft with steps on the long end of the shaft.  
(Shafts J, K and T are additionally machined)  
(If the shaft is not to be shortened, leave the X dimension blank)




Size	X	Lmax
30	3 to 25	X-2
50	3.5 to 36	X-2.5
63	3.5 to 41	X-2.5
80	4 to 50	X-3
100	5 to 60	X-4

**Symbol: A38** Note) Except for flange style  
The shaft can be further shortened by machining a round shaft with steps on the short end of the shaft.  
(Shaft K are additionally machined)  
(If the shaft is not to be shortened, leave the Y dimension blank)




Size	Y	Lmax
30	1 to 25	Y
50	1 to 36	Y
63	1 to 41	Y
80	1 to 50	Y
100	1 to 60	Y

**Symbol: A40** Note) Except for flange style  
Shaft through-hole  
(Shafts K and T are additionally machined)




Size	d
30	ø2.5
50	ø4 to ø 7.5
63	ø4 to ø 8
80	ø6.8 to ø11
100	ø6.8 to ø13

**Symbol: A41** Note) Except for flange style  
Shaft through-hole  
(Shafts J, X and Z are additionally machined)




Size	d
30	ø2.5
50	ø4 to ø 7.5
63	ø4 to ø 8
80	ø6.8 to ø11
100	ø6.8 to ø13

**Symbol: A43** Note) Except for flange style  
Shaft through-hole and female thread  
(Shafts K and T are additionally machined)



Size	30	50	63	80	100
Thread	ø2.5	—	—	—	—
M3	—	—	—	—	—
M5	—	ø4	ø4	—	—
M6	—	ø5	ø5	—	—
M8	—	—	ø6.8	ø 6.8	ø 6.8
M10	—	—	—	ø 8.5	ø 8.5
M12	—	—	—	ø10.3	ø10.3
Rc(PT)1/8	—	—	—	ø 8	ø 8
Rc(PT)1/4	—	—	—	—	ø11

**Symbol: A44** Note) Except for flange style  
Shaft through-hole and female thread  
(Shafts J, X and Z are additionally machined)



Size	30	50	63	80	100
Thread	ø2.5	—	—	—	—
M3	—	—	—	—	—
M5	—	ø4	ø4	—	—
M6	—	ø5	ø5	—	—
M8	—	—	ø6.8	ø 6.8	ø 6.8
M10	—	—	—	ø 8.5	ø 8.5
M12	—	—	—	ø10.3	ø10.3
Rc(PT)1/8	—	—	—	ø 8	ø 8
Rc(PT)1/4	—	—	—	—	ø11



# Series CRA1

## Made to Order Specifications

### Change of Shaft End Shape/-XA45 to -XA46

### Change of Rotation Range (Size 50 to 100)/-XC8 to -XC11

Consult SMC for further information on specifications, dimensions and delivery.

## 1 Symbols

### Change of shaft end shape -XA45, XA46

#### Additional reminders


- Enter the dimensions within a range that allows for additional machining.
- SMC will make appropriate arrangements if no dimensions, tolerance, or finish instructions are given in the diagram.
- Enter the desired figures in the  portion of the diagram.

#### Symbol: A45

Note) Except for the flange style.

The shaft can be further shortened by machining an intermediate flat on the long end of the shaft (the position is that of the standard flat, the key groove part).

(Shafts J, K and T are additionally machined.)




Size	X	W	L1max	L2max
30	8.5 to 25	1 to 2	X - 2	L1-2
50	12.5 to 36	1 to 5.5	X - 2.5	L1-2
63	13.5 to 41	1 to 6.5	X - 2.5	L1-2
80	16.5 to 50	1 to 8	X - 3	L1-3
100	21 to 60	1.5 to 10.5	X - 4	L1-4

#### Symbol: A46

Note) Except for the flange style.

The shaft can be further shortened by machining an intermediate chamfering on the short end of the shaft (the position is that of the standard chamfering, the key groove part).

(Shaft K is additionally machined.)



Size	Y	W	L1max	L2max
30	6.5 to 25	1 to 2	Y	L1-2
50	10 to 36	1 to 5.5	Y	L1-2
63	11 to 41	1 to 6.5	Y	L1-2
80	13.5 to 50	1 to 8	Y	L1-3
100	17 to 60	1.5 to 10.5	Y	L1-4

## 2 Symbols

### Change of rotation range -XC8 to XC11

CRA1 → Refer to the "How to Order" on p.4-197

#### Specification


Applicable size	50, 63, 80, 100
Applicable shaft style	Shaft S, W, Y

The patterns with the rotation angle of 90° and 180° are applicable to the respective patterns with the rotation angles of 100° and 190° of the Made to order specifications.

Symbol  
XC8 to -XC11

#### Symbol: C8


The rotation range is changed.



Note) If it is pressurized from the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C9


The rotation range is changed.



Note) If it is pressurized from the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C10


The rotation range is changed.



Note) If it is pressurized from the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C11

The rotation range is changed.



Note) If it is pressurized from the port indicated with the arrow, the shaft rotates in the clockwise direction.



# Series **CRA1** Made to Order Specifications Reverse Mounting of Rotation Shaft (Size: 50 to 100) **/-XC7** Change of Rotation Range (Size: 30 to 100) **/-XC30**

Consult SMC for further information on specifications, dimensions and delivery.

## 3 Reverse mounting of rotation shaft Symbol **-XC7**

CRA1 →Refer to p.4-197 for "How to Order". XC7

Reverse mounting of rotation shaft  
(-XC7)

### Specifications

Applicable size	50, 63, 80, 100
Applicable shaft style	Shaft S, W, X, T, J

## 4 Fluorine grease Symbol **-XC30**

CRA1 →Refer to p.4-197 for "How to Order". XC30


Fluorine grease

Lubricant oil in the seal part of packing and inner wall of the cylinder is changed to fluorine type.

### Specifications

Applicable size	30, 50, 63, 80, 100
Applicable shaft style	S, W, X, Y, Z, T, J, K

\*Refer to p.4-177 for other specifications.  
\*\*Except for air-hydro type.





# Series **CRA1** (Size 50 to 100) Made to Order Specifications Change of Rotation Range and Rotation Direction of Shaft/-XC31 to -XC36

Consult SMC for further information on specifications, dimensions and delivery.

## 5 Change of the rotation range and the rotation direction of shaft Symbols -XC31 to XC36

**CRA1** →Refer to the "How to Order" on p.4-197

**-XC31**

### Specification


Applicable size	50, 63, 80, 100
Applicable shaft style	Shaft S, W, Y

•The rotation range and the rotation direction of the shaft are changed. (-XC31 to -XC36)

The patterns with the rotation angle of 90° and 180° are applicable to the respective patterns with the rotation angles of 100° and 190° of the Made to order specification.

#### Symbol: **C31**


The rotation range is changed and the rotating direction is reversed.



Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: **C32**


The rotation range is changed and the rotating direction is reversed.



Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: **C33**


The rotation range is changed and the rotating direction is reversed.



Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: **C34**


The rotation range is changed and the rotating direction is reversed.



Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: **C35**


The rotation range is changed and the rotating direction is reversed.



Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: **C36**

The rotation range is changed and the rotating direction is reversed.



Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.



# Series **CRA1** (Size 50 to 100) Made to Order Specifications Change of Rotation Range and Angle Adjusting Direction/-XC37 to -XC42

Consult SMC for further information on specifications, dimensions and delivery.

Symbols

## 6 Change of rotation range and the angle adjusting direction -XC37 to XC42

CRA1 → Refer to the "How to Order" on p.4-197 —XC37

### Specification


Applicable size	50, 63, 80, 100
Applicable shaft style	Shaft S, W, Y

• The rotation range and the angle adjusting direction are changed. (-XC37 to XC42)


The patterns with the rotation angle of 90° and 180° are applicable to the respective patterns with the rotation angles of 100° and 190° of the Made to order specification.

#### Symbol: C37

The rotation range and the angle adjusting direction of the angle adjustable style are changed.




The rotation range under the adjustment of an angle at 60° is indicated below.




Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C38

The rotation range and the angle adjusting direction of the angle adjustable style are changed.




The rotation range under the adjustment of an angle at 60° is indicated below.




Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C39

The rotation range and the angle adjusting direction of the angle adjustable style are changed.




The rotation range under the adjustment of an angle at 60° is indicated below.




Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C40

The rotation range and the angle adjusting direction of the angle adjustable style are changed.




The rotation range under the adjustment of an angle at 60° is indicated below.




Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C41

The rotation range and the angle adjusting direction of the angle adjustable style are changed.




The rotation range under the adjustment of an angle at 60° is indicated below.




Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C42

The rotation range and the angle adjusting direction of the angle adjustable style are changed.



The rotation range under the adjustment of an angle at 60° is indicated below.



Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.



# Series **CRA1** (Size 50 to 100) Made to Order Specifications Change of Rotation Range and Angle Adjusting Direction/-XC43 to -XC46

Consult SMC for further information on specifications, dimensions and delivery.

Symbols

## 6 Change of rotation range and angle adjusting direction **-XC43 to XC46**

CRA1 →Refer to the "How to Order" on p.4-197 —XC43

### Specification


Applicable size	50, 63, 80, 100
Applicable shaft style	Shaft S, W, Y

- The rotation range and the angle adjusting direction are changed. (-XC43 to XC46)


The patterns with the rotation angle of 90° and 180° are applicable to the respective patterns with the rotation angles of 100° and 190° of the Made to order specification.

#### Symbol: C43

The rotation range and the angle adjusting direction of the angle adjustable style are changed.




The rotation range under the adjustment of an angle a 60° is indicated below




#### Symbol: C44

The rotation range and the angle adjusting direction of the angle adjustable style are changed.




The rotation range under the adjustment of an angle at 120° is indicated below




#### Symbol: C45

The rotation range and the angle adjusting direction of the angle adjustable style are changed.




The rotation range under the adjustment of an angle at 120° is indicated below




#### Symbol: C46

The rotation range and the angle adjusting direction of the angle adjustable style are changed.



The rotation range under the adjustment of an angle at 120° is indicated below





# Series CRA1 Made to Order Specifications

## Change of Rotation Range and Angle Adjusting Direction Angle adjusting screw moved to the left /-XC47 to XC52

Consult SMC for further information on specifications, dimensions and delivery.

### 7 Change of rotation range and angle adjusting direction (Angle adjusting screw moved to the left) -XC47 to XC52

Symbols

CRA1 →Refer to the "How to Order" on p.4-197

-XC47

#### Specification


Applicable size	50, 63, 80, 100
Applicable shaft style	Shaft S, W, Y

- The rotation range and the angle adjusting direction are changed. (-XC47 to XC52)


The patterns with the rotation angle of 90° and 180° are applicable to the respective patterns with the rotation angles of 100° and 190° of the Made to order specification.

#### Symbol: C47

For the angle adjusting style, angle adjusting screws are mounted to the left cover.




The rotation range under the adjustment of an angle at 60° is indicated below




Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C48

For the angle adjusting style, angle adjusting screws are mounted to the left cover.




The rotating range under the adjustment of an angle at 60° is indicated below




Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C49

For the angle adjusting style, angle adjusting screws are mounted to the left cover.




The rotating range under the adjustment of an angle at 60° is indicated below




Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C50

For the angle adjusting style, angle adjusting screws are mounted to the left cover.




The rotation range under the adjustment of an angle at 60° is indicated below




Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C51

For the angle adjusting style, angle adjusting screws are mounted to the left cover.




The rotation range under the adjustment of an angle at 60° is indicated below




Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.

#### Symbol: C52

For the angle adjusting style, angle adjusting screws are mounted to the left cover.



The rotation range under the adjustment of an angle at 60° is indicated below



Note) If it is pressurized to the port indicated with the arrow, the shaft rotates in the clockwise direction.



# Series CRA1

## Made to Order Specifications

### Change of Rotation Range and Angle Adjusting Direction

Angle adjusting screw  
moved to the left.

/-XC53 to XC58

Consult SMC for further information on specifications, dimensions and delivery.

#### Symbols

## 7 Change of rotation range and angle adjusting direction (Angle adjusting screw moved to the left) -XC53 to XC58

CRA1 →Refer to the "How to Order" on p.4-197 —XC53

#### Specification


Applicable size	50, 63, 80, 100
Applicable shaft style	Shaft S, W, Y

- The rotation range and the angle adjusting direction of the shaft are changed. (-XC53 to XC58)


The patterns with the rotation angle of 90° and 180° are applicable to the respective patterns with the rotation angles of 100° and 190° of the Made to order specification.

#### Symbol: C53

For the angle adjusting style, angle adjusting screws are mounted to the left cover.




The rotation range under the adjustment of an angle at 60° is indicated below.




#### Symbol: C54

For the angle adjusting style, angle adjusting screws are mounted to the left cover.




The rotation range under the adjustment of an angle at 60° is indicated below.




#### Symbol: C55

For the angle adjusting style, angle adjusting screws are mounted to the left cover.




The rotation range under the adjustment of an angle at 120° is indicated below.




#### Symbol: C56

For the angle adjusting style, angle adjusting screws are mounted to the left cover.




The rotation range under the adjustment of an angle at 120° is indicated below.




#### Symbol: C57

For the angle adjusting style, angle adjusting screws are mounted to the left cover.




The rotation range under the adjustment of an angle at 120° is indicated below.




#### Symbol: C58

For the angle adjusting style, angle adjusting screws are mounted to the left cover.



The rotation range under the adjustment of an angle at 120° is indicated below.





# Series **CRA1** Made to Order Specifications Change of Port Position (Size 30 to 100)/-XA59 to XA61 Reverse Auto Switch Mounting (Size 50 to 100)/-XC62

Consult SMC for further information on specifications, dimensions and delivery.

Symbols

**8**

Change of port position (Mounting location of the cover is changed.)

**-XC59 to XC61**

CRA1

→Refer to the "How to Order" on p.4-197

XC59

**Specification** \*Except for the solenoid valve equipped style.

Applicable size	30, 50, 63, 80, 100
-----------------	---------------------

Applicable shaft style	Shaft S, W, X, Y, Z, T, J, K
------------------------	------------------------------



- Port position is changed. (-XC59 to -XC61)

The patterns with the rotation angle of 90° and 180° are applicable to the respective patterns with the rotation angles of 100° and 190° of the Made to order specification.

For the bumper equipped type, the needle position is on the opposite side of the port.



**Symbol: C59**

Direction of the port is changed. (upwards)





**Symbol: C60**

Direction of the port is changed. (downwards)



**Symbol: C61**

Direction of the port is changed. (backwards)



**9**

Reverse mounting of the auto switch against the standard

Symbol

**-XC62**


CRA1

→Refer to the "How to Order" auto switch equipped type on p.4-185

XC62

**Symbol: C62**

The auto switch is reverse mounted to the standard.





# Series **CRA1** (Size 50 to 100) Made to Order Specifications One Side Air-hydro, One Side Air Style/-XC63 to XC64

Consult SMC for further information on specifications, dimensions and delivery.

## 10 One side air-hydro, One side air style

Symbols

-XC63, -XC64

CRA1 →Refer to the "How to Order" on p.4-197 —XC63

### Specifications

Applicable size	50, 63, 80, 100
Applicable shaft style	Shaft S, W, X, Y Z, T, J, K


\*Except for the solenoid valve equipped type, angle adjustable type and air cushion equipped type.

- One side air-hydro, One side air
- XC63: Left side air  
Right side air-hydro
- XC64: Left side air-hydro  
Right side air

The patterns with the rotation angle of 90°and 180° are applicable to the respective patterns with the rotation angles of 100°and 190° of the Made to order specification.

### Symbol: C63


One side air, one side air-hydro specifications (Left side air, right side hydro)



The figure shows the pressurized situation to the hydro pressure port.

### Symbol: C64

One side air, one side air-hydro specifications (Left side hydro, right side air)



The figure shows the pressurized situation to the air pressure port.



# Series **CRA1** (Size 30) Made to Order Specifications Without Key Groove (Shaft Style Variations)/Shaft Style: T, J, K


Consult SMC for further information on specifications, dimensions and delivery.

Symbols

**11**

Without key groove (Shaft style variations)

Shaft style: T, J, K



## Specifications

Style	Pneumatic*
Size	30
Shaft style	Single round rod end (T), Double round rod end (K), Double rod end/(w/o long rod end key & with four chamfers) (J)
Cushion	Without cushion
Auto switch	Mountable
Mounting style	Basic, Foot

\*Refer to p.4-177 for other specifications.

## Dimensions

(mm)

Shaft style	T (Single round shaft)	J (Double round shaft/Long shaft without key & with four chamfers)	K (Double round shaft)
Shape			




# Series **CRA1** (Size 50 to 100) Made to Order Specifications Without Key Groove (Shaft Style Variations)/Shaft Style: T, J, K

Consult SMC for further information on specifications, dimensions and delivery.

## 12 Without key groove (Shaft Variations)

Symbols

Shaft style: T, J, K



### Specifications

Style	Pneumatic	Air-hydro
Size	50, 63, 80, 100	
Fluid	Air (Non-lube)	Hydric oil
Shaft style	Single round shaft (T), Double round shaft (K), Double shaft/Long shaft without key and with four chamfers (J)	
Cushion	Not attached	Not attached
Auto switch	Mountable	
Mounting style	Basic, Foot	



Note) Except for flange style.  
\*Refer to p.4-177 for other specifications.

### Dimensions

(mm)

Shaft style	T(Single round shaft)		J(Double shaft/Long shaft without key & with four chamfers)					K(Double round shaft)		
Shape										
Size	D(g6)	H	D(g6)	H	M	N	UU	D(g6)	H	UU
50	15	36	15	36	20	15	118	15	36	134
63	17	41	17	41	22	17	139	17	41	158
80	20	50	20	50	25	20	167	20	50	192
100	25	60	25	60	30	25	202	25	60	232



\* Refer to p.4-182 and 4-183 for other specifications.



# Series **CRA1** (Size 30) Made to Order Specifications Shaft Variations/Shaft Style: S, X, Y, Z

Consult SMC for further information on specifications, dimensions and delivery.

## 13 Shaft variations

Symbols

Shaft style: S, X, Y, Z

C□RA1 Mounting Shaft style 30 Rotation



Refer to "How to Order" on p.4-176 and 4-185

### Shaft style

<b>S</b>	Single shaft key
<b>X</b>	Single shaft with four chamfers
<b>Y</b>	Double shaft key
<b>Z</b>	Double shaft with four chamfers

Six shaft types other than standard shaft type W (Double shaft) of size 30 are made into patterns.


### Specifications

Style	Pneumatic
Size	30
Max. operating pressure	1MPa
Min. operating pressure	0.1MPa
Shaft style	Single shaft key (S), Double shaft with four chamfers (X), Double shaft key (Y), Double shaft with four chamfers (Z)
Mounting	Basic, Foot
Auto switch	Mountable




\*Refer to p.4-177 for other specifications.


### S(Single shaft key)




### X(Single shaft with four chamfers)



### Y(Double shaft key)



### Z(Double shaft with four chamfers)





# Series **CRA1** Made to Order Specifications Stainless Steel for Main Part/-X6 Heat Resistant Style/-X7

Consult SMC for further information on specifications, dimensions and delivery.

## 14 Stainless steel for main part **-X6**

C □ RA1

Refer to the "How to Order" on p.4-176, 4-185

Symbol

**-X6**

S — X6

Stainless steel  
for main part

For applications in areas that pose a risk of rust or corrosion, a portion of the materials used in the standard parts has been changed to stainless steel.

### Specifications

Style	Pneumatic
Size	<b>30, 50, 63, 80, 100</b>
Fluid	Air (Non-lube)
Max. operating pressure	1MPa
Min. operating pressure	0.1MPa
Stainless steel part	Shaft, Bolt, Parallel key
Cushion	30—Without cushion 50 to 100—With or without air cushion
Auto switch	Mountable

\*Specifications other than indicated above are the same as that shown on p.4-177

\*\*Except for the angle adjustable style.

## 15 Heat resistant style **-X7**

CRA1

Refer to the "How to Order" on p.4-176 and 4-185

Symbol

**-X7**

— X7

Heat resistant style

In this rotary actuator, the material of the seals has been changed to the heat resistant type (to withstand up to 100°C), for applications in environments that exceed the standard specification temperatures of 0 to 60°C.

### Specifications

Style	Pneumatic
Size	<b>30, 50, 63, 80, 100</b>
Rotation	90°, 180° (Size 30 to 100) 100°, 190° (Size 50 to 100)
Ambient and fluid temperature	0 to 100°C
Lubrication	ISO VG32
Seal material	Fluorine rubber
Shaft style	Single shaft, Double shaft, Single shaft with four chamfers, double shaft key, Double shaft four chamfers Double round shaft, Double shaft (Round shaft, With four chamfers), Double round shaft
Cushion	30 — Without cushion 50 to 100 —With or without air cushion
Auto switch	Not mountable

\*Specifications other than indicated above are the same as that shown on p.4-177

\*\*Except for models with solenoid valve.

## 16 Fluorine rubber seal **-X16**

CDRA1

Refer to the "How to Order" on p.4-185 and 4-185

Symbol

**-X16**

— X16

Fluorine rubber seal

Seal is now changed to fluoro rubber.

### Specifications

Style	Pneumatic
Size	<b>30, 50, 63, 80, 100</b>
Fluid	Air (No lubrication)
Max. operating pressure	1MPa
Min. operating pressure	0.1MPa
Ambient and fluid temperature	0°C to 60°C (No condensation)
Seal material	Fluorine rubber
Cushion	30 — Not equipped 50 to 100 — Note equipped, With air cushion
Auto switch	Mountable

\*Specifications other than indicated above are the same as that shown on p.4-177


\*\*Except for models with solenoid valve.




# Series **CRA1** Made to Order Specifications Both Sides Angle Adjustable Style/-X10 One Side Angle Adjustable, One Side Cushion Style/-X11

Consult SMC for further information on specifications, dimensions and delivery.

## 17 Both sides angle adjustable Style **-X10** Symbol



## 18 One side angle adjustable, One side cushion style **-X11** Symbol



### Sepecifications

Style	Pneumatic
Size	<b>50, 63, 80, 100</b>
Rotation	90°, 180°, 100°, 190°
Shaft style	Single shaft (S), Double shaft (W), Single shaft with four chamfers (X), Double shaft key (Y), Double shaft with four chamfers (Z), Single round shaft (T), Double shaft/Round shaft, four chamfers (J), Double round shaft (K)
Cushion	Without cushion
Variations	With auto switch, With solenoid valve





\*Refer to p.4-177 for other specifications.

### Sepecifications

Type	Pneumatic
Size	<b>50, 63, 80, 100</b>
Rotation	90°, 180°, 100°, 190°
Shaft type	Single shaft (S), Double shaft (W), Single shaft with four chamfers (X), Double shaft key (Y), Double shaft with four chamfers (Z), Single round shaft (T), Double shaft/Round shaft, Four chamfers (J), Double round shaft (K)
Cushion	With cushion on one side
Auto switch	Mountable
Variations	With auto switch, With solenoid valve



\*Refer to p.4-177 for other specifications.



\* Refer to p.4-182 and 4-183 for dimensions.