# 3-Color Display Digital Flow Switch for Water

•3-color/2-screen display





IP65



Main screen
Sub screen

Instantaneous flow rate\*1

Set value













#### Instantaneous flow rate\*1

Accumulated value

Peak/Bottom value

Line name

Fluid temperature\*2

- \*1 Main screen shows the instantaneous flow rate only.
- \*2 Fluid temperature can be displayed only when the digital flow switch with a temperature sensor is selected.
- \*3 Sub screen can be turned off.

New have been added to the integrated display type.










- Applicable fluid: Deionized water, chemical liquids, etc.
- Integrated type and remote type added to series

**PF3W** Series
















### 🦰 Non-grease



#### **Mounting**



# Added: Measured flow rate 250 L/min type

#### Variations

Variations		Rated flow range	Flow	adjustment valve	e/Temperature s	ensor	Port size	
Туре	Applicable fluid	[L/min]	None	Flow adjustment valve	Temperature sensor	Flow adjustment valve + Temperature sensor	Rc, NPT, G	
Integrated		0.5 to 4					3/8	
	Water	2 to 16					3/8, 1/2	
Remote Sensor	Ethylene glycol aqueous solution	5 to 40					1/2, 3/4	
Monitor		10 to 100					3/4, 1	
		50 to 250					11/4, 11/2	
PVC piping Integrated type	Deionized water	10 to 100	•	_	_	_	25A	
Remote Sensor Monitor	Chemical liquids		•	_	_	_	30A	

# 3-color display Digital flow monitor: The set value can be copied to up to 10 flow monitors simultaneously.

The settings of the master monitor (source of copy) can be copied to the slave monitors.

- Reduced setting labor
- Minimized risk of setting mistakes





Slave side



COPY

22228







10 units














#### p. 16

### Supports the IO-Link communication protocol



#### Configuration File (IODD File\*1)

• Manufacturer • Product part no. • Set value

\*1 IODD File:

IODD is an abbreviation of IO Device Description. This file is necessary for setting the device and connecting it to a master. Save the IODD file on the PC to be used to set the device prior to use.

IO-Link is an open communication interface technology between the sensor/ actuator and the I/O terminal that is an international standard, IEC61131-9.



IO-Link Compatible Device: Digital Flow Switch for Water

# Device settings can be set by

- the master.
   Threshold value
- Operation mode, etc.

#### Read the device data.

- Switch ON/OFF signal and analog value
- Device information:

Manufacturer, Product part number, Serial number, etc.

- Normal or abnormal device status
- Cable breakage



0

0

0

#### Implement diagnostic bits in the process data.

The diagnostic bit in the cyclic process data makes it easy to find problems with the equipment.

It is possible to find problems with the equipment in real time using the cyclic (cycle) data and to monitor such problems in detail with the noncyclic (aperiodic) data.

#### **Process Data**

Bit offset	Item	Note
0	OUT1 output	0: OFF 1: ON
1	OUT2 output	0: OFF 1: ON
8	Diagnosis (error)	0: OFF 1: ON
9	Diagnosis (flow rate)	0: OFF 1: ON
10	Diagnosis (temperature)	0: OFF 1: ON
16 to 31	Measured temperature value	Signed 16 bit
32 to 47	Measured flow rate value	Signed 16 bit

## Diagnosis items • Over current error

- Above the rated flow range
- · Accumulated flow error
- Above the rated temperature range
- Below the rated temperature range
   Internal product malfunction
- Temperature sensor failure


Bit offset	47	46	45	44	43	42	41	40	39	38	37	36	35	34	33	32
Item		Measured flow rate value (PD)														
Bit offset	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
Item		Measured temperature value (PD)														
Bit offset	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Item		Reservation Temperature Flow rate Error Reservation				OUT2	OUT1									
	Diagnosis											Switch	output			

#### **Application Examples**

# For the predictive maintenance of cooling water problems

Monitors flow rate and temperature's "switch ON/ OFF signals" and "analog values" to determine the cooling status

The process and cooling status can be compared.



#### **Display function**

Displays the output communication status and indicates the presence of communication data









#### **Operation and Display**

Communication with master	IO-Link status indicator light	Status		Screen display	Description	
	<b>*</b> 1		=	Operate	ModE ofE	Normal communication status (readout of measured value)
			Normal	Start up		At the start of communication
				Preoperate	ModE PrE	At the start of communication
Yes	Flashing)	IO-Link mode	Abnormal	Version does not match	Er 15	The IO-Link version does not match that of the master. The master uses version 1.0.
				Lock	ModE LoE	Backup and restore required due to data storage lock.
No				Communication disconnection	ModE oPE ModE Strt ModE PrE	Normal communication was not received for 1 second or longer.
	OFF	5	SIO m	ode	ModE Sio	General switch output

<sup>\*1</sup> In IO-Link mode, the IO-Link indicator will be ON or flashing.

# CONTENTS

3-Color Display Digital Flow Switch for Water PF3W Series

3-Color Display Digit	al Flow	Switch	for Water	PF3W Series
-----------------------	---------	--------	-----------	-------------

3-Color Display Digital Flow Switch for PVC Piping PF3W Series

3-Color Display Digital Flow Monitor for Water PF3W3 Series





How to Order	p. :	0
Specifications (Integrated Display)	р. (	6
Specifications (Remote Sensor Unit)	р.	7
Temperature Sensor Specifications	o. 6, 7	7
Set Flow Range and Rated Flow Range	р.	7
Analog Output	p. 8	8
Operating Pressure and Proof Pressure	p. 8	8
Flow Rate Characteristics (Pressure Loss: Without Flow Adjustment Valve)	р. 9	9
Straight Piping Length and Accuracy (Reference Value)	р. 9	9
Flow Rate Characteristics of Flow Adjustment Valve	p. 10	0
Measurable Range for Ethylene Glycol Aqueous Solution (Reference Value)	p. 10	0
Wetted Parts Construction	p. 10	0
Internal Circuits and Wiring Examples	p. 1	1
Dimensions	p. 12	2
Made to Order		
EPDM seal material (-X109)		
Analog 4 to 20 mA 2-output type (-X128)	p. 1	5
Brass piping material specification (-X143)	p. 1	5
IO Link compatible ( VAAE)	- 47	^









How to Order	p. 17
Specifications (Integrated Display)	p. 18
Analog Output	p. 18
Operating Pressure and Proof Pressure	p. 18
Specifications (Remote Sensor Unit)	p. 19
Flow Rate Characteristics (Pressure Loss)	p. 19
Straight Piping Length and Accuracy (Reference Value)	p. 19
Wetted Parts Construction	p. 20
Internal Circuits and Wiring Examples	p. 11
Dimensions	p. 21
Made to Order	
EPDM seal material (-X109)	p. 23

3-Color Display Digital Flow Monitor for Water PF3	3W3 Series
How to Order	p. 24
Specifications	p. 25
Analog Output	p. 25
Internal Circuits and Wiring Examples	p. 26
Dimensions	p. 27
Function Details	p. 28
Applicable Fluids	p. 31
Safety Instructions	Back cover

# 3-Color Display

# **Digital Flow Switch for Water**

# PF3W Series (ERUS



#### **How to Order**

#### Remote sensor unit Output specification/Temperature sensor

For how to order of remote monitor unit. refer to page 24.

Symbo	OUT1	OUT2	Temperature
Symbo	Flow rate	Temperature	sensor
1	Analog 1 to 5 V	_	None
2	Analog 4 to 20 mA	_	None
1T	Analog 1 to 5 V	Analog 1 to 5 V	With temperature sensor



- To use in combination with remote monitor (PF3W3 series), select analog output of 1 to 5 V of flow rate (output symbol "-1" or "-1T").
- Analog output of 4 to 20 mA with temperature sensor is made to order. (Refer to page 15.)

#### Remote sensor unit/Unit printed on label

Symbol	Instantaneous flow	Temperature
Nil	L/min	°C
<b>G</b> *1	L/min (gal/min)	°C/°F

- \*1 Under the New Measurement Act, units other than SI (symbol "Nil") cannot be used in Japan.
- G: Made to order


Reference: 1 [L/min] ← 0.2642 [gal/min] 1 [gal/min] ←→ 3.785 [L/min] °F = 9/5°C + 32

Remote sensor unit









Rated flow range (Flow range)

_		
	Symbol	Rated flow range
	04	0.5 to 4 L/min
	20	2 to 16 L/min
	40	5 to 40 L/min
	11	10 to 100 L/min
	21	50 to 250 L/min

#### Thread type

	<u> </u>	
Nil	Rc	
N	NPT	
F	G*1	

\*1 ISO 228 equivalent

#### Port size

Symbol	Port	F	Rated	flow	range	Э
Syllibol	size	04	20	40	11	21
03	3/8	•	•	_	—	_
04	1/2	_	•	•	_	_
06	3/4	_	_	•	•	_
10	1/1	_	_	_	•	_
12	1 1/4	_	_	_	_	•
14	1 1/2	_	_	_	_	•

#### Flow adjustment valve

Symbol	With/without flow	Rated flow range				
Symbol	adjustment valve	04	20	40	11	21
Nil	None	•	•	•	•	•
S	Yes	•	•	•	_	_

\* 100 and 250 L/min types with flow adjustment

- valves are not available. The flow adjustment valve OUT1
- of this product is not suitable for applications which require constant adjustment of flow rate.
- \*1 External input: The accumulated value, peak value, and bottom value can be reset.
- \*2 For units with temperature sensor, only OUT2 can be set as either temperature output or flow rate output. Setting when shipped is for temperature output.

#### Integrated display Output specification/Temperature sensor

	Symbol	COTT	0012		remperature
	Symbol	Flow rate	Flow rate	Temperature	sensor
	Α	NPN	NPN	_	
	В	PNP	PNP	_	
	С	NPN	Analog 1 to 5 V	_	
	D	NPN	Analog 4 to 20 mA	_	None
	Е	PNP	Analog 1 to 5 V	_	None
(	F	PNP	Analog 4 to 20 mA	_	
	G	NPN	External input*1		
	Н	PNP	External input*1	_	
,	ΑT	NPN	(NPN) <u></u> ∗	2, NPN	
	BT	PNP	(PNP) 🚣	2→ PNP	With
t	СТ	NPN	(Analog 1 to 5 V) *	Analog 1 to 5 V	temperature
	DT	NPN	(Analog 4 to 20 mA) *	Analog 4 to 20 mA	sensor
	ET	PNP	(Analog 1 to 5 V) 💒	2 Analog 1 to 5 V	3611301
	FT	PNP	(Analog 4 to 20 mA) *	Analog 4 to 20 mA	

#### Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Description	Part no.	Qty.	No	ote
	ZS-40-K	1	For PF3W704/720/504/520	With 4 tapping screws (3 x 8)
Bracket*1	ZS-40-L	1	For PF3W740/540	With 4 tapping screws (3 x 8)
	ZS-40-M	1	For PF3W711/511	With 4 tapping screws (4 x 10)
Lead wire with M8 connector	ZS-40-A	1	Lead wire length: 3 m	

\*1 For units with flow adjustment valve, 2 brackets are required.

## Calibration certificate (Only for flow rate)


Nil None With calibration certificate

 The certificate is written in both Japanese and English. The integrated display type with temperature sensor can only display the flow rate.

#### Made to order

X109	EPDM seal material
	Analog 4 to 20 mA 2-output type*1
X143	Brass piping material specification
X445	IO-Link compatible*2

- \*1 Applicable only for remote type with temperature sensor (Refer to page 15.) \*2 Integrated display type only
- Bracket (Option)



Bracket is not available for 250 L/min type.

#### Integrated display/Unit specification


Symbol Instantaneous flow		Accumulated flow	Temperature
M L/min		L	°C
G	gal/min gal		°C
F	gal/min	gal	°F
J	L/min	L	°F

- \* Under the New Measurement Act, units other than SI (symbol "M") cannot be used in Japan.
- G, F, J: Made to order

Reference: 1 [L/min] ↔ 0.2642 [gal/min] 1 [gal/min] ↔ 3.785 [L/min]

 $^{\circ}F = 9/5^{\circ}C + 32$ 

Lead wire (Option)







# 3-Color Display Digital Flow Switch for Water **PF3W** Series

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

#### Specifications (Integrated Display)

M	odel		PF3W704	PF3W720	PF3W740	PF3W711	PF3W721	
Applicable fluid				ous solution (with visco				
Detection metho	od		Karman vortex					
Rated flow range		0.5 to 4 L/min	2 to 16 L/min	5 to 40 L/min	10 to 100 L/min	50 to 250 L/min		
D:!			0.35 to 5.50 L/min	1.7 to 22.0 L/min	3.5 to 55.0 L/min	7 to 140 L/min	20 to 350 L/min	
Display flow ran	ige		(Flow under 0.35 L/min is displayed as "0.00")	(Flow under 1.7 L/min is displayed as "0.0")	(Flow under 3.5 L/min is displayed as "0.0")	(Flow under 7 L/min is displayed as "0")	(Flow under 20 L/min is displayed as "0")	
Set flow range			0.35 to 5.50 L/min	1.7 to 22.0 L/min	3.5 to 55.0 L/min	7 to 140 L/min	20 to 350 L/min	
Smallest settab	le increm	nent	0.01 L/min	0.1 L	_/min	1 L/min	2 L/min	
Conversion of accumulate	ed pulse (Pulse	e width: 50 ms)	0.05 L/pulse	0.1 L/pulse	0.5 L/pulse	1 L/pulse	2 L/pulse	
Fluid temperatu	re			0 to 90°C (No freez			0 to 70°C (No freezing or condensation)	
Display unit					us flow: L/min, Accumu			
Accuracy				Display value	e: ±3% F.S. Analog outp	out: ±3% F.S.		
Repeatability					±2% F.S.*2			
Temperature ch				<u> </u>	5% F.S. (25°C standard	d)		
Operating press		je*3			0 to 1 MPa			
Proof pressure*					1.5 MPa		T	
Pressure loss (withou	t flow adjus	tment valve)			the maximum flow		60 kPa or less at the maximum flow	
Accumulated flo	w range	*4		999.9 L		999999999 L		
	range		By 0.1 L	By 0.5 L		By 1 L		
Switch output				NPN	or PNP open collector of	output		
		d current			80 mA			
		lied voltage	28 VDC					
		oltage drop	NPN: 1 V or less (at load current of 80 mA) PNP: 1.5 V or less (at load current of 80 mA)					
Response time*2,5 Output protection Output Flow rate mode Temperature		0.5 s/1 s/2 s						
		Short-circuit protection Select from Hysteresis, Window comparator, Accumulated output, or Accumulated pulse output modes.						
		Select from Hysteresis, window comparator, Accumulated output, or Accumulated pulse output modes.  Select from Hysteresis mode or Window comparator mode.						
		se time*6						
Analog autnut	Voltage							
Analog output	Current		Voltage output: 1 to 5 V Output impedance: 1 kΩ					
Hysteresis	Current	output	Output current: 4 to 20 mA Max. load impedance: 300 Ω for 12 VDC, 600 Ω for 24 VDC  Variable					
External input			Variable  Voltage free input: 0.4 V or less (Reed or Solid state), input for 30 ms or longer					
Display method			2-screen display (Main screen: 4-digit, 7-segment, 2-color, Red/Green Sub screen: 6-digit, 11-segment, White) Display values updated 5 times per second					
Indicator light			Output 1, Output 2: Orange					
Power supply vo	oltage		12 to 24 VDC ±10%					
Current consum		,			50 mA or less			
	Enclosu	ıre			IP65			
		nperature range		0 to 50°	C (No freezing or conde	nsation)		
Environment		numidity range			age: 35 to 85% R.H. (No			
		d voltage*7			minute between termin			
	Insulation resistance							
Standards and regulations		ns			MC directive/RoHS directive/RoHS directive/RoHS			
Wattad parts				PPS, S	tainless steel 304, FKM,	SCS13		
Wetted parts ma					Non-grease			
Piping port size			3/8	3/8, 1/2	1/2, 3/4	3/4, 1	1 1/4, 1 1/2	
Without temperature sen			210 g	260 g	410 g	720 g	890 g	
₩ith temperature sense	or/Without flow	adjustment valve	285 g	335 g	530 g	860 g	1075 g	
With temperature sense Without temperature sense With temperature sense			310 g	360 g	610 g		_	
<b>★</b> With temperature sens	sor/With flow a	djustment valve	385 g	435 g	730 g		_	
With lead wir	With lead wire with connector			<del></del>	+85 g	<del></del>	<del></del>	

- \*1 Refer to the graph of measurable range for ethylene glycol aqueous solution on page 10. Measurement is possible as long as the fluid does not corrode the wetted parts and viscosity is 3 mPa·s (3 cP) or less. Be aware that water leakage may occur due to internal seal shrinkage or swelling depending on the type of fluid. If 0.5 s is selected for the response time of the switch output, the repeatability will be ±3% F.S.
- The operating pressure range and proof pressure may change according to the fluid temperature. Refer to the graphs on page 8.
- Cleared when the power supply is turned off. The hold function can be selected. (Intervals of 2 or 5 minutes can be selected.) If the 5-minute interval is selected, the life of the memory element (electronic parts) is limited to 1 million times. (If energized for 24 hours, life is calculated as 5 minutes x 1 million = 5 million minutes = about 9.5 years.) Therefore, if using the hold function, calculate the memory life for your operating conditions, and use within this life. The response time when the set value is 90% in relation to the step input (The response time is 7 s when it is output by the temperature sensor.) The response time until the set value reaches 90% in relation to the step input (The response time is 7 s when it is analog output by the temperature sensor is used, it will be 250 VAC.

- \*8 For details, refer to "Wetted Parts Construction" on page 10.
- \*9 When the piping diameter or piping passage is restricted, the specifications may not be satisfied.


  \* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

#### Temperature Sensor Specifications

Rated temperature range	0 to 100°C*1		
Set/Display temperature range	−10 to 110°C		
Smallest settable increment	1°C		
Display unit	°C		
Display accuracy	±2°C		
Analog output accuracy	±3% F.S.		
Response time	7 s*2		
Ambient temperature characteristics	±5% F.S.		
the reted temperature range refere cololy to that of the temperature			

The rated temperature range refers solely to that of the temperature sensor. The fluid temperature range specification of the flow switch as a whole is 0 to 90°C





The OUT2 can be selected from either the output for temperature or flow rate by button operation.



<sup>\*2</sup> The response time refers solely to that of the temperature sensor.

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

#### Specifications (Remote Sensor Unit)

Refer to page 25 for monitor unit specifications.

Model		PF3W504	PF3W520	PF3W540	PF3W511	PF3W521	
Αp	plicable fluid		Water and ethylene glycol aqueous solution (with viscosity of 3 mPa⋅s [3 cP] or less)*1				
De	tection metho	od	Karman vortex				
Ra	Rated flow range		0.5 to 4 L/min	2 to 16 L/min	5 to 40 L/min	10 to 100 L/min	50 to 250 L/min
Flu	uid temperatu	re	0 t	o 90°C (No freezi	ng or condensation	on)	0 to 70°C (No freezing or condensation)
-	curacy				±3% F.S.		
	peatability				±2% F.S.		
-	mperature ch			±5%	F.S. (25°C stand	ard)	
	perating press				0 to 1 MPa*2		
	oof pressure*				1.5 MPa		
Pressure loss (without flow adjustment valve)		4	15 kPa or less at	the maximum flov	V	60 kPa or less at the maximum flow	
		Response time*3			1 s		
An	alog output	Voltage output			1 to 5 V Output in		
		Current output			oad impedance: 30	-, -, -	
	dicator light		For power supply status, flow rate indicator (Blinking speed changes in response to flow rate.), and other error indicator				
Po	wer supply v	oltage	12 to 24 VDC ±10%				
Cι	rrent consun		30 mA or less				
		Enclosure	IP65				
		Operating temperature range	0 to 50°C (No freezing or condensation)				
En	vironment	Operating humidity range	Operation, Storage: 35 to 85% R.H. (No condensation)				
		Withstand voltage*4	1000 VAC for 1 minute between terminals and housing				
		Insulation resistance	50 M $\Omega$ or more (500 VDC measured via megohmmeter) between terminals and housing				
Sta	andards and I	egulations	CE marking (EMC directive/RoHS directive), UL (CSA)				)
w	etted parts ma	aterial*5	PPS, Stainless steel 304, FKM, SCS13				
					Non-grease		
Pi	ping port size		3/8	3/8, 1/2	1/2, 3/4	3/4, 1	1 1/4, 1 1/2
	Without temperature sensor/Without flow adjustment valve		195 g	245 g	395 g	705 g	875 g
_	₩ith temperature sensor/Without flow adjustment valve		270 g	320 g	515 g	840 g	1060 g
ej	Without temperature sensor/With flow adjustment valve		295 g	345 g	595 g	_	_
≥	With temperature sen	sor/With flow adjustment valve	370 g	415 g	715 g	_	_
L	With lead wir	e with connector			+85 g		

- \*1 Refer to the graph of measurable range for ethylene glycol aqueous solution on page 10. Measurement is possible as long as the fluid does not corrode the wetted parts and viscosity is 3 mPa·s (3 cP) or less. Be aware that water leakage may occur due to internal seal shrinkage or swelling depending on the type
- \*2 The operating pressure range and proof pressure may change according to the fluid temperature. Refer to the graphs on page 8.
- \*3 The response time until the set value reaches 90% in relation to the step input (The response time is 7 s when it is analog output by the temperature
- sensor.)
  \*4 When the temperature sensor is used, it will be 250 VAC.
- \*5 For details, refer to "Wetted Parts Construction" on page 10.
- \*6 When the piping diameter or piping passage is restricted, the specifications may not be satisfied.
- \* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

#### Temperature Sensor Specifications

Rated temperature range	0 to 100°C*1
Analog output accuracy	±3% F.S.
Response time	7 s*2
Ambient temperature characteristics	±5% F.S.

- The rated temperature range refers solely to that of the temperature sensor. The fluid temperature range specification of the flow switch as a whole is 0 to 90°C.
- \*2 The response time refers solely to that of the temperature sensor.


#### **Set Flow Range and Rated Flow Range**

### **⚠** Caution

#### Set the flow rate within the rated flow range.

The set flow range is the range of flow rate within which setting is possible.

The rated flow range is the range within which the sensor specifications (accuracy, etc.) are satisfied. It is possible to set a value outside of the rated flow range if it is within the set flow range. However, the satisfaction of the specifications cannot be guaranteed.





For the PF3W5 series, the display flow range and set flow range are the same as those of the flow monitor PF3W3 series.




#### **Analog Output**

#### Flow rate/Analog output








## Fluid temperature/Analog output


# **PF3W7/5**

Voltage output	0.6 V	1 V	
Current output	2.4 mA	4 mA	
	С	D	
Voltage output	5 V	5.4 V	
Current output	20 mA	21.6 mA	




#### **Operating Pressure and Proof Pressure**


#### PF3W704/720/740/504/520/540




#### PF3W704S/720S/740S/504S/520S/540S



#### PF3W711/511




#### PF3W721/521




#### Flow Rate Characteristics (Pressure Loss: Without Flow Adjustment Valve)


#### PF3W704/504




#### PF3W720/520




#### PF3W740/540




#### PF3W711/511



#### PF3W721/521




#### Straight Piping Length and Accuracy (Reference Value)




- The smaller the piping size, the more the product is affected by the straight piping length.
- · Fluid pressure has almost no affect.
- Low flow rate lessens the effect of the straight piping length.
- Use a straight pipe that is 8 cm or longer in length to satisfy the ±3% F.S. specification. (11 cm or longer for 100 L/min and 250 L/min types)

#### Pressure: 0.3 MPa PF3W704/504 Piping diameter: ø12




#### PF3W720/520






PF3W740/540


Pressure: 0.3 MPa Piping diameter: ø16









No data for 4 cm, or for under 5 cm, as these cannot be used due to piping dimensions.






### Flow Rate Characteristics of Flow Adjustment Valve


#### PF3W704S/504S




#### PF3W720S/520S




#### PF3W740S/540S



# Measurable Range for Ethylene Glycol Aqueous Solution (Reference Value)



#### **Wetted Parts Construction**



#### **Component Parts**


Oomp.	Onent raits		
No.	Description	Material	Note
	Attachment	SCS13	Stainless steel 304 equivalent PF3W704/720/740/711/504/520/540/511
'	Attachment	Stainless steel 304	PF3W721/521
2	Seal	FKM	
3	Body	PPS	
4	Sensor	PPS	
5	Temperature sensor	Stainless steel 304	
6	Temperature sensor body	Stainless steel 304	
7	Flow adjustment valve body	PPS	
8	Flow adjustment valve cover	PPS	
9	Flow adjustment valve shaft	Stainless steel 304	
10	Shaft support	PPS	
11	Seal	FKM	
12	Seal	FKM	

#### Internal Circuits and Wiring Examples


PF3W7□□

-A(T)

NPN (2 outputs)




-B(T) PNP (2 outputs)




-C(T)/D(T)

C(T): NPN + Analog voltage output D(T): NPN + Analog current output




#### -E(T)/F(T)


E(T): PNP + Analog voltage output F(T): PNP + Analog current output



-G NPN + External input



PNP + External input




#### Accumulated pulse output wiring examples

-A(T)/C(T)/D(T)/G A(T): NPN (2 outputs)

C(T), D(T): NPN + Analog output

G: NPN + External input






-B(T)/E(T)/F(T)/H B(T): PNP (2 outputs)

E(T), F(T): PNP + Analog output

G: PNP + External input




#### PF3W5□□


-1/2

1: Analog voltage output

2: Analog current output




#### -1T Analog voltage output (With temperature sensor output)




#### **Dimensions**





Connector pin number




Pin no.	Pin name
1	DC (+)
2	OUT2
3	DC (-)
4	OUT1












# PF3W504/520/540/511/521








#### For PF3W521






																							[mm]
Model	Port size	_	Δ.Δ	В	D	DD	E	F	G	н		V		N	Р			Brac	ket di	imen	sions		
Model	(Rc, NPT, G)	A	AA	В	ן די	שט	=	-	G	п	J	,	<b>-</b>	IN	P	S	Т	U	٧	W	WX	Υ	Z
PF3W704/504	3/8	70	50	30	60	45.6	40.6	15.2	24	14	35	26	18	13.6	ø2.7 depth 14	24	22	32	40	50	4.5	5	1.5
PF3W720/520	3/8, 1/2	78	54	30	60	45.6	40.6	15.2	27	18	39	30	18	13.6	ø2.7 depth 12	28	22	32	40	50	4.5	5	1.5
PF3W740/540	1/2, 3/4	98	71	38	68	53.6	48.6	19.2	32	28	49	35	28	16.8	ø2.7 depth 12	34	30	42	48	58	4.5	5	1.5
PF3W711/511	3/4, 1	124	92	46	77	62.6	57.6	23.0	41	42	63	48	28	18.0	ø3.5 depth 14	44	36	48	58	70	5.5	7	2.0
	1 1/4, 1 1/2	104	74							31	52	39.5											
PF3W721/521	G1 1/4	108	76	56	91	76.6	71.6	28.5	54	33	54	41.5	25	27.5	ø3.5 depth 14	_	—	_	—	—	_	_	—
	G1 1/2	112	78							35	56	43.5											


#### **Dimensions**

# PF3W704/720/740/711/721-□-□T Integrated display: With temperature sensor




		[mm]
Model	A	AA
PF3W704/504-□-□T	81	50
PF3W720/520-□-□T	89	54
PF3W740/540-□-□T	109	71
PF3W711/511-□-□T	135	92
PF3W721/521-□-□T	115	74
PF3W721/521-F12-□T	119	76
PF3W721/521-F14-□T	123	78

# PF3W504/520/540/511/521-□-□T Remote sensor unit: With temperature sensor




#### PF3W704S/720S/740S

Integrated display: With flow adjustment valve




### PF3W504S/520S/540S



													[mm]	
Model	_	АА	В	D	F	к		_   N	Р	D	Q	Q number	Bracket dimensions	
Model	A	AA	P	ט	Г		-	l IN		Q	of rotations	S	Т	
PF3W704S/504S	104	50	63.6 (Max. 68.6)	70.2	34	58.5	18	13.6	ø2.7 depth 10	ø19	6	56.5	22	
PF3W720S/520S	112	54	63.6 (Max. 68.6)	74.2	34	62.5	18	13.6	ø2.7 depth 10	ø19	6	60.5	22	
PF3W740S/540S	142	71	75.25 (Max. 81)	94.5	44	79.0	28	16.8	ø2.7 depth 10	ø28	7	78.0	30	


### Dimensions

# PF3W704S/720S/740S-□-□T Integrated display: With temperature sensor and flow adjustment valve



					[mm]
Model	Α	AA	D	K	s
PF3W704S/504S-□-□T	115	50	81.2	69.5	67.5
PF3W720S/520S-□-□T	123	54	85.2	73.5	71.5
PF3W740S/540S-□-□T	153	71	105.5	90.0	89.0


# PF3W504S/520S/540S-□-□T Remote sensor unit: With temperature sensor and flow adjustment valve



#### ZS-40-A Lead wire with M8 connector

OUT1 Black

4



## Lead Wire Specifications

Conductor	Nominal cross section	AWG23
	O.D.	Approx. 0.7 mm
	Material	Heat-resistant PVC
Insulator	O.D.	Approx. 1.1 mm
	Color	Brown, White, Black, Blue
Sheath	Material	Heat- and oil-resistant PVC
Finished	O.D.	ø4

- \* 4-wire type lead wire with M8 connector used for the PF3W series
- $\ast~$  For wiring, refer to the "Operation Manual" on the SMC website (http://www.smcworld.com).



# **Made to Order**



Please contact SMC for detailed dimensions, specifications, and lead times.

	Symbol
1 EPDM seal material	-X109
Seal material for wetted parts changed to EPDM	
PF3W5 <u>X109</u>	
PF3W7 <del>X109</del>	
● EPDM seal material	
Refer to page 5 for details of How to Order.	
* Not compatible with units with flow adjustment valve	
Please special-order separately.	
	Symbol
2 Analog 4 to 20 mA 2-output type	-X128
Output specification of remote type with a temperature sensor: Analog 4 to 20 mA 2 outputs	
PF3W5	
♦ Analog 4 to 20 mA 2-output type	
Refer to page 5 for details of How to Order.	
. Describe an efficient for a final control of	
* Remote monitor unit is equipped as standard.	
	Symbol
Brass piping material specification	-X143
Piping (attachment) material changed to brass	
PF3W5 <u>X143</u>	
PF3W7 <u>X143</u>	
	Fire the last property   Piping (attachment)
▶ Brass piping (attachment) material specification	
Refer to page 5 for details of How to Order.	

\* Not compatible with units with flow adjustment valve Please special-order separately.

Surface treatment is not applied on piping.




4 IO-Link compatible

Symbol -X445

Supports the IO-Link communication protocol

#### **How to Order**



#### Rated flow range (Flow range)

04	0.5 to 4 L/min							
20	2 to 16 L/min							
40	5 to 40 L/min							
11	10 to 100 L/min							
21	50 to 250 L/min							

#### 2 Thread type

<u> </u>	icaa type
Nil	Rc
N	NPT
F	G*1
*1 ISO	228 compliant

## 3 Piping port size

Cumbal	Port size	w rar	nge			
Syllibol	Port Size	04	20	40	11	21
03	3/8	•	•	_	_	_
04	1/2	_	•	•	_	_
06	3/4	_	_	•	•	_
10	1	_	_	_	•	_
12	1 1/4	_	_	_	_	•
14	1 1/2	_	_	_	_	•

#### Output specification/Temperature sensor

Symbol	Output specification		Temperature
Syllibol	OUT1	OUT2	sensor
LT	IO-Link: Switch output (N/P)	_	Yes

#### **5** Lead wire (Option)

Nil	With lead wire with M8 connector (3 m)
N	Without lead wire with M8 connector
Q	With M12-M8 conversion lead wire (0.1 m)*2

\*2 A cable (3 m) with an M12 connector is also available separately.

Click here for details.

#### 6 Unit specification

Symbol	Instantaneous flow	Accumulated flow	Temperature
Nil	gal/min	gal	°C
M	L/min	Ĺ	°C

- \* Under the New Measurement Act, units other than SI (symbol "M") cannot be used in Japan.
- \* Reference: 1 [L/min] = 0.2642 [gal/min] 1 [gal/min] = 3.785 [L/min]

### Bracket (Option)

<u> </u>		
Nil	None	
R	With bracket	

#### Calibration certificate (Only for flow rate)

, •	<b>,</b>
Nil	None
Α	Yes

\* The certificate is written in both Japanese and English. The integrated display type with temperature sensor can only display the flow rate. The temperature sensor is not calibrated.

#### **Specifications**

	Model	PF3W704	PF3W720	PF3W740	PF3W711	PF3W721	1
A 1.1.0 *1		9999999999 L		999999999 L			1
AC	cumulated flow range*1	By 0	).1 L		By 1 L		1
Ħ	Maximum applied voltage		30	V (NPN outp	ut)		]
output	Internal voltage drop		1.5 V or less	(at load curre	nt of 80 mA)		]
	Delay time*2			3.5 ms			
Switch	Delay tille -		Variable from	0 to 60 s/0.01	s increments		
Ĭ₹	Output Flow rate	Select from Hysteresis, Window comparator, Accumulated output,					
Ś	mode Flow rate	Accumulated pulse output, Error output, or Switch output OFF modes.					
ower supply voltage	When used as a switch output device	th 12 to 24 VDC, including ripple (p-p) 10%					
Power sup	When used as an IO-Link device	18 to 30 VDC, including ripple (p-p) 10%					
Digital filter*3		Select from 0.5 s, 1.0 s, 2.0 s, 5.0 s, 10.0 s, 15.0 s, 20.0 s, or 30.0 s.		s, or 30.0 s.	]		
Envir	onment Withstand voltage	250 VAC	for 1 minute l	oetween exter	nal terminals a	ınd case	
Standards and regulations CE marking (EMC directive/RoHS directive)		)					

- \*1 Cleared when the power supply is turned off The hold function can be selected. If the 5-minute interval is selected, the life of the memory element (electronic parts) is limited to 3.7 million times. (If energized for 24 hours, life is calculated as 5 minutes x access times (3.7 million) = 18.5 million minutes = about 35 years.) Therefore, if using the hold function, calculate the memory life for your operating conditions, and use within this life.
- \*2 Does not include the value of the digital filter
- \*3 The response time until the set value reaches 90% in relation to the step input (The response time is 7 s when it is output by the temperature sensor.)


#### Communication Specifications (IO-Link mode)


Sommanioadion opositioations (10 Link mode)			
IO-Link type	Device		
IO-Link version	V1.1		
Communication speed	COM2 (38.4 kbps)		
Configuration file	IODD file*1		
Minimum cycle time	3.5 ms		
Process data length	Input data: 6 bytes, Output data: 0 byte		
On request data communication	Yes		
Data storage function	Yes		
Event function	Yes		
Vendor ID	131 (0x0083)		
Device ID*2	PF3W704-□-LT□-M-X445: 330 (0x014A) PF3W720-□-LT□-M-X445: 310 (0x0136) PF3W740-□-LT□-M-X445: 317 (0x013D) PF3W711-□-LT□-M-X445: 331 (0x014B) PF3W721-□-LT□-M-X445: 332 (0x014C)		

- \*1 The configuration file can be downloaded from the SMC website, http://www.smcworld.com
- \*2 The device ID differs according to each product type (flow range, whether or not a temperature sensor is provided, etc.).

Other specifications and dimensions that are not indicated are the same as those of the standard product. For details, refer to page 6 and later.









# 3-Color Display

# **Digital Flow Switch for PVC Piping**

# PF3W Series ( E RU US



#### **How to Order**

For how to order of remote monitor unit. refer to page 24.

#### Remote sensor unit Output specification •

	•
Symbol	OUT1
1	Analog 1 to 5 V
2	Analog 4 to 20 mA

To use in combination with remote monitor (PF3W3 series), select analog output of 1 to 5 V of flow rate (output symbol "-1").

#### Remote sensor unit/Unit printed on label

Symbol	Instantaneous flow	
Nil	L/min	
G*1	L/min	
G*	(gal/min)	

- Under the New Measurement Act, units other than SI (symbol "Nil") cannot be used in Japan.
- G: Made to order

Reference: 1 [L/min] ← 0.2642 [gal/min] 1 [gal/min] ← 3.785 [L/min]

**Calibration certificate** (Only for flow rate)

` ,	
Nil	None
Α	With calibration certifica

The certificate is written in both Japanese

and English. The integrated display type with temperature sensor can only display the flow

# Remote sensor unit PF3W 5

Integrated display PF3W 7 11 - U 25 - A





Remote sensor unit Integrated display

#### Rated flow range (Flow range)

Symbol	Rated flow range
11	10 to 100 L/min
21	30 to 250 L/min

### Connection type

PVC pipe

#### 

Symbol Port		Rated flow range		Pipe
Symbol	size	11	21	O.D.*1
25	25A	•	_	32 mm
30	30A	_	•	38 mm

\*1 JIS K 6742 equivalent

### Integrated display

#### Output specification

Symbol	OUT1	OUT2	
Α	NPN	NPN	
В	PNP	PNP	
С	NPN	Analog 1 to 5 V	
D	NPN	Analog 4 to 20 mA	
E	PNP	Analog 1 to 5 V	
F	PNP	Analog 4 to 20 mA	
G	NPN	External input	
Н	PNP	External input	


External input: The accumulated value, peak value, and bottom value can be reset.

#### Made to order

X109 EPDM seal material

(Refer to page 23.)

#### Bracket (Option)



Bracket is not available for 250 L/min

#### Integrated display/Unit specification


Symbol	Instantaneous flow	Accumulated flow
M	L/min	L
G	gal/min	gal

- \* Under the New Measurement Act, units other than SI (symbol "M") cannot be used in Japan.
- \* G: Made to order

Reference: 1 [L/min] ↔ 0.2642 [gal/min]

1 [gal/min] ↔ 3.785 [L/min]

Lead wire (Option)



#### Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Description	Part no.	Qty.	Note
Bracket	ZS-40-M	1	For PF3W711/511 With 4 tapping screws (4 x 10)
Lead wire with M8 connector	ZS-40-A	1	Lead wire length: 3 m



# 3-Color Display Digital Flow Switch for PVC Piping **PF3W Series**

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

#### Specifications (Integrated Display)

M	odel	PF3W711	PF3W721	
Applicable fluid		Water and ethylene glycol aqueous solution	n (with viscosity of 3 mPa·s [3 cP] or less)*1	
Detection method		Karman vortex		
Rated flow range		10 to 100 L/min	30 to 250 L/min	
Dianley flow res		7 to 140 L/min	20 to 350 L/min	
Display flow rar	ige	(Flow under 7 L/min is displayed as "0")	(Flow under 20 L/min is displayed as "0")	
Set flow range		7 to 140 L/min	20 to 350 L/min	
Smallest settab	le increment	1 L/min	2 L/min	
	accumulated pulse	1 L/pulse	2 L/pulse	
Fluid temperatu	ıre	0 to 70°C (No freezi		
Display unit			L, Display values updated 5 times per second	
Accuracy		Display value: ±3% F.S.		
Repeatability		±2% l		
Temperature ch		±5% F.S. (25		
Operating press			MPa	
Proof pressure	<b>\$3</b>	1 N		
Pressure loss			the maximum flow	
Accumulated flo	ow range*4		9999 L	
	on rungo		1 L	
Switch output			n collector output	
	Max. load current	80 mA		
	Max. applied voltage	28 VDC		
	Internal voltage drop	NPN: 1 V or less (at load current of 80 mA) PNP: 1.5 V or less (at load current of 80 mA)  0.5 s/1 s/2 s		
	Response time*2, 5	Short-circuit protection		
	Output protection Output mode Flow rate			
	Response time*6	Select from Hysteresis, Window comparator, Accumulated output, or Accumulated pulse output modes.		
Analog output	Voltage output	0.5 s/1 s/2 s (linked with the switch output)		
Analog output	Current output	Voltage output: 1 to 5 V Output impedance: 1 kΩ  Output current: 4 to 20 mA Max. load impedance: 300 Ω for 12 VDC, 600 Ω for 24 VDC		
Hysteresis	Current output	Output current: 4 to 20 mA Max. load impedance: 300 Ω for 12 VDC, 600 Ω for 24 VDC  Variable		
External input		Variable  Variable  Voltage free input: 0.4 V or less (Reed or Solid state), input for 30 ms or longer		
Display method	i	2-screen display (Main screen: 4-digit, 7-segment, 2-color, Red/Green Sub screen: 6-digit, 11-segment, White)		
Indicator light		Output 1, Output 2: Orange		
Power supply v	oltage	12 to 24 VDC ±10%		
Current consun		50 mA	or less	
	Enclosure	IP	65	
	Operating temperature range	0 to 50°C (No freezing or condensation)		
Environment	Operating humidity range			
	Withstand voltage	1000 VAC for 1 minute betw	ween terminals and housing	
	Insulation resistance	50 M $\Omega$ or more (500 VDC measured via megohameter) between terminals and housing		
Standards and	regulations	CE marking (EMC directive/RoHS directive), UL (CSA)		
Wetted parts material*7		PPS, FKM, CPVC		
		Non-grease		
Piping port size	*8	25A	30A	
Weight	Without lead wire with connector	285 g	340 g	
weigni	With lead wire with connector	370 g	425 g	

- \*1 Refer to the graph of measurable range for ethylene glycol aqueous solution on page 10. Measurement is possible as long as the fluid does not corrode the wetted parts and viscosity is 3 mPa·s (3 cP) or less. Refer to the list of applicable fluids on page 31. Be aware that water leakage may occur due to internal seal shrinkage or swelling depending on the type of fluid.

- snrinkage or swelling depending on the type of fluid.

  2 If 0.5 s is selected for the response time of the switch output, the repeatability will be ±3% F.S.

  3 The operating pressure range and proof pressure may change according to the fluid temperature. Refer to the graph below.

  4 Cleared when the power supply is turned off. The hold function can be selected. (Intervals of 2 or 5 minutes can be selected.)

  If the 5-minute interval is selected, the life of the memory element (electronic parts) is limited to 1 million times. (If energized for 24 hours, life is calculated as 5 minutes x 1 million = 5 million minutes = about 9.5 years.) Therefore, if using the hold function, calculate the memory life for your operating conditions, and use within this life.

  5 The response time when the set value is 90% in relation to the step input.


- \*6 The response time until the set value is 90% in relation to the step input
  \*6 The response time until the set value reaches 90% in relation to the step input
  \*7 For details, refer to "Wetted Parts Construction" on page 20.
  \*8 When the piping diameter or piping passage is restricted, the specifications may not be satisfied.
  \* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

#### Analog Output

#### Flow rate/Analog output


			,		
	_	В		С	_
	A	11	21		١
Voltage output	1 V	1.4 V	1.5 V	5 V	
Current output	4 mA	5.6 mA	5.9 mA	20 mA	

Model	Rated flow [L/min]		
Model	Minimum	Maximum	
PF3W711/511	10	100	
PF3W721/521	30	250	



#### **Operating Pressure and Proof Pressure**

#### PF3W711/721/511/521 (for PVC Piping)





For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

#### Specifications (Remote Sensor Unit)

Refer to page 25 for monitor unit specifications.

Model		PF3W511	PF3W521	
Applicable fluid		Water and ethylene glycol aqueous solution (with viscosity of 3 mPa s [3 cP] or less)*1		
Detection method	od	Karman vortex		
Rated flow rang	je	10 to 100 L/min 30 to 250 L/min		
Fluid temperatu	ire	0 to 70°C (No freezi	ng or condensation)	
Accuracy		±3%	F.S.	
Repeatability		±2%	F.S.	
Temperature ch	aracteristics	±5% F.S. (25	°C standard)	
Operating press		0 to 1	MPa*2	
Proof pressure	*2	1 M	1Pa	
Pressure loss		45 kPa or less at t	the maximum flow	
	Response time*3	1		
Analog output	Voltage output	Voltage output: 1 to 5 V Output impedance: 1 kΩ		
	Current output	Output current: 4 to 20 mA Max. load impedance: 300 $\Omega$ for 12 VDC, 600 $\Omega$ for 24 VDC		
Indicator light		For power supply status, flow rate indicator (Blinking speed changes in response to flow rate.), and other error indicator		
Power supply voltage		12 to 24 VDC ±10%		
Current consumption		30 mA or less		
	Enclosure	IP65		
	Operating temperature range	0 to 50°C (No freezing or condensation)		
Environment	Operating humidity range	Operation, Storage: 35 to 8		
	Withstand voltage	1000 VAC for 1 minute between terminals and housing		
	Insulation resistance	50 M $\Omega$ or more (500 VDC measured via megohmmeter) between terminals and housing		
Standards and regulations		CE marking (EMC directive/RoHS directive), UL (CSA)		
Wetted parts material*4		PPS, FKM, CPVC		
		Non-grease		
Piping port size		25A	30A	
Weight	Without lead wire with connector	270 g	325 g	
weigni	With lead wire with connector	355 g	410 g	

<sup>\*1</sup> Refer to the graph of measurable range for ethylene glycol aqueous solution on page 10. Measurement is possible as long as the fluid does not corrode the wetted parts and viscosity is 3 mPa·s (3 cP) or less. Refer to the list of applicable fluids on page 31.

\*2 The operating pressure range and proof pressure may change according to the fluid temperature. Refer to the graphs below.

\*3 The response time until the set value reaches 90% in relation to the step input


\*4 For details, refer to "Wetted Parts Construction" on page 20.

\*5 When the piping diameter or piping passage is restricted, the specifications may not be satisfied.


\* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

#### Flow Rate Characteristics (Pressure Loss)


#### PF3W711/511




#### PF3W721/521




#### Straight Piping Length and Accuracy (Reference Value)



- Fluid pressure has almost no effect.
- To maintain ±3% F.S. in the specifications, use a straight pipe that is 11 cm or longer in length.



#### **Wetted Parts Construction**



**Component Parts** 

Odinponent i arts				
No.	Description	Material	Note	
1	PVC pipe	CPVC		
2	Seal	FKM		
3	Body	PPS		
4	Sensor	PPS		

**Replacement Parts** 

No.	Description	Part no.	Qty.
4	PVC pipe (25A)	ZS-40-U25	1
'	PVC pipe (30A)	ZS-40-U30	1
5	25A retaining plate (With two M5 x 80 hexagonal socket head cap screws)	ZS-40-U25-A	1
5	30A retaining plate (With two M5 x 65 hexagonal socket head cap screws)	ZS-40-U30-A	1

<sup>\*</sup> Replacing the PVC pipe may cause accuracy to fluctuate by 1 to 2%.

### **Internal Circuits and Wiring Examples**


Refer to page 11.

#### **Dimensions**

#### PF3W711-U25 Integrated display 154 57.6 77 23 $(\Phi)$ $\bigoplus$ П 0 30 2 28 0 2 x 25A 59 48 42 57 (35.5)Connector pin number Example Pin no. Pin name DC (+) 2 OUT2 OUT IN\_ 3 DC (-) 4 OUT1 EFF Tespeli 63 62.6 PF3W511-U25 $\oplus$ Remote sensor unit $\otimes$ $\oplus$ 0

#### **ZS-40-A** Lead wire with M8 connector

OUT1 Black



#### **Lead Wire Specifications**

-----i

OUT

Conductor	Nominal cross section	AWG23
	O.D.	Approx. 0.7 mm
	Material	Heat-resistant PVC
Insulator	O.D.	Approx. 1.1 mm
	Color	Brown, White, Black, Blue
Sheath	Material	Heat- and oil-resistant PVC
Finished	O.D.	ø4

\* 4-wire type lead wire with M8 connector used for the PF3W series


IN\_


\* For wiring, refer to the "Operation Manual" on the SMC website (http://www.smcworld.com).

4


#### **Dimensions**

# PF3W721-U30 Integrated display







# Body side Connector pin number





Pin no.	Pin name
1	DC (+)
2	OUT2
3	DC (-)
4	OUT1






#### PF3W521-U30 Remote sensor unit






# Body side Connector pin number



Pin name
DC (+)
Not used
DC (-)
OUT1



# **PF3W** Series Made to Order



Please contact SMC for detailed dimensions, specifications, and lead times.

<u></u>	Symbol
1 EPDM seal material	-X109
Seal material for wetted parts changed to EPDM	
PF3W5	

EPDM seal material

Refer to page 17 for details of How to Order.

PF3W7 - U -[

# 3-Color Display

# Digital Flow Monitor for Water



# PF3W3 Series



# **PF3W30**

3 Remote monitor unit


For remote sensor units, select the analog output 1 to 5 V type. Applicable sensors: PF3W5□□-□□-1(T)

#### Output specification •

Symbol	OUT1	OUT2
Α	NPN	NPN
В	PNP	PNP
С	NPN	Analog 1 to 5 V
D	NPN	Analog 4 to 20 mA
E	PNP	Analog 1 to 5 V
F	PNP	Analog 4 to 20 mA
G	NPN	External input
Н	PNP	External input
J	Analog 1 to 5 V	Analog 1 to 5 V
K	Analog 4 to 20 mA	Analog 4 to 20 mA

In combination with remote sensor unit with temperature sensor, only OUT2 can be set for temperature sensor output.

#### Lead wire ⊌



The lead wire does not come connected, but it is shipped together with the product.

#### Remote monitor unit/Unit specification

Symbol	Instantaneous flow	Accumulated flow	Temperature
M	L/min	L	°C
G	gal/min	gal	°C
F	gal/min	gal	°F
J	L/min	L	°F

- \* Under the New Measurement Act, units other than SI (symbol "M") cannot be used in Japan.
- G, F, J: Made to order

Reference: 1 [L/min] ← 0.2642 [gal/min]


1 [gal/min] ↔3.785 [L/min]
°F = 9/5°C + 32

### Calibration certificate (Only flow monitor)

Nil	None
Α	With calibration certificate


\* The certificate is written in both Japanese and English.

#### Option 2



The connector does not come connected, but it is shipped together with the product.

#### Option 1



### Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Description	Part no.	Note
Panel mount adapter	ZS-26-B	With waterproof seal and screws
Front protective cover + Panel mount adapter	ZS-26-C	With waterproof seal and screws
Front protective cover only	ZS-26-01	Separately order panel mount adapter, etc.
Power supply/output connection lead wire	ZS-40-W	Lead wire length: 2 m
Sensor connector (e-con)	ZS-28-CA-4	1 pc.
Lead wire with connector for copying	ZS-40-Y	Connect up to 10 slave units



For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

#### **Specifications**

	Model			PF3W30□				
Display flow ra	ange	0.35 to 4.50 L/min	1.7 to 18.0 L/min	3.5 to 45.0 L/min	7 to 112 L/min	20 to 280 L/min		
Display now is	ange	(Flow under 0.35 L/min is displayed as "0.00")	(Flow under 1.7 L/min is displayed as "0.0")	(Flow under 3.5 L/min is displayed as "0.0")	(Flow under 7 L/min is displayed as "0")	(Flow under 20 L/min is displayed as "0")		
Set flow range		0.35 to 4.50 L/min	1.7 to 18.0 L/min	3.5 to 45.0 L/min	7 to 112 L/min	20 to 280 L/min		
Smallest setta	ble increment	0.01 L/min		_/min	1 L/min	2 L/min		
Conversion of	accumulated pulse	0.05 L/pulse	0.1 L/pulse	0.5 L/pulse	1 L/pulse	2 L/pulse		
Display unit				us flow: L/min, Accumu				
Accuracy			Display value:	±0.5% F.S. Analog out	put: ±0.5% F.S.			
Repeatability				±0.5% F.S.				
Temperature of	haracteristics			).5% F.S. (25°C standar				
Accumulated 1	flow range*1	999999			99999999 L			
		By 0.1 L	By 0.5 L		By 1 L			
Switch output			NPN	or PNP open collector of	output			
	Max. load current			80 mA				
	Max. applied voltage			28 VDC				
	Internal voltage drop	NPN: 1 V	or less (at load current	of 80 mA) PNP: 1.5 V	or less (at load current	of 80 mA)		
	Response time*2	1 s/2 s						
	Output protection							
	Output Flow rate	Select from Hysteresis, Window comparator, Accumulated output, or Accumulated pulse output modes.						
	mode Temperature			elect from Hysteresis mode or Window comparator mode.				
	Response time*3	1 s/2 s (linked with the switch output)						
Analog output		Voltage output: 1 to 5 V Output impedance: 1 kΩ						
	Current output	Output current: 4 to 20 mA Max. load impedance: 300 $\Omega$ for 12 VDC, 600 $\Omega$ for 24 VDC						
Hysteresis		Variable						
External input		Voltage free input: 0.4 V or less (Reed or Solid state), input for 30 ms or longer						
Input/output		Input for copy mode						
Display metho		2-screen display (Main screen: 4-digit, 7-segment, 2-color, Red/Green Sub screen: 6-digit, 11-segment, White), Display values updated 5 times per second						
Indicator light		Output 1, Output 2: Orange						
Power supply		12 to 24 VDC ±10%						
Current consu	Imption	50 mA or less  Power supply output 5P connector, sensor connection 4P connector (e-con)						
Connection	F.,							
1	Enclosure			panel mount adapter a		otional parts are used.)		
	Operating temperature range			C (No freezing or conde				
Environment Operating humidity range				age: 35 to 85% R.H. (No				
	Withstand voltage Insulation resistance	1000 VAC for 1 minute between terminals and housing						
Standards and		50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing CE marking (EMC directive/RoHS directive), UL (CSA)						
	ver supply/output connection lead wire		CE marking (Er		uve), UL (USA)			
WAIGHT	ver supply/output connection lead wire r supply/output connection lead wire							
with power	suppry/output connection lead wire	<u> </u>		100 g				

- \*1 Cleared when the power supply is turned off. The hold function can be selected. (Intervals of 2 or 5 minutes can be selected.)


  If the 5-minute interval is selected, the life of the memory element (electronic parts) is limited to 1 million times. (If energized for 24 hours, life is calculated as 5 minutes x 1 million = 5 million minutes = about 9.5 years.) Therefore, if using the hold function, calculate the memory life for your operating conditions, and use within this life.
- \*2 The response time when the set value is 90% in relation to the step input (The response time is 7 s when it is output by the temperature sensor.)
- \*3 The response time until the set value reaches 90% in relation to the step input (The response time is 7 s when it is analog output by the temperature sensor.)
- \* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

#### **Temperature Sensor Specifications**

Rated temperature range	0 to 100°C*1
Set/Display temperature range	−10 to 110°C
Smallest settable increment	1°C
Display unit	°C
Analog output accuracy	±3% F.S.
Response time	7 s* <sup>2</sup>
Ambient temperature characteristics	±5% F.S.

\*1 The rated temperature range refers solely to that of the temperature sensor. The fluid temperature range specification of the flow switch as a whole is 0 to 90°C.

#### The output related to the temperature sensor is OUT2 only.




The OUT2 can be selected from either the output for temperature or flow rate by button operation.

#### **Analog Output**

#### Flow rate/Analog output

_					и			
			11			ľ		
Voltage output						l		
Current output	4 mA	6 mA	5.6 mA	5.9 mA	20 mA			
The values of B vary according to the range.								

	-				
Model	Flow rate [L/min]				
Model	Minimum	Maximum			
PF3W504	0.5	4			
PF3W520	2	16			
PF3W540	5	40			
PF3W511	10	100			
PF3W521	30	250			




#### Fluid temperature/Analog output

				, -							
/	Α	В	Output								
oltage output	0.6 V	1 V	D	<b>↓</b> -				_,			
urrent output	2.4 mA	4 mA	Č	<del> </del>			/	_	İ		
							/ I		I		
/	С	D				/	i		l		
oltage output	5 V	5.4 V			/		!		l		
urrent output	20 mA	21.6 mA		١,			- 1		l I		
ith remo		mbination unit with	A f	<b>/</b>			i I I		       		
			−10°C	0°C			100°C	1		Fluid temperat	ure


<sup>\*2</sup> The response time refers solely to that of the temperature sensor.

#### **Internal Circuits and Wiring Examples**

#### -A NPN (2 outputs)




#### -B PNP (2 outputs)




#### -C/D

C: NPN + Analog voltage output D: NPN + Analog current output




#### -E/F


E: PNP + Analog voltage output F: PNP + Analog current output



#### -G NPN + External input




#### -H PNP + External input



#### -J/K

J: Analog voltage output K: Analog current output





#### Accumulated pulse output wiring examples

#### -A/C/D/G


A: NPN (2 outputs)

C, D: NPN + Analog output







-B/E/F/H B: PNP (2 outputs) E, F: PNP + Analog output G: PNP + External input







#### **Dimensions**








#### Front protective cover + Panel mount adapter



#### **Panel fitting dimensions**

Applicable panel thickness: 0.5 to 8 mm (Without waterproof seal) 0.5 to 6 mm (With waterproof seal)



#### Sensor connector Pin no. Terminal Connector no. Lead wire color\*1 DC (+) Brown (2) N.C./IN White (Not used/Temperature sensor 1 to 5 V input) DC (-) 3 Blue INPUT Black (Flow rate sensor 1 to 5 V input) 4 When using the lead wire with M8 connector included with the PF3W5 series Power supply/output connection lead wire **Lead Wire Specifications** Nominal cross section AWG26 Conductor O.D. Approx. 0.5 mm 5 Gray COPY Material Cross-linked vinyl 4 White OUT2 Insulator O.D. Approx. 1.0 mm 3 Black OUT1 2 Blue DC (-) Color Brown, Blue, Black, White, Gray Sheath Material Oil- and heat-resistant vinyl 1 Brown DC (+) 2000 Finished O.D. ø3.5



# **Function Details**

#### Integrated Display (PF3W7 series)/Remote Monitor Unit (PF3W3 series)

#### Output operation

The output operation can be selected from the following:

Output (hysteresis mode and window comparator mode) corresponding to instantaneous flow rate, output corresponding to accumulated flow, or accumulated pulse output.

At the time of shipment from the factory, it is set to hysteresis mode and normal output.

When a temperature sensor is attached, the output to the temperature sensor is selectable only for OUT2. (Refer to "How to Order" for details.)

#### ■ Display color

The display color can be selected for each output condition. The selection of the display color provides visual identification of abnormal values. (The display color depends on OUT1 setting.)

Green for ON, Red for OFF
Red for ON, Green for OFF
Red all the time
Green all the time

#### ■ Response time

The response time can be selected to suit the application. (1 second for default setting)

Abnormalities can be detected more quickly by setting the response time to 0.5 seconds.

The effect of the pump fluctuation and flickering of the display can be reduced by setting the response time to 2 seconds.

\* The temperature sensor output is fixed to 7 seconds.

Deenenee	Applicable model			
Response time	Integrated display PF3W7 series	Remote monitor unit PF3W3 series		
0.5 seconds	•	_		
1 second	•	•		
2 seconds	•	•		

#### ■ External input function -

This function can be used only when the optional external input is present. The accumulated flow, peak value, and bottom value can be reset remotely.

Accumulated value external reset: A function to reset the accumulated flow value when an external input signal is applied.

In accumulated increment mode, the accumulated value will reset to and increase from zero.

In accumulated decrement mode, the accumulated value will reset to and decrease from the set value.

When the accumulated value is stored to memory, every time the accumulated value external reset is activated, the memory (EE-PROM) will be accessed. Take into consideration that the maximum number of times the memory can be accessed is 1 million times. The total number of external inputs and the accumulated value memorizing time interval should not exceed 1 million times.

Peak/Bottom value reset: Peak and bottom value are reset.

#### ■ Forced output function

The output is turned on/off in a fixed state when starting the system or during maintenance. This enables the confirmation of wiring and prevents system errors due to unexpected output.

For the analog output type, when ON the output will be 5 V or 20 mA, and when OFF, it will be 1 V or 4 mA.

Also, an increase or decrease of the flow and temperature will not change the on/off status of the output while the forced output function is activated.

#### ■ Accumulated value hold

The accumulated value is not cleared even when the power supply is turned off.

The accumulated value is memorized every 2 or 5 minutes during measurement and continues from the last memorized value when the power supply is turned on again.

The life time of the memory device is 1 million access times. Take this into consideration before using this function.

#### ■ Selection of display on sub screen

The display on the sub screen in measuring mode can be set.



Integrated display

Remote monitor unit

Set value display	Accumulated value display	Peak value display	Bottom value display
Displays the set value (The set value	Displays the accumulated value (The	Displays the peak value	Displays the bottom value
of OUT2 cannot be displayed.)	accumulated value of OUT2 cannot be		
GSAC FLOW SYITCH	displayed.)	GSMC FLOW SWITCH  HISH FOR WATER	GSAC FLOW SWITCH
Line name display	Fluid temperature display	OFF	
Displays the line name (Up to 6	Displays the fluid temperature	Displays nothing	
alphanumeric characters can be input.)	(When the temperature sensor type is		
	selected.)		
GONC FLOW SWITCH  SMILE PER  FOR WATER	FORWARES FLOW SWITCH S	GONC FLOW SWITCH  FROM NATURE	

\* The above are examples of integrated displays. (Same as remote monitor unit)

#### ■ Power-saving mode

The display can be turned off to reduce power consumption. In power-saving mode, only decimal points blink.

If any button is pressed during power-saving mode, the display is recovered for 30 seconds to check the flow, etc.

#### ■ Setting of security code

The user can select whether a security code must be entered to release the key lock. At the time of shipment from the factory, it is set such that a security code is not required.

#### ■ Peak/Bottom value display

The maximum (minimum) flow rate is detected and updated from when the power supply is turned on. In peak (bottom) value display mode, this maximum (minimum) flow rate is displayed.

#### ■ Keylock function


Prevents operation errors such as accidentally changing setting values



### Integrated Display (PF3W7 series)/Remote Monitor Unit (PF3W3 series)

#### ■ Analog output free range function

This function allows a flow that generates an output of 5 V or 20 mA to be changed. (This function is not available for the analog output to the temperature.) This function is available if the analog output type is used. The value can be changed between 10% of the maximum value of the rated flow and the maximum value of the display range.




#### ■ Copy function (Remote monitor unit/PF3W3 series)

The settings of the master monitor (source of copy) can be copied to the slave monitors, reducing setting labor and minimizing the risk of setting mistakes.

The set value can be copied to up to 10 flow monitors simultaneously.

(Maximum transmission distance: 4 m)



#### **■** Error display function

When an error or abnormality arises, the location and contents are displayed.

				Applicab	le model
Display	Description	Contents	Action	Integrated display PF3W7 series	Remote monitor unit PF3W3 series
Er 1	OUT1 over current error	A load current of 80 mA or more is applied to the switch output (OUT1).	Eliminate the cause of the over current by turning off the power supply and	•	•
Er2	OUT2 over current error	A load current of 80 mA or more is applied to the switch output (OUT2).	then turning it on again.	•	•
ннн	Instantaneous flow error	The flow rate has exceeded the display flow range (rated flow x approx. 1.4).	Decrease the flow rate.	•	•
LLL	Unconnected sensor error	Remote sensor unit is not connected to the monitor unit. Or, sensor output is less than 0.6 V.	Connect the sensor or check the sensor output voltage.	_	•
(Alternately displays) [999] and [999999])	Accumulated flow error	The flow rate exceeds the accumulated flow rate range. (Decimal points start blinking due to the flow range.)	Clear the accumulated flow rate. (This error is irrelevant when accumulated flow is not being used.)	•	•
cHHH	Over upper limit of temperature	Fluid temperature exceeds 110°C.	Lower the fluid temperature.	•	•
	Under lower limit of temperature	Fluid temperature is under -10°C.	Raise the fluid temperature.	•	•
	Unconnected temperature sensor error	Temperature sensor output wire is not connected.	Connect the temperature output wire.		
cLLL		Temperature sensor is not connected to the remote sensor unit.	Check if or not the remote sensor unit is connected to a temperature sensor.		•
	Temperature sensor failure	If the above actions to correct the lower limit of fluid temperature and unconnected sensor are taken and error message still appears, the temperature sensor of the remote sensor unit may be damaged.	Please contact SMC for investigation.	_	•
ErO					
Er4	System error	Internal data error	Turn the power off and then on again.		
Er5	Cystolli elloi	micrial data enoi	If the error cannot be rectified, please		
Er8			contact SMC for investigation.		
Er12	Temperature sensor failure	Temperature sensor may be damaged.		•	_

If the error cannot be solved after the instructions above are performed, please contact SMC for investigation.



# Function Details **PF3W** Series


### Remote Sensor Unit (PF3W5 series)

#### **■POWER** indicator function

It is possible to check whether power supply is reaching the product. When power is supplied to the product, the indicator lights up green.

#### **■FLOW** indicator function

Status of the flow rate can be checked visually. When the flow rate increases, the green lamp blinks faster. When below the measurable lower limit of flow rate, the lamp turns off, when above the measurable upper limit of flow rate, red lamp turns on.



#### ■Error display function

When an error or abnormality arises, the location and contents are displayed.

LED display	Description	Contents	Action
POWER Green Red FLOW FLOW indicator: Red ON	Over upper limit of flow rate	Flow is approximately 110% or more of the rated flow.	Decrease the flow rate.
POWER indicator: Blinking red	Temperature measurement range error	Fluid temperature is either under –10°C or over 110°C.	Adjust the fluid temperature within the measurable temperature range.
POWER Red FLOW  POWER indicator: Blinking red FLOW indicator: Red ON	Over upper limit of flow rate and temperature measurement range error	Refer to above.	Refer to above.

LED display	Description	Contents	Action
POWER Red Red FLOW  POWER indicator: Red ON FLOW indicator: Red ON  POWER Red Red FLOW  POWER indicator: Red ON FLOW indicator: Blinking red	System error	Internal data error or other errors occur.	Turn the power off and then on again. If the error cannot be rectified, please contact SMC for investigation.
POWER Red FLOW  POWER indicator: Red ON FLOW indicator: OFF		Temperature sensor may be damaged.	

If the error cannot be solved after the above instructions are performed, please contact SMC for investigation.

### Material and Fluid Compatibility Check List (Guide)


Chemical		Compatibility
Ammonium hydroxide		×
Isobutyl alcohol		×*3
Isopropyl alcohol		<b>○</b> *1, 2
Hydrochloric acid	Concentration 30% or less	O*2
Hydrogen peroxide	Concentration 5% or less	0
Nitric acid (except fuming nitric acid)	Concentration 10% or less	O*2
Deionized water		0
Sodium hydroxide (caustic soda)	Concentration 50% or less	×*3
Sulfuric acid (except fuming sulfuric acid)	Concentration 30% or less	0
Phosphoric acid	Concentration 50% or less	0

The material and fluid compatibility check list provides reference values as a guide only, therefore we do not guarantee the application to our product.

- \*1 Since static electricity may be generated, implement suitable countermeasures.
- \*2 Fluid may pass through. Fluid that has passed through may have an impact on components made
- \*3 Karman vortex measurement cannot be carried out due to high viscosity.
- SMC is not responsible for its accuracy and any damage happened because of this data.

Table symbols

- : Can be used : Can be used under certain conditions
- x: Cannot be used





# **⚠** Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)\*1), and other safety regulations.

Caution: Caution indicates a hazard with a low level of risk which, If not avoided, could result in minor or moderate injury.

-----

Warning: Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

⚠ Danger: Danger if not avoided, will result in death or serious injury. **Danger** indicates a hazard with a high level of risk which, \*1) ISO 4414: Pneumatic fluid power - General rules relating to systems.

ISO 4413: Hydraulic fluid power – General rules relating to systems.

IEC 60204-1: Safety of machinery - Electrical equipment of machines. (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots - Safety.

#### **⚠Warning**

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.

- 1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
- 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
- 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

4. Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.

- 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
- 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalog.
- 3. An application which could have negative effects on people, property, or animals requiring special safety analysis.
- 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

#### **⚠** Caution

1. The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing industries.

If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary. If anything is unclear, contact your nearest sales branch.

#### Limited warranty and Disclaimer/ **Compliance Requirements**

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

#### **Limited warranty and Disclaimer**

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.\*2)
  - Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.
  - 2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered.

Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

#### Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

#### **⚠** Caution

#### SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

#### **Revision History**

- Edition B \* The remote type has been added.
  - \* Units with a flow adjustment valve have been added
  - \* The 100 L/min type has been added.
  - \* The PVC piping type has been added. \* Number of pages has been increased from 16 to 32.

- Edition C \* The 250 L/min type has been added.
  - \* The analog 4 to 20 mA 2-output type (-X128) has been added to made to order options. \* The brass piping material specification (-X143) has been added to made to order options
  - \* Number of pages has been decreased from 32 to 28.

QW

- Edition D \* The PF3W7□-X445 has been added. \* Number of pages has been increased from 28 to 36.

↑ Safety Instructions Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.