ISO Cylinder ISO Standard (15552) CP96 Series ø32, ø40, ø50, ø63, ø80, ø100, ø125 RoHS New Lightweight @15% C85 An adjustable position trunnion has been added. C85-S/T C85W Weight reduced Compared with the previous CP96 series (ø40, 100 mm str By adopting a new cushion method (Air cushion + Bumper cushion), Cycle time shortened (Applicable cylinder: ø32 to ø100) Cushion stroke time Air cushion Air cushion Previous Shortened cushion Air cushion **Bumper cushion** New **Bumper cushion** Bumper cushion reduces the metal noise that occurs when piston stops (Applicable cylinder: ø32 to ø100)



Weight reduced

Achieved weight reduction by changing rod cover shape

Bore size [mm]	CP96 [kg]	Reduction rate [%]
32	0.74	11
40	1.02	15
50	1.74	11
63	2.12	12
80	3.40	11
100	4.33	11

* Compared with the previous CP96 series (100 mm stroke)



Auto switch mounting surface

CNOMO grooves

Groove for the D-M9□, A9□ type

Mount a switch from the head end for attaching to the CNOMO

groove on the port surfaces.



- The cushion stroke time can now be reduced with the double cushioning, which improves the cycle time.
- The bumper cushion reduces the metal noise that occurs when the piston stops at the end of the stroke.



Auto switch mounting

- Switch can be slid in for mounting.
- Groove for M9, A9 switches and CNOMO groove are on all four sides. Max. four sides, slide-in mountable

Auto switch can be slid in.

Mountable from both the head end and the rod end.





Various mounting bracket options Mounting brackets can be combined according to the operating conditions. Rod end (KJ) C85 Rod clevis (GKM) 3 .3 Adjustable position trunnion (V) C85W Floating joint (JA) C85-S/T **C85K** Double clevis (D) **CP96** Series C85K-S/T **C85R** Single clevis (C) C75 Clevis pivot bracket (E) Rod flange (F) C75W **Double clevis** pivot bracket (DS) C75-S/T Single clevis (C) Axial foot (L) C75K C75K-S/T Clevis pivot bracket with ball joint (ES) **C75R** Single clevis Single clevis with ball joint (CS) CP96 with ball joint (CS) CP96K Head flange (G) **C**96 Axial foot (L) C96K **Series Variations** C96Y Bore size [mm] ISO Standards Page Туре C55 Standard Double acting, CP96 Series Single rod 129 Double acting,



Double rod

Double acting,

Single rod

Double acting, Double rod

ISO 15552

Non-rotating rod

CP96K Series

a

141



Applicable Auto Switches/Refer to the Web Catalog or Best Pneumatics for further information on auto switches.

		Electrical	tor t	Wiring		Load vo	ltage	Auto switch	Lea	d wire	length	[m]	Pre-wired	Ann	licable
Туре	Special function	entry	Indicator light	(Output)		DC	AC	model	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	connector		bad
ج ج				3-wire (NPN)		5 V, 12 V		M9N			•	0	0	IC	
switch	—	Grommet		3-wire (PNP)]	5 V, 12 V		M9P				0	0	circuit	
				2-wire		12 V		M9B			۲	0	0	—	
auto	Diagnostic			3-wire (NPN)		5 V, 12 V		M9NW				0	0	IC	Delaw
a a	indication		Yes	3-wire (PNP)	24 V	5 V, 12 V		M9PW			۲	0	0	circuit	Relay, PLC
state	(2-color indicator)	Grommet		2-wire		12 V] [M9BW	۲		•	0	0	-	FLO
at a	Motor registerst	Giommer		3-wire (NPN)]	5 V, 12 V		M9NA *1	0	0		0	0	IC	
Solid	Water-resistant (2-color indicator)			3-wire (PNP)		5 V, 12 V] [M9PA *1	0	0	•	0	0	circuit	
Ň				2-wire		12 V		M9BA*1	0	0		0	0	—	
Reed auto switch			Yes	3-wire (NPN equivalent)	_	5 V	—	A96	•	—	•	_	_	IC circuit	—
vito	– vitcla	Grommet					100 V	A93					_	—	Delev
Ree sv			No	2-wire 24 V		12 V	100 V or less	A90	•	_	•	_	_	IC circuit	Relay, PLC

*1 Water-resistant type auto switches can be mounted on the above models, but SMC cannot guarantee water resistance.

* Lead wire length symbols: 0.5 m Nil (Example) M9NW

1 m ······· M (Example) M9NWM 3 m ······ L (Example) M9NWL

- 5 m ······· Z (Example) M9NWZ

* Since there are other applicable auto switches than listed above, refer to page 146 for details.

The D-A9 \square /M9 \square /M9 \square W/M9 \square A auto switches are shipped together, but not assembled. *

The D-Y59A, Y69A, Y7P, Y7DW, Z7D, Z80 cannot be mounted on the CP96 series.

Moreover, the D-M9 and A9 auto switches cannot be mounted on square groove of the CP96 series.



* Solid state auto switches marked with "O" are produced upon receipt of order.

ISO Standard (15552) Air Cylinder: Standard Type Double Acting, Single/Double Rod **CP96 Series**

Specifications

Bore siz	ze [mm]	32	40	50	63	80	100	125				
Action				C	ouble actin	g						
Fluid					Air							
Proof pre	essure				1.5 MPa							
Max. operat	ing pressure		1.0 MPa									
Min. operati	ng pressure		0.05 MPa									
Ambient temperat	and fluid ures				ch: –20 to 7 ch: –10 to 6	``	0,					
Lubricati	on			Not re	quired (Nor	n-lube)						
Operating p	iston speed		50 to 1000 mm/s 50 to									
	Up to 500	+2 0										
Allowable	501 to 1000			+2				+1.4				
tolerance	1001 to 1500			+2				+1.8				
	1501 to 2000			+3				+2.2				
Cushion			Air cushior	n on both er	nds + Bump	per cushion		Air cushion				
Port size		G 1/8	G 1/4	G 1/4	G 3/8	G 3/8	G 1/2	G 1/2				
Mounting	9				flange, Hea unnion, Adj	•	•					

Standard Strokes

Bore size [mm]	Standard stroke [mm]	Max. stroke
32	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500	2000
40	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500	2000
50	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600	2000
63	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600	2000
80	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600, 700, 800	2000
100	25, 50, 80, 100, 125, 160, 200, 250, 320, 400, 500, 600, 700, 800	2000
125	_	2000

Aside from the standard strokes, intermediate strokes are also available in 1 mm increments and are produced upon receipt of order.

* Strokes exceeding the max. stroke are available as a special order.

Accessories

Ν	Nounting	Basic	Foot	Rod flange	Head flange	Single clevis	Double clevis	Adjustable position trunnion
Standard	Rod end nut					•		
Standard	Clevis pin	-	_	_	—	_		—
	Rod end							
Option	Rod clevis							
	Rod boot							

* Do not use a rod end (or floating joint) together with a single clevis with a ball joint (or clevis pivot bracket with a ball joint).

* Refer to pages 137 to 140 for dimensions and part numbers of the accessories.

A Precautions

Be sure to read this before handling the products. Refer to page 219 for I safety instructions. For actuator and auto switch precautions, refer to I I the "Handling Precautions for SMC Products" and the "Operation I Manual" on the SMC website: http://www.smcworld.com





Made to Made to Order Order (For details, refer to pages 148 to 155.)

Symbol	Specifications
-XA🗆	Change of rod end shape
-XB6	Heat-resistant cylinder (-10 to 150°C)
-XC4	With heavy duty scraper
-XC7	Tie-rod, tie-rod nut, etc. made of stainless steel
-XC10	Dual stroke cylinder/Double rod type
-XC11	Dual stroke cylinder/Single rod type
-XC22	Fluororubber seal
-XC35	With coil scraper
-XC65	Made of stainless steel (Combination of -XC7 and -XC68)
-XC68	Made of stainless steel (with hard chrome plated piston rod)
-XC85	Grease for food processing equipment
-XC88	Spatter-resistant coil scraper, Lube-retainer, grease for welding (Piston rod: Stainless steel 304)
-XC89	Spatter-resistant coil scraper, Lube-retainer, grease for welding (Piston rod: S45C)

Refer to pages 145 and 146 for cylinders with auto switches.

- · Auto Switch Proper Mounting Position (Detection at stroke end)
- · Minimum Stroke for Auto Switch Mounting · Operating Range
- · How to Mount and Move the Auto Switch

Made to Order

Related Products

CP96 Series

Theoretical Output

Bore size	Rod size	Operating	Piston			0	peratin	g pres	sure [N	IPa]		
[mm]	[mm]	direction	area [mm²]	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
32	12	OUT	804	161	241	322	402	482	563	643	724	804
32	12	IN	691	138	207	276	346	415	484	553	622	691
40	16	OUT	1257	251	377	503	629	754	880	1006	1131	1257
40	10	IN	1056	211	317	422	528	634	739	845	950	1056
50	20	OUT	1963	393	589	785	982	1178	1374	1570	1767	1963
50	20	IN	1649	330	495	660	825	989	1154	1319	1484	1649
63	20	OUT	3117	623	935	1247	1559	1870	2182	2494	2805	3117
03	20	IN	2803	561	841	1121	1402	1682	1962	2242	2523	2803
80	25	OUT	5027	1005	1508	2011	2514	3016	3519	4022	4524	5027
00	25	IN	4536	907	1361	1814	2268	2722	3175	3629	4082	4536
100	25	OUT	7854	1571	2356	3142	3927	4712	5498	6283	7068	7854
100	20	IN	7363	1473	2209	2945	3682	4418	5154	5890	6627	7363
125	32	OUT	12272	2454	3682	4909	6136	7363	8590	9817	11045	12272
125	52	IN	11468	2294	3440	4587	5734	6881	8027	9174	10321	11468

► OUT

-

IN

[N]

* Theoretical output [N] = Pressure [MPa] x Piston area [mm²]

Weight (Guide)

								[kg]
Bo	ore size [mm]	32	40	50	63	80	100	125
	Basic	0.46	0.66	1.14	1.48	2.42	3.25	6.82
Basic weight	Foot	0.62	0.86	1.52	1.94	3.31	4.34	9.42
	Flange	0.66	0.89	1.61	2.06	3.72	5.06	10.92
	Single clevis	0.62	0.89	1.51	2.08	3.49	4.98	10.97
	Double clevis	0.66	0.98	1.59	2.19	3.70	5.36	11.07
	Adjustable position trunnion	0.60	0.95	1.47	2.16	3.22	4.80	8.75
Additional weight per 50 mm of stroke	All mounting brackets	0.14	0.18	0.30	0.32	0.49	0.54	0.84
Accessories	Rod end	0.07	0.11	0.:	22	0.	40	1.20
Accessories	Rod clevis	0.09	0.15	0.	34	0.	69	1.84

Calculation: Example) CP96SD40-100C

Additional weight0.18 (kg/50 st)
 Cylinder stroke100 [st]

0.98 + 0.18 x 100 ÷ 50 = **1.34 [kg]**

Allowable Kinetic Energy



(Example) Find the upper limit of rod end load when an air cylinder of ø63 is operated at 500 mm/s. From a point indicating 500 mm/s on the axis of abscissas, extend a line upward and find a point where it intersects with a line for the 63 mm bore size. Extend a line from the intersection to the left and find a load mass 80 kg.

ISO Standard (15552) Air Cylinder: Standard Type Double Acting, Single/Double Rod **CP96** Series

Construction



SMC

Component Parts

No.	Description	Material	Note
1	Rod cover	Aluminum die-cast	
2	Head cover	Aluminum die-cast	
3	Cylinder tube	Aluminum alloy	
4	Piston rod	Carbon steel	
-	Distan	Aluminum alloy	ø32 to ø63, ø125
5	Piston	Aluminum die-cast	ø80, ø100
6	Cushion ring A	Aluminum alloy	
7	Cushion ring B	Aluminum alloy	
8	Cushion seal holder	Aluminum alloy	ø32 to ø100
9	Tie-rod	Carbon steel	
10	Tie-rod nut	Steel	
11	Flat washer	Steel	ø80, ø100
12	Rod end nut	Steel	
13	Cushion valve	Resin	ø32 to ø100
13	Cusilion valve	Steel wire	ø125
14	Bushing	Bearing alloy	
15	Cushion seal	Urethane	
16	Bumper	Urethane	ø32 to ø100
17	Wear ring	Resin	
18	Piston seal	NBR	
19	Rod seal	NBR	
20	Cylinder tube gasket	NBR	
21	Cushion valve seal	NBR	
22	Magnet		
23	Retaining ring	Steel for spring	ø125
24	Rod seal holder	Stainless steel	ø125
25	Retaining ring	Steel for spring	ø125

Replacement Parts/Seal Kit (Single rod)

Bore size [mm]	Kit no.	Contents
32	CS95-32	
40	CS95-40	
50	CS95-50	
63	CS95-63	Kits include items
80	CS95-80	(3, 1) 10 (3.
100	CS96-100	
125	CS96-125	

* Seal kits consist of items (5, (7) to (20) and can be ordered by using the seal kit number corresponding to each bore size.

 The seal kit includes a grease pack (10 g for ø32 to ø50, 20 g for ø63 and ø80, 30 g for ø100 and ø125).
 Order with the following part number when only the grease pack is needed.

Grease pack part number: GR-S-010 (10 g), GR-S-020 (20 g)

Seal Kit (Double rod)

Bore size [mm]	Kit no.	Contents
32	CS95W-32	
40	CS95W-40	
50	CS95W-50	
63	CS95W-63	Kits include items
80	CS95W-80	
100	CS96W-100	
125	CS96W-125]

* Seal kits consist of items (), () to 2) and can be ordered by using the seal kit number corresponding to each bore size.

 The seal kit includes a grease pack (10 g for ø32 to ø50, 20 g for ø63 and ø80, 30 g for ø100 and ø125).

Order with the following part number when only the grease pack is needed. Grease pack part number: GR-S-010 (10 g), GR-S-020 (20 g)

Made to Order

Related Products

CP96 Series

Dimensions

Basic: CP96S (D) B Bore size - Stroke C (J)





Bore size [mm]		m] With rod	A	ø₿ d11	BG	øD	E	EE	G	н	кк	L2	L8	L9	L12	PL	R	RT	SL	sw	VA	VD	WA	WB	wн	zz
32	Up to 2000	Up to 1000	22	30	16	12	47	G 1/8	28.9	48	M10 x 1.25	15	94	4	6	13	32.5	M6 x 1	8	10	4	4	4	7	26	146
40	Up to 2000	Up to 1000	24	35	16	16	54	G 1/4	32.6	54	M12 x 1.25	17	105	4	6.5	14	38	M6 x 1	8	13	4	4	5	8.9	30	163
50	Up to 2000	Up to 1000	32	40	16	20	66	G 1/4	32	69	M16 x 1.5	24	106	5	8	14	46.5	M8 x 1.25	-	17	4	4	6	5.1	37	179
63	Up to 2000	Up to 1000	32	45	16	20	77	G 3/8	38.6	69	M16 x 1.5	24	121	5	8	16	56.5	M8 x 1.25	—	17	4	4	9	6.3	37	194
80	Up to 2000	Up to 1000	40	45	17	25	99	G 3/8	38.4	86	M20 x 1.5	30	128	—	10	16	72	M10 x 1.5	—	22	4	4	11.5	6	46	218
100	Up to 2000	Up to 1000	40	55	17	25	118	G 1/2	42.9	91	M20 x 1.5	32	138	—	10	18	89	M10 x 1.5	—	22	4	4	17	10	51	233
125	Up to 2000	Up to 1000	54	60	20	32	144	G 1/2	58	119	M27 x 2	40	160	—	13	19	110	M12 x 1.75	—	27	6	6	17	15	65	285
*1 Minim	*1 Minimum stroke for trunnion mounting: 1 mm for bore size 32 to 80, 5 mm for bore size 100, 10 mm for bore size 125																									

Bore									é	!											ł	า					
size [mm]	ø d	ø e	f	1 to 50	51 to 100	101 to 150	151 to 200	201 to 300	301 to 400	401 to 500	501 to 600	601 to 700	701 to 800	801 to 900	901 to 1000	1 to 50	51 to 100	101 to 150	151 to 200	201 to 300	301 to 400	401 to 500	501 to 600	601 to 700	701 to 800	801 to 900	901 to 1000
32	54	36	23	12.5	25	37.5	50	75	100	125	150	175	200	225	250	75	88	100	113	138	163	188	213	238	263	288	313
40	54	36	23	12.5	25	37.5	50	75	100	125	150	175	200	225	250	75	88	100	113	138	163	188	213	238	263	288	313
50	64	51	25	12.5	25	37.5	50	75	100	125	150	175	200	225	250	87	100	112	125	150	175	200	225	250	275	300	325
63	64	51	25	12.5	25	37.5	50	75	100	125	150	175	200	225	250	87	100	112	125	150	175	200	225	250	275	300	325
80	68	56	30	12.5	25	37.5	50	75	100	125	150	175	200	225	250	103	116	128	141	166	191	216	241	266	291	316	341
100	76	56	32	12.5	25	37.5	50	75	100	125	150	175	200	225	250	103	116	128	141	166	191	216	241	266	291	316	341
125	82	75	40	10	20	30	40	60	80	100	120	140	160	180	200	130	140	150	160	180	200	220	240	260	280	300	320

SMC

Dimensions

Basic: CP96S (D) B Bore size - Stroke C (J) W



With rod boot at one end



																											1 2
Bore size [mm]		range*1 nm]	A	øB d11	BG	øD	Е	EE	G	н	ł	KK	L2	L8	L9	L12	PL	R	RT	SL	sw	VD	WA	WB	wн	ΖY	CP96K
32	Up to	o 1000	22	30	16	12	47	G 1/8	28.9	48	M10	x 1.25	5 15	94	4	6	13	32.5	M6 x 1	8	10	4	4	7	26	190	ဖြ
40	Up to	o 1000	24	35	16	16	54	G 1/4	32.6	54	M12	x 1.25	5 17	105	4	6.5	5 14	38	M6 x 1	8	13	4	5	8.9	30	213	960
50	Up to	o 1000	32	40	16	20	66	G 1/4	32	69	M16	6 x 1.5	24	106	5	8	14	46.5	M8 x 1.2	5 —	17	4	6	5.1	37	244	$\overline{}$
63	Up to	o 1000	32	45	16	20	77	G 3/8	38.6	69	M16	6 x 1.5	24	121	5	8	16	56.5	M8 x 1.2	5 —	17	4	9	6.3	37	259	96K
80	Up to	o 1000	40	45	17	25	99	G 3/8	38.4	86	M20) x 1.5	30	128	-	10	16	72	M10 x 1.	5 —	22	4	11.5	6	46	300	Ľΰ
100	Up to	o 1000	40	55	17	25	118	G 1/2	42.9	91	M20) x 1.5	32	138	-	10	18	89	M10 x 1.	5 —	22	4	17	10	51	320	
125	Up to	o 1000	54	60	20	32	144	G 1/2	58	119	M2	27 x 2	40	160	-	13	19	110	M12 x 1.7	5 —	27	6	17	15	65	398	С96У
*1 Minim	um s	strok	e for	r trunr	nion n	nount	ing: 1	mm fo	or bore	e size	32 to	80, 5	mm	for bo	re siz	e 100), 10 n	nm for	ore size	125							$\underline{\square}$
							-		1												ı						C55
Bore				1	51	101	151	201	301	401	501	601	701	801	901	1	51	101 1	51 201	301	401	501	601	701	801	901	ΰ
size [mm]	ød	øe	T	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to to	to	to	to	to	to	to	to	\square
				50	100	150	200	l							1000	50	100		200 300	400	500	600	-	800	900	1000	
32	54		_	12.5		37.5		75		125		-	200		250	75	88		13 138	163	188	213	_	263	288	313	Auto Switch
40	54		-	12.5		37.5		75	100	125			200		250	75	88	100 1	13 138	163	188	-		263	288	313	Na Au
50	64	51	25	12.5	25	37.5	50	75	100	125	150	175	200	225	250	87	100	112 1	25 150	175	200	225	250	275	300	325	
63	64	51	25	12.5	25	37.5	50	75	100	125	150	175	200	225	250	87	100	112 1	25 150	175	200	225	250	275	300	325	e to
80	68	56	30	12.5	25	37.5	50	75	100	125	150	175	200	225	250	103	116	128 1	41 166	191	216	241	266	291	316	341	Made to Order
100	76	56	32	12.5	25	37.5	50	75	100	125	150	175	200	225	250	103	116	128 1	41 166	191	216	241	266	291	316	341	
125	82	75	40	10	20	30	40	60	80	100	120	140	160	180	200	130	140	150 1	60 180	200	220	240	260	280	300	320	Related Products
																											odu
																											ሮፚ

CP96 Series

Dimensions

Basic: CP96S (D) B Bore size - Stroke C (JJ) W

With rod boot at both ends



Bore size [mm]	-	e range*1 mm]	A	BG	øD	E		EE	G	i	к	к	L	_8	L9	L12	PL	R		R	г	SL	sw	VD	w	A 1	WB
32	Up to	o 1000	22	16	12	47	7 G	à 1/8	28.	9	M10>	x 1.25		94	4	6	13	32.	5	M6 :	x 1	8	10	4	4		7
40	Up to	o 1000	24	16	16	54	1 G	à 1/4	32.	6	M12>	(1.25	1	05	4	6.5	14	38		M6 :	(1	8	13	4	5		8.9
50	Up to	o 1000	32	16	20	66	3 G	i 1/4	32		M16	x 1.5	1	06	5	8	14	46.	5 I	M8 x	1.25	-	17	4	6		5.1
63	Up to	o 1000	32	16	20	77	7 G	à 3/8	38.	6	M16	x 1.5	1	21	5	8	16	56.	5 I	M8 x	1.25	-	17	4	9		6.3
80	Up to	o 1000	40	17	25	99	9 G	à 3/8	38.	4	M20	x 1.5	1	28	-	10	16	72		M10>	1.5	-	22	4	11.	5	6
100	Up to	o 1000	40	17	25	118	3 G	à 1/2	42.	9	M20	x 1.5	1	38	-	10	18	89		M10>	1.5	-	22	4	17	-	10
125	Up to	o 1000	54	20	32	144	1 G	à 1/2	58		M27	′ x 2	1	60	-	13	19	110	Ν	/12 x	1.75	-	27	6	17	-	15
*1 Minim	um str	roke for	r truni	nion r	noun	ting: 1	mm	for bo	ore si	ze 32	to 80). 5 m	m for	bore	size	100.1	0 mm	for b	ore s	ize 12	25		÷				
												,			0.20	, .											
Poro										2		,			0.20						h	1					
Bore size	ød	øe	f	1	51	101	151	201	<i>(</i> 301		501	601	701	801	901	1	51		151	201	h		501	601	701	801	901
	ød	øe	f	1 to 50	to	to	to	to	301 to	401 to	501 to	601 to	701 to	801 to	901 to	1 to	51 to	101 to	151 to	201 to	h 301 to	401 to	to	to	to	to	to
size	ø d	ø e 36		50		to 150			301	401	501 to 600	601 to 700	701 to 800	801 to 900	901 to 1000	1 to 50	51	101 to 150	151	201 to 300	h 301 to	401 to 500	to 600	to 700		to 900	to 1000
size [mm]			23		to 100 25	to	to 200	to 300	301 to 400	401 to 500	501 to 600 150	601 to 700	701 to 800	801 to	901 to 1000 250	1 to 50 75	51 to 100	101 to 150 100	151 to 200	201 to 300 138	h 301 to 400	401 to 500 188	to 600 213	to 700	to 800	to 900 288	to 1000 313
size [mm] 32	54	36	23 23	50 12.5 12.5	to 100 25	to 150 37.5 37.5	to 200 50	to 300 75 75	301 to 400 100 100	401 to 500 125 125	501 to 600 150 150	601 to 700 175 175	701 to 800 200 200	801 to 900 225 225	901 to 1000 250 250	1 to 50 75 75	51 to 100 88 88	101 to 150 100 100	151 to 200 113 113	201 to 300 138	h 301 to 400 163 163	401 to 500 188 188	to 600 213 213	to 700 238 238	to 800 263 263	to 900 288 288	to 1000 313 313
size [mm] 32 40	54 54	36 36	23 23 25	50 12.5	to 100 25 25	to 150 37.5	to 200 50 50	to 300 75	301 to 400 100	401 to 500 125 125 125	501 to 600 150 150 150	601 to 700 175 175	701 to 800 200 200 200	801 to 900 225	901 to 1000 250 250 250	1 to 50 75 75 87	51 to 100 88	101 to 150 100 100 112	151 to 200 113 113 125	201 to 300 138 138 150	h 301 to 400 163 163 175	401 to 500 188 188 200	to 600 213 213 225	to 700 238	to 800 263	to 900 288 288 300	to 1000 313 313
size [mm] 32 40 50	54 54 64	36 36 51	23 23 25 25	50 12.5 12.5 12.5	to 100 25 25 25 25	to 150 37.5 37.5 37.5	to 200 50 50 50	to 300 75 75 75	301 to 400 100 100 100	401 to 500 125 125 125	501 to 600 150 150 150 150	601 to 700 175 175 175	701 to 800 200 200 200	801 to 900 225 225 225	901 to 1000 250 250 250 250	1 to 50 75 75 87 87 87	51 to 100 88 88 100	101 to 150 100 100 112 112	151 to 200 113 113	201 to 300 138 138 150	h 301 to 400 163 163 175 175	401 to 500 188 188 200 200	to 600 213 213	to 700 238 238 250 250	to 800 263 263 275 275	to 900 288 288 300	to 1000 313 313 325 325
size [mm] 32 40 50 63	54 54 64 64	36 36 51 51	23 23 25 25 30	50 12.5 12.5 12.5 12.5	to 100 25 25 25 25 25 25 25	to 150 37.5 37.5 37.5 37.5	to 200 50 50 50 50	to 300 75 75 75 75 75	301 to 400 100 100 100 100	401 to 500 125 125 125 125 125	501 to 600 150 150 150 150 150	601 to 700 175 175 175 175 175	701 to 800 200 200 200 200 200	801 to 900 225 225 225 225 225 225	901 to 1000 250 250 250 250 250	1 to 50 75 75 87 87 87	51 to 100 88 88 100 100 116	101 to 150 100 100 112 112 128	151 to 200 113 113 125 125	201 to 300 138 138 150 150	h 301 to 400 163 163 175 175 191	401 to 500 188 188 200 200 216	to 600 213 213 225 225 241	to 700 238 238 250 250	to 800 263 263 275 275 291	to 900 288 288 300 300	to 1000 313 313 325 325 341

Bore

size

[mm] 32

40

50

63

125

Bore

size R TF FB E2

[mm]

32 32 64 7 50

40 36 72 9 55

50 45

63 50 100

80 63 126

Max.

157

AO

Dimensions: With Mounting Bracket (Dimensions are common to single rod and double rod.)

Axial foot (L)



Rod flange (F)





Head flange (G)





90 9

> 9 80

12 100 [mm]

142 144

161 163

170 175

185 190

210 215

250 270

[mm]

WMF

79 16 10

90 20 10

110 25 12

120 25 12

153 30 16

45 20

UF

70

C85

C85W

C85-S/T

C85K

C85K-S/T

C85R

C75

C75W

C75-S/T

C75K-S/T C75K

C75R

CP96

CP96K

C96

C96K

C96Y

C55

E1 TR AH AO AT AB SA XA

48 32 32 10 4.5 7

55 36 36 11 4.5 10

68 45 45 12 5.5 10

80 50 50 12 5.5 10

100 120 75 71 16 6.5 14.5 220 230

8 16

Max 90 90

25

80 100 63 63 14 6.5 12

Single clevis (C) Double clevis (D)





Single clevis (C)



		25	20	24	5			
							[mm]
Bore size [mm]	EW	CD H9	L	MR	XD	UB h14	CB H14	EB
32	$26_{-0.6}^{-0.2}$	10	12	9.5	142	45	26	65
40	28 ^{-0.2}	12	15	12	160	52	28	75
50	32 ^{-0.2}	12	15	12	170	60	32	80
63	$40^{-0.2}_{-0.6}$	16	20	16	190	70	40	90
80	$50_{-0.6}^{-0.2}$	16	20	16	210	90	50	110
100	$60_{-0.6}^{-0.2}$	20	25	20	230	110	60	140
125	70 ^{-0.5}	25	Min. 30	Max. 26	275	130	70	Max. 157

Auto Switch Made to Order **Related Products**

Double clevis (D)



CP96 Series

Dimensions: With Mounting Bracket (Dimensions are common to single rod and double rod.)

Adjustable position trunnion (V)





Bore size [mm] Part no. (Bracket) TM TL eTD eN TW L1 TZ 32 V5032P 50 12 12 64 25 74 40 V5040P 63 16 16 74 28 95 50 V5050P 75 16 16 86 28 107 63 V5063P 90 20 20 101 36 130 80 V5080P 110 20 20 121 36 150							[mm]
40 V5040P 63 16 16 74 28 95 50 V5050P 75 16 16 86 28 107 63 V5063P 90 20 20 101 36 130 80 V5080P 110 20 20 121 36 150	size	Part no. (Bracket)	тм	TL		тw	L1	тz
50 V5050P 75 16 16 86 28 107 63 V5063P 90 20 20 101 36 130 80 V5080P 110 20 20 121 36 150	32	V5032P	50	12	12	64	25	74
63 V5063P 90 20 20 101 36 130 80 V5080P 110 20 20 121 36 150	40	V5040P	63	16	16	74	28	95
80 V5080P 110 20 20 121 36 150	50	V5050P	75	16	16	86	28	107
	63	V5063P	90	20	20	101	36	130
	80	V5080P	110	20	20	121	36	150
100 V5100P 132 25 25 144 48 182	100	V5100P	132	25	25	144	48	182
125 V5125P 160 25 25 169 48 210	125	V5125P	160	25	25	169	48	210

[mm] Minimum Middle Maximum Bore Trunnion size XV XV Ζ holding Ζ Ζ XV force [mm] MIN. MIN. MAX. MAX. 95 3500 N 32 73 78.6 100.6 67.4 89.4 40 82.5 106.5 87.4 111.4 5000 N 76.6 100.6 5000 N 50 83 115 90 122 97 129 129.5 101.4 133.4 11000 N 63 93.6 125.6 97.5 80 98.8 138.8 110 150 121.2 161.2 11000 N 100 117.9 157.9 120 160 122.1 162.1 14000 N **125** 147 201 145 199 143 197 14000 N

® 136-1

SMC



Dimensions: Mounting Brackets

Axial foot (L)



											[mm]
Bore size [mm]	Part no.	АВ	TG ±0.2	E	TR	AO	AU	АН	АТ	R2	Screw size
32	L5032	7	32.5	48	32	10	24	32	4.5	15	M6 x 16L
40	L5040	10	38	55	36	11	28	36	4.5	17.5	M6 x 16L
50	L5050	10	46.5	68	45	12	32	45	5.5	20	M8 x 20L
63	L5063	10	56.5	80	50	12	32	50	5.5	22.5	M8 x 20L
80	L5080	12	72	100	63	14	41	63	6.5	22.5	M10 x 20L
100	L5100	14.5	89	120	75	16	41	71	6.5	27.5	M10 x 20L
125	L5125	16	110	Max. 157	90	Max. 25	45	90	8	30	M12 x 25L
* Cunn	light with	2 foot	brooko	a and	1 m	untin	a cor	014/0			

* Supplied with 2 foot brackets and 4 mounting screws.

Flange (F, G)



_												[mm]
	Bore size [mm]	Part no.	D H11	ø FB	TG ±0.2	Е	R	MF	TF	UF	L4	Screw size
	32	F5032	30	7	32.5	50	32	10	64	79	5	M6 x 20L
	40	F5040	35	9	38	55	36	10	72	90	5	M6 x 20L
_	50	F5050	40	9	46.5	70	45	12	90	110	6.5	M8 x 20L
	63	F5063	45	9	56.5	80	50	12	100	120	6.5	M8 x 20L
	80	F5080	45	12	72	100	63	16	126	153	9	M10 x 25L
	100	F5100	55	14	89	120	75	16	150	178	9	M10 x 25L
_	125	F5125	60	16	110	Max. 157	90	20	180	Max. 224	10.5	M12 x 25L

* Supplied with 4 mounting screws.

Single clevis (C)



													[mm]
Bore size [mm]	Part no.	E1	EW	TG₁	FL	l1	L	l2	ø d 1	øCD	MR	ø d 2	R1
32	C5032	45	26-0.2	32.5	22	5	12	5.5	30	10	9.5	6.6	6.5
40	C5040	51	28-0.2	38	25	5	15	5.5	35	12	12	6.6	6.5
50	C5050	64	32-0.2	46.5	27	5	15	6.5	40	12	12	9	8.5
63	C5063	74	40-0.2	56.5	32	5	20	6.5	45	16	16	9	8.5
80	C5080	94	50-0.2	72	36	5	20	10	45	16	16	11	11
100	C5100	113	$60^{-0.2}_{-0.6}$	89	41	5	25	10	55	20	20	11	12
125	C5125	Max. 157	70-0.5	110	50	7	30	10	60	25	26	13.5	10

* Supplied with 4 mounting screws.

Dimensions: Mounting Brackets, Pivot Brackets for Cylinder Mounting

Double clevis (D)



														[mm]
Bore size [mm]	Part no.	TG₁	FL	l1	L	l2	ø d 1	øCD	MR	ø d 2	R1	E2	UB	СВ
32	D5032	32.5	22	5	12	5.5	30	10	9.5	6.6	6.5	48	45	26
40	D5040	38	25	5	15	5.5	35	12	12	6.6	6.5	56	52	28
50	D5050	46.5	27	5	15	6.5	40	12	12	9	8.5	64	60	32
63	D5063	56.5	32	5	20	6.5	45	16	16	9	8.5	75	70	40
80	D5080	72	36	5	20	10	45	16	16	11	11	95	90	50
100	D5100	89	41	5	25	10	55	20	20	11	12	115	110	60
125	D5125	110	50	7	30	10	60	25	26	13.5	10	Max. 157	130	70

 $\ast\,$ Supplied with 4 mounting screws, clevis pin, and clevis pin bracket.

Clevis pivot bracket (E)



Single clevis with ball joint (CS)



A	
H	

L

														[mm]
Bore size [mm]	Part no.	A	B (Max.)	с	øDн7	EN 0 -0.1	ER (Max.)	ø F н11	øE	L	øM	Ν	Ρ	H ±0.5
32	CS5032	32.5	10.5	22	10	14	15	30	6.6	45	10.5	5.5	5	—
40	CS5040	38	12	25	12	16	18	35	6.6	55	11	5.5	5	—
50	CS5050	46.5	15	27	16	21	20	40	9	65	15	6.5	5	51
63	CS5063	56.5	15	32	16	21	23	45	9	75	15	6.5	5	—
80	CS5080	72	18	36	20	25	27	45	11	95	18	10	5	70
100	CS5100	89	18	41	20	25	30	55	11	115	18	10	5	—
125	CS5125	110	25	50	30	37	40	60	13.5	140	20	10	7	100
· Cupplic	d with 1	mour	ting											

* Supplied with 4 mounting screws.

Related Made to Auto Products Order Switch

Dimensions: Pivot Brackets for Cylinder Mounting

Double clevis pivot bracket (DS)/for ES accessory





																		[mm]
Bore size [mm]	Part no.	E	Bı	B2	B₃	L1	TG₁	т	€1 (Min.)	l2	FL	H (Max.)	ø d 1	ø d 2	ø d 3	øCN	SR (Max.)	R
32	DS5032	45	14	34	3.3	11.5	32.5	3	5	5.5	22	10	30	10.5	6.6	10	11	17
40	DS5040	55	16	40	4.3	12	38	4	5	5.5	25	10	35	11	6.6	12	13	20
50	DS5050	65	21	45	4.3	14	46.5	4	5	6.5	27	12	40	15	9	16	18	22
63	DS5063	75	21	51	4.3	14	56.5	4	5	6.5	32	12	45	15	9	16	18	25
80	DS5080	95	25	65	4.3	16	72	4	5	10	36	16	45	18	11	20	22	30
100	DS5100	115	25	75	6.3	16	89	4	5	10	41	16	55	18	11	20	22	32
125	DS5125	140	37	97	6.3	24	110	6	7	10	50	20	60	20	13.5	30	30	42

* Supplied with 4 mounting screws, clevis pin, and clevis pin bracket.

Clevis pivot bracket with ball joint (ES)





															[mm]
Bore size [mm]	Part no.	ø d з	øCN	ø S 5	K ₁	K 2 (Max.)	l2	G₁	G2	G ₃ (Max.)	EN	EU	СН	H6	ER (Max.)
32	ES5032	11	10	6.6	38	51	8.5	21	18	31	14	10.5	32	10	15
40	ES5040	11	12	6.6	41	54	8.5	24	22	35	16	12	36	10	18
50	ES5050	15	16	9	50	65	10.5	33	30	45	21	15	45	12	20
63	ES5063	15	16	9	52	67	10.5	37	35	50	21	15	50	12	23
80	ES5080	18	20	11	66	86	11.5	47	40	60	25	18	63	14	27
100	ES5100	18	20	11	76	96	12.5	55	50	70	25	18	71	15	30
125	ES5125	20	30	13.5	94	124	17	70	60	90	37	25	90	20	40



Dimensions: Piston Rod Accessories

Floating joint: JA





		[mm]													
Bore size [mm]	Part no.	М	A	В	С	øD	E	F	G	Н	Р	U	Load [kN]	Weight [g]	Angle
32	JA30-10-125	M10 x 1.25	49.5	19.5	—	24	5	8	8	17	9	0.5	2.5	70	
40	JA40-12-125	M12 x 1.25	60	20	—	31	6	11	11	22	13	0.75	4.4	160	
50, 63	JA50-16-150	M16 x 1.5	71.5	22	—	41	7.5	14	13.5	27	15	1	11	300	$\pm 0.5^{\circ}$
80, 100	JAH50-20-150	M20 x 1.5	101	28	31	59.5	11.5	24	16	32	18	2	18	1080	
125	JA125-27-200	M27 x 2	123	34	38	66	13	27	20	41	24	2	28	1500	

* Black color

Rod clevis: GKM (ISO 8140)



									[mm]
Bore size [mm]	Part no.	е	b	d	ø f h11 (Shaft)	ø f нэ (Hole)	l1	c (Min.)	a (Max.)
32	GKM10-20	M10 x 1.25	10 ^{+0.5} +0.15	40	10	10	52	20	20
40	GKM12-24	M12 x 1.25	12 ^{+0.5} +0.15	48	12	12	62	24	24
50, 63	GKM16-32	M16 x 1.5	16 ^{+0.5}	64	16	16	83	32	32
80, 100	GKM20-40	M20 x 1.5	20 ^{+0.5} +0.15	80	20	20	105	40	40
125	GKM30-54	M27 x 2	30 ^{+0.5}	110	30	30	148	54	55

* Supplied with clevis pin and clevis pin bracket.

Rod end: KJ (ISO 8139)





SMC

	- ²⁰ - -								[mm]
Bore size [mm]	Part no.	d₃	ø d 1 н9	h	d 6 (Max.)	b 1 h12	<i>е</i> (Min.)	α	l3
32	KJ10D	M10 x 1.25	10	43	28	14	20	4°	15
40	KJ12D	M12 x 1.25	12	50	32	16	22	4°	17
50, 63	KJ16D	M16 x 1.5	16	64	42	21	28	4°	23
80, 100	KJ20D	M20 x 1.5	20	77	50	25	33	4°	27
125	KJ27D	M27 x 2	30	110	70	37	51	4°	36





Applicable Auto Switches/Refer to the Web Catalog or Best Pneumatics for further information on auto switches.

		Electrical	to	M/inim m		Load volt	age	Auto s	switch	Lea	d wire	length	n [m]	Pre-wired	Anneli	aabla
Туре	Special function	Electrical entry	Indicator light	Wiring (Output)		DC	AC	mo	del	0.5	1	3	5	connector		cable ad
		entry	<u> </u>	(Output)		DC	AC	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	CONNECTOR		au
Ę				3-wire (NPN)		5 V, 12 V		M9NV	M9N				0	0	IC	
switch	—	Grommet		3-wire (PNP)		5 V, 12 V		M9PV	M9P				0	0	circuit	
				2-wire		12 V		M9BV	M9B				0	0	_	
auto	Diagnostic			3-wire (NPN)		5 V, 12 V		M9NWV	M9NW				0	0	IC	
e al	indication		Yes	3-wire (PNP)	24 V	5 V, 12 V	—	M9PWV	M9PW			۲	0	0	circuit	Relay, PLC
state	(2-color indicator)	Grommet		2-wire		12 V 5 V, 12 V		M9BWV	M9BW				0	0	_	
l st		Gronniner		3-wire (NPN)			V 12 V	M9NAV*1	M9NA *1	0	0	۲	0	0	IC	
Solid	Water-resistant (2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PAV*1	M9PA *1	0	0	•	0	0	circuit	
Ň				2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	—	
Reed auto switch			Yes	3-wire (NPN equivalent)	—	5 V	—	A96V	A96	•	—	•	-	_	IC circuit	_
vito	vitca –	Grommet					100 V	A93V*2	A93					_	—	Delau
Ree sv				2-wire	24 V	12 V	100 V or less	A90V	A90	•	_	•	_	_	IC circuit	Relay, PLC

*1 Water-resistant type auto switches can be mounted on the above models, but SMC cannot guarantee water resistance.

Please contact SMC regarding water-resistant types with the above model numbers.

*2 The 1 m lead wire is only applicable to the D-A93.

* Lead wire length symbols: 0.5 m ······· Nil (Example) M9NW

- 1 m ······· M (Example) M9NWM
 - 3 m ······· L (Example) M9NWL
 - 5 m ······· Z (Example) M9NWZ

* Since there are other applicable auto switches than listed above, refer to page 146 for details.

* The D-A9 \square /M9 \square /M9 \square W/M9 \square AL auto switches are shipped together, but not assembled.

* The D-Y59A, Y69A, Y7P, Y7DW, Z7D, Z80 cannot be mounted on the CP96 series.

Moreover, the D-M9DD and A9D auto switches cannot be mounted on square groove of the CP96 series.



* Solid state auto switches marked with "O" are produced upon receipt of order.

ISO (15552) Standard Air Cylinder: Non-rotating Rod Type Double Acting, Single/Double Rod **CP96K Series**





Specifications

Bore size [mm]	32	40	50	63	80	100				
Action	Double acting									
Fluid			A	ir						
Proof pressure			1.5 I	MPa						
Maximum operating pressure			1.0	MPa						
Minimum operating pressure			0.05	MPa						
Ambient and fluid temperatures			to switch: –2 to switch: –1	· ·	0,					
Lubrication			Not required	l (Non-lube)						
Operating piston speed			50 to 10	00 mm/s						
Allowable stroke tolerance		Up to 500	stroke: +2 , 5	01 to 1000 s	troke: +2.4					
Cushion		Air cushic	on on both er	nds + Bumpe	er cushion					
Port size	G 1/8	G 1/4	G 1/4	G 3/8	G 3/8	G 1/2				
Mounting	Basic, Axial foot, Rod flange, Head flange, Single clevis, Double clevis, Adjustable position trunnion									
Non-rotating accuracy	±0	±0.5° ±0.3°								
Allowable rotational torque [N·m]	0.25	0.45	0.64 0.79							

Maximum Strokes

Bore size [mm]	Maximum stroke
32	500
40	500
50	600
63	600
80	800
100	800
A 1 1 6 11 1	

* Aside from the standard strokes, intermediate strokes are also available in 1 mm increments and are produced upon receipt of order.

* Strokes exceeding the max. stroke are available as a special order.

Accessories

N	Nounting	Basic	Foot	Rod flange	Head flange	Single clevis	Double clevis	Adjustable position trunnion
Chanaland	Rod end nut	•	•	•	•	•	•	•
Standard	Clevis pin	_	—	_	_	_	•	_
	Rod end	•	•	•	•	•	•	•
Option	Rod clevis	•	•	•	•	•	•	•
	Rod boot	_	—	_	_	_	_	_

* Do not use a rod end (or floating joint) together with a single clevis with a ball joint (or clevis pivot bracket with a ball joint).

* Refer to pages 137 to 140 for dimensions and part numbers of the accessories.

A Precautions

Be sure to read this before handling the products. Refer to page 219 for safety i instructions. For actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: http://www.smcworld.com

Refer to pages 145 and 146 for cylinders with auto switches.

· Auto Switch Proper Mounting Position (Detection at stroke end)

 \cdot Minimum Stroke for Auto Switch Mounting

· Operating Range

· How to Mount and Move the Auto Switch

CP96K Series

Construction



Component Parts

No.	Description	Material	Q'ty	Note
1	•		,	
	Rod cover	Aluminum die-cast	1	Trivalent chromated
2	Head cover	Aluminum die-cast	1	Trivalent chromated
3	Cylinder tube	Aluminum alloy	1	Hard anodized
4	Piston rod	Stainless steel	1	
5	Piston	Aluminum alloy	1	
6	Cushion ring	Rolled steel	2	Trivalent zinc chromated
7	Piston nut	Rolled steel	1	Trivalent zinc chromated
8	Non-rotating guide	Bearing alloy	1	
9	Cushion valve	Resin	2	
10	Tie-rod	Carbon steel	4	Trivalent zinc chromated
11	Tie-rod nut	Rolled steel	8	Trivalent zinc chromated
12	Cushion seal holder	Aluminum alloy	2	Anodized
13	Wear ring	Resin	1	
14	Rod seal	NBR	1	
15	Piston seal	NBR	1	
16	Cushion seal	Urethane	2	
17	Cushion valve seal	NBR	2	
18	Cylinder tube gasket	NBR	2	
19	Bumper	Urethane	2	
20	Rod end nut	Rolled steel	1	Trivalent zinc chromated
21	Magnet	—	(1)	
22	Flat washer	Steel	8	For ø80, ø100
23	Hexagon socket head set screw	Steel wire	2	Trivalent black zinc chromated

Replacement Parts/Seal Kit (Single rod)

		<u> </u>
Bore size [mm]	Kit no.	Contents
32	CK95-32	
40	CK95-40	
50	CK95-50	Kits include items
63	CK95-63	13 to 16, 18.
80	CK95-80	
100	CK96-100	

* Seal kits consist of items (13 to (16), (18) and can be ordered by using the seal kit number corresponding to each bore size.

 The seal kit includes a grease pack (10 g for ø32 to ø50, 20 g for ø63 and ø80, 30 g for ø100).

Order with the following part number when only the grease pack is needed.

Grease pack part number: GR-S-010 (10 g), GR-S-020 (20 g)

Seal Kit (Double rod)

Bore size [mm]	Kit no.	Contents
32	CK95W-32	
40	CK95W-40	
50	CK95W-50	Kits include items
63	CK95W-63	14 to 16, 18.
80	CK95W-80	
100	CK96W-100	
	÷	·

 Seal kits consist of items (4) to (6), (8) and can be ordered by using the seal kit number corresponding to each bore size.

 The seal kit includes a grease pack (10 g for ø32 to ø50, 20 g for ø63 and ø80, 30 g for ø100).

Order with the following part number when only the grease pack is needed.

Grease pack part number: GR-S-010 (10 g), GR-S-020 (20 g)

Dimensions (Without mounting bracket)



CP96K (D) B Bore size - Stroke CW



* Mounting brackets are the same as standard type. Refer to page 136 for details.

																												2
Bore size [mm]	Stroke range [mm]	A	øB d11	D1	øD	EE	PL	RT	L12	кк	sw	G	BG	L8	VD	VA	WA	WB	wн	zz	zγ	Е	R	L2	L9	н	SL	Auto Switch
32	Up to 500	22	30	12.2	12	G 1/8	13	M6 x 1	6	M10 x 1.25	10	28.9	16	94	4	4	4	7	26	146	190	47	32.5	15	4	48	8	<u>ت</u> 2
40	Up to 500	24	35	14.2	16	G 1/4	14	M6 x 1	6.5	M12 x 1.25	13	32.6	16	105	4	4	5	8.9	30	163	213	54	38	17	4	54	8	Made 1 Orde
50	Up to 600	32	40	19	20	G 1/4	14	M8 x 1.25	8	M16 x 1.5	17	32	16	106	4	4	6	5.1	37	179	244	66	46.5	24	5	69	—	
63	Up to 600	32	45	19	20	G 3/8	16	M8 x 1.25	8	M16 x 1.5	17	38.6	16	121	4	4	9	6.3	37	194	259	77	56.5	24	5	69	—	Related Products
80	Up to 800	40	45	23	25	G 3/8	16	M10 x 1.5	10	M20 x 1.5	22	38.4	17	128	4	4	11.5	6	46	218	300	99	72	30	—	86	_	Selat
100	Up to 800	40	55	23	25	G 1/2	18	M10 x 1.5	10	M20 x 1.5	22	42.9	17	138	4	4	17	10	51	233	320	118	89	32	—	91		<u> </u>

CP96 Series **Auto Switch Mounting**

Auto Switch Proper Mounting Position (Detection at stroke end)









Auto Switch Proper Mounting Position [mm]

Auto switch model		□W(V)	D-A9□(V)		
Bore size	Α	В	Α	В	
32	14	10.5	10	6.5	
40	14	14	10	10	
50	15.5	14.5	11.5	10.5	
63	16.5	15.5	12.5	11.5	
80	21.5	18	17.5	14	
100	21.5	19	17.5	15	
125	16	16	12	12	

 Adjust the auto switch after confirming the operating conditions in the actual setting.

The D-M9□V/M9□WV/M9□AV/A9□V are mountable on ø32 to ø63.

Minimum Stroke for Auto Switch Mounting

								[mm]
Auto switch model	Number of auto switches	32	40	50	63	80	100	125
	2 (Same surface)				50			
D-M9□ D-M9□W	1, 2 (Different surfaces)				10			
	n				10 + 40 (n - 2)			-
	2 (Same surface)			40				
D-M9⊟V D-M9⊟WV	1, 2 (Different surfaces)			10				
	n		10 + 3	30 (n – 2)				
	2 (Same surface)	55			Ę	50		-
D-M9□A	1, 2 (Different surfaces)	15			-	10		
	n	15 + 40 (n - 2)			10 + 40	0 (n – 2)		
	2 (Same surface)			40				
D-M9□AV	1, 2 (Different surfaces)			10				
	n		10 + 3	30 (n – 2)				
	2 (Same surface)				50			
D-A9□	1, 2 (Different surfaces)				10			
	n	10 + 40 (n – 2)						
	2 (Same surface)			40				
D-A9⊡V	1, 2 (Different surfaces)			10				
	n		10 + 3	30 (n – 2)				

* n = 3, 4, 5…

* The D-M9 V/M9 WV/M9 AV/A9 V are mountable on ø32 to ø63.

Operating Range

							[mm]
Auto switch			E	Bore size	ə		
model	32	40	50	63	80	100	125
D-M9□(V) D-M9□W(V) D-M9□A(V)	4	4	5	6	5.5	6	7
D-A9□(V)	7	8	8.5	9.5	9.5	10.5	12.5

* Values which include hysteresis are for guideline purposes only, they are not a guarantee (assuming approximately ±30% dispersion) and may change substantially depending on the ambient environment.

* The D-M9_V/M9_WV/M9_AV/A9_V are mountable on ø32 to ø63.

How to Mount and Move the Auto Switch

<applicable auto="" switch=""> Solid state switch D-M9N(V)/M9P(V)/M9B(V) D-M9NW(V)/M9PW(V)/M9BW(V) D-M9NA(V)/M9PA(V)/M9BA(V) Reed switch</applicable>	
Reed Switch	
How to Mount and Move the Auto Auto switch mounting screw	R

• Use a watchmaker's screwdriver with a handle diameter of 5 to 6 mm when tightening the auto switch mounting screw.

Auto switch mounting screw tightening torque [N·m]

Auto switch model	Tightening torque
D-M9□(V) D-M9□W(V) D-M9□A(V)	0.05 to 0.15
D-A9□(V)	0.10 to 0.20

* As a guide, turn 90° from the position where it comes to feel tight.

* The D-M9□ and A9□ cannot be mounted on square groove of the CP96 series.

* The D-M9 V/M9 WV/M9 AV/A9 V are mountable on ø32 to ø63.

Other than the applicable auto switches listed in "How to Order", the following auto switches are mountable. L L Refer to the Web Catalog or Best Pneumatics for the detailed specifications. I Туре Model Electrical entry Features Applicable bore size I D-M9NV, M9PV, M9BV ____ н **Diagnostic indication** D-M9NWV, M9PWV, M9BWV (2-color indicator) Solid state L ø32 to ø63 Grommet (Perpendicular) Water-resistant I D-M9NAV, M9PAV, M9BAV (2-color indicator) I D-A93V, A96V L Reed н **D-A90V** Without indicator light I * Normally closed (NC = b contact) solid state auto switches (D-M9 E(V)) are also available. For details, refer to the Web Catalog or Best Pneumatics. L With pre-wired connector is also available for solid state auto switches. For details, refer to the Web Catalog or Best Pneumatics.

I

L

I

I

I

L

I

L

Auto Switch

Made to Order

Related Products

SMC

Prior to Use Auto Switch Connections and Examples

Source Input Specifications

Sink Input Specifications



Connect according to the applicable PLC input specifications, as the connection method will vary depending on the PLC input specifications.

Examples of AND (Series) and OR (Parallel) Connections

* When using solid state auto switches, ensure the application is set up so the signals for the first 50 ms are invalid.

3-wire AND connection for NPN output

(Using relays)



3-wire AND connection for PNP output (Using relays)



2-wire AND connection



When two auto switches are connected in series, a load may malfunction because the load voltage will decline when in the ON state. The indicator lights will light up when both of the auto switches are in the ON state. Auto switches with a load voltage less than 20 V

cannot be used.



Internal voltage drop in auto switch is 4 V.

(Performed with auto switches only)





2-wire OR connection

SMC



Load voltage at OFF = Leakage current x 2 pcs. x Load impedance = 1 mA x 2 pcs. x 3 k Ω = 6 V

Example: Load impedance is $3 \text{ k}\Omega$. Leakage current from auto switch is 1 mA.

3-wire OR connection for NPN output



3-wire OR connection for PNP output



(Reed)

Because there is no current leakage, the load voltage will not increase when turned OFF. However, depending on the number of auto switches in the ON state, the indicator lights may sometimes grow dim or not light up, due to the dispersion and reduction of the current flowing to the auto switches.

CP96 Series Simple Specials/Made to Order

Example Specials The following special specifications can be ordered as a simplified Made-to-Order. Please contact your local sales representative for more details.

Symbol	Specifications	(Stand	P96 ard type) e acting Double rod
-XA0 to 30	Change of rod end shape	•	•
Made	e to Order	I	I
Symbol	Specifications	(Stand	P96 ard type)
		Single rod	e acting Double rod
-XB6	Heat-resistant cylinder (-10 to 150°C)*1	•	•
-XC4	With heavy duty scraper	•	
-XC7	Tie-rod, tie-rod nut, etc. made of stainless steel	•	•
-XC10	Dual stroke cylinder/Double rod type	•	
-XC11	Dual stroke cylinder/Single rod type	•	
-XC22	Fluororubber seal	•	•
-XC35	With coil scraper	•	•
-XC65	Made of stainless steel (Combination of -XC7 and -XC68)	•	•
-XC68	Made of stainless steel (with hard chrome plated piston rod)	•	
-XC88	Spatter-resistant coil scraper, Lube-retainer, grease for welding (Piston rod: Stainless steel 304)	•	
-XC89	Spatter-resistant coil scraper, Lube-retainer, grease for welding (Piston rod: S45C)		•

*1 The products with an auto switch are not compatible.

CP96 Series **Simple Specials**

The following changes are dealt with through the Simple Specials System.

For details, refer to the Simple Specials in the Web Catalog. http://www.smcworld.com

1 Change of Rod End Shape

Applicable Series

Description	Model	Action	Symbol for change of rod end shape
Standard tuna	CP96S	Double acting, Single rod	XA0 to 30
Standard type	CP96S-W	Double acting, Double rod	XA0 to 30

Symbol -XA0 to -XA30

APrecautions

- 1. SMC will make appropriate arrangements if no dimension, tolerance, or finish instructions are given in the diagram.
- Standard dimensions marked with "*" will be as follows to the rod diameter (D). Enter any special dimension you require.
- $D \le 6 \rightarrow D 1$ mm, $6 < D \le 25 \rightarrow D 2$ mm, $D > 25 \rightarrow D 4$ mm
- 3. In the case of the double rod type and single acting retraction type, enter the dimensions when the rod is retracted.
- 4. Only one side of a double rod can be manufactured.
- 5. "A0" is the same shape as the standard type. (The specifications of A0 are that only dimensions A and H are changed from the standard type.)



CP96 Series Made to Order

Please contact SMC for detailed dimensions, specifications, and lead times.



Symbol 1 Heat-resistant Cylinder (–10 to 150°C) -XB6 Air cylinder which changed the seal material and grease, so that it could be used even at higher temperature up to 150°C. Applicable Series Description Model Action CP96S Double acting, Single rod Standard type CP96S-W Double acting, Double rod How to Order Standard model no. -XB6 Heat-resistant cylinder Specifications * Operate without lubrication from a pneumatic system lubricator. Ambient temperature range –10 to 150°C Please contact SMC for details on the maintenance intervals for this Seal material Fluororubber cylinder, which differ from those of the standard cylinder. Grease Heat-resistant grease In principle, it is impossible to make built-in magnet type and the one with auto switch. Specifications other than above Same as standard type and external dimensions

Warning Precautions

Be aware that smoking cigarettes etc. after your hands have come into contact with the grease used in this cylinder can create a gas that is hazardous to humans.

2 With Heavy Duty Scraper

But, as for the one with auto switch, and the heat-resistant cylinder with heat-resistant auto switch, since it will be differed depending on the series, please contact SMC.

Piston speed is ranged from 50 to 500 mm/s.

-XC4	Symbol	
	-XC4	

It is suitable for using cylinders under the environment, where there are much dusts in a surrounding area by using a heavy duty scraper on the wiper ring, or using cylinders under earth and sand exposed to the die-casted equipment, construction machinery, or industrial vehicles.

∕∂SMC

Applicable Series

Description	Model	Action	Note
Standard type	CP96S	Double acting, Single rod	ø32 to ø100
Standard type	CP96S-W	Double acting, Double rod	ø32 to ø100

How to Order



Specifications: Same as standard type Dimensions: Same as standard type

▲Caution

Do not replace heavy duty scrapers.

Since heavy duty scrapers are press-fit, do not replace the cover only, but rather the entire rod cover assembly.

Related Products

3 Tie-rod, Tie-rod Nut, etc. Made of Stainless Steel

When using in locations where the rust generation or corrosion likelihood exists, the standard parts material have been partly changed to the stainless steel.

Applicable Series

Description	Model	Action
	CP96S	Double acting, Single rod
Standard type	CP96S-W	Double acting, Double rod

How to Order

Standard model no.	-XC7
Tie-rod, tie-rod nut, etc. mad stainless s	

Specifications

Parts changed to stainless steel	Tie-rod, Tie-rod nut, Mounting bracket nut, Spring washer, Lock nut
Specifications other than above	Same as standard type
Dimensions	Same as standard type

* For bore size ø125, the cushion valve, rod seal holder, and retaining ring will also be stainless steel.

4 Dual Stroke Cylinder/Double Rod Type

Two cylinders are constructed as one cylinder in a back-to-back configuration allowing the cylinder stroke to be controlled in three steps.

Applicable Series

Description	Model	Action	Note	
Standard type	CP96S	Double acting, Single rod	Excludi	ng clevis type
How to Order				Specifications
CP96S Mounting	type Bore size	- Stroke A + Stroke	B C – XC10	Maximum manufacturable stroke [mm]
	Bore Size			1000
		Dual s	troke cylinder •	
Function				
		e is supplied to ports Stroke rokes A and B retract.		/hen air pressure is supplied to ports and \mathbf{O} , B out strokes.
	A When air pressure	e is supplied to ports Stroke trokes.		Then air pressure is supplied to ports and \mathbf{O} , both strokes A and B out strokes.

Dimensions (Dimensions other than below are the same as standard type.)



Bore size [mm]	L8	zz	NA	NB	GC
32	198	294	67.8	10	36
40	220	328	75.2	10	38
50	222	360	74	10	38
63	252	390	87.2	10	42
80	270	442	90.8	14	46
100	290	472	99.8	14	50
125	334	572	130	14	52

Symbol

Symbol

-XC10

Made to Order CP96 Series





CP96 Series

6 Fluororubber Seal

Applicable Series

Description	Model	Action
Standard type	CP96S	Double acting, Single rod
Stanuaru type	CP96S-W	Double acting, Double rod

How to Order

Standard model no.



(including bumper)

Specifications

Seal material	Fluororubber	
Ambient temperature range	With auto switch: -10° C to 60° C (No freezing) ^{*1} Without auto switch: -10° C to 70° C (No freezing)	
Specifications other than above and external dimensions	Same as standard type	

*1 Please contact SMC, as the type of chemical and the operating temperature may not allow the use of this product.

Symbol

-XC22

Symbol

-XC35

Cylinders with auto switches can also be produced; however, auto switch related parts (auto switch units, mounting brackets, built-in magnets) are the same as standard products. Before using these, please contact SMC regarding their suitability for the operating environment.

7 With Coil Scraper

It gets rid of frost, ice, weld spatter, cutting chips adhered to the piston rod, and protects the seals etc.

Applicable Series

Description	Model	Action	Note
Standard tuna	CP96S	Double acting, Single rod	ø32 to ø100
Standard type	CP96S-W	Double acting, Double rod	ø32 to ø100

How to Order

Standard model no.

With coil scraper

- XC35

Specifications: Same as standard type Dimensions: Same as standard type

Made to Order CP96 Series

	Symbol
8 Made of Stainless Steel (Combination of -XC7 and -XC68)	-XC65

Suitable for the cases it is likely to generate rust by being immersed in the water and corrosion.

Applicable Series

Description	Model	Action
Standard type	CP96S	Double acting, Single rod
Standard type	CP96S-W	Double acting, Double rod

* There is a maximum stroke limit for CP96 cylinder.

Maximum Stroke

Maximum Stroke	[mm]
Double acting, Single rod	Double acting, Double rod
ø32: 1800 ø40 to ø100: 1700 ø125: 1600	1000 (Same as standard type)

Specifications

Parts changed to stainless steel	Piston rod, Rod end nut, Tie-rod, Tie-rod nut, Mounting bracket nut, Spring washer, Lock nut
Other specifications and external dimensions	Same as standard type

* For bore size ø125, the cushion valve, rod seal holder, and retaining ring will also be stainless steel.

How to Order



9 Made of Stainless Steel (With Hard Chrome Plated Piston Rod)	E

[mm]

Suitable for the cases it is likely to generate rust by being immersed in the water and corrosion.

Applicable Series

Description	Model	Action
Standard type	CP96S	Double acting, Single rod
	CP96S-W	Double acting, Double rod

Maximum Stroke

Double acting, Single rod	Double acting, Double rod
ø32: 1800 ø40 to ø100: 1700 ø125: 1600	1000 (Same as standard type)

Specifications

Parts changed to stainless steel	Piston rod, Rod end nut	
Other specifications and external dimensions	Same as standard type	

How to Order

Standard model no.

- XC68

C85 C85W C85-S/T **C85K** C85K-S/T **C85R** C75 C75W C75-S/T C75K C75K-S/T C75R CP96 CP96K **C**96 **C96K** C96Y C55

Symbol

XC68

10 Grease for Food Processing Equipment

Food grade grease (certified by NSF-H1) is used as lubricant.

Applicable Series

Description	Model	Action	Note
Standard turna	CP96S	Double acting, Single rod	ø32 to ø100
Standard type	CP96S-W	Double acting, Double rod	ø32 to ø100

- XC85

How to Order

Standard model no.

Grease for food processing equipment

Specifications

Seal material	Nitrile rubber	
Grease	Grease for food processing equipment	
Auto switch	Mountable	
Dimensions	Same as those of the standard type	
Specifications other than the above	Same as those of the standard type	

A Warning Precautions

Be aware that smoking cigarettes, etc., after your hands have come into contact with the grease used in this cylinder can create a gas that is hazardous to humans.

<Not installable>

Food zone	An environment where food which will be sold as merchandize,
	directly touches the cylinder's components
Splash zone	An environment where food which will not be sold as
	merchandize, directly touches the cylinder's components
<installable></installable>	
Non-food zone	An environment where there is no contact with food



- Avoid using this product in the food zone. (Refer to the figure above.)
 When the product is used in an area of liquid splash, or a water
- resistant function is required for the product, please consult SMC. • Operate without lubrication from a pneumatic system lubricator.
- Use the following grease pack for the maintenance work. GR-H-010 (Grease: 10 g)
- Please contact SMC for details on the maintenance intervals for this cylinder, which differ from those of the standard cylinder.

_	Symbol
11 Spatter-resistant Coil Scraper, Lube-retainer, Grease for Welding (Piston rod: Stainless steel 3	304) -XC88

Reduces spatter adhesion and improves durability by the use of the coil scraper, Lube-retainer and grease for welding.

Applicable Series

Description	Model	Action	Note
Standard type	CP96S	Double acting, Single rod	ø32 to ø100
Standard type	CP96S-W	Double acting, Double rod	ø32 to ø100

How to Order

Standard model no.

- <u>XC88</u>

Spatter-resistant coil scraper, Lube-retainer, grease for welding (Piston rod: Stainless steel 304)

Specifications

Piston rod	Stainless steel 304 (With hard chrome plated)	
Scraper	With coil scraper, With Lube-retainer	
Grease	Grease for welding	
Other specifications and external dimensions	Same as standard type	





SMC

12 Spatter-resistant Coil Scraper, Lube-retainer, Grease for Welding (Piston rod: S45C)

Symbol -XC89

Reduces spatter adhesion and improves durability by the use of the coil scraper, Lube-retainer and grease for welding.

Applicable Series

Description	Model	Action	Note
Ctondoud trunc	CP96S	Double acting, Single rod	ø32 to ø100
Standard type	CP96S-W	Double acting, Double rod	ø32 to ø100

How to Order

Standard model no.

- XC89

• Spatter-resistant coil scraper, Lube-retainer, grease for welding (Piston rod: S45C)

Specifications

Piston rod	S45C (With hard chrome plated)	
Scraper	With coil scraper, With Lube-retainer	
Grease	Grease for welding	
Other specifications and external dimensions	Same as standard type	



CP96 Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 219 for safety instructions. For actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: http://www.smcworld.com

Adjustment

Marning

1. Do not open the cushion valve more than the allowable number of rotations (following table).

Although the cushion valve is caulked as a retaining mechanism, do not open the cushion valve more than the allowable number of rotations. If air is supplied and operation started without confirming the above condition, the cushion valve may be ejected from the cover.

The allowable number of rotations refers to the number of rotations until the restrictor of the cushion valve is completely opened from the completely closed state.

2. Keep the screwing torque and the unscrewing torque of the cushion valve to the allowable torque or below (following table).

If a screwing torque or unscrewing torque beyond the allowable torque is applied, the valve will be damaged when the valve is closed completely or exceeds the retaining mechanism when the valve is opened completely, which will dislocate the engagement of the screw and eject the valve.

Bore size [mm]	Cushion valve width across flats	Hexagon wrench	Allowable number of rotations	Allowable torque [N·m]
32, 40	2	JIS 4648 Hexagon wrench key 2	4	0.02
50, 63	2	JIS 4648 Hexagon wrench key 2	4.5	0.02
80, 100	3	JIS 4648 Hexagon wrench key 3	5.5	0.06
125	4	JIS 4648 Hexagon wrench key 4	5	0.10

3. Be certain to activate the air cushion at the stroke end.

When the air cushion is inactivated, if the allowable kinetic energy exceeds the value on page 131, the piston rod assembly or the tie-rod may be damaged. Set the air cushion to valid when operating the cylinder.

ACaution

1. When mounting a foot, flange, single clevis, or double clevis mounting bracket to the cylinder, use a hexagon wrench of the size stated in the table below.

Bore size [mm]	Width across flats	Tightening torque [N·m]
32, 40	4	4.8
50, 63	5	10.4
80, 100	6	18.2
125	10	30.1

2. To mount the adjustable position trunnion mounting bracket to a cylinder, refer to the assembly instructions in the operation manual on the SMC website.