Free Mount Cylinder

CU Series

A space-saving air cylinder with multiple surfaces capable of mounting directly. Offered in rich variations.



Space-saving

The multiple surface direct mounting with a square body and no brackets allows the freedom of the mounting surface.

This enables space-saving designs for equipment.

Mounting







Series Variations

001100 14114110110				
Series	Action	Rod	Bore size (mm)	Page
Standard	Double acting	Single rod		727
CU Series	Double acting	Double rod		734
	Single acting	Single rod (Spring return/Extend)		739
Non-rotating	Davida a stina	Single rod		746
CUK Series	Double acting	Double rod		750
0	Single acting	Single rod (Spring return/Extend)	0.10.10.00.05.00	754
Long stroke CU Series	Double acting	Single rod	6, 10, 16, 20, 25, 32	760
Long stroke, Non-rotating rod CUK Series	Double acting	Single rod		764
With air cushion CU-A Series	Double acting	Single rod	20, 25, 32	768
For vacuum ZCUK Series	Double acting	Single rod	10, 16, 20, 25, 32	777

Combinations of Standard Products and Made

CU Series

: Standard

: Made to Order specifications

○: Special product (Contact SMC for details.)

-: Not available

Series		CU			CUK		
		(Standard)		l)	Non-rotatin	g)	
Action/	Double	acting	Single acting	Double	acting	Single acting	
Туре	Single rod	Double rod	Single rod	Single rod	Double rod	Single rod	

Symbol	Specification	Applicable bore size			ø6 to	ø32			
Standard	Standard		•	•	•	•	•	•	
D	Built-in magnet	ø6 to ø32	•	•	•	•	•	•	
10-, 11-, 21-, 22-	Clean series	ø6 to ø25	•	_	_	_	_	_	
25A-	Copper (Cu) and zinc (Zn)-free Note 3)	ø10 to ø32	•	0	0	•	0	0	
20-	Copper Note 2) and Fluorine-free	ø6 to ø32	•	0	0	•	0	0	
XB6	Heat-resistant cylinder (–10 to 150 °C)		0	0	_	0	0	_	
хв7	Cold-resistant cylinder (-40 to 70 °C)		0	0	_	0	0	_	
ХВ9	Low-speed cylinder (10 to 50 mm/s) Note 1)		0	0	_	0	0	_	
XB13	Low-speed cylinder (5 to 50 mm/s) Note 1)	ø6 to ø32	©	0	_	©	0	_	
XC19	Intermediate stroke (5 mm spacer)		0	0	_	0	0	_	
XC22	Fluororubber seals		©	0	0	0	0	0	
XC34	Rod not extending beyond non-rotating plate		_		_	0	0	0	

Note 1) Refer to the **Web Catalog** for low-speed cylinders.

Note 2) Copper-free for the externally exposed part. For details, refer to the **Web Catalog** Note 3) For details, refer to the SMC website.



to Order Specifications

CU Series

(Long	U stroke) acting	(Long stroke,	JK Non-rotating)	CU-A (Air cushion) Double acting	ZCUK (For vacuum) Double acting	CUX (Low-speed cylinder) Note) Double acting
Single rod			Double rod	Single rod	Single rod	Single rod
	ø6 to	ø32		ø20 to ø32	ø10 t	o ø32
•	•	•	•	•	•	•
•	•	•	•	•	•	•
ı		_	_	_	ı	(ø16 or more)
•	0	•	0	0	0	_
•	0	•	0	0	0	_
0	0	0	0	_	0	_
0	0	0	0	_	0	_
0	0	0	0	_	0	_
0	0	0	0	_	0	_
0	0	0	0	_	0	0
0	0	0	0	_	0	_
_	_	0	0	_	0	_




Precautions on Free Mount

1. Operating speed

Make sure to connect a speed controller to the cylinder and adjust its speed to 500 mm/s or less.

If a load is to be attached to the end of the rod, adjust the speed to the maximum speed shown in Graph (1) or less, in accordance with the added mass.

Graph (1) Load Mass and Maximum Speed



How to read the graph

 Using the CU10 to drive a load weighing 2.5 kg: From the vertical axis in the graph on the left, extend the horizontally from 2.5 kg., and drop down from the point at which it intersects with the tube bore ø10. The maximum speed will be 141 mm/s.

2. Rod end allowable lateral load

Make sure that the lateral load that is applied to the rod end will be no more than the values shown in the tables.

The tables show the value for a single rod. For double rods, please contact SMC.

Standard Double Acting, Single Rod

Without auto switch: CU□-□D

Model		Stroke (mm)											
iviodei	5	10	15	20	25	30	40	50	60	70	80	90	100
CU6	0.085	0.075	0.068	0.061	0.056	0.052	0.045	0.039	0.035	_	_	_	_
CU10	0.34	0.30	0.27	0.25	0.23	0.21	0.18	0.16	0.15	_	_	_	_
CU16	0.69	0.61	0.55	0.50	0.46	0.43	0.37	0.33	0.29	_	_	_	_
CU20	2.2	2.0	1.8	1.6	1.5	1.4	1.2	1.1	1.0	0.92	0.85	0.78	0.73
CU25	3.5	3.2	3.0	2.7	2.6	2.4	2.1	1.9	1.7	1.6	1.4	1.3	1.2
CU32	5.4	4.9	4.6	4.3	4.0	3.8	3.3	3.0	2.8	2.5	2.3	2.2	2.0

With auto switch: CDU□-□D

Model		Stroke (mm)											
iviouei	5	10	15	20	25	30	40	50	60	70	80	90	100
CDU6	0.085	0.075	0.068	0.061	0.056	0.052	0.045	0.039	0.035	_	_	_	_
CDU10	0.34	0.30	0.27	0.25	0.23	0.21	0.18	0.16	0.15	_	_	_	_
CDU16	0.99	0.89	0.81	0.74	0.69	0.64	0.56	0.50	0.45	—	_	_	_
CDU20	3.0	2.7	2.5	2.3	2.1	2.0	1.8	1.6	1.4	1.3	1.2	1.1	1.0
CDU25	4.7	4.3	4.0	3.7	3.5	3.2	2.9	2.6	2.4	2.2	2.0	1.9	1.7
CDU32	7.1	6.6	6.1	5.7	5.4	5.1	4.6	4.1	3.8	3.5	3.2	3.0	2.8

Non-rotating Rod Type

Without auto switch: CUK□-□D

	Stroke (mm)											
5	10	15	20	25	30	40	50	60	70	80	90	100
0.075	0.068	0.061	0.056	0.052	0.048	0.042	0.037	0.033	_	_	_	_
0.30	0.27	0.25	0.23	0.21	0.20	0.17	0.15	0.14	_	_	_	_
0.55	0.50	0.46	0.43	0.40	0.37	0.33	0.29	0.26	—	_	_	_
1.8	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.92	0.85	0.78	0.73	0.68
3.0	2.7	2.6	2.4	2.2	2.1	1.9	1.7	1.6	1.4	1.3	1.2	1.2
4.3	4.0	3.8	3.5	3.3	3.2	2.9	2.6	2.4	2.2	2.1	2.0	1.8
	0.075 0.30 0.55 1.8 3.0	0.075 0.068 0.30 0.27 0.55 0.50 1.8 1.6 3.0 2.7	0.075 0.068 0.061 0.30 0.27 0.25 0.55 0.50 0.46 1.8 1.6 1.5 3.0 2.7 2.6	0.075 0.068 0.061 0.056 0.30 0.27 0.25 0.23 0.55 0.50 0.46 0.43 1.8 1.6 1.5 1.4 3.0 2.7 2.6 2.4	0.075 0.068 0.061 0.052 0.052 0.30 0.27 0.25 0.23 0.21 0.55 0.50 0.46 0.43 0.40 1.8 1.6 1.5 1.4 1.3 3.0 2.7 2.6 2.4 2.2	5 10 15 20 25 30 0.075 0.068 0.061 0.052 0.048 0.30 0.27 0.25 0.23 0.21 0.20 0.55 0.50 0.46 0.43 0.40 0.37 1.8 1.6 1.5 1.4 1.3 1.2 3.0 2.7 2.6 2.4 2.2 2.1	5 10 15 20 25 30 40 0.075 0.088 0.061 0.056 0.052 0.048 0.042 0.30 0.27 0.23 0.23 0.21 0.20 0.17 0.55 0.50 0.46 0.43 0.40 0.37 0.33 1.8 1.6 1.5 1.4 1.3 1.2 1.1 3.0 2.7 2.6 2.4 2.2 2.1 1.9	5 10 15 20 25 30 40 50 0.075 0.088 0.081 0.056 0.052 0.048 0.042 0.037 0.30 0.27 0.25 0.23 0.21 0.20 0.17 0.15 0.55 0.50 0.46 0.43 0.40 0.37 0.33 0.29 1.8 1.6 1.5 1.4 1.3 1.2 1.1 1.0 3.0 2.7 2.6 2.4 2.2 2.1 1.9 1.7	5 10 15 20 25 30 40 50 60 0.075 0.088 0.081 0.056 0.052 0.048 0.042 0.037 0.033 0.30 0.27 0.25 0.23 0.21 0.20 0.17 0.15 0.14 0.55 0.50 0.46 0.43 0.40 0.37 0.33 0.29 0.26 1.8 1.6 1.5 1.4 1.3 1.2 1.1 1.0 0.92 3.0 2.7 2.6 2.4 2.2 2.1 1.9 1.7 1.6	5 10 15 20 25 30 40 50 60 70 0.075 0.088 0.081 0.052 0.048 0.042 0.037 0.033 — 0.30 0.27 0.25 0.23 0.21 0.20 0.17 0.15 0.14 — 0.55 0.50 0.46 0.43 0.40 0.37 0.33 0.29 0.26 — 1.8 1.6 1.5 1.4 1.3 1.2 1.1 1.0 0.92 0.85 3.0 2.7 2.6 2.4 2.2 2.1 1.9 1.7 1.6 1.4	5 10 15 20 25 30 40 50 60 70 80 0.075 0.088 0.081 0.056 0.052 0.048 0.042 0.037 0.033 — — 0.30 0.27 0.25 0.23 0.21 0.20 0.17 0.15 0.14 — — 0.55 0.50 0.46 0.43 0.40 0.37 0.33 0.29 0.26 — — 1.8 1.6 1.5 1.4 1.3 1.2 1.1 1.0 0.92 0.85 0.78 3.0 2.7 2.6 2.4 2.2 2.1 1.9 1.7 1.6 1.4 1.3	5 10 15 20 25 30 40 50 60 70 80 90 0.075 0.088 0.081 0.056 0.052 0.048 0.042 0.037 0.033 <

With auto switch: CDUK□-□D

Model						Str	oke (n	nm)					
Widdei	5	10	15	20	25	30	40	50	60	70	80	90	100
CDUK6	0.075	0.068	0.061	0.056	0.052	0.048	0.042	0.037	0.033	_	_	_	_
CDUK10	0.30	0.27	0.25	0.23	0.21	0.20	0.17	0.15	0.14	_	_	_	_
CDUK16	0.81	0.74	0.69	0.64	0.60	0.56	0.50	0.45	0.41	_	_	_	_
CDUK20	2.5	2.3	2.1	2.0	1.9	1.8	1.6	1.4	1.3	1.2	1.1	1.0	1.0
CDUK25	4.0	3.7	3.5	3.2	3.1	2.9	2.6	2.4	2.2	2.0	1.9	1.7	1.6
CDUK32	5.7	5.4	5.1	4.8	4.6	4.4	4.0	3.6	3.4	3.1	2.9	2.7	2.6

Single Acting, Spring Return (S)

Without auto switch: CU□-□S (N)

Model	Str	oke (n	nm)
iviouei	5	10	15
CU6	0.19	0.17	0.15
CU10	0.66	0.59	0.60
CU16	1.4	1.3	1.3
CU20	4.7	4.2	4.4
CU25	6.8	6.2	6.5
CU32	10	9.8	10

With auto switch: CDU□-□S (N) With auto switch: CDU□-□T (N)

Model	Stroke (mm)							
Wodel	5	10	15					
CDU6	0.17	0.15	0.13					
CDU10	0.66	0.59	0.60					
CDU16	1.6	1.5	1.5					
CDU20	5.3	4.8	4.9					
CDU25	7.6	7.0	7.2					
CDU32	12	11	11					

Non-rotating Rod Type Single Acting, Spring Return (S) Without auto switch: CUK□-□S(N)

Model	Stroke (mm)						
Model	5	10	15				
CUK6	0.17	0.15	0.14				
CUK10	0.59	0.54	0.56				
CUK16	1.1	1.0	1.1				
CUK20	3.9	3.6	3.8				
CUK25	5.7	5.3	5.7				
CUK32	8.5	7.9	8.6				

With auto switch: CDUK□-□S (N)

Model	Str	oke (n	nm)
Model	5	10	15
CDUK6	0.15	0.13	0.12
CDUK10	0.59	0.54	0.56
CDUK16	1.3	1.2	1.3
CDUK20	4.4	4.1	4.3
CDUK25	6.5	6.1	6.4
CDUK32	9.7	9.1	9.6

Single Acting, Spring Extend (T)

Without auto switch: CU - T(N)

Model	Stroke (mm)					
Model	5	10	15			
CU6	0.067	0.059	0.052			
CU10	0.29	0.26	0.24			
CU16	0.99	0.89	0.81			
CU20	2.2	2.0	1.8			
CU25	3.5	3.2	3.0			
CU32	5.4	4.9	4.6			

Model	Stroke (mm)						
Model	5	10	15				
CDU6	0.062	0.055	0.049				
CDU10	0.29	0.26	0.24				
CDU16	0.99	0.89	0.81				
CDU20	3.0	2.7	2.5				
CDU25	4.7	4.3	4.0				
CDU32	7.1	6.6	6.1				

Non-rotating Rod Type Single Acting, Spring Extend (T) Without auto switch: CUK□-□T (N)

Model	Stroke (mm)					
Widdei	5	10	15			
CUK6	0.059	0.052	0.047			
CUK10	0.26	0.24	0.22			
CUK16	0.81	0.74	0.69			
CUK20	1.8	1.6	1.5			
CUK25	3.0	2.7	2.6			
CUK32	4.3	4.0	3.8			


With auto switch: CDUK□-□T(N)

Model	Stroke (mm)					
Model	5	10	15			
CDUK6	0.055	0.049	0.044			
CDUK10	0.26	0.24	0.22			
CDUK16	0.81	0.74	0.69			
CDUK20	2.5	2.3	2.1			
CDUK25	4.0	3.7	3.5			
CDUK32	5.7	5.4	5.1			

(N)

Free Mount Cylinder **Double Acting, Single Rod CU** Series Ø6, Ø10, Ø16, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1271 to 1365 for further information on auto switches

	mouble ridio Civil							Auto switch model Lead wir			wire I	ength	n (m)	D			
Туре	Special function	Electrical entry	Indicator light	Wiring (Output)	ı			Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	Pre-wired connector	Applica	ble load	
				3-wire (NPN)		5 V. 12 V		M9NV	M9N	•	•	•	0	0	IC		
	_			3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit		
اء ہ				2-wire		12 V		M9BV	M9B	•	•	•	0	0	_		
Solid state auto switch	5			3-wire (NPN)		5 V, 12 V		M9NWV	M9NW	•	•	•	0	0	IC	Dalau	
Sa	Diagnostic indication	agnostic indication 2-color indicator) Grommet	Yes	3-wire (PNP)	2-wire (NPN) 24 V 12 V 15 V 12 V	V 3 V, 12 V	- L	M9PWV	M9PW	•	•	•	0	0	circuit	Relay,	
등육	(2-color indicator)					2-wire	12 V		M9BWV	M9BW	•	•	•	0	0	_	PLC
a S	Water resistant			3-wire (NPN)		EV 10 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC]	
	(2-color indicator)			3-wire (PNP)		5 V, 12 V	3 V, 12 V	3 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit
	(2-color indicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_	1	
등				3-wire	5.14			A96V	A96						IC		
× is		Yes (NPN equiva	(NPN equivalent)	_ 5 V		_	A96V	A96	•	_	•	_	_	circuit	_		
Reed auto switch	_	Grommet		2-wire	24 V	12 V	100 V	A93V*2	A93	•	•	•	•	_	_	Relay,	
ant	act.		No	∠-wire	24 V	12 V	100 V or less	A90V	A90	•	_	•	_	_	IC circuit	PLC	

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
- *2 1 m type lead wire is only applicable to D-A93
- * Lead wire length symbols: 0.5 m Nil (Example) M9NW
 - M (Example) M9NWM
 - 3 m ···· L (Example) M9NWL 5 m ···· Z (Example) M9NWZ
- * Since there are applicable auto switches other than the above, refer to page 782 for details. * For detail about auto switches with pre-wired connector, refer to pages 1340 and 1341.
- * Auto switches are shipped together but not assembled.

* Solid state auto switches marked with "O" are produced upon receipt of order.

CU Series



Specifications

Bore size (mm)	6	10	16	20	25	32			
Fluid	Air								
Proof pressure			1.05	МРа					
Maximum operating pressure			0.7	MPa					
Minimum operating pressure	0.12 MPa	0.06	MPa	0.05 MPa					
Ambient and fluid temperature	Without auto switch: -10 to 70°C (No freezing)								
,	With auto switch: -10 to 60°C (No freezing)								
Lubrication			Nor	ı-lube					
Piston speed			50 to 5	00 mm/s					
Cushion	Rubber bumper								
Rod end thread	Male thread								
Stroke length tolerance			+1.0 0	mm					

Symbol

Double acting, Single rod, Rubber bumper



Standard Stroke

Bore size (mm)	Standard stroke (mm)					
6, 10, 16	5, 10, 15, 20, 25, 30					
20, 25, 32	5, 10, 15, 20, 25, 30, 40, 50					

For "Long Stroke", refer to page 760.

Made to Order Specifications Click here for details

Symbol Specifications -XB6 Heat resistant (-10 to 150°C) -XB7 Cold resistant (-40 to 70°C) -XB9 Low speed (10 to 50 mm/s) -XB13 Low speed (5 to 50 mm/s) -XC19 Intermediate stroke (5 mm spacer) -XC22 Fluororubber seals

For clean room specifications, refer to the Web Catalog

Tightening Torque/	When mounting the CU series, refer to the below table.

Bore size (mm)	Hexagon socket head cap screw dia.	Proper tightening torque (N·m)				
6, 10	M3	1.08 ±10%				
16	M4	2.45 ±10%				
20, 25	M5	5.10 ±10%				
32	M6	8.04 ±10%				

hearetical Output

I neoretical Output									
Bore size	Rod size	Operating	Piston area	Opera	iting pressure	(MPa)			
(mm)	(mm)	direction	(mm²)	0.3	0.5	0.7			
6	3	OUT	28.3	8.49	14.2	19.8			
0	3	IN	21.2	6.36	10.6	14.8			
10	4	OUT	78.5	23.6	39.3	55.0			
10		IN	66.0	19.8	33.0	46.2			
16	6	OUT	201	60.3	101	141			
10		IN	172	51.6	86.0	121			
20	8	OUT	314	94.2	157	220			
20	· •	IN	264	79.2	132	185			
25	10	OUT	491	147	246	344			
25	'0	IN	412	124	206	288			
20	10	OUT	804	241	402	563			
32	12	INI	601	207	346	454			

Weight/():	Denotes t	he values	with D-A9	3.				(g)				
Model	Cylinder stroke (mm)											
Wodei	5	10	15	20	25	30	40	50				
C(D)U6-□D	22 (27)	25 (35)	28 (38)	31 (41)	34 (44)	37 (47)	_	_				
C(D)U10-□D	36 (41)	40 (50)	44 (54)	48 (58)	52 (62)	56 (66)	_	_				
C(D)U16-□D	50 (75)	56 (86)	62 (92)	68 (98)	74 (104)	80 (110)	_	_				
C(D)U20-□D	95 (128)	106 (143)	117 (154)	128 (165)	139 (176)	150 (187)	172 (209)	194 (231)				
C(D)U25-□D	176 (230)	193 (252)	210 (269)	227 (286)	244 (303)	261 (320)	295 (354)	329 (388)				
C(D)U32-□D	262 (335)	286 (364)	310 (388)	334 (412)	358 (436)	382 (460)	430 (508)	478 (556)				

* For the auto switch weight, refer to page 1271.

Moisture **Control Tube IDK Series**

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.

Low-speed Cylinder

CU X Mounting bracket Bore size - Stroke

Low-speed Cylinder

Smooth operation with a little sticking and slipping at low speed. Can start smoothly with a little ejection even after being rendered for hours.



Specifications

Bore size (mm)	10	16	20	25	32					
Fluid	Air									
Proof pressure		1.05 MPa								
Max. operating pressure		0.7 MPa								
Ambient and fluid	W	ithout auto sw	itch: -10 to 70	°C (No freezin	g)					
temperature		With auto swit	ch: -10 to 60°0	C (No freezing))					
Lubricant		Not a	pplicable (Non	-lube)						
Piston speed	ø10, ø16: 1 to 300 mm/s									
riston specu	ø20 to ø32: 0.5 to 300 mm/s									
Cushion		Rubber bumper on both ends								
Rod end thread	Male thread									
Stroke length tolerance	+1.0 0									

Minimum Operating Pressure


Bore size (mm)	10	16	20	25	32					
Minimum Operating Pressure (MPa)	0.06	0.06	0.05	0.05	0.05					


The dimensions are the same as the double acting, single rod type. Refer to the ${\bf Web\ Catalog}$ for details.

SMC


Construction

ø6








ø16 to ø32



With auto switch







Component Parts

No.	Description	Material	Note
1	Cylinder tube	Aluminum alloy	Hard anodized
2	Head cover	Brass	ø6 to ø10, Electroless nickel plated
2	nead cover	Aluminum alloy	ø16 to ø32, Chromated
	Piston	Brass	ø6
3	Piston	Aluminum alloy	ø10 to ø32, Chromated
4	Piston rod	Stainless steel	
5	Bumper A	Urethane	
6	Bumper B	Urethane	
7 Retaining ring		Carbon tool steel	Phosphate coated

Component Parts

	pononi i arto		
No.	Description	Material	Note
8	Rod end nut	Carbon steel	Chromated
9	Bushing	Bearing alloy	
10	Magnet holder	Brass	ø6
11	Magnet	_	
12	Auto switch	_	
13	Piston gasket		
14*	Piston seal	NBR	
15*	Rod seal	NDA	
16*	Gasket		

Replacement Parts: Seal Kit

Bore size (mm)	Kit no.	Contents									
10	CU10D-PS										
16	CU16D-PS	Set of nos. above (4, (5, (6)									
20	CU20D-PS										
25	CU25D-PS										
32	CLISSE DC										

^{*} Seal kit includes (4, 15, 16. Order the seal kit, based on each bore size.


Seal kit includes a grease pack (10 g).

Order with the following part number when only the grease pack is needed.


Grease pack part number: GR-S-010 (10 g)

Dimensions: Double Acting, Single Rod


ø**6**, ø**10**



ø16 to ø32



Rod End Nut/Accessory



Part no.	Applicable bore size (mm)	d	Нι	В1	C ₁
NTP-006	6	M3 x 0.5	1.8	5.5	6.4
NTP-010	10	M4 x 0.7	2.4	7	8.1
NTJ-015C	16	M5 x 0.8	4	8	9.2
NT-015A	20	M6 x 1.0	5	10	11.5
NT-02	25	M8 x 1.25	5	13	15.0
NT-03	32	M10 x 1.25	6	17	19.6

																	(mm)
Bore size (mm)	A	A'	В	С	D	Е	GA	GB	н	J	к	L	мм	NN	Р	Ö	QA
6	7	_	13	22	3	7	15	10	13	10	17	_	M3 x 0.5	M3 x 0.5 depth 5	3.2	_	_
10	10	_	15	24	4	7	16.5	10	16	11	18	_	M4 x 0.7	M3 x 0.5 depth 5	3.2	_	_
16	11	12.5	20	32	6	7	16.5 ^{Note)}	11.5	16	14	25	5	M5 x 0.8	M4 x 0.7 depth 6	4.5	4	2
20	12	14	26	40	8	9	19	12.5	19	16	30	6	M6 x 1.0	M5 x 0.8 depth 8	5.5	9	4.5
25	15.5	18	32	50	10	10	21.5	13	23	20	38	8	M8 x 1.25	M5 x 0.8 depth 8	5.5	9	4.5
32	10.5	22	40	62	12	11	23	12.5	27	24	48	10	M10 v 1 25	M6 v 1 0 denth 9	6.6	13.5	4.5

Bore size	R	т			With auto switch		
(mm)			S	Z	S	Z	
6	7	6 depth 4.8	33	46	33	46	
10	9	6 depth 5	36	52	36	52	
16	12	7.6 depth 6.5	30	46	40	56	
20	16	9.3 depth 8	36	55	46	65	
25	20	9.3 depth 9	40	63	50	73	
32	24	11 depth 11.5	42	69	52	79	

Note) 5 stroke (CU16-5D): 14.5 mm




CU Series Auto Switch Mounting

Proper Auto Switch Mounting Position (Detection at stroke end) and Its Mounting Height

D-A9□

D-M9□

D-M9□W D-M9□A





(): Denotes the values of D-A96.

D-A9□V D-M9□V D-M9□WV

D-M9□AV







(): Denotes the values of D-A9□V.

(mm

Bore size	D-A9□, D-A9□V		D-M9□, D-M9□W		D-M9□V, D-M9□WV		D-M9□A			D-M9□AV					
(mm)	Α	В	W	Α	В	W	Α	В	W	Α	В	W	Α	В	w
6	13.5	-0.5	2.5 (5)	17.5	3.5	6.5	17.5	3.5	4.5	17.5	3.5	8.5	17.5	3.5	6.5
10	12.5	3.5	-1.5 (1)	16.5	7.5	2.5	16.5	7.5	0.5	16.5	7.5	4.5	16.5	7.5	2.5
16	16	4	-2 (0.5)	20	8	1.5	20	8	-0.5	20	8	3.5	20	8	1.5
20	20	6	-4 (-1.5)	24	10	0	24	10	-2	24	10	2	24	10	0
25	22.5	7	-5.5 (-3)	26.5	11	-1.5	26.5	11	-3.5	26.5	11	0.5	26.5	11	-1.5
32	23.5	8.5	-6.5 (-4)	27.5	12.5	-2.5	27.5	12.5	-4.5	27.5	12.5	-0.5	27.5	12.5	-2.5

Note 1) Figures in the table above are used as a reference when mounting the auto switches for stroke end detection. In the case of actually setting the auto switches, adjust them after confirming their operation.

Note 2) Negative figures in the table W indicate an auto switch is mounted inward from the edge of the cylinder body.

Note 3) In the case of the 5 stroke or the 10 stroke, there are times in which the auto switch will not turn OFF or 2 auto switches will turn ON simultaneously due to their movement range. Therefore, set the position approximately 1 to 4 mm outward from the values given in the table above. Then, perform an operation inspection to make sure that the auto switches operate normally (if 1 switch is used, make sure that it turns ON and OFF properly; if 2 auto switches are used, make sure that both auto switches turn ON).

Note 4) () in column W is the dimensions of D-A90 and A93.

Operating Range

						(mm)				
Auto switch model	Bore size									
Auto switch model	6	10	16	20	25	32				
D-A9□, A9□V	5	6	9	11	12.5	14				
D-M9□, M9□V										
D-M9□W, M9□WV	3	4	5.5	7	7	7.5				
D-M9□A, M9□AV										


^{*} Since the operating range is provided as a guideline including hysteresis, it cannot be guaranteed (assuming approximately $\pm 30\%$ dispersion).

It may vary substantially depending on an ambient environment.

Minimum Stroke for Auto Switch Mounting

			(mm)						
No. of auto	Applicable auto switch								
switches mounted	D-A9□, D-A9□V	D-M9□, D-M9□V	D-M9□W, D-M9□WV D-M9□A, D-M9□AV						
1 pc.	5	5	5						
2 pcs.	10	5	10						

Auto Switch Groove Position




		(mm)
Bore size (mm)	Α	В
6	8.2	9
10	10.3	13
16	15	18
20	21	23
25	27	25
32	35	27

Caution on Proximity Installation

When free mounting cylinders equipped with auto switches are used, the auto switches could activate unintentionally if the installed distance is less than the dimensions shown in the table. Therefore, make sure to provide a greater clearance. Due to unavoidable circumstances, if they must be used with less distance than the dimensions given in the table, the cylinders must be shielded. Therefore, affix a steel plate or a magnetic shield plate (MU-S025) to the area on the cylinder that corresponds to the adjacent auto switch. (Please contact SMC for details.) Auto switches may malfunction if a shield plate is not used.




Material: Ferrite stainless steel, Thickness: 0.3 mm The product can be attached to the cylinder since the bottom side is a seal type.



Bore size (mm)	Mounting pitch L (mm)
6	18
10	20
16	33
20	40
25	46
32	56

Free Mount Cylinder Double Acting, Double Rod CUV Series Ø6, Ø10, Ø16, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1271 to 1365 for further information on auto switches.


		Electrical	ight	Wiring	L	oad voltag	ge	Auto switc	h model	Lead	wire l	ength	n (m)	Pre-wired				
Type	Special function	entry	Indicator light	(Output)	1	DC		DC AC		Perpendicular	icular In-line		1 (M)	3 (L)	5 (Z)	connector	Applicable load	
				3-wire (NPN)		5 V. 12 V		M9NV	M9N	•	•	•	0	0	IC			
				3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit			
ا ج ہ	Diagnostic indication (2-color indicator)			2-wire		12 V		M9BV	M9B	•	•	•	0	0	_	1		
ig at				3-wire (NPN)		5 V. 12 V		M9NWV	M9NW	•	•	•	0	0	IC	Relay,		
s b		Grommet	Yes	3-wire (PNP) 24 V	5 V, 12 V	_	M9PWV	M9PW	•	•	•	0	0	circuit	PLC			
등원	(2-color indicator)			2-wire		12 V		M9BWV	M9BW	•	•	•	0	0	_	PLC		
တ မ	10/-1				3-wire (NPN)	PN)	5 V. 12 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC	1	
	Water resistant (2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit			
	(2-color indicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_	1		
Reed auto switch		Crommet	Yes	3-wire		5 V	_	A96V	A96	•	_	•	_	_	IC circuit	_		
8 S		Grommet	Grommet		2-wire 24 V		12 V	100 V	A93V*2	A93	•	•	•	•	_	_	Relay,	
a l	ant		No	2-wire 24 v		12 V	100 V or less	A90V	A90	•	-	•	_	_	IC circuit	PLC		

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance.
- Consult with SMC regarding water resistant types with the above model numbers. *2 1 m type lead wire is only applicable to D-A93.
- - 1 m M (Example) M9NWM
 - 3 m L (Example) M9NWL 5 m Z (Example) M9NWZ
- * Since there are applicable auto switches other than the above, refer to page 782 for details. * For detail about auto switches with pre-wired connector, refer to pages 1340 and 1341.
- * Auto switches are shipped together but not assembled.



Free Mount Cylinder Double Acting, Double Rod CUW Series





Standard Stroke


Bore size (mm)	Standard stroke (mm)
6, 10, 16	5, 10, 15, 20, 25, 30, 40, 50, 60
20, 25, 32	5, 10, 15, 20, 25, 30, 40, 50, 60, 70, 80, 90, 100

Theoretical Output

(N)

Symbol

Double acting, Single rod, Rubber bumper



Bore size	Rod size	Piston area	Operating pressure (MPa)						
(mm)	(mm)	(mm²)	0.3	0.5	0.7				
6	3	21.2	6.36	10.6	14.8				
10	4	66.0	19.8	33.0	46.2				
16	6	172	51.6	86.0	121				
20	8	264	79.2	132	185				
25	10	412	124	206	288				
32	12	691	207	346	484				

Weight/(): Denotes the values with D-A93.

(g)

													(3
Model						5	Stroke (mm	1)					
iviodei	5	10	15	20	25	30	40	50	60	70	80	90	100
C(D)UW6-□D	27 (32)	30 (40)	34 (44)	37 (47)	40 (50)	44 (54)	51 (61)	58 (68)	65 (75)	-	_	_	_
C(D)UW10-□D	44 (49)	49 (59)	53 (63)	58 (68)	62 (72)	67 (77)	76 (86)	85 (95)	94 (104)	_	_	_	_
C(D)UW16-□D	74 (99)	81 (111)	88 (118)	95 (125)	102 (132)	109 (139)	123 (153)	137 (167)	151 (181)	_	_	_	_
C(D)UW20-□D	132 (165)	145 (182)	158 (195)	171 (208)	184 (221)	197 (234)	223 (260)	250 (287)	275 (312)	301 (338)	327 (364)	353 (390)	379 (416)
C(D)UW25-□D	240 (294)	260 (319)	280 (339)	300 (359)	321 (380)	341 (400)	381 (440)	421 (480)	461 (520)	501 (560)	541 (600)	581 (640)	621 (680)
C(D)UW32-□D	365 (438)	394 (472)	422 (500)	451 (529)	479 (557)	508 (586)	586 (664)	622 (700)	679 (757)	736 (814)	793 (871)	850 (928)	907 (985)

^{*} For the auto switch weight, refer to page 1271.

Tightening Torque

When mounting the CUW series, refer to page 728.

Moisture Control Tube **IDK Series**

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.


Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.




Construction


ø6


With auto switch







ø10





ø16 to ø32





Component Parts

No.	Description	Material	Note
1	Cylinder tube	Aluminum alloy	Hard anodized
2	Rod cover	Aluminum alloy	Chromated
3	Rod cover retainer	Aluminum alloy	Hard anodized
4	Piston	Brass	ø6
5	Distant	Brass	ø6
э	Piston	Aluminum alloy	ø10 to ø32, Chromated
6	Piston rod	Stainless steel	
7	Piston rod	Stainless steel	ø6
- 8	Bushing	Bearing alloy	

Component Parts

No. Description Mate	rial Note
9 Bumper Ureth	ane
10 Rod end nut Carbon	steel Chromated
11 Hexagon socket head cap screw Carbon	steel Chromated
12 Magnet —	
13 Auto switch —	-
14 Piston gasket	
15* Piston seal NB	
16* Rod seal	n
17* Gasket	

Replacement Parts: Seal Kit


		E	Bore size (mm) / Part no	D.						
	10	10 16 20 25 32								
Kit no.	CUW10D-PS	CUW16D-PS	CUW20D-PS	CUW25D-PS	CUW32D-PS					

^{*} Seal kit includes (5, (6, (7)). Order the seal kit, based on each bore size.


Seal kit includes a grease pack (10 g).
 Order with the following part number when only the grease pack is needed.
 Grease pack part number: GR-S-010 (10 g)

Free Mount Cylinder Double Acting, Double Rod CUW Series


Dimensions: Double Acting, Double Rod



ø16 to ø32



Rod End Nut/Accessory



Material: Carbon steel

Part no.	Applicable bore size (mm)	d	Нı	Вı	C ₁
NTP-006	6	M3 x 0.5	1.8	5.5	6.4
NTP-010	10	M4 x 0.7	2.4	7	8.1
NTJ-015C	16	M5 x 0.8	4	8	9.2
NT-015A	20	M6 x 1.0	5	10	11.5
NT-02	25	M8 x 1.25	5	13	15.0
NT-03	32	M10 x 1.25	6	17	19.6

Bore size (mm)	Α	A'	В	С	D	E	GA	GB	н	J	к	L	ММ	NN	Р	Q	QA
6	7	_	13	22	3	7	15	16	13	10	17	-	M3 x 0.5	M3 x 0.5 depth 5	3.2	_	_
10	10	_	15	24	4	7	16.5	16	16	11	18	_	M4 x 0.7	M3 x 0.5 depth 5	3.2	—	_
16	11	12.5	20	32	6	7	16.5 Note)	19	16	14	25	5	M5 x 0.8	M4 x 0.7 depth 6	4.5	4	2
20	12	14	26	40	8	9	19	21.5	19	16	30	6	M6 x 1.0	M5 x 0.8 depth 8	5.5	9	4.5
25	15.5	18	32	50	10	10	21.5	22	23	20	38	8	M8 x 1.25	M5 x 0.8 depth 8	5.5	9	4.5
32	19.5	22	40	62	12	11	23	22.5	27	24	48	10	M10 x 1.25	M6 x 1.0 depth 9	6.6	13.5	4.5

Bore size	R	SA	-	w	Without a	uto switch	With auto switch		
(mm)	_ n	SA		W	S	Z	S	Z	
6 7		6	6 depth 4.8	13	38	70	38	70	
10	9	6	6 depth 5	16	36	74	36	74	
16	12	7.5	7.6 depth 6.5	16	30	69.5	40	79.5	
20	16	9	9.3 depth 8	19	36	83	46	93	
25	20	9	9.3 depth 9	23	40	95	50	105	
32	24	10	11 depth 11.5	27	42	106	52	116	


Note 1) 5 stroke (CUW16-5D): GA = 14.5

Note 2) The two chamfered positions for the double rod type are not identical.

CUW Series Auto Switch Mounting


Proper Auto Switch Mounting Position (Detection at stroke end) and Mounting Height


D-A9□ D-M9□ D-M9□W D-M9□A



(): Denotes the values of D-A96.

D-A9□V D-M9□V D-M9□WV D-M9□AV





(): Denotes the values of D-A9□V.

															(
Bore size	D-A	D-A9□, D-A9□V			D-M9□, D-M9□W			D-M9□V, D-M9□WV			D-M9□A			D-M9□AV		
(mm)	Α	В	w	Α	В	w	Α	В	w	Α	В	w	Α	В	w	
6	13.5	5.5	-3.5 (-1)	17.5	9.5	0.5	17.5	9.5	-1.5	17.5	9.5	2.5	17.5	9.5	0.5	
10	12.5	9.5	-7.5 (-5)	16.5	13.5	-3.5	16.5	13.5	-5.5	16.5	13.5	-1.5	16.5	13.5	-3.5	
16	16	11.5	-9.5 (-7)	20	15.5	-5.5	20	15.5	-7.5	20	15.5	-3.5	20	15.5	-5.5	
20	20	15	-13 (-10.5)	24	19	-9	24	19	-11	24	19	-7	24	19	-9	
25	22.5	16	-14.5 (-12)	26.5	20	-10.5	26.5	20	-12.5	26.5	20	-8.5	26.5	20	-10.5	
32	23.5	18.5	-16.5 (-14)	27.5	22.5	-12.5	27.5	22.5	-14.5	27.5	22.5	-10.5	27.5	22.5	-12.5	

Note 1) Figures in the table above are used as a reference when mounting the auto switches for stroke end detection. In the case of actually setting the auto switches, adjust them after confirming their operation.

Note 2) Negative figures in the table W indicate an auto switch is mounted inward from the edge of the cylinder body.

Note 3) In the case of the 5 stroke or the 10 stroke, there are times in which the auto switch will not turn OFF or 2 auto switches will turn ON simultaneously due to their movement range. Therefore, set the position approximately 1 to 4 mm outward from the values given in the table above. Then, perform an operation inspection to make sure that the auto switches operate normally (if 1 switch is used, make sure that it turns ON and OFF properly; if 2 auto switches are used, make sure that both auto switches turn ON).

Note 4) () in column W is the dimensions of D-A90 and A93.

Operating Range

						(mm)					
Auto switch model		Bore size (mm)									
Auto switch model	6	10	16	20	25	32					
D-A9□, A9□V	5	6	9	11	12.5	14					
D-M9□, M9□V											
D-M9□W, M9□WV	3	4	5.5	7	7	7.5					
D-M9□A, M9□AV											

^{*} Since the operating range is provided as a guideline including hysteresis, it cannot be guaranteed (assuming approximately ±30% dispersion). It may vary substantially depending on an ambient environment.


Minimum Stroke for Auto Switch Mounting

No. of auto	Applicable auto switch					
switches mounted	D-A9□, D-A9□V	D-M9□, D-M9□V	D-M9□W, D-M9□WV D-M9□A, D-M9□AV			
1 pc.	5	5	5			
2 pcs.	10	5	10			

(mm)

Free Mount Cylinder Single Acting, Single Rod, Spring Return/Extend **CU** Series Ø6, Ø10, Ø16, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1971 to 1365 for further information on auto switch

Applicable Auto Switches/Heler to pages 1271 to 1365 for further information on auto switches.																				
		Flootrical	틄	\A/ississ or	L	oad voltag	ge Auto switc		h model	Lead	wire I	ength	n (m)	Dua minad						
Туре	Special function	Electrical entry	Indicator light	Wiring (Output)			AC	Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	Pre-wired connector	Applica	ble load				
				3-wire (NPN)		5 V. 12 V		M9NV	M9N	•	•	•	0	0	IC					
	_			3-wire (PNP)		3 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit					
ء د				2-wire		12 V		M9BV	M9B	•	•	•	0	0	_					
Solid state auto switch	5			3-wire (NPN)	24 V 5 V, 12 V	5 V 40 V	5 V 40 V	5 V 10 V	E V 10 V	E V 10 V		M9NWV	M9NW	•	•	•	0	0	IC	Dalau.
SS	Diagnostic indication	Grommet	Yes	3-wire (PNP)		3 V, 12 V	v, 12 v —	M9PWV	M9PW	•	•	•	0	0	circuit	Relay, PLC				
등욕	(2-color indicator)			2-wire		12 V 5 V, 12 V			M9BWV	M9BW	•	•	•	0	0	_	PLC			
a S	Water resistant			3-wire (NPN)						M9NAV*1	M9NA*1	0	0	•	0	0	IC			
	(2-color indicator)			3-wire (PNP)				M9PAV*1	M9PA*1	0	0	•	0	0	circuit					
	(2-color indicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_					
등				3-wire		5 V		A96V	A96						IC					
ž e		Grommet	Yes	(NPN equivalent)	_	5 V	_	ASOV	A96	•	_	•	_	_	circuit	_				
Reed auto switch	_	Gioillinet		2-wire	24 V	12 V	100 V	A93V*2	A93	•	•	•	•	_	_	Relay,				
Ē			No	2-wire	24 V	12 V	100 V or less	A90V	A90	•	_	•	_	_	IC circuit	PLC				

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
- *2 1 m type lead wire is only applicable to D-A93
- * Lead wire length symbols: 0.5 m ···· Nil (Example) M9NW * Solid state auto switches marked with "O" are produced upon receipt of order. M (Example) M9NWM
 - ···· L (Example) M9NWL ··· Z (Example) M9NWZ 5 m
- * Since there are applicable auto switches other than the above, refer to page 782 for details.
- * For detail about auto switches with pre-wired connector, refer to pages 1340 and 1341.
- * Auto switches are shipped together but not assembled.

CU Series




Specifications

Bore size (mm)	6	10	16	20	25	32		
Fluid	Air							
Proof pressure		1.05 MPa						
Maximum operating pressure	0.7 MPa							
Minimum operating pressure	0.2 MPa	0.2 MPa 0.15 MPa 0.13 MPa						
Ambient and fluid temperature	Without auto switch: -10 to 70°C (No freezing)							
Ambient and hald temperature	With auto switch: −10 to 60°C (No freezing)							
Lubrication	Non-lube							
Piston speed	50 to 500 mm/s							
Cushion	Rubber bumper							
Rod end thread	Male thread							
Stroke length tolerance	+ 1.0 mm							

Note) ø6 with auto switch type: One side rubber bumper

Symbol



Standard Stroke

Bore size (mm)	Standard stroke (mm)	
6, 10, 16, 20, 25, 32	5, 10, 15	

erol Made to Order Specifications

Click here for details						
Symbol	Specifications					
-XC22	Fluororubber seals					

Theoretical Output

A -4!	Bore size	Ope	Operating pressure (MPa)				
Action	(mm)	0.3	0.5	0.7			
	ø6	4.99	10.7	16.3			
	ø 10	16.7	32.4	48.1			
Continue restrum (C)	ø 16	45.6	86.3	126			
Spring return (S)	ø 20	73	136	199			
	ø 25	119	218	316			
	ø 32	207	368	529			
	ø6	2.86	7.10	11.3			
	ø 10	12.9	26.1	39.3			
0	ø 16	37.2	71.8	106			
Spring extend (T)	ø 20	58	111	164			
	ø 25	95	178	260			
	ø 32	173	312	450			

For the reactive force of spring return, refer to page 1572.

Weight/(): Denotes the values with D-A93

weight/(): Denotes the values with D-A93.						
Model	Stroke (mm)					
Wodel	5	10	15			
C(D)U6-□S,T	22 (27)	25 (35)	28 (38)			
C(D)U10-□S,T	36 (41)	40 (50)	48 (58)			
C(D)U16-□S,T	50 (75)	56 (86)	71 (101)			
C(D)U20-□S,T	95 (128)	106 (143)	133 (170)			
C(D)U25-□S,T	176 (230)	193 (252)	235 (294)			
C(D)U32-□S,T	262 (335)	286 (364)	347 (425)			

Tightening Torque

When mounting a CU single acting series, refer to page 728.

Spring reaction force

Refer to page 1572 (Table (3): Spring Reaction Force).


Moisture Control Tube IDK Series


When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.


Construction

Single acting, Spring return






ø16 to ø32



Component Parts

No.	Description	Material	Note
1	Cylinder tube	Aluminum alloy	Hard anodized
	Head cover	Brass	ø6 to ø10, Electroless nickel plated
2	neau cover	Aluminum alloy	ø16 to ø32, Chromated
	Piston	Brass	ø6
3	3 Piston	Aluminum alloy	ø10 to ø32, Chromated
4	Piston	Aluminum alloy	ø10
5	Piston rod	Stainless steel	
6	Bumper A	Urethane	
7	Bumper B	Urethane	
-8	Return spring	Piano wire	Zinc chromated

With auto switch



Component Parts

COIII	ponent i arts		
No.	Description	Material	Note
9	Spring seat	Brass	
10	Spring seat	Brass	
11	Retaining ring	Carbon tool steel	Phosphate coated
12	Rod end nut	Carbon steel	Chromated
13	Bushing	Bearing alloy	
14	Magnet holder	Brass	ø6
15	Magnet	_	
16	Auto switch	_	
17	Piston gasket		
18*	Piston seal	NBR	
19*	Gasket		

Replacement Parts: Seal Kit

		Bore size (mm) / Part no.							
	10	16	20	25	32				
Kit no	CU10S-PS	CU16S-PS	CU20S-PS	CU25S-PS	C11325-PS				

^{*} Seal kit includes (8), (9). Order the seal kit, based on each bore size.

Grease pack part number: GR-S-010 (10 g)


^{*} Seal kit includes a grease pack (10 g).

Order with the following part number when only the grease pack is needed.


Construction

Single acting, Spring extend


ø6




With auto switch





ø10





Ø16 to Ø32





Component Parts

No.	Description	Material	Note	
1	Cylinder tube	Aluminum alloy	Hard anodized	
2	Head cover	Brass	ø6 to ø10, Electroless nickel plated	
2	neau cover	Aluminum alloy	ø16 to ø32, Chromated	
	Piston	Brass	ø6	
3	Piston	Aluminum alloy	ø10 to ø32, Chromated	
4	Piston	Aluminum alloy	ø10, Chromated	
5	Piston rod	Stainless steel		
- 6	Bumper A	Urethane		
7	Bumper B	Urethane		
-8	Return spring	Piano wire	Zinc chromated	

Component Parts

No.	Description	Material	Note
9	Spring seat	Brass	
10	Stopper	Brass	ø6
11	Retaining ring	Carbon tool steel	Phosphate coated
12	Rod end nut	Carbon steel	Chromated
13	Bushing	Bearing alloy	
14	Plug with fixed orifice	Alloy steel	Black dyed
15	Magnet	_	
16	Auto switch	_	
17	Piston gasket		
18*	Piston seal	NBR	
19*	Rod seal		

Replacement Parts: Seal Kit

•			Bore size (mm) / Part no.		
	10	16	20	25	32
Kit no	CU10T-PS	CU16T-PS	CU20T-PS	CU25T-PS	CU32T-PS

^{*} Seal kit includes ®, 9. Order the seal kit, based on each bore size.


Seal kit includes a grease pack (10 g).


Order with the following part number when only the grease pack is needed.

Grease pack part number: GR-S-010 (10 g)


Dimensions: Single Acting, Spring Return


ø6, ø10






ø16 to ø32





Rod End Nut/Accessory



		Material	Car	bon	steel
Part no.	Applicable bore size (mm)	d	Hı	В1	C ₁
NTP-006	6	M3 x 0.5	1.8	5.5	6.4
NTP-010	10	M4 x 0.7	2.4	7	8.1
NTJ-015C	16	M5 x 0.8	4	8	9.2
NT-015A	20	M6 x 1.0	5	10	11.5
NT-02	25	M8 x 1.25	5	13	15.0
NT-03	32	M10 x 1.25	6	17	19.6


																			(mm)
Bore size (mm)	A	A'	В	С	D	E	GA	GB	н	J	к	L	ММ	NN	Р	Q	QA	R	т
6	7	_	13	22	3	7	15	10	13	10	17	_	M3 x 0.5	M3 x 0.5 depth 5	3.2	_	_	7	6 depth 4.8
10	10	_	15	24	4	7	16.5	10	16	11	18	_	M4 x 0.7	M3 x 0.5 depth 5	3.2	_	_	9	6 depth 5
16	11	12.5	20	32	6	7	16.5	11.5	16	14	25	5	M5 x 0.8	M4 x 0.7 depth 6	4.5	4	2	12	7.6 depth 6.5
20	12	14	26	40	8	9	19	12.5	19	16	30	6	M6 x 1.0	M5 x 0.8 depth 8	5.5	9	4.5	16	9.3 depth 8
25	15.5	18	32	50	10	10	21.5	13	23	20	38	8	M8 x 1.25	M5 x 0.8 depth 8	5.5	9	4.5	20	9.3 depth 9
32	19.5	22	40	62	12	11	23	12.5	27	24	48	10	M10 x 1.25	M6 x 1.0 depth 9	6.6	13.5	4.5	24	11 depth 11.5

_	Bore size		W	ithout a	uto swit	ch			,	With aut	to switch	1	
			S			Z			s			Z	
(mm)	5 st	10 st	15 st	5 st	10 st	15 st	5 st	10 st	15 st	5 st	10 st	15 st
6		38	43	48	51	56	61	38	43	48	51	56	61
10		41	46	56	57	62	72	41	46	56	57	62	72
16		35	40	50	51	56	66	45	50	60	61	66	76
20		41	46	56	60	65	75	51	56	66	70	75	85
25		45	50	60	68	73	83	55	60	70	78	83	93
32		47	52	62	74	79	89	57	62	72	84	89	99


CU Series

Dimensions: Single Acting, Spring Extend


ø**6**, ø**10**



ø16 to ø32



Rod End Nut/Accessory



	1	Material:	Carl	on s	steel
Part no.	Applicable bore size (mm)	d	Нı	Вı	C ₁
NTP-006	6	M3 x 0.5	1.8	5.5	6.4
NTP-010	10	M4 x 0.7	2.4	7	8.1
NTJ-015A	16	M5 x 0.8	4	8	9.2
NT-015A	20	M6 x 1.0	5	10	11.5
NT-02	25	M8 x 1.25	5	13	15.0
NT-03	32	M10 v 1 25	6	17	19.6

																				(mm)
Bore size (mm)	А	A'	В	С	D	E	GA	GB	н	J	к	L	ММ	NN	Р	Q	QA	R	т	v
6	7	_	13	22	3	7	15	10	13	10	17	_	M3 x 0.5	M3 x 0.5 depth 5	3.2	_	_	7	6 depth 4.8	_
10	10	_	15	24	4	7	16.5	10	16	11	18	_	M4 x 0.7	M3 x 0.5 depth 5	3.2	_	_	9	6 depth 5	_
16	11	12.5	20	32	6	7	16.5	11.5	16	14	25	5	M5 x 0.8	M4 x 0.7 depth 6	4.5	4	2	12	7.6 depth 6.5	3.5
20	12	14	26	40	8	9	19	12.5	19	16	30	6	M6 x 1.0	M5 x 0.8 depth 8	5.5	9	4.5	16	9.3 depth 8	5
25	15.5	18	32	50	10	10	21.5	13	23	20	38	8	M8 x 1.25	M5 x 0.8 depth 8	5.5	9	4.5	20	9.3 depth 9	5
32	19.5	22	40	62	12	11	23	12.5	27	24	48	10	M10 x 1.25	M6 x 1.0 depth 9	6.6	13.5	4.5	24	11 depth 11.5	5


		V	/ithout a	uto swite	:h				With aut	o switch		
Bore size		S			z			s			z	
(mm)	5 st	10 st	15 st	5 st	10 st	15 st	5 st	10 st	15 st	5 st	10 st	15 st
6	38	43	48	56	66	76	38	43	48	56	66	76
10	41	46	56	62	72	87	41	46	56	62	72	87
16	45	50	60	66	76	91	45	50	60	66	76	91
20	41	46	56	65	75	90	51	56	66	75	85	100
25	45	50	60	73	83	98	55	60	70	83	93	108
22	47	E2	60	70	90	104	57	60	70	90	00	114

CU Series **Auto Switch Mounting**

Minimum Stroke for Auto Switch Mounting

			(mm)
		Applicable auto switch	
No. of auto switches mounted	D-A9□, D-A9□V	D-M9□, D-M9□V	D-M9□W, D-M9□WV D-M9□A, D-M9□AV
1 pc.	5	5	5
2 pcs.	10	5	10

Proper Auto Switch Mounting Position (Detection at Stroke End) and Mounting Height: Single Acting, Spring Return



Single Ac	ting, Sp	ring i	Return	1												(mm)
Bore size	Stroko					9□, D-M	9□W	D-M9	⊒V, D-M	9□WV		D-M9□ <i>A</i>	1)-M9□A	v
(mm)	Stroke	Α	В	w	Α	В	w	Α	В	w	Α	В	w	Α	В	w
6	All stroke	13.5	0	2.5 (5)	17.5	4	6.5	17.5	4	4.5	17.5	4	8.5	17.5	4	6.5
10	5, 10 15	12.5 17.5	3.5	-1.5 (1)	16.5 21.5	7.5	2.5	16.5 21.5	7.5	0.5	16.5 21.5	7.5	4.5	16.5 21.5	7.5	2.5
16	5, 10 15	16 21	4	-2 (0.5)	20 25	8	2	20 25	8	-0.5	20 25	8	4	20 25	8	1.5
20	5, 10 15	20 25	6	-4 (-1.5)	24 29	10	0	24 29	10	-2	24 29	10	2	24 29	10	0
25	5, 10 15	22.5 27.5	7	-5.5 (-3)	26.5 31.5	11	-1.5	26.5 31.5	11	-3.5	26.5 31.5	11	0.5	26.5 31.5	11	-1.5
32	5, 10 15	23.5 28.5	8.5	-6.5 (-4)	27.5 32.5	12.5	-2.5	27.5 32.5	12.5	-4.5	27.5 32.5	12.5	-0.5	27.5 32.5	12.5	-2.5

Singl	e	Δc	tina	Spring	Extend

Single Ac																(mm)
Bore size	Stroke	D-A9	D□, D-A	9□V	D-M9	□, D- M9	9□W	D-M9	□V, D-M	9□WV		D-M9□A	١		-M9□A	v
(mm)	Siloke	Α	В	W	Α	В	W	Α	В	W	Α	В	W	Α	В	W
6	All stroke	10.5	1.5	0.5 (3)	14.5	5.5	4.5	14.5	5.5	2.5	14.5	5.5	6.5	14.5	5.5	4.5
10	5, 10	12.5	3.5	-1.5 (1)	16.5	7.5	2.5	16.5	7.5	0.5	16.5	7.5	4.5	16.5	7.5	2.5
10	15	12.0	8.5	-6.5 (-4) 16.5	12.5	-2.5	10.5	12.5	-4.5	10.0	12.5	-0.5	10.5	12.5	-2.5	
16	5, 10	16	4	-2 (0.5)	20	8	2		8	0	20	8	4		8	2
16	15	10	9	-7 (-4.5)	20	13	-3	20	13	-5	20	13	-1	20	13	-3
	5, 10	20	6	-4 (-1.5)	24	10	0	0.4	10	-2	24	10	2	0.4	10	0
20	15	20	11	-9 (-6.5)	24	15	-5	24	15	-7	24	15	-3	24	15	-5
	5, 10	00.5	7	-5.5 (-3)	26.5	11	-1.5		11	-3.5	00.5	11	0.5		11	-1.5
25	15	22.5	12	-10.5 (-8)	20.5	16	-6.5	26.5	16	-8.5	26.5	16	-4.5	26.5	16	-6.5
	5, 10	23.5	8.5	-6.5 (-4)	27.5	12.5	-2.5		12.5	-4.5	27.5	12.5	-0.5		12.5	-2.5
32	15	23.5	13.5	-11.5 (-9)	27.5	17.5	-7.5	27.5	17.5	-9.5	27.5	17.5	-5.5	27.5	17.5	-7.5

Note 1) Figures in the table above are used as a reference when mounting the auto switches for stroke end detection. In the case of actually setting the auto switches, adjust them after confirming their operation.

Note 2) Negative figures in the table W indicate an auto switch is mounted inward from the edge of the cylinder body.

Note 3) In the case of the 5 stroke or the 10 stroke, there are times in which the auto switch will not turn OFF or 2 auto switches will turn ON simultaneously due to their movement range. Therefore, set the position approximately 1 to 4 mm outward from the values given in the table above. Then, perform an operation inspection to make sure that the auto switches operate normally (if 1 switch is used, make sure that it turns ON and OFF properly; if 2 auto switches are used, make sure that both auto switches turn ON).

Note 4) () in column W is the dimensions of D-A90 and A93.






Free Mount Cylinder: Non-rotating Rod Type **Double Acting, Single Rod**

CUK Series

Ø6, Ø10, Ø16, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1271 to 1365 for further information on auto switches.

		Electrical	Hgi	Wiring	l	oad voltag	ge	Auto switc	h model	Lead	wire l	ength	(m)	Pre-wired		
Туре	Special function	entry	Indicator light	(Output)		DC	AC	Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	connector	Applica	ble load
				3-wire (NPN)		5 V. 12 V		M9NV	M9N	•	•	•	0	0	IC	
	_			3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit	
ے ہ				2-wire		12 V		M9BV	M9B	•	•	•	0	0	_	
d state switch	Dia			3-wire (NPN)		5 V. 12 V		M9NWV	M9NW	•	•	•	0	0	IC	Relay,
SS	Diagnostic indication (2-color indicator)	Grommet	Yes	3-wire (PNP)	24 V	5 V, 12 V	_	M9PWV	M9PW	•	•	•	0	0	circuit	PLC
Solid auto s	(2-color indicator)			2-wire		12 V		M9BWV	M9BW	•	•	•	0	0	_	FLC
o ≅	Water resistant			3-wire (NPN)		5 V. 12 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC	
	(2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit	
	(2-color iridicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_	
ed		Crammat	Yes	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	_	•	_	_	IC circuit	_
B c	Reed auto switch	Grommet		2-wire	24 V	12 V	100 V	A93V*2	A93	•	•	•	•	_	_	Relay,
anı			No	2-wire	24 V	12 V	100 V or less	A90V	A90	•	_	•	_	_	IC circuit	PLC

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance.
- Consult with SMCregarding water resistant types with the above model numbers. *2 1 m type lead wire is only applicable to D-A93.
- * Lead wire length symbols: 0.5 m ····· Nil (Example) M9NW 1 m M (Example) M9NWM
 - 3 m L (Example) M9NWL
 - 5 m Z (Example) M9NWZ
- * Since there are applicable auto switches other than the above, refer to page 782 for details. * For detail about auto switches with pre-wired connector, refer to pages 1340 and 1341.
- * Auto switches are shipped together but not assembled.



* Solid state auto switches marked with "O" are produced upon receipt of order.

Free Mount Cylinder: Non-rotating Rod Type Double Acting, Single Rod CUK Series



Symbol

Double acting, Single rod, Rubber bumper



Standard Stroke

Bore size (mm)	Standard stroke (mm)					
6, 10, 16	5, 10, 15, 20, 25, 30					
20, 25, 32	5, 10, 15, 20, 25, 30, 40, 50					

Note) For long stroke, refer to page 764.

Made to Order

Made to Order Specifications Click here for details

Symbol	Specifications
-XB6	Heat resistant (-10 to 150°C)
-XB7	Cold resistant (-40 to 70°C)
-XB9	Low speed (10 to 50 mm/s)
-XB13	Low speed (5 to 50 mm/s)
-XC19	Intermediate stroke (5 mm spacer)
-XC22	Fluororubber seals
-XC34	Non-rotating plate with workpiece mounting screw (No extended part on the rod end)

Specifications

Bore size (mm)	6	10	16	20	25	32			
Fluid				Air					
Proof pressure			1.05	МРа					
Maximum operating pressure	0.7 MPa								
Minimum operating pressure	0.15 MPa 0.10 MPa 0.08 MPa								
Ambient and fluid temperature	Without auto switch: -10 to 70°C (No freezing)								
Ambient and haid temperature	With auto switch: -10 to 60°C (No freezing)								
Lubrication			Nor	n-lube					
Piston speed			50 to 5	00 mm/s					
Cushion			Rubbei	r bumper					
Rod end thread	Male thread								
Stroke length tolerance	^{+1.0} mm								
Rod non-rotating accuracy Note)	±0.8° ±0.5°								

Note) No load: Rod at retracted

Minimum Stroke for Auto Switch Mounting

(mm)

		Applicable auto switch									
switches	No. of auto switches mounted	D-A9□, D-A9□V	D-M9□, D-M9□V	D-M9□W, D-M9□WV							
	1 pc.	5	5	5							
	2 pcs.	10	5	10							

Weight/(): Denotes the values with D-A93.

(g)

Poro sizo (mm)				Stroke	(mm)			
Bore size (mm)	5	10	15	20	25	30	40	50
C(D)UK6-□D	28 (33)	31 (41)	34 (44)	37 (47)	40 (50)	43 (53)	_	_
C(D)UK10-□D C(D)UK16-□D	43 (48)	47 (57)	51 (61)	55 (65)	59 (69)	63 (73)	_	_
	60 (85)	66 (96)	72 (102)	78 (108)	84 (114)	90 (120)	_	_
C(D)UK20-□D	113 (147)	124 (164)	136 (176)	148 (188)	160 (200)	172 (211)	195 (235)	219 (260)
C(D)UK25-□D	212 (266)	229 (288)	246 (305)	263 (322)	280 (339)	297 (356)	335 (390)	370 (424)
C(D)UK32-□D	331 (404)	357 (435)	383 (461)	409 (487)	435 (513)	461 (539)	513 (591)	565 (643)

^{*} For the auto switch weight, refer to page 1271.

Allowable Rotational Torque

Bore size (mm)	6	10	16	20	25	32
Allowable rotational torque (N-m)	0.0015	0.02	0.04	0.10	0.15	0.20

Tightening Torque

When mounting the CUK series, refer to page 732.

Theoretical Output

Specifications are the same as CU series double acting, single rod. Refer to page 728.

Auto Switch Mounting Position

For the auto switch mounting position of the CDUK series, refer to page 732, since specifications are the same as standard type, double acting, single rod type.

⚠ Precautions

Be sure to read this before handling the products. Refer to page 20 for safety instructions and pages 21 to 30 for actuator and auto switch precautions.

Operating Precautions

 Do not place your fingers in the clearance between the non-rotating plate and the cylinder tube.

Your fingers could get caught between the non-rotating plate and the cylinder tube when the piston rod retracts. Therefore, never place your finger in this area.

Because the cylinder outputs a great force, it could lead to injury if precautions are not taken to prevent your fingers from getting caucht.

2. When using the non-rotating type, make sure that rotational torque is not applied to the piston rod. If rotational torque must be applied due to unavoidable circumstances, make sure to use it at the allowable rotational torque or less, which is shown in the table on the right.

Moisture Control Tube IDK Series


When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.


Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.




CUK Series

Construction





ø16 to ø32




Component Parts


No.	Description	Material	Note
1	Cylinder tube	Aluminum alloy	Hard anodized
2	Head cover	Brass	ø6 to ø10, Electroless nickel plated
	neau cover	Aluminum alloy	ø16 to ø32, Chromated
3	Piston	Brass	ø6
	riston	Aluminum alloy	ø10 to ø32, Chromated
4	Piston rod	Stainless steel	
5	Bumper A	Urethane	
6	Bumper B	Urethane	
7	Retaining ring	Carbon tool steel	Phosphate coated
8	Rod end nut	Carbon steel	Chromated
9	Bushina	Oil-impregnated	
	Dusting	sintered alloy	
10	Magnet holder	Brass	ø6


Replacement Parts: Seal Kit

Bore size (mm)	Kit no.	Contents
10	CU10D-PS	
16	CU16D-PS	
20	CU20D-PS	Set of nos. above (9, 20, 21.
25	CU25D-PS	
32	CU32D-PS	

With auto switch







Component Parts

No.	Description	Material	Note
11	Magnet	_	
12	Auto switch	_	
13	Non-rotating plate	Aluminum alloy	Nickel plated
14	Guide rod	Stainless steel	
15	Bushing	Bearing alloy	
16	Hexagon socket head cap screw	Carbon steel	Chromated
7	Hexagon socket head set screw	Carbon steel	Chromated
8	Piston gasket		
19*	Piston seal	NDD	
20°	Rod seal	NBR	
21*	Gasket		


^{*} Seal kit includes (9, 20, 2). Order the seal kit, based on each bore size.


Seal kit includes a grease pack (10 g).
 Order with the following part number when only the grease pack is needed.
 Grease pack part number: GR-S-010 (10 g)

Free Mount Cylinder: Non-rotating Rod Type Double Acting, Single Rod CUK Series

Dimensions: Non-rotating Rod Type; Double Acting, Single Rod










2 x NN

ø16 to ø32







Rod End Nut/Accessory Material: Carbon steel





Part no.	Applicable bore size (mm)	d	Ηı	В1	C ₁
NTP-006	6	M3 x 0.5	1.8	5.5	6.4
NTP-010	10	M4 x 0.7	2.4	7	8.1
NTJ-015C	16	M5 x 0.8	4	8	9.2
NT-015A	20	M6 x 1.0	5	10	11.5
NT-02	25	M8 x 1.25	5	13	15.0
NT-03	32	M10 x 1.25	6	17	19.6

(mm)

Bore size (mm)	А	A'	В	С	D	Е	F	FL	FK	FY	GA	GB	Н	J	к	L	ММ
6	7	_	13	22	3	7	8	9	11	20.5	15	10	18	10	17	_	M3 x 0.5
10	10	_	15	24	4	7	8	12	12	22	16.5	10	21	11	18	_	M4 x 0.7
16	11	12.5	20	32	6	7	8	17	13	28	16.5 Note)	11.5	26	14	25	5	M5 x 0.8
20	12	14	26	40	8	9	8	20	16	33	19	12.5	29	16	30	6	M6 x 1.0
25	15.5	18	32	50	10	10	10	22	20	43.5	21.5	13	33	20	38	8	M8 x 1.25
32	10.5	22	40	62	12	11	12	20	2/	51 E	23	125	42	24	48	10	M10 v 1 25

Bore size	NN	P	Q QA	R	т	Υ	Without auto switch With auto switch				
(mm)	ININ	F	Q	QA N		•	,	S	Z	S	Z
6	M3 x 0.5 depth 5	3.2	_	_	7	6 depth 4.8	10.5	33	51	33	51
10	M3 x 0.5 depth 5	3.2	_	_	9	6 depth 5	11.5	36	57	36	57
16	M4 x 0.7 depth 6	0.7 depth 6 4.5 4 2 12		12	7.6 depth 6.5	15.5	30	56	40	66	
20	M5 x 0.8 depth 8	5.5	9	4.5	16	9.3 depth 8	19.5	36	65	46	75
25	M5 x 0.8 depth 8	5.5	9	4.5	20	9.3 depth 9	24.5	40	73	50	83
32	M6 x 1.0 depth 9	6.6	13.5	4.5	24	11 depth 11.5	30.5	42	84	52	94

Note) 5 stroke (CUK16-5D): GA = 14.5




Free Mount Cylinder: Non-rotating Rod Type **Double Acting, Double Rod**

CUKW Series

Ø6, Ø10, Ø16, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1271 to 1365 for further information on auto switches

		Florendered	light) A (: -:	L	oad voltag	je	Auto switc	h model	Lead	wire l	ength	n (m)	Down contract									
Туре	Special function	Electrical entry	Indicator li	Wiring (Output)	ı	DC AC F		Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	Pre-wired connector	Applica	ble load							
				3-wire (NPN)		5 V. 12 V		M9NV	M9N	•	•	•	0	0	IC								
	_			3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit								
ء ج				2-wire		12 V		M9BV	M9B	•	•	•	0	0	_]							
switch switch	5	1		3-wire (NPN)		5 V 40 V	5 V 40 V	5 V 40 V	5 V 10 V	5 V 10 V	5 V. 12 V		M9NWV	M9NW	•	•	•	0	0	IC	Relay,		
s p	Diagnostic indication	color indicator) Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Yes	3-wire (PNP)	24 V	5 V, 12 V	_	M9PWV	M9PW	•	•	•	0	0	circuit	PLC
Solid auto s	(2-color indicator)			2-wire	12 V		M9BWV	M9BW	•	•	•	0	0	_	PLC								
a s	14/-1]		3-wire (NPN)		5 1/ 40 1/	5 V. 12 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC	1						
	Water resistant (2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit								
	(2-color indicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_]							
ch				3-wire		5 V		A96V	A96						IC								
i vit	ii i	— Grommet Y	Yes	(NPN equivalent)	_	- 5 V	_	A90V	A90	•	_	•	_	_	circuit	_							
Reed to switch	_	Gioillilet		2-wire	24 V	12.1/	100 V	A93V*2	A93	•	•	•	•	_	_	Relay,							
anto			No	Z-Wire	24 V	24 V 12 V		A90V	A90	•	_	•	_	_	IC circuit	PLC							

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
- *2 1 m type lead wire is only applicable to D-A93
- * Lead wire length symbols: 0.5 m Nil (Example) M9NW 1 m M (Example) M9NWM 3 m L (Example) M9NWL
- * Solid state auto switches marked with "O" are produced upon receipt of order.
- ···· Z (Example) M9NWZ * Since there are applicable auto switches other than the above, refer to page 782 for details.
- * For detail about auto switches with pre-wired connector, refer to pages 1340 and 1341.
- * Auto switches are shipped together but not assembled.



Free Mount Cylinder: Non-rotating Rod Type Double Acting, Double Rod CUKW Series




Specifications

<u> </u>										
Bore size (mm)	6	10	16	20		25	32			
Fluid	Air									
Proof pressure	1.05 MPa									
Maximum operating pressure	0.7 MPa									
Minimum operating pressure	0.18 MPa 0.13 MPa 0.11 MPa									
Ambient and fluid temperature	Without auto switch: -10 to 70°C (No freezing)									
Ambient and huid temperature	With auto switch: -10 to 60°C (No freezing)									
Lubrication			Non	-lube						
Piston speed			50 to 50	00 mm/s						
Cushion			Rubber	bumper						
Rod end thread	Male thread									
Stroke length tolerance		⁺ ^{1.0} mm								
Rod non-rotating accuracy Note)	±0.8° ±0.5°									

Note) No load: Rod in the non-rotating plate side at retracted

Symbol

Non-rotating rod, Rubber bumper



Standard Stroke

Bore size (mm)	Standard stroke (mm)
6, 10, 16	5, 10, 15, 20, 25, 30, 40, 50, 60
20, 25, 32	5, 10, 15, 20, 25, 30, 40, 50, 60, 70, 80, 90, 100

Minimum Stroke for Auto Switch Mounting

(mm)

No. of outs		Applicable auto switch								
No. of auto switches mounted	D-A9□, D-A9□V	D-M9□, D-M9□V	D-M9□W, D-M9□WV							
1 pc.	5	5	5							
2 pcs.	10	5	10							

Weight/(): Denotes the values with D-A93.

(g) Stroke (mm) Model 5 10 15 20 25 30 40 50 60 70 80 90 100 40 (50) 64 (74) C(D)UKW6-□D (38) (46) (53)(56)(60) (67)(81) 51 (56) 65 (75) 56 60 69 83 02 101 C(D)UKW10-□D (66) (70) (84) (93) (102) (79)84 (109) 91 (121) 105 133 147 C(D)UKW16-□D (128)(135)(142)(149)(163)(177)(191)150 (185) 219 275 (315) 303 163 177 191 205 247 359 387 C(D)UKW20-D (203)(217)(245)(286) (371)(399)(427)(455)(231)(259)(343)276 (330) 296 (355) 316 336 357 377 421 462 (516) 500 541 (600) 582 623 664 C(D)UKW25-□D (375)(395)(416) (436)(476)(559)(641) (682)(723)434 465 495 526 556 587 669 709 831 892 953 1014 C(D)UKW32-DD (507)(543)(573)(665)(747)(787)(970)(1031)(1092)

Theoretical Output

Specifications are the same as double acting, double rod (CUW series). Refer to page 735.

Allowable Rotational Torque

Ensure that rotational torque is not applied to the piston rod of the CUKW series. If rotational torque are applied unavoidably, refer to page 747.

Tightening Torque

When mounting the CUKW series, refer to page 728.

Auto Switch Mounting Position

For the auto switch mounting position of the CUKW series, refer to page 738, since specifications are the same as double acting, double rod type.

Moisture **Control Tube IDK Series**

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.



^{*} For the auto switch weight, refer to page 1271.


CUKW Series

Construction


ø6


8 6 17 14 21 17 8 9 20 4 5 2 22 3 11 7 10 Section AA 16 13

With auto switch





ø10





ø16 to ø32





Component Parts

No.	Description	Material	Note		
1	Cylinder tube	Aluminum alloy	Hard anodized		
2	Rod cover	Aluminum alloy	Chromated		
3	Rod cover retainer	Aluminum alloy	Hard anodized		
4	Piston	Brass	ø6		
- 5	Piston	Brass	ø6		
5	Piston	Aluminum alloy	ø10 to ø32, Chromated		
6	Piston rod	Stainless steel			
7	Piston rod	Stainless steel	ø6		
8	Bushing	Bearing alloy			
9	Bumper	Urethane			
10	Rod end nut	Carbon steel	Chromated		
11	Hexagon socket head cap screw	Carbon steel	Chromated		

Component Parts

No.	Description	Material	Note
12	Magnet	_	
13	Auto switch	_	
14	Non-rotating plate	Aluminum alloy	Nickel plated
15	Guide rod	Stainless steel	
16	Bushing	Bearing alloy	
17	Hexagon socket head cap screw	Carbon steel	Chromated
18	Hexagon socket head set screw	Carbon steel	Chromated
19	Piston gasket		
20*	Piston seal	NBR	
21*	Rod seal	INDH	
22*	Gasket		

Replacement Parts: Seal Kit

		Bore size (mm) / Part no.								
	10 16 20 25 32									
Kit no.	CUW10D-PS	CUW16D-PS	CUW20D-PS	CUW25D-PS	CUW32D-PS					

^{*} Seal kit includes @, @, @. Order the seal kit, based on each bore size.

Order with the following part number when only the grease pack is needed. Grease pack part number: GR-S-010 (10 g)






^{*} Seal kit includes a grease pack (10 g).

Free Mount Cylinder: Non-rotating Rod Type Double Acting, Double Rod CUKW Series

Dimensions: Non-rotating Rod Type; Double Acting, Double Rod



9 6.6 13.5 Note 1) 5 stroke (CUKW16-5D): GA = 14.5

4.5 16 9

4.5 20 9

4.5

45 4 2 12 7.5

5.5

5.5

16

20

25

32

24 Note 2) The two chamfered positions for the double rod type are not identical.

10

7.6 depth 6.5

9.3 depth 8

9.3 depth 9

11 depth 11.5 27

16 15.5 30 79.5 40 89.5

19 19.5

23 24.5 40 105 50 115


30.5 42 121 52 131



36 93 46 103

Free Mount Cylinder: Non-rotating Rod Type Single Acting, Spring Return/Extend **CUK** Series Ø6, Ø10, Ø16, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1271 to 1365 for further information on auto switches.

			gH		Load voltage Auto switch model Lead wire length (m)													
Туре	Special function	Electrical entry	Indicator light	Wiring (Output)	-	DC	AC	Perpendicular	In-line	0.5 (Nil)	1	3 (L)	5 (Z)	Pre-wired connector	Applica	ble load		
				3-wire (NPN)		5 V. 12 V		M9NV	M9N	•	•	•	0	0	IC			
	_			3-wire (PNP)		3 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit			
ے ہ				2-wire		12 V		M9BV	M9B	•	•	•	0	0	_	1		
je ta	6			3-wire (NPN)		5 V. 12 V		M9NWV	M9NW	•	•	•	0	0	IC	Dalau		
SS	Diagnostic indication	Grommet \	Grommet Y	Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Yes	3-wire (PNP)	ire (PNP) 24 V 5 V, 12 V	0	0	circuit	Relay,
Solid state auto switch	(2-color indicator)			2-wire		12 V		M9BWV	M9BW	•	•	•	0	0	_	PLC		
တ ၕ	Motor registent			3-wire (NPN)		5 V. 12 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC]		
	Water resistant (2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit			
	(2-color indicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_	1		
Reed auto switch				3-wire		5 V		A96V	A96	•		_			IC			
S ed		Grommet	Yes	(NPN equivalent)		_ 5v .			ASO	_		_			circuit	_		
5 B	_	Gioillilet		2-wire	24 V	12.1/	100 V	A93V*2	A93	•	•	•	•	_		Relay,		
an			No	2-wire	24 V	24 V 12 V 100		A90V	A90	•	-	•	_		IC circuit	PLC		

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMCregarding water resistant types with the above model numbers.
- *2 1 m type lead wire is only applicable to D-A93.
- * Lead wire length symbols: 0.5 m Nil (Example) M9NW * Solid state auto switches marked with "O" are produced upon receipt of order. ··· M (Example) M9NWM 1 m 3 m L (Example) M9NWL
- * Since there are applicable auto switches other than the above, refer to page 782 for details.

... Z (Example) M9NWZ

- * For detail about auto switches with pre-wired connector, refer to pages 1340 and 1341.
- * Auto switches are shipped together but not assembled.



Free Mount Cylinder: Non-rotating Rod Type Single Acting, Spring Return/Extend **CUK Series**




Specifications

Bore size (mm)	6	10	16	20	25	32			
Fluid	Air								
Proof pressure	1.05 MPa								
Maximum operating pressure			0.7	MPa					
Minimum operating pressure	0.23 MPa 0.18 MPa 0.16 MPa				6 MPa				
Ambient and fluid temperature	Without auto switch: -10 to 70°C (No freezing)								
Ambient and naid temperature	With auto switch: -10 to 60°C (No freezing)								
Lubrication			Non	-lube					
Piston speed			50 to 50	00 mm/s					
Cushion Note 1)	Rubber bumper on both ends								
Rod end thread	Male thread								
Stroke length tolerance	+1.0 0 mm								
Rod non-rotating accuracy Note 2)	±0.8° ±0.5°				:0.5°				

Note 1) ø6: With auto switch, single rubber bumper

Note 2) No load: Rod at retracted

Symbol



Standard Stroke

No. of switches

2 pcs.

(mm)

Bore size (mm)	Standard stroke (mm)
6, 10, 16, 20, 25, 32	5, 10, 15

Made to Order Specifications Click here for details

Symbol	Specifications
-XC22	Fluororubber seals
-XC34	Non-rotating plate with workpiece mounting screw (No extended part on the rod end)

Minimum Stroke for Auto Switch Mounting

10

IIIIIuiii S	illulii Stroke for Auto Switch Mounting (mr											
		Applicable auto switch										
o. of auto hes mounted	D-A9□, D-A9□V	D-M9□, D-M9□V	D-M9□W, D-M9□WV									
1 pc.	5	5	5									

5

Weight/(): Denotes the values with D-A93.

(g)

10

Madel		Stroke (mm)			
Model	5	10	15		
C(D)UK6-□S	28	31	34		
	(33)	(41)	(44)		
C(D)UK10-□S	43	47	55		
	(48)	(57)	(65)		
C(D)UK16-□S	60	66	81		
	(85)	(90)	(111)		
C(D)UK20-□S	113	124	153		
	(147)	(164)	(193)		
C(D)UK25-□S	212	229	271		
	(266)	(288)	(330)		
C(D)UK32-□S	331	357	422		
	(404)	(435)	(500)		

^{*} For the auto switch weight, refer to page 1271.

Tightening Torque

When mounting a CUK single acting series, refer to page 728.

Theoretical Output

Specifications are the same as single acting, spring return/spring extend type (CU series). Refer to page 740.

Spring Reaction Force

Refer to page 1572 (Table (3): Spring Reaction Force).

Auto Switch Mounting Position

For the auto switch mounting position of CDUK series single acting, spring return/spring extend, refer to page 745, since specification are the same as standard type, single acting, spring return/spring extend type.

Allowable Rotational Torque

Make sure that rotational torque is not applied to the piston rod of the CUK series single acting type cylinder. If the rotation torque were applied unavoidably, refer to page 747.

Moisture Control Tube IDK Series

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions. Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.




CUK Series


Construction

Single acting, Spring return







With auto switch





ø10





Ø16 to Ø32





Component Parts

	p					
No.	Description	Material	Note			
1	Cylinder tube	Aluminum alloy	Hard anodized			
2	Head cover	Brass	ø6 to ø10, Electroless nickel plated			
2	nead cover	Aluminum alloy	ø16 to ø32, Chromated			
3	Piston	Brass	ø6			
3	Piston	Aluminum alloy	ø10 to ø32, Chromated			
4	Piston	Aluminum alloy	ø10			
5	Piston rod	Stainless steel				
6	Bumper A	Urethane				
7	Bumper B	Urethane				
- 8	Return spring	Piano wire	Zinc chromated			
9	Spring seat	Brass				
10	Spring seat	Brass				

Component Parts

	iponent i arts		
No.	Description	Material	Note
11	Retaining ring	Carbon tool steel	Phosphate coated
12	Rod end nut	Carbon steel	Chromated
13	Bushing	Bearing alloy	
14	Magnet holder	Brass	ø6
15	Magnet	_	
16	Auto switch	_	
17	Non-rotating plate	Aluminum alloy	Nickel plated
18	Guide rod	Stainless steel	
19	Bushing	Bearing alloy	
20	Hexagon socket head cap screw	Carbon steel	Chromated
21	Hexagon socket head set screw	Carbon steel	Chromated
22	Piston gasket		
23*	Piston seal	NBR	
24*	Gasket		

Replacement Parts: Seal Kit

		Bore size (mm) / Part no	ore size (mm) / Part no.							
	10	16	20	25	32					
Kit no.	CU10S-PS	CU16S-PS	CU20S-PS	CU25S-PS	CU32S-PS					


^{*} Seal kit includes ②, ②. Order the seal kit, based on each bore size.

^{*} Seal kit includes a grease pack (10 g).


Order with the following part number when only the grease pack is needed. Grease pack part number: GR-S-010 (10 g)

Construction


Single acting, Spring extend





With auto switch



ø10







Component Parts

Description	Material	Note
Cylinder tube	Aluminum alloy	Hard anodized
Hand same	Brass	ø6 to ø10, Electroless nickel plated
nead cover	Aluminum alloy	ø16 to ø32, Chromated
B****	Brass	ø6
Piston	Aluminum alloy	ø10 to ø32, Chromated
Piston	Aluminum alloy	ø10, Chromated
Piston rod	Stainless steel	
Bumper A	Urethane	
Bumper B	Urethane	
Return spring	Piano wire	Zinc chromated
Spring seat	Brass	
Stopper	Brass	ø6
Retaining ring	Carbon tool steel	Phosphate coated
	Cylinder tube Head cover Piston Piston Piston rod Bumper A Bumper B Return spring Spring seat Stopper	Cylinder tube Aluminum alloy Head cover Brass Aluminum alloy Brass Aluminum alloy Brass Aluminum alloy Piston Piston od Stainless steel Bumper A Urethane Bumper B Urethane Return spring Piano wire Spring seat Brass Stopper Brass

Component Parts

	•		
No.	Description	Material	Note
12	Rod end nut	Carbon steel	Chromated
13	Bushing	Bearing alloy	
14	Plug with fixed orifice	Alloy steel	Black dyed
15	Magnet	-	
16	Auto switch		
17	Non-rotating plate	Aluminum alloy	Nickel plated
18	Guide rod	Stainless steel	
19	Bushing	Bearing alloy	
20	Hexagon socket head cap screw	Carbon steel	Black zinc chromated
21	Hexagon socket head set screw	Carbon steel	Black zinc chromated
22	Piston gasket		
23*	Piston seal	NBR	
24*	Rod seal		

Replacement Parts: Seal Kit

		Bore size (mm) / Part no.											
	10	16	20	25	32								
Kit no.	CU10T-PS	CU16T-PS	CU20T-PS	CU25T-PS	CU32T-PS								

^{*} Seal kit includes ②, ②. Order the seal kit, based on each bore size.

Grease pack part number: GR-S-010 (10 g)




^{*} Seal kit includes a grease pack (10 g).


Order with the following part number when only the grease pack is needed.

CUK Series


Dimensions: Non-rotating Rod Type; Single Acting, Spring Return









ø16 to ø32













Rod End Nut/Accessory Material: Carbon stee														
Part no.	Applicable bore size (mm)	d	Ηı	В1	C ₁									
NTP-006	6	M3 x 0.5	1.8	5.5	6.4									
NTP-010	10	M4 x 0.7	2.4	7	8.1									
NTJ-015C	16	M5 x 0.8	4	8	9.2									
NT-015A	20	M6 x 1.0	5	10	11.5									
NT-02	25	M8 x 1.25	5	13	15.0									
NT-03	32	M10 x 1.25	6	17	19.6									

Bore size (mm)	А	A'	В	С	D	E	F	FL	FK	FY	GA	GВ	Н	J	к	L	ММ	NN
6	7	_	13	22	3	7	8	9	11	20.5	15	10	18	10	17	_	M3 x 0.5	M3 x 0.5 depth 5
10	10	_	15	24	4	7	8	12	12	22	16.5	10	21	11	18	-	M4 x 0.7	M3 x 0.5 depth 5
16	11	12.5	20	32	6	7	8	17	13	28	16.5	11.5	26	14	25	5	M5 x 0.8	M4 x 0.7 depth 6
20	12	14	26	40	8	9	8	20	16	33	19	12.5	29	16	30	6	M6 x 1.0	M5 x 0.8 depth 8
25	15.5	18	32	50	10	10	10	22	20	43.5	21.5	13	33	20	38	8	M8 x 1.25	M5 x 0.8 depth 8
32	19.5	22	40	62	12	11	12	29	24	51.5	23	12.5	42	24	48	10	M10 x 1.25	M6 x 1.0 depth 9

D								W	ithout a	uto swit	tch			١	Vith aut	o switc	h	
Bore size (mm)	Р	P Q		R	Т	Y	S		Z			S			Z			
(111111)							5 st	10 st	15 st	5 st	10 st	15 st	5 st	10 st	15 st	5 st	10 st	15 st
6	3.2	_	_	7	6 depth 4.8	10.5	38	43	48	56	61	66	38	43	48	56	61	66
10	3.2	_	_	9	6 depth 5	11.5	41	46	56	62	67	77	41	46	56	62	67	77
16	4.5	4	2	12	7.6 depth 6.5	15.5	35	40	50	61	66	76	45	50	60	71	76	86
20	5.5	9	4.5	16	9.3 depth 8	19.5	41	46	56	70	75	85	51	56	66	80	85	95
25	5.5	9	4.5	20	9.3 depth 9	24.5	45	50	60	78	83	93	55	60	70	88	93	103
32	6.6	13.5	4.5	24	11 depth 11.5	30.5	47	52	62	89	94	104	57	62	72	99	104	114

Dimensions: Non-rotating Rod Type; Single Acting, Spring Extend





Rod End Nut/Accessory Material: Carbon steel											
Part no.	Applicable bore size (mm)	d	Hı	В1	C ₁						
NTP-006	6	M3 x 0.5	1.8	5.5	6.4						
NTP-010	10	M4 x 0.7	2.4	7	8.1						
NTJ-015C	16	M5 x 0.8	4	8	9.2						
NT-015A	20	M6 x 1.0	5	10	11.5						
NT-02	25	M8 x 1.25	5	13	15.0						
NT-03	32	M10 x 1.25	6	17	19.6						

Bore size (mm)	А	A'	В	С	D	Е	F	FL	FK	FY	GA	GB	н	J	к	L	ММ	NN
6	7	_	13	22	3	7	8	9	11	20.5	15	10	18	10	17	_	M3 x 0.5	M3 x 0.5 depth 5
10	10	_	15	24	4	7	8	12	12	22	16.5	10	21	11	18	_	M4 x 0.7	M3 x 0.5 depth 5
16	11	12.5	20	32	6	7	8	17	13	28	16.5	11.5	26	14	25	5	M5 x 0.8	M4 x 0.7 depth 6
20	12	14	26	40	8	9	8	20	16	33	19	12.5	29	16	30	6	M6 x 1.0	M5 x 0.8 depth 8
25	15.5	18	32	50	10	10	10	22	20	43.5	21.5	13	33	20	38	8	M8 x 1.25	M5 x 0.8 depth 8
32	19.5	22	40	62	12	11	12	29	24	51.5	23	12.5	42	24	48	10	M10 x 1.25	M6 x 1.0 depth 9


								Without auto switch				With auto switch						
Bore size (mm)	P	Q	QA	R	Т	Y		S			Z			S			Z	
(11111)							5 st	10 st	15 st	5 st	10 st	15 st	5 st	10 st	15 st	5 st	10 st	15st
6	3.2	_	_	7	6 depth 4.8	10.5	38	43	48	61	71	81	38	43	48	61	71	81
10	3.2	_	_	9	6 depth 5	11.5	41	46	56	67	77	92	41	46	56	67	77	92
16	4.5	4	2	12	7.6 depth 6.5	15.5	45	50	60	76	86	101	45	50	60	76	86	101
20	5.5	9	4.5	16	9.3 depth 8	19.5	41	46	56	75	85	100	51	56	66	85	95	110
25	5.5	9	4.5	20	9.3 depth 9	24.5	45	50	60	83	93	108	55	60	70	93	103	118
32	6.6	13.5	4.5	24	11 depth 11.5	30.5	47	52	62	94	104	119	57	62	72	104	114	129

Free Mount Cylinder: Long Stroke Type Double Acting, Single Rod

CU Series

Ø6, Ø10, Ø16, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1271 to 1365 for further information on auto switches.

		Electrical	igh	Wiring	l	oad voltag	ge	Auto switch	h model	Lead	wire l	ength	(m)	Pre-wired		
Туре	Type Special function entry		Indicator light	(Output)	DC		AC	Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	connector	Applicable load	
				3-wire (NPN)		5 V. 12 V		M9NV	M9N	•	•	•	0	0	IC	
	_			3-wire (PNP)		J V, 12 V		M9PV	M9P	•	•	•	0	0	circuit	
ء ج	Diagnostic indication Grommet		2-wire		12 V		M9BV	M9B	•	•	•	0	0	_		
je ta			3-wire (NPN)	ire (NPN) 5 V, 12 V			M9NWV	M9NW	•	•	•	0	0	IC	Relay,	
SS	Diagnostic indication		Yes	3-wire (PNP)	24 V	3 V, 12 V	_	M9PWV	M9PW	•	•	•	0	0	circuit	PLC
Solid auto s	(2-color indicator)			2-wire		12 V		M9BWV	M9BW	•	•	•	0	0	_	
S E	Mater registent			3-wire (NPN)	5 V, 12 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC		
	Water resistant (2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit	
	(2-color indicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_	
Reed to switch		Grommet	Yes	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	_	•	_	_	IC circuit	_
S S	Reauto s	Gioillilet		2-wire	24 V	12 V	100 V	A93V*2	A93	•	•	•	•	_	_	Relay,
ani			No	2-wire	24 V	12 V	100 V or less	A90V	A90	•	-	•	_	_	IC circuit	PLC

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
- *2 1 m type lead wire is only applicable to D-A93.
- * Lead wire length symbols: 0.5 m Nil (Example) M9NW
 - 3 m L (Example) M9NWL
 - 5 m ······ Z (Example) M9NWZ
 - 1 m M (Example) M9NWM

* Solid state auto switches marked with "O" are produced upon receipt of order.

- * Since there are applicable auto switches other than the above, refer to page 782 for details.
- * For detail about auto switches with pre-wired connector, refer to pages 1340 and 1341. * Auto switches are shipped together but not assembled.




Free Mount Cylinder: Long Stroke Type Double Acting, Single Rod CU Series



Specifications

Bore size (mm)	6	10	16	20	25	32		
Fluid			A	ir				
Proof pressure			1.05	MPa				
Maximum operating pressure			0.7	MPa				
Minimum operating pressure	0.12 MPa	0.06	MPa	(0.05 MPa	a		
Ambient and fluid temperature	Witho	ut auto s	witch: -1	10 to 70°C (No freezing				
Ambient and nata temperature	With auto switch: -10 to 60°C (No freezing)							
Lubrication			Non	-lube				
Piston speed			50 to 50	00 mm/s				
Cushion			Rubber	bumper				
Rod end thread			Male	thread				
Stroke length tolerance	+ 1.0 mm							

Symbol



Standard Stroke

Bore size (mm)	Standard stroke (mm)
6, 10, 16	40, 50, 60
20, 25, 32	60, 70, 80, 90, 100

Made to Order Specifications Click here for details

Symbol	Specifications
-XB6	Heat resistant (-10 to 150°C)
-XB7	Cold resistant (-40 to 70°C)
-XB9	Low speed (10 to 50 mm/s)
-XB13	Low speed (5 to 50 mm/s)
-XC19	Intermediate stroke (5 mm spacer)
-XC22	Fluororubber seals

weignt/():	Denotes th	e values wit	th D-A93.				(g)
Model				Stroke (mm))		
iviodei	40	50	60	70	80	90	100
C(D)U6-□D	43 (53)	49 (59)	55 (65)	_	_	_	_
C(D)U10-□D	64 (74)	72 (82)	80 (90)	_	_	_	_
C(D)U16-□D	92 (122)	104 (134)	116 (146)	_	_	_	_
C(D)U20-□D	_	_	216 (253)	238 (275)	260 (297)	282 (319)	304 (341)
C(D)U25-□D	_	_	363 (422)	397 (456)	431 (490)	465 (524)	499 (558)
C(D)U32-□D	_	_	526 (604)	574 (652)	622 (700)	670 (748)	718 (796)

^{*} For the auto switch weight, refer to page 1271.

Auto Switch Mounting Position

For the auto switch mounting position of CDU long stroke series, refer to page 732, since specifications are the same as standard type, double acting, single rod type.

Tightening Torque

Refer to page 728 for mounting a long stroke

Theoretical Output

Specifications are the same as CU series double acting, single rod. Refer to page 728.

Moisture **Control Tube IDK Series**


When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.




Construction


ø6



ø10



Ø16 to Ø32



Component Parts

No.	Description	Material	Note
1	Cylinder tube	Aluminum alloy	Hard anodized
2	Rod cover	Aluminum alloy	Hard anodized
3	Head cover	Brass	ø6 to ø10, Electroless nickel plated
3	ricua cover	Aluminum alloy	ø16 to ø32, Chromated
4	Piston	Brass	ø6
4	1 iston	Aluminum alloy	ø10 to ø32, Chromated
5	Piston rod	Stainless steel	
6	Bumper A	Urethane	
7	Bumper B	Urethane	

Replacement Parts: Seal Kit


Bore size (mm)	Kit no.	Contents
10	CU10D-PS	
16	CU16D-PS	
20	CU20D-PS	Set of nos. above (4, (5, (6.
25	CU25D-PS	
32	CU32D-PS	


- * Seal kit includes (4), (5), (6). Order the seal kit, based on each bore size.
- * Seal kit includes a grease pack (10 g).


Order with the following part number when only the grease pack is needed.

Grease pack part number: GR-S-010 (10 g)

With auto switch








Component Parts


00	ipononii i ai to		
No.	Description	Material	Note
8	Retaining ring	Carbon tool steel	Phosphate coated
9	Rod end nut	Carbon steel	Chromated
10	Magnet holder	Brass	ø6
11	Magnet	_	
12	Auto switch	_	
13	Piston gasket		
14*	Piston seal	NBR	
15*	Rod seal	INDIN	
16*	Gasket		

Dimensions: Double Acting, Single Rod


ø6, ø10



ø16 to ø32



Rod End Nut/Accessory



Material: Carbon stee										
Part no.	Applicable bore (mm)	d	Нι	В1	C ₁					
NTP-006	6	M3 x 0.5	1.8	5.5	6.4					
NTP-010	10	M4 x 0.7	2.4	7	8.1					
NTJ-015C	16	M5 x 0.8	4	8	9.2					
NT-015A	20	M6 x 1.0	5	10	11.5					
NT-02	25	M8 x 1.25	5	13	15.0					
NT-03	32	M10 x 1.25	6	17	19.6					

																	(mm)
Bore size (mm)	А	A'	В	С	D	E	GA	GB	н	J	к	L	мм	NN	Р	Q	QA
6	7	_	13	22	3	7	15	10	13	10	17	_	M3 x 0.5	M3 x 0.5 depth 5	3.2	_	
10	10	_	15	24	4	7	16.5	10	16	11	18	_	M4 x 0.7	M3 x 0.5 depth 5	3.2	_	_
16	11	12.5	20	32	6	7	16.5	11.5	16	14	25	5	M5 x 0.8	M4 x 0.7 depth 6	4.5	4	2
20	12	14	26	40	8	9	19	12.5	19	16	30	6	M6 x 1.0	M5 x 0.8 depth 8	5.5	9	4.5
25	15.5	18	32	50	10	10	21.5	13	23	20	38	8	M8 x 1.25	M5 x 0.8 depth 8	5.5	9	4.5
32 19.5 22 40 62		12	11	23	12.5	27	24	48	10	M10 x 1 25	M6 x 1.0 denth 9	6.6	13.5	4.5			

Bore size		-	Without a	uto switch	With auto switch		
(mm)	R	'	S	Z	S	Z	
6	7	6 depth 4.8	33	46	33	46	
10 9		6 depth 5	36	52	36	52	
16	12	7.6 depth 6.5	30	46	40	56	
20	16	9.3 depth 8	36	55	46	65	
25	20	9.3 depth 9	40	63	50	73	
32	24	11 denth 11 5	42	69	52	70	




Free Mount Cylinder: Long Stroke Type Non-rotating Rod, Double Acting, Single Rod

CUK Series

Ø6, Ø10, Ø16, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1271 to 1365 for further information on auto switches.

		Electrical	Hgi	Wiring	l	oad voltag	je	Auto switc	h model	Lead wire leng		ength	n (m)	Pre-wired		
Туре	Special function	entry	Indicator light	(Output)	DC		AC	Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	connector	Applica	ble load
				3-wire (NPN)	5 V. 12 V			M9NV	M9N	•	•	•	0	0	IC	
	_			3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit	
ی ہ				2-wire		12 V	ı	M9BV	M9B	•	•	•	0	0	_	
₽at	5			3-wire (NPN)		V 5 V, 12 V		M9NWV	M9NW	•	•	•	0	0	IC	Relay,
Solid state auto switch	Diagnostic indication (2-color indicator)	Grommet	Yes	3-wire (PNP)	24 V		_	M9PWV	M9PW	•	•	•	0	0	circuit	PLC
	(2-color indicator)			2-wire				M9BWV	M9BW	•	•	•	0	0	_	
s s	Water resistant			3-wire (NPN)		5 V, 12 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC]
	(2-color indicator)			3-wire (PNP)	5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit		
	(2-color indicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_	
Reed auto switch				3-wire	_	5 V	_	A96V	A96	•		•	_	_	IC	
s vi	_	Grommet	Yes	(NPN equivalent)						_		_			circuit	
و ي		Giominet		2-wire 24 V		12 V	100 V	A93V*2	A93	•	•	•	•	_		Relay,
au			No			12 0	100 V or less	A90V	A90	•	-	•	<u> </u>	_	IC circuit	PLC

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance.
- Consult with SMC regarding water resistant types with the above model numbers.
- *2 1 m type lead wire is only applicable to D-A93. * Lead wire length symbols: 0.5 m
 - 1 m M (Example) M9NWM
 - ···· L (Example) M9NWL


···· Nil (Example) M9NW

- ···· Z (Example) M9NWZ
- * Since there are applicable auto switches other than the above, refer to page 782 for details. * For detail about auto switches with pre-wired connector, refer to pages 1340 and 1341.
- * Auto switches are shipped together but not assembled.

* Solid state auto switches marked with "O" are produced upon receipt of order.

Free Mount Cylinder: Long Stroke Type Non-rotating Rod, Double Acting, Single Rod CUK Series






Note) No load: Rod at retracted



Symbol

Double acting, Single rod, Rubber bumper



Made to Order

Made to Order Specifications Click here for details

Symbol	Specifications
-XB6	Heat resistant (-10 to 150°C)
-XB7	Cold resistant (-40 to 70°C)
-XB9	Low speed (10 to 50 mm/s)
-XB13	Low speed (5 to 50 mm/s)
-XC19	Intermediate stroke (5 mm spacer)
-XC22	Fluororubber seals
-XC34	Non-rotating plate with workpiece mounting screw (No extended part on the rod end)

Standard Stroke

(mm)

Bore size (mm)	Standard stroke (mm)
6, 10, 16	40, 50, 60
20, 25, 32	60, 70, 80, 90, 100

Weight/(): Denotes the values with D-A93.

(g)

Model			(Stroke (mm)		
Wodel	40	50	60	70	80	90	100
C(D)UK6-□D	49 (59)	55 (65)	61 (71)	_	_	_	_
C(D)UK10-□D	71 (81)	79 (89)	87 (97)	_	_	_	_
C(D)UK16-□D	102 (132)	114 (144)	126 (156)	_	_	_	_
C(D)UK20-□D	_	_	243 (284)	267 (308)	291 (332)	315 (356)	339 (380)
C(D)UK25-□D	_	_	405 (460)	440 (495)	475 (530)	510 (565)	545 (600)
C(D)UK32-□D	_	_	617 (695)	669 (747)	721 (799)	773 (851)	825 (903)

^{*} For the auto switch weight, refer to page 1271.

Allowable Rotational Torque

Make sure that rotational torque is not applied to the piston rod of a long stroke type cylinder. If the rotation torque were applied unavoidably, refer to page 747 for details.

Tightening Torque

When mounting a CUK long stroke series, refer to page 728.

Theoretical Output

Specifications are the same as CU series double acting, single rod. Refer to page 728.

Auto Switch Mounting Position

For the auto switch mounting position of CDUK long stroke series, refer to page 732, since specifications are the same as standard type, double acting, single rod type.

Moisture Control Tube IDK Series


When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.


Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.




CUK Series

Construction







Component Parts

No.	Description	Material	Note
1	Cylinder tube	Aluminum alloy	Hard anodized
2	Rod cover	Aluminum alloy	Hard anodized
3	Head cover	Brass	ø6 to ø10, Electroless nickel plated
3	i ieau covei	Aluminum alloy	ø16 to ø32, Chromated
4	Piston	Brass	ø6
4	FISIOII	Aluminum alloy	ø10 to ø32, Chromated
5	Piston rod	Stainless steel	
6	Bumper A	Urethane	
7	Bumper B	Urethane	
8	Retaining ring	Carbon tool steel	Phosphate coated
9	Rod end nut	Carbon steel	Chromated
10	Magnet holder	Brass	ø6


Replacement Parts: Seal Kit


Bore size (mm)	Kit no.	Contents
10	CU10D-PS	
16	CU16D-PS	
20	CU20D-PS	Set of nos. above 19, 20, 21.
25	CU25D-PS	
32	CU32D-PS	


- * Seal kit includes (19, 20, 21). Order the seal kit, based on each bore size.
- * Seal kit includes a grease pack (10 g).

Order with the following part number when only the grease pack is needed. Grease pack part number: GR-S-010 (10 g)

With auto switch









Component Parts

	P					
No.	Description	Material	Note			
11	Magnet	_				
12	Auto switch	_				
13	Non-rotating plate	Aluminum alloy	Nickel plated			
14	Guide rod	Guide rod Stainless steel				
15	Bushing	ushing Bearing alloy				
16	Hexagon socket head cap screw	Carbon steel	Chromated			
17	Hexagon socket head set screw	Carbon steel	Chromated			
18	Piston gasket					
19	Piston seal	NBR				
20	Rod seal	INDH				
21	Gasket					

Free Mount Cylinder: Long Stroke Type Non-rotating Rod, Double Acting, Single Rod CUK Series

Dimensions: Non-rotating Rod Type; Double Acting, Single Rod





Roa Ena Ni	ut/Access	sory Mat	erial:	Carbo	n steel
Part no.	Applicable bore size (mm)	d	Hı	В1	C ₁
NTP-006	6	M3 x 0.5	1.8	5.5	6.4
NTP-010	10	M4 x 0.7	2.4	7	8.1
NTJ-015C	16	M5 x 0.8	4	8	9.2
NT-015A	20	M6 x 1.0	5	10	11.5
NT-02	25	M8 x 1.25	5	13	15.0
NT-03	32	M10 x 1.25	6	17	19.6

Bore size (mm)	А	A'	В	С	D	Е	F	FL	FK	FY	GA	GB	н	J	к	L	ММ
6	7	_	13	22	3	7	8	9	11	20.5	15	10	18	10	17	_	M3 x 0.5
10	10	_	15	24	4	7	8	12	12	22	16.5	10	21	11	18	-	M4 x 0.7
16	11	12.5	20	32	6	7	8	17	13	28	16.5	11.5	26	14	25	5	M5 x 0.8
20	12	14	26	40	8	9	8	20	16	33	19	12.5	29	16	30	6	M6 x 1.0
25	15.5	18	32	50	10	10	10	22	20	43.5	21.5	13	33	20	38	8	M8 x 1.25
32	19.5	22	40	62	12	11	12	29	24	51.5	23	12.5	42	24	48	10	M10 x 1.25

	Bore size	NN	Р	۵	QA	R	-	v	Without a	uto switch	With auto switch	
(mm)		ININ	-	l u	QA.	n		•	S	Z	S	Z
	6	M3 x 0.5 depth 5	3.2	_	_	7	6 depth 4.8	10.5	33	51	33	51
	10	M3 x 0.5 depth 5	3.2	_	_	9	6 depth 5	11.5	36	57	36	57
	16	M4 x 0.7 depth 6	4.5	4	2	12	7.6 depth 6.5	15.5	30	56	40	66
	20	M5 x 0.8 depth 8	5.5	9	4.5	16	9.3 depth 8	19.5	36	65	46	75
	25	M5 x 0.8 depth 8	5.5	9	4.5	20	9.3 depth 9	24.5	40	73	50	83
	32	M6 x 1.0 depth 9	6.6	13.5	4.5	24	11 depth 11.5	30.5	42	84	52	94

Free Mount Cylinder with Air Cushion

CU Series

New air cushion mechanism




Extended dimensions (compared to the standard CU models) are hardly noticeable.

• Overall length: +1.5 to 7 mm with air cushior


• Overall height: +0 to 2 mm 1
No air cushion protrusion.

· Overall width: not affected



(mm						
Bore	Extended dimensions					
size	Length	Height				
ø20	7	2				
ø25	1.5	0				
ø32	4	0				


Unique air cushion construction requires no cushion ring.



- 1) When the piston is retracting, air is exhausted through both A and A' until piston seal H passes air passage A.
- 2 After piston seal H has passed air passage A, air is exhausted only through A'. The section marked with slanted lines becomes a cushion chamber, and an air cushion effect is
- 3 When air is supplied for the piston extension, the check valve opens and the piston extends with no delay.

Free mounting


3 types of mounting orientations can be accommodated depending on the installation conditions.



Approximately 2.4 times of allowable kinetic energy

(Compared to the old CU series with rubber bumper)

Improved allowable kinetic energy absorption.



Improved repeatability


When compared to rubber bumper type actuators, air cushion type cylinders are less likely to be affected by pressure fluctuations, and therefore better able to achieve a stable and smooth stroke.

Improved sound insulation (Reduced impact noise at the stroke end)


 Noise reduction of more than 11 dB is possible (compared to the CU20 series with rubber bumper).

Interchangeable mounting

Mounting dimensions (J, K, R, and E) are the same as the rubber bumper type CU series.




Size Variations





Free Mount Cylinder with Air Cushion **CU** Series ø20, ø25, ø32

How to Order



Applicable Auto Switches/Refer to pages 1271 to 1403 for further information on auto switches

	Applicable Auto Switches/Heier to pages 1271 to 1403 for further information on auto switches.																			
		Et a state and	ig.) A (Wiring (Output) DC Ad		ge	Auto switch model			wire I	ength	(m)							
Туре	Special function	Electrical entry	Indicator light				DC AC		In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	connector	Applica	ble load				
				3-wire (NPN)		5 V. 12 V		M9NV	M9N	•	•	•	0	0	IC					
	_			3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit					
ے ہ				2-wire		12 V		M9BV	M9B	•	•	•	0	0	_					
d state switch	6			3-wire (NPN)		51/ 401/	5 1/ 40 1/	5 V 40 V	5 V. 12 V	5 1/ 40 1/		M9NWV	M9NW	•	•	•	0	0	IC	Dalau
s b	Diagnostic indication	Grommet	Yes	3-wire (PNP)	24 V	24 V 5 V, 12 V	v, 12 v —	M9PWV	M9PW	•	•	•	0	0	circuit	Relay,				
Solid auto s	(2-color indicator)			2-wire					12 V		M9BWV	M9BW	•	•	•	0	0	_	PLC	
S H	10/-4			3-wire (NPN)		5 V, 12 V	5 V 40 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC	1			
	Water resistant (2-color indicator)			3-wire (PNP)				M9PAV*1	M9PA*1	0	0	•	0	0	circuit					
	(2-color indicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_					
Reed auto switch		Crommet	Yes	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	_	•	_	_	IC circuit	_				
Re	_	Grommet		2-wire	24.1/	2414	100 V	A93V*2	A93	•	•	•	•	_	_	Relay,				
ant			No	Z-WIFE	24 V	24 V 12 V	100 V or less	A90V	A90	•	_	•	_	_	IC circuit	PLC				

* Solid state auto switches marked with "O" are produced upon receipt of order.

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance.
- Consult with SMC regarding water resistant types with the above model numbers. *2 1 m type lead wire is only applicable to D-A93.
- * Lead wire length symbols: 0.5 m Nil (Example) M9NW ···· M (Example) M9NWM 1 m
 - ··· L (Example) M9NWL 5 m Z (Example) M9NWZ
- * Since there are applicable auto switches other than the above, refer to page 782 for details.
- * For detail about auto switches with pre-wired connector, refer to pages 1340 and 1341.
- * Auto switches are shipped together but not assembled.





Specifications

Type	Pneumatic (Non-lube)		
Fluid	Air		
Proof pressure	1.0 MPa		
Maximum operating pressure	0.7 MPa		
Minimum operating pressure	0.08 MPa		
Ambient and fluid temperature	Without auto switch: -10°C to 70°C (No freezing)		
Ambient and naid temperature	With auto switch: -10°C to 60°C (No freezing)		
Rod end thread	Male thread		
Stroke length tolerance	+ 1.0 0		
Piston speed	50 to 500 mm/s		

Effective Cushion Length

Bore size (mm)	20	25	32
Effective cushion length (mm)	6.6	6.7	7.7

Standard Stroke

Bore size (mm)	Standard stroke (mm)
20, 25, 32	20, 30, 40, 50, 60, 70, 80, 90, 100

^{*} Intermediate strokes are also available upon receipt of order. Please contact SMC. Minimum stroke length is 20 mm.

Tightening Torque/ When mounting the CU series rightening Torque/ refer to the table below.

Bore size (mm)	Hexagon socket head cap screw size	Proper tightening torque (N·m)		
20, 25 M5		5.10 ±10%		
32	M6	8.04 ±10%		

Allowable Kinetic Energy

Refer to "Selection" on page 776 regarding allowable kinetic energy.

Theoretical Output

		- оит	•	- IN
Į				J

(N)

(g)

Operating	Operating pressure (MPa)				
direction	0.3	0.5	0.7		
OUT	94.2	157	220		
IN	79.2	132	185		
OUT	147	246	344		
IN	124	206	288		
OUT	241	402	563		
IN	207	346	454		
	direction OUT IN OUT IN OUT OUT OUT	OUT 94.2 IN 79.2 OUT 147 IN 124 OUT 241	Out Out Out		

Weight

Basic Weight

ore size	Standard stroke (mm)									
(mm)	20	30	40	50	60	70	80	90	100	
20	186	208	230	252	274	296	318	340	362	
25	289	323	357	391	425	459	493	527	561	
32	464	512	560	608	656	704	752	800	848	

Moisture **Control Tube IDK Series**

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.


Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.

Additional Weight	(
Bore size (mm)	Magnet
20	5
25	6
20	



CU Series

Construction



Component Parts

No.	Description	Material	No. of pcs.	Note
1	Cylinder tube	Aluminum alloy	1	Hard anodized
2	Rod cover	Aluminum alloy	1	Hard anodized
3	Head cover	Aluminum alloy	1	Chromated
4	Piston	Aluminum alloy	1	Chromated
5	Piston rod	Stainless steel	1	
6	Retaining ring	Carbon tool steel	1	Phosphate coated
7	Rod end nut	Carbon steel	1	Chromated
8	Cushion needle assembly	_	(2)	
9	Steel ball	Carbon steel	2	
10	Magnet	_	1	
11	Auto switch	_	(2)	
12	Piston gasket	NBR	1	
13	Piston seal	NBR	2	
14	Rod seal	NBR	1	
15	Gasket	NBR	1	


Replacement Parts: Seal Kit


Bore size (mm)	Kit no.	Contents
ø 20	CU20A-PS	
ø 25	CU25A-PS	Set of nos. above
ø 32	CU32A-PS	19, 19, 19.

- * Seal kit includes ①, ①, ⑤. Order the seal kit, based on each bore size.
- Seal kit includes a grease pack (10 g).
 Order with the following part number when only the grease pack is needed.

Grease pack part number: GR-S-010 (10 g)







(mm)

Bore size (mm)	Port size	Α	A'	В	С	CA	СВ	D	E	GA	GB	н	J	JA
20	M5 x 0.8	12	14	26	42	20	22	8	9	29	27	19	16	12
25	M5 x 0.8	15.5	18	32	50	25	25	10	10	32.5	22.5	23	20	15
32	1/8	19.5	22	40	62	31	31	12	11	35	25	27	24	19

Bore size (mm)	к	KA	L	ММ	NN	Р	Q	R	т	s	z	Standard stroke
20	30	5	6	M6 x 1.0	M5 x 0.8 depth 8	5.5	13	16	9.3 depth 8	53	72	00 00 40 50 00
25	38	6	8	M8 x 1.25	M5 x 0.8 depth 8	5.5	23.5	20	9.3 depth 9	51.5	74.5	20, 30, 40, 50, 60,
32	48	7	10	M10 x 1.25	M6 x 1.0 depth 9	6.6	29	24	11 depth 11.5	56	83	70, 80, 90, 100

Rod End Nut/Accessory






	Material: Carbon ste									
Part no.	Applicable bore size (mm)	d	Ηı	Вı	C ₁					
NT-015A	20	M6 x 1.0	5	10	11.5					
NT-02	25	M8 x 1.25	5	13	15.0					
NT-03	32	M10 x 1.25	6	17	19.6					


SMC

CU Series Auto Switch Mounting

Proper Auto Switch Mounting Position (Detection at stroke end) and Its Mounting Height



(): Denotes the values of D-A96.



(): Denotes the values of D-M9 V, D-M9 WV.

																(mm)
Bore size D-A9□, D-A9□V				D-M9□, D-M9□W			D-M9□V, D-M9□WV			D-M9□A			D-M9□AV			
	(mm)	Α	В	W	Α	В	W	Α	В	w	Α	В	W	Α	В	W
	20	18	15	13 (10.5)	22	19	9	22	19	11	22	19	11	22	19	13
	25	20	11	9 (6.5)	24.5	15	5	24.5	15	7	24.5	15	7	24.5	15	9
	32	22.5	13.5	11.5 (9)	26.5	17.5	7.5	26.5	17.5	9.5	26.5	17.5	9.5	26.5	17.5	11.5

Note 1) Figures in the table above are used as a reference when mounting the auto switches for stroke end detection.

Operating Range

			(mm)
Switch model	В	ore size (mn	1)
Switch model	20	25	32
D-A9□, A9□V	11	12.5	14
D-M9□, M9□V D-M9□W, M9□WV D-M9□A, M9□AV	7	7	7.5


Since the operating range is provided as a guideline including hysteresis, it cannot be guaranteed (assuming approximately ±30% dispersion).

It may vary substantially depending on an ambient environment.



In the case of actually setting the auto switches, adjust them after confirming their operation. Note 2) Values in () are dimensions for D-A90 and A93 type.

Auto Switch Rail Position



		(mm)
Bore size (mm)	Α	В
20	21	23
25	27	25
32	35	27


Caution on Proximity Installation

When free mounting cylinders equipped with auto switches are used, the auto switches could activate unintentionally if the installed distance is less than the dimensions shown in the table. Therefore, make sure to provide a greater clearance. Due to unavoidable circumstances, if they must be used with less distance than the dimensions given in the table, the cylinders must be shielded. Therefore, affix a steel plate or a magnetic shielding plate (MU-SO25) to the area on the cylinder that corresponds to the adjacent auto switch. (Please contact SMC for details.) Auto switches may malfunction if a shielding plate is not used.

Dimensions of shielding plate (MU-S025) that is sold separately are indicated as reference.



Material: Ferrite stainless steel, Thickness: 0.3 mm The product can be attached to the cylinder since the bottom side is a seal type.



Bore size (mm)	Mounting pitch L (mm)
20	40
25	46
32	56



CU Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 20 for safety instructions and pages 21 to 30 for actuator and auto switch precautions.

Installation and Removal of Retaining Rings

⚠Caution

- Use appropriate pliers (Type C retaining ring installing tool) for installation and removal of retaining rings.
- 2. Even when using appropriate pliers (Type C retaining ring installing tool), proceed with caution as there is a danger of the retaining ring flying off the end of the pliers (tool) and causing bodily injury or damage to nearby equipment. After installation, make sure that the retaining ring is securely seated into the retaining ring groove before supplying air.

Mounting

⚠Caution

1. Refer to the below table for mounting cylinders.

Tightening Torque

Bore sizes (mm)	Hexagon socket head cap screw (mm)	Proper tightening torque (N0m)
20, 25	M5	5.10 ±10%
32	M6	8.04 ±10%

Selection


△Caution

1. Operate the cylinder to the stroke end.

When the stroke is restricted by an external stopper or a clamped workpiece, sufficient cushioning and noise reduction may not be achieved.

Strictly observe the limiting ranges for load mass and maximum speed (Graph (1)). Also, the limiting ranges provided here are based on the condition that the cylinder is operated to the stroke end with a proper cushion needle adjustment.

If operated beyond the limiting ranges, excessive impact will occur and this may cause damage to equipment.



Selection

∧ Caution

Adjust the cushion needle to reduce excessive kinetic energy from the piston impact at the stroke end by allowing it to absorb sufficient kinetic energy during the cushion stroke.

If due to improper adjustment, the piston impacts the stroke end with excessive kinetic energy (values above those given in Table (1)), an excessive impact will occur and this may cause damages to equipment.

(.1)


Table (1) Allowable Kinetic Energy at Piston Impact

		, ш. г. гологи ппърс	(0)					
	20	20 25 32						
Piston speed	50 to 500 mm/s							
Allowable kinetic energy	0.055	0.09	0.15					

 Strictly observe the limiting ranges for the piston rod lateral load (Graph (2)).

If operated beyond the limiting ranges, equipment life may be reduced or damage to equipment may occur.

Piston Rod Lateral Load (Graph (2))



Cushion Needle Adjustment

∕∖∖Caution

 Keep the adjustment range for the cushion needle between the fully closed position and the rotations shown below.

	Rotations
ø20 to ø32	2.5 rotations or less

Use a 3 mm flat head watchmakers' screwdriver to adjust the cushion needle. The adjustment range for the cushion needle must be between the fully closed position and the open position ranges indicated in the above table. A retaining mechanism prevents the cushion needle from slipping out; however, it may spring out during operation if it is rotated beyond the ranges shown above.

Free Mount Cylinder for Vacuum

ZCUK Series


A free mount cylinder with a vacuum passage in the rod to meet the requirements for (Air cylinder) + (Vacuum pad).

A vacuum passage has been provided in the rod of the CUK cylinder to enable a vacuum pad to be installed on the end of the rod.




Not necessary to provide vacuum tubing space at the end of the rod.

The area around the vacuum pad is uncluttered.




Free Mount Cylinder for Vacuum ZCUK Series

How to Order




74	nicable Auto 3	WILCIICS	7 / N t	elel to pages 127 i	10 1303	ioi the u	ietalieu sp	ecilications	on auto si	VILCITE	:5.					
			턆		L	oad volta	ge	Auto swite	Lead	wire I	ength	n (m)	Di			
Туре	Special function	Electrical entry	Indicator	Wiring (Output)	D	С	AC	Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	Pre-wired connector	Applical	ole load
_				3-wire (NPN)	3-wire (NPN) 3-wire (PNP) 2-wire 3-wire (NPN) 3-wire (PNP) 2-wire 24 V 5 V, 12 V 5 V, 12 V 12 V	5 V 40 V		M9NV	M9N	•	•	•	0	0	IC	
switch	_			3-wire (PNP)			M9PV	M9P	•	•	•	0	0	circuit		
S				2-wire		12 V	1	M9BV	M9B	•	•	•	0	0	_	
anto	D:		١.	3-wire (NPN)			1	M9NWV	M9NW	•	•	•	0	0	IC	Relay,
	Diagnostic indication (2-color indicator)	Grommet	Ş	3-wire (PNP)			_	M9PWV	M9PW	•	•	•	0	0		PLC
state	(2-color indicator)		ľ	2-wire			1	M9BWV	M9BW	•	•	•		0	_	1 20
S				3-wire (NPN)		5V.12V	1	M9NAV*1	M9NA*1	0	0	•	0	0	IC	
Solid	Water resistant (2-color indicator)			3-wire (PNP)		50,120		M9PAV*1	M9PA*1	0		•		0	circuit	
	(2-color indicator)			2-wire		12V		M9BAV*1	M9BA*1	0	0	•	0	0		
Reed auto switch		Grommet	,es	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	_	•	_	_	IC circuit	_
2 S		Gronninet	Ĺ	2-wire	24 V	12 V	100 V	A93V*2	A93	•	•	•	•	1		Relay,
ani			No	∠-wire	24 V	12 V	100 V or less	A90V	A90	•		•	I —		IC circuit	PLC

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot quarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
- *2 1 m type lead wire is only applicable to D-A93 (Example) M9NW * Lead wire length symbols: 0.5 m Nil
 - * Solid state auto switches 1 m----- M (Example) M9NWM marked with "O" are produced upon receipt of order.
- * Refer to pages 1340 and 1341 for the details on auto switches with a
 - pre-wired connector



Free Mount Cylinder for Vacuum **ZCUK** Series



Specifications

Bore size (mm)	ø10	ø16	ø 20	ø 25	ø 32				
Fluid			Air						
Proof pressure		1.05 MPa							
Maximum operating pressure			0.7 MPa						
Minimum operating pressure	0.13	0.13 MPa 0.11 MPa							
Vacuum port pressure	-101 kPa to 0.6 MPa (At vacuum release 0 to 0.6 MPa) Note)								
Ambient and fluid temperature		Without auto switch: -10 to +70°C (No freezing) With auto switch: -10 to +60°C (No freezing)							
Lubrication		١	Not require	d					
Piston speed		50	to 500 mr	n/s					
Cushion		Rubber b	umper on	both sides					
Stroke allowance			+1.0						
Rod tip screw	Wit	With or without (Pad direct mounting)							
Mounting			Basic type)					
Applicable pad		Refer to p	page 780 f	or details.					

Note) For a cap type, supply pressure only when vacuum is released. That pressure should be less than the cylinder pressure.

Non-rotating Rod Accuracy

(No load/At retraction of the rod at the locking plate side)

(· · · · · · · · · · · · · · · · · · ·									
Bore size (mm)	ø 10	ø 16	ø 20	ø 25	ø 32				
Non-rotating rod accuracy	±0.	8°		±0.5°					

⚠ Precautions

- Be sure to read this before handling the products.
- Refer to page 20 for safety instructions and pages 21 to 30 for
 - actuator and auto switch precautions.

 Do not place your finger in the clearance between the detent plate and the cylinder tube. Never put your finger between the non-rotating plate and cylinder tube. Your finger may be pinched when the piston rod retracts. If your finger is caught, it could injure your finger

because the cylinder outputs a considerable amount of force.

2. Make sure that rotational torque is not applied to the piston rod. If this is unavoidable, operate the cylinder within the allowable rotational torque listed in the table below

Allowable Rotational Torque

Bore size (mm)					
Allowable rotational torque (N-m)	0.02	0.04	0.10	0.15	0.20

- 3. To secure a workpiece to the end of the piston rod, tighten the workpiece onto the piston rod with the piston rod fully retracted so that torque is not applied to the piston rod.
- 4. To install a cylinder, tighten it within the torque values indicated in the table below.

Proper Tightening Torque

Bore size (mm)	Hexagon socket head bolt diameter (mm)	Proper tightening torque (N·m)
ø10	M3	1.08 ± 10%
ø 16	M4	2.45 ± 10%
ø20, ø25	M5	5.10 ± 10%
ø 32	M6	8.04 ± 10%

Moisture **Control Tube IDK Series**

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions. Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.



ZCUK Series


Standard Stroke

Applicable cylinder		Double acting type/Single rod type/Non-rotating rod							
Stroke (mm)		Stroke (mm)							
Bore size (mm)	5	10	15	20	25	30	40	50	
10	•	•	•	•	•	•	_	_	
16	•	•	•	•	•	•	_	_	
20	•	•	•	•	•	•	•	•	
25	•	•	•	•	•	•	•	•	
32	•	•	•	•	•	•	•	•	

Theoretical Output/Double Acting Type

Unit:								
Bore size	Rod dia.	Piston area	Operating pressure (MPa)					
(mm)	(mm)	(mm²)	0.3	0.5	0.7			
10	4	66.0	19.8	33	46.2			
16	6	172	51.6	86	121			
20	8	264	79.2	132	185			
25	10	412	124	206	289			
32	12	691	207	346	484			

Mounting



Minimum Stroke for Mounting Auto Switch

	Applicable auto switch						
Number of auto switches	D-A9□, D-A9□V	D-M9□, D-M9□V	D-M9□W, D-M9□WV				
1 pc.	5	5	5				
2 pcs.	10	5	10				

Cylinder/Applicable Pad

• In the case of rod end male thread

Use ZPT series pad (perpendicular vacuum entry/female thread mounting).

Cylinde	er	Pad (ZPT02 to 50□□-B4 to 10)												
Model	Bore size					Ro	d dia	a. (n	nm)					Thread
Wodei	(mm)	2	4	6	8	10	13	16	20	25	32	40	50	dia.
ZCUKC	10	•	•	•	•	_	_	_	_	_	_	_	_	M4 x 0.7
ZCUKQ	16	•	•	•	•	•	•	•	-	-	_	_	_	M5 x 0.8
ZCDUKC	20	_	_	_	_	•	•	•	•	•	lacksquare	_	_	M6 x 1.0
ZCDUKQ	25	_	_	_	_	_	_	_	•	•	•	•	•	M8 x 1.25
	32	_	_	_	_	_	_	_	•	•	•	•	•	M10 x 1.25


• In the case of pad direct mounting

Use ZP series pad (single unit).

Cylinder		Pad (ZP02 to 50□□)											
Model	Bore size		Rod dia. (mm)										
iviouei		2	4	6	8	10	13	16	20	25	32	40	50
	10 Note 1)	•	•	•	•	_	_	_	_	_	_	_	_
ZCUKD	16	•	•	•	•	_	_	_	_	_	_	_	_
ZCDUKH	20	_	_	_	_	•	•	•	_	_	_	_	_
ZCDUKR	25	<u> </u>	_	_	_	_	_	_	•	•	•	_	_
	32	_	_	_	_	_	_	_	_	_	_	•	•

Note) When using "ZC(D)UK_R^U10", use ZP02 to 08U□-X11. Pad shape is flat only.

Auto Switch Groove



Bore size	Α	В
10	10.3	13
16	15	18
20	21	23
25	27	25
32	35	27

Construction


Cap piping/Male thread: ZC(D)UKC


ø10



Pad direct mounting In the case of

ZC(D)UKD







ø16 to ø32









With auto switch

Component Parts

No.	Description	Material	Note
1	Cylinder tubing	Aluminum alloy	Hard anodized
2	Rod cover B	Aluminum alloy	Chromated
3	Сар	Aluminum alloy	Anodized
4	Piston	Aluminum alloy	Chromated
5	Piston rod	Stainless steel	
6	Bush	Bearing alloy	
7	Plate	Aluminum alloy	Nickel plated
8	Guide rod	Stainless steel	
9	Bush	Bearing alloy	
10	Hexagon socket head cap screw	Carbon steel	Chromated
11	Hexagon socket set screw	Carbon steel	Chromated
12	Hexagon socket head cap screw	Carbon steel	Nickel plated

Component Parts

Component Parts										
No.	Description	Material	Note							
13	Bumper	Urethane								
14	Magnet	_								
15	Auto switch	_								
16	Rod end nut	Carbon steel	Chromated							
17	Piston gasket	NBR								
18*	Piston seal									
19*	Rod seal	NBR								
20*	Gasket	INDIN								
21*	Gasket for cap									
22	Seal washer	Rolled steel/NBR								

Replacement Parts: Seal Kit

- wh hihi	. 9				
			Bore size / Part no.		
Kit no.	ø10	ø16	ø20	ø25	ø32
	ZCU10-PS	ZCU16-PS	ZCU20-PS	ZCU25-PS	ZCU32-PS

^{*} Seal kit includes (8, (9, 20 and 2). Order the seal kit based on each bore size.

Grease pack part no.: GR-S-010 (10 g)

^{*} Seal kit includes a grease pack (10 g).


Order with the following part number when only the grease pack is needed.





Construction

Rod piping-Male thread: ZC(D)UKQ


ø10







ø16 to ø32



Component Parts

No.	Description	Material	Note
1	Cylinder tubing	Aluminum alloy	Hard anodized
2	Rod cover B	Aluminum alloy	Chromated
3	Rod cover retainer plate	Aluminum alloy	Anodized
4	Piston	Aluminum alloy	Chromated
5	Piston rod	Stainless steel	
6	Bush	Bearing alloy	
7	Plate	Aluminum alloy	Nickel plated
8	Guide rod	Stainless steel	
9	Bush	Bearing alloy	
10	Hexagon socket head cap screw	Carbon steel	Chromated
11	Hexagon socket set screw	Carbon steel	Chromated
12	Hexagon socket head cap screw	Carbon steel	Nickel plated

Component Parts

No.	Description	Material	Note
13	Bumper	Urethane	
14	Magnet	_	
15	Auto switch	_	
16	Rod end nut	Carbon steel	Chromated
17	Piston gasket	NBR	
18	Socket	Carbon steel	ø16 only
19	Gasket		ø16 only
20*	Piston seal	NBR	
21*	Rod seal	INDIN	
22*	Gasket		
23	Seal washer	Rolled steel/NBR	

Replacement Parts: Seal Kit Rod piping

	•				
			Bore size / Part no.		
Kit no.	ø10	ø16	ø20	ø25	ø32
	CUW10D-PS	CUW16D-PS	CUW20D-PS	CUW25D-PS	CUW32D-PS

 $[\]ast$ Seal kit includes 20, 21 and 22. Order the seal kit based on each bore size.


^{*} Seal kit includes a grease pack (10 g).

Order with the following part number when only the grease pack is needed.

Grease pack part no.: GR-S-010 (10 g)

Vacuum Piping: Cap Piping/Rod End Shape: Male Thread ZC(D)UKC Cylinder bore - Stroke D

2 x ø3.2 through ø10 Seal washer Port size 2 x M5 x 0.8 0 7 30 + Stroke 16.5 Vacuum port size M4×0.7 12 M5×0.8 2 x ø3.2 through 4 x ø6 depth 5 counterbore 10 12 36 + Stroke 20 + Stroke 21 15 77 + 2 x Stroke



Model	Port	size	Stroke range	_	Α.	ь	_	ød	øD	_	_	FK	FI	FV	GA	GC
Model	Air port	Vacuum port	(mm)	_ ^	^	P	١.	υu	שט	_	_ F	FK	LL	[[GA	GC
ZC(D)UKC16	M5 x 0.8	M5 x 0.8	5 to 30	11	12.5	20	32	2	6	7	8	13	17	28	16.5 Note 1)	31
ZC(D)UKC20	M5 x 0.8	1/8	5 to 50	12	14	26	40	3	8	9	8	16	20	33	19	33.5
ZC(D)UKC25	M5 x 0.8	1/8	5 to 50	15.5	18	32	50	4	10	10	10	20	22	43.5	21.5	34
ZC(D)UKC32	1/8	1/8	5 to 50	19.5	22	40	62	5	12	11	12	24	29	51.5	23	34.5

Model	Н	J	L	ММ	øP	Q	QA	R	s	SA	øΤ	Υ	z
ZC(D)UKC16	26	14	5	M5 x 0.8	4.5	4	2	12	30 (40)	19.5	7.6 depth 6.5	15.5	75.5 (85.5)
ZC(D)UKC20	29	16	6	M6 x 1.0	5.5	9	4.5	16	36 (46)	21	9.3 depth 8	19.5	86 (96)
ZC(D)UKC25	33	20	8	M8 x 1.25	5.5	9	4.5	20	40 (50)	21	9.3 depth 9	24.5	94 (104)
ZC(D)UKC32	42	24	10	M10 x 1.25	6.6	13.5	4.5	24	42 (52)	22	11 depth 11.5	30.5	106 (116)

^{():} In the case of a mounted auto switch.

Note 1) In the case of ZCUKC16-5D: 14.5 mm.

ZCUK Series

Vacuum Piping: Cap Piping/Rod End Shape: Pad Direct Mounting ZC(D)UKD Cylinder bore - Stroke D

ø10 2 x ø3.2 through Port size Pad for ZCUKD10 (ZP02 to 08U*-X11) 2 x M5 x 0.8 Φ 30 + Stroke 7 16.5 Vacuum port size M5×0.8 12 2 x ø3.2 through 8 4 x ø6 depth 5 counterbore 15 36 + Stroke 20 + Stroke 77 + 2 x (Stroke) ø16 to ø32 2 x M5 x 0.8 (ø32: 1/8) 2 x øP through ð. Use ZP series pad. GC + Stroke Vacuum port size

Model	Port	size	Stroke range	øΑ	Λ,	В	_	ød	øD	_	_	EK	EI	FY	GA	GC
Wodel	Air port	Vacuum port	(mm)	WA.	^		"	_{bu}	00	_		FK			GA	ac
ZC(D)UKD16	M5 x 0.8	M5 x 0.8	5 to 30	5	7	20	32	2	6	7	8	13	17	28	16.5 Note 1)	31
ZC(D)UKD20	M5 x 0.8	1/8	5 to 50	6.6	8	26	40	3	8	9	8	16	20	33	19	33.5
ZC(D)UKD25	M5 x 0.8	1/8	5 to 50	8	9	32	50	4	10	10	10	20	22	43.5	21.5	34
ZC(D)UKD32	1/8	1/8	5 to 50	11.5	10.5	40	62	5	12	11	12	24	29	51.5	23	34.5

2 x øP through 4 x øT counterbore S + Stroke

Z + 2 x Stroke


SA + Stroke


Model	Н	J	L	øΡ	Q	QA	R	s	SA	øΤ	w	Y	z
ZC(D)UKD16	26	14	5	4.5	4	2	12	30 (40)	19.5	7.6 depth 6.5	3.5	15.5	75.5 (85.5)
ZC(D)UKD20	29	16	6	5.5	9	4.5	16	36 (46)	21	9.3 depth 8	5	19.5	86 (96)
ZC(D)UKD25	33	20	8	5.5	9	4.5	20	40 (50)	21	9.3 depth 9	5	24.5	94 (104)
ZC(D)UKD32	42	24	10	6.6	13.5	4.5	24	42 (52)	22	11 depth 11.5	5	30.5	106 (116)

^{():} In the case of a mounted auto switch.

Note 1) In the case of ZCUKD16-5D: 14.5 mm.

Vacuum Piping: Rod Piping/Rod End Shape: Male Thread ZC(D)UKQ Cylinder bore - Stroke D





Model	Port	size	Stroke range	Δ	Δ,	В	_	ød	øD	F	F	FK	FI	FV	GA	GC
Wiodei	Air port	Vacuum port	(mm)	^	^		"	»u	80	_	٠.	· · · ·			<u>سم</u>	ao
ZC(D)UKQ16	M5 x 0.8	M5 x 0.8 Note 2)	5 to 30	11	12.5	20	32	2	6	7	8	13	17	28	16.5 Note 1)	19
ZC(D)UKQ20	M5 x 0.8	M5 x 0.8	5 to 50	12	14	26	40	3	8	9	8	16	20	33	19	21.5
ZC(D)UKQ25	M5 x 0.8	M5 x 0.8	5 to 50	15.5	18	32	50	4	10	10	10	20	22	43.5	21.5	22
ZC(D)UKQ32	1/8	1/8	5 to 50	19.5	22	40	62	5	12	11	12	24	29	51.5	23	22.5

Model	н	НА	J	L	ММ	øΡ	Q	QA	R	s	SA	øΤ	Y	z
ZC(D)UKQ16	26	5	14	5	M5 x 0.8	4.5	4	2	12	30 (40)	7.5	7.6 depth 6.5	15.5	68.5 (78.5)
ZC(D)UKQ20	29	5	16	6	M6 x 1.0	5.5	9	4.5	16	36 (46)	9	9.3 depth 8	19.5	79 (89)
ZC(D)UKQ25	33	5	20	8	M8 x 1.25	5.5	9	4.5	20	40 (50)	9	9.3 depth 9	24.5	87 (97)
ZC(D)UKQ32	42	5	24	10	M10 x 1.25	6.6	13.5	4.5	24	42 (52)	10	11 depth 11.5	30.5	99 (109)

^{():} In the case of a mounted auto switch.


Note 1) In the case of ZCUKQ16-5D: 14.5 mm.


Note 2) In the case of socket equipped type.





Vacuum Piping: Rod Piping/Rod End Shape: Pad Direct Mounting ZC(D)UKR Cylinder bore - Stroke D





Model	Port	size	Stroke range	øΑ		В	_		~_	_	_	FK	EI	EV	GA	GC
Wodel	Air port	Vacuum port	(mm)	ØA	Α .	В.	٠.	ød	ø D	_	-	FK	FL	- 1	GA	GC
ZC(D)UKR16	M5 x 0.8	M5 x 0.8 Note 2)	5 to 30	5	7	20	32	2	6	7	8	13	17	28	16.5 Note 1)	19
ZC(D)UKR20	M5 x 0.8	M5 x 0.8	5 to 50	6.6	8	26	40	3	8	9	8	16	20	33	19	21.5
ZC(D)UKR25	M5 x 0.8	M5 x 0.8	5 to 50	8	9	32	50	4	10	10	10	20	22	43.5	21.5	22
ZC(D)UKR32	1/8	1/8	5 to 50	11.5	10.5	40	62	5	12	11	12	24	29	51.5	23	22.5

Model	н	НА	J	L	øΡ	Q	QA	R	s	SA	øΤ	w	Υ	z
ZC(D)UKR16	26	5	14	5	4.5	4	2	12	30 (40)	7.5	7.6 depth 6.5	3.5	15.5	68.5 (78.5)
ZC(D)UKR20	29	5	16	6	5.5	9	4.5	16	36 (46)	9	9.3 depth 8	5	19.5	79 (89)
ZC(D)UKR25	33	5	20	8	5.5	9	4.5	20	40 (50)	9	9.3 depth 9	5	24.5	87 (97)
ZC(D)UKR32	42	5	24	10	6.6	13.5	4.5	24	42 (52)	10	11 depth 11.5	5	30.5	99 (109)


^{():} In the case of a mounted auto switch.


Note 1) In the case of ZCUKQ16-5D: 14.5 mm.

Note 2) In the case of socket equipped type.

Dimensions of Pad Mounted Model


Rod end shape: Male thread






																						•						
Model				FI	at/FI	at w	ith ri	bs							De	ер						Bel	lows					Applicable
Model	Dia.(mm)	2	4	6	8	10	13	16	20	25	32	40	50	10	16	25	40	6	8	10	13	16	20	25	32	40	50	pad model
7C(D)UKC10	øDQ	2.6	4.8	7	9	_	_	_	_	_	_	_	_	_	_	_	_	7	9	_	_	_	_	_	_	_	-	
ZC(D)UKC10 ZC(D)UKQ10	HQ	19.5	19. 5	19. 5	19. 5	_	_	_	_	_	_	_	_	_	_	<u> </u>	_	20. 5	20. 5	_	_	_	_	<u> </u>	_	_	-	ZPT□□□-B4
2C(D)UKQ10	HP	36. 5	36. 5	36. 5	36. 5	_	_	_	_	_	_	_	_	_	_	_	_	37. 5	37. 5	_	_	_	_	_	_	_	_	
ZC(D)UKC16	øDQ	2.6	4.8	7	9	12	15	18	_	_	_	_	_	12	18	_	_	7	9	12	15	18	_	_	_	_	_	
ZC(D)UKQ16	HQ	19. 5	19.5	19. 5	19. 5	21	21	21.5	_	_	_	_	_	24	25	—	_	20. 5	20. 5	25	27. 5	29	_	<u> </u>	_	_	-	ZPT□□□-B5
ZC(D)ORG10	HP	41.5	41.5	41.5	41.5	44	42	42. 5	_	_	_	_	 —	45	46	 —	_	42. 5	42. 5	46	48. 5	50	_	 —	—	_	-	
ZC(D)UKC20	øDQ	_	_	_	_	12	15	18	23	28	35	_	_	12	18	28	_	_	_	12	15	18	22	27	34	_	-	
ZC(D)UKQ20	HQ	_	_	_	-	21	21	21. 5	23	23	23. 5	_	_	24	25	29	_	_	 —	25	27. 5	29	32. 5	33	38	_	-	ZPT□□□-B6
20(0)01(020	HP	 -	_	I —	 -	44	44	44. 5	46	46	46. 5	_	—	47	48	52	_	—	—	48	50. 5	52	55. 5	56	61	_	-	
ZC(D)UKC25	øDQ	_	_	<u> </u>	_	_	_	_	23	28	35	43	53	_	_	28	43	_	_	_	_	_	22	27	34	43	53	
ZC(D)UKQ25	HQ	_	_	_	-	_	_	_	29	29	29. 5	32	33	_	_	35	42. 5	_	-	_	_	_	38. 5	39	44	47. 5	51. 5	ZPT□□□-B8
20(b)0KQ23	HP	_	_	_	-	-	_	_	54	54	54. 5	57	58	_	_	60	67. 5	_	 —	_	_	_	63. 5	64	69	72. 5	76. 5	
ZC(D)UKC32	ø DQ	_	_	<u> </u>	-	_	_	_	23	28	35	43	53	_	_	28	43	_	_	_	_	<u> </u>	22	27	34	43	53	
ZC(D)UKQ32	HQ	_	_	_	_	_	_	_	32	32	32. 5	35	36	_	_	38	45. 5	_	_	_	_	_	41. 5	42	47	50. 5	54. 5	ZPT□□□-B10
20(5)01(432	HP	-	_	_	-	_	_	_	64	64	64. 5	67	68	_	_	70	77. 5	_	<u> </u>	_	_	_	73. 5	74	79	82. 5	86. 5	

Rod end shape: Pad direct mounting






Mandal				FI	at/F	at w	ith ri	bs							De	ер						Bell	ows					Applicable
Model	Dia.(mm)	2	4	6	8	10	13	16	20	25	32	40	50	10	16	25	40	6	8	10	13	16	20	25	32	40	50	pad model
ZC(D)UKD10	øDQ	2.6	4.8	7	9	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	Note)
ZC(D)UKR10	HQ	10	10	10	10	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	_	—	ZP□U□-X11
20(0)01110	HP	26	26	26	26	_	_	-	_	_		_	_		_	_		-	_		_	_		-	_	_		
ZC(D)UKD16	øDQ	2.6	4.8	7	9	_	 —	_	_	 —	_	_	 —	_	—	 —	_	7	9	_	_	 —	_	_	—	_	 -	
ZC(D)UKR16	HQ	12	12	12	12	_	_	_	_	_	_	_	_	_	_	_	_	13	13	_	_	_	_	_	_	_	 	ZP
ZC(D)UKH IO	HP	31	31	31	31	_	 —	_	_	 —	_	_	 —	_	_	 —	_	32	32	-	_	_	1	_	_	_	_	
70/70	øDQ	_	_	_	_	12	15	18	_	_	_	_	_	12	18	_	_	_	_	12	15	18	_	_	_	_	_	
ZC(D)UKD20 ZC(D)UKR20	HQ	_	_	_	_	12	12	12. 5	_	_	_	_	_	15	16	_	_	_	_	16	18. 5	20	_	_	_	_	 -	ZP□□□
20(0)01(120	HP	_		_	_	33	33	33. 5	_	_	-	_	_	36	37	_		_	_	37	39. 5	41		_	_	_		
ZC(D)UKD25	øDQ	_	_	_	_	_	_	_	23	28	35	_	_	_	_	28	_	_	_	_	_	_	22	27	34	_	_	
ZC(D)UKR25	HQ	_	_	_	_	_	_	_	14	14	14. 5	_	_	_	_	20	_	_	_	_	_	_	23. 5	24	29	_	 -	ZP
20(D)0KH23	HP	_		_	_	_	_	-	38	38	38. 5	_	_	-	_	44		_	_		_	_	47. 5	48	53	_		
ZC(D)UKD32 ZC(D)UKR32	ø DQ	_	_	_	_	_	_	_	_	_	_	43	53	_	_	_	43	_	_	_	_	_	_	_	_	43	53	
	HQ	_	_	_	_	_	_	_	_	_	_	18. 5	19. 5	_	_	_	29	_	_	_	_	_	_	_	_	34	38	ZP□□□
20(D)0KH32	HP	_		_	_	_	_	-	_	_	-	50	51	-	_	_	60. 5	_	_		_	_		_	_	65. 5	69. 5	

Note) ZP□U□-X11: Flat type only.


Accessory Dimensions (Attached only to a rod end male thread type.)

Rod end nut



			IVIC	atemai.	Caibo	II SIC
Part no.	Applicable cylinder bore (mm)	d	Н	В	С	D
NTP-010	10	M4 x 0.7	2.4	7	8.1	6.8
NTJ-015C	16	M5 x 0.8	4	8	9.2	7.8
NT-015A	20	M6 x 1.0	5	10	11. 5	9.8
NT-02	25	M8 x 1.25	5	13	15. 0	12. 5
NT-03	32	M10 v 1 25	6	17	19.6	16 5

Seal washer





Material: Core sheet — Rolled steel

		Seai -	- INDN
Part no.	Applicable cylinder bore (mm)	t	D
WCS4 x 0.7	10	1.2	11.5
WCS5 x 0.8	16	1.2	12.5
WCS6 x 1	20	1.2	14.0
WCS8 x 1	25	1.6	15.5
WCS10 x 1	32	16	18.0

ZCUK Series Auto Switch Mounting

Proper Auto Switch Mounting Position (Detection at stroke end) and Mounting Height





(): Denotes the values of D-A9 \square V.

															(mm)
Bore size	D-A9	□, D-A	\9□V	D-M9	□, D- M	9□W	D-M9□V, D-M9□WV				D-M9□	4	D-M9□AV		
(mm)	Α	В	w	Α	В	W	Α	В	W	Α	В	W	Α	В	w
10	12.5	3	-1.5 (1)	16.5	7.5	2.5	16.5	7.5	0.5	16.5	7.5	4.5	16.5	7.5	2.5
16	16	4	-2 (0.5)	20	8	1.5	20	8	0	20	8	3.5	20	8	2
20	20	6	-4 (-1.5)	24	10	0	24	10	-2	24	10	2	24	10	0
25	22.5	7	-5.5 (-3)	26.5	11.5	-1.5	26.5	11.5	-3.5	26.5	11.5	0.5	26.5	11.5	-1.5
32	23.5	8	-6.5 (-4)	27.5	12.5	-2.5	27.5	12.5	-4.5	27.5	12.5	-0.5	27.5	12.5	-2.5

Note 1) Figures in the table above are used as a reference when mounting the auto switches for stroke end detection. In the case of actually setting the auto switches, adjust them after confirming their operation.

Note 2) Negative figures in the table show dimensions mounted inside cylinder body.

Note 3) In the case of 5 mm stroke or the 10 mm stroke, there are times in which the auto switches will not turn OFF or 2 auto switches will turn ON simultaneously due to their movement range. Therefore, set the position approximately 1 to 4 mm outward from the values given in the table above. Then, perform an operation inspection to make sure that the auto switches operate normally (if 1 switch is used, make sure that it turns ON and OFF properly; if 2 auto switches are used, make sure that both switches turn ON).

Note 4) Figures in () in the table W are D-A90 and A93.

Operation Range					(mm)						
Auto quitab madal	Bore size										
Auto switch model	10	16	20	25	32						
D-A9□, A9□V	6	9	11	12.5	14						
D-M9□, M9□V D-M9□W, M9□WV	4	5	7	7	7						
D-M9□A, M9□AV											

^{*} Since this is the average value at a normal temperature including hysteresis (tolerance ±30%), it is not guaranteed.

Figures may change substantially depending upon the surrounding environment.

Mounting of Auto Switch

Cautions on Proximity Installation

When free mounting cylinders equipped with auto switches are used, the auto switches could activate unintentionally if the installed distance is less than the dimensions shown in the table. Therefore, make sure to provide a greater clearance. Due to unavoidable circumstances, if they must be used with less distance than the dimensions given in the table, the cylinders must be shielded. Therefore, affix a steel plate or a magnetic shielding plate (MU-S025) to the area on the cylinder that corresponds to the adjacent auto switch. (Please contact SMC for details.) Auto switches may malfunction if a shielding plate is not used.

malfunction if a shielding plate is no	
Bore size (mm)	Mounting pitch L (mm)
10	20
16	33
20	40
25	46



Shielding plate (MU-S025) dimensions



Material: Ferrite stainless steel, Thickness: 0.3 mm The product is attached to the cylinder since the bottom side is pre-treated with adhesive glue.

Weight

Basic Type/With Auto Switch (): Denotes the values with D-A93.

Unit: g

Madal	Bore size	Cylinder stroke (mm)												
Model	(mm)	5	10	15	20	25	30	40	50					
	10	63 (68)	69 (79)	75 (85)	81 (91)	87 (97)	93 (103)	_	_					
	16	103 (128)	115 (145)	127 (157)	139 (169)	151 (181)	163 (193)	_	_					
ZC(D)UKC	20	180 (214)	204 (244)	228 (267)	252 (292)	276 (316)	300 (340)	348 (388)	396 (436)					
	25	304 (358)	343 (402)	382 (441)	421 (480)	460 (519)	499 (558)	577 (636)	655 (714)					
	32	514 (587)	574 (652)	634 (712)	694 (772)	754 (832)	814 (892)	934 (1012)	1054 (1132)					
	10	49 (54)	53 (63)	57 (67)	61 (71)	65 (75)	69 (79)	_	_					
	16	79 (104)	86 (116)	93 (123)	100 (130)	107 (137)	114 (144)	_	_					
ZC(D)UKQ	20	145 (179)	159 (198)	173 (212)	187 (226)	201 (240)	215 (254)	243 (282)	271 (310)					
	25	259 (313)	279 (338)	299 (358)	319 (378)	339 (398)	359 (418)	399 (458)	439 (498)					
	32	421 (494)	451 (529)	481 (559)	511 (589)	541 (619)	571 (649)	631 (709)	691 (769)					

Besides the models listed in How to Order, the following auto switches are applicable.

- * For solid state switches, auto switches with a pre-wired connector are also available. Refer to pages 1340 and 1341 for details.
- * Normally closed (NC = b contact) solid state switches (D-M9□E(V)) are also available. Refer to page 1290 for details.