For details about certified products conforming to international standards, visit us at <u>www.smcworld.com</u>.

5 Port Pilot Operated Solenoid Valve Rubber Seal, Plug-in/Non Plug-in Series VFR2000



Non plug-in type

JIS Symbol



	Fluid				Air			
S	Operating	2 position sing	le/3 position	0.2 to 0.9 MPa				
tior	pressure range	2 position	n double		0.1 to 0.9 MPa	V		
fica	Ambient and fluid te	mperature		–10 to 50°C (No freezing. Refer to page 3-13-4.)			
ecit	Lubrication				Not required ⁽¹⁾			
ŝ	Manual override				Non-locking push type			
Ne	Mounting orientation	า			Unrestricted	N		
Va	Shock/Vibration res	istance			300/50 m/s ² (2)	_		
	Enclosure				Dustproof	N		
S	Coil rated voltage			100, 200 VAC (50/60 Hz), 24 VDC				
tion	Allowable voltage flu	uctuation		-15	to -10% of rated voltage	N		
icat	Apparent power (AC	(3)	Inrush	5.6 VA/50 Hz, 5.0 VA/60 Hz				
scif	ripparent power (/ te) ()	Holding	3.4 VA (2.1	W)/50 Hz, 2.3 VA (1.5 W)/60 Hz			
spe	Power consumption	(DC) ⁽³⁾			1.8 W			
ity				Plug-in type	Conduit terminal	-		
ectric	Electrical entry			Non plug-in	Grommet, Grommet terminal Conduit terminal, DIN terminal	V		
Ξ				туре	L plug connector, M plug connector	N		
0	Note 1) Use turbine oi	I Class 1 (IS	O VG32), if	lubricated.	Note 3) At rated voltage	V		
2	Note 2) Impact resista	ance: No ma	Ifunction o	ccurred when it	is tested with a drop tester in the axial			
e –		directio	on and at t	he right angles	to the main valve and armature in both	E		

energized and de-energized states every once for each condition. (Valu at the initial period) Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. Test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature.

Option Specifications

-	
Pilot type	External pilot Note)
Manual override	Non-locking push type A (Extended), Locking type B (Tool required), Looking type C (Lever)
Coll roted voltage	110 to 120, 220, 240 VAC 50/60 Hz
Coll rated voltage	12, 100 VDC
Porting specifications	Bottom ported
Option	With light/surge voltage suppressor
Note) Operating pressure: 0	to 0.9 MPa
Pilot pressure: 2 posit	ion single/3 position 0.2 to 0.9 MPa
2 position double 0.1	to 0.9 MPa

(Values at the initial period)

Model

		Mc	odel				Flow chara	cteristics (1)			Max ⁽²⁾	(2)	(1)
Typ	Type of		Port	1-	$1 \rightarrow 4/2 (P \rightarrow A/B)$ $4/2 \rightarrow 5/3 (A/B \rightarrow EA/EB$						Response	(4) Weight	
acti	ation	Plug-in	Non plug-in	Rc	C [dm³/(s·bar)]	b	Cv	C [dm³/(s·bar)]	b	Cv	cycle (Hz)	time (ms)	(kg)
Ľ	Cinala	VEDOTOO	VEDOITO	1/8	2.5	0.18	0.58	3.0	0.27	0.70	10	20 or 1000	0.34
sitic	Single	VFR2100	VFR2110	1⁄4	2.8	0.24	0.62	3.0	0.27	0.70	10	20 of less	(0.32)
öd	Doublo	VEDOOOO	VEDOOTO	1⁄8	2.4	0.21	0.56	3.1	0.28	0.74	10	20 or 1000	0.42
2	Double	VFR2200	VFR2210	1/4	2.6	0.27	0.62	3.1	0.28	0.74	10	20 01 1855	(0.44)
	Closed	VEDOOOO	VEDOOTO	1⁄8	1.3	0.45	0.36	1.4	0.46	0.41	E	20 or loss	0.43
Б	center	VFR2300	VFR2310	1/4	1.3	0.45	0.36	1.4	0.46	0.41	5	SU OF less	(0.45)
sitio	Exhaust	VED0400	VED0440	1/8	0.79	0.53	0.24	3.1 [0.89]	0.24 [0.51]	0.74 [0.27]	-	00 av lass	0.43
bo	center	VFR2400	VFR2410	1/4	0.79	0.53	0.24	3.1 [0.89]	0.24 [0.51]	0.74 [0.27]	5	30 or less	(0.45)
c	Pressure	VEDOEOO	VEDOSTO	1⁄8	2.8 [0.65]	0.24 [0.60]	0.68 [0.21]	0.89	0.53	0.27	_	00	0.43
	center	VFR2500	VFR2510	1/4	3.2 [0.75]	0.26 [0.55]	0.73 [0.23]	0.89	0.53	0.27	5	30 or less	(0.45)

Note 1) []: Denotes the normal position.

Note 2) Min. operating frequency is once in 30 days. (As per JIS B 8375)

Note 3) Based on dynamic performance test, JIS B 8375-1981. (0.5 MPa, Coil temperature: 20°C, at rated voltage, without surge voltage suppressor) Note 4) For VFR2 00- FZ-01 (): VFR2 10- DZ-01 (): VFR2



VFN





Cylinder Speed Chart

Use as a guide for selection. Please confirm the actual conditions with SMC Sizing Program.

							Bore	e size							
System	Average speed (mm/s)	Series CM Pressure C Load facto Stroke 300).5 MPa r 50%) mm			Series ME Pressure Load facto Stroke 50	B/CA1 ^{Note)} 0.5 MPa or 50% 0 mm				Serie Press Load Strok	s CS1 sure 0. factor e 1000	5 MPa 50%) mm		
		ø20	ø25	ø32	ø40	ø40	ø50	ø63	ø80	ø100	ø12	25	ø140	ø160	
A	800 700 600 500 400 300 200 100 0											Pe up Ho	rpendicul ward actu prizontal a	ar, iation	V
В	800 700 600 500 400 300 200 100 0														V
с	800 700 600 500 400 300 200 100 0														V V
D	800 700 600 500 400 300 200 100 0														V E V
E	800 700 600 500 400 300 200 100 0														

* It is when the cylinder is extending that is meter-out controlled by speed controller which is directly connected with cylinder, and its needle valve with being fully open. * The average velocity of the cylinder is what the stroke is divided by the total stroke time.

* Load factor: ((Load weight x 9.8)/Theoretical force) x 100% Note) The Series CA1 has been changed to the Series CA2.

System Components

System	Solenoid valve	Speed controller	Silencer	Tube bore x Length
А		AS2000-01 AN110-01 (S = 2.5 mm ²) (S = 35 mm ²)		T0425 x 1 m
В	VFR2000	AS3000-02 (S = 12 mm ²)	AN110-01 (S = 35 mm ²)	T0604 x 1 m
С	nc 78	AS3000-02 (S = 12 mm ²)	AN110-01 (S = 35 mm ²)	T0806 x 1 m
D	Series	AS4000-02 (S = 21 mm ²)	AN110-01 (S = 35 mm ²)	T1075 x 1 m
E	Rc ¹ /4	AS4000-02 (S = 21 mm ²)	AN110-01 (S = 35 mm ²)	T1209 x 1 m

How to Order Sub-plate Assembly

			Pilot	type		
			Nil	In	ternal	pilot
Ciala nantadi			R	E	kternal	pilot
<side ported=""></side>) Chroc	d tuno
Plua-in	VFR2000	-LP-	02		mea	iu type
· J		L		ᆍ.	Nil	Rc
Non plug-in	VFS2000	-LS-	02		F	G
<bottom ported<="" th=""><th>></th><th></th><th></th><th>T .</th><th>Ν</th><th>NPT</th></bottom>	>			T .	Ν	NPT
			╘╴╧╴	╧	Т	NPTF
Plug-in	VFR2000	-LP-B	02	ΨŪ		
Non plug-in	VFS2000	-LS-B	02			
				- Pip	ing i	oort
Note) Mount	ting bolts and g	askets are not	attached	<u>(Р,</u>	A, B	port)
				0	1	1⁄8
				02	2	1/4

EA, EB port: Rc 1/8

Construction



3 position closed center/exhaust center/pressure center





Pressure center: VFR25□0





12 (5

a

Component Parts

No.	Description	Material	Note	No.	Description	Material	Note
1	Body	Aluminum die-casted	Platinum silver	7	Piston	Resin	
2	Sub-plate	Aluminum die-casted	Platinum silver	8	Piston	Resin	
3	Spool valve	Aluminum, NBR		9	Junction cover	Resin	
(4)	Adapter plate	Aluminum die-casted	Platinum silver	10	Light cover assembly	Resin	
5	Adapter plate	Aluminum die-casted	Platinum silver	1	Spool spring	Stainless steel	
6	End plate	Resin	Black	12	Return spring	Stainless steel	

Replacement Parts

No	Description	Motorial	Part no.							
INO.	Description	Material	VFR21□0	VFR22□0	VFR23□0/24□0/25□0					
13	Gasket	NBR	AXT624-20-2	AXT624-20-2	AXT624-20-2					
14	Hexagon socket head screw	Steel	AXT624-26 (M3 x 31)	AXT624-26 (M3 x 31)	AXT624-26 (M3 x 31)					
(15)	Pilot valve assembly	—	Refer to "How to Order Pilot Valve Assembly" on page 3-5-10.							
_	Sub-plate assembly	_	Refer to	Refer to "How to Order Sub-plate Assembly" on page 3-5-11.						





Non Plug-in 2 position single













Series VFR2000 Manifold Specifications

Manifold Specifications

Basa madal	Miring	Porting specifications	Port size		Stations	Applicable
Dase model	winng	A, B port	P, EA, EB	Α, Β	Stations	valve model
Blug in type	 With terminal block 				2 to 15	
VV5FR2-01	With multi-connectorWith D-sub connector				2 to 8	VFR2□00-□F
Non plug-in type VV5FR2-10	Grommet Grommet terminal Conduit terminal DIN terminal L plug connector M plug connector	_{Note)} Side/Bottom	1/4	¹ ⁄ ₈ , 1⁄ ₄ C6, C8	2 to 15	VFR2□10-□G VFR2□10-□E VFR2□10-□T VFR2□10-□D VFR2□10-□L VFR2□10-□M

Note) Side ported and bottom ported cannot be taken at the same time.

How to Order Manifold Assembly

<Example> Plug-in type with terminal block (6 stations, one-piece junction cover)

- VV5FR2-01T1-061-02 1 set (Manifold base part no.)
- *VFR2100-5FZ 3 sets (2 position single part no.)
- *VFR2200-5FZ 2 sets (2 position double part no.)
- *VVFS2000-10A1 set (Blanking plate assembly part no.)
- The asterisk denotes the symbol for assembly. Prefix it to the part nos. of the solenoid valve, etc.
- Valve arrangement is counted from the D side.

When ordering, specify the part nos. in order from the 1st. station in the D side. When entry of part numbers becomes complicated, indicate on the manifold specification sheet.

Plug-in Type: With Terminal Block

 Since lead wires of solenoid are connected with the term on upper surface of terminal corresponding lead wires power source can be wired a 	valve inals VV block from Serie	5 S VFR	R2 –	017 	C Sy	mbol ·	08	1-	- 02 - 02	2		→ Thre	ead
bottom of terminal block.	I III III		u 		Sumh	Pas	sage	Porting	Symbol	P, EA, EB	A, B *	Nil	Rc
		P	'lug-in ty	/pe •	Synt	P	EA, EB	A B	01		1/8	F	G
One piece junct	ion cover WI	th teri	minal blo	DCK	1			Side	02		1/4	Ν	NPT
U side	Rem	Jur	nction co	over 🖡	2	* Common	Common	Bottom	C6	1/4	One-touch fitting for ø6	Т	NPTF
		Nil	Individual j cove	unction r	3 4	* Common	Individual	Side Bottom	C8		One-touch fitting for ø8		
Ac. 100 .000 0 000	0000	1	One-piece j cove	unction r	5	* Individual	Common	Side Bottom	М		Mixed		
Individual	Conduit wiring		Sta	tions	7	* Individual	Individual	Side	C	* For b 1/8 is	ottom ported, only availabl	e.	
junction cover D side	D side		02 2 :	stations	8 * 0	otion		Bottom					
			15 15	stations	-								

∟

specification sheet.

<Example> Non plug-in type: 6 stations

the solenoid valve, etc.

Valve arrangement is counted from the D side.

VV5FR2-10-061-01 1 set (Manifold base part no.)

*VFR2110-5D 5 sets (2 position single part no.)

*VFR2410-5D 1 set (3 position exhaust part no.)

*VVFS2000-R-01-2..... 1 set (Individual EXH spacer part no.)

The asterisk denotes the symbol for assembly. Prefix it to the part nos. of

When ordering, specify the part nos. in order from the 1st. station in the D side.

When entry of part numbers becomes complicated, indicate on the manifold

Plug-in Type: With Multi-connector (For wiring specifications, refer to page 3-5-8.)





Note) P port or EA/EB port of symbol "3" to "8" can be individual port with block plate.

Therefore, if using individual SUP spacer or individual EXH spacer for individual port, its symbol is "1".

Manifold/Option Parts Assembly

Individual SUP spacer

Setting individual SUP spacer on the manifold block enables individual SUP port for each valve.

Bo	dy type	Plug-in type	Non plug-in type
Ö	Rc ¹ /8	VVFS2000-P-01-1	VVFS2000-P-01-2
Part	Rc ¹ /4	VVFS2000-P-02-1	VVFS2000-P-02-2



Individual EXH spacer

Setting individual EXH spacer on the manifold block enables individual EXH port for each valve.

Bo	dy type	Plug-in type	Non plug-in type		
no.	Rc ¹ /8	VVFS2000-R-01-1	VVFS2000-R-01-2		
Part	Rc ¹ /4	VVFS2000-R-02-1	VVFS2000-R-02-2		



SUP block disk

When supplying manifold with more than two different kinds of pressure, high and low, insert a block disk in between stations subjected to different pressures.

Body type	Plug-in type	Non plug-in type
Part no.	AXT625-12A	

EXH block disk

When valve exhaust affects the other stations in the circuit, insert EXH block disk in between stations to separate valve exhaust.

Body type Plug-in type		Non plug-in type	
Part no.	AXT625-12A		



Throttle valve spacer

Needle valve set on the manifold block can control cylinder speed by throttling exhaust.

Body type	Plug-in type	Non plug-in type	
Part no.	VVFS2000-20A-1	VVFS2000-20A-2	



Interface regulator

Interface regulator set on the manifold block can regulate pressure for each valve. (Refer to "Flow Characteristics" on page 3-5-6 before operation.)

		-	
Body type	Plug-in type	Non plug-in type	
P port regulation	ARBF2000-00-P-1	ARBF2000-00-P-2	



Air release valve spacer

Valve VFR21□0 (single) can be used as air release valve by combining with release valve spacer.

Body type	Plug-in type	Non plug-in type	
Part no.	VVFS2000-24A-1 ^L _R	VVFS2000-24A-2 k	
) L: U side mount R: D side mount		

SUP stop valve spacer Note)

If SUP stop valve spacer is set, valve can be removed for maintenance without stopping air pressure supply for other valves.

	Body type	Plug-in type	Non plug-in type
Part no.		VVFS2000-37A-1	VVFS2000-37A-2
(Height will be 23.2 mm higher.)			

Please contact SMC for details.

Note) Used with manifold base.



Blanking plate

It is used by attaching on the manifold block for being prepared for removing a valve for maintenance reasons or planning to mount a spare valve, etc.

Body type	Plug-in type	Non plug-in type	
Part no.	VVFS2000-10A		

Manifold Option

With control unit

- Plug-in/Non Plug-in type
 Filter, regulation valve, pressure switch and air release valve all combine to form one unit.
- Piping processes are eliminated.



For details, refer to page 3-5-24.

With serial interface unit for serial transmission Plug-in type

- Solenoid valve wiring process reduced considerably.
- Disperse installation possible. Manifold solenoid valve: 8 stations max, 32 positions (512 solenoids).
- Maintenance and inspection are easy.



For details, refer to "Serial Transmission" catalog separately.



Manifold Plug-in type











Manifold with Control Unit -

- Control unit (Filter, Regulator, Pressure switch, Air release valve) are all standardized to the one unit, and can be mounted on the manifold base without any attachments.
- Piping processes are eliminated.



Plug-in type



Non plug-in type

A Caution

Air filter with auto-drain or manual drain must be mounted with the air filter at the bottom.

Manifold Specifications

Manifold	Plug-in type: VV5FR2-01□		Non plug-in type: VV5FR2-10	
	With terminal block		Grommet, Grommet terminal	
Wiring	With multi-connector		Conduit terminal, DIN terminal	
	With D-sub connector		L plug connector, M plug connector	
Applicable value	VFR2□00-□F		VFR2□10-□G, VFR2□10-□E	
Applicable valve			VFR2010-0T, VFR2010-0DY	
model			VFR2□10-□L, VFR2□10-□M	
Deuting energifications	Common SUP, Common EXH			
Porting specifications	A, B port	Side: Rc ¹ /8, ¹ /4, C6, C8, Bottom: Rc ¹ /8 (Option)		
nc	P, EA, EB port	EA, EB port Side: Rc ¹ /4, Bottom: Rc ¹ /8 (Option)		
Stations	2 to 15 stations * (With multi-connector/D-sub connector: 2 to 8 stations)			
* Including station of control unit				

 \mathcal{O}^{*}

Control Unit Specifications

Air filter (With auto-drain/With manual drain)		
Filtration degree	5 um	
Regulator	- F	
Set pressure		
(Outlet pressure)	0.05 to 0.85 MPa	
Pressure switch		
Set pressure	0.1 to 0.6 MBo	
range: OFF	0.1 10 0.6 MPa	
Differential	0.08 MPa	
Contact	1a	
Indicator light	LED (RED)	
Max. switch capacity	2 VA AC, 2 W DC	
Max. operating	24 VAC, DC or less: 50 mA	
current	100 VAC, DC: 20 mA	
Inside voltage drop	4 V or less	
Air release valve (Single only)		
Operating	0.2 to 0.9 MPa	
pressure range	0.2 10 0.9 MI a	

Control Unit/Option

Air release	<plug-in type=""> VVFS2000-24A-1R (D side mounting) VVFS2000-24A-1L (U side mounting)</plug-in>		
valve spacer	<non plug-in="" type="">VVFS2000-24A-2R (D side mounting)VVFS2000-24A-2L (U side mounting)</non>		
Pressure ⁽²⁾ switch	IS1000P-2-1		
Blanking	For filter regulator	MP2-2	
nlate	For pressure switch	MP3-2	
plate	For air release valve	AXT625-18A	
Filter element	111511-5B		
Note 1) Refer to "Manifold Option" on page 3-5-23.			
Note 2) Pressure switch cannot be mounted			

Note 2) Pressure switch cannot be mounted later on non plug-in type.



*VFR2100-5FZ 5 sets (2 position single part no.)
*VFR2200-5FZ······ 2 sets (2 position double part no.)
The exteriol denotes the symbol for examply. Drafiv it to the part nee of

The asterisk denotes the symbol for assembly. Prefix it to the part nos. of the solenoid valve, etc.

The 1st and 2nd station are used for control unit mounting.

When ordering, specify the part nos. in order from the 3rd. station in the D side. When entry of part numbers becomes complicated, indicate on the manifold specification sheet.

*VFR2110-5D·························5 sets (2 position single part no.)

The asterisk denotes the symbol for assembly. Prefix it to the part nos. of the solenoid valve, etc.

The 1st and 2nd station are used for control unit mounting.

When ordering, specify the part nos. in order from the 3rd. station in the D side. When entry of part numbers becomes complicated, indicate on the manifold specification sheet.





Replacement Parts

No.	Description	Material	Part no.	
1	Connection fitting A	Steel plate		AXT625-4-1
2	Connection fitting B	Steel plate		AXT625-5
3	Gasket A	NBR		AXT625-17
4	Gasket B	NBR		AXT625-16
(5)	O-ring	NBR		18 x 15 x 1.5
6	O-ring	NBR		10.5 x 7.5 x 1.5
$\overline{\mathcal{O}}$	O-ring	NBR		8 x 5 x 1.5
	Adaptar plata accombly		For 01T	AXT625-28-1A
_	Audplei plate assembly		For 01T1	(Terminal and adapter plate)
(8)			For 01C	AXT625-28-1
	Adapter plate	Resin	For 01F	VVF2000-26-6
			For 01SU	AXT625-6

_					
No.	Description	Material	Part no.		
9	Junction cover assembly	_	For 01T	AXT625-28-3A	
			For 01T1	AXT625-28-7A-Stations	
			For 01C		
			For 01F	VVF2000-26-5A-Stations	
			For 01SU	AZ738-10A-Stations	
13	Rubber plug	NBR	For 01T	AVT000.00	
			For 01SU	AX1623-22	

Replacement Parts: Sub Assembly

J	Note) Manifold Base/Construction: Plug-in type with termin	al block.
---	--	-----------

	•			
No.	Description	Assembly part no.	Component parts	Applicable manifold base
10	Manifold block assembly ⁽¹⁾	AXT625-20A- ¹ _{C6} _{C8} ⁽²⁾	Manifold block (1), Metal joint (1), (2), O-ring (5), (6), (7) Terminal (8), Junction cover (9), Adaptor plate, Pin housing, Guide	Plug-in type
		AXT625-10A- ¹ C8 C8	Manifold block (1), Metal joint (1), (2), O-ring (5), (6), (7)	Non plug-in type
1)	End plate (U side) assembly	AXT625-2A-20	End plate (U) ①, Metal joint ①, ②, Gasket A ③, Guard ③	Plug-in type With terminal block $\begin{pmatrix} For 01T\\01T1 \end{pmatrix}^{(3)}$
		AXT625-2A-10	End plate (U) (1), Metal joint (1), (2), Gasket A (3), Guard (3)	Non plug-in type (For 10) ⁽³⁾
12	End plate (D side) assembly	AXT625-3A-20	End plate (D) ¹ / ₂ , Metal joint ¹ , ² / ₂ , Gasket B ⁴ / ₂ , Guard ¹ / ₃ , Steel ball	Plug-in type With terminal block (01T) (3)
		AXT625-3A-10	End plate (D) ⁽¹⁾ , Metal joint ⁽¹⁾ , ⁽²⁾ , Gasket B ⁽⁴⁾ , Guard ⁽³⁾ , Steel ball	Non plug-in type (For 10) ⁽³⁾

Note 1) For side ported

Note 2) 1: A, B port size Rc $1/_8$, 2: A, B port size Rc $1/_4$ Note 3) Please contact SMC if parts except for 10/01T/01T1 are needed.