## 3-Screen Display

# **High-Precision Digital Pressure Switch**




ole						Piping		
Applicable fluid	Applicat fluid A		Output type Enclosure		Copy function	M5 female thread	1/8 (R, NPT)	1/4 (R, NPT, G) (URJ*1/TSJ*2)
	ZSE20(F)/ ISE20 p.9		1 output	IP40	_	•	•	_
Air	ZSE20A(F)/ ISE20A p.11		2 outputs Analog output (Voltage/Current)	IP40	•	•	•	_
	ZSE20B(F)-(L)/ ISE20B-(L)	MAZ (	2 outputs Analog output (Voltage/Current)	IP65	•			_
	ISE20B-(L)		IO-Link/ Switch: 1 output		*4			
General fluids	ZSE20C(F)/ ISE20C(H) p.24		2 outputs Analog output (Voltage/Current)	IP65	•	●*3	(Rc thread only)	•
*1 Face seal fitting *2 Compression fitting *3 With 1/4 (R, NPT, G) M5 female threaded *4. A block parameter or data storage function is provided with the IO-I ink compatible type								

Face seal fitting \*2 Compression fitting \*3 With 1/4 (R, NPT, G) M5 female threaded \*4 A block parameter or data storage function is provided with the IO-Link compatible type.

**ZSE20** (F)/ISE20 Series





Snap Pressing the and buttons simultaneous-Now with a snap shot ly for a minimum of 1 second will make the set value function (threshold value) the same as the current pressure value. shot function for set value reading Push Push Release the buttons after Setting start ---" is displayed on the Setting complete right side sub screen.


**Easy Screen Switching** It is possible to change the settings while checking the measured value.

Main screen	
Measured value (Current pressure value)	ΠΠΠΠ
Sub screen/Left side Label (Display item)	
Sub screen/Right side	
Set value (Threshold value)	



\* One additional arbitrary display mode can be added via the function settings. (Refer to p. 3.)
 \* Example for 1 output







## Improved Operability

## Other Sub Screen Display

The peak value or bottom value, or both values can be displayed on one screen!

\* Peak and bottom values are maintained even if the power supply is cut.





 A combination of the displays shown above and the set values can be displayed on the 2 sub screens.

# Delay Time 1.5 ms<sup>\*1</sup> or less


\*1 Select from 1.5 ms or less, 20 ms, 100 ms, 500 ms, 1000 ms, 2000 ms, or 5000 ms.

## **Convenient Functions**

Functions	Copy function	Auto-shift function	Security code	Power saving mode	Resolution switch function	MPa/kPa switch function
20	—	—	•	•	•	•
20A	•	•	•	•	•	•
20B	•	•	•	•	•	•
20B-L	—	—	•	•	•	•
20C	•	•	•	٠	•	•

#### Copy function

The settings of the master sensor can be copied to the slave sensors.



#### Auto-shift function

This measures the pressure at the time of external input and uses it as a reference to correct the on-off point of the switch.

#### Security code

The key locking function keeps unauthorized persons from tampering with the settings.

#### Power saving mode

Power consumption is reduced by turning off the monitor.

Series	Current consumption	Reduction rate*1		
20	25 mA or less	Approx. 60% reduction		
20A		4 400/		
20B(-L)	35 mA or less	Approx. 40% reduction		
20C		reduction		

SMC

\*1 In power saving mode

## Display resolution switch

#### function

Reduces monitor flickering




(Only the displayed values are changed; the accuracy remains the same.)


### MPa/kPa switch function

Vacuum, compound, and/or positive pressure can be displayed in MPa or kPa.



## Compact & Lightweight






## Mounting

Available Mounting Options								
Series	Bracket A	Bracket B	Bracket C	Panel mount				
20	•	•	—	•				
20A	•	•	_	•				
20B(-L)	•	•	—	•				
20C	•	_	•	•				

## The bracket configuration allows for mounting in four orientations.



## IO-Link Compatible ZSE20B(F)-L/ISE20B-L DIS Visualization of operation/equipment status/Remote monitoring and control by communication Configuration File (IODD File\*1) •Manufacturer •Product part no. •Set value

IO-Link is an open communication interface technology between the sensor/actuator and the I/O terminal that is an international standard, IEC61131-9.

IP65

**IO-Link Compatible Device** 

ZSE20B(F)-L/ISE20B-L

Operate moc

#### IODD is an abbreviation of IO Device Description. This file is necessary for setting the device and connecting it to a master. Save the IODD file on the PC to be used to set the device prior to use.

\*1 IODD File:

#### Read the device data. • Switch ON/OFF signal and analog value • Device information:

- Manufacturer, Product part number,
- Serial number, etc.
- Normal or abnormal device status
- Cable breakage

## Implement diagnostic bits in the process data.

PC

0

0 

 $\bigcirc$ 0

 $\bigcirc$ 

**IO-Link Master** 

The diagnostic bit in the cyclic process data makes it easy to find problems with the equipment. It is possible to find problems with the equipment in real time using the cyclic (cycle) data and to monitor such problems in detail with the noncyclic (aperiodic) data.

Fieldbus

PLC

master.

etc

Threshold value


·Operation mode,

**Device settings** 

can be set by the

#### **Process Data**


IO mod



## **Display function**

Displays the output communication status and indicates the presence of communication data


#### **Operation and Display**







corrosion resistance due to the use of stainless steel 316L for the parts in contact with fluid (pressure sensor and fitting). A pressure switch that has a restrictor installed in the fitting is available to prevent the sensor from being damaged by water hammer or fluid inertia. (Refer to p. 38 for details.)



## Introduction of Series

	1 output IP40 ZSE/ISE20 p. 9			2 outputs IP40 ZSE/ISE20A p. 11		
Applicable fluid				Air		
Model	For vacuum pressure	For compound pressure	For positive pressure	For vacuum pressure	For compound pressure	For positive pressure
Rated pressure range	0 101 kPa	100 kPa -100 kPa	1 MPa	0 0	100 kPa 	1 MPa
Withstand pressure	500 kPa	500 kPa	1.5 MPa	500 kPa	500 kPa	1.5 MPa
Output	1 output (NPN/PNP)			2 outputs (NPN/PNP)		
specification				Analog (Voltage/Current)		
Enclosure	IP40				IP40	
Piping			M5 female threa	ad, R1/8, NPT1/8		
Note		_		Сору	function, Auto-shift fu	nction

## CONTENTS

# 3-Screen Display High-Precision Digital Pressure Switch ZSE20(F)/ISE20 Series

How to Orderp. 9
Specifications p. 10
Set Pressure Range and Rated Pressure Range p. 17
Analog Output p. 17
IO-Link: Process Data p. 17
Functions p. 17
Internal Circuits and Wiring Examplesp. 18
Dimensions

## 3-Screen Display High-Precision Digital Pressure Switch ZSE20A(F)/ISE20A Series

How to Order	····· p. 11
Specifications	····· p. 12
Set Pressure Range and Rated Pressure Range	····· p. 17
Analog Output	····· p. 17
IO-Link: Process Data	····· p. 17
Functions	····· p. 17
Internal Circuits and Wiring Examples	····· p. 18
Dimensions	····· p. 20

2 outp		SE20B p. 13	2 outputs IP65 ZSE/ISE20C p.24					
IO-Link 1 outp	out IP65 ZSE/I	SE20B-L p. 15		General fluids				
For vacuum pressure	For compound pressure	For positive pressure	For vacuum pressure	For compound pressure	For positive pressure (1 MPa)	For positive pressure (2 MPa)		
O-Link compatible/ L type 0 0 0	IO-Link compatible/ L type 100 kPa 100 kPa	IO-Link compatible/ L type 1 MPa 1 MPa 1 MPa 0	0 0 0	100 kPa -100 kPa	1 MPa	2 MPa		
500 kPa	500 kPa	1.5 MPa	500 kPa	500 kPa	2 MPa	4 MPa		
2 out	puts (NPN/PNP)/IO-L	.ink <sup>*4</sup>	2 outputs (NPN/PNP)					
An	Analog (Voltage/Current)*5			Analog (Voltage/Current)				
IP65			IP65					
M5 fe	male thread, R1/8, N	PT1/8	R1/4*1, NPT1/4*1, G1/4*1, Rc1/8, URJ1/4*2, TSJ1/4*3					
Copy fu	nction <sup>*5</sup> , Auto-shift fu	nction <sup>*5</sup>	Copy function, Auto-shift function					
	ode (NPN or PNP swit		*1 M5 female threaded *2 Face seal fitting *3 Compression fitting					

\*5 This function is not provided with the IO-Link compatible type.

#### 3-Screen Display High-Precision Digital Pressure Switch ZSE20B(F)/ISE20B Series

How to Order	p.	13
Specifications	p.	14

#### 3-Screen Display High-Precision Digital Pressure Switch/ **IO-Link Compatible**

### ZSE20B(F)-L/ISE20B-L Series


How to Order	·· р. 15
Specifications	· р. 16
Set Pressure Range and Rated Pressure Range	·· р. 17
Analog Output ·····	·· р. 17
IO-Link: Process Data	·· р. 17
Functions	·· р. 17
Internal Circuits and Wiring Examples	·· р. 19
Dimensions	·· p. 20

#### 3-Screen Display High-Precision Digital Pressure Switch for General Fluids

### ZSE20C(F)/ISE20C(H) Series

How to Order       p. 2.         Specifications       p. 2.         Set Pressure Range and Rated Pressure Range       p. 2.         Analog Output       p. 2.         Functions       p. 2.         Internal Circuits and Wiring Examples       p. 2.	5 6 6
Dimensions p. 2	8
Function Details       p. 3.         Made to Order       p. 3.         Safety Instructions       Back cover	8

## 1 Output **3-Screen Display High-Precision** RoHS **Digital Pressure Switch** IP40 ZSE20(F)/ISE20 Series



**SMC** 

Panel mount

adapter + Front protection cover

ZS-46-D

D

When only optional parts are required, order with the part numbers listed below.					
Description	Part no.	Note			
Bracket A	ZS-46-A1	Tapping screw: Nominal size 3 x 8 L (2 pcs.)			
Bracket B	ZS-46-A2	Tapping screw: Nominal size 3 x 8 L (2 pcs.)			
Panel mount adapter	ZS-46-B	—			
Panel mount adapter + Front protection cover	ZS-46-D	—			
Lead wire with connector	ZS-46-3L	3-core, 2 m, Non-waterproof (Without waterproof cover)			
Front protection cover	ZS-27-01	—			
R1/8 Piping adapter	ZS-46-N1				
NPT1/8 Piping adapter	ZS-46-N2	Co			
9					

# 3-Screen Display High-Precision Digital Pressure Switch **ZSE20(F)/ISE20** Series

## For details on the specific product

### Specifications

precautions, refer to the "Operation Manual" on the SMC website.

ZSE20(F)/ISE20

ZSE20A(F)/ISE20A

ZSE20B(F)/ISE20B

Rated pressure range Display/Set pressure range Display/Smallest settable increment Withstand pressure Power supply voltage Current consumption Protection Display accuracy Repeatability Femperature characteristics Dutput type Dutput mode	Air, N 0.0 to -101.0 kPa 10.0 to -105.0 kPa 0.1 500 12 to 2 ±2% F.S.	ZSE20F (Compound pressure)           Ion-corrosive gas, Non-flammable           -100.0 to 100.0 kPa           -105.0 to 105.0 kPa           kPa           24 VDC ±10%, Ripple (p-p) 10% of 25 mA or less           Polarity protection           ±1 digit (Ambient temperature of ±0.2% F.S. ±1 digit	-0.100 to 1.000 MPa -0.105 to 1.050 MPa 0.001 MPa 1.5 MPa or less
Display/Set pressure range Display/Smallest settable increment Withstand pressure Power supply voltage Current consumption Protection Display accuracy Repeatability Femperature characteristics Dutput type	10.0 to -105.0 kPa 0.1 500 12 to 2 ±2% F.S.	-105.0 to 105.0 kPa kPa 24 VDC ±10%, Ripple (p-p) 10% of 25 mA or less Polarity protection ±1 digit (Ambient temperature of	-0.105 to 1.050 MPa 0.001 MPa 1.5 MPa or less
Display/Smallest settable increment Withstand pressure Power supply voltage Current consumption Protection Display accuracy Repeatability Femperature characteristics Dutput type	0.1 500 12 to 2 ±2% F.S.	kPa kPa 24 VDC ±10%, Ripple (p-p) 10% of 25 mA or less Polarity protection ±1 digit (Ambient temperature of	0.001 MPa 1.5 MPa or less
Vithstand pressure Power supply voltage Current consumption Protection Display accuracy Repeatability Femperature characteristics Dutput type	500 12 to 2 ±2% F.S.	kPa 24 VDC ±10%, Ripple (p-p) 10% of 25 mA or less Polarity protection ±1 digit (Ambient temperature of	1.5 MPa or less
Power supply voltage Current consumption Protection Display accuracy Repeatability Temperature characteristics Dutput type	12 to 2 ±2% F.S.	24 VDC ±10%, Ripple (p-p) 10% of 25 mA or less Polarity protection ±1 digit (Ambient temperature of	or less
Current consumption Protection Display accuracy Repeatability Femperature characteristics Dutput type	±2% F.S.	25 mA or less Polarity protection ±1 digit (Ambient temperature of	
Protection Display accuracy Repeatability Femperature characteristics Dutput type		Polarity protection ±1 digit (Ambient temperature of	25 +3°C)
Display accuracy Repeatability Femperature characteristics Dutput type		±1 digit (Ambient temperature of	25 +3°C)
Repeatability Femperature characteristics Dutput type		•	25 +3°C)
Temperature characteristics Dutput type		+0.2% FS +1 digit	
Dutput type		±0.2 /01.0. ±1 digit	
		±2% F.S. (25°C standard)	
Dutput mode	N	PN or PNP open collector 1 outp	ut
-	Hysteresis mode, V	Vindow comparator mode, Error o	output, Output OFF
Switch operation		Normal output, Reversed output	
Max. load current	80 mA		
Max. applied voltage (NPN only)	28 V		
nternal voltage drop (Residual voltage)	1 V or less (at load current of 80 mA)		
Delay time <sup>*1</sup>	1.5 ms or less (with anti	i-chattering function: 20, 100, 500	), 1000, 2000, 5000 ms)
Hysteresis mode Window comparator mode	Variable from 0*2		
Short circuit protection		Yes	
Jnit <sup>*3</sup>	MPa, kPa, kgf/cm <sup>2</sup> , k	oar, psi, inHg, mmHg	MPa, kPa, kgf/cm <sup>2</sup> , bar, psi
Display type	-	LCD	· · · · · · · · · · · · · · · · · · ·
Number of screens	3-screen display (Main screen, Sub screen x 2)		en x 2)
Display color	1) Main screen: Red/Green 2) Sub screen: Orange		
Number of display digits			segments for other)
ndicator light	Lights up when switch output is turned ON. OUT1: Orange		
-	0	, 10, 50, 100, 500, 1000, 5000 m	S
Enclosure		IP40	
Withstand voltage	1000 VAC	for 1 minute between terminals a	nd housing
nsulation resistance	50 M $\Omega$ or more (500 VDC measured via megohymmeter) between terminals and housing		
Operating temperature range	Operating: -5 to 50°C, Stored: -10 to 60°C (No condensation or freezing)		
Dperating humidity range	Operating/Stored: 35 to 85%RH (No condensation)		
dards UL/CSA (E216656), CE, RoHS			
ength of lead wire with connector 2 m			
	elay time <sup>*1</sup> ysteresis Hysteresis mode Window comparator mode hort circuit protection nit <sup>*3</sup> isplay type umber of screens isplay color umber of display digits idicator light nclosure /ithstand voltage sulation resistance perating temperature range perating humidity range	elay time*1       1.5 ms or less (with ant         ysteresis       Hysteresis mode         Window comparator mode       hort circuit protection         hort circuit protection       ml*3         mit*3       MPa, kPa, kgf/cm², t         isplay type       3-screet         umber of screens       3-screet         isplay color       1) Main screen: 4 di         umber of display digits       1) Main screen: 4 dig         idicator light       Lights up wh         conclosure       0         //ithstand voltage       1000 VAC         sulation resistance       50 MΩ or more (500 VDC n         perating temperature range       Operating: -5 to 50°         perating humidity range       Operating:	elay time*1       1.5 ms or less (with anti-chattering function: 20, 100, 500         ysteresis       Hysteresis mode         Window comparator mode       Variable from 0*2         hort circuit protection       Yes         nit*3       MPa, kPa, kgf/cm², bar, psi, inHg, mmHg         isplay type       LCD         umber of screens       3-screen display (Main screen; Sub screen; Sub screen; 2) Sub screen: Orange         umber of display digits       1) Main screen: 4 digits (7 segments)         umber of display digits       1) Main screen: 4 digits (Upper 1 digit 11 segments, 7         dicator light       Lights up when switch output is turned ON. O         0, 10, 50, 100, 500, 1000, 5000 m       1000 VAC for 1 minute between terminals a         isulation resistance       50 MΩ or more (500 VDC measured via megohmmeter) betw         perating temperature range       Operating: -5 to 50°C, Stored: -10 to 60°C (No cond         UL/CSA (E216656), CE, RoHS       UL/CSA (E216656), CE, RoHS

\*2 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value greater than the amount of fluctuation, or chattering will occur.

\*3 Setting is only possible for models with the units selection function. Only MPa or kPa is available for models without this function.

\*4 The response time indicates when the set value is 90% in relation to the step input.

\* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.


#### **Piping Specifications and Weights**

Model		M5	01	N01	
Port size	Port size M5 x 0.8 R1/8 NPT1			NPT1/8	
Matariala of parts in	Sensor pressure receiving area Silicon				
Materials of parts in contact with fluid	Pining port (Common) PBL CB156 Heat-resistant PPS ()-ring		O-ring: HNBR		
	Piping port	—	C3604 (Electroless nickel plat	ing), Stainless steel 304, NBR	
Waight	Body	22 g	32 g	34 g	
Weight	Lead wire with connector		+35 g		

#### **Cable Specifications**

Conductor area		0.15 mm <sup>2</sup> (AWG26)	
Inculator	O.D.	1.0 mm	
Insulator	Color	Brown, Blue, Black (3-core)	
Sheath Finished O.D.		ø3.4	

"Set Pressure Range and Rated Pressure Range," "Functions" ⇒ p. 17 "Internal Circuits and Wiring Examples" → p. 18 "Dimensions" → From p. 20



3-Screen Display High-Precision Digital Pressure Switch **ZSE20A(F)/ISE20A Series** 

#### For details on the specific product precautions, refer to the "Operation

### Specifications

Manual" on the SMC website.

	Mo	odel	ZSE20A (Vacuum pressure)	ZSE20AF (Compound pressure)	ISE20A (Positive pressure)
Applicable fluic	1		Air, ۱	Non-corrosive gas, Non-flammabl	e gas
	Rated pre	ssure range	0.0 to -101.0 kPa	-100.0 to 100.0 kPa	-0.100 to 1.000 MPa
Dreesure	Display/S	et pressure range	10.0 to -105.0 kPa	-105.0 to 105.0 kPa	-0.105 to 1.050 MPa
Pressure	Display/S	mallest settable increment	0.1	kPa	0.001 MPa
	Withstand pressure		500	) kPa	1.5 MPa
	Power supply voltage		12 to 1	24 VDC ±10%, Ripple (p-p) 10%	or less
Power supply	Current c	onsumption		35 mA or less	
	Protection			Polarity protection	
	Display accuracy		±2% F.S.	±1 digit (Ambient temperature of	25 ±3°C)
	Repeatab	ility		±0.2% F.S. ±1 digit	
Accuracy	Analog ou	Itput accuracy	±2.5%	F.S. (Ambient temperature of 25	±3°C)
-	-	Itput linearity		±1% F.S.	
	Temperat	ure characteristics		±2% F.S. (25°C standard)	
	Output ty		N	PN or PNP open collector 2 output	uts
	Output m		Hysteresis mode,	Window comparator mode, Error	output, Output OFF
	Switch op			Normal output, Reversed output	
	Max. load			80 mA	
		ied voltage (NPN only)		28 V	
Switch output	Internal voltage drop (Residual voltage)		1	V or less (at load current of 80 m	A)
	Delay time*1 Hysteresis mode Window comparator mode			i-chattering function: 20, 100, 500	
					, 1000, 2000, 0000
			Variable from 0*2		
	Short circuit protection		Yes		
	Voltage Output type		Voltage out	tput: 1 to 5 V	Voltage output: 0.6 to 5 V
	output Output impedance		l lonage ea	Approx. 1 kΩ	
	• a.p.a.	Output type	Current outp	ut: 4 to 20 mA	Current output: 2.4 to 20 mA
Analog output	Current	0	· · · · · · · · · · · · · · · · · · ·	mpedance at power supply voltage	•
	output	Load impedance	Maximum load l	at power supply voltage	
			Minimum load impedance: 50 $\Omega$		
	Input type	<u> </u>		Non-voltage input: 0.4 V or less	P
Auto-shift	Input mod		Se	lect from Auto-shift or Auto-shift z	rero
nput	Input time			5 ms or more	
	Unit*3	•	MPa kPa kof/cm <sup>2</sup>	bar, psi, inHg, mmHg	MPa, kPa, kgf/cm <sup>2</sup> , bar, psi
	Display ty	ne		LCD	
	Number o	•	3-0000	en display (Main screen, Sub scre	2en x 2)
			0-50166	1) Main screen: Red/Green	
Display	Display co	blor	2) Sub screen: Red/Green		
			1) Main screen: 4 di		
	Number o	f display digits	,	gits (Upper 1 digit 11 segments, 7	' segments for other)
	Indicator	liaht			
Digital filter*4	mulcator	ngin	Lights up when switch output is turned ON. OUT1, OUT2: Orange 0, 10, 50, 100, 500, 1000, 5000 ms		
	Enclosure			IP40	10
	Withstand		1000 \/AC	for 1 minute between terminals a	nd housing
Environment		resistance			
Invironment			50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing Operating: –5 to 50°C, Stored: –10 to 60°C (No condensation or freezing)		
		temperature range			
	Operating	humidity range	Operating/Stored: 35 to 85%RH (No condensation)		
Standards				UL/CSA (E216656), CE, RoHS	
ength of lead	wire with c	onnector		2 m	

\*1 Value without digital filter (at 0 ms)

\*2 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value greater than the amount of fluctuation, or chattering will occur.

\*3 Setting is only possible for models with the units selection function. Only MPa or kPa is available for models without this function.

\*4 The response time indicates when the set value is 90% in relation to the step input.

\* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

#### **Piping Specifications and Weights**

Model		M5	01	N01	
Port size		M5 x 0.8	R1/8	NPT1/8	
Sensor pressure receiving area Silicon					
contact with fluid	Aterials of parts in Piping port (Common)		PBT, CB156, Heat-resistant PPS, O-ring: HNBR		
contact with hulu	Piping port	<ul> <li>C3604 (Electroless nickel plating), Stainless steel 304, NE</li> </ul>		ing), Stainless steel 304, NBR	
Waight	Body	24 g	34 g	36 g	
Weight	Lead wire with connector		+39 g		

#### **Cable Specifications**

Conduct	or area	0.15 mm <sup>2</sup> (AWG26)	
Insulator O.D. Color		1.0 mm	
insulator	Color	Brown, Blue, Black, White, Gray (5-core)	
Sheath	Finished O.D.	ø3.5	


ZSE20(F)/ISE20

Made to Order

"Set Pressure Range and Rated Pressure Range," "Functions" ⇒ p. 17 "Internal Circuits and Wiring Examples" ➡ From p. 18 "Dimensions" ➡ From p. 20



# 2 Outputs + Analog Output (Voltage/Current) ( C C C C Us 3-Screen Display High-Precision Digital Pressure Switch IP65 **ZSE20B(F)/ISE20B Series**



7S-46-N2

NPT1/8 Piping adapter

3-Screen Display High-Precision Digital Pressure Switch **ZSE20B(F)/ISE20B Series** 

### Specifications

For details on the specific product precautions, refer to the "Operation Manual" on the SMC website.

	M	odel	ZSE20B (Vacuum pressure)	ZSE20BF (Compound pressure)	ISE20B (Positive pressure)
Applicable fluid	۲. د		Air, N	Non-corrosive gas, Non-flammable	e gas
	Rated pre	essure range	0.0 to -101.0 kPa	-100.0 to 100.0 kPa	-0.100 to 1.000 MPa
Pressure	Display/S	et pressure range	10.0 to -105.0 kPa	-105.0 to 105.0 kPa	-0.105 to 1.050 MPa
Pressure	Display/Smallest settable increment		0.1	kPa	0.001 MPa
	Withstand	d pressure	500	kPa	1.5 MPa
		pply voltage	12 to 2	24 VDC ±10%, Ripple (p-p) 10% o	or less
Power supply	Current c	onsumption		35 mA or less	
	Protection			Polarity protection	
	Display accuracy		±2% F.S.	$\pm 1$ digit (Ambient temperature of	25 ±3°C)
	Repeatab			±0.2% F.S. ±1 digit	
Accuracy	-	utput accuracy	±2.5%	5 F.S. (Ambient temperature of 25	±3°C)
		utput linearity		±1% F.S.	
		ure characteristics		±2% F.S. (25°C standard)	
	Output ty	•		PN or PNP open collector 2 outpu	
	Output me			Nindow comparator mode, Error o	
	Switch op			Normal output, Reversed output	
		Max. load current 80 mA			
Switch output		plied voltage (NPN only) 28 V			
Switch output	Internal voltage drop (Residual voltage)			V or less (at load current of 80 m	/
	Delay time		1.5 ms or less (with ant	i-chattering function: 20, 100, 500	), 1000, 2000, 5000 ms)
	Hysteresis	Hysteresis mode	Variable from 0*2		
	Window comparator mode				
		cuit protection	Yes		
	Voltage	Output type			Voltage output: 0.6 to 5 V
	output	Output impedance		Approx. 1 kΩ	
Analog output	í I	Output type	Current outpu		
Analog output	Current	1	Maximum load in	mpedance at power supply voltag	
	output	Load impedance		at power supply voltag	
	Ļ'	L	Minimum load impedance: 50 Ω		
Auto-shift	Input type		L	Non-voltage input: 0.4 V or less	
input	Input mod		Select from Auto-shift or Auto-shift zero.		
per	Input time	<u>+</u>		5 ms or more	
	Unit*3		MPa, kPa, kgf/cm <sup>2</sup> , k	bar, psi, inHg, mmHg	MPa, kPa, kgf/cm <sup>2</sup> , bar, psi
	Display ty	•		LCD	
	Number o	f screens	3-scree	en display (Main screen, Sub scre	en x 2)
Display	Display co	olor		1) Main screen: Red/Green	
			2) Sub screen: Orange		
	Number c	of display digits	1) Main screen: 4 di		
			2) Sub screen: 4 digits (Upper 1 digit 11 segments, 7 segments for other)		
	Indicator	light	Lights up when switch output is turned ON. OUT1, OUT2: Orange		
Digital filter*4	· <u> </u>		0, 10, 50, 100, 500, 1000, 5000 ms		
	Enclosure	-		IP65	· · · · · · · · · · · · · · · · · · ·
_	Withstand	0		for 1 minute between terminals an	
Environment		n resistance		neasured via megohmmeter) betw	
	_ · _ ·	g temperature range		°C, Stored: –10 to 60°C (No conde	
	Operating	g humidity range	Operating	g/Stored: 35 to 85%RH (No conde	ensation)
Standards				UL/CSA (E216656), CE, RoHS	
Length of lead wire with connector			2 m		

\*2 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value greater than the amount of fluctuation, or chattering will occur.

\*3 Setting is only possible for models with the units selection function. Only MPa or kPa is available for models without this function.

\*4 The response time indicates when the set value is 90% in relation to the step input.

\* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

#### **Piping Specifications and Weights**

Model		M5	01	N01
Port size		M5 x 0.8	R1/8	NPT1/8
Materials of seats in	Sensor pressure receiving area		Silicon	
Materials of parts in contact with fluid	Piping port (Common)	PBT, CB156, Heat-resistant PPS, O-ring: HNBR		
contact with hulu	Piping port	<ul> <li>C3604 (Electroless nickel plating), Stainless steel 30</li> </ul>		ing), Stainless steel 304, NBR
Waight	Body	24 g	34 g	36 g
Weight	Lead wire with connector	+39 g		

#### **Cable Specifications**


Conduct	or area	0.15 mm <sup>2</sup> (AWG26)	
Inculator	0.D.	1.0 mm	
Insulator	Color	Brown, Blue, Black, White, Gray (5-core)	
Sheath Finished O.D.		ø3.5	

Function Details Made to Order

"Set Pressure Range and Rated Pressure Range," "Functions" ⇒ p. 17 "Internal Circuits and Wiring Examples" ➡ From p. 18 "Dimensions" ➡ From p. 20



# IO-Link Compatible (1 Output) 3-Screen Display High-Precision Digital Pressure Switch **ZSE20B(F)-L/ISE20B-L Series**



# 3-Screen Display High-Precision Digital Pressure Switch **ZSE20B(F)-L/ISE20B-L Series**

## Specifications/IO-Link Compatible

For details on the specific product precautions, refer to the "Operation Manual" on the SMC website.

ZSE20(F)/ISE20

ZSE20A(F)/ISE20A

ZSE20B(F)/ISE20B

Model		ZSE20B-L (Vacuum pressure)	ZSE20BF-L (Compound pressure)	ISE20B-L (Positive pressure)	
Applicable fluid	1	-	Air, Non-corrosive gas, Non-flammable gas		
	Rated press	ure range	0.0 to -100.0 kPa	-100.0 to 100.0 kPa	0.000 to 1.000 MPa
D	Display/Set	pressure range	10.0 to -105.0 kPa	-105.0 to 105.0 kPa	-0.105 to 1.050 MPa
Pressure	Display/Smallest settable increment		0.1	kPa	0.001 MPa
	Withstand pressure		500	kPa	1.5 MPa
	Power supply When used as a switch output device (When not used as an IO-Link device)		12 to 24 V	/DC $\pm$ 10% with 10% voltage ripp	le or less
Power supply	voltage	When used as an IO-Link device	18 t	o 30 VDC, including ripple (p-p) 1	10%
	Current con	sumption		35 mA or less	
	Protection			Polarity protection	
	Display acc	uracy	±2% F.S.	±1 digit (Ambient temperature of	25 ±3°C)
Accuracy	Repeatabilit	У		±0.2% F.S. ±1 digit	
	Temperature	e characteristics		±2% F.S. (25°C standard)	
	Output type	Output type Select from NPN or PNP open collector output.		output.	
	Output mod	e		Vindow comparator, Error output,	
	Switch oper	ation		Normal output, Reversed output	
-	Max. load cu	urrent		80 mA	
Switch output	Max. applied	ax. applied voltage 30 V (NPN output)			
(SIO mode)	Internal voltage drop (Residual voltage)		1.5	V or less (at load current of 80 n	nA)
	Delay time*	1	1.5 ms or less, variable from 0 to 60 s/0.01 s increments		increments
-		ysteresis mode /indow comparator mode		Variable from 0*2	
-	Short circuit	t protection	Yes		
	Unit*3			MPa, kPa, kgf/cm², bar, psi	
-	Display type	)			
<b></b> .	Number of s		3-screen display (Main screen, Sub screen x 2)		en x 2)
Display	Display cold	or	Main screen: Red/Green, Sub screen: Orange		Drange
-	Number of c	lisplay digits	Main screen: 4 digits (7 segments)	Sub screen: 4 digits (Upper 1 digit 1	1 segments, 7 segments for other)
-	Indicator lig	ht		witch output is turned ON (OUT1	
Digital filter*4			Vari	able from 0 to 30 s/0.01 s increm	ents
Length of lead	wire with cor	nector		2 m	
	Enclosure			IP65	
Ē	Withstand v	oltage	1000 VAC	for 1 minute between terminals a	nd housing
Environment	Insulation re	esistance	50 M $\Omega$ or more (500 VDC m	neasured via megohmmeter) betw	ween terminals and housing
	Operating te	emperature range	Operating: -5 to 50°	C, Stored: -10 to 60°C (No cond	ensation or freezing)
	Operating h	umidity range	Operating	g/Stored: 35 to 85%RH (No cond	ensation)
Standards				CE, RoHS	
	IO-Link type	9		Device	
	<b>IO-Link vers</b>	ion		V1.1	
	Communica	tion speed		COM2 (38.4 kbps)	
	Configuratio	on file		IODD file*5	
Communication	Minimum cy	cle time		2.3 ms	
(IO-Link mode)	Process dat	a length	Inpu	ut data: 2 bytes, Output data: 0 by	/tes
	On request	data communication		Yes	
	Data storage	e function		Yes	
	Data storage function		Event function Yes		
	Event functi	011		res	

\*1 Value without digital filter (at 0 ms)

\*2 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value greater than the amount of fluctuation, or chattering will occur.

\*3 Setting is only possible for models with the units selection function. Only MPa or kPa is available for models without this function.

\*4 The response time indicates when the set value is 90% in relation to the step input.

\*5 The configuration file can be downloaded from the SMC website, http://www.smcworld.com

\* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

#### **Piping Specifications and Weights**

Model		M5	01	N01	
Port size		M5 x 0.8 R1/8 NPT1/8			
Materiala of nexts in	Sensor pressure receiving area		Silicon		
Materials of parts in contact with fluid	Piping port (Common)	PBT, CB156, Heat-resistant PPS, O-ring: HNBR			
	Piping port	<ul> <li>C3604 (Electroless nickel plating), Stainless steel 304, 1</li> </ul>		ing), Stainless steel 304, NBR	
Weight	Body	24 g	34 g	36 g	
weight	Lead wire with connector		+39 g		

#### **Cable Specifications**

Conduct	or area	0.15 mm <sup>2</sup> (AWG26)			
Inculator	0.D.	1.0 mm			
Insulator	Color	Brown, Blue, Black, White, Gray (5-core)			
Sheath	Finished O.D.	ø3.5			

Function Details Made to Order

"Set Pressure Range and Rated Pressure Range," "Functions" ⇒ p. 17 "Internal Circuits and Wiring Examples" → p. 19 "Dimensions" → From p. 20



## **ZSE20** (F)/ISE20 Series


### Set Pressure Range and Rated Pressure Range

#### Set the pressure within the rated pressure range.

The set pressure range is the range of pressure within which setting is possible. The rated pressure range is the range of pressure that satisfies the specifications (accuracy, linearity, etc.) of the switch. Although it is possible to set a value outside the rated pressure range, the specifications cannot be guaranteed even if the value stays within the set pressure range.


	witch			Pressu	re range	
0	witch	–100 kPa	0	100 kPa	500 kPa	1 MPa
For vacuum pressure	ZSE20 ZSE20A ZSE20B ZSE20B-L	–101 kPa –105 kPa –100 kPa	0	0 kPa		
For compound pressure	ZSE20F ZSE20AF ZSE20BF ZSE20BF-L	–100 kPa –105 kPa –100 kPa		100 kPa 105 kPa 100 kPa		
For positive pressure	ISE20 ISE20A ISE20B ISE20B-L	-100 kPa -105 kPa (-0.105 MPa)	0			1 MPa 1.05 MPa 1 MPa
		Rated pressure range of t	ne switch	Set pressure range	of the switch Rated pres	ssure range of the IO-Link product

## Analog Output<sup>\*1</sup>



### **IO-Link: Process Data**

#### Relationship between the process data and pressure value




### **Functions**

Sub screen setting function	The display of the sub screen can be selected.
Auto-preset function	This function calculates a rough set value automatically based on the on-going operation.
Display value fine adjustment function	Evens out deviations in the displayed value
Peak value indication function	Can retain the maximum pressure value displayed during measurement
Bottom value indication function	Can retain the minimum pressure value displayed during measurement
Keylock function (Selectable security code)	The keyboard can be locked to prevent the accidental operation of the operation switch.
Zero-clear function	The pressure display can be set to zero when the pressure is open to the atmosphere.
Error indication function	This function displays the error location and content when a problem or error has occurred.
Anti-chattering function	Prevents possible malfunctions due to sudden fluctuations in the primary pressure by adjusting the delay time
Units selection function	Can convert the display value
Power saving mode	Reduces power consumption
Display resolution switch function	Converts the display resolution from the normal value of 1/1000 to 1/100 Can reduce flickering of the monitor
$\textbf{kPa} \leftrightarrow \textbf{MPa} \textbf{ switch function}$	Converts the unit between kPa and MPa
Copy function*1	The settings of the master sensor can be copied to the slave sensors.
Auto-shift function <sup>*1</sup>	Measures the pressure at the time of external input and uses it as a reference to correct the set value of the switch
*1 Not available for the 20/20B-L	

**SMC** 

e for the 20/20B-L



\*1 Refer to p. 37.


18


Function Details

Made to Order


# **ZSE20** (F)/ISE20 Series

### Internal Circuits and Wiring Examples






### -R: NPN (2 outputs) + Copy function -S: NPN (2 outputs) + Copy function




\*1 Refer to p. 37.




### -L: (IO-Link/Switch: 1 output)


When used as a switch output device (When not used as an IO-Link device = When in SIO mode) NPN open collector 1 output setting PNP open collector 1 output setting




#### When used as an IO-Link device




### -T: PNP (2 outputs) + Auto-shift input -V: PNP (2 outputs) + Auto-shift input




### -T: PNP (2 outputs) + Copy function -V: PNP (2 outputs) + Copy function








## **ZSE20** (F)/ISE20 Series




# 3-Screen Display High-Precision Digital Pressure Switch **ZSE20** (F)/ISE20 Series




## **ZSE20** (F)/ISE20 Series

### **Dimensions**


### Panel fitting dimensions




Multiple (2 pcs. or more) secure mounting <Horizontal>




Panel mount example <Horizontal>




Panel mount example <Vertical>



<Vertical> 0 31<sub>-0.4</sub> 24 or more 31 x n pcs. + 3.5 x (n pcs. -1)





# ZSE20C(F)/ISE20C(H) Series

For details on the specific product precautions, refer to the "Operation Manual" on the SMC website.

### **Specifications**

Applicable fluid Pressure	1					ISE20CH (Positive pressure)		
Pressure			Liquids a	ind gases that do not co	rrode stainless steel 630	and 304		
Pressure	Rated pre	ssure range	0.0 to -101.0 kPa	-100.0 to 100.0 kPa	-0.100 to 1.000 MPa	-0.100 to 2.000 MPa		
Pressure	Display/S	et pressure range	10.0 to -105.0 kPa	-105.0 to 105.0 kPa	-0.105 to 1.050 MPa -0.105 to 2.100 MF			
-	Display/S	mallest settable increment	0.1 kPa		0.001	I MPa		
	Withstand	l pressure	500	kPa	2 MPa	4 MPa		
	Power su	oply voltage	1	2 to 24 VDC ±10% with	10% voltage ripple or les	S		
Power supply	Current c	onsumption		35 mA	or less			
	Protection			Polarity p	protection			
	Display ad	ccuracy	±	2% F.S. ±1 digit (Ambier	nt temperature of 25 $\pm$ 3°C	C)		
	Repeatab	ility		±0.2% F.	S. ±1 digit			
Accuracy	Analog ou	itput accuracy		±2.5% F.S. (Ambient te	emperature of 25 ±3°C)			
	Analog ou	itput linearity		±1%	5 F.S.			
	Temperat	ure characteristics		±3% F.S. (25	°C standard)			
	Output ty	pe		NPN or PNP open	collector 2 outputs			
	Output me	ode	Hysteresis	· · ·	tor mode, Error output, 0	Output OFF		
	Switch op	eration		Normal output,	Reversed output			
	Max. load	current			mA			
Switch output	Max. appl	ied voltage (NPN only)		28	3 V			
omion output		Itage drop (Residual voltage)		(	d current of 80 mA)			
	Delay time	<b>e</b> *1	1.5 ms or less (with anti-chattering function: 20, 100, 500, 1000, 2000, 5000 ms)					
	Hysteresis	Hysteresis mode		Variable from 0*2				
	,	Window comparator mode						
	Short circ	uit protection			es	1		
	Voltage	Output type	Voltage out		Voltage output: 0.6 to 5 V	Voltage output: 0.8 to 5 V		
	output	Output impedance			x. 1 kΩ	1		
Analog output		Output type	Current output: 4 to 20 mA Current output: 2.4 to 20 mA Current output: 3.2 to 20 mA					
	Current output	Load impedance	Maximum load impedance at power supply voltage of 12 V: 300 $\Omega$ at power supply voltage of 24 V: 600 $\Omega$ Minimum load impedance: 50 $\Omega$					
	Input type	)	Non-voltage input: 0.4 V or less					
Auto-shift	Input mod	le	Select from Auto-shift or Auto-shift zero.					
input	Input time	)	5 ms or more					
	Unit*3		MPa, kPa, kgf/cm <sup>2</sup> , b	ar, psi, inHg, mmHg	MPa, kPa, kg	ſ/cm², bar, psi		
	Display ty	ре	LCD					
	Number o	f screens	3-screen display (Main screen, Sub screen x 2)					
Display	Display color		1) Main screen: Red/Green 2) Sub screen: Orange					
	Number o	f display digits	<ol> <li>Main screen: 4 digits (7 segments)</li> <li>Sub screen: 4 digits (Upper 1 digit 11 segments, 7 segments for other)</li> </ol>					
	Indicator	light	Lights up when switch output is turned ON (OUT1, OUT2: Orange)					
Digital filter*4			0, 10, 50, 100, 500, 1000, 5000 ms					
	Enclosure	)		IP	65			
	Withstand	l voltage	250 VAC for 1 minute between terminals and housing					
Environment	Insulation	resistance	2 M $\Omega$ or more (50	VDC measured via meg	ohmmeter) between tern	ninals and housing		
	Operating	temperature range	Operating: -	5 to 50°C, Stored: -10 to	o 60°C (No condensation	n or freezing)		
	Operating	humidity range	C	perating/Stored: 35 to 8	5%RH (No condensatior	ו)		
Standards			UL/CSA (E216656), CE, RoHS					
Length of lead	wire with c	onnector		2	m			

\*1 Value without digital filter (at 0 ms)

\*2 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value greater than the amount of fluctuation, or chattering will occur.

\*3 Setting is only possible for models with the units selection function. Only MPa or kPa is available for models without this function.

\*4 The response time indicates when the set value is 90% in relation to the step input.

\* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

#### **Piping Specifications and Weights**

1 191115	iping opeenieutiene and weighte								
	Model	02	N02	F02	C01	A2	B2		
Port siz	ze	R1/4	R1/4 NPT1/4 G1/4 Rc1/8		URJ1/4	TSJ1/4			
Materials	of parts in contact with fluid	ct with fluid Pressure sensor: Stainless steel 630, Fitting: Stainless stee					steel 304		
	Body (Rear ported)	51 g	51 g	48 g	47 g	54 g	46 g		
Weight	Body (Bottom ported)	77 g	78 g	74 g	65 g	81 g	72 g		
	Lead wire with connector	+39 g							

#### **Cable Specifications**

Conductor area		0.15 mm <sup>2</sup> (AWG26)
Insulator	0.D.	1.0 mm
insulator	Color	Brown, Blue, Black, White, Gray (5-core)
Sheath	Finished O.D.	ø3.5



# 3-Screen Display High-Precision Digital Pressure Switch for General Fluids ZSE20C(F)/ISE20C(H) Series


#### Set Pressure Range and Rated Pressure Range

#### Set the pressure within the rated pressure range.

The set pressure range is the range of pressure within which setting is possible. The rated pressure range is the range of pressure that satisfies the specifications (accuracy, linearity, etc.) of the switch. Although it is possible to set a value outside the rated pressure range, the specifications cannot be guaranteed even if the value stays within the set pressure range.

Cudal	- In	Pressure range							티벌		
Switch	n -	-100	) kPa	0	100	) kPa	500 kPa	1	MPa	2 MPa	10 10 10
For	25000	–101 kPa 🛛	1	0							ZSE20
vacuum ZS pressure	SE20C	–105 kPa	1		10 kPa						
For		–100 kPa				100 kPa					
compound ZS pressure	SE20CF	–105 kPa	i !	i		105 kPa					
		-100 kPa		1		1			1 MPa		20A
For	E20C	–105 kPa (–0.105 MPa)	! 						1.05 MPa	l l	
positive		–100 kPa		1			1			2 MPa	A(F)/ISI
ISE	E20CH	–105 kPa	1			1	1		<u>'</u>	2.1 MPa	
1 1		(–0.105 MPa)							, · ·	· · · · · · · · · · · · · · · · · · ·	ZSE20/

### Analog Output



Range	Rated pressure range	Α	В	С
For vacuum pressure	0.0 to –101.0 kPa	10.1 kPa	0	–101.0 kPa
For compound pressure	-100.0 to 100.0 kPa	—	–100.0 kPa	100.0 kPa
For positive	-0.100 to 1.000 MPa	–0.100 MPa	0	1.000 MPa
pressure	-0.100 to 2.00 MPa	-0.100 MPa*1	0	2.00 MPa

\*1 Analog output is 0.8 [V] or 3.2 [mA] at the pressure A.

## **Functions**

Sub screen setting function	The display of the sub screen can be selected.
Auto-preset function	This function calculates a rough set value automatically based on the on-going operation.
Display value fine adjustment function	Evens out deviations in the displayed value
Peak value indication function	Can retain the maximum pressure value displayed during measurement
Bottom value indication function	Can retain the minimum pressure value displayed during measurement
Keylock function (Selectable security code)	The keyboard can be locked to prevent the accidental operation of the operation switch.
Zero-clear function	The pressure display can be set to zero when the pressure is open to the atmosphere.
Error indication function	This function displays the error location and content when a problem or error has occurred.
Anti-chattering function	Prevents possible malfunctions due to sudden fluctuations in the primary pressure by adjusting the delay time
Units selection function	Can convert the display value
Power saving mode	Reduces power consumption
Display resolution switch function	Converts the display resolution from the normal value of 1/1000 to 1/100
Display resolution switch function	Can reduce flickering of the monitor
$\textbf{kPa} \leftrightarrow \textbf{MPa} \textbf{ switch function}$	Converts the unit between kPa and MPa
Copy function	The settings of the master sensor can be copied to the slave sensors.
Auto-shift function	Measures the pressure at the time of external input and uses it as a reference to correct the set value of the switch


ZSE20C(F)/ISE20C(H) ZSE20B(F)-L/ISE20B-L




ZSE20(F)/ISE20

ZSE20B(F)/ISE20B


# ZSE20C(F)/ISE20C(H) Series




# -R: NPN (2 outputs) + Analog voltage output -S: NPN (2 outputs) + Analog current output




### -R: NPN (2 outputs) + Auto-shift input -S: NPN (2 outputs) + Auto-shift input




### -R: NPN (2 outputs) + Copy function -S: NPN (2 outputs) + Copy function




#### -T: PNP (2 outputs) + Analog voltage output -V: PNP (2 outputs) + Analog current output




#### -T: PNP (2 outputs) + Auto-shift input -V: PNP (2 outputs) + Auto-shift input




#### -T: PNP (2 outputs) + Copy function -V: PNP (2 outputs) + Copy function




3-Screen Display High-Precision Digital Pressure Switch for General Fluids **ZSE20C(F)/ISE20C(H)** Series




# ZSE20C(F)/ISE20C(H) Series




3-Screen Display High-Precision Digital Pressure Switch for General Fluids **ZSE20C(F)/ISE20C(H)** Series




# ZSE20C(F)/ISE20C(H) Series





Ε


Panel mount adapter (Bottom ported) (Part no.: ZS-35-B)



<u>8888</u>


8888 8888 •••••


34.5




Panel thickness 0.5 to 7

6.3






3-Screen Display High-Precision Digital Pressure Switch for General Fluids **ZSE20C(F)/ISE20C(H)** Series




# ZSE20C(F)/ISE20C(H) Series

### Dimensions


### Panel fitting dimensions (Rear ported)



Panel mount example <Horizontal>



Panel mount example <Vertical>




Panel fitting dimensions (Bottom ported)


\* + P3-04 1855




<Horizontal>

Multiple (2 pcs. or more) secure mounting







# ZSE20 (F)/ISE20 Series

### **Function Details**

The  $\mathsf{F}\square$  in ( ) shows the function code number. Refer to the operation manual for details about operation procedures and function codes.

When using with IO-Link, the set values cannot be changed by

H 1


H\_1=|(A-B)/2|

#### A Auto-preset function (F4)

Auto-preset function, when selected in the initial setting, calculates and stores the set value from the measured pressure. For example, if this function is used for suction verification, the optimum set value is determined automatically by performing suction and release of several workpieces.


communication.

#### Suction Verification



#### **B** Display value fine adjustment function (F6)

Fine adjustment of the indicated value of the pressure sensor can be made within the range of  $\pm 5\%$  of the read value. (The scattering of the indicated value can be eliminated.)



#### When the display value fine adjustment function is used, the set pressure value may change $\pm 1$ digit.

#### C Peak/Bottom value display

This function constantly detects and updates the maximum (minimum) pressure when the power is supplied, and allows to hold the maximum (minimum) pressure value.

The held value is maintained even if the power supply is cut. When the **s** and **v** buttons are simultaneously pressed for 1 second or longer, while "holding", the held value will be reset.

#### D Keylock function

Formula for Obtaining the Set Value

P\_1 or n\_1


P\_1=A-(A-B)/4

 $n_1 = B + (A - B)/4$ 

Prevents operation errors such as accidentally changing setting values

Indicated value at the time of shipment

value fine adjustment function



This function clears and resets the zero value on the display of measured pressure.

The indicated value can be adjusted within  $\pm 7\%$  F.S. of the pressure when ex-factory. (ZSE20 F (for compound pressure): ±3.5% F.S.)

#### F Error display function

When an error or abnormality arises, the location and contents are displayed.

Error name	Error code	Description	Action	
Over current error		Load current of 80 mA or more is applied to the switch output.	Turn the power off and remove the cause of the over current. Then supply the power again.	
Residual pressure error	<b>[r]</b> IEro	During zero-clear operation, pressure over $\pm$ 7% F.S. ( $\pm$ 3.5% F.S. for compound pressure) is present. Note that the mode is returned to measurement mode automatically 1 second later. The zero clear range varies by $\pm$ 1% F.S. due to variation between individual products.	Perform zero-clear operation again after restoring the applied pressure to an atmospheric pressure condition.	
Applied	XXX	Supply pressure exceeds the maximum set pressure.	Reset applied pressure to a level	
pressure error		Supply pressure is below the minimum set pressure.	within the set pressure range	
System error	Er 0 Er 7 Er 4 Er 8 Er 6 Er 9	Internal data error	Turn the power off and then on again. If the failure cannot be solved, please contact SMC for investigation.	
Copy error	<b>Er 13</b> St Ru	The copy function does not operate properly.	After clearing the error by pressing the and buttons simultaneously for a mini- mum of 1 second, check the wiring and the model, and then attempt to copy again.	
IO-Link master version error	Er 15	IO-Link version does not match that of the master.	Ensure that the master IO-Link version matches the device version.	

If the error cannot be reset after the above measures are taken, or errors other than those above are displayed, please contact SMC for investigation.


#### Function Details **ZSE20 (F)**/**ISE20** Series

### **Function Details**

The  $\mathsf{F}\square$  in ( ) shows the function code number. Refer to the operation manual for details about operation procedures and function codes


#### G Anti-chattering function (Simple setting mode or F1)

A large bore cylinder or ejector consumes a large volume of air in operation and may experience a temporary drop in the supply pressure. This function prevents detection of such temporary drops in the supply pressure as an error by changing the delay time setting.



<Principle>

This function averages pressure values measured during the response time set by the user and then compares the average pressure value with the pressure set point value to output the result on the switch.



#### H Units selection function (F0)

Display units can be switched with this function.

Display unit	MPA	kPA	kGF	bAr	PSi	inCH	mmHG
Smallest settable increment	MPa*1	kPa	kgf/cm <sup>2</sup>	bar	psi	inHg	mmHg
ZSE20□ (Vacuum pressure)	0.001	0.1	0.001	0.001	0.01	0.1	1
ZSE20□F (Compound pressure)	0.001	0.1	0.001	0.001	0.02	0.1	1
ISE20□ (Positive pressure)	0.001	1	0.01	0.01	0.1		
ISE20□H (Positive pressure)	0.001	1	0.01	0.01	0.2		

\*1 The ZSE20 (vacuum pressure) and ZSE20 F (compound pressure) will have different setting and display resolution when the unit is set to MPa.

#### Selection of power saving mode (F80)

The power saving mode can be selected.

It shifts to the power saving mode without button operation for 30 seconds.

It is set to the normal mode (Power saving mode is OFF.) at a time of shipment from the factory.

(During power saving mode, [ECo] will flash in the sub screen and the operation light will be ON (only when the switch is ON).)

#### J Setting of security code (F81)

The user can select whether a security code must be entered to release the key lock. At a time of shipment from the factory, it is set such that a security code is not required.


# ZSE20 (F)/ISE20 Series

## The F $\square$ in ( ) shows the function code number. Refer to the operation manual for details about operation procedures and function codes.

### **Function Details**


#### K Copy function (F97) (Z/ISE20A, 20B, 20C series only)

The settings of the master sensor can be copied to the slave sensors, reducing setting labor and minimizing the risk of setting mistakes. The set value can be copied to up to 10 switches simultaneously. (Maximum transmission distance: 4 m)



L Auto-shift function (F5) (Z/ISE20A, 20B, 20C series only)

When there are large fluctuations in the supply pressure, the switch may fail to operate correctly. The auto-shift function compensates for such supply pressure fluctuations. It measures the pressure at the time of auto-shift signal input and uses it as the reference pressure to correct the set value on the switch.



\*1 When delay time is 1.5 ms or less

When the auto-shift function is selected, " $\Re_{1,0} = _{000}$ " will be displayed on the sub screen for about 1 second, and the pressure value at that point will be saved as reference value " $\ell_{2,5}$ ." Based on the saved reference value, output on-off points controlled by set values<sup>\*2</sup> such as " $p_{2,1}$ ," " $\mu_{2,1}$ ," " $p_{2,2}$ ," and " $\mu_{2,2}$ " will also be rectified.

\*2 When an output is reversed, output on-off points displayed at " $n_{-}$  I," " $H_{-}$  I," " $n_{-}$  Z," and " $H_{-}$  Z" will be rectified.

The above is an example in hysteresis mode. On-off points are similarly rectified in window comparator mode. Outputs that enable the auto-shift function can be changed via the settings. \* This function is not provided with the IO-Link compatible type.

- 1) Wire as shown in the figure on the left.
- Select the slave sensor which is to be the master, and change it into a master using the buttons. (In the default setting, all sensors are set as slaves.)
- 3) Press the **S** button on the master sensor to start copying.

\* This function is not provided with the IO-Link compatible type.

#### Settable Range for Auto-Shift Input

	Set pressure range	Settable range
Compound pressure	–105.0 to 105.0 kPa	–210 to 210 kPa
Vacuum pressure	10.0 to –105.0 kPa	115.0 to –115.0 kPa
Positive pressure	-0.105 to 1.050 MPa	-1.155 to 1.155 MPa
Positive pressure*3	-0.105 to 2.100 MPa	-2.20 to 2.205 MPa

\*3 Z/ISE20C series only

#### Auto-shift zero

The basic function of auto-shift zero is the same as that of autoshift. However, it corrects values on the display based on a pressure value of "U", which is set as the reference value when auto-shift function is selected.



ZSE20 (F)/ISE20 Series Made to Order

Please contact SMC for detailed dimensions, specifications, and delivery times.

## 1 Parts in Contact with Fluid: Stainless Steel 316L

This pressure switch has better corrosion resistance because it uses stainless steel 316L for the parts in contact with fluid (pressure sensor and fitting).

Specifications

ZSE20C(F)

500 kPa

Models other than those above have the same specifications

Liquids and gases do not

corrode stainless steel 316L.


Model

Withstand pressure

Applicable fluid

as the standard product.

#### How to Order



#### Enter the standard product number. (Refer to p. 24.)


Not applicable to the rated pressure -0.1 to 2 MPa specifications (ISE20CH).

\* A restrictor (equivalent to -X510) is installed inside the fitting. (Piping specifications A2(L) and B2(L) are excluded.)

## **Restrictor-installed Fitting**

A restrictor is installed inside the fitting in order to reduce the effects of water collision with inertia force in the piping when adsorption is broken.

#### How to Order



### 3 M12 4-pin Pre-wired Connector (Lead wire length 100 mm)


#### Lead Wire with M12 Connector

Series	20	20A	20B(-L)	20C	
ZS-46-5LM12 (Non-waterproof)	0	0	—	—	
ZS-46-5FM12 (Waterproof)	—	—	0	0	
If the second se Second second sec					

If you wish for the sensor (switch body) and the lead wire to be shipped together, please contact SMC.

#### Pin no. Lead wire color Pin name DC (-) Blue 2 Function Gray OUT (2) З White 4 OUT (1) Black 5 DC (+) Brown


#### Connector pin assignment 2 White



Connector size M12

Nothing is connected to "Function." If you intend to make a connection to "Function," please contact SMC

Sheath O.D. ø3.5





ISE20C

1.5 MPa

ZSE20(F)/ISE20

ZSE20C(F)/ISE20C(H)

## ▲ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "**Caution**," "**Warning**" or "**Danger**." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)<sup>\*1</sup>, and other safety regulations.

- Caution: indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.
- Warning: Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

**Danger** indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

### **A**Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

- 2. Only personnel with appropriate training should operate machinery and equipment.
  - The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.
- 3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.
  - The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
  - 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
  - Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

# 4. Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.

- 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
- 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalog.
- An application which could have negative effects on people, property, or animals requiring special safety analysis.
- 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

- \*1) ISO 4414: Pneumatic fluid power General rules relating to systems.
  - ISO 4413: Hydraulic fluid power General rules relating to systems. IEC 60204-1: Safety of machinery – Electrical equipment of machines. (Part 1: General requirements)
  - ISO 10218-1: Manipulating industrial robots Safety. etc.

## 

 The product is provided for use in manufacturing industries. The product herein described is basically provided for peaceful use in manufacturing industries. If considering using the product in other industries, consult SMC beforehand

and exchange specifications or a contract if necessary. If anything is unclear, contact your nearest sales branch.

#### Limited warranty and Disclaimer/ Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

#### Limited warranty and Disclaimer

- The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.\*2) Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.
  - 2) Vacuum pads are excluded from this 1 year warranty. A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

#### **Compliance Requirements**

- The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

## 

## SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

#### **Revision History**

<ul> <li>New variations (for general fluids, IP65, 2 outputs, and analog output) have been added.</li> <li>Number of pages has been increased from 16 to 36.</li> </ul>	VX
 <ul> <li>The IO-Link compatible type has been added.</li> <li>Number of pages has been increased from 36 to 40.</li> </ul>	WR

A Safety Instructions Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.