### **Electric Actuator**



Rod Type | Guide Rod Type



- Intermediate strokes have been added to the LEY63.
- Normally-closed solid state auto switches have been
- The JXC series step motor controller has been added.



Step Motor (Servo/24 VDC) Servo Motor (24 VDC) Type



### Rod Type LEY Series

Size: 16, 25, 32, 40 p. 35

### Long stroke:

Max. 500 mm (LEY32, 40)

### **Mounting variations**

- •Direct mounting: 3 directions, Bracket mounting: 3 types
- · Either positioning or pushing control can be selected. It is possible to hold the actuator with the rod pushing a workpiece, etc.

Rod type Auto switch mountable



Size: 16, 25, 32, 40 p. 105

### Guide Rod Type LEYG Series

Lateral end load: 5 times more\*1

\*1 Compared with the rod type, size 25, and 100 mm stroke

Compatible with sliding bearings and ball bushing bearings Compatible with moment loads and stoppers (sliding bearings)

• Either positioning or pushing control can be selected. It is possible to hold the actuator with the rod pushing a workpiece, etc.





Guide rod type

Guide rod type/ In-line motor type

CE cAL us

Guide rod type/

In-line motor type


**AC Servo Motor Type** 

Rod Type LEY Series Size: 25, 32, 63

**▶**p. **41, 48** Dust-tight/Water-jet-proof (IP65 Equivalent): -X5

- •High-output motor (100/200/400 W)
- Improved high-speed transfer ability · High acceleration/deceleration
- compatible (5000 mm/s<sup>2</sup>) Pulse input/CC-Link/SSCNET

   types
- With internal absolute encoder










- DeviceNet™/IO-Link direct input type JXCE1/91/P1/D1/L1 Series
- ▶ Programless type LECP1 Series (14 positioning points)
- ▶ Pulse input type LECPA Series










Step Motor (Servo/24 VDC) | Servo Motor (24 VDC) | Type

Rod Type | LEY Series/Size: 16, 25, 32, 40

### Control of intermediate positioning and pushing is possible.

High precision with ball screws

(Positioning repeatability: ±0.02 mm)



#### **Rod end brackets**





Double



Applicable to the D-M9□, D-M9□E, and D-M9□W (2-color indicator)


The auto switches should be ordered separately. Refer to pages 101 to 103 for details.



AC Servo Motor Type

### Rod Type LEY Series/Size: 25, 32, 63

- High-output motor (100/200/400 W)
- Improved high-speed transfer ability
- High acceleration/deceleration compatible (5000 mm/s²)
- With internal absolute encoder
- \* An incremental encoder can also be selected.
- Positioning repeatability: ±0.01 mm (High-precision type)



### Large bore size 63

### Selectable motor mounting position (4 directions)









Max. work load [kg]

	Top/Parallel	In-line
Horizontal	200	80
Vertical	115	72

Max. force [N]

Top/Parallel	3343
In-line	1910

- High-output motor: 400 w
- Max. speed: 1000 mm/s
  - \* 500 mm stroke
- Dust-tight/Water-jet-proof specification (IP65 equivalent)
  - Option



Step Motor (Servo/24 VDC) Servo Motor (24 VDC) Type

Guide Rod Type LEYG Series/Size: 16, 25, 32, 40

Compact, integrated guide rods Lateral load resistance and high non-rotating accuracy

Compatible with sliding bearings and ball bushing bearings

 Sliding bearings Suitable for lateral load applications such as when using a stopper where impact is applied

 Ball bushing bearings Smooth operation suitable for pushers and lifters

### Improved rigidity

Lateral end load: 5 times more\*

\*1 Compared with the rod type, size 25, and 100 mm stroke Motor top mounting type



In-line motor type

Non-rotating accuracy improved by using two guide rods


Bore size [mm]	16	25	32	40	
Sliding bearings	±0.	06°	±0.05°		
Ball bushing bearings	±0.05°	±0.04°			

When the cylinder is retracted (initial value), the non-rotating accuracy without a load and without deflection of the guide rods will be below the values shown in the


**AC Servo Motor** Type

Guide Rod Type LEYG Series/Size: 25, 32








When using auto switches for the guide rod type LEYG series, refer to page 187.



### Dust-tight/Water-jet-proof (IP65 Equivalent)








### Simple setting allows for immediate use!

### **O"Easy Mode" for simple setting**

For immediate use, select "Easy Mode."







### <When a TB (teaching box) is used>

- The simple screen without scrolling promotes ease of setting and operation.
- Choose an icon from the first screen to select a function.
- Set the step data and check the monitor on the second screen.









### **Teaching box screen**

 Data can be set by inputting only the position and speed. (Other conditions are preset.)

Step	Axis 1
Step No.	0
Posn	50.00 mm
Speed	200 mm/s



Step	Axis 1
Step No.	1
Posn	80.00 mm
Speed	100 mm/s

### "Normal Mode" for detailed setting


### Select "Normal Mode" when detailed setting is required.

- Step data can be set in detail.
- Parameters can be set.
- Signals and terminal status can be monitored.
- JOG and constant rate movement, return to origin, test drive, and testing of forced output can be performed.

### <When a PC is used> Controller setting software

 Step data setting, parameter setting, monitoring, teaching, etc., are displayed in different windows.






### <When a TB (teaching box) is used>

- Multiple step data can be stored in the teaching box and transferred to the controller.
- Continuous test drive by up to 5 step data

#### **Teaching box screen**


 Each function (step data setting, test drive, monitoring, etc.) can be selected from the main menu.



### The actuator and controller are provided as a set. (They can be ordered separately as well.)

Confirm that the combination of the controller and actuator is correct.

- <Check the following before use.>
- ① Check the actuator label for the model number. This number should match that of the controller.
- ② Check that the Parallel I/O configuration matches (NPN or PNP).



### **Fieldbus Network**

## Fieldbus-compatible Gateway (GW) Unit


LEC-G Series ▶p. 203

Oconversion unit for Fieldbus network and LEC serial communication

Applicable Fieldbus protocols: CC-Link V2 Device Net Properties Ether Net / IP

Two methods of operation
Step data input: Operate using preset step data in the controller.
Numerical data input: The actuator operates using values such as position and speed from the PLC.


O Values such as position and speed can be checked on the PLC.



### Programless Type LECP1 Series Pp. 207


### No programming required!

Allows for the setting up of electric actuator operation without using a PC or teaching box



### Pulse Input Type LECPA Series ▶p. 214

This driver uses pulse signals to allow positioning at any position.
 The actuator can be controlled from the customers' positioning unit.



- Return-to-origin command signal Enables automatic return-to-origin action
- With force limit function (Pushing force/Gripping force operation available) Pushing force/Positioning operation is possible by switching signals.



### **Function**

Item	Step data input type LECA6	Programless type LECP1	Pulse input type LECPA
Step data and parameter setting	<ul><li>Input from controller setting software (PC)</li><li>Input from teaching box</li></ul>	Selected using controller operation buttons	Input from controller setting software (PC)     Input from teaching box
Step data "position" setting	Numerical value input from controller setting software (PC) or teaching box     Input numerical value     Direct teaching     JOG teaching	Direct teaching     JOG teaching	No "Position" setting required     Position and speed set by pulse signal
Number of step data	64 points	14 points	_
Operation command (I/O signal)	Step No. [IN*] input $\Rightarrow$ [DRIVE] input	Step No. [IN*] input only	Pulse signal
Completion signal	[INP] output	[OUT*] output	[INP] output

### Setting Items

TB: Teaching box PC: Controller setting software


Item		Contents		Easy Normal Mode Mode		Programless type LECP1*1	Pulse input type	
			ТВ	РС	TB/PC	LEGPT	LECPA	
	Movement MOD	Selection of "absolute position" and "relative position"	Δ	•	•	Fixed value (ABS)		
	Speed	Transfer speed	•	• • •		Select from 16 levels		
	D ini	[Position]: Target position [Pushing]: Pushing start position				Direct teaching	No setting required	
	Position					JOG teaching		
	Acceleration/Deceleration	Acceleration/deceleration during movement	•	•	•	Select from 16 levels		
Step data	Pushing force	Rate of force during pushing operation	•	•	•	Select from 3 levels (weak, medium, and strong)	Set in units of 1 %	
setting (Excerpt)	Trigger LV	Target force during pushing operation	Δ	•	•	No setting required (same value as pushing force)	Set in units of 1 %	
	Pushing speed	Speed during pushing operation	Δ	•	•		Set in units of 1 mm/s	
	Moving force	Force during positioning operation	Δ	•	•		Set to (Different values for each actuator) %	
	Area output	Conditions for area output signal to turn ON	Δ	•	•		Set in units of 0.01 mm	
	In position	[Position]: Width to the target position [Pushing]: How much it moves during pushing	Δ	•	•	No setting required	Set to (Different values for each actuator) or more (Units: 0.01 mm)	
	Stroke (+)	+ side position limit	×	×	•		Set in units of 0.01 mm	
Parameter	Stroke (-)	- side position limit	×	×	•		Set in units of 0.01 mm	
setting	ORIG direction	Direction of the return to origin can be set.	×	×	•	Compatible	Compatible	
(Excerpt)	ORIG speed	Speed during return to origin	×	×	•	No setting required	Set in units of 1 mm/s	
	ORIG ACC	Acceleration during return to origin	×	×	•	No setting required	Set in units of 1 mm/s <sup>2</sup>	
	JOG		•	•	•	Hold down the MANUAL button $(\bigcirc\bigcirc)$ for uniform sending (speed is a specified value).	Continuous operation at the set speed can be tested while the switch is being pressed.	
Took	MOVE		×	•	•	Press the MANUAL button ((()) once for sizing operation (speed and sizing amount are specified values).	Operation at the set distance and speed from the current position can be tested.	
Test	Return to ORIG		•	•	•	Compatible	Compatible	
	Test drive	Operation of the specified step data	•	•	(Continuous operation)	Compatible	Not compatible	
	Forced output	ON/OFF of the output terminal can be tested.	×	×	•		Compatible	
Monitor	DRV mon	Current position, speed, force, and the specified step data can be monitored.	•	•	•	Not compatible	Compatible	
WOTHER	In/Out mon	Current ON/OFF status of the input and output terminal can be monitored.	×	×	•		Compatible	
AL M	Status	Alarm currently being generated can be confirmed.	•	• • •		Compatible (display alarm group)	Compatible	
ALM	ALM Log record   Alarms generated in the past can be confirmed.		×	×	•		Compatible	
File	Save/Load	Step data and parameters can be saved, forwarded, and deleted.	×	×	•	Not compatible	Compatible	
Other	Language	Can be changed to Japanese or English	•	•	•		Compatible	

<sup>△:</sup> Can be set from TB Ver. 2.\*\* (The version information is displayed on the initial screen.) \*1 The LECP1 programless type cannot be used with the teaching box and controller setting kit.



### **Fieldbus Network**

# EtherCAT®/EtherNet/IP™/PROFINET/ DeviceNet™/IO-Link Direct Input Type Step Motor Controller/JXC□ Series ▶₽.224

















### **Two types of operation command**

**Step no. defined operation**: Operate using the preset step data in the controller.

**Numerical data defined operation**: The actuator operates using values such as position and speed from the PLC.


ONumerical monitoring available


Numerical information, such as the current speed, current position, and alarm codes, can be monitored on the PLC.

### **Transition wiring of communication cables**

Two communication ports are provided.


- \* For the DeviceNet™ type, transition wiring is possible using a branch connector.
- \* 1 to 1 in the case of IO-Link





### **Multi-Axis Step Motor Controller**

- Speed tuning control\*1 (3 Axes: JXC92 4 Axes: JXC73/83/93)
- Linear/circular interpolation




- Positioning/pushing operation
- Step data input (Max. 2048 points)
- Space saving, reduced wiring
- Absolute/relative position coordinate instructions
- \*1 This controls the speed of the following axis when the speed of the primary axis drops due to the effects of an external force and when a speed difference with the following axis occurs. This control is not for synchronizing the position of the primary axis and following axis.

### For 3 Axes JXC92 Series

- EtherNet/IP Type
- Width: Approx. 38 % reduction






### For 4 Axes JXC73/83/93 Series


Parallel I/O/ EtherNet/IP Type

reduction











### Step Data Input: Max. 2048 points



### For 3 Axes

### 3-axis operation can be set collectively in one step.

Step	Axis	Movement	Speed	Position	Acceleration	Deceleration	Pushing	Trigger	Pushing	Moving	Area 1	Area 2	In position	Comments
Siep	AXIS	mode	mm/s	mm	mm/s <sup>2</sup>	mm/s²	force	ĹV		force	mm	mm	mm	Comments
	Axis 1	ABS	500	100.00	3000	3000	0	85.0	50	100.0	10.0	30.0	0.5	
0	Axis 2	ABS	500	100.00	3000	3000	0	85.0	50	100.0	10.0	30.0	0.5	
	Axis 3	ABS	500	100.00	3000	3000	0	85.0	50	100.0	10.0	30.0	0.5	
	Axis 1	INC	500	200.00	3000	3000	0	85.0	50	100.0	0	0	0.5	
1	Axis 2	INC	500	200.00	3000	3000	0	85.0	50	100.0	0	0	0.5	
	Axis 3	INC	500	200.00	3000	3000	0	85.0	50	100.0	0	0	0.5	
						İ	i	İ				İ	İ	
	Axis 1	SYN-I	500	100.00	3000	3000	0	0	0	100.0	0	0	0.5	
2046	Axis 2	SYN-I	0	0.00	0	0	0	0	0	100.0	0	0	0.5	
	Axis 3	SYN-I	0	0.00	0	0	0	0	0	100.0	0	0	0.5	
	Axis 1	CIR-R	500	0.00	3000	3000	0	0	0	100.0	0	0	0.5	
0047	Axis 2	CIR-R	0	50.00	0	0	0	0	0	100.0	0	0	0.5	
2047	Axis 3*1		0	0.00	0	0	0	0	0	100.0	0	0	0.5	
	Axis 4*1		0	25.00	0	0	0	0	0	100.0	0	0	0.5	

\*1 When circular interpolation (CIR-R, CIR-L, CIR-3) is selected in the movement mode, input the X and Y coordinates in the rotation centre position or input the X and Y coordinates in the passing position.

		otation centre position of input the A and 1 coordinates in the passing position.
Movement mode	Pushing operation	Details
Blank	×	Invalid data (Invalid process)
ABS	0	Moves to the absolute coordinate position based on the origin of the actuator
INC	0	Moves to the relative coordinate position based on the current position
LIN-A	×	Moves to the absolute coordinate position based on the origin of the actuator by linear interpolation
LIN-I	×	Moves to the relative coordinate position based on the current position by linear interpolation
CIR-R* <sup>2</sup>	×	With Axis 1 assigned to the X-axis and Axis 2 to the Y-axis, it moves in the clockwise direction by circular interpolation. The target position and rotation centre position are specified according to the relative coordinates from the current position. The position data is assigned as follows.  Axis 1: Target position X  Axis 2: Target position Y  Axis 3*1: Rotation centre position X  Axis 4*1: Rotation centre position Y
CIR-L* <sup>2</sup>	×	With Axis 1 assigned to the X-axis and Axis 2 to the Y-axis, it moves in the counter-clockwise direction by circular interpolation. The target position and rotation centre position are specified according to the relative coordinates from the current position. The position data is assigned as follows. Axis 1: Target position X  Axis 2: Target position Y  Axis 3*1: Rotation centre position X  Axis 4*1: Rotation centre position Y
SYN-I	×	Moves to the relative coordinate position based on the current position by speed tuning control*3
CIR-3* <sup>2</sup>	×	With Axis 1 assigned to the X-axis and Axis 2 to the Y-axis, it moves based on the three specified points by circular interpolation. The target position and passing position are specified according to the relative coordinates from the current position. The position data is assigned as follows. Axis 1: Target position X  Axis 2: Target position Y  Axis 3*1: Passing position X  Axis 4*1: Passing position Y

<sup>\*2</sup> Performs a circular operation on a plane using Axis 1 and Axis 2



<sup>\*3</sup> This controls the speed of the following axis when the speed of the primary axis drops due to the effects of an external force and when a speed difference with the following axis occurs. This control is not for synchronizing the position of the primary axis and following axis.



### For 4 Axes

### 4-axis operation can be set collectively in one step.

Cton	Axis	Movement	Speed	Position	Acceleration	Deceleration	Positioning/	Area 1	Area 2	In position	Commente
Step	otep Axis r	mode	mm/s	mm	mm/s <sup>2</sup>	mm/s²	Pushing	mm	mm	mm	Comments
	Axis 1	ABS	100	200.00	1000	1000	0	6.0	12.0	0.5	
0	Axis 2	ABS	50	100.00	1000	1000	0	6.0	12.0	0.5	
	Axis 3	ABS	50	100.00	1000	1000	0	6.0	12.0	0.5	
	Axis 4	ABS	50	100.00	1000	1000	0	6.0	12.0	0.5	
	Axis 1	INC	500	250.00	1000	1000	1	0	0	20.0	
	Axis 2	INC	500	250.00	1000	1000	1	0	0	20.0	
'	Axis 3	INC	500	250.00	1000	1000	1	0	0	20.0	
	Axis 4	INC	500	250.00	1000	1000	1	0	0	20.0	
2046	Axis 4	ABS	200	700	500	500	0	0	0	0.5	
	Axis 1	ABS	500	0.00	3000	3000	0	0	0	0.5	
2047	Axis 2	ABS	500	0.00	3000	3000	0	0	0	0.5	
2047	Axis 3	ABS	500	0.00	3000	3000	0	0	0	0.5	
	Axis 4	ABS	500	0.00	3000	3000	0	0	0	0.5	

Movement mode	Pushing operation	Details
Blank	×	Invalid data (Invalid process)
ABS	0	Moves to the absolute coordinate position based on the origin of the actuator
INC	0	Moves to the relative coordinate position based on the current position
LIN-A	×	Moves to the absolute coordinate position based on the origin of the actuator by linear interpolation
LIN-I	×	Moves to the relative coordinate position based on the current position by linear interpolation
CIR-R* <sup>1</sup>	×	With Axis 1 assigned to the X-axis and Axis 2 to the Y-axis, it moves in the clockwise direction by circular interpolation. The target position and rotation centre position are specified according to the relative coordinates from the current position. The position data is assigned as follows. Axis 1: Target position X Axis 2: Target position Y Axis 3: Rotation centre position X Axis 4: Rotation centre position Y
CIR-L*1	×	With Axis 1 assigned to the X-axis and Axis 2 to the Y-axis, it moves in the counter-clockwise direction by circular interpolation. The target position and rotation centre position are specified according to the relative coordinates from the current position. The position data is assigned as follows. Axis 1: Target position X Axis 2: Target position Y Axis 3: Rotation centre position X Axis 4: Rotation centre position Y
SYN-I	×	Moves to the relative coordinate position based on the current position by speed tuning control*2

<sup>\*1</sup> Performs a circular operation on a plane using Axis 1 and Axis 2

### Controller Setting Software (Connection with a PC)

For 3 Axes	For 4 Axes
JXC92	JXC73/83/93

### Easy file management

Load	The step data is loaded from the file.
Save	The step data is saved in a file.
Upload	The step data is loaded from the controller.
Download	The step data is written in the controller.

#### **Abundant edit functions**

Сору	The selected step data is copied to the clipboard.
Delete	The selected step data is deleted.
Cut	The selected step data is cut.
Paste (Insert)	The step data copied to the clipboard is inserted into the cursor's position.
Paste (Overwrite)	The step data copied to the clipboard overwrites the data at the cursor position.
Insert	A blank line is inserted in the selected step data line.

#### Operation confirmation of entered step data

operation community of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of control of	
0 =	Enter the step number to be executed.
	Executes the specified step number.
Stop	Displays whether the step number is being executed or stopped.
All axes return to origin	Performs a return to origin of all the valid axes.

#### Step data window






<sup>\*2</sup> This controls the speed of the following axis when the speed of the primary axis drops due to the effects of an external force and when a speed difference with the following axis occurs. This control is not for synchronizing the position of the primary axis and following axis.

#### **System Construction/General Purpose I/O** Provided by the customer Electric actuator/ Rod type **PLC** Power supply for I/O signal 24 VDC\*1 I/O cable p. 199, 213 Controller type Part no. LECA6 LEC-CN5-□ **LECP1 (Programless)** LEC-CK4-□ Controller\*2 To CN5 Programless type ■ Touch Operator Interface/Human-Machine LECP1 Interface (Provided by the customer) p. 207 \* The teaching box, controller setting kit, and To CN4 GP4501T/GP3500T To CN3 Touch Operator Interface/Human-Machine Schneider Electric Japan Holdings Ltd. Interface cannot be connected. Cockpit parts can be **Pro-face** downloaded for free for the best interface via the Pro-face website. To CN2 By using the cockpit parts, adjustments To CN1 Provided by the customer can be made from the Touch Operator Step data input type Power supply for controller Interface. LECA6 24 VDC\*1 p. 191 Power supply plug (Accessory) \*1 When compliance with UL is GOT2000 Series <Applicable cable size> required, the electric actuator and Mitsubishi Electric Corporation AWG20 (0.5 mm<sup>2</sup>) controller should be used with a GOT2000 Sample screens for UL1310 Class 2 power supply. monitoring and changing the current value Actuator cable\*2 p. 197, 212 and set value of the Controller type Standard cable Robotic cable electric actuator can be downloaded for LECA6 (Step data input type) LE-CA-□ free via the Mitsubishi LECP1 (Programless type) LE-CP-□-S LE-CP-Electric website. \*2 Can be included as an option. Refer to the "How to Order" page of the actuator. **Options** Teaching box p. 201 ● Communication cable for controller setting p. 200 (With 3 m cable) Communication cable: LEC-W2A-C LEC-T1-3JG□ USB cable: LEC-W2-U Controller setting software USB driver Communication cable Download from SMC's website: (3 m)https://www.smc.eu or USB cable

PC

\* Cannot be used with the programless type (LECP1)


### **System Construction/Fieldbus Network**




#### **System Construction/Pulse Signal** Provided by the customer Electric actuator/ Rod type **PLC** Current limiting resistor p. 220 LEC-PA-R-□ The current limiting re-Power supply for I/O signal 24 VDC\*1 sistor is used when the pulse signal output of the positioning unit is open \*1 When compliance with UL is collector output. For details, refer to page 215. required, the electric actuator and driver should be used with a UL1310 Class 2 power supply. Driver\*2 I/O cable p. 220 **Driver type** Part no. **LECPA** LEC-CL5-□ To CN5 To CN4 To CN3 To CN2 To CN1 Provided by the customer Pulse input type **LECPA** Power supply for driver 24 VDC\* p. 214 Power supply plug (Accessory) \*1 When compliance with UL is re-<Applicable cable size> AWG20 (0.5 mm<sup>2</sup>) quired, the electric actuator and driver should be used with a UL1310 Class 2 power supply. • Actuator cable\*2 p. 219 Standard cable Robotic cable LECPA (Pulse input type) LE-CP-□-S LE-CP-\*2 Can be included as an option. Refer to the "How to Order" page of the actuator. **Options** ● Communication cable for controller setting p. 221 Teaching box p. 222 (With 3 m cable) Communication cable: LEC-W2A-C LEC-T1-3JG□ USB cable: LEC-W2-U Controller setting software USB driver Communication cable \* Download from SMC's website: or https://www.smcworld.com **USB** cable

PC


### System Construction/Fieldbus Network (EtherCAT®/EtherNet/IP™/PROFINET/DeviceNet™/IO-Link Direct Input Type)




### System Construction/EtherNet/IP™ Type (JXC92)



### System Construction/Parallel I/O (JXC73/83)



### System Construction/EtherNet/IP™ Type (JXC93)



### **AC Servo Motor Driver**

### LECS / LECSS-T/LECY Series List



- \*1 For positioning types, the settings need to be changed in order to use the max. set values. Setup software (MR Configurator2™) LEC-MRC2 is required.
- \*2 Available when a Mitsubishi motion controller is used as the master
- \*3 Available when a motion controller is used as the master
- \* For customer-provided PLC and motion controller setting and usage instructions, confirm with the retailer or manufacturer.



### LECS□/LECSS-T/LECY□ Series

### Gain adjustment using auto tuning **Auto-tuning function** Speed Speed Settling time Settling • Controls the difference between the command value and the actual time action Time Time Vibration suppression control function • Automatically suppresses low-frequency machine vibrations (1 to 100 Hz)

### **AC Servo Motor Driver**

### With display setting function

#### **One-touch** adjustment button

One-touch servo adjustment

#### **Display**

Display the monitor, parameters, and alarm.

#### **Settings**

Set the parameters, monitor display, etc., with push buttons.



#### **Display**

Display the monitor, parameters, and alarm.

#### **Settings**

Set the parameters, monitor display, etc., with push buttons.



(With the front cover opened)

**LECSB** 

#### **Display**

Display the communication status with the driver, the alarm, and the point table no.

### **Settings**

Control the Baud rate, station number, and the occupied station count.



(With the front cover opened) **LECSC** 

#### **Display**

Display the communication status with the driver and the alarm.

#### **Settings**

Switches for selecting the axis and switching to the test operation



(With the front cover opened) **LECSS** 

#### **Display**

Display the communication status with the driver and the alarm.

### **Settings**

Switches for axis setting, switching to the test



LECSS2-T


control axis deactivation, operation, etc.

#### **Settings**

Switches for station address, communication speed, number of transmission bytes, etc.

#### **Display**

Display the driver status and alarm.




**Settings** 


Switches for station address, number of transmission bytes, etc.


#### **Display**


Display the driver status and alarm.





**LECYU** 































### **SMC Electric Actuator**

### Rod Type (Step Motor (Servo/24 VDC)) Servo Motor

p. **34, 104** 









**LEY** Series

	Size	Pushing force [N]	Stroke [mm]
	16	141	Up to 300
	25	452	Up to 400
į	32	707	Up to 500
ľ	40	1058	Up to 500

LEYG Serie

Size	Pushing force [N]	Stroke [mm]
16	141	Up to 200
25	452	Up to 300
32	707	Up to 300
40	1058	Up to 300

#### AC Servo Moto

p. **34, 104** 



**LEY** Series

Size	Pushing force [N]	Stroke [mm]
25	485	Up to 400
32	588	Up to 500
63	3343	Up to 800

**LEY** Series

Size	Pushing force [N]	Stroke [mm]
25	485	Up to 400
32	736	Up to 500
63	1910	Up to 800

I FVG Sories

LL I G Jelles		
Size	Pushing force [N]	Stroke [mm]
25	485	Up to 300
32	588	Op 10 300

LEYG Series

Size	Pushing force [N]	Stroke [mm]
25	485	Up to 300
32	736	Op 10 300

#### Slide Table (Step Motor (Servo/24 VDC)) (Servo Motor (24 VDC))

LES Series

Size

8

16

25

Rod type

Basic type/R type



Max. work

load [kg]

3

5

	In
Stroke	1
[mm]	
30, 50, 75	

30, 50

75, 100 30, 50, 75

100, 125, 150

Symmetrical type/L type LES L Series



n-line motor type/D type .ES□D Series



LESH Series

Basic type/R type LESH□R Series



90	0.0	

Size	Max. work load [kg]	Stroke [mm]
8	2	50, 75
16	6	50, 100
25	9	50, 100
	9	150

Symmetrical type/L type LESH□L Series



In-line motor type/D type **LESH**□**D** Series



#### Miniature (Step Motor (Servo/24 VDC))

LEPY Series

Size	Max. work load [kg]	Stroke [mm]
6	1	25, 50, 75
10	2	25, 50, 75

Slide table type LEPS Series



LEPS Series Stroke Max. work Size load [kg] [mm] 25 6

50

10

### Rotary Table Step Motor (Servo/24 VDC)

Basic type LER Series







I ED out

LER Ser	es			
Size	Rotating	ing torque [N⋅m] Max. sp		speed [°/s]
Size	Basic	High torque	Basic	High torque
10	0.2	0.3		
30	0.8	1.2	420	280
50	6.6	10		

### **SMC Electric Actuator**

### Gripper (Step Motor (Servo/24 VDC)

2-finger type LEHZ Series



LEHZ Series

Max. gripping force [N]		Stroke/both
Basic	Compact	sides [mm]
1.4	6	4
14	8	6
40	20	10
40	28	14
130	_	22
210	_	30
	14 40 130	Basic         Compact           14         6           8         40           28         30

2-finger type With dust cover **LEHZJ** Series



**LEHZJ** Series

Size	Max. gripping force [N]		Stroke/both	
Size	Basic	Compact	sides [mm]	
10	14	6	4	
16		8	6	
20	40	28	10	
25		<b>4</b> 8	14	

2-finger type Long stroke LEHF Series



**LEHF** Series

Size	Max. gripping force [N]	Stroke/both sides [mm]
10	7	16 (32)
20	28	24 (48)
32	120	32 (64)
40	180	40 (80)

\* ( ): Long stroke

3-finger type LEHS Series



LEHS Series

Size	Max. gripping force [N]		Stroke/
Size	Basic	Compact	diameter [mm]
10	5.5	3.5	4
20	22	17	6
32	90	_	8
40	130	_	12

### Controller/Driver

p. **190** 

### Single Axis Controller

Step data input type Servo motor (24 VDC) **LECA6** Series



Gateway unit LEC-G Series

Programless type Step motor (Servo/24 VDC) **LECP1** Series

Pulse input type Step motor (Servo/24 VDC) **LECPA** Series







EtherCAT®/EtherNet/IP™/PROFINET/DeviceNet™/IO-Link direct input type

JXC□ Series





EtherNet/IP



Device Net



**IO**-Link



#### **Multi-Axis Controller**

EtherNet/IP™ direct input type

For 3 axes JXC92 Series



Parallel I/O/EtherNet/IP™ direct input type

For 4 axes JXC73 Series JXC83 Series



JXC93 Series EtherNet/IP



### **Driver**

p. **246** 

#### **AC Servo Motor Driver**

Pulse input type LECSA Series LECSB Series

Absolute encoder (LECSB)
 Built-in positioning function (LECSA)



LECSA Series LECSB Series

CC-Link direct input type LECSC Series

CC-Link



SSCNET Ⅲ type **LECSS** Series





SSCNET II/H type LECSS-T Series





MECHATROLINK-Ⅱ type **LECYM** Series .... MECHATROLINK - II





MECHATROLINK-Ⅲ type **LECYU** Series .... MECHATROLINK-III









### **Electric Actuator/Rod Type LEY Series**



Step Motor (Servo/24 VDC) Servo Motor (24 VDC)		
ORod Type LEY Series		
Model Selection	p.	35
How to Order		
Specifications	р.	59
Construction	p.	61
Dimensions	p.	63
Accessory Mounting Brackets	p.	97
AC Servo Motor		
LECS Series		
○Rod Type LEY Series Size 25, 32		
Model Selection	p.	41
How to Order	p.	69
Specifications	p.	71
Construction	p.	73
Dimensions	p.	74
Rod Type LEY Series Size 63 Dust-tight/Water-jet-proof (IP65 Equivalent) * Option		
Model Selection	p.	41
How to Order	р.	79
Specifications	p.	80
Construction	p.	81
Dimensions	p.	82
LECY□ Series		
○Rod Type LEY Series		
Model Selection	p.	48
How to Order	p.	87
Specifications	p.	89
Construction	p.	91
Dimensions	p.	92
Auto Switch	p.	101

### Electric Actuator/Guide Rod Type LEYG Series







de nou Type LETG Series	
Step Motor (Servo/24 VDC) Servo Motor (24 VDC)	
<b>○Guide Rod Type</b> <i>LEYG Series</i>	
Model Selection	
How to Order	
Specifications	
Construction	•
Dimensions	
Support Block	p. 133
AC Servo Motor	
LECS Series	
<b>○Guide Rod Type LEYG Series</b>	
Model Selection	p. 111
How to Order	p. 135
Specifications	p. 137
Construction	p. 138
Dimensions	p. 139
Support Block	p. 141
LECY□ Series	
<b>○Guide Rod Type </b> <i>LEYG Series</i>	
Model Selection	p. 116
How to Order	
Specifications	
Construction	
Dimensions	p. 147
Support Block	p. 149





Programless Controller/*LECP1 Series* ..... p. 207 Step Motor Driver/LECPA Series ...... p. 214 Communication Cable for Controller Setting/*LEC-W2A* ... p. 221 Teaching Box/*LEC-T1* p. 222 EtherCAT®/EtherNet/IP™/PROFINET/DeviceNet™/IO-Link Direct Input Type/JXCE1/91/P1/D1/L1 Series ..... p. 224 Controller Setting Kit/JXC-W2 ......p. 229 Teaching Box/*LEC-T1* ...... p. 231

	p. 100
□3-Axis Step Motor (Servo/24 VDC) Controlle EtherNet/IP™ Type/ <i>JXC92 Series</i>	
<b>○4-Axis Step Motor (Servo/24 VDC) Controlle</b>	r
Parallel I/O Type/ <i>JXC73/83</i> Series EtherNet/IP™ Type/ <i>JXC93</i> Series	
<b>○AC Servo Motor Driver</b>	
LECSA/LECSB/ LECSC/LECSS Series LECSS-T Series	p. 250 p. 250

LECYM/LECYU Series .....




### Rod Type LEY Series









Step Motor/Servo Motor Controller/Driver p. 200 AC Servo Motor Driver p. 246



### **Model Selection**



### Selection Procedure

### Positioning Control Selection Procedure


Check the work load-speed. (Vertical transfer)



### Selection Example

#### Operating conditions

- Workpiece mass: 4 [kg]
- •Speed: 100 [mm/s]
- Acceleration/Deceleration: 3000 [mm/s²]
- •Stroke: 200 [mm]
- Workpiece mounting condition: Vertical upward downward transfer




#### Step 1 Check the work load-speed. <Speed-Vertical work load graph>

Select the target model based on the workpiece mass and speed with reference to the <Speed-Vertical work load graph>.

Selection example) The LEY16B is temporarily selected based on the graph shown on the right side.

It is necessary to mount a guide outside the actuator when used for horizontal transfer. When selecting the target model, refer to the horizontal work load in the specifications on page 59 and the precautions.



<Speed-Vertical work load graph> (LEY16/Step motor)

#### Step 2 Check the cycle time.

Calculate the cycle time using the following calculation method.

• Cycle time T can be found from the following equation.

•T1: Acceleration time and T3: Deceleration time can be obtained by the following equation.


•T2: Constant speed time can be found from the following equation.

$$T2 = \frac{L - 0.5 \cdot V \cdot (T1 + T3)}{V}$$
 [s]

•T4: Settling time varies depending on the conditions such as motor types, load and in position of the step data. Therefore, calculate the settling time with reference to the following value.

Calculation example)

T1 to T4 can be calculated as follows.



L: Stroke [mm] ... (Operating condition)

V : Speed [mm/s] ··· (Operating condition)

a1: Acceleration [mm/s<sup>2</sup>] ··· (Operating condition)


a2: Deceleration [mm/s<sup>2</sup>] ··· (Operating condition)

T1: Acceleration time [s] ... Time until reaching the set speed

T2: Constant speed time [s] ... Time while the actuator is operating at a constant speed

T3: Deceleration time [s] ... Time from the beginning of the constant speed operation to stop

T4: Settling time [s] ··· Time until positioning is completed



Therefore, the cycle time can be obtained as follows.

$$T = T1 + T2 + T3 + T4 = 0.033 + 1.967 + 0.033 + 0.2 = 2.233$$
 [s]

Based on the above calculation result, the LEY16B-200 is selected.



LEY

LEYG

Ē

EYG.

LEY-X5

25A-LEY

LECA6

LEC-G

LECP1

LECPA

LECS

LECY

AC Servo Motor

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)


Environment

AC Servo Motor

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

#### **Pushing Control Selection Procedure**

Step 1 Check the duty ratio.



Model Selection LEY/25A-LEY Series


Check the lateral load on the rod end.

The duty ratio is a ratio of the operation time in one cycle.

#### Selection Example

#### Operating conditions

- Mounting condition: Horizontal (pushing)
  - Duty ratio: 20 [%] •Speed: 100 [mm/s]
- Jig weight: 0.2 [kg]
- Pushing force: 60 [N] •Stroke: 200 [mm]



## Step 1 Check the duty ratio.

#### <Conversion table of pushing force-duty ratio>

Select the [Pushing force] from the duty ratio with reference to the <Conversion table of pushing force-duty ratio>.

Selection example)

Based on the table below,

• Duty ratio: 20 [%]

Therefore, the set value of pushing force will be 70 [%].

## <Conversion table of pushing force-duty ratio>

(LEY16/Step motor)

Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]
40 or less	100	_
50	70	12
70	20	1.3
85	15	0.8

- [Set value of pushing force] is one of the step data input to the controller.
- [Continuous pushing time] is the time that the actuator can continuously keep pushing.

## Step 2 Check the pushing force. <Force conversion graph>

Select the target model based on the set value of pushing force and force with reference to the <Force conversion graph>.

Selection example)

Based on the graph shown on the right side,

- Set value of pushing force: 70 [%]
- Pushing force: 60 [N]

Therefore, the **LEY16B** is temporarily selected.

## Step 3 Check the lateral load on the rod end.

#### <Graph of allowable lateral load on the rod end>

Confirm the allowable lateral load on the rod end of the actuator: LEY16□, which has been selected temporarily with reference to the <Graph of allowable lateral load on the rod end>.


Selection example)

Based on the graph shown on the right side,


- Jig weight: 0.2 [kg] ≈ 2 [N]
- Product stroke: 200 [mm]

Therefore, the lateral load on the rod end is in the allowable range.


Based on the above calculation result, the LEY16B-200 is selected.



**Duty ratio = A/B x 100 [%]** 



\*1 Set values for the controller.



<Graph of allowable lateral load on the rod end>


# Model Selection LEY/25A-LEY Series

Step Motor (Servo/24 VDC) Servo Motor (24 VDC) Secondary Battery Compatible


## Speed-Work Load Graph (Guide) For Step Motor (Servo/24 VDC) LECP1, LECPMJ, JXC□1

Refer to page 38 for the LECPA,  $JXC\square_3^2$ and page 39 for the LECA6.


#### Horizontal




#### LEY25□ for acceleration/deceleration: 2000 mm/s<sup>2</sup>




#### LEY32□ for acceleration/deceleration: 2000 mm/s<sup>2</sup>




#### LEY40□ for acceleration/deceleration: 2000 mm/s<sup>2</sup>




#### Vertical




#### LEY25□



#### LEY32□



#### LEY40□



LEY

LEYG

Щ

LEYG

LEY-X5

25A-LEY

LECA6

LEC-G

LECP1

LECPA

LECS

LECY

AC Servo Motor


Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)


Environment


## Speed-Work Load Graph (Guide) For Step Motor (Servo/24 VDC) LECPA, JXC□<sup>2</sup><sub>3</sub>


Refer to page 37 for the LECP1, LECPMJ, JXC□1 and page 39 for the LECA6.

#### Horizontal













#### Vertical









## Model Selection LEY/25A-LEY Series


Step Motor (Servo/24 VDC) Servo Motor (24 VDC) Secondary Battery Compatible

## Speed-Work Load Graph (Guide) For Servo Motor (24 VDC) LECA6

Refer to page 37 for the LECP1, LECPMJ. JXC□1 and page 39 for the LECPA, JXC□<sup>2</sup><sub>3</sub>.


#### Horizontal






#### Vertical


#### LEY16□A




#### LEY25□A




#### LEY25□A



#### Graph of Allowable Lateral Load on the Rod End (Guide)




[Stroke] = [Product stroke] + [Distance from the rod end to the centre of gravity of the workpiece]




#### Rod Displacement: δ [mm]

Stroke	30	50	100	150	200	250	300	350	400	450	500
16	±0.4	±0.5	±0.9	±0.8	±1.1	±1.3	±1.5	_	_	_	_
25	±0.3	±0.4	±0.7	±0.7	±0.9	±1.1	±1.3	±1.5	±1.7	_	_
32, 40	±0.3	±0.4	±0.7	±0.6	±0.8	±1.0	±1.1	±1.3	±1.5	±1.7	±1.8



#### Non-rotating Accuracy of Rod



Size	Non-rotating accuracy θ
16	±1.1°
25	±0.8°
32	10.70
40	±0.7°

<sup>\*</sup> Avoid using the electric actuator in such a way that rotational torque would be applied to the piston rod.

This may cause the deformation of the non-rotating guide, abnormal auto switch responses, play in the internal guide, or an increase in the sliding resistance.

LEY

LEYG

LEY

LEYG

LEY-X5

25A-LEY

LECA6

LEC-G

LECP1

LECPA

LECS

LECY

AC Servo Motor

Motor (Servo/24 VDC)/Servo Motor (24 VDC)

Step


Environment

AC Servo Motor

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)


#### Step Motor (Servo/24 VDC)

#### LEY16




Ambient temperature	Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]
25 °C or less 85 or less		100	_
	40 or less	100	_
40 °C	50	70	12
40 C	70	20	1.3
	85	15	0.8

#### LEY25




Ambient temperature	Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]
40 °C or less	65 or less	100	_

#### LEY32



Ambient temperature	Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]
25 °C or less	85 or less	100	_
40 °C	65 or less	100	_
40 C	85	50	15


#### LEY40



#### \*1 Set values for the controller


### Servo Motor (24 VDC)

#### LEY16□A



Ambient temperature	Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]
40 °C or less	95 or less	100	_

#### LEY25□A



Ambient temperature	Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]
40 °C or less	95 or less	100	_

#### <Limit Values for Pushing Force and Trigger Level in Relation to Pushing Speed> Without Load

	VVILLIO	ut L	Jau					
	Model	Lead	Pushing speed [mm/s]	Pushing force (Setting input value)	Model	Lead	Pushing speed [mm/s]	Pushing force (Setting input value)
	LEY16	A/B/C	21 to 50	60 to 85 %	LEY16□A	A/B/C	21 to 50	80 to 95 %
	LEY25	A/B/C	21 to 35	50 to 65 %	LEY25□A	A/B/C	21 to 35	80 to 95 %
	LEY32	Α	24 to 30	60 to 85 %				
	LE 132	B/C	21 to 30	00 10 00 %				
	LEY40	Α	24 to 30	50 to 65 %				
		B/C	21 to 30	50 10 65 %				

There is a limit to the pushing force in relation to the pushing speed. If the product is operated outside of the range (low pushing force), the completion signal [INP] may be output before the pushing operation has been completed (during the moving operation). If operating with the pushing speed below the min. speed, please check for operating problems before using the product.

#### <Set Values for Vertical Upward Transfer Pushing Operations>

For vertical loads (upward), set the pushing force to the max. value shown below and operate at the work load or less.

Model	LE	Y16	6□	LE	Y2	5□	LE	Y32	2	LE	Y40	וו	LE	Y16	□Α	LE	Y25	⊒A
Lead				Α														
Work load [kg]	1	1.5	3	2.5	5	10	4.5	9	18	7	14	28	1	1.5	3	1.2	2.5	5
Pushing force	8	35 %	6	6	65 °	6	8	35 %	6	6	65 %	,	(	95 %	, 0	(	95 %	, 0

AC Servo Motor LECS Series

**Electric Actuator/Rod Type** 

LEY/LEY-X5/25A-LEY Series Dust-tight/Water-jet-proof (IP65 Equivalent) Secondary Battery Compatible

**Model Selection** 

LEY-X5 Series ▶p. 163 25A-LEY Series ▶p. 181

LEY Series ▶ p. 69, 79 | LECY □ Series ▶ p. 87

#### Selection Procedure

#### Positioning Control Selection Procedure

Check the work load-speed. (Vertical transfer)




#### Selection Example

#### Operating conditions

- •Workpiece mass: 16 [kg]
- •Speed: 300 [mm/s]
- Acceleration/Deceleration: 5000 [mm/s<sup>2</sup>]
- •Stroke: 300 [mm]
- •Workpiece mounting condition: Vertical upward

downward transfer




Size 25, 32, 63

#### Step 1 Check the work load-speed. <Speed-Vertical work load graph>

Select the target model based on the workpiece mass and speed with reference to the <Speed-Vertical work load graph>.

Selection example) The LEY25B is temporarily selected based on the graph shown on the right side.

\* It is necessary to mount a guide outside the actuator when used for horizontal transfer. When selecting the target model, refer to the horizontal work load in the specifications on pages 71, 72, 80, 89, 90, and 164 and the precautions.



<Speed-Vertical work load graph> (LEY25)

The regeneration option may be necessary. Refer to pages 43 and 44 for "Required Conditions for Regeneration Option."

#### Step 2 Check the cycle time.

Calculate the cycle time using the following calculation method.

• Cycle time T can be found from the following equation.

$$T = T1 + T2 + T3 + T4 [s]$$


•T1: Acceleration time and T3: Deceleration time can be obtained by the following equation.

•T2: Constant speed time can be found from the following equation.

$$T2 = \frac{L - 0.5 \cdot V \cdot (T1 + T3)}{V} [s]$$

•T4: Settling time varies depending on the motor type and load. The value below is recommended.

$$T4 = 0.05 [s]$$



L: Stroke [mm] ... (Operating condition)

V : Speed [mm/s] ··· (Operating condition)

a1: Acceleration [mm/s<sup>2</sup>] ··· (Operating condition)

a2: Deceleration [mm/s2] ··· (Operating condition)

T1: Acceleration time [s] ... Time until reaching the set speed


T2: Constant speed time [s] ... Time while the actuator is operating at a constant speed

T3: Deceleration time [s] ... Time from the beginning of the constant speed operation to stop

T4: Settling time [s] ... Time until positioning is completed

Calculation example)

T1 to T4 can be calculated as follows.



T4 = 0.05 [s]

Therefore, the cycle time can be obtained as follows.

T = T1 + T2 + T3 + T4 = 0.06 + 0.94 + 0.06 + 0.05 = 1.11 [s]

**∠** 

Model Selection LEY/LEY-X5/25A-LEY Series

AC Servo Motor Size 25, 32, 63 Dust-tight/Water-jet-proof (IP65 Equivalent) Secondary Battery Compatible

## **Selection Procedure**

#### **Force Control Selection Procedure**



The duty ratio is a ratio of the operation time in one cycle.

#### Selection Example


#### Operating conditions

Mounting condition: Horizontal (pushing)

• Jig weight: 0.5 [kg]

•Force: 255 [N]

- Duty ratio: 60 [%]
- •Speed: 100 [mm/s]
- •Stroke: 300 [mm]



## Step 1 Check the duty ratio.

#### <Conversion table of force-duty ratio>

Select the [Force] from the duty ratio with reference to the <Conversion table of force-duty ratio>.

Selection example)

Based on the table below,

• Duty ratio: 60 [%]

Therefore, Torque limit/Command value will be 30 [%].

#### <Conversion table of force-duty ratio>

#### (LEY25/AC Servo motor)

Torque limit/ Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
25 or less	100	_
30	60	1.5

- [Torque limit/Command value [%]] is the set value for the driver.
- [Continuous pushing time] is the time that the actuator can continuously keep pushing.

## Step 2 Check the force. <Force conversion graph>

Select the target model based on the torque limit/command value and pushing force with reference to the <Force conversion graph>.

Selection example)

Based on the graph shown on the right side,

- •Torque limit/Command value: 30 [%]
- Force: 255 [N]

Therefore, the **LEY25B** is temporarily selected.

## Step 3 Check the lateral load on the rod end.

## <Graph of allowable lateral load on the rod end>

Confirm the allowable lateral load on the rod end of the actuator: LEY25B, which has been selected temporarily with reference to the <Graph of allowable lateral load on the rod end>.


Selection example)

Based on the graph shown on the right side,

- Jig weight: 0.5 [kg] ≈ 5 [N]
- Product stroke: 300 [mm]

Therefore, the lateral load on the rod end is in the allowable range.


#### Based on the above calculation result, the LEY25S2B-300 is selected.




Check the lateral load

on the rod end.

#### **Duty ratio = A/B x 100 [%]**




<Force conversion graph> (LEY25)



<Graph of allowable lateral load on the rod end>

## Speed-Vertical Work Load Graph/Required Conditions for "Regeneration Option"

#### LEY25 S<sub>6</sub>/T6 (Motor mounting position: Top/Parallel, In-line)




#### Required conditions for "Regeneration option"

\* Regeneration option is required when using product above regeneration line in graph. (Order separately.)


#### "Regeneration Option" Models

Size	Model
LEY25□	LEC-MR-RB-032
LEY32□	LEC-MR-RB-032
LEY63□	LEC-MR-RB-12


#### **LEY32**□S<sub>7</sub><sup>3</sup>/T7 (Motor mounting position: Top/Parallel)



#### LEY32DS<sub>7</sub><sup>3</sup>/T7 (Motor mounting position: In-line)



## LEY63 S<sub>8</sub>/T8 (Motor mounting position: Top/Parallel, In-line)




E

Model Selection LEY/LEY-X5/25A-LEY Series

AC Servo Motor Size 25, 32, 63 Dust-tight/Water-jet-proof (IP65 Equivalent) Secondary Battery Compatible

## Speed-Horizontal Work Load Graph/Required Conditions for "Regeneration Option"

#### LEY25 S<sub>6</sub><sup>2</sup>/T6 (Motor mounting position: Top/Parallel, In-line)




#### Required conditions for "Regeneration option"

\* Regeneration option is required when using product above regeneration line in graph. (Order separately.)


## "Regeneration Option" Models

Size	Model
LEY25□	LEC-MR-RB-032
LEY32□	LEC-MR-RB-032
LEY63□	_


## LEY32□S<sub>7</sub>/T7 (Motor mounting position: Top/Parallel)



### LEY32DS<sub>7</sub>/T7 (Motor mounting position: In-line)



## LEY63 S<sub>8</sub>4/T8 (Motor mounting position: Top/Parallel, In-line)




Allowable Stro	ke Spee	ed															[mm/s]	
Model	AC servo	L	Lead Stroke [mm]															
Model	motor	Symbol	[mm]	30	50	100	150	200	250	300	350	400	450	500	600	700	800	
LEVOE C2/TC		Α	12		900 600 —							_	_					
LEY25 S <sub>6</sub> /T6  (Motor mounting position:)	100 W	В	6				450				30	00	_	_		_		
Top/Parallel, In-line	/□40	С	3				225				15	50	_	_		_		
( Top/Faranei, III-iiile )		(Motor ro	tation speed)			(-	4500 rpn	n)			(3000	rpm)	_	_		_		
LEY32□S <sup>3</sup> /T7		Α	20					1200					80	00		_		
Motor mounting position:	200 W	В	10					600					40	400		_		
Top/Parallel	/□60	С	5	300							20	00	_					
( TOP/T dialiei		(Motor ro	tation speed)	(3600 rpm)						(2400	2400 rpm) —							
LEY32DS <sup>3</sup> /T7		Α	16	1000						64	40	_						
Motor mounting position:	200 W	В	8		500								32	20				
In-line	/□60	С	4	250							16	60						
( """""		(Motor ro	tation speed)				(;	3750 rpn	1)				(2400	rpm)	_			
		Α	20						1000						800	600	500	
LEVCO C4/TO		В	10						500						400	300	250	
LEY63 S <sub>8</sub> /T8  Motor mounting position:	400 W	С	5		250								200	150	125			
Top/Parallel, In-line	/□60		tation speed)					(3	8000 rpm	1)					(2400 rpm)	(1800 rpm)	(1500 rpm)	
TOP/I alaliel, III-lille		L*1	2.86							7	0							
		(Motor ro	tation speed)	on speed) (1470 rpm)														




## **Force Conversion Graph (Guide)** For LECSA, LECSB, LECSC, LECSS

#### LEY25□S<sub>6</sub><sup>2</sup> (Motor mounting position: Top/Parallel, In-line)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
25 or less	100	_
30	60	1.5

#### **LEY32**□S<sub>7</sub> (Motor mounting position: Top/Parallel)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
25 or less	100	_
30	60	1.5

#### LEY63□S<sub>8</sub> (Motor mounting position: Top/Parallel, In-line)



Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
25 or less	100	_
30	60	1.5
40	30	0.5
50	20	0.16

## LEY32DS<sup>3</sup> (Motor mounting position: In-line)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
25 or less	100	_
30	60	1.5

Environment


## Force Conversion Graph (Guide) For LECSS-T

#### LEY25□T6 (Motor mounting position: Top/Parallel, In-line)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
20 or less	100	_
24	60	1.5

#### LEY32 T7 (Motor mounting position: Top/Parallel)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
20 or less	100	_
24	60	1.5

#### LEY63 T8 (Motor mounting position: Top/Parallel, In-line)



Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
20 or less	100	_
24	60	1.5
32	30	0.5
40	20	0.16


#### LEY32DT7 (Motor mounting position: In-line)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
20 or less	100	_
24	60	1.5

AC Servo Motor Size 25, 32, 63 Dust-tight/Water-jet-proof (IP65 Equivalent) Secondary Battery Compatible

## Graph of Allowable Lateral Load on the Rod End (Guide)




[Stroke] = [Product stroke] + [Distance from the rod end to the centre of gravity of the workpiece]




## Rod Displacement: $\delta$ [mm]

Stroke	30	50	100	150	200	250	300	350	400	450	500	600	700	800
25	±0.3	±0.4	±0.7	±0.7	±0.9	±1.1	±1.3	±1.5	±1.7	_	_	_	_	_
32	±0.3	±0.4	±0.7	±0.6	±0.8	±1.0	±1.1	±1.3	±1.5	±1.7	±1.8	_	_	_
63	_	±0.5	±0.7	±0.9	±1.2	±1.1	±1.3	±1.5	±1.7	±1.9	±2.1	±1.7	±2.0	±2.2



## **Non-rotating Accuracy of Rod**



Size	Non-rotating accuracy θ
25	±0.8°
32	±0.7°
63	±0.6°

<sup>\*</sup> Avoid using the electric actuator in such a way that rotational torque would be applied to the piston rod.

This may cause the deformation of the non-rotating guide, abnormal auto switch responses, play in the internal guide, or an increase in the sliding resistance.



口

**Model Selection** 

AC Servo Motor LECY□ Series

LEY Series ▶ p. 87 LECS Series ▶ p. 69, 79

**Electric Actuator/Rod Type** 

**LEY-X5** Series ▶ p. **169 25A-LEY** Series ▶ p. **183** 

## Selection Procedure

**Positioning Control Selection Procedure** 



Check the work load-speed. (Vertical transfer)





Size 25, 32, 63

#### Selection Example

#### Operating conditions

- •Workpiece mass: 16 [kg]
- •Speed: 300 [mm/s]
- Acceleration/Deceleration: 5000 [mm/s<sup>2</sup>]
- •Stroke: 300 [mm]
- •Workpiece mounting condition: Vertical upward





0

200

#### <Speed-Vertical work load graph> (LEY25)

Speed [mm/s]

400 600 800 1000 1200

## Step 1 Check the work load-speed. <Speed-Vertical work load graph>

Select the target model based on the workpiece mass and speed with reference to the <Speed-Vertical work load graph>.

Selection example) The LEY25B is temporarily selected based on the graph shown on the right side.

\* It is necessary to mount a guide outside the actuator when used for horizontal transfer. When selecting the target model, refer to the horizontal work load in the specifications on pages 89 and 90 and the precautions.

The regenerative resistor may be necessary. Refer to pages 50 and 51 for "Conditions for Regenerative Resistor (Guide)."

## Step 2 Check the cycle time.

Calculate the cycle time using the following calculation method.

• Cycle time T can be found from the following equation.

$$T = T1 + T2 + T3 + T4 [s]$$

•T1: Acceleration time and T3: Deceleration time can be obtained by the following equation.

•T2: Constant speed time can be found from the following equation.


$$T2 = \frac{L - 0.5 \cdot V \cdot (T1 + T3)}{V}$$
 [s]

•T4: Settling time varies depending on the motor type and load. The value below is recommended.

$$T4 = 0.05 [s]$$

Calculation example)

T1 to T4 can be calculated as follows.



L: Stroke [mm] ... (Operating condition)

V : Speed [mm/s] ··· (Operating condition)

a1: Acceleration [mm/s<sup>2</sup>] ··· (Operating condition)


a2: Deceleration [mm/s2] ··· (Operating condition)

T1: Acceleration time [s] ... Time until reaching the set speed

T2: Constant speed time [s] ... Time while the actuator is operating at a constant speed

T3: Deceleration time [s] ... Time from the beginning of the constant speed operation to stop

T4: Settling time [s] ... Time until positioning is completed



$$T2 = \frac{L - 0.5 \cdot V \cdot (T1 + T3)}{V} = \frac{300 - 0.5 \cdot 300 \cdot (0.06 + 0.06)}{300} = 0.94 [s]$$

$$T4 = 0.05 [s]$$

Therefore, the cycle time can be obtained as follows.

$$T = T1 + T2 + T3 + T4 = 0.06 + 0.94 + 0.06 + 0.05 = 1.11$$
 [s]


Based on the above calculation result, the LEY25V6B-300 is selected.



AC Servo Motor Size 25, 32, 63 Dust-tight/Water-jet-proof (IP65 Equivalent) Secondary Battery Compatible

## Selection Procedure

#### **Pushing Control Selection Procedure**





Check the lateral load on the rod end.


\* The duty ratio is a ratio of the operation time in one cycle.

#### Selection Example

#### Operating conditions

- Mounting condition: Horizontal (pushing)
- Jig weight: 0.5 [kg]
- •Force: 255 [N]

- Duty ratio: 60 [%]
- Pushing speed: 35 [mm/s]
- •Stroke: 300 [mm]



#### Step 1 Check the duty ratio.

#### <Conversion table of pushing force-duty ratio>

Select the [Pushing force] from the duty ratio with reference to the <Conversion table of pushing force-duty ratio>.

Selection example)

Based on the table below,

• Duty ratio: 60 [%]

Therefore, Torque limit/command value will be 90 [%].

## <Conversion table of pushing force-duty ratio>

#### (LEY25/AC Servo motor)

Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]			
75 or less	100	_			
90	60	1.5			

- [Set value of pushing force] is one of the data input to the driver.
- [Continuous pushing time] is the time that the actuator can continuously keep pushing.

## Step 2 Check the pushing force. <Force conversion graph>


Select the target model based on the torque limit/command value and pushing force with reference to the <Force conversion graph>.

Selection example)

Based on the graph shown on the right side,

- •Torque limit/Command value: 90 [%]
- Pushing force: 255 [N]

Therefore, the **LEY25B** is temporarily selected.



<Force conversion graph> (LEY25)

#### Step 3 Check the lateral load on the rod end.

#### <Graph of allowable lateral load on the rod end>

Confirm the allowable lateral load on the rod end of the actuator: LEY25B, which has been selected temporarily with reference to the <Graph of allowable lateral load on the rod end>.


Selection example)

Based on the graph shown on the right side,

- Jig weight: 0.5 [kg] ≈ 5 [N]
- Product stroke: 300 [mm]

Therefore, the lateral load on the rod end is in the allowable range.

#### Based on the above calculation result, the LEY25V6B-300 is selected.



<Graph of allowable lateral load on the rod end>




₩


Model Selection LEY/LEY-X5/25A-LEY Series

AC Servo Motor Size 25, 32, 63 Dust-tight/Water-jet-proof (IP65 Equivalent) Secondary Battery Compatible


## Speed-Work Load Graph/Conditions for "Regenerative Resistor" (Guide)


## LEY25□V6 (Motor mounting position: Top/Parallel, In-line)







## **LEY32**□V7 (Motor mounting position: Top/Parallel)





#### LEY32DV7 (Motor mounting position: In-line)





#### "Regenerative resistor" area


- \* When using the actuator in the "Regenerative resistor" area, download the "AC servo drive capacity selection program/SigmaJunmaSize+" from the SMC website. Then, calculate the necessary regenerative resistor capacity to prepare an appropriate external regenerative resistor.
- \* Regenerative resistor should be provided by the customer.


#### **Applicable Motor/Driver**

Madal		Applicable model
Model	Motor	Servopack (SMC driver)
LEY25□	SGMJV-01A3A	SGDV-R90A11□ (LECYM2-V5) SGDV-R90A21□ (LECYU2-V5)
LEY32□	SGMJV-02A3A	SGDV-1R6A11□ (LECYM2-V7) SGDV-1R6A21□ (LECYU2-V7)

## Speed-Work Load Graph/Conditions for "Regenerative Resistor" (Guide)

#### LEY63□V8 (Motor mounting position: Top/Parallel, In-line)





#### "Regenerative resistor" area

- \* When using the actuator in the "Regenerative resistor" area, download the "AC servo drive capacity selection program/SigmaJunmaSize+" from the SMC website. Then, calculate the necessary regenerative resistor capacity to prepare an appropriate external regenerative resistor.
- \* Regenerative resistor should be provided by the customer.

#### **Applicable Motor/Driver**

Product no.		Applicable model
Product no.	Motor	Servopack (SMC driver)
LEY63□	SGMJV-04A3A	SGDV-2R8A11□ (LECYM2-V8) SGDV-2R8A21□ (LECYU2-V8)

## Allowable Stroke Speed


Allowable Stro	llowable Stroke Speed [mm/s]												
Model	AC servo	L	ead			S	Stroke [mm]						
iviodei	motor	Symbol	[mm]	Up to 30 Up to 50 Up to 100 Up to 150 Up to 200 Up to 250 Up to 300 Up to 350 Up to 400 U			Up to 450	Up to 500	Up to 600	Up to 700	Up to 800		
LEY25□V6		Α	12		900		600	_	_	_	_	_	
( Motor mounting )	100 W	В	6		450		300		_		_		
position:	/□40	С	3		225		150	_	_	_	_	_	
Top/Parallel, In-line		(Motor rot	tation speed)		(4500 rpm)		(3000 rpm)		_		_		
LEY32□V7		Α	20		1200			80	0	_	_	_	
( Motor mounting )	200 W /□60	В	10		600			40	0		_		
position:		С	5		300			20	0	_	_	_	
Top/Parallel		(Motor rot	tation speed)	speed) (3600 rpm)			(2400 rpm)			_			
LEY32DV7		Α	16		1000			640		_	_	_	
( Motor mounting )	200 W	В	8		500			32	.0		_	_	
position:	/□60	С	4		250			160 —		_	_	_	
l In-line		(Motor rot	tation speed)		(3750 rpm)			(2400 rpm)			_	_	
		Α	20	_	<del>-</del> 1000					800	600	500	
LEY63□V8		В	10	_		500				400	300	250	
( Motor mounting )	400 W	С	5	_	<del>-</del> 250				<del>-</del> 250 200		200	150	125
position:	/□60	(Motor rot	tation speed)	eed) — (3000 rpm)					(2400 rpm)	(1800 rpm)	(1500 rpm)		
Top/Parallel, In-line		L	2.86	_			70						
		(Motor rot	tation speed)	_		(1470 rpm)							



# Model Selection LEY/LEY-X5/25A-LEY Series AC Servo Motor Size 25, 32, 63 Dust-tight/Water-jet-proof (IP65 Equivalent) Secondary Battery Compatible


## Force Conversion Graph (Guide)

#### LEY25 V6 (Motor mounting position: Top/Parallel, In-line)




	Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]			
75 or less 90		100	_			
		60	1.5			

#### LEY32 U7 (Motor mounting position: Top/Parallel)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
75 or less	100	_
an	60	1.5

## LEY32DV7 (Motor mounting position: In-line)



Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]		
75 or less	100	_		
90	60	1.5		


## LEY63 V8 (Motor mounting position: Top/Parallel, In-line)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]		
75 or less	100	_		
90	60	1.5		
120	30	0.5		
150	20	0.16		

AC Servo Motor Size 25, 32, 63 Dust-tight/Water-jet-proof (IP65 Equivalent) Secondary Battery Compatible

## Graph of Allowable Lateral Load on the Rod End (Guide)




[Stroke] = [Product stroke] + [Distance from the rod end to the centre of gravity of the workpiece]




## Rod Displacement: $\delta$ [mm]

Stroke	30	50	100	150	200	250	300	350	400	450	500	600	700	800
25	±0.3	±0.4	±0.7	±0.7	±0.9	±1.1	±1.3	±1.5	±1.7	_	_	_	_	_
32	±0.3	±0.4	±0.7	±0.6	±0.8	±1.0	±1.1	±1.3	±1.5	±1.7	±1.8	_	_	_
63	_	±0.5	±0.7	±0.9	±1.2	±1.1	±1.3	±1.5	±1.7	±1.9	±2.1	±1.7	±2.0	±2.2



## **Non-rotating Accuracy of Rod**



Size	Non-rotating accuracy θ
25	±0.8°
32	±0.7°
63	±0.6°

<sup>\*</sup> Avoid using the electric actuator in such a way that rotational torque would be applied to the piston rod.

This may cause the deformation of the non-rotating guide, abnormal auto switch responses, play in the internal guide, or an increase in the sliding resistance.

Specific Product Precautions

# **Electric Actuator/ Rod Type**

**LEY** Series LEY16, 25, 32, 40



(RoHS)


Dust-tight/Water-jet-proof ▶p. 155 Secondary Battery Compatible ▶p. 175

**How to Order** 



Motor mounting position: Top/Parallel

Motor mounting position: In-line



### 1 Size 16 25

32 40

#### 2 Motor mounting position

	<u> </u>
_	Top mounting
R	Right side parallel
L	Left side parallel
D	In-line

## Motor type

O IVIO	• Motor type								
Symbol	Time	Applicable size			Compatible				
	Type	LEY16	LEY25	LEY32/40	controll	er/driver			
	Step motor (Servo/24 VDC)	•	•	•	LECP1 LECPA	JXCE1 JXC91 JXCP1 JXCD1 JXCL1			
Α	Servo motor (24 VDC)	•	•	_	LE	CA6			

## 4 Lead [mm]

Symbol	LEY16	LEY25	LEY32/40
Α	10	12	16
В	5	6	8
С	2.5	3	4

#### 5 Stroke [mm]

30	30
to	to
500	500

<sup>\*</sup> For details, refer to the applicable stroke table

## 6 Motor option\*2

_	<ul><li>Without option</li></ul>			
С	With motor cover			
В	With lock			
W	With lock/motor cover			



#### Rod end thread

_	Rod end female thread					
М	Rod end male thread (1 rod end nut is included.)					

## 8 Mounting\*3

Symbol	Type	Motor mounting position			
Symbol	туре	Top/Parallel	In-line		
_	Ends tapped/Body bottom tapped*4	•	•		
L	Foot	•	_		
F	Rod flange*4	●*6	•		
G	Head flange*4	●*7	_		
D	Double clevis*5	•	_		

#### 9 Actuator cable type/length\*9

Standard cable [m]						
None						
S1	1.5*11					
S3	3*11					
S5	5*11					

Roboti	[m]		
R1	1.5	RA	10*8
R3	3	RB	15*8
R5	5	RC	20*8
R8	8*8		


Applicable Stroke Table <sup>↑</sup> ■: Standard												
Stroke Model [mm]		50	100	150	200	250	300	350	400	450	500	Manufacturable stroke range
LEY16	•	•	•					_	_	-	_	10 to 300
LEY25	•	•	•	•	•	•	•	•	•		_	15 to 400
LEY32/40	•	•			•		•	•	•	•		20 to 500

For auto switches, refer to pages 101 to 103.



## Electric Actuator/Rod Type LEY Series Step Motor (Servo/24 VDC) Servo Motor (24 VDC)

Series (For details, refer to page 57.)



## Controller/Driver type\*10

_	Without controller/driver					
1N	LECP1*11 NPN					
1P	(Programless type)	PNP				
AN	LECPA*11 *13	NPN				
AP	(Pulse input type)	PNP				

## I/O cable length\*14, Communication plug

_	Without cable (Without communication plug connector)				
1	1.5 m				
3	3 m* <sup>15</sup>				
5	5 m* <sup>15</sup>				
S	Straight type communication plug connector				
Т	T-branch type communication plug connector				




## Controller/Driver mounting

_	Screw mounting
D	DIN rail*16

## JXC Series (For details, refer to page 57.



D



- \*1 Please consult with SMC for non-standard strokes as they are
- produced as special orders. When "With lock" or "With lock/motor cover" is selected for the top mounting and right/left side parallel types, the motor body will stick out from the end of the body for size 16/40 with strokes of 30 mm or less. Check for interference with workpieces before selecting a model.

For single axis

- \*3 The mounting bracket is shipped together with the product but does not come assembled. \*4 For the horizontal cantilever mounting of the rod flange, head flange, or
- ends tapped types, use the actuator within the following stroke range
- ·LEY25: 200 mm or less ·LEY32/40: 100 mm or less
  \*5 For the mounting of the double clevis type, use the actuator within the following stroke range.
  ·LEY16: 100 mm or less ·LEY25: 200 mm or less ·LEY32/40: 200 mm or less
- The rod flange type is not available for the LEY16/40 with a 30 mm stroke and motor option "With lock," "With lock/motor cover."
- \*7 The head flange type is not available for the LEY32/40.
  \*8 Produced upon receipt of order (Robotic cable only)

- \*9 The standard cable should only be used on fixed parts.
- For use on moving parts, select the robotic cable. \*10 For details on controllers/drivers and compatible motors, refer to the compatible controller/driver on the next page.
- \*11 Only available for the motor type "Step motor"
- Not compliant with CE
- \*12 Not compliant with CE
  \*13 When pulse signals are open collector, order the current limiting resistor (LEC-PA-R-□) on page 220 separately.
  \*14 When "Without controller/driver" is selected for controller/driver types, I/O cable cannot be selected. Refer to page 199 (For LECA6), page 213(For LECP1), or page 220 (For LECPA) if I/O cable is required.
  \*15 When "Pulse input type" is selected for controller/driver types, pulse input usable only with differential Only 15 m cables usable with open collector.
- usable only with differential. Only 1.5 m cables usable with open collector
- \*16 The DIN rail is not included. Order it separately. \*17 Select "—" for anything other than DeviceNet™

## **⚠** Caution

#### [CE-compliant products]

DeviceNet™

IO-Link

- 1) EMC compliance was tested by combining the electric actuator LEY series and the controller LEC/JXC series.
  - The EMC depends on the configuration of the customer's control panel and the relationship with other electrical equipment and wiring. Therefore, compliance with the EMC directive cannot be certified for SMC components incorporated into the customer's equipment under actual operating conditions. As a result, it is necessary for the customer to verify compliance with the EMC directive for the machinery and equipment as a whole.
- 2 For the servo motor (24 VDC) specification, EMC compliance was tested by installing a noise filter set (LEC-NFA). Refer to page 199 for the noise filter set. Refer to the LECA series Operation Manual for installation.

#### [UL-compliant products (For the LEC series)]


When compliance with UL is required, the electric actuator and controller/ driver should be used with a UL1310 Class 2 power supply.

#### The actuator and controller/driver are sold as a package.

Confirm that the combination of the controller/driver and actuator is correct.

## <Check the following before use.>

- 1 Check the actuator label for the model number. This number should match that of the controller/driver.
- 2 Check that the Parallel I/O configuration matches (NPN or PNP).



Refer to the Operation Manual for using the products. Please download it via our website, https://www.smc.eu





## Compatible Controller/Driver

## **LEC**□ Series

Туре	Step data input type	Programless type	Pulse input type		
Series	LECA6	LECP1	LECPA		
Features	Value (Step data) input Standard controller	Capable of setting up operation (step data) without using a PC or teaching box	Operation by pulse signals		
Compatible motor	Servo motor (24 VDC)	Servo motor (Servo/24 VDC)			
Max. number of step data	64 points	14 points	_		
Power supply voltage		24 VDC			
Reference page	191	207	214		

## JXC□ Series

Туре	EtherCAT® direct input type	EtherNet/IP™ direct input type	PROFINET direct input type	DeviceNet <sup>TM</sup> direct input type	IO-Link direct input type
Series	JXCE1	JXC91	JXCP1	JXCD1	JXCL1
Features	EtherCAT® direct input	EtherNet/IP™ direct input	PROFINET direct input	DeviceNet™ direct input	IO-Link direct input
Compatible motor			Step motor (Servo/24 VDC)		
Max. number of step data			64 points		
Power supply voltage			24 VDC		
Reference page			224		_

<b>SMC</b>
------------



#### **Specifications**

#### Step Motor (Servo/24 VDC)

		Model			LEY16			LEY25			LEY32			LEY40			
		Horizontal (LECP1,	(3000 [mm/s <sup>2</sup> ])	6	17	30	20	40	60	30	45	60	50	60	80		
		JXC□1)	(2000 [mm/s <sup>2</sup> ])	10	23	35	30	55	70	40	60	80	60	70	90		
	Work load [kg]*1	Horizontal (LECPA,	(3000 [mm/s <sup>2</sup> ])	4	11	20	12	30	30	20	40	40	30	60	60		
60		JXC□3)	(2000 [mm/s <sup>2</sup> ])	6	17	30	18	50	50	30	60	60	_	_	_		
specifications		Vertical	(**************************************	2	4	8	8	16	30	11	22	43	13	27	53		
Citi	Pushing 1	force [N	*2 *3 *4	14 to 38	27 to 74	51 to 141	63 to 122	126 to 238	232 to 452	80 to 189	156 to 370	296 to 707	132 to 283	266 to 553	562 to 1058		
or spe	Connect	LECP1/ JXC⊡1		15 to 500	8 to 250	4 to 125	18 to 500	9 to 250	5 to 125	24 to 500	12 to 300	6 to 150	24 to 500	12 to 350	6 to 175		
Actuator	[0]	LECPA/	∕JXC□3²								12 to 250	6 to 125	24 to 300	12 to 150	6 to 75		
Act			eration [mm/s <sup>2</sup> ]						30								
	Pushing s				50 or less 35 or less 30 or less 30 or less												
		<del></del>	ability [mm]		±0.02												
	Lost motio		6		0.1 or less												
	Screw lea			10	5	2.5	12	6	3	16	8	4	16	8	4		
			tance [m/s <sup>2</sup> ]*7		50/20 Ball screw + Belt (LEY□)/Ball screw (LEY□D)												
	Actuation						Ball					'□D)					
	Guide typ							Slidii	ng bushin		rod)						
			re range [°C]						5 to								
	· ·		range [%RH]						less (No	condens							
ons	Motor siz				□28			□42			□56.4			□56.4			
cati	Motor typ	е							motor (S								
ij	Encoder						Inc	remental			ılse/rotati	on)					
sbe	Rated vol							- 10	24 VDC	5 ±10 %			1				
Electric specifications	Power con				23 16			40 15			50 48			50 48			
ec			nen operating [W]*9 onsumption [W]*10		43			48			104			106			
	Type*11	ous power co	maumpholi [w]		43				on-magne	aticina lo				100			
unit	Holding f	orce [NI]		20	39	78	78	157	294	108	216	421	127	265	519		
ock u	Power co			20	2.9	70	70	5									
Lo	Rated vol				2.3			<u> </u>	24 VDC	: +10 %	<u> </u>			<u> </u>			
*1			rimum value	of the wor	rk load Δ	n avtarnal	auida is	nacassan			d (Friction	coefficie	ant of quid	o: 0 1 or 1	ass) Tha		

\*1 Horizontal: The maximum value of the work load. An external guide is necessary to support the load (Friction coefficient of guide: 0.1 or less). The actual work load and transfer speed change according to the condition of the external guide. Also, speed changes according to the work load. Check "Model Selection" on pages 37 and 38.

Vertical: Speed changes according to the work load. Check "Model Selection" on pages 37 and 38.

The values shown in ( ) are the acceleration/deceleration.

Set these values to be 3000 [mm/s<sup>2</sup>] or less.

- \*2 Pushing force accuracy is  $\pm 20$  % (F.S.).
- \*3 The pushing force values for LEY16□ is 35 % to 85 %, for LEY25□ is 35 % to 65 %, for LEY32□ is 35 % to 85 %, and for LEY40□ is 35 % to 65 %. The pushing force values change according to the duty ratio and pushing speed. Check "Model Selection" on page 40.
- \*4 The speed and force may change depending on the cable length, load, and mounting conditions. Furthermore, if the cable length exceeds 5 m, then it will decrease by up to 10 % for each 5 m. (At 15 m: Reduced by up to 20 %)
- \*5 The allowable speed for pushing operation. When push conveying a workpiece, operate at the vertical work load or less.
- \*6 A reference value for correcting an error in reciprocal operation
- \*7 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
  - Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
- \*8 The power consumption (including the controller) is for when the actuator is operating.
- \*9 The standby power consumption when operating (including the controller) is for when the actuator is stopped in the set position during the operation. Except during the pushing operation
- \*10 The maximum instantaneous power consumption (including the controller) is for when the actuator is operating. This value can be used for the selection of the power supply.
- \*11 With lock only
- \*12 For an actuator with lock, add the power consumption for the lock.



Щ

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

## **Specifications**

Servo Motor (24 VDC)

	M	lodel		LEY16□A			LEY25□A	
	Work load	Horizontal (3000 [mm/s <sup>2</sup> ])	3	6	12	7	15	30
	[kg]*1	Vertical (3000 [mm/s <sup>2</sup> ])	2	4	8	3	6	12
	Pushing	g force [N]*2 *3	16 to 30	30 to 58	57 to 111	18 to 35	37 to 72	66 to 130
ns	Speed	[mm/s]	1 to 500	1 to 250	1 to 125	2 to 500	1 to 250	1 to 125
Actuator specifications	Max. accelera	tion/deceleration [mm/s <sup>2</sup> ]			30	00		
fica	Pushing	speed [mm/s]*4		50 or less			35 or less	
eci	Positioning	g repeatability [mm]			±0.	.02		
sb	Lost mo	otion [mm]*5			0.1 o	r less		
tor	Screw I	ead [mm]	10	5	2.5	12	6	3
tua	Impact/Vibra	tion resistance [m/s²]*6			50/	/20		
Ac	Actuati	on type		Ball screw -	+ Belt (LEY	□)/Ball scre	w (LEY□D)	
	Guide t	уре		SI	iding bushin	g (Piston ro	od)	
	Operating to	emperature range [°C]			5 to	40		
	Operating h	numidity range [%RH]		90	or less (No	condensati	on)	
ns	Motor s	size		□28			□42	
specifications	Motor o	output [W]		30			36	
ica	Motor t	ype			Servo moto	or (24 VDC)		
ecit	Encode		Inc	remental A	B phase (80		ation)/Z pha	ase
sbe	Rated v	oltage [V]			24 VDC	±10 %		
ric	Power co	nsumption [W]*7		40			86	
Electric	Standby power co	nsumption when operating [W]*8	4 (Hori	zontal)/6 (V	'ertical)	4 (Horiz	zontal)/12 (\	/ertical)
Ē		ous power consumption [W]*9		59			96	
t ons	Type*10	)			Non-magn	etising lock		
Lock unit specifications	Holding	force [N]	20	39	78	78	157	294
SCIE C	Power co	nsumption [W]*11		2.9			5	
eds Sbe	Rated v	oltage [V]			24 VDC	±10 %		

- \*1 Horizontal: The maximum value of the work load. An external guide is necessary to support the load (Friction coefficient of guide: 0.1 or less). The actual work load and transfer speed change according to the condition of the external guide. Vertical: Check "Model Selection" on page 39 for details. The values shown in ( ) are the acceleration/deceleration. Set these values to be 3000 [mm/s2] or less.
- \*2 Pushing force accuracy is ±20 % (F.S.).

Electric Actuator/Rod Type LEY Series

Step Motor (Servo/24 VDC) Servo Motor (24 VDC)

- \*3 The thrust setting values for LEY16A□ is 60 % to 95 % and for LEY25A□ is 70 % to 95 %. The pushing force values change according to the duty ratio and pushing speed. Check "Model Selection" on page 40.
- \*4 The allowable speed for pushing operation. When push conveying a workpiece, operate at the vertical work load or
- \*5 A reference value for correcting an error in reciprocal operation
- \*6 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
  - Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
- \*7 The power consumption (including the controller) is for when the actuator is operating.
- \*8 The standby power consumption when operating (including the controller) is for when the actuator is stopped in the set position during the operation. Except during the pushing operation
- \*9 The maximum instantaneous power consumption (including the controller) is for when the actuator is operating. This value can be used for the selection of the power supply.
- \*10 With lock only
- \*11 For an actuator with lock, add the power consumption for the lock.

## Weight

Weight: Motor Top/Parallel Type

weight	. motor re	י ישי	uiu		• у	PC_																						
	Series			L	EY1	6						L	EY2	:5								L	EY3	2				
Stro	oke [mm]	30	50	100	150	200	250	300	30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500
Product	Step motor	0.58	0.62	0.73	0.87	0.98	1.09	1.20	1.18	1.25	1.42	1.68	1.86	2.03	2.21	2.38	2.56	2.09	2.20	2.49	2.77	3.17	3.46	3.74	4.03	4.32	4.60	4.89
weight [kg]	Servo motor	0.58	0.62	0.73	0.87	0.98	1.09	1.20	1.14	1.21	1.38	1.64	1.82	1.99	2.17	2.34	2.52	l —	_	_	l —	_	l —	_	_	_	_	_

	Series					L	EY4	0				
Stro	oke [mm]	30	50	100	150	200	250	300	350	400	450	500
Product	Step motor	2.39	2.50	2.79	3.07	3.47	3.76	4.04	4.33	4.62	4.90	5.19
weight [kg]	Servo motor	_	_	_	_	_	_	_	_	_	_	_

Weight: In-line Motor Type

	Series			LI	EY16	SD						LI	EY25	5D								LI	EY32	2D				
Stro	oke [mm]	30	50	100	150	200	250	300	30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500
Product	Step motor	0.58	0.62	0.73	0.87	0.98	1.09	1.20	1.17	1.24	1.41	1.67	1.85	2.02	2.20	2.37	2.55	2.08	2.19	2.48	2.76	3.16	3.45	3.73	4.02	4.31	4.59	4.88
weight [kg]	Servo motor	0.58	0.62	0.73	0.87	0.98	1.09	1.20	1.13	1.20	1.37	1.63	1.81	1.98	2.16	2.33	2.51	_	_	_	_	_	_	_	_	_		_

	Series					LI	<b>EY40</b>	D				
Stro	oke [mm]	30	50	100	150	200	250	300	350	400	450	500
Product	Step motor	2.38	2.49	2.78	3.06	3.46	3.75	4.03	4.32	4.61	4.89	5.18
weight [kg]	Servo motor	_	_	_	_	_	_	_	_	_	_	_


Additional Weig	gnt				[kg]
	Size	16	25	32	40
Lock		0.12	0.26	0.53	0.53
Motor cover		0.02	0.03	0.04	0.05
Lock/Motor cover		0.16	0.32	0.61	0.62
Rod end male thread	Male thread	0.01	0.03	0.03	0.03
nou ellu illale tilleau	Nut	0.01	0.02	0.02	0.02
Foot bracket (2 sets	including mounting bolt)	0.06	0.08	0.14	0.14
Rod flange (includi	ng mounting bolt)	0.13	0.17	0.20	0.20
Head flange (include	ling mounting bolt)	0.13	0.17	0.20	0.20
Double clevis (including pin,	retaining ring, and mounting bolt)	0.08	0.16	0.22	0.22






## Construction

Motor top mounting type: LEY  $^{25}_{32}_{40}$ 




Motor top/parallel type With lock/motor cover




## Construction

In-line motor type: LEY  $^{25}_{32}$  D 40



In-line motor type: With lock/motor cover



Component Parts

Com	ponent Parts		
No.	Description	Material	Note
1	Body	Aluminium alloy	Anodised
2	Ball screw shaft	Alloy steel	
3	Ball screw nut	Synthetic resin/Alloy steel	_
4	Piston	Aluminium alloy	
5	Piston rod	Stainless steel	Hard chrome plating
6	Rod cover	Aluminium alloy	
7	Bearing holder	Aluminium alloy	_
8	Rotation stopper	POM	
9	Socket	Free cutting carbon steel	Nickel plating
10	Connected shaft	Free cutting carbon steel	Nickel plating
11	Bushing	Bearing alloy	
12	Bearing	_	
13	Return box	Aluminium die-cast	Coating
14	Return plate	Aluminium die-cast	Coating
15	Magnet	_	
16	Wear ring holder	Stainless steel	Stroke 101 mm or more
17	Wear ring	POM	Stroke 101 mm or more
18	Screw shaft pulley	Aluminium alloy	
19	Motor pulley	Aluminium alloy	
20	Belt	_	
21	Parallel pin	Stainless steel	
22	Seal	NBR	
23	Retaining ring	Steel for spring	Phosphate coated
24	Motor	_	

No.	Description	Material	Note
25	Motor cover	Synthetic resin	Only "With motor cover"
26	Grommet	Synthetic resin	Only "With motor cover"
27	Motor block	Aluminium alloy	Anodised
28	Motor adapter	Aluminium alloy	Anodised/LEY16, 25 only
29	Hub	Aluminium alloy	
30	Spider	NBR	
31	Motor cover with lock	Aluminium alloy	Only "With lock/motor cover"
32	Cover support	Aluminium alloy	Only "With lock/motor cover"
33	Socket (Male thread)	Free cutting carbon steel	Nickel plating
34	Nut	Alloy steel	Zinc chromated

## Replacement Parts (Motor top/parallel only)/Belt

No.	Size	Order no.
	16	LE-D-2-1
21	25	LE-D-2-2
	32, 40	LE-D-2-3


#### **Replacement Parts/Grease Pack**

Applied portion	Order no.
Piston rod	GR-S-010 (10 g) GR-S-020 (20 g)

<sup>\*</sup> Apply grease on the piston rod periodically. Grease should be applied at 1 million cycles or 200 km, whichever comes first.



## **Dimensions: Motor Top/Parallel**




- \*1 Range within which the rod can move when it returns to origin Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.
- \*2 Position after return to origin
- $*3 \ [ \ ]$  for when the direction of return to origin has changed
- \*4 The direction of rod end width across flats ( $\square K$ ) differs depending on the products.

														[mm]									
Size	Stroke	Α	В	С	D	ЕН	EV	н	J	к	L	М	<b>O</b> 1	R	s	Т	U	V		motor	Servo		Υ
	range [mm]																		W	X	W	Х	
16	10 to 100	101	90.5	10	16	34	34.3	M5 x 0.8	18	14	10.5	25.5	M4 x 0.7	7	35	67.5	0.5	28	61.8	80.3	62.5	81	22.5
10	101 to 300	121	110.5	10	10	34	34.3	IVIO X U.O	10	14	10.5	25.5	W4 X U.7	′	33	07.5	0.5	20	01.0	60.3	02.5	01	22.5
25	15 to 100	130.5	116	13	20	44	45.5	M8 x 1.25	24	17	14.5	34	M5 x 0.8	8	46	92	4	42	63.4	0E /	59.6	81.6	26.5
25	101 to 400	155.5	141	13	20	44	45.5	IVIO X 1.23	24	17	14.5	34	O.U X CIVI	0	40	92		42	03.4	03.4	59.6	01.0	20.5
32	20 to 100	148.5	130	13	25	E4	56.5	Mo v 1 OF	//8 x 1.25 31	22	10 5	40	M6 x 1.0	10	60	60 118	4	56.4	68.4	95.4			34
32	101 to 500	178.5	160	13	25	51	36.3	IVIO X 1.23		1 22	2   18.5	40	IVIO X 1.U		0 60		'	30.4	00.4	95.4			34
40	20 to 100	148.5	130	13	25	51	56.5	M8 x 1.25	31	22	18.5	40	M6 x 1.0	10	60	118	4	56.4	90.4	117.4			34
40	101 to 500	178.5	160	13	25	51	36.3	IVIO X 1.23	31	22	10.5	40	IVIO X 1.U	10	60	110		30.4	90.4	117.4		_	34


Bod	y Botton	n Ta	pped	I							[mm]
Size	Stroke range [mm]	MA	МВ	МС	MD	МН	ML	МО	MR	ХА	ХВ
	10 to 39			17	23.5		40				
16	40 to 100	15	35.5	32	2 31 23		40	M4 x 0.7	5.5	3	4
	101 to 300			62	46		60				
	15 to 39			24	32		50				
	40 to 100			42 41							
25	101 to 124	20	46		41	29		M5 x 0.8	6.5	4	5
	125 to 200			59	49.5		75				
	201 to 400			76	58						
	20 to 39			22	36		50				
22	40 to 100			36	43		50				
32 40	101 to 124	25	55	30	43	30		M6 x 1	8.5	5	6
40	125 to 200			53	51.5	j	80				
	201 to 500			70	60						


# Electric Actuator/Rod Type LEY Series Step Motor (Servo/24 VDC) Servo Motor (24 VDC)


## **Dimensions: Motor Top/Parallel**



\* When the motor is mounted on the left or right side in parallel, the groove for auto switch on the side to which the motor is mounted is hidden.








		[mm]
Size	<b>T</b> 2	<b>X</b> 2
16	7.5	124.5
25	7.5	129
32	7.5	141.5
40	7.5	162 5



## **Dimensions: In-line Motor**



- \*1 Range within which the rod can move when it returns to origin Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.
- \*2 Position after return to origin
- \*3 [ ] for when the direction of return to origin has changed
- \*4 The direction of rod end width across flats ( $\square$ K) differs depending on the products.


																						[mm]
Size	Stroke range [mm]	Step motor	Servo motor	В	С	D	ЕН	EV	н	J	K	L	М	O <sub>1</sub>	R	s	т	U	v	Step motor	Servo motor	Υ
	rango [mm]	_ A	4																	V	<b>V</b>	
16	10 to 100	166.3	167	92	10	16	34	34.3	M5 x 0.8	18	14	10 E	25.5	Mayoz	7	35	35.5	0.5	28	61.8	62.5	24
10	101 to 300	186.3	187	112	10	16	34	34.3	IVIS X U.6	10	14	10.5	25.5	M4 x 0.7	/	35	35.5	0.5	20	01.0	62.5	24
25	15 to 100	195.4	191.6	115.5	13	20	44	1E E	M8 x 1.25	24	17	115	24	MEVOO	8	15	46.5	1.5	42	63.4	E0.6	26
25	101 to 400	220.4	216.6	140.5	13	20	44	45.5	IVIO X 1.25	24	17	14.5	34	M5 x 0.8	0	45	46.5	1.5	42	03.4	59.6	20
20	20 to 100	216.9	_	128	13	0.5	F4	FC F	M0 v 1 05	0.1	00	10.5	40	MCvd	10		C1	-	FC 4	CO 4		20
32	101 to 500	246.9	_	158	13	25	51	56.5	M8 x 1.25	31	22	18.5	40	M6 x 1	10	60	61	1	56.4	68.4	_	32
40	20 to 100	238.9	_	128	10	0.5	F4	FC F	M0 v 1 0F	0.1	00	10.5	40	MCvd	10		C1	4	FC 4	00.4		20
40	101 to 500	268.9		158	13	25	51	50.5	M8 x 1.25	31	22	18.5	40	M6 x 1	10	60	61	1	56.4	90.4		32

Bod	Body Bottom Tapped [mm													
Size	Stroke range [mm]	MA	МС	MD	МН	ML	МО	MR	ХА	ХВ				
	10 to 39		17	23.5		40								
16	40 to 100	15	32	31	23	40	M4 x 0.7	5.5	3	4				
	101 to 300		62	46		60								
	15 to 39		24	32		50								
25	40 to 100		42	41		30								
	101 to 124	20	42 41	29		M5 x 0.8	6.5	4	5					
	125 to 200		59	49.5		75								
	201 to 400		76	58										
	20 to 39		22	36		50								
40 ⊦	40 to 100		36	43		50								
	101 to 124	25	30	43	30		M6 x 1	8.5	5	6				
	125 to 200		53	51.5		80								
-	201 to 500		70	60										

LEYG


**Dimensions: In-line Motor** 

With motor cover: LEY<sup>25</sup><sub>32</sub>D□B-□C 40 C




						[111111]	
Size	Stroke range	Α	<b>T</b> 2	<b>X</b> 2	L	CV	
16	100st or less	169	7.5	66.5	35	43	
10	101st or more, 200st or less	189	7.5	00.5	35	43	
25	100st or less	198.5	7.5	68.5	46	54.5	
25	101st or more, 400st or less	223.5	7.5	00.5	40	34.5	
32	100st or less	220	7.5	73.5	60	68.5	
32	101st or more, 500st or less	250	7.5	73.5	00	00.5	
40	100st or less	242	7.5	95.5	60	68.5	
40	101st or more, 500st or less	272	7.5	95.5	60	06.5	

# A □B-□B With lock: LEY



					[mm]		
Size	Ctroko rongo	Step motor	Servo motor	Step motor	Servo motor		
Size	Stroke range	-	4	VB			
16	100st or less	207.8	208.5	103.3	104		
10	101st or more, 200st or less	227.8	228.5	103.3	104		
25	100st or less	235.9	232.1	103.9	100.1		
25	101st or more, 400st or less	260.9	257.1	103.9	100.1		
32	100st or less	259.9	_	111.4			
32	101st or more, 500st or less	289.9	_	111.4	_		
40	100st or less	281.9		133.4			
	101st or more, 500st or less	311.9	_	133.4	_		

# With lock/motor cover: LEY <sup>16</sup> <sub>32</sub> <sub>40</sub> A C




						[mm]	
Size	Stroke range	Α	T <sub>2</sub>	<b>X</b> 2	L	CV	
16	100st or less	210.5	7.5	108	35	43	
10	101st or more, 300st or less	230.5	7.5	100	33	43	
25	100st or less	239	7.5	109	46	54.4	
25	101st or more, 400st or less	264	7.5	109	40	34.4	
32	100st or less	263	7.5	116.5	60	68.5	
32	101st or more, 500st or less	293	7.5	116.5	60	00.5	
40	100st or less	285	7.5	138.5	60	68.5	
40	101st or more, 500st or less	315	7.5	136.5	60	00.5	




#### **Dimensions**






		<del></del> -	-			[mm]
Size	B <sub>1</sub>	<b>C</b> <sub>1</sub>	Hı	L <sub>1</sub>	L <sub>2</sub>	ММ
16	13	12	5	24.5	14	M8 x 1.25
25	22	20.5	8	38	23.5	M14 x 1.5
32, 40	22	20.5	8	42.0	23.5	M14 x 1.5

- \* The L<sub>1</sub> measurement is when the unit is in the original position. At this position, 2 mm at the end.
- \* Refer to page 97 for details on the rod end nut and mounting bracket.
- Refer to the "Handling" precautions on pages 185 to 187 when mounting end brackets such as knuckle joint or workpieces.





Included parts	
<ul> <li>Foot bracket</li> </ul>	

Body mounting bolt

Foot										<b>→</b>   <b>∢</b>	-			[mm]
Size	Stroke range [mm]	Α	LS	LS <sub>1</sub>	LL	LD	LG	LH	LT	LX	LY	LZ	х	Υ
16	10 to 100	106.1	76.7	16.1	5.4	6.6	2.8	24	2.3	48	40.3	62	9.2	5.8
10	101 to 300	126.1	96.7	10.1	5.4	0.0	2.0	24	2.3	70	40.0	02	9.2	5.6
25	15 to 100	136.6	98.8	19.8	8.4	6.6	3.5	30	2.6	57	51.5	71	11.2	5.8
25	101 to 400	161.6	123.8	19.0	0.4	0.0	3.5			57	31.5	/	11.2	5.6
32	20 to 100	155.7	114	19.2	11.3	6.6	4	36	3.2	76	61.5	00	11.0	7
40	101 to 500	185.7	144	19.2	11.3	0.0	4	36	3.2	76	01.5	90	11.2	/


Material: Carbon steel (Chromate treated)

- st The A measurement is when the unit is in the original position. At this position, 2 mm at the end.
- $* \ \ When the motor mounting is the right or left side parallel type, the head side foot bracket should be mounted outward.$


# Electric Actuator/Rod Type LEY Series Step Motor (Servo/24 VDC) Servo Motor (24 VDC)

#### **Dimensions**







25 Rod flange: LEY32 ]**B**-[ 40







Head flange: LEY25□□B-C



for the LEY32/40.

Included parts Flange

· Body mounting bolt

**Rod/Head Flange** 

Rod/Head Flange										
Size	FD	FT	FV	FX	FZ	LL	M			
16	6.6	8	39	48	60	2.5				
25	5.5	8	48	56	65	6.5	34			
32, 40	5.5	8	54	62	72	10.5	40			

Material: Carbon steel (Nickel plating)


- Included parts Double clevis
  - · Body mounting bolt
- · Clevis pin
- · Retaining ring
- \* Refer to page 97 for details on the rod end nut and mounting bracket.

Double Clevis										
Size	Stroke range [mm]	Α	CL	СВ	CD	СТ				
16	10 to 100	128	119	20	8	5				
25	15 to 100	160.5	150.5		10	5				
25	101 to 200	185.5	175.5		10	5				
32	20 to 100	180.5	170.5		10	6				
40	101 to 200	210.5	200.5		10					


Si	ze	Stroke range [mm]	CU	cw	сх	cz	L	RR	
1	6	10 to 100	12	18	8	16	10.5	9	
2	25	15 to 100	14	20	18	36	14.5	10	
		101 to 200	14	20	10	30			
3	2	20 to 100	1.1	22	10	26	10 E	10	
4	0	101 to 200	14	22	18	36	18.5	10	

Material: Cast iron (Coating)


The A and CL measurements are when the unit is in the original position. At this position, 2 mm at the end.



]**B-**[



Double clevis: LEY32





# **Electric Actuator/ Rod Type**


LEY Series LEY25, 32 Size 25, 32





Dust-tight/Water-jet-proof▶p. 163 Secondary Battery Compatible▶p. 181 LECY□ Series▶p. 87

#### **How to Order**



#### Accuracy

Hoodidoy							
Basic type							
Н	High-precision type						

### 2 Size 25

## Motor mounting position

_	Top mounting					
R	Right side parallel					
L	Left side parallel					
D	In-line					

- \*1 For motor type S2 and S6, the compatible driver par number suffixes are S1 and S5 respectively.
- \*2 For motor type T6, the compatible driver part numbe suffix is T5.
- \*3 For details on the driver, refer to page 246.

#### 4 Motor type

	Symbol	Туре	Output [W]	Actuator size	Compatible drivers*3	UL- compliant
	S2*1	AC servo motor (Incremental encoder)	100	25	LECSA□-S1	_
	S3	AC servo motor (Incremental encoder)	200	32	LECSA□-S3	_
	S6*1	AC servo motor (Absolute encoder)	100	25	LECSB□-S5 LECSC□-S5 LECSS□-S5	_
rt	<b>S7</b>	AC servo motor (Absolute encoder)	200	32	LECSB□-S7 LECSC□-S7 LECSS□-S7	_
er	<b>T6</b> *2	AC servo motor	100	25	LECSS2-T5	•
	T7	(Absolute encoder)	200	32	LECSS2-T7	•

#### 5 Lead [mm]

Symbol	LEY25	LEY32*1
Α	12	16 (20)
В	6	8 (10)
С	3	4 (5)

\*1 The values shown in ( ) are the leads for the size 32 top mounting, right/left side parallel

(Equivalent leads which include the pulley ratio [1.25:1])

## 6 Stroke [mm]

30	30
to	to
500	500

For details, refer to the applicable stroke table

#### Motor option

_	Without option
В	With lock*1

\*1 When "With lock" is selected for the top mounting and right/left side parallel types, the motor body will stick out from the end of the body for size 25 with strokes of 30 mm or less. Check for interference with workpieces before selecting a model.

#### 8 Rod end thread

_	Rod end female thread
М	Rod end male thread
	(1 rod end nut is included.)

#### 9 Mounting\*1

Symbol	Type	Motor mounting position				
	туре	Top/Parallel	In-line			
_	Ends tapped/ Body bottom tapped *2	•	•			
L	Foot	•	_			
F	Rod flange*2	<b>●</b> *4	•			
G	Head flange*2	●*5	_			
D	Double clevis*3					

- \*1 The mounting bracket is shipped together with the product but does not come assembled.
- \*2 For the horizontal cantilever mounting of the rod flange, head flange, or ends tapped types, use the actuator within the following stroke range.
- ·LEY25: 200 mm or less ·LEY32: 100 mm or less \*3 For the mounting of the double clevis type, use the actuator within the following stroke range.
- •LEY25: 200 mm or less •LEY32: 200 mm or less \*4 The rod flange type is not available for the LEY25
- with a 30 mm stroke and motor option "With lock."
- \*5 The head flange type is not available for the LEY32.

#### policable Stroke Table

Applicable Stroke Table   Standard													
Stroke [mm]	30	50	100	150	200	250	300	350	400	450	500	Manufacturable stroke range	
LEY25		•			•					_	_	15 to 400	
LEY32												20 to 500	

\* Please consult with SMC for non-standard strokes as they are produced as special orders.

For auto switches, refer to pages 101 to 103.

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

AC Servo Motor

Environment

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

LECPA

AC Servo Motor

LECY

Electric Actuator/Rod Type LEY Series

AC Servo Motor Size 25, 32





Motor mounting position: Top/Parallel

Motor mounting position: In-line

#### Cable type\*1 \*2

-	3.0 .7 p 0
_	Without cable
S	Standard cable
R	Robotic cable (Flexible cable)

- \*1 The motor and encoder cables are included. (The lock cable is also included when the motor with lock option is selected.)
- \*2 Standard cable entry direction is
  - · Top/Parallel: (A) Axis side
  - · In-line: (B) Counter axis side (Refer to page 264 for details.)

## Cable length\*1 [m]

_	Without cable
2	2
5	5
Α	10

\*1 The length of the motor, encoder, and lock cables are the same.

## Driver type\*1

	Compatible driver	Power supply voltage [V]	UL-compliant
_	Without driver		
A1	LECSA1-S□	100 to 120	
A2	LECSA2-S□	200 to 230	_
B1	LECSB1-S□	100 to 120	_
B2	LECSB2-S□	200 to 230	_
C1	LECSC1-S□	100 to 120	_
C2	LECSC2-S□	200 to 230	_
S1	LECSS1-S□	100 to 120	
S2	LECSS2-S□	200 to 230	_
32	LECSS2-T□	200 to 240	•

\*1 When a driver type is selected, a cable is included. Select the cable type and cable length. Example)

S2S2: Standard cable (2 m) + Driver (LECSS2)

S2 : Standard cable (2 m) : Without cable and driver

## 13 I/O cable length [m]\*1

	<u> </u>
_	Without cable
Н	Without cable (Connector only)
1	1.5

\*1 When "Without driver" is selected for driver type, only "-: Without cable" can be selected. Refer to page 265 if I/O cable is required. (Options are shown on page 265.)

#### **Compatible Driver**

Compandic Dity	CI									
Driver type	Pulse input type /Positioning type	Pulse input type	CC-Link direct input type	SSCNET III type	SSCNETII/H type					
Series	LECSA	LECSB	LECSC	LECSS	LECSS-T					
Number of point tables	Up to 7	_	Up to 255 (2 stations occupied)	_	_					
Pulse input	0	0	_	_	_					
Applicable network	_	_	CC-Link	SSCNET II	SSCNET III /H					
Control encoder	Incremental 17-bit encoder	Absolute 18-bit encoder	Absolute 18-bit encoder	Absolute 18-bit encoder	Absolute 22-bit encoder					
Communication function	USB communication	USB communication,	RS422 communication	USB com	munication					
Power supply voltage [V]			0 to 120 VAC (50/60 Hz) 200 to 240 VAC (50/60 Hz) (50/60 Hz)							
Reference page	246									



## Specifications: LECSA/LECSB/LECSC/LECSS

\* Refer to the next page for the LECSS-T.

		Model		LEY25Se (Top	o/Parallel)/LEY	25DS <sup>2</sup> (In-line)	LEY3	2S <sup>3</sup> (Top/Pa	arallel)	LEY	/32DS <sup>3</sup> (In-	line)			
	Work los	al Float	Horizontal*1	18	50	50	30	60	60	30	60	60			
	Work loa	ia [kg]	Vertical	8	16	30	9	19	37	12	24	46			
	Force [N]	*2 (Set value:	15 to 30 %)	65 to 131	127 to 255	242 to 485	79 to 157	154 to 308	294 to 588	98 to 197	192 to 385	368 to 736			
	Max.*3	Stroke	Up to 300	900	450	225	1200	600	300	1000	500	250			
	speed	range	305 to 400	600	300	150	1200		300	1000	300	250			
us	[mm/s]		405 to 500	_	_	_	800	400	200	640	320	160			
specifications	Pushing	speed [mm/	/s]* <sup>4</sup>		35 or less			30 or less			30 or less				
<u>3</u>	Max. accel	eration/decelera	ation [mm/s <sup>2</sup> ]		5000				50	00					
彦	Position	ing	Basic type		±0.02										
be	repeatab	ility [mm]	High-precision type					±0.01							
	Loct mo	tion [mm]*5	Basic type					0.1 or less							
엹			might-precision type					0.05 or less							
Actuator		n] (including p		12	6	3	20	10	5	16	8	4			
Ac	Impact/Vib	oration resistar	nce [m/s <sup>2</sup> ]*6		50/20 50/20										
	Actuatio					screw (LEY□D)	Ball so	rew + Belt [		Ball screw					
	Guide ty			Sliding bushing (Piston rod)  Sliding bushing (Piston rod)											
		g temperature			5 to 40		5 to 40								
	Operating	g humidity rar	nge [%RH]	90 or less (No condensation) 90 or less (No condensation)											
		ation option	l .	May be required depending on speed and work load (Refer to pages 43 and 44.)											
2	Motor ou	ıtput/Size			100 W/□40		200 W/□60								
ē	Motor ty	pe		AC servo	motor (100/		AC servo motor (100/200 VAC)								
pecifications	Encoder								der (Resolution						
Š	Power		Horizontal		45	r type So, S	7. Absolute	65	ler (Resolution	011: 202 144	65				
Spe		ption [W]*7	Vertical		145			175		175					
		ver consumption			2			2			2				
Electric	when operat		Vertical		8			8			8				
음		aneous power cons			445			724		8 724					
	Type*10	ilicous power cons	oumphon [W]		440		Non	magnetising	ı lock		124				
	Holding	force [N]		131	255	485	157	308	588	197	385	736			
ock unit		nsumption [W	1 at 20 °C*11	101	6.3	400	137	7.9	300	191	7.9	730			
2 9	Rated vo		J 41 20 0		0.0			7.9 24 VDC <sub>-10 %</sub>			1.5				
S		ntage [v]					0.1		6						

- \*1 This is the maximum value of the horizontal work load. An external guide is necessary to support the load. The actual work load changes according to the condition of the external guide. Confirm the load using the actual device.
- \*2 The force setting range (set values for the driver) for the force control with the torque control mode. Set it with reference to "Force Conversion Graph" on page 45. When the control equivalent to the pushing operation of the controller LECP series is performed, select the LECSS driver and combine it with the Simple Motion (manufactured by Mitsubishi Electric Corporation) which has a pushing operation function.
- \*3 The allowable speed changes according to the stroke. Set the number of rotations according to speed.
- \*4 The allowable collision speed for collision with the workpiece with the torque control mode
- \*5 A reference value for correcting an error in reciprocal operation

- \*6 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
  - Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
- \*7 The power consumption (including the driver) is for when the actuator is operating.
- \*8 The standby power consumption when operating (including the driver) is for when the actuator is stopped in the set position during the operation.
- \*9 The maximum instantaneous power consumption (including the driver) is for when the actuator is operating.
- \*10 Only when motor option "With lock" is selected
- \*11 For an actuator with lock, add the power consumption for the lock.

#### Weight

Proc												[kg]									
	Series	LE,	Y25S <sub>6</sub>	(Moto	r mou	ınting	positio	n: To	p/Para	llel)		LEY3	32S7 (	Moto	r mou	nting	positi	on: To	op/Pa	rallel)	
	Stroke [mm]	30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500
je s	Incremental encoder	1.31	1.38	1.55	1.81	1.99	2.16	2.34	2.51	2.69	2.42	2.53	2.82	3.29	3.57	3.85	4.14	4.42	4.70	4.98	5.26
울	Absolute encoder	1.37	1.44	1.61	1.87	2.05	2.22	2.40	2.57	2.75	2.36	2.47	2.76	3.23	3.51	3.79	4.08	4.36	4.64	4.92	5.20

	Series	LE,	LEY25DS <sub>6</sub> (Motor mounting position: In-line)								LEY32DS <sub>7</sub> (Motor mounting position: In-line							ne)			
	Stroke [mm]		50									50	100	150	200	250	300	350	400	450	500
	Incremental encoder				1.84	2.02	2.19	2.37	2.54	2.72	2.44	2.55	2.84	3.31	3.59	3.87	4.16	4.44	4.72	5.00	5.28
€ ≥	Absolute encoder	1.40	1.47	1.64	1.90	2.08	2.25	2.43	2.60	2.78	2.38	2.49	2.78	3.25	3.53	3.81	4.10	4.38	4.66	4.94	5.22

<b>Additional Weigh</b>	t		[kg]					
	Size	25	32					
Lock	Incremental encoder	0.20	0.40					
LOCK	Absolute encoder [S6/S7]	0.30	0.66					
Rod end male thread	Male thread	0.03	0.03					
nou enu maie umeau	Nut	0.02	0.02					
Foot bracket (2 se	ts including mounting bolt)	0.08	0.14					
Rod flange (includ	ing mounting bolt)	0.17	0.20					
Head flange (including mounting bolt)								
Double clevis (including	pin, retaining ring, and mounting bolt)	0.16	0.22					



### Specifications: LECSS-T

		Model		LEY25T6 (Top	o/Parallel)/LEY2	25DT6 (In-line)	LEY3	2T7 (Top/Pa	arallel)	LEY	/32DT7 (In-	line)		
	Work los	al Fleat	Horizontal*1	18	50	50	30	60	60	30	60	60		
	work loa	Work load [kg]  Force [N]*2 (Set value Max.*3 speed [mm/s] Stroke range  Pushing speed [mm Max. acceleration/deceler Positioning repeatability [mm]  Lost motion [mm]*5  Lead [mm] (including Impact/Vibration resista Actuation type Guide type Operating temperature Operating humidity range Regeneration option Motor output/Size Motor type  Encoder  Power consumption [W]*7		8	16	30	9	19	37	12	24	46		
	Force [N]	ork load [kg]  proce [N]*2 (Set value: 1! ax.*3 peed range		65 to 131	127 to 255	242 to 485	79 to 157	154 to 308	294 to 588	98 to 197	192 to 385	368 to 736		
	Max.*3	Chualea	Up to 300	900	450	225	1200	600	300	1000	500	250		
	speed		305 to 400	600	300	150	1200	600	300	1000	500	250		
l Su	[mm/s]	•	405 to 500	_	_	_	800	400	200	640	320	160		
specifications	Pushing	speed [mm/	/s]* <sup>4</sup>		35 or less			30 or less			30 or less			
<u>8</u>	Max. accele				5000				50	00				
l ∰	Positioni	ing	Basic type		±0.02				±0.	.02				
be	repeatab	ility [mm]	High-precision type		±0.01				±0.	.01				
	Lost mot	tion [mm]*5	Basic type					0.1 or less						
울			High-precision type					0.05 or less						
Actuator				12	6	3	20	10	5	16 8 4				
A			nce [m/s <sup>2</sup> ]*6		50/20					0/20				
					elt (LEY□)/Ball s		Ball so	rew + Belt [			Ball screw			
				Sliding	bushing (Pis	ton rod)		S	liding bushin		d)			
					5 to 40				5 to					
			<del></del>	90 or less (No condensation) 90 or less (No condensation)										
			<u> </u>	May be required depending on speed and work load (Refer to pages 45 and 46.)										
ည					100 W/□40				200 V					
<u>.</u>	Motor ty	pe		AC sen	vo motor (20	00 VAC)		A	.C servo mot	tor (200 VA	C)			
pecifications	Encoder				Motor	type T6, T7	: Absolute 2	2-bit encode	er (Resolutio	n: 4194304	p/rev)			
ĕ	Power		Horizontal		45			65			65			
S	consum	otion [W]*7	Vertical		145			175			175			
Electric					2			2			2			
<u>8</u>		*	Vertical		8			8			8			
	Max. instanta	neous power cons	sumption [W]*9		445			724 724						
it ons	Type*10			Non-magnetising lock 131 255 485 157 308 588 197										
cunit				131 255 485				157 308 588			385	736		
Lock		nsumption [W	] at 20 °C*11		6.3			7.9			7.9			
- os	Rated vo	Itage [V]						24 VDC <sub>-10 %</sub>	5					

- \*1 This is the maximum value of the horizontal work load. An external guide is necessary to support the load. The actual work load changes according to the condition of the external guide. Confirm the load using the actual device.
- \*2 The force setting range (set values for the driver) for the force control with the torque control mode. Set it with reference to "Force Conversion Graph (Guide)" on page 48. When the control equivalent to the pushing operation of the controller LECP series is performed, combine the Simple Motion (manufactured by Mitsubishi Electric Corporation) which has a pushing operation function.
- \*3 The allowable speed changes according to the stroke.
- \*4 The allowable collision speed for collision with the workpiece with the torque control mode
- \*5 A reference value for correcting an error in reciprocal operation

- \*6 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.) Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
- \*7 The power consumption (including the driver) is for when the actuator is operating. \*8 The standby power consumption when operating (including the driver) is for when the actuator is stopped in the set position during the operation.
- \*9 The maximum instantaneous power consumption (including the driver) is for when the actuator is operating.
- \*10 Only when motor option "With lock" is selected
- \*11 For an actuator with lock, add the power consumption for the lock.

### Weight

#### **Product Weight**

oa	act weight																				
	Series LEY25T6 (Motor mounting position: Top/Parall											LEY3	32T7 (	(Moto	r mou	nting	positi	on: T	op/Pa	rallel)	
	Stroke [mm]	30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500
Motor	Absolute encoder	1.4	1.5	1.6	1.9	2.0	2.2	2.4	2.6	2.7	2.3	2.4	2.7	3.2	3.5	3.8	4.1	4.3	4.6	4.9	5.2

Series																						
Stroke [mm]	30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500		
Absolute encoder	1.4	1.5	1.6	1.9	2.1	2.2	2.4	2.6	2.8	2.4	2.5	2.8	3.2	3.5	3.8	4.1	4.4	4.6	4.9	5.2		


#### **Additional Weight**


Additional Weight											
	Size	25	32								
Lock	Absolute encoder [T6/T7]	0.3	0.4								
Rod end male thread	Male thread	0.03	0.03								
nou enu maie uneau	Nut	0.02	0.02								
Foot bracket (2 set	ts including mounting bolt)	0.08	0.14								
Rod flange (includ	ing mounting bolt)	0.17	0.20								
Head flange (inclu	ding mounting bolt)	0.17	0.20								
Double clevis (including	pin, retaining ring, and mounting bolt)	0.16	0.22								




### Construction

### Motor top mounting type: LEY $_{32}^{25}$





### In-line motor type: $LEY_{32}^{25}D$



### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminium alloy	Anodised
2	Ball screw shaft	Alloy steel	
3	Ball screw nut	Synthetic resin/Alloy steel	
4	Piston	Aluminium alloy	
5	Piston rod	Stainless steel	Hard chrome plating
6	Rod cover	Aluminium alloy	
7	Bearing holder	Aluminium alloy	
8	Rotation stopper	POM	
9	Socket	Free cutting carbon steel	Nickel plating
_10	Connected shaft	Free cutting carbon steel	Nickel plating
_11	Bushing	Bearing alloy	
12	Bearing	_	
13	Return box	Aluminium die-cast	Coating
14	Return plate	Aluminium die-cast	Coating
15	Magnet	_	
16	Wear ring holder	Stainless steel	Stroke 101 mm or more
17	Wear ring	POM	Stroke 101 mm or more
18	Screw shaft pulley	Aluminium alloy	
19	Motor pulley	Aluminium alloy	
20	Belt	_	
21	Parallel pin	Stainless steel	
_22	Seal	NBR	

No.	Description	Material	Note
23	Retaining ring	Steel for spring	
24	Motor adapter	Aluminium alloy	Coating
25	Motor	_	
26	Motor block	Aluminium alloy	Coating
27	Hub	Aluminium alloy	
28	Spider	Urethane	
29	Socket (Male thread)	Free cutting carbon steel	Nickel plating
30	Nut	Alloy steel	Zinc chromated

### Replacement Parts (Motor top/parallel only)/Belt

No.	Size	Order no.
00	25	LE-D-2-2
20	32	LE-D-2-4

### **Replacement Parts/Grease Pack**


Applied portion	Order no.
Piston rod	GR-S-010 (10 g) GR-S-020 (20 g)

<sup>\*</sup> Apply grease on the piston rod periodically. Grease should be applied at 1 million cycles or 200 km, whichever comes first.



LEY

### **Dimensions: Motor Top/Parallel**



- \*1 Range within which the rod can move Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.
- \*2 The direction of rod end width across flats ( $\square K$ ) differs depending on the products.


																			[mm]
Size	Stroke range [mm]	Α	В	С	D	EH	EV	Н	J	K	٦	M	<b>O</b> 1	R	s	Т	U	Υ	V
25	15 to 100	130.5	116	13	20	44	45.5	M8 x 1.25	24	17	14.5	34	M5 x 0.8	8	46	92	4	26.5	40
25	105 to 400	155.5	141	13	20	44	45.5	IVIO X 1.23	24	17	14.5	34	IVIO X U.O	0	40	92	'	20.5	40
32	20 to 100	148.5	130	13	25	<b>51</b>	56.5	M8 x 1.25	31	22	18.5	40	M6 x 1.0	10	60	118	4	34	60
32	105 to 500	178.5	160	13	25	51	30.3	IVIO X 1.23	31	22	10.5	40	IVIO X 1.0	10	60	110	'	34	60

	0		Inc	rement	al enco	der			Abso	lute end	oder [S	6/S7]			Abso	lute end	oder [T	6/T7]	
Size	Stroke range [mm]	Wi	ithout lo	ck	١	Vith loc	k	W	ithout lo	ck	٧	Vith lock	<	W	ithout lo	ck	٧	Vith lock	K
	[111111]	W	Х	Z	W	Х	Z	W	Х	Z	W	Х	Z	W	Х	Z	W	Х	Z
0.5	15 to 100	0.7	100	444	100.0	150.0	15.0	00.4	115.4	111	100 5	150.5	15.0	00.4	115.4	111	100	150	15.0
25	105 to 400	87	120	14.1	123.9	156.9	15.8	82.4	115.4	14.1	123.5	156.5	15.8	82.4	115.4	14.1	123	156	15.8
32	20 to 100	88.2	128.2	17.1	116.8	156.8	17.1	76.6	116.6	17.1	116.1	156.1	17.1	76.6	116.6	17.1	113.4	153.4	17.1
32	105 to 500	00.2	128.2	17.1	110.8	150.8	17.1	70.6	110.6	17.1	110.1	130.1	17.1	76.6	110.6	17.1	113.4	153.4	17.1

Body	Bottom <sup>-</sup>	Гарре	d								[mm]
Size	Stroke range [mm]	MA	МВ	МС	MD	МН	ML	МО	MR	XA	ХВ
	15 to 39			24	32		50				
	40 to 100			40	44		30				
25	101 to 124	20	46	42	42 41 29 59 49.5			M5 x 0.8	6.5	4	5
	125 to 200					75					
	201 to 400			76 58							
	20 to 39			22	36		50				
	40 to 100			36	43		50				
32	101 to 124	25	55	30	40	30		M6 x 1	8.5	5	6
	125 to 200		53 51.5		80						
	201 to 500			70	60						



### **Dimensions: Motor Top/Parallel**




\* When the motor is mounted on the left or right side in parallel, the groove for auto switch on the side to which the motor is mounted is hidden.

Electric Actuator/Rod Type LEY Series

AC Servo Motor Size 25, 32

### **Dimensions: In-line Motor**



\*1 Range within which the rod can move

Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.

\*2 The direction of rod end width across flats ( $\square K$ ) differs depending on the products.

Size	Stroke range [mm]	С	D	ЕН	EV	Н	J	K	L	М	<b>O</b> 1	R	S	Т	U	В	V [mm]
25	15 to 100 105 to 400	13	20	44	45.5	M8 x 1.25	24	17	14.5	34	M5 x 0.8	8	45	46.5	1.5	136.5 161.5	40
32	20 to 100 105 to 500	13	25	51	56.5	M8 x 1.25	31	22	18.5	40	M6 x 1.0	10	60	61	1	156 186	60


		Incremental encoder					Abso	lute end	coder [S	6/S7]		Absolute encoder [T6/T7]								
Size	Stroke range	Wi	thout lo	ck	١ ١	Vith loc	k	W	thout lo	ck	\ \	Vith lock	<	Wi	thout lo	ck	V	Vith loc	:k	
	[mm]	Α	W	Z	Α	W	Z	Α	W	Z	Α	W	Z	Α	VB	VC	Α	VB	VC	
	15 to 100	238	87	11.0	274.9	123.9	16.3	233.4	82.4 14.6	146	274.5	123.5 16.3	16.0	233.4	90 4 14	146	274	123	16.0	
25	105 to 400	263	07	14.6	299.9	123.9		258.4		14.0	299.5		10.3	258.4	82.4	14.6	299	123	16.3	
32	20 to 100	262.7	00.0	171	291.3	1100	171	251.1	70.0	171	290.6	116.1 1	171	251.1	70.0	17.1	287.9	110.4	171	
	105 to 500	292.7	88.2	17.1	321.3	116.8	16.8 17.1	281.1	76.6	17.1	320.6		17.1	281.1	76.6	6   17.1	317.9	113.4 1	17.1	

Body	Body Bottom Tapped [mm										
Size	Stroke range [mm]	MA	МС	MD	МН	ML	МО	MR	XA	ХВ	
	15 to 39		24	32		50	M5 x 0.8	6.5			
25	40 to 100		42	41		30			4	5	
	101 to 124	20		41	29						
	125 to 200		59	49.5		75					
	201 to 400		76	58							
	20 to 39		22	36		50		8.5			
	40 to 100		36	43							
32	101 to 124	25	30	40	30		M6 x 1		5	6	
,	125 to 200		53	51.5		80					
	201 to 500		70	60							



### **Dimensions**

### End male thread: LEY 32 B-DM C





- \* Refer to page 97 for details on the rod end nut and mounting bracket.
- Refer to the precautions on page 187 when mounting end brackets such as knuckle joint or workpieces.


	[m								
Size	B <sub>1</sub>	C <sub>1</sub>	Hı	L <sub>1</sub>	L <sub>2</sub>	ММ			
25	22	20.5	8	38	23.5	M14 x 1.5			
32	22	20.5	8	42.0	23.5	M14 x 1.5			

\* The L<sub>1</sub> measurement is when the unit is in the original position. At this position, 2 mm at the end.









Į	Foot [mr										[mm]				
Ī	Size	Stroke range [mm]	Α	LS	LS <sub>1</sub>	LL	LD	LG	LH	LT	LX	LY	LZ	Х	Υ
	25	15 to 100	136.6	98.8	19.8	.8 8.4	6.6	3.5	30	2.6	57	51.5	71	11.2	5.8
	25	101 to 400	161.6	123.8	19.0										
ı	32	20 to 100	155.7	114	10.2	11 2	6.6		36	3.2	76	61.5	00	11.0	7
		101 to 500	185.7	144	19.2	19.2 11.3	0.0	4	36	3.2	/6	61.5	90	11.2	<i>'</i>

Material: Carbon steel (Chromate treated)

- \* The A measurement is when the unit is in the Z-phase first detecting position. At this position, 2 mm at the end
- \* When the motor mounting is the right or left side parallel type, the head side foot bracket should be mounted outward.


[mm]

AC Servo Motor


### Electric Actuator/Rod Type LEY Series AC Servo Motor Size 25, 32

### **Dimensions**





### Head flange: LEY25 B- B- C



The head flange type is not available for the LEY32.

Included parts


- Flange
- · Body mounting bolt

Rod/Head Flange

Size	FD	FT	FV	FX	FZ	LL	M	
25	5.5	8	48	56	65	6.5	34	
32	5.5	8	54	62	72	10.5	40	

Material: Carbon steel (Nickel plating)

Double clevis: LEY $_{32}^{25}$  B---D



Included parts

- Double clevis
- · Body mounting bolt
- · Clevis pin
- · Retaining ring
- \* Refer to page 97 for details on the rod end nut and mounting bracket.

#### Double Clevis

Doub	ie Cievis				[mm
Size	Stroke range [mm]	Α	CL	CD	СТ
25	15 to 100	160.5	150.5	10	5
25	101 to 200	185.5	175.5	10	5
32	20 to 100	180.5	170.5	10	6
32	101 to 200	210.5	200.5	10	0

Size	Stroke range [mm]	CU	cw	сх	CZ	L	RR	
25	15 to 100	14	20	18	36	14.5	10	
20	101 to 200	17			00	14.5	10	
32	20 to 100	1.1	22	18	36	18.5	10	
32	101 to 200	14	22	10	30	10.5	10	

Material: Cast iron (Coating)

The A and CL measurements are when the unit is in the Z-phase first detecting position. At this position, 2 mm at the end.

### **Electric Actuator/** Rod Type Dust-tight/Water-jet-proof (IP65 Equivalent)

LEY Series

LEY63






LECY□ Series p. 87

Refer to page 41 for model selection.

and B below.

### How to Order



### Accuracy

_	Basic type
Н	High-precision type

2 Size

63

### Motor mounting position

_	Top mounting
R	Right side parallel
L	Left side parallel
D	In-line

### 6 Stroke [mm]

50	50
to	to
800	800
	50 to 800

For details, refer to the applicable stroke table below.

### 4 Motor type

Symbol	mbol Type		Actuator size	Compatible driver	UL-com- pliant
S4	AC servo motor (Incremental encoder)	400	63	LECSA2-S4	_
S8	AC servo motor (Absolute encoder)	400	63	LECSB2-S8 LECSC2-S8 LECSS2-S8	_
T8	encodery			LECSS2-T8	

### Lead [mm]

Symbol	LEY63	ı
Α	20	
В	10	
С	5	
L	2.86*1 *2	

\*1 Screw lead 5 mm, Pulley ratio [4:7] equivalent lead \*2 Only available for top mounting and right/left

side parallel types

### Dust-tight/Water-jet-proof

_	IP5x equivalent (Dust-protected)
Р	IP65 equivalent (Dust-tight/Water-jet-proof)/
•	With vent hole tap

- When using the dust-tight/water-jet-proof (IP65 equivalent), correctly mount the fitting and tubing to the vent hole tap, and then place the end of the tubing in an area not exposed to dust or water.
- The fitting and tubing should be provided separately by the customer. Select [Applicable tubing O.D.: Ø 4 or more, Connection thread: Rc1/8].
- \* Cannot be used in an environment where oil such as cutting oil splashes or it is constantly exposed to water. Take appropriate protective measures. For details on enclosure, refer to "Enclosure" on page 188.

### With lock

**1** Motor option

<b>1</b> Мо	Mounting*1													
Cumbal	Tuno		Motor mounting position											
Symbol	Туре		Top/Parallel	In-line										
_	Ends tapped/	*2	•											

Without option

Symbol	Type	Motor mounting position					
	туре	Top/Parallel	In-line				
_	Ends tapped/ Body bottom tapped*2	•	•				
L	Foot		_				
F	Rod flange*2		•				
D	Double clevis*3		_				

### 9 Rod end thread

_	Rod end female thread
М	Rod end male thread
IVI	(1 rod end nut is included.)

	Without cable	_	Withou
S	Standard cable	2	2
R	Robotic cable (Flexible cable)	5	5
*1 The	motor and encoder cables are included.	Α	10

\*2 The length of the encoder, motor, and lock cables are the same.

### \*1 The mounting bracket is shipped together with the product but does not come assembled.

- \*2 For the horizontal cantilever mounting of the rod flange or ends tapped types, use the actuator within the following stroke range.
  - LEY63: 400 mm or less
- \*3 For the mounting of the double clevis type, use the actuator within the following stroke range.
  - LEY63: 300 mm or less

### Cable length\*2 [m]

_	Without cable
2	2
5	5
Α	10

### B Driver type

	ver type		
	Compatible driver	Power supply voltage	UL-compliant
_	Without dr	_	
A2	LECSA2/Pulse input (Incremental encoder)	200 V to 230 V	_
B2	LECSB2/Pulse input (Absolute encoder)	200 V to 230 V	_
C2	LECSC2/CC-Link (Absolute encoder)	200 V to 230 V	_
S2	LECSS2-S/SSCNET III (Absolute encoder)	200 V to 230 V	_
32	LECSS2-T/SSCNET III/H (Absolute encoder)	200 V to 240 V	•

\* When a driver type is selected, a cable is included. Select the cable type and cable length.

Example) S2S2: Standard cable (2 m) + Driver (LECSS2)

S2 : Standard cable (2 m)

—: Without cable and driver

### 14 I/O cable length [m]\*1

Cable type\*1

_	Without cable
Н	Without cable (Connector only)
1	1.5

(The lock cable is also included when the

motor with lock option is selected.)

Standard cable entry direction is • Top/Parallel: (A) Axis side • In-line: (B) Counter axis side (Refer to page 264 for details.)

\*1 When "Without driver" is selected for driver type, only "-: Without cable" can be selected. Refer to page 265 if I/O cable is required. (Options are shown on page 265.)

### **Applicable Stroke Table**

Stroke [mm]	50	100	150	200	250	300	350	400	450	500	600	700	800	Manufacturable stroke range
LEY63		•	•	•	•	•	•		•	•			•	50 to 800

Please consult with SMC for non-standard strokes as they are produced as special orders.



Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

LEYG

AC Servo Motor

Electric Actuator/Rod Type LEY Series AC Servo Motor Size 63 Dust-tight/Water-jet-proof (IP65 Equivalent)

Option

### **Specifications**

		Model			LEY63S <sub>8</sub> <sup>4</sup> /T8	(Top/Parallel)		LEY	63DS <sub>8</sub> /T8 (In-	line)				
		,	Horizontal*1	40	70	80	200	40	70	80				
	Work load [k	91	Vertical*14	19	38	72	115	19	38	72				
	Force [N]/Set	value*2: 15 to	o 50 %*3 *4	156 to 521	304 to 1012	573 to 1910	1003 to 3343	156 to 521	304 to 1012	573 to 1910				
	*5		Up to 500	1000	500	250		1000	500	250				
	Max. speed	Stroke	505 to 600	800	400	200	70	800	400	200				
(0	[mm/s]	range	605 to 700	600	300	150	] /0 [	600	300	150				
ü			705 to 800	500	250	125		500	250	125				
specifications	Pushing spe						30 or less							
i£i	Max. accelera	ation/decelera	ation [mm/s <sup>2</sup> ]		5000		3000		5000					
e	Positioning r	epeatability	Basic type				±0.02							
	[mm]		High-precision type				±0.01							
ğ	Lost motion	[mm]* <sup>7</sup>	Basic type				0.1 or less							
Actuator		• •	High-precision type				0.05 or less		1					
Aci			g pulley ratio)	20	10	5	5 (2.86)	20	10	5				
_	Impact/Vibra		e [m/s²]*8				50/20							
	Actuation typ	ре			Ball screw + Bel		Ball screw + Belt [Pulley ratio 4:7]		Ball screw					
	Guide type			Sliding bushing (Piston rod)										
		nperature rar	<del></del>	5 to 40										
		midity range	[%RH]	90 or less (No condensation)										
	Regeneration			May be required depending on speed and work load (Refer to pages 43 and 44.)										
ဟ	Motor output	/Size		400 W/□60										
on	Motor type			AC servo motor (200 VAC)										
specifications	Encoder			Motor type S4: Incremental 17-bit encoder (Resolution: 131072 p/rev) Motor type S8: Absolute 18-bit encoder (Resolution: 262144 p/rev) Motor type T8: Absolute 22-bit encoder (Resolution: 4194304 p/rev)										
spe	Dawer age		Horizontal				210							
	Power consu	mption [w]**	Vertical				230							
Electric	Standby power	rconsumption	Horizontal				2							
Ele	when operating	g [W]* <sup>10</sup>	Vertical				18							
		ous power cons	sumption [W]*11				1275							
it	Type*12						n-magnetising lo							
catic	Holding force			313	607	1146	2006	313	607	1146				
Lock unit ecification		mption [W] a	t 20 °C*13				7.9							
ds	Rated voltage	e [V]					24 VDC <sup>0</sup> <sub>-10 %</sub>							

- **\*1** This is the maximum value of the horizontal work load. An external guide is necessary to support the load. The actual work load changes according to the condition of the external guide. Confirm the load using the actual device.
- Set values for the driver
- The force setting range (set values for the driver) for the force control with the torque control mode. The force and duty ratio change according to the set value. Set it with reference to "Force Conversion Graph" on page 45. When the control equivalent to the pushing operation of the controller LECP series is performed, select the LECSS driver and combine it with the Simple Motion (manufactured by Mitsubishi Electric Corporation) which has a pushing operation function.
- For the motor type T8, the set value is from 12 to 40 %. The allowable speed changes according to the stroke. Set the number of rotations according to speed. The allowable collision speed for collision with the workpiece with the torque control mode

- \*7 A reference value for correcting an error in reciprocal operation
  \*8 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)

Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)

\*9 The power consumption (including the driver) is for when the actuator is operating.

\*10 The standby power consumption when operating (including the driver) is for when the actuator is stopped in the set position during the operation.

\*11 The maximum instantaneous power consumption (including the driver) is for when the actuator is operating.

\*12 Only when motor option "With lock" is selected

- \*13 For an actuator with lock, add the power consumption for the lock.
  \*14 When mounting vertically and using the product facing upwards in an environment where water is present, take necessary measures to prevent water from splashing on the rod cover, because water will accumulate on the rod seal due to the structure of the product.

### Weight

Pr	oduct Weight													[kg]
Series LEY63S <sub>8</sub> (Motor mounting position: Top/Parallel)														
	Stroke [mm]	50	100	150	200	250	300	350	400	450	500	600	700	800
type	Incremental encoder	4.9	5.4	6.0	6.6	7.8	8.3	8.9	9.4	10.0	10.5	12.2	13.4	14.5
	Absolute encoder (Motor type S8)	5.0	5.5	6.1	6.7	7.9	8.4	9.0	9.5	10.1	10.6	12.3	13.5	14.6
Motol	Absolute encoder (Motor type T8)	4.9	5.4	6.0	6.6	7.8	8.3	8.9	9.4	10.0	10.5	12.2	13.4	14.5
	Series LEY63DS <sup>4</sup> (Motor mounting position: In-line)													


	Series	LEY63DS <sub>8</sub> (Motor mounting position: In-line										)		
	Stroke [mm]	50	100	150	200	250	300	350	400	450	500	600	700	800
type	Incremental encoder	5.1	5.6	6.2	6.7	7.9	8.4	9.0	9.6	10.2	10.7	12.4	13.5	14.7
	Absolute encoder (Motor type S8)	5.2	5.7	6.3	6.8	8.0	8.5	9.1	9.7	10.3	10.8	12.5	13.6	14.8
Motor	Absolute encoder (Motor type T8)	5.1	5.6	6.2	6.7	7.9	8.4	9.0	9.6	10.2	10.7	12.4	13.5	14.7


Additiona	al Weight	[kg]
	Size	63
	Incremental encoder	0.4
Lock	Absolute encoder (Motor type S8)	0.6
	Absolute encoder (Motor type T8)	0.4
Rod end	Male thread	0.12
male thread	Nut	0.04
Foot bracket (2	sets including mounting bolt)	0.26
Rod flange (	including mounting bolt)	0.51
	is (including pin, g, and mounting bolt)	0.58


\* Option

### Construction


### Motor top mounting type: LEY63







### In-line motor type: LEY63D



### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminium alloy	Anodised
2	Ball screw shaft	Alloy steel	
3	Ball screw nut	Resin/Alloy steel	
4	Piston	Aluminium alloy	
5	Piston rod	Stainless steel	Hard chrome plating
6	Rod cover	Aluminium alloy	
7	Bearing holder	Aluminium alloy	
8	Rotation stopper	Resin	
9	Socket	Free cutting carbon steel	Nickel plating
10	Bushing	Lead bronze cast	
11	Bearing	_	
12	Return box	Aluminium alloy	Coating
13	Return plate	Aluminium alloy	Coating
14	Magnet	_	
15	Wear ring holder	Stainless steel	

Deplessment	Doute	/N/10+0×	+/	marallal	anly//Dal	
Replacement	raits	(INIOLOI	ιορ/	paranei	Ulliy // Del	L

ĺ	No.	Size	Lead	Order no.
	19	63	A/B/C	LE-D-2-5
	19	03	L	LE-D-2-6

No.	Description	Material	Note
16	Wear ring	Resin	
17	Screw shaft pulley	Aluminium alloy	
18	Motor pulley	Aluminium alloy	
19	Belt	_	
20	Lock nut	Alloy steel	Black dyed
21	Seal	NBR	
22	Retaining ring	Steel for spring	
23	Motor adapter	Aluminium alloy	Coating
24	Motor	_	
25	Socket (Male thread)	Free cutting carbon steel	Nickel plating
26	Nut	Alloy steel	Trivalent chromated
27	Motor block	Aluminium alloy	Coating
28	Spacer A	Stainless steel	
29	Hub	Aluminium alloy	
30	Spider	Urethane	

### **Replacement Parts/Grease Pack**

Applied portion	Order no.
Piston rod	GR-S-010 (10 g) GR-S-020 (20 g)

<sup>\*</sup> Apply grease on the piston rod periodically. Grease should be applied at 1 million cycles or 200 km, whichever comes first.




Ē


AC Servo Motor

Electric Actuator/Rod Type LEY Series AC Servo Motor Size 63 Dust-tight/Water-jet-proof (IP65 Equivalent)

\* Option

### **Dimensions: Motor Top/Parallel**






- \*1 Range within which the rod can move Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.
- \*2 The direction of rod end width across flats (□K) differs depending on the products.

### IP65 equivalent (Dust-tight/Water-jet-proof): LEY63 Della P

(View ZZ)



\*1 When using the dust-tight/water-jet-proof (IP65 equivalent), correctly mount the fitting and tubing to the vent hole tap, and then place the end of the tubing in an area not exposed to dust or water. The fitting and tubing should be provided separately by the customer. Select [Applicable tubing O.D.: Ø 4 or more, Connection thread: Rc1/8].

																			[mm]
Size	Stroke range [mm]	Α	В	С	D	EH	EV	н	J	К	L	М	<b>O</b> 1	R	S	Υ	Т	U	V
	Up to 200	192.6	155.2																
63	205 to 500	227.6	190.2	21	40	76	82	M16 x 2	44	36	37.4	60	M8 x 1.25	16	80	32.2	146	4	60
	505 to 800	262.6	225.2																

			ln	crement	al enco	der			Abs	olute end	coder	[S8]		Absolute encoder [T8]																					
Size	Stroke range [mm]	W	ithout le	ock	1	With loc	k	Without lock			With lock			Without lock			With lock																		
	[IIIIII]	W	Х	Z	W	Х	Z	W	Х	Z	W	Х	Z	W	Х	Z	W	Х	Z																
63	Up to 200	110.2 150.2																					15.6												
	205 to 500		10.2 150.2	15.6 (16.6)*1	138.8	178.8	15.6 (16.6)*1	15.6	98.5   138.5	.5 15.6	138	178	15.6 (16.6)*1	98.3   138	138.3	15.6 (16.6)*1	135.1	175.1	15.6 (16.6)*1																
	505 to 800			(10.0)						(10.0)			(10.0)			(10.0)			(10.0)																

\*1 The values in ( ) are the dimensions when L is selected for screw lead.


Dady	Dattam	Tanned
		12000

Body E	Bottom Ta	pped								[mm]
Size	Stroke range [mm]	MA	МС	MD	МН	ML	МО	MR	XA	ХВ
	50 to 74		24	50						
63	75 to 124		45	60.5		65		10	6	
	125 to 200	38	58	67	44		M8 x 1.25			7
	201 to 500		86	81		100				
	501 to 800		80	01		135				




### **Dimensions: Motor Top/Parallel**

### Motor left side parallel type: LEY63L



[mm]
Size S<sub>1</sub> T<sub>2</sub> U
63 84 142 4






\* When the motor is mounted on the left or right side in parallel, the groove for auto switch on the side to which the motor is mounted is hidden.

Electric Actuator/Rod Type LEY Series AC Servo Motor Size 63 Dust-tight/Water-jet-proof (IP65 Equivalent)

\* Option

### **Dimensions: In-line Motor**



- \*1 Range within which the rod can move Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.
- \*2 The direction of rod end width across flats (\(\subseteq K\)) differs depending on the products.


Size	Stroke range [mm]	С	D	EH	EV	Н	J	К	L	М	<b>O</b> 1	R	s	Т	U	В	V		
	Up to 200																	190.7	
63	205 to 500	21	40	76	82	M16 x 2	44	36	37.4	60	M8 x 1.25	16	78	83	5	225.7	60		
	505 to 800															260.7			

	Q	Incremental encoder							Absolute encoder [S8]						Absolute encoder [T8]				
Size	Stroke range [mm]	Wit	hout loc	k	With lock			Without lock			With lock			Without lock			With lock		
	[iiiiii]	Α	W	Z	Α	W	Z	Α	W	Z	Α	W	Z	Α	W	Z	Α	W	Z
	Up to 200	338.3			366.9			326.6			366.1			326.4			363.2		
63	205 to 500	373.3	110.2	8.1	401.9	138.8	8.1	361.6	98.5	8.1	401.1	138	8.1	361.4	98.3	8.1	398.2	135.1	8.1
	505 to 800	408.3			436.9			396.6			436.1			396.4			433.2		

**Body Bottom Tapped** 

Body Bottom Tapped [mm									[mm]	
Size	Stroke range [mm]	MA	МС	MD	МН	ML	МО	MR	XA	ХВ
	50 to 74	38	24	50	0.5 7 44	65	M8 x 1.25	10	6	7
	75 to 124		45	60.5						
63	125 to 200		58	67						
	201 to 500		86	6 81		100				
	501 to 800		00 01	01		135				

### IP65 equivalent (Dust-tight/Water-jet-proof): LEY63D□□-□P (View ZZ)




When using the dust-tight/water-jet-proof (IP65 equivalent), correctly mount the fitting and tubing to the vent hole tap, and then place the end of the tubing in an area not exposed to dust or water. The fitting and tubing should be provided separately by the customer.

Select [Applicable tubing O.D.: Ø 4 or more, Connection thread: Rc1/8].

Option


### **Dimensions**


### End male thread: LEY63□□-□□M




\*1 The measurement 76.4 is when the unit is in the Z-phase detecting position. At this position, 4 mm from the end of the operating range.

### Foot: LEY63 D-DL







### Included parts


- Foot bracket
- Body mounting bolt

#### Material: Carbon steel (Chromate treated)

- \* The overall length is when the unit is in the Z-phase detecting position. At this position, 4 mm from the end of the operating range.
- When the motor mounting is the right or left side parallel type, the head side foot bracket should be mounted outward.

	[mm]
LA	LS
200.8	133.2
235.8	168.2
270.8	203.2
	200.8

### Rod flange: LEY63□□-□□F




#### Included parts

- Flange
- Body mounting bolt

Material: Carbon steel (Nickel plating)

\*1 When the unit is in the Z-phase detecting position. At this position, 4 mm from the end of the operating range.

### Double clevis: LEY63 DD-DD



Included parts
<ul> <li>Double clevis</li> </ul>
<ul> <li>Body mounting bolt</li> </ul>
• Clavic pin

<ul> <li>Body mounting bo</li> </ul>
<ul> <li>Clevis pin</li> </ul>
<b>D</b>

Retaining ring

		[mm]
Stroke range [mm]	DA	CL
50 to 200	236.6	222.6
201 to 500	271.6	257.6
501 to 800	306.6	292.6

Material: Cast iron (Coating)

\* The overall length is when the unit is in the Z-phase detecting position. At this position, 4 mm from the end of the operating range.

Specific Product Precautions

<b>SMC</b>
------------

### **Electric Actuator/ Rod Type**


LEY Series LEY25, 32, 63



Dust-tight/Water-jet-proof (IP65 Equivalent)▶p. 169 Secondary Battery Compatible▶p. 183

LECS□ Series >p. 69, 79

### **How to Order**



### Accuracy

<b>O</b> Hooding				
_	Basic type			
Н	High-precision type			

	Size	
2	5	

2

32 63

iz	е
	1

### Motor mounting position

_	Top mounting
R	Right side parallel
L	Left side parallel
D	In-line

### **4** Motor type

U IVIO	Motor type				
Symbol	Туре	Output [W]	Size	Compatible driver	
<b>V6</b> *1	AC servo motor (Absolute encoder)	100	25	LECYM2-V5 LECYU2-V5	
V7		200	32	LECYM2-V7 LECYU2-V7	
V8		400	63	LECYM2-V8 LECYU2-V8	

\*1 For motor type V6, the compatible driver part number suffix is V5.

### 5 Lead [mm]

Symbol	LEY25	LEY32*1	LEY63	
Α	12	16 (20)	20	
В	6	8 (10)	10	
С	3	4 (5)	5	
L	_	_	2.86*2	

- \*1 The values shown in ( ) are the leads for the top mounting, right/left side parallel types. (Equivalent leads which include the pulley ratio [1.25:1])
- \*2 Only available for top mounting and right/left side parallel types (Equivalent leads which include the pulley ratio [4:7])

### 6 Stroke [mm]

30	30
to	to
800	800

\* For details, refer to the applicable stroke table below.

### Dust-tight/Water-jet-proof (Only available for LEY63)

Symbol	LEY25/32	LEY63
_	IP4x equivalent	IP5x equivalent (Dust-protected)
Р	_	IP65 equivalent (Dust-tight/ Water-jet-proof)/With vent hole tap

- When using the dust-tight/water-jet-proof (IP65 equivalent), correctly mount the fitting and tubing to the vent hole tap, and then place the end of the tubing in an area not exposed to dust or water.
- The fitting and tubing should be provided separately by the customer. Select [Applicable tubing O.D.: Ø 4 or more, Connection thread:
- Cannot be used in environments exposed to cutting oil, etc. Take appropriate protective measures. For details on enclosure, refer to "Enclosure" on page 188.

### 8 Motor option

_	Without option
В	With lock

\* When "With lock" is selected for the top mounting and right/left side parallel types, the motor body will stick out from the end of the body for size 25 with strokes of 30 mm or less. Check for interference with workpieces before selecting a model.



### 9 Rod end thread

_	Rod end female thread
M	Rod end male thread (1 rod end nut is included.)

Applicable Stroke	Applicable Stroke Table   •: Standar														
Stroke [mm]	30	50	100	150	200	250	300	350	400	450	500	600	700	800	Manufacturable stroke range
LEY25	•	•	•	•	•	•	•	•	•	_	_	_	_	_	15 to 400
LEY32	•	•	•	•	•	•	•	•	•		•	_	_	_	20 to 500
LEY63	_	•	•	•	•	•	•	•	•		•			•	50 to 800

Please consult with SMC for non-standard strokes as they are produced as special orders.





Motor mounting position: Top/Parallel

Motor mounting position: In-line

Mounting\*1

5	Cumbal	Type	Motor moun	ting position
	Symbol	Type	Top/Parallel	In-line
		Ends tapped/ Body bottom tapped*2	•	•
	L	Foot	•	_
	F	Rod flange*2	●*4	•
	G	Head flange*2	●*5	
	D	Double clevis*3		

- \*1 The mounting bracket is shipped together with the product but does not come assembled.
- \*2 For the horizontal cantilever mounting of the ends tapped, rod flange, or head flange types, use the actuator within the following stroke range.
  - · LEY25: 200 mm or less · LEY32: 100 mm or less · LEY63: 400 mm or less
- \*3 For the mounting of the double clevis type, use the actuator within the following stroke range.
  - · LEY25: 200 mm or less · LEY32: 200 mm or less · LEY63: 300 mm or less
- \*4 The rod flange type is not available for the LEY25 with a 30 mm stroke and motor option "With lock."
- \*5 The head flange type is not available for the LEY32/LEY63.

Cable type\*1

_	Without cable
S	Standard cable
R	Robotic cable (Flexible cable)

<sup>\*1</sup> The motor and encoder cables are included. The motor cable for lock option is included when the motor with lock option is selected.

Cable length [m]\*1

_	Without cable
3	3
5	5
Α	10
С	20

<sup>\*1</sup> The length of the motor and encoder cables are the same. (For with lock)

13 Driver type

\	Compatible driver	Power supply voltage [V]
_	Without driver	_
12	LECYM2-V□	200 to 230
J2	LECYU2-V□	200 to 230
		Without driver LECYM2-V□


When a driver type is selected, a cable is included. Select the cable type and cable

1/O cable length [m]\*1

	<u> </u>
_	Without cable
Н	Without cable (Connector only)
1	1.5

\*1 When "Without driver" is selected for driver type, only "-: Without cable" can be selected. Refer to page 278 if I/O cable is required. (Options are shown on page 278.)

**Compatible Driver** 







### **Specifications**

		Model		LEY25V6 (Top	o/Parallel)/LEY	25DV6 (In-line)	LEY3	2V7 (Top/Pa	arallel)	LEY32DV7 (In-line)					
	Warls Iaa	al Floari	Horizontal*1	18	50	50	30	60	60	30	60	60			
	Work load [kg]		Vertical	8	16	30	9	19	37	12	24	46			
	Force [N]*2 (Set value: 45 to 90 %		<b>%)</b>	65 to 131	127 to 255	242 to 485	79 to 157	154 to 308	294 to 588	98 to 197	192 to 385	368 to 736			
	Max.*3	Stroke	Up to 300	900	450	225	1200	600	300	1000	500	250			
	speed	range	305 to 400	600	300	150	1200	000	300	1000	300	250			
ns	[mm/s]	range	405 to 500	_	_	_	800	400	200	640	320	160			
을	Pushing	speed [mm/	/s]*4		35 or less			30 or less			30 or less				
ca	Max. accele	eration/decelera	ation [mm/s <sup>2</sup> ]		5000				50	00					
pecifications	Positioni	ng	Basic type		±0.02				±0.	.02					
	repeatab	ility [mm]	High-precision type		±0.01				±0.	.01					
S	Lost mot	ion*5	Basic type		0.1 or less				0.1 o	r less					
Actuator	[mm]		High-precision type		0.05 or less				0.05 c	or less					
Ę	Lead [mm	] (including p	ulley ratio)			10	5	16	8	4					
Ac	Impact/Vib	ration resista	nce [m/s <sup>2</sup> ]*6		50/20		50/20								
	Actuatio	n type		Ball screw + Be	elt (LEY□)/Ball s	screw (LEY□D)	Ball screw + Belt [1.25:1] Ball screw								
	Guide ty	ре		Sliding	bushing (Pis	ton rod)	Sliding bushing (Piston rod)								
	Operating	temperature	range [°C]		5 to 40		5 to 40								
	Operating	humidity ra	nge [%RH]	90 or les	ss (No conde	nsation)	90 or less (No condensation)								
	Conditions f	or* <sup>7</sup>	Horizontal		Not required		Not required								
	"Regenerati	ve resistor" [kg]	Vertical		6 or more		4 or more								
ns	Motor ou	tput/Size			100 W/□40		200 W/□60								
specifications	Motor ty	ре		AC ser	vo motor (20	00 VAC)	AC servo motor (200 VAC)								
<u>2</u>	Encoder					Absolute	te 20-bit encoder (Resolution: 1048576 p/rev)								
증	Power		Horizontal		45			65			65				
sbe	consump	tion [W]*8	Vertical		145			175			175				
<u>.</u> 2	Standby pow	er consumption	Horizontal		2			2			2				
ectric	when operat	ing [W]*9	Vertical		8			8			8				
ä		neous power consu	umption [W]*10		445			724			724				
t	Type*11						Non-	-magnetising	lock						
cation	Holding			131	255	485	157	308	588	197	385	736			
Si ii	Power cor	sumption [W	] at 20 °C*12	5.5 6 6											
ads	Rated vo	Itage [V]						24 VDC +10 %	6						

- \*1 This is the maximum value of the horizontal work load. An external guide is necessary to support the load. The actual work load changes according to the condition of the external guide. Confirm the load using the actual device.
- \*2 The force setting range (set values for the driver) for the force control with the torque control mode. Set it with reference to "Force Conversion Graph (Guide)" on page 52.
- \*3 The allowable speed changes according to the stroke.
- \*4 The allowable collision speed for collision with the workpiece with the torque control mode
- \*5 A reference value for correcting an error in reciprocal operation
- \*6 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)

Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)

- \*7 The work load conditions which require "Regenerative resistor" when operating at the maximum speed (Duty ratio: 100 %). Order the regenerative resistor separately. For details, refer to "Conditions for Regenerative Resistor (Guide)" on pages 50 and 51.
- \*8 The power consumption (including the driver) is for when the actuator is operating.
- \*9 The standby power consumption when operating (including the driver) is for when the actuator is stopped in the set position during the operation.
- \*10 The maximum instantaneous power consumption (including the driver) is for when the actuator is operating.
- \*11 Only when motor option "With lock" is selected
- \*12 For an actuator with lock, add the power consumption for the lock.

### Weight

Product Weight	roduct Weight															[kg]				
Series	LEY	25V6	(Moto	r mou	ınting	positi	on: To	p/Pai	allel)		LEY3	32V7	(Moto	r mou	nting	positi	ion: T	op/Pa	rallel)	
Stroke [mm]	30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500
Weight [kg]	1.2	1.3	1.6	1.7	1.9	2.1	2.2	2.4	2.6	2.3	2.4	2.7	3.2	3.5	3.8	4.0	4.3	4.6	4.9	5.2
Series	Series LEY25DV6 (Motor mounting position: In-line)												V7 (N	lotor ı	mount	ting p	ositio	n: In-li	ine)	
Stroke [mm]	30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500
Weight [kg]	1.2	1.3	1.5	1.7	1.9	2.1	2.3	2.4	2.6	2.3	2.4	2.7	3.2	3.5	3.8	4.1	4.3	4.6	4.9	5.2

Additional Weight [kg]										
	Size	25	32							
Lock	0.30	0.60								
Rod end male thread	Male thread	0.03	0.03							
nou enu maie imeau	Nut	0.02	0.02							
Foot bracket (2 se	ts including mounting bolt)	0.08	0.14							
Rod flange (includ	ing mounting bolt)	0.17	0.20							
Head flange (inclu	0.17	0.20								
Double clevis (including	pin, retaining ring, and mounting bolt)	0.16	0.22							



Electric Actuator/Rod Type LEY Series AC Servo Motor Size 25, 32, 63

### **Specifications**

	Model			LEY63V8 (	Top/Parallel)		LE	Y63DV8 (In-li	ne)				
Work load [kg	,	Horizontal*1	40	70	80	200	40	70	80				
Work load [kg	J	Vertical	19	38	72	115	19	38	72				
Force [N]/Set v	/alue*2 : 45 to	o 150 %*3	156 to 521	304 to 1012	573 to 1910	1003 to 3343	156 to 521	304 to 1012	573 to 1910				
*4		Up to 500	1000	500	250		1000	500	250				
	Stroke	505 to 600	800	400	200	70	800	400	200				
[mm/s]	range	605 to 700	600	300	150	] /0	600	300	150				
ဋ		705 to 800	500	250	125		500	250	125				
Pushing speed	d [mm/s]*5					30 or less							
Pushing speed Max. accelerat Positioning re [mm]	tion/decelera	tion [mm/s²]		5000 3000 5000									
Positioning re	peatability	Basic type	±0.02										
<u>[mm]</u>		High-precision type		±0.01									
	nm1*6	Basic type				0.1 or less							
<u> </u>		High-precision type				0.05 or less							
Screw lead [m			20	10	20	10	5						
▼ Impact/Vibrati	on resistanc	e [m/s²]*7				50/20							
Actuation type	•			Ball screw		Ball screw + Belt [Pulley ratio 4:7]		Ball screw					
Guide type					Slidin	g bushing (Pisto	n rod)						
Operating tem	•	0 1 1	5 to 40										
Operating hun			90 or less (No condensation)										
Conditions for*		Horizontal				Not required							
"Regenerative r		Vertical				2.5 or more							
ဖု Motor output/9	Size					400 W/□60							
Motor type						ervo motor (200							
Encoder				Ab	solute 20-bit en	coder (Resolution	on: 1048576 p/i	rev)					
Motor outputs  Motor type  Encoder  Power consum	notion [W]*9	Horizontal				210							
		Vertical				230							
Standby power of when operating		Horizontal				2							
when operating		Vertical				18							
wax. mstantaneo	ous power cons	sumption [W]*11				1275							
Type*12 Holding force Power consum				ı		n-magnetising lo		I					
Holding force			313	607	1146	2006	313	607	1146				
		20 °C*13				6							
Rated voltage	[V]					24 VDC +10 %							

- \*1 This is the maximum value of the horizontal work load. An external guide is necessary to support the load. The actual work load changes according to the condition of the external guide. Confirm the load using the actual device.
- \*2 Set values for the driver
- \*3 The force setting range (set values for the driver) for the force control with the torque control mode. The force and duty ratio change according to the set value. Set it with reference to "Force Conversion Graph (Guide)" on page 52.
- \*4 The allowable speed changes according to the stroke.
- \*5 The allowable collision speed for collision with the workpiece with the torque control mode
- \*6 A reference value for correcting an error in reciprocal operation
- \*7 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)

Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)

- \*8 The work load conditions which require "Regenerative resistor" when operating at the maximum speed (Duty ratio: 100 %)
- \*9 The power consumption (including the driver) is for when the actuator is operating.
- \*10 The standby power consumption when operating (including the driver) is for when the actuator is stopped in the set position during the operation.
- \*11 The maximum instantaneous power consumption (including the driver) is for when the actuator is operating.
- \*12 Only when motor option "With lock" is selected
- \*13 For an actuator with lock, add the power consumption for the lock.

### Weight


Product Weight													[kg]
Series		LEY63V8 (Motor mounting position: Top/Parallel)											
Stroke [mm]	50	100	150	200	250	300	350	400	450	500	600	700	800
Weight [kg]	4.8	5.3	6.0	6.0 6.5		8.2	8.8	9.3	9.9	10.4	12.1	13.3	14.4
Series			LEY	63D\	/8 (M	otor r	noun	ting p	ositio	n: In	-line)		
Stroke [mm]	50	100	150	200	250	300	350	400	450	500	600	700	800
Weight [kg]	5.0	5.5	6.1	6.6	7.8	8.3	9.0	9.5	10.1	10.6	12.3	13.4	14.6


Additional Weight									
	Size	63							
Lock									
Rod end	Male thread	0.12							
male thread	Nut	0.04							
Foot bracket (2	sets including mounting bolt)	0.26							
Rod flange (	including mounting bolt)	0.51							
Double clevis (including pin, retaining ring, and mounting bolt)									




### Construction











**Component Parts** 

No.	Description	Material	Note
1	Body	Aluminium alloy	Anodised
2	Ball screw shaft	Alloy steel	
3	Ball screw nut	Resin/Alloy steel	
4	Piston	Aluminium alloy	
5	Piston rod	Stainless steel	Hard chrome plating
6	Rod cover	Aluminium alloy	
7	Bearing holder	Aluminium alloy	
8	Rotation stopper	POM	
9	Socket	Free cutting carbon steel	Nickel plating
10	Connected shaft	Free cutting carbon steel	Nickel plating
11	Bushing	Bearing alloy	
12	Bearing	_	
13	Return box	Aluminium die-cast	Coating
14	Return plate	Aluminium die-cast	Coating
15	Magnet	_	
16	Wear ring holder	Stainless steel	Stroke 101 mm or more
17	Wear ring	POM	Stroke 101 mm or more
18	Screw shaft pulley	Aluminium alloy	

No.	Description	Material	Note
19	Motor pulley	Aluminium alloy	
20	Belt	_	
21	Parallel pin	Stainless steel	
22	Seal	NBR	
23	Retaining ring	Steel for spring	Phosphate coated
24	Motor adapter	Aluminium alloy	Coating
25	Motor	_	
26	Motor block	Aluminium alloy	Coating
27	Hub	Aluminium alloy	
28	Spider	Urethane	
29	Socket (Male thread)	Free cutting carbon steel	Nickel plating
30	Nut	Alloy steel	Zinc chromated


Replacement Parts (Motor top/parallel only)/Belt


No.	Size	Order no.	No.	Size	Lead	Order no.
00	<b>25</b> LE-D-2-2	LE-D-2-2	00	60	A/B/C	LE-D-2-5
20	32	LE-D-2-4	20	63	L	LE-D-2-6

Ē

### Electric Actuator/Rod Type LEY Series AC Servo Motor Size 25, 32, 63


### **Dimensions: Motor Top/Parallel**





### IP65 equivalent (Dust-tight/Water-jet-proof): LEY63□□-□P

(View ZZ)



\*1 When using the dust-tight/water-jet-proof (IP65 equivalent), correctly mount the fitting and tubing to the vent hole tap, and then place the end of the tubing in an area not exposed to dust or water. The fitting and tubing should be provided separately by the customer.
Select [Applicable tubing O.D.: Ø 4 or more, Connection thread: Rc1/8].

																			[mm]
Size	Stroke range [mm]	Α	В	С	D	EH	EV	Н	J	к	L	М	O <sub>1</sub>	R	s	Т	U	Υ	V
25	15 to 100	130.5	116	13	20	44	45.5	M8 x 1.25	24	17	14.5	34	M5 x 0.8	8	46	92	4	26.5	40
25	105 to 400	155.5	141	13	20	44	45.5	IVIO X 1.25	24	17	14.5	34	IVIS X U.6	0	40	92	'	20.5	40
32	20 to 100	148.5	130	13	25	51	56.5	M8 x 1.25	31	22	18.5	40	M6 x 1.0	10	60	118	4	34	60
32	105 to 500	178.5	160	13	25	51	36.3	IVIO X 1.25	31	22	10.5	40	IVIO X 1.0	10	60	110	'	34	60
	Up to 200	192.6	155.2																
63	205 to 500	227.6	190.2	21	40	76	82	M16 x 2	44	36	37.4	60	M8 x 1.25	16	80	146	4	32.2	60
	505 to 800	262.6	225.2																

Size	Stroke range	V	/ithout	lock	,	With Io	ck	Е	G
Size	[mm]	W	X	Z	W	X	Z	Г	G
25	15 to 100	00 E	115.5	11	107 5	160.5	11	2	4
25	105 to 400	02.5	115.5	''	127.5	160.5	11		4
32	20 to 100	80	120	14	120	160	14	2	4
32	105 to 500	00	120	14	120	160	14	2	4
	50 to 200			10.5			10.5		
- · ·	205 to 500	98.5	138.5	12.5 (13.5)*1	138.5	178.5	12.5 (12.5)*1	4	8
	505 to 800			(13.5)			(13.3)		

_	_	
*1	L	lead


Body	y Bottom	Ta	ppe	d							[mm]
Size	Stroke range [mm]	MA	МВ	МС	MD	МН	ML	МО	MR	XA	ХВ
	15 to 35			24	32		50				
	40 to 100		46	42	41		50	M5 x 0.8			
25	105 to 120	20		72	41	29			6.5	4	5
	125 to 200			59	49.5		75				
	205 to 400			76	58						
	20 to 35		55	22	36		50				
	40 to 100			36	43		50				
32	105 to 120	25		30	43	30	80	M6 x 1	8.5	5	6
	125 to 200			53	51.5						
	205 to 500			70	60						
	50 to 70			24	50						
	75 to 120			45	60.5		65				
63	125 to 200	38	52.2	58	67	44		M8 x 1.25	10	6	7
	205 to 500			86	81		100				
	505 to 800			00	01		135				





### **Dimensions: Motor Top/Parallel**

Motor left side parallel type: LEY 32 L

Motor right side parallel type: LEY 32 R 63








\* When the motor is mounted on the left or right side in parallel, the groove for auto switch on the side to which the motor is mounted is hidden.

LEY

AC Servo Motor

# Electric Actuator/Rod Type LEY Series AC Servo Motor Size 25, 32, 63

### **Dimensions: In-line Motor**



- Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.
- \*2 The direction of rod end width across flats (□K) differs depending on the products.

																	[mm]
Size	Stroke range [mm]	С	D	EH	EV	н	J	K	L	M	O <sub>1</sub>	R	s	Т	U	В	V
25	15 to 100	13	20	44	45.5	M8 x 1.25	24	17	14.5	34	M5 x 0.8	8	45	46.5	1.5	136.5	40
	105 to 400 20 to 100															161.5 156	
32	105 to 500	13	25	51	56.5	M8 x 1.25	31	22	18.5	40	M6 x 1.0	10	60	61	1	186	60
	50 to 200															190.7	
63	205 to 500	21	40	76	82	M16 x 2	44	36	37.4	60	M8 x 1.25	16	78	83	5	225.7	60
	505 to 800															260.7	


ĺ	Size	Stroke range	Wit	hout lo	ck	V	Vith lock		F	G
25	[mm]	Α	W	Z	Α	W	Z	_ F	G	
	25	15 to 100	233.5	82.5	11.5	278.5	127.5	11.5	2	4
	32	105 to 400	258.5	02.5	11.5	303.5	127.5	11.5		4
		20 to 100	254.5	80	14	294.5	120	14	2	4
	32	105 to 500	284.5	00	14	324.5	120		~	4
	63	50 to 200	326.6			366.6			4	
		205 to 500	361.6	98.5	5	401.6	138.5			8
		505 to 800	396.6			436.6				

Roa	y Bottom	ıap	pec							[mm]
Size	Stroke range [mm]	МА	МС	MD	МН	ML	МО	MR	XA	ХВ
	15 to 35		24	32		50				
	40 to 100		42	41		50				
25	105 to 120	20	42	41	29		M5 x 0.8	6.5	4	5
	125 to 200		59	49.5		75				
	205 to 400		76	58						
	20 to 35		22	36		50				
	40 to 100	25	36 43	13		50				
32	105 to 120			43	30	80	M6 x 1	8.5	5	6
	125 to 200		53	51.5						
	205 to 500		70	60						
	50 to 70		24	50						
	75 to 120		45	60.5		65				
63	125 to 200	38	58	67	44		M8 x 1.25	10	6	7
	205 to 500		86	81	1	100				
	505 to 800		00	01		135				

IP65 equivalent (Dust-tight/Water-jet-proof): LEY63D□□-□P

\* LEY63 only

(View ZZ)




\*1 When using the dust-tight/water-jet-proof (IP65 equivalent), correctly mount the fitting and tubing to the vent hole tap, and then place the end of the tubing in an area not exposed to dust or water. The fitting and tubing should be provided separately by the customer. Select [Applicable tubing O.D.: Ø 4 or more, Connection thread: Rc1/8].





### **Dimensions**


### End male thread: LEY32 □□ B C □□ M



- Refer to page 97 for details on the rod end nut and mounting bracket.
- Refer to the precautions on page 187 when mounting end brackets such as knuckle joint or workpieces.

						[mm]
Size	B <sub>1</sub>	C <sub>1</sub>	H <sub>1</sub>	L <sub>1</sub> *1	L <sub>2</sub>	MM
25	22	20.5	8	38	23.5	M14 x 1.5
32	22	20.5	8	42.0	23.5	M14 x 1.5
63	27	26	11	76.4	39	M18 x 1.5

\*1 The L<sub>1</sub> measurement is when the unit is in the Z-phase first detecting position. At this position, 2 mm at the end (size 25, 32) and 4 mm at the end (size 63).



Material: Carbon steel (Chromate treated)

235.8

270.8

168.2

203.2

205 to 500

505 to 800

63

\* The A measurement is when the unit is in the Z-phase first detecting position. At this position, 2 mm at the end (size 25, 32) and 4 mm at the end (size 63).

50 | 3.2 | 95

88

110 | 14.2 | 8

29.2

8.6 5

25.2


\* When the motor mounting is the right or left side parallel type, the head side foot bracket should be mounted outward.




### Electric Actuator/Rod Type LEY Series AC Servo Motor Size 25, 32, 63

### **Dimensions**









available for the LEY32/LEY63.

Included parts ·Flange ·Body mounting bolt


### d/Hood Florage

HOU/F	ROG/Head Flange [mm]										
Size	FD	FT	FV	FX	FZ	LL	М				
25	5.5	8	48	56	65	6.5	34				
32	5.5	8	54	62	72	10.5	40				
63	9	9	80	92	108	28.4	60				

Material: Carbon steel (Nickel plating)

The LL measurement is when the unit is in the Z-phase first detecting position. At this position, 2 mm at the end (size 25, 32) and 4 mm at the end (size 63).

# Double clevis: LEY 32



\* Refer to page 97 for details on the rod end nut and mounting bracket.

> Included parts Double clevis · Body mounting bolt Clevis pin

Retaining ring

**Double Clevis** 

Double Clevis [mm]											
Size	Stroke range [mm]	Α	CL	CD	СТ	CU	cw	сх	CZ	L	RR
25	15 to 100	160.5	150.5	10	5	14	20	18	36	14.5	10
25	105 to 200	185.5	175.5	10	5	14	20	10	30	14.5	10
32	20 to 100	180.5	170.5	10	6	14	22	18	36	18.5	10
32	105 to 200	210.5	200.5	10	0	14	22	10	30	10.5	10
63	50 to 200	236.6	222.6	14	8						
	205 to 500	271.6	257.6	_	_	22	30	22	44	37.4	14
	505 to 800	306.6	292.6	_	_						

Material: Cast iron (Coating)

The A and CL measurements are when the unit is in the Z-phase first detecting position. At this position, 2 mm at the end (size 25, 32) and 4 mm at the end (size 63).

### **LEY** Series

### **Accessory Mounting Brackets**


### **Accessory Brackets/Support Brackets**

### Single Knuckle Joint

\* If a knuckle joint is used, select the body option [end male thread].

### I-G02

I-G04



[mm]

Part no.	Applicable size	Α	<b>A</b> 1	E <sub>1</sub>	Lı	ММ	Rı	U <sub>1</sub>	ND <sub>H10</sub>	NX
I-G02	16	34	8.5	□16	25	M8 x 1.25	10.3	11.5	8 +0.058	8 -0.2
I-G04	25, 32, 40	42	14	Ø 22	30	M14 x 1.5	12	14	10 +0.058	18 -0.3
I-G05	63	56	18	Ø 28	40	M18 x 1.5	16	20	14 +0.070	22 -0.3

### **Knuckle Pin**

Common with double clevis pin



Material: Carbon steel

Part no.	Applicable size	Dd9	Lı	L <sub>2</sub>	d	m	t	Retaining ring
IY-G02	16	8 -0.040	21	16.2	7.6	1.5	0.9	Type C retaining ring 8
IY-G04	25, 32, 40	10 -0.040	41.6	36.2	9.6	1.55	1.15	Type C retaining ring 10
IY-G05	63	14 -0.050	50.6	44.2	13.4	2.05	1.15	Type C retaining ring 14


### **Mounting Bracket Part Nos.**

Mounting	Order		Applica	ble size		Contents
bracket	qty.	16	25	32, 40	63	Contents
Foot	2*1	LEY-L016	LEY-L025	LEY-L032	LEY-L063	Foot bracket x 2 Mounting bolt x 4
Flange	1	LEY-F016	LEY-F025	LEY-F032	LEY-F063	Flange x 1 Mounting bolt x 4
Double clevis	1	LEY-D016	LEY-D025	LEY-D032	LEY-D063	Clevis x 1 Mounting bolt x 4 Clevis pin x 1 Type C retaining ring for axis x 2

<sup>\*1</sup> When ordering foot brackets, order 2 pieces per actuator.

### **Double Knuckle Joint**

Y-G02 Y-G04



Material: Carbon steel

Material: Cast iron

* Knuckle pin and retaining ring are included.										
Part no.	Applicable size	Α	<b>A</b> 1	E <sub>1</sub>	L <sub>1</sub>	ММ	R <sub>1</sub>			
Y-G02	16	34	8.5	□16	25	M8 x 1.25	10.3			
Y-G04	25, 32, 40	42	16	Ø 22	30	M14 x 1.5	12			
Y-G05	63	56	20	Ø 28	40	M18 x 1.5	16			

	Part no.	Applicable size	U <sub>1</sub>	ND <sub>H10</sub>	NX	NZ	L	Applicable pin part no.
	Y-G02	16	11.5	8 +0.058	8 +0.4 +0.2	16	21	IY-G02
Ī	Y-G04	25, 32, 40	14	10 +0.058	18 +0.5	36	41.6	IY-G04
	Y-G05	63	20	14 +0.070	22 +0.5	44	50.6	IY-G05

### **Rod End Nut**






Material: Carbon steel

					[111111]
Part no.	Applicable size	d	н	В	С
NT-02	16	M8 x 1.25	5	13	15.0
NT-04	25, 32, 40	M14 x 1.5	8	22	25.4
NT-05	63	M18 x 1.5	11	27	31.2

Ē

Simple Joint Brackets \* The joint is not included in type A and type B mounting brackets. Therefore, it must be ordered separately.

### Joint and Mounting Bracket (Type A/B)/Part No.



Allowable Ed	cent	ricity	[mm]
Applicable size	25	32	40
Eccentricity tolerance		±1	
Backlash		0.5	

Mounting bracket

YA Type A mounting bracket

YB Type B mounting bracket

<How to Order>

**03** 25, 32, 40

• The joint is not included in type A and type B mounting brackets. Therefore, it must be ordered separately


Type B mounting bracket

	0.00.00	oopa.a.o.j.	
Example)			Order no.
<ul> <li>Joint</li> </ul>			LEY-U025

Type A mounting bracket ..... YA-03


Joint and Mounting Bracket (Type A/B)/Part No.

Appliachle size	Joint	Applicable mounting	ng bracket part no.
Applicable size	part no.	Type A mounting bracket	Type B mounting bracket
25, 32, 40	LEY-U025	YA-03	YB-03



Part no.	Applicable size	UA	С	d <sub>1</sub>	d <sub>2</sub>	Н	K	L	UT	Weight [g]
LEY-U025	25, 32, 40	17	11	16	8	M8 x 1.25	14	7	6	22

### Type A Mounting Bracket




Material: Chromium molybdenum steel

Part no.	Applicable size	В	D	E	F	M	T <sub>1</sub>	<b>T</b> 2	U
YA-03	25, 32, 40	18	6.8	16	6	42	6.5	10	6

Part no.	Applicable size	٧	W	Weight [g]
YA-03	25, 32, 40	18	56	55

### **Type B Mounting Bracket**



Material: Stainless steel

F	Part no.	Applicable size	В	D	Е	J	M	ØO	
	YB-03	25, 32, 40	12	7	25	9	34	11.5 depth 7.5	
	·	Applicable						Maight	

Part no.	Applicable size	T <sub>1</sub>	<b>T</b> 2	٧	W	RS	Weight [g]
YB-03	25, 32, 40	6.5	10	18	50	9	80

### Floating Joints (Refer to the Web Catalogue for details.)

●For Male Thread/JC (Light weight type)

• With the aluminium case



### ●For Male Thread/JS (Stainless steel)

 Stainless steel 304 (Appearance)

 Dust cover Fluororubber/Silicone rubber



	Applicable size	Thread size
,	16	M8 x 1.25
	25, 32, 40	M14 x 1.5
	63	M18 x 1.5



### For Male Thread/JA



For Female Thread/JB




Applicable size	Thread size
16	M5 x 0.8
25, 32, 40	M8 x 1.25
63	M16 x 2

### **LEY** Series

### **Auto Switch Mounting**

### **Proper Auto Switch Mounting Position**


Applicable auto switches: D-M9 $\square$ (V), D-M9 $\square$ E(V), D-M9 $\square$ W(V), D-M9 $\square$ A(V)



[mm] Auto switch position Return to origin Operating range Size Stroke range distance Mounting: Left facing Mounting: Right facing C 10 to 100 21.5 33.5 16 46.5 34.5 (2) 2.9 105 to 300 41.5 53.5 27 15 to 100 39 25 62.5 50.5 (2) 4.2 105 to 400 52 64 42.5 20 to 100 30.5 32/40 65.5 53.5 (2)4.9 105 to 500 60.5 72.5 50 to 200 37 49 63 205 to 500 72 86 84 74 (4) 9.8 505 to 800 107 119

- \*1 Figures in the table above are used as a reference when mounting the auto switches for stroke end detection. Adjust the auto switch after confirming the operating condition in the actual setting.
- \*2 Switches cannot be mounted on the motor mounting side surface.
- \*3 For the LEYG with a guide, switches cannot be mounted on the guide attachment side (rod side).
- \*4 Since the operating range is provided as a guideline including hysteresis, it cannot be guaranteed (assuming approximately ±30% dispersion). It may change substantially depending on the ambient environment.

### **Auto Switch Mounting**



### Auto Switch Mounting Screw

<b>Tightening Torque</b>	[N·m]
Auto switch model	Tightening torque
D-M9□(V) D-M9□E(V) D-M9□W(V)	0.05 to 0.15
D-M9□A(V)	0.05 to 0.10

\* When tightening the auto switch mounting screw (included with auto switch), use a watchmaker's screwdriver with a handle diameter of about 5 to 6 mm.





### **Solid State Auto Switch Direct Mounting Type**

D-M9N(V)/D-M9P(V)/D-M9B(V) **(** € RoHS



### Grommet

- 2-wire load current is reduced (2.5 to 40 mA).
- Using flexible cable as standard



### **⚠Caution**

### **Precautions**

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

### Auto Switch Specifications

Refer to the SMC website for details on products that are compliant with international standards.

PLC: Programmable Logic Controller

D-M9□, D-M9□V (With indicator light)									
Auto switch model	D-M9N	D-M9NV	D-M9P D-M9PV		D-M9B	D-M9BV			
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular			
Wiring type		3-wire				vire			
Output type	NF	NPN PNP				_			
Applicable load	IC circuit, Relay, PLC				24 VDC relay, PLC				
Power supply voltage	5	5, 12, 24 VDC (4.5 to 28 V)				_			
Current consumption		10 mA	or less		_				
Load voltage	28 VDC	or less	_	_	24 VDC (10 to 28 VDC)				
Load current		40 mA	or less		2.5 to 40 mA				
Internal voltage drop	0.8 V or l	ess at 10 mA	(2 V or less	at 40 mA)	4 V o	r less			
Leakage current		100 μA or less at 24 VDC			0.8 mA	or less			
Indicator light		Red L	ED illuminate	es when turne	ed ON.				
Standard			CE marki	ng, RoHS					

**Oilproof Heavy-duty Lead Wire Specifications** 

Auto switch model		D-M9N(V)	D-M9N(V) D-M9P(V)				
Sheath	Outside diameter [mm]	2.6					
Insulator	Number of cores	3 cores (Brow	n/Blue/Black)	2 cores (Brown/Blue)			
irisulator	Outside diameter [mm]						
Conductor	Effective area [mm²]		0.15				
Conductor	Strand diameter [mm]	0.05					
Minimum bending radius	s [mm] (Reference values)		17				


- \* Refer to the **Web Catalogue** for solid state auto switch common specifications.
- Refer to the Web Catalogue for lead wire lengths.


### Weight

[g]

Auto switch model		D-M9N(V)	D-M9P(V)	D-M9B(V)		
	0.5 m ( <del></del> )	8		7		
Lead wire length	1 m ( <b>M</b> )	14		13		
	3 m ( <b>L</b> )	41		41		38
	5 m ( <b>Z</b> )	68		63		

**Dimensions** [mm]





## Normally Closed Solid State Auto Switch Direct Mounting Type

### Grommet

- Output signal turns on when no magnetic force is detected.
- Can be used for the actuator adopted by the solid state auto switch D-M9 series (excluding special order products)



### **.**⚠Caution

### **Precautions**

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

### Auto Switch Specifications

Refer to the SMC website for details on products that are compliant with international standards.

PLC: Programmable Logic Controller

D-M9□E, D-M9□EV (With indicator light)							
Auto switch model	D-M9NE	D-M9NEV	D-M9PE	D-M9PEV	D-M9BE	D-M9BEV	
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular	
Wiring type	3-wire			2-wire			
Output type	NPN PNP		Ī	_			
Applicable load	IC circuit, Relay, PLC			24 VDC relay, PLC			
Power supply voltage	5, 12, 24 VDC (4.5 to 28 V)			_			
Current consumption	10 mA or less			_			
Load voltage	28 VDC or less —			24 VDC (10 to 28 VDC)			
Load current	40 mA or less			2.5 to	40 mA		
Internal voltage drop	0.8 V or less at 10 mA (2 V or less at 40 mA)			4 V or less			
Leakage current	100 μA or less at 24 VDC			0.8 mA	or less		
Indicator light	Red LED illuminates when turned ON.						
Standard	CE marking, RoHS						

Oilproof Heavy-duty Lead Wire Specifications

Auto sw	Auto switch model		D-M9PE(V)	D-M9BE(V)
Sheath	Outside diameter [mm]	2.6		
Insulator	Number of cores		n/Blue/Black)	2 cores (Brown/Blue)
Ilisulatoi	Outside diameter [mm]	0.88		
Conductor	Effective area [mm²]	0.15		
Conductor	Strand diameter [mm]	0.05		
Minimum bending radius [mm] (Reference values)		17		

- Refer to the Web Catalogue for solid state auto switch common specifications.
- Refer to the Web Catalogue for lead wire lengths.


### Weight


Auto switch model		D-M9NE(V)	D-M9PE(V)	D-M9BE(V)
0.5 m ( <del></del> )		8		7
Lead wire length	1 m ( <b>M</b> )*1	14		13
	3 m ( <b>L</b> )	41		38
	5 m ( <b>Z</b> )*1	68		63

<sup>\*1</sup> The 1 m and 5 m options are produced upon receipt of order.

### **Dimensions**

[mm] D-M9□E D-M9□EV





# 2-Colour Indicator Solid State Auto Switch Direct Mounting Type D\_MON(W/V)/D\_MOD(W/V)/D\_MOD(W/V)/ C C COLORS

D-M9NW(V)/D-M9PW(V)/D-M9BW(V)  $\subset \in$ 



[g]

### Grommet

- 2-wire load current is reduced (2.5 to 40 mA).
- Using flexible cable as standard spec.
- The proper operating range can be determined by the colour of the light. (Red → Green ← Red)



### **△**Caution

#### **Precautions**

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

### **Auto Switch Specifications**

Refer to the SMC website for details on products that are compliant with international standards.

PLC: Programmable Logic Controller

D-M9□W, D-M9□WV (With indicator light)							
Auto switch model	D-M9NW	D-M9NWV	D-M9PW	D-M9PWV	D-M9BW	D-M9BWV	
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular	
Wiring type	3-wire 2-		2-v	vire			
Output type	NPN		PI	NP	_		
Applicable load	IC circuit, Relay, PLC 24 VDC relay,		elay, PLC				
Power supply voltage	5, 12, 24 VDC (4.5 to 28 V) —			_			
Current consumption	10 mA or less —		_				
Load voltage	28 VDC	28 VDC or less — 24 VDC (10 to 2		to 28 VDC)			
Load current	40 mA or less		2.5 to 40 mA				
Internal voltage drop	0.8 V or less at 10 mA (2 V or less at 40 mA)			4 V or less			
Leakage current	100 μA or less at 24 VDC 0.8 mA or less			or less			
Indicator light	Operating range Red LED illuminates. Proper operating range Green LED illuminates.			S.			
Standard	CE marking, RoHS						

Oilproof Flexible Heavy-duty Lead Wire Specifications

Auto switch model		D-M9NW(V)	D-M9PW(V)	D-M9BW(V)
Sheath	Outside diameter [mm]	2.6		
Insulator	Number of cores	3 cores (Brow	3 cores (Brown/Blue/Black)	
insulator	Outside diameter [mm]	0.88		
Effective area [mm²]		0.15		
Conductor	Strand diameter [mm]	0.05		
Minimum bending radius [mm] (Reference values)		17		

- \* Refer to the Web Catalogue for solid state auto switch common specifications.
- \* Refer to the Web Catalogue for lead wire lengths.

Weight

Auto switch model		D-M9NW(V) D-M9PW(V)		D-M9BW(V)		
0.5 m ( <del></del> )		8		7		
Lead wire length	1 m ( <b>M</b> )	14		13		
	3 m ( <b>L</b> )	41		41		38
	5 m ( <b>7</b> )	6	63			

D-M9 W

D-M9 W

D-M9 W

Mounting screw M2.5 x 4 L

Slotted set screw (flat point)

Indicator light

22.8

**多SMC** 



Step Motor/Servo Motor Controller/Driver p. 190 AC Servo Motor Driver p. 246

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

LEY

25A-LEY LEY-X5

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

LECPA LECP1 LEC-G LECA6

JXC

LECY□ | LECS□ AC Servo Motor


Electric Actuator/Guide Rod Type **LEYG** Series

### **Model Selection**

LEYG Series ▶p. 121





### **Selection conditions**




<sup>\*1</sup> For the sliding bearing type, the speed is restricted with a horizontal/moment load.

### **Vertical Mounting, Sliding Bearing**








### **Vertical Mounting, Ball Bushing Bearing**

# 3 35 mm stroke or less 100 LEYG16L LEYG25L 100 LEYG25L 100 Eccentric distance L [mm]


\* The limit of vertical load mass varies depending on "lead" and "speed." Check "Speed-Work Load Graph" on pages 107 to 109.




1000

### **Moment Load Graph**

### Horizontal Mounting, Sliding Bearing






Set the speed to less than or equal to the values shown below.


Motor type	LEYG□M□A	LEYG□M□B	LEYG□M□C
Step motor (Servo/24 VDC)	200 mm/s	125 mm/s	75 mm/s
Servo motor (24 VDC)	200 mm/s	200 mm/s	125 mm/s

- For the specifications below, operate the system at the "load mass" shown in the graph x 80 %
  - LEYG25MAA/Servo motor (24 VDC), Lead 12

### Horizontal Mounting, Ball Bushing Bearing

#### $\bigcirc$ L = 50 mm Max. speed = 200 mm/s or less






120 125


100

8 L = 100 mm Max. speed = 200 mm/s or less




35 40





### Operating Range when Used as a Stopper


### LEYG M (Sliding bearing)




### **∆** Caution

#### **Handling Precautions**

- When used as a stopper, select a model with a stroke of 30 mm or less.
- LEYG L (ball bushing bearing) cannot be used as a stopper.
- Workpiece collision in series with guide rod cannot be permitted (Fig. a).
- The body should not be mounted on the end. It must be mounted on the top or bottom (Fig. b).





### **LEYG** Series

Step Motor (Servo/24 VDC) Servo Motor (24 VDC)


Speed-Work Load Graph (Guide)

These graphs show the work load when the external guide is used together. When using the LEYG alone, refer to pages 105 and 106.

Refer to page 108 for the LECPA JXC□<sup>2</sup> and page 109 for the LECA6.


### For Step Motor (Servo/24 VDC) LECP1, LECPMJ, JXC□1






### LEYG25<sup>M</sup>□






### LEYG32<sup>™</sup>□

### for acceleration/deceleration: 2000 mm/s<sup>2</sup>




### LEYG40<sup>™</sup>□

### for acceleration/deceleration: 2000 mm/s<sup>2</sup>




### Vertical


### LEYG16<sup>™</sup>□




### LEYG25<sup>M</sup>□



### LEYG32<sup>M</sup>□



### LEYG40<sup>™</sup>□



Щ

\* These graphs show the work load when the external guide is used together. When using the LEYG alone, refer to pages 105 and 106.

1.5

0

0

Refer to page 107 for the LECP6, JXC□1 and page 109 for the LECA6.


Lead 10: LEYG16<sup>M</sup>A


500


600


Model Selection **LEYG Series** Step Motor (Servo/24 VDC) Servo Motor (24 VDC)


#### Speed-Work Load Graph (Guide) For Step Motor (Servo/24 VDC) LECPA, JXC $\square_3^2$



















Speed [mm/s]








Step Motor (Servo/24 VDC) Servo Motor (24 VDC)

#### Speed-Work Load Graph (Guide) For Servo Motor (24 VDC) LECA6


Refer to page 107 for the LECP1, JXC $\square$ 1 and page 108 for the LECPA, JXC $\square$ 3.

#### Horizontal






#### LEYG25<sup>M</sup>□A




#### Vertical

#### LEYG16<sup>M</sup>□A



#### LEYG25<sup>M</sup>□A




#### Model Selection **LEYG Series** Step Motor (Servo/24 VDC) Servo Motor (24 VDC)

#### Force Conversion Graph (Guide)


#### Step Motor (Servo/24 VDC)

#### LEYG16<sup>M</sup>□




Ambient temperature	Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]
25 °C or less	85 or less	100	_
	40 or less	100	_
40 °C	50	70	12
40 C	70	20	1.3
	85	15	0.8

#### LEYG25<sup>M</sup>□




Ambient temperatur	Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]
40 °C or les	65 or less	100	_

#### LEYG32<sup>M</sup>□



Ambient temperature	Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]
25 °C or less	85 or less	100	_
40 °C	65 or less	100	_
40 C	85	50	15

#### LEYG40<sup>M</sup>□




65 or less

#### \*1 Set values for the controller

#### Servo Motor (24 VDC)


#### LEYG16<sup>M</sup>A□



1.6	=V	325	M	ΑΓ	
	= 1 1	523		$\boldsymbol{A}$	

95 or less

40 °C or less



Ambient temperature	Set value of pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]
40 °C or less	95 or less	100	_

#### <Limit Values for Pushing Force and Trigger Level in **Relation to Pushing Speed>**

WILLIOU	IL LO	au						
Model	Lead	Pushing speed [mm/s]	Pushing force (Setting input value)		Model	Lead	Pushing speed [mm/s]	Pushing force (Setting input value)
LEYG16 <sup>M</sup>	A/B/C	21 to 50	60 to 85 %		LEYG16 <sup>M</sup> □A	A/B/C	21 to 50	80 to 95 %
LEYG25 <sup>M</sup>	A/B/C	21 to 35	50 to 65 %		LEYG25 <sup>M</sup> □A	A/B/C	21 to 35	80 to 95 %
LEYG32 <sup>M</sup>	Α	24 to 30	CO += OF 0/					
LETUSZL	B/C	21 to 30	60 to 85 %					
LEYG40 <sup>M</sup>	Α	24 to 30	E0 to 65 %					
LETG40L	B/C	B/C 21 to 30 50 to 65 9						

There is a limit to the pushing force in relation to the pushing speed. If the product is operated outside of the range (low pushing force), the completion signal [INP] may be output before the pushing operation has been completed (during the moving operation).

If operating with the pushing speed below the min. speed, please check for operating problems before using the product.

#### <Set Values for Vertical Upward Transfer Pushing Operations>

For vertical loads (upward), set the pushing force to the max. value shown below and operate at the work load or less.

Model	LE	/G16	S <u>M</u> □	LE	/G25	M□	LE	/G32	200□	LE	/G40	) <sup>M</sup> [	LEY	G16	¹□A	LEY	G25 <sup>N</sup>	¹□A
Lead	Α	В	С	Α	В	С	Α	В	С	Α	В	С	Α	В	С	Α	В	С
Work load [kg]	0.5	1	2.5	1.5	4	9	2.5	7	16	5	12	26	0.5	1	2.5	0.5	1.5	4
Pushing force	8	35 %	6	6	65 %	, o	8	35 %	0	6	65 %	6	9	95 %	, o	9	95 %	, o

# **Model Selection**

LEYG Series ▶ p. 135 | LECY□ Series ▶ p. 143




#### **Moment Load Graph**

#### **Selection conditions**


		Vertical	Horiz	ontal
Mounting position			·m	·m
Max. speed [mm/s]		"Speed-Vertical Work Load Graph"	200 or less	Over 200
Bearing Sliding bearing  Ball bushing bearing		Graphs ①, ②	Graphs 5, 6*1	Graphs 7, 8
		Graphs ③, ④	Graphs 9, 10	Graphs (1), (12)

<sup>\*1</sup> For the sliding bearing type, the speed is restricted with a horizontal/moment load.

#### **Vertical Mounting, Sliding Bearing**








#### **Vertical Mounting, Ball Bushing Bearing**

# 3 35 mm stroke or less LEYG32L LEYG25L O.1 10 LEYG25L O.1 10 Eccentric distance L [mm]






Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

Model Selection **LEYG Series** AC Servo Motor


#### **Moment Load Graph**

#### Horizontal Mounting, Sliding Bearing


#### 5 L = 50 mm Max. speed = 200 mm/s or less




6 L = 100 mm Max. speed = 200 mm/s or less



7 L = 50 mm Max. speed = Over 200 mm/s




8 L = 100 mm Max. speed = Over 200 mm/s




#### **Horizontal Mounting, Ball Bushing Bearing**


#### 9 L = 50 mm Max. speed = 200 mm/s or less








#### 1) L = 50 mm Max. speed = Over 200 mm/s




12 L = 100 mm Max. speed = Over 200 mm/s



#### Operating Range when Used as a Stopper


#### LEYG M (Sliding bearing)




#### **∆** Caution

#### **Handling Precautions**

- When used as a stopper, select a model with a stroke of 30 mm or less.
- LEYG□L (ball bushing bearing) cannot be used as a stopper.
- Workpiece collision in series with guide rod cannot be permitted (Fig. a).
- The body should not be mounted on the end. It must be mounted on the top or bottom (Fig. b).








#### Speed-Vertical Work Load Graph/Required Conditions for "Regeneration Option"

\* These graphs show the work load when the external guide is used together. When using the LEYG alone, refer to pages 111 and 112.

#### **LEYG25** S<sub>6</sub><sup>2</sup>/T6 (Motor mounting position: Top mounting/In-line)




#### Required conditions for "Regeneration option"

 Regeneration option is required when using product above regeneration line in graph. (Order separately.)


#### "Regeneration Option" Models

Size	Model			
LEYG25□	LEC-MR-RB-032			
LEYG32□	LEC-MR-RB-032			

#### LEYG32S<sub>7</sub>/T7 (Motor mounting position: Top mounting)




#### LEYG32DS<sub>7</sub><sup>3</sup>/T7 (Motor mounting position: In-line)



#### Speed-Horizontal Work Load Graph/Required Conditions for "Regeneration Option"

#### **LEYG25** S<sub>6</sub>/T6 (Motor mounting position: Top mounting/In-line)




#### Required conditions for "Regeneration option"

 Regeneration option is required when using product above regeneration line in graph. (Order separately.)


#### "Regeneration Option" Models

Size	Model		
LEYG25□	LEC-MR-RB-032		
LEYG32□	LEC-MR-RB-032		

#### LEYG32S<sub>7</sub><sup>3</sup>/T7 (Motor mounting position: Top mounting)



#### LEYG32DS<sup>3</sup>/T7 (Motor mounting position: In-line)




<sup>\*</sup> These graphs show the work load when the external guide is used together. When using the LEYG alone, refer to pages 111 and 112.

LEY


#### Force Conversion Graph: LECSA, LECSB, LECSC, LECSS

#### **LEYG25** S<sub>6</sub> (Motor mounting position: Top mounting/In-line)



Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
25 or less	100	_
30	60	1.5


#### LEYG32S<sup>3</sup><sub>7</sub> (Motor mounting position: Top mounting)



Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
25 or less	100	_
30	60	1.5

#### LEYG32DS<sup>3</sup><sub>7</sub> (Motor mounting position: In-line)


Model Selection **LEYG Series** 



[	Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
	25 or less	100	_
	30	60	1.5


#### Force Conversion Graph: LECSS-T

#### **LEYG25**□**T6** (Motor mounting position: Top mounting/In-line)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
20 or less	100	_
24	60	1.5

#### LEYG32T7 (Motor mounting position: Top mounting)



#### Torque limit/Command value [%] Duty ratio [%] Continuous pushing time [minute] 20 or less


#### LEYG32DT7 (Motor mounting position: In-line)



Torque limit/Command value [%] Duty ratio [%]		Continuous pushing time [minute]
20 or less	100	_
24	60	1.5




#### **Allowable Rotational Torque of Plate**




					<b>T</b> [N⋅m]	
Model		Stroke [mm]				
Model	30	50	100	200	300	
LEYG16M	0.70	0.57	1.05	0.56	_	
LEYG16L	0.82	1.48	0.97	0.57	_	
LEYG25M	1.56	1.29	3.50	2.18	1.36	
LEYG25L	1.52	3.57	2.47	2.05	1.44	
LEYG32M	2.55	2.09	5.39	3.26	1.88	
LEYG32L	2.80	5.76	4.05	3.23	2.32	
LEYG40M	2.55	2.09	5.39	3.26	1.88	
LEYG40L	2.80	5.76	4.05	3.23	2.32	

#### **Non-rotating Accuracy of Plate**



Size	Non-rotating accuracy θ			
Size	LEYG□M	LEYG□L		
16 25 32 40	0.06°	0.05°		
	0.05°	0.04°		
	0.05°			

#### Plate Displacement: $\boldsymbol{\delta}$



					[mm]	
Model		Stroke [mm]				
iviodei	30	50	100	200	300	
LEYG16M	±0.20	±0.25	±0.24	±0.27	_	
LEYG16L	±0.13	±0.12	±0.17	±0.19	_	
LEYG25M	±0.26	±0.31	±0.25	±0.38	±0.36	
LEYG25L	±0.13	±0.13	±0.17	±0.20	±0.23	
LEYG32M	±0.23	±0.29	±0.23	±0.36	±0.34	
I FVG32I	+0.11	+0.11	+0.15	+0.10	+0.22	

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

Environment

LECA6 Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEC-G

LECP1 LECPA

LECS

AC Servo Motor LECY

AC Servo Motor LECY□ Series **Electric Actuator/Guide Rod Type** 


## **Model Selection**

LEYG Series ▶p. 143 LECS□ Series ▶p. 135

**LEYG** Series


#### **Moment Load Graph**


#### Selection conditions



<sup>\*1</sup> For the sliding bearing type, the speed is restricted with a horizontal/moment load.


#### **Vertical Mounting, Sliding Bearing**







#### 2 Over 75 mm stroke 100 LEYG32M□ Load mass m [kg] 10 0.1 1000 100 Eccentric distance L [mm]

#### Vertical Mounting, Ball Bushing Bearing











#### **Moment Load Graph**

#### **Horizontal Mounting, Sliding Bearing**


#### 5 L = 50 mm Max. speed = 200 mm/s or less




#### 7 L = 50 mm Max. speed = Over 200 mm/s



#### 6 L = 100 mm Max. speed = 200 mm/s or less




#### 8 L = 100 mm Max. speed = Over 200 mm/s




#### Horizontal Mounting, Ball Bushing Bearing


#### 9 L = 50 mm Max. speed = 200 mm/s or less




#### 1) L = 50 mm Max. speed = Over 200 mm/s



10 L = 100 mm Max. speed = 200 mm/s or less




#### 12 L = 100 mm Max. speed = Over 200 mm/s



#### Operating Range when Used as a Stopper


#### LEYG M (Sliding bearing)




#### **⚠** Caution

#### **Handling Precautions**

- \* When used as a stopper, select a model with a stroke of 30 mm or less.
- \* LEYG L (ball bushing bearing) cannot be used as a stopper.
- \* Workpiece collision in series with guide rod cannot be permitted (**Fig. a**).
- The body should not be mounted on the end. It must be mounted on the top or bottom (Fig. b).





# Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

AC Servo Motor LEYG

LEY

LEY-X5 Environment 25A-LEY

> LECA6 LEC-G

> LECP1 LECPA

LECS


LECY


Model Selection **LEYG Series** 

\* These graphs show the work load when the external guide is used together. When using the LEYG alone, refer to pages 116 and 117.


#### Speed–Work Load Graph/Conditions for "Regenerative Resistor" (Guide)


LEYG25□V6 (Motor mounting position: Top mounting/In-line)







#### **LEYG32V7 (Motor mounting position: Top mounting)**





#### **LEYG32DV7** (Motor mounting position: In-line)





#### "Regenerative resistor" area

- \* When using the actuator in the "Regenerative resistor" area, download the "AC servo drive capacity selection program/SigmaJunmaSize+" from the SMC website. Then, calculate the necessary regenerative resistor capacity to prepare an appropriate external regenerative resistor.
- \* Regenerative resistor should be provided by the customer.

Applicable	Motor/	Driver
------------	--------	--------


Model	Applicable model		
Model	Motor	Servopack (SMC driver)	
LEYG25□	SGMJV-01A3A	SGDV-R90A11□ (LECYM2-V5) SGDV-R90A21□ (LECYU2-V5)	
LEYG32□	SGMJV-02A3A	SGDV-1R6A11□ (LECYM2-V7) SGDV-1R6A21□ (LECYU2-V7)	






#### **Force Conversion Graph**

#### LEYG25 ☐ V6 (Motor mounting position: Top mounting/In-line)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
75 or less 100		_
90	60	1.5

#### **LEYG32**□**V7** (Motor mounting position: Top mounting)



Torque limit/Command value [%]	orque limit/Command value [%] Duty ratio [%]	
75 or less	100	_
90	60	1.5

#### **LEYG32DV7** (Motor mounting position: In-line)




Torque limit/Command value [%]	Duty ratio [%]	Continuous pushing time [minute]
75 or less	100	_
90	60	1.5

AC Servo Motor

LEY

AC Servo Motor

#### **Allowable Rotational Torque of Plate: T**




					ı [ıv·ııı]
Model	Stroke [mm]				
Model	30	50	100	200	300
LEYG25M	1.56	1.29	3.50	2.18	1.36
LEYG25L	1.52	3.57	2.47	2.05	1.44
LEYG32M	2.55	2.09	5.39	3.26	1.88
LEYG32L	2.80	5.76	4.05	3.23	2.32

Model Selection **LEYG** Series


AC Servo Motor

#### Non-rotating Accuracy of Plate: $\theta$



Size	LEYG□M	LEYG□L
25	±0.06°	10.040
32	±0.05°	±0.04°

#### Plate Displacement: $\boldsymbol{\delta}$



					[mm]		
Model	Stroke [mm]						
Model	30	50	100	200	300		
LEYG25M	±0.26	±0.31	±0.25	±0.38	±0.36		
LEYG25L	±0.13	±0.13	±0.17	±0.20	±0.23		
LEYG32M	±0.23	±0.29	±0.23	±0.36	±0.34		
LFYG32I	+0.11	+0.11	+0.15	+0.19	+0.22		


# **Electric Actuator/ Guide Rod Type**


**LEYG** Series LEYG16, 25, 32, 40














#### 1 Size 16 25

32 40

<b>❷</b> Bearing type <sup>∗1</sup>					
M	Sliding bearing				
L	Ball bushing bearing				

#### Motor mounting position

	<u> </u>
_	Top mounting
D	In-line

#### 4 Motor type

• meter type							
Cumbal	Type	A	pplicable siz	Compatible controller/			
Symbol	Type	LEYG16	LEYG25	LEYG32/40	dr	iver	
ı	Step motor (Servo/24 VDC)	•	•	•	LECP1 LECPA	JXCE1 JXC91 JXCP1 JXCD1 JXCL1	
Α	Servo motor (24 VDC)	•	•	_	LE	CA6	

#### **5** Lead [mm]

Symbol	LEYG16	LEYG25	LEYG32/40	
Α	10	12	16	
В	5	6	8	
С	2.5	3	4	

#### 6 Stroke\*2 \*3 [mm]

	<u> </u>
30	30
to	to
300	300

For details, refer to the applicable stroke table below.

#### Motor option\*4

_	<ul><li>Without option</li><li>With motor cover</li></ul>						
С							
В	With lock						
W With lock/motor cove							

#### 8 Guide option\*5

_	Without option					
F	With grease retaining function					

#### 9 Actuator cable type/length\*7

Standard cable [m]				
_	None			
S1	1.5*9			
S3	3*9			
S5	5*9			

	_							
Robotic cable [m]								
R1	1.5	RA	10*6					
R3	3	RB	15* <sup>6</sup>					
R5	5	RC	20*6					
R8	8*6							

#### Applicable Stroke Table\*2

Applicable Stroke Table - Standa								: Standard
Stroke [mm] Model		50	100	150	200	250	300	Manufacturable stroke range [mm]
LEYG16	•	•	•	•	•	_	_	10 to 200
LEYG25	•	•	•	•	•	•	•	15 to 300
LEYG32/40	•	•	•		•	•	•	20 to 300

For auto switches, refer to pages 101 to 103.


#### Use of auto switches for the guide rod type LEYG series

- · Auto switches must be inserted from the front side with the rod (plate) sticking out.
- · Auto switches cannot be fixed with the parts hidden behind the guide attachment (the side of the rod that sticks out).
- Please consult with SMC when using auto switches on the side of the rod that sticks out, as it is produced as a special order.



Electric Actuator/Guide Rod Type LEYG Series Step Motor (Servo/24 VDC) Servo Motor (24 VDC)

#### Series (For details, refer to page 123.)



#### Controller/Driver type\*8

_	Without controller/drive	er
6N	LECA6	NPN
6P	(Step data input type)	PNP
1N	LECP1*9	NPN
1P	(Programless type)	PNP
AN	LECPA*9 *11	NPN
AP	(Pulse input type)	PNP

#### I/O cable length\*12, Communication plug

_	Without cable (Without communication plug connector)
1	1.5 m
3	3 m* <sup>13</sup>
5	5 m* <sup>13</sup>
S	Straight type communication plug connector
T	T-branch type communication plug connector



#### Controller/Driver mounting

	Screw mounting
D	DIN rail* <sup>14</sup>

#### JXC Series (For details, refer to page 123.




Р

D

**PROFINET** 

DeviceNet™

IO-Link



 Communication plug connector for DeviceNet™\*15

_	Without plug connector
S	Straight type
Т	T-branch type

\*1 When [M: Sliding bearing] is selected, the maximum speed of lead [A] is 400 mm/s (at no-load, horizontal mounting). The speed is also restricted with a horizontal/moment load. Refer to "Model Selection" on page 105.

For single axis

- \*2 Please consult with SMC for non-standard strokes as they are
- produced as special orders.
  There is a limit for mounting the size 32/40 top mounting types and strokes of 50 mm or less. Refer to the dimensions.
- \*4 When "With lock" or "With lock/motor cover" is selected for the top mounting type, the motor body will stick out from the end of the body for size 16/40 with strokes of 30 mm or less. Check for interference with workpieces before selecting a model.
- \*5 Only available for size 25, 32, and 40 sliding bearings (Refer to "Construction" on page 128.)
- \*6 Produced upon receipt of order (Robotic cable only)
- The standard cable should only be used on fixed parts. For use on moving parts, select the robotic cable.

- \*8 For details on controllers/drivers and compatible motors, refer to the
- compatible controller/driver on the next page.

  \*9 Only available for the motor type "Step motor"
- Not compliant with CE
- \*11 When pulse signals are open collector, order the current limiting resistor (LEC-PA-R-□) on page 220 separately.

  \*12 When "Without controller/driver" is selected for controller/driver types,
- I/O cable cannot be selected. Refer to page 199 (For LECA6), page 213 (For LECP1), or page 220 (For LECPA) if I/O cable is required.
- \*13 When "Pulse input type" is selected for controller/driver types, pulse input usable only with differential. Only 1.5 m cables usable with open collector
- \*14 The DIN rail is not included. Order it separately. \*15 Select "—" for anything other than DeviceNet™

#### **⚠** Caution

#### [CE-compliant products]

- 1) EMC compliance was tested by combining the electric actuator LEY series and the controller LEC/JXC series.
  - The EMC depends on the configuration of the customer's control panel and the relationship with other electrical equipment and wiring. Therefore, compliance with the EMC directive cannot be certified for SMC components incorporated into the customer's equipment under actual operating conditions. As a result, it is necessary for the customer to verify compliance with the EMC directive for the machinery and equipment as a whole.
- 2 For the servo motor (24 VDC) specification, EMC compliance was tested by installing a noise filter set (LEC-NFA). Refer to page 199 for the noise filter set. Refer to the LECA series Operation Manual for installation.

#### [UL-compliant products (For the LEC series)]


When compliance with UL is required, the electric actuator and controller/ driver should be used with a UL1310 Class 2 power supply.

#### The actuator and controller/driver are sold as a package.

Confirm that the combination of the controller/driver and actuator is correct.

#### <Check the following before use.>

- 1 Check the actuator label for the model number. This number should match that of the controller/driver.
- 2 Check that the Parallel I/O configuration matches (NPN or PNP).



Refer to the Operation Manual for using the products. Please download it via our website, https://www.smc.eu



#### **Compatible Controller/Driver**

#### **LEC**□ Series

Туре	Step data input type	Programless type	Pulse input type			
Series	LECA6	LECP1	LECPA			
Features	Value (Step data) input Standard controller	Capable of setting up operation (step data) without using a PC or teaching box	Operation by pulse signals			
Compatible motor	Servo motor (24 VDC)		motor 24 VDC)			
Max. number of step data	64 points	14 points	_			
Power supply voltage						
Reference page	191	207 214				

#### JXC□ Series

Туре	EtherCAT® direct input type	EtherNet/IP™ direct input type	PROFINET direct input type	DeviceNet <sup>TM</sup> direct input type	IO-Link direct input type
Series	JXCE1	JXC91	JXCP1	JXCD1	JXCL1
Features	EtherCAT® direct input	EtherNet/IP™ direct input	PROFINET direct input	DeviceNet™ direct input	IO-Link direct input
Compatible motor	anost mput	an ook input	Step motor (Servo/24 VDC)	anost input	an ook mput
Max. number of step data			64 points		
Power supply voltage			24 VDC		
Reference page			224		

**SMC** 



#### **Specifications**

#### Step Motor (Servo/24 VDC)

		Mode	I		LEYG16 <sup>M</sup> LEYG25 <sup>M</sup> LEYG32 <sup>M</sup> LE										M L							
		Horizontal	Acceleration/Deceleration at 3000 [mm/s <sup>2</sup> ]	6	17	30	20	40	60	30	45	60	50	60	80							
			Acceleration/Deceleration at 2000 [mm/s <sup>2</sup> ]	10	23	35	30	55	70	40	60	80	60	70	90							
	Work load [kg ]*1	Horizontal	Acceleration/Deceleration at 3000 [mm/s <sup>2</sup> ]	4	11	20	12	30	30	20	40	40	30	60	60							
ons			Acceleration/Deceleration at 2000 [mm/s <sup>2</sup> ]	6	17	30	18	50	50	30	60	60	_	_	_							
specifications		Vertical	Acceleration/Deceleration at 3000 [mm/s <sup>2</sup> ]	1.5	3.5	7.5	7	15	29	9	20	41	11	25	51							
be	Pushing '	force	[N]*2 *3 *4	14 to 38	27 to 74	51 to 141	63 to 122	126 to 238	232 to 452	80 to 189	156 to 370	296 to 707	132 to 283	266 to 553	562 to 1058							
Actuator s	Speed [mm/s]*4		CP1/JXC□1	15 to 500	8 to 250	4 to 125	18 to 500	9 to 250	5 to 125	24 to 500				12 to 350								
Actı		LE	CPA/JXC□3								12 to 250	6 to 125	24 to 300	12 to 150	6 to 75							
1			celeration [mm/s <sup>2</sup> ]							00												
	Pushing speed [mm/s]*5			,	50 or less	;	;	35 or less			30 or less	5		30 or less	5							
			eatability [mm]	±0.02																		
	Lost mot			0.1 or less																		
	Screw lea			10										4								
			sistance [m/s <sup>2</sup> ]*7	50/20																		
	Actuation			Ball screw + Belt (LEYG□□), Ball screw (LEYG□□D)																		
	Guide typ		[00]	Sliding bearing (LEYG□M), Ball bushing bearing (LEYG□L)  5 to 40																		
			p. range [°C]					00			-4:\											
0	Motor siz		ty range [%RH]		□28			90 or 42	less (No	condensa	alion) □56.4			□56.4								
ion	Motor typ				□20				motor (S	  anyo/24 \				□30.4								
icat	Encoder	,,,					Inc		A/B phas			on)										
Electric specifications	Rated vo	Itage I	TV1				1110	Terrieritai	24 VDC		iisc/iotati	011)										
sp			ption [W]*8		23			40	2110	/ = 10 /0	50			50								
ctri			on when operating [W]*9		16			15			48			48								
Ele	,,		r consumption [W]*10		43			48			104			106								
ns	Type*11							N	on-magn	etising lo	ck											
unit	Holding f	orce [	[N]	20	39	78	78	157	294	108	216	421	127	265	519							
Lock unit ecifications	Power co	nsum	ption [W]*12	2.9 5 5 5																		
ads 1	Rated vo	Itage	[V]						24 VDC	±10 %												
*1	Horizontal:	An ov	tornal quido is	nococcan	to suppo	ort the lea	d (Eriction	coofficio	nt of quid	lo: 0.1 or	loce) The	actual v	ork load	Horizontal: An external guide is necessary to support the load (Friction coefficient of guide: 0.1 or less). The actual work load and transfer spe								

\*1 Horizontal: An external guide is necessary to support the load (Friction coefficient of guide: 0.1 or less). The actual work load and transfer speed change according to the condition of the external guide. Also, speed changes according to the work load. Check "Model Selection" on pages 107 and 108.

Vertical: Speed changes according to the work load. Check "Model Selection" on pages 107 and 108.

Set the acceleration/deceleration values to be 3000 [mm/s²] or less.

- \*2 Pushing force accuracy is ±20 % (F.S.).
- \*3 The pushing force values for LEYG16 is 35 % to 85 %, for LEYG25 is 35 % to 65 %, for LEYG32 is 35 % to 85 %, and for LEYG40 is 35 % to 65 %. The pushing force values change according to the duty ratio and pushing speed. Check "Model Selection" on page 110.
- \*4 The speed and force may change depending on the cable length, load and mounting conditions. Furthermore, if the cable length exceeds 5 m, then it will decrease by up to 10 % for each 5 m. (At 15 m: Reduced by up to 20 %)
  - When [M: Sliding bearing] is selected, the maximum speed of lead [A] is 400 mm/s (at no-load, horizontal mounting).
  - The speed is also restricted with a horizontal/moment load. Refer to "Model Selection" on page 105.
- \*5 The allowable speed for the pushing operation
- \*6 A reference value for correcting an error in reciprocal operation
- \*7 Impact resistance: No malfunction occurred when it was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
  - Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
- \*8 The power consumption (including the controller) is for when the actuator is operating.
- \*9 The standby power consumption when operating (including the controller) is for when the actuator is stopped in the set position during the operation. Except during the pushing operation
- \*10 The maximum instantaneous power consumption (including the controller) is for when the actuator is operating. This value can be used for the selection of the power supply.
- \*11 With lock only
- \*12 For an actuator with lock, add the power consumption for the lock.



Щ

AC Servo Motor

#### Electric Actuator/Guide Rod Type LEYG Series Step Motor (Servo/24 VDC) Servo Motor (24 VDC)

#### **Specifications**

Servo Motor (24 VDC)

		Mod	lel	L	EYG16 <sup>™</sup>	□A	LEYG25 <sup>M</sup> □A						
	Work load	Horizontal	Acceleration/Deceleration at 3000 [mm/s <sup>2</sup> ]	3	6	12	7	15	30				
	[kg]*1	Vertical	Acceleration/Deceleration at 3000 [mm/s <sup>2</sup> ]	1.5	3.5	7.5	2	5	11				
ns	Pushin	g for	ce [N]*2 *3	16 to 30	30 to 58	57 to 111	18 to 35	37 to 72	66 to 130				
atio	Speed	mm/	s]	1 to 500	1 to 250	1 to 125	2 to 500	1 to 250	1 to 125				
Ę	Max. accele	eration/	deceleration [mm/s <sup>2</sup> ]			30	00						
eci	Pushin	g spe	eed [mm/s]*4		50 or less			35 or less					
Actuator specifications	Positioni	ng re	peatability [mm]			±0.	.02						
tor	Lost me	otion	[mm]*5			0.1 o	r less						
tua	Screw I	ead	[mm]	10	5	2.5	12	6	3				
Ac			resistance [m/s <sup>2</sup> ]*6			50/							
	Actuati	on ty	ре	Ball s	crew + Bel	t (LEYG⊡□	□), Ball scr	ew (LEYG	□□D)				
	Guide t	ype		Sliding b	earing (LE	YG□M), Ba	all bushing	bearing (L	.EYG□L)				
	-	_	mp. range [°C]			5 to							
			dity range [%RH]		90 (	or less (No	condensat	ion)					
ns	Motor s	ize			□28			□42					
atio	Motor o		ıt [W]		30			36					
Ę	Motor t					Servo moto	`	,					
Electric specifications	Encode			lr	ncremental	A/B (800 p		on)/Z phas	ie .				
g	Rated v					24 VDC	±10 %						
ric			umption [W]*7		40			86					
ec.			otion when operating [W]*8	4 (Hori	zontal)/6 (\	/ertical)	4 (Horiz	ontal)/12 (	Vertical)				
			ower consumption [W]*9		59			96					
it	Type*10				ı	Non-magn	etising lock	(					
Lock unit specifications	Holding			20	39	78	78	157	294				
Loc	Power co		nption [W]*11		2.9			5					
gs	Rated v	oltaç	ge [V]			24 VDC	±10 %						

- \*1 Horizontal: An external guide is necessary to support the load (Friction coefficient of guide: 0.1 or less). The actual work load and transfer speed change according to the condition of the external guide. Vertical: Check "Model Selection" on page 109 for details.
- Set the acceleration/deceleration values to be 3000 [mm/s2] or less.
- \*2 Pushing force accuracy is ±20 % (F.S.)
- \*3 The thrust setting values for LEYG16□A□ is 60 % to 95 % and for LEYG25□A□ is 70 % to 95 %. The pushing force values change according to the duty ratio and pushing speed. Check "Model Selection" on page 110.
- \*4 The allowable speed for the pushing operation
- \*5 A reference value for correcting an error in reciprocal operation
- \*6 Impact resistance: No malfunction occurred when it was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
  - Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
- \*7 The power consumption (including the controller) is for when the actuator is operating.
- \*8 The standby power consumption when operating (including the controller) is for when the actuator is stopped in the set position during the operation. Except during the pushing operation
- \*9 The maximum instantaneous power consumption (including the controller) is for when the actuator is operating. This value can be used for the selection of the power supply.
- \*10 With lock only
- \*11 For an actuator with lock, add the power consumption for the lock.

#### Weight

**Weight: Motor Top Mounting Type** 

			<u>, , , , , , , , , , , , , , , , , , , </u>																	
M	odel		LE	EYG16	SM				LE	EYG25	5M					LE	EYG32	2M		
Stroke [mm]		30	50	100	150	200	30	50	100	150	200	250	300	30	50	100	150	200	250	300
Product	Step motor	0.83	0.97	1.20	1.49	1.66	1.67	1.86	2.18	2.60	2.94	3.28	3.54	2.91	3.17	3.72	4.28	4.95	5.44	5.88
weight [kg]	Servo motor	0.83	0.97	1.20	1.49	1.66	1.63	1.82	2.14	2.56	2.90	3.24	3.50	_	_	_	_	_	_	_
M	odel		LE	EYG1	3L				LI	EYG2	5L					LE	EYG32	2L		
Stroke [mm]		30	50	100	150	200	30	50	100	150	200	250	300	30	50	100	150	200	250	300
Product	Step motor	0.84	0.97	1.14	1.43	1.58	1.68	1.89	2.13	2.56	2.82	3.14	3.38	2.91	3.18	3.57	4.12	4.66	5.17	5.56
weight [kg]	Servo motor	0.84	0.97	1.14	1.43	1.58	1.64	1.85	2.09	2.52	2.78	3.10	3.34	_	_	_	_	_	_	_
Model				LE	YG40	M					LE	EYG40	)L							
Stroke [mm]		30	50	100	150	200	250	300	30	50	100	150	200	250	300					
Product	Step motor	3.21	3.47	4.02	4.58	5.25	5.74	6.18	3.21	3.48	3.87	4.42	4.96	5.47	5.86					
weight [kg]	Servo motor	_	_	_	_	_	_	_	_	_	_	_	_	_	_					

#### Weight: In-line Motor Type

IV	lodei		Lt	EYGIC	IVI				L	= Y G 2 5	IVI					LE	= Y G 32	2IVI		
Stroke [mm]		30	50	100	150	200	30	50	100	150	200	250	300	30	50	100	150	200	250	300
Product	Step motor	0.83	0.97	1.20	1.49	1.66	1.66	1.85	2.17	2.59	2.93	3.27	3.53	2.90	3.16	3.71	4.27	4.94	5.43	5.87
weight [kg]	Servo motor	0.83	0.97	1.20	1.49	1.66	1.62	1.81	2.13	2.55	2.89	3.23	3.49	_	_	_	_	_	_	_
		1		->/04/	21					->/-							->/-	21		
Model			LI	EYG16	ίL				LI	EYG2	oL					LI	EYG32	2L		
Stroke [mm]		30	50	100	150	200	30	50	100	150	200	250	300	30	50	100	150	200	250	300
Product	Step motor	0.84	0.97	1.14	1.43	1.58	1.67	1.88	2.12	2.55	2.81	3.13	3.37	2.90	3.17	3.56	4.11	4.65	5.16	5.55
weight [kg]	Servo motor	0.84	0.97	1.14	1.43	1.58	1.63	1.84	2.08	2.51	2.77	3.09	3.33	_	_	_	_	_	_	_
M	Model			LE	YG40	M					LE	EYG40	)L			1				
																i				

Me	odel			LE	EYG40	M					LE	EYG4	0L		
Stroke [mm]		30	50	100	150	200	250	300	30	50	100	150	200	250	300
Product	Step motor	3.20	3.46	4.01	4.57	5.24	5.73	6.17	3.20	3.47	3.86	4.41	4.95	5.46	5.85
weight [kg]	Servo motor	_	_	_	_	_	_	_	_	_	_	_	_		_


<b>Additional Weight</b>	Ad	diti	onal	We	eiaht
--------------------------	----	------	------	----	-------

Additional Weight [kg]										
Size	16	25	32	40						
Lock	0.12	0.26	0.53	0.53						
Motor cover	0.02	0.03	0.04	0.05						
Lock/Motor cover	0.16	0.32	0.61	0.62						







#### Construction




Motor top mounting type With lock/motor cover



In-line motor type




In-line motor type
With lock/motor cover




# Electric Actuator/Guide Rod Type LEYG Series

#### Step Motor (Servo/24 VDC) Servo Motor (24 VDC)


#### Construction







Felt material is inserted to retain grease at the sliding part of the sliding bearing. This lengthens the life of the sliding part, but does not guarantee it permanently.



#### **Component Parts**

COIII	ponent Parts		
No.	Description	Material	Note
1	Body	Aluminium alloy	Anodised
2	Ball screw shaft	Alloy steel	
3	Ball screw nut	Synthetic resin/Alloy steel	
4	Piston	Aluminium alloy	
5	Piston rod	Stainless steel	Hard chrome plating
6	Rod cover	Aluminium alloy	
7	Bearing holder	Aluminium alloy	
8	Rotation stopper	POM	
9	Socket	Free cutting carbon steel	Nickel plating
10	Connected shaft	Free cutting carbon steel	Nickel plating
11	Bushing	Bearing alloy	
12	Bearing	_	
13	Return box	Aluminium die-cast	Coating
14	Return plate	Aluminium die-cast	Coating
15	Magnet	_	
16	Wear ring holder	Stainless steel	Stroke 101 mm or more
17	Wear ring	POM	Stroke 101 mm or more
18	Screw shaft pulley	Aluminium alloy	
19	Motor pulley	Aluminium alloy	
20	Belt	_	
21	Parallel pin	Stainless steel	
22	Seal	NBR	
23	Retaining ring	Steel for spring	Phosphate coated
24	Motor	_	
25	Motor cover	Synthetic resin	Only "With motor cover"
26	Grommet	Synthetic resin	Only "With motor cover"
27	Guide attachment	Aluminium alloy	Anodised

No.	Description	Material	Note
28	Guide rod	Carbon steel	
29	Plate	Aluminium alloy	Anodised
30	Plate mounting cap screw	Carbon steel	Nickel plating
31	Guide cap screw	Carbon steel	Nickel plating
32	Sliding bearing	Bearing alloy	
33	Lube-retainer	Felt	
34	Holder	Resin	
35	Retaining ring	Steel for spring	Phosphate coated
36	Ball bushing	_	
37	Spacer	Aluminium alloy	Chromated
38	Motor block	Aluminium alloy	Anodised
39	Motor adapter	Aluminium alloy	Anodised/LEY16, 25 only
40	Hub	Aluminium alloy	
41	Spider	NBR	
42	Motor cover with lock	Aluminium alloy	Only "With lock/motor cover"
43	Cover support	Aluminium alloy	Only "With lock/motor cover"

#### Replacement Parts/Belt

Hepi	accilicii	t i aits/Deit
No.	Size	Order no.
	16	LE-D-2-1
20	25	LE-D-2-2
	32, 40	LE-D-2-3

#### **Replacement Parts/Grease Pack**

Applied portion	Order no.
Piston rod	GR-S-010 (10 g)
Guide rod	GR-S-020 (20 g)


\* Apply grease on the piston rod periodically.

Grease should be applied at 1 million cycles or 200 km, whichever comes



#### **Dimensions: Motor Top Mounting**

\*1 Range within which the rod can move when it returns to origin Make sure workpieces mounted on the rod do not interfere with the work




Ø XA H9 depth XA 4 x OA thread depth OB

Section XX

#### LEYG L (Ball bushing bearing) [mm]

Size	Stroke range	L	DB				
16	90st or less	75	8				
16	91st or more, 200st or less	105	٥				
	114st or less	91					
25	115st or more, 190st or less	115	10				
	191st or more, 300st or less	133					
32	114st or less	97.5					
-	115st or more, 190st or less	116.5	13				
40	191st or more, 300st or less	134					



LEYC	<b>LEYG</b>								
Size	Stroke range	L	DB						
	64st or less	51.5							
16	65st or more, 90st or less 74.5		10						
	91st or more, 200st or less	105							
	59st or less	67.5							
25	60st or more, 185st or less	100.5	12						
	186st or more, 300st or less	138							
32	54st or less	74							
32 40	55st or more, 180st or less	107	16						
40	181st or more, 300st or less	144							


#### **LEYG**□M, **LEYG**□L Common

LEY(	LEYG□M, LEYG□L Common [mm]																				
Size	Stroke range	Α	В	С	DA	EA	EB	EH	EV	FA	FB	FC	G	GA	Н	J	K	M	NA	NB	NC
	39st or less	109	90.5	37																	
16	40st or more, 100st or less			52	16	35	69	83	41.1	8	10.5	8.5	4.3	31.8	74.3	24.8	23	25.5	M4 x 0.7	7	5.5
	101st or more, 200st or less	129	110.5	82																	
	39st or less	141.5	116	50	-																
0.5	40st or more, 100st or less	_		67.5		40	0.5	100	50.0		44.5	40.5		40.0	000	00.0	00	0.4			0.5
25	101st or more, 124st or less	400 5			20	46	85	103	52.3	11	14.5	12.5	5.4	40.3	98.8	30.8	29	34	M5 x 0.8	8	6.5
	125st or more, 200st or less	166.5	141	84.5	-																
	201st or more, 300st or less 39st or less			102 55																	
	40st or more, 100st or less	160.5	130	55	-																
32	101st or more, 124st or less			68	25	60	101	123	63.8	12	18.5	16.5	5.4	50.3	125.3	38.3	30	40	M6 x 1.0	10	8.5
40	125st or more, 200st or less	190.5	160	85	- 25	60	101	123	03.0	12	10.5	10.5	5.4	50.5	125.3	30.3	30	40	IVIO X 1.U	10	0.5
	201st or more, 300st or less	190.5	100	102	-																
	20131 01 111016, 30031 01 1633			102									<u> </u>								
Size	Stroke range	OA	ОВ	Р	Q	S	Т	U	٧	Step VA	motor VB	VA	motor VB	WA	WB	wc	Х	XA	XB	Υ	Z
	39st or less									10	10	10	10	25	19						
16	40st or more, 100st or less	M5 x 0.8	10	65	15	25	79	6.8	28	80.3	61.8	81	62.5	40	26.5	55	44	3	4	22.5	6.5
	101st or more, 200st or less													70	41.5	75	1		'		
	39st or less													35	26	70					
	40st or more, 100st or less	1												50	20.5	70					
25	101st or more, 124st or less	M6 x 1.0	12	80	18	30	95	6.8	42	85.4	63.4	81.6	59.6	50	33.5		54	4	5	26.5	8.5
	125st or more, 200st or less													70	43.5	95					
	201st or more, 300st or less													85	51						
	39st or less	]												40	28.5	75					
	40st or more, 100st or less													50	33.5	/ 5					
32	101st or more, 124st or less	M6 x 1.0	12	95	28	40	117	7.3	56.4	95.4	68.4	—	-				64	5	6	34	8.5
	125st or more, 200st or less	_												70	43.5	105					
	201st or more, 300st or less													85	51						
	39st or less													40	28.5	75					
	40st or more, 100st or less													50	33.5			_			
40	101st or more, 124st or less	M6 x 1.0	12	95	28	40	117	7.3	56.4	117.4	90.4	_	_			105	64	5	6	34	8.5
	125st or more, 200st or less													70	43.5	105					
	201st or more, 300st or less													85	51						

LEY


# Electric Actuator/Guide Rod Type LEYG Series Step Motor (Servo/24 VDC) Servo Motor (24 VDC)


#### **Dimensions: Motor Top Mounting**




		[mm]
Size	<b>T</b> 2	<b>X</b> 2
16	7.5	83
25	7.5	88.5
32	7.5	98.5
40	7.5	120.5

Motor cover material: Synthetic resin








				[mm			
Size	Step	motor	Servo motor				
Size	W	Х	W	Х			
16	103.3	121.8	104.0	122.5			
25	103.9	125.9	100.1	122.1			
32	111.4	138.4	_	_			
40	133.4	160.4	_	_			


#### With lock/motor cover: LEYG 35 □□ **B** -□W 40



		[mm
Size	<b>T</b> 2	<b>X</b> 2
16	7.5	124.5
25	7.5	129
32	7.5	141.5
40	7.5	163.5




#### **Dimensions: In-line Motor**




201st or more, 300st or less

#### **Dimensions: In-line Motor**




							[IIIIIII]
Size	Stroke range	Α	T <sub>2</sub>	<b>X</b> 2	L	Н	CV
16	100st or less	177	7.5	66.5	35	49.8	43
10	101st or more, 200st or less	197	7.5	00.5	33	49.0	43
25	100st or less	209.5	7.5	68.5	46	61.3	54.5
25	101st or more, 300st or less	234.5	7.5		40		54.5
32	100st or less	232	7.5	73.5	60	75.8	68.5
32	101st or more, 300st or less	262	7.5	73.5	00		08.5
40	100st or less	254	7.5	95.5	60	75.8	68.5
40	101st or more, 300st or less	284	7.5	95.5	00	75.0	08.5

#### 16 With lock: LEYG 32 \_\_\_A □D□ B -□B 40



					[mm]	
Size	Ctroko rongo	Step motor   Servo motor		Step motor	Servo motor	
Size	Stroke range		4	VB		
16	100st or less	215.8	216.5	103.3	104	
10	101st or more, 200st or less	235.8	236.5	103.3		
25	100st or less	246.9	243.1	103.9	100.1	
25	101st or more, 300st or less	271.9	268.1	103.9	100.1	
32	100st or less	271.9	_	111.4	_	
32	101st or more, 300st or less	301.9	_	111.4		
40	100st or less	293.9	_	133.4		
40	101st or more, 300st or less	323.9		133.4		

# 16 A 32D□B-□W 40 C With lock/motor cover: LEYG



								[mm]
	Size	Stroke range	Α	T <sub>2</sub>	<b>X</b> 2	L	Н	CV
	16	100st or less	218.5	7.5	108	35	49.8	43
	10	101st or more, 300st or less	238.5	7.5			49.0	
	25	100st or less	250	7.5	109	46	61.3	54.4
	25	101st or more, 300st or less	275	7.5	109			
	32	100st or less	275	7.5	116.5	60	75.8 75.8	68.5
	32	101st or more, 300st or less	305					
Ī	40	100st or less	297	7.5				
	40	101st or more, 300st or less	327	7.5	136.5	60		





#### **Support Block**


#### Guide for support block application

When the stroke exceeds 100 mm and the mounting orientation is horizontal, the body will be bent. Mounting the support block is recommended. (Please order it separately from the models shown below.)

#### **Support Block Model**







#### **⚠** Caution

Do not install the body using only a support block. The support block should be used only for support.

										[mm]
Size	Model	Stroke range	EB	G	GA	OA	ОВ	ST	wc	X
16	LEYG-S016	100st or less	69	4.3	31.8	M5 x 0.8	10	16	55	44
10	LE1G-3016	101st or more, 200st or less	09	4.3	31.0	IVIO X 0.6	10	10	75	44
25	LEYG-S025	100st or less	O.E.	85 5.4	40.3	M6 x 1.0	12	20	70	54
25	LE1G-5025	101st or more, 300st or less	00						95	54
32	LEYG-S032	100st or less	101	(5.4)	(50.2)	M6 x 1.0	12	22	75	64
40	40 LEYG-5032	101st or more, 300st or less	101	(5.4)	(50.3)	IVIO X 1.0	12	22	105	64

\* Two body mounting screws are included with the support block.

\* The through holes of the LEYG-S032 cannot be used for the motor top mounting type. Use taps on the bottom.

_		
	CIV	W

# **Electric Actuator/ Guide Rod Type**


LEYG Series LEYG25, 32





LECY□ Series p. 143

#### **How to Order**



#### Accuracy

Basic type High-precision type

### 2 Size

32

3 Bearing type Sliding bearing Ball bushing bearing

## 4 Motor mounting position

Top mounting D In-line

Motor type\*1

O IVIO	Wotor type ·								
Symbol	Туре	Output [W]	Actuator size	Compatible driver*3	UL-compliant				
S2	AC servo motor (Incremental encoder)	100	25	LECSA□-S1	_				
<b>S</b> 3	AC servo motor (Incremental encoder)	200	32	LECSA□-S3	_				
S6	AC servo motor (Absolute encoder)	100   25		LECSB□-S5 LECSC□-S5 LECSS□-S5	_				
<b>S</b> 7	AC servo motor (Absolute encoder)	200	32	LECSB□-S7 LECSC□-S7 LECSS□-S7	_				
<b>T6</b> *2	AC servo motor	100	25	LECSS2-T5	•				
T7	(Absolute encoder)	200	32	LECSS2-T7					

6 Lead [mm]

Symbol	LEYG25	LEYG32*1				
Α	12	16 (20)				
В	6	8 (10)				
С	3	4 (5)				

- \*1 The values shown in ( ) are the leads for the size 32 top mounting type. (Equivalent leads which include the pulley ratio [1.25:1])
- \*1 For motor type S2 and S6, the compatible driver part number suffixes are S1 and S5 respectively.
- \*2 For motor type T6, the compatible driver part number suffix is T5.
- \*3 For details on the driver, refer to page 246.

#### Stroke [mm]

30	30
to	to
300	300

- \* For details, refer to the applicable stroke table below.
- \* There is a limit for mounting the size 3 2 top mounting type and strokes of 50 mm or less. Refer to the dimensions.

#### **8** Motor option

_	Without option
В	With lock

#### 9 Guide option

_	Without option
F	With grease retaining function

Only available for size 25 and 32 sliding bearings (Refer to "Construction" on page

#### Cable type\*1 \*2

— Without cable						
S	Standard cable					
R	Robotic cable (Flexible cable)					

- \*1 The motor and encoder cables are included. (The lock cable is also included when the motor with lock option is selected.)
- \*2 Standard cable entry direction is
  - · Top mounting: (A) Axis side
  - · In-line: (B) Counter axis side (Refer to page 264 for details.)

#### Cable length\*1 [m]

_	Without cable
2	2
5	5
Α	10

\*1 The length of the motor, encoder, and lock cables are the same.

Applicable Stroke Table • Standard								
Stroke Model [mm]	30	50	100	150	200	250	300	Manufacturable stroke range
LEYG25	•	•	•		•			15 to 300
LEYG32		•	•		•	•		20 to 300

Please consult with SMC for non-standard strokes as they are produced as special orders.

For auto switches, refer to pages 101 to 103.



Environment

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

#### Electric Actuator/Guide Rod Type LEYG Series AC Servo Motor





Motor mounting position: Top mounting

Motor mounting position: In-line

Driver type\*1

	TO: Lypo		
	Compatible driver	Power supply voltage [V]	UL-compliant
_	Without driver		1
A1	LECSA1-S□	100 to 120	
A2	LECSA2-S□	200 to 230	_
B1	LECSB1-S□	100 to 120	_
B2	LECSB2-S□	200 to 230	_
C1	LECSC1-S□	100 to 120	_
C2	LECSC2-S□	200 to 230	_
S1	LECSS1-S□	100 to 120	_
S2	LECSS2-S□	200 to 230	_
32	LECSS2-T□	200 to 240	•

\*1 When a driver type is selected, a cable is included. Select the cable type and cable length.

Example)

S2S2: Standard cable (2 m) + Driver (LECSS2)

: Standard cable (2 m) : Without cable and driver I/O cable length [m]\*1

	-, -	ease iongin [m]
_	_	Without cable
H	1	Without cable (Connector only)
	1	1.5

\*1 When "Without driver" is selected for driver type, only "-: Without cable" can be selected. Refer to page 265 if I/O cable is required. (Options are shown on page 265.)

#### Use of auto switches for the guide rod type LEYG series

- · Auto switches must be inserted from the front side with the rod (plate) sticking out.
- · Auto switches cannot be fixed with the parts hidden behind the guide attachment (the side of the rod that sticks out).
- · Please consult with SMC when using auto switches on the side of the rod that sticks out, as it is produced as a special order.

**Compatible Driver** 

Companible Driv	CI									
Driver type	Pulse input type /Positioning type	Pulse input type	CC-Link direct input type	SSCNET III type	SSCNETIII/H type					
Series	LECSA	LECSB	LECSC	LECSS	LECSS-T					
Number of point tables	Up to 7	_	Up to 255 (2 stations occupied)	_	_					
Pulse input	0	0	_	_	_					
Applicable network	_	_	CC-Link	SSCNET II	SSCNET II/H					
Control encoder	Incremental 17-bit encoder	Absolute 18-bit encoder	Absolute 18-bit encoder	Absolute 18-bit encoder	Absolute 22-bit encoder					
Communication function	USB communication	USB communication,	munication							
Power supply voltage [V]		100 to 120 VAC (50/60 Hz) 200 to 240 VAC (50/60 Hz) (50/60 Hz)								
Reference page		246								



#### **Specifications**

	Model		LETG25 D36/10 (III-IIIIe)			LETG32L	S <sup>3</sup> /T7 (Top					
	Work load [kg]	Horizontal*1	18	50	50	30	60	60	30	60	60	
	. 01	Vertical	7	15	29	7	17	35	10	22	44	
	Force [N]*2 (Set value: 15	5 to 30 %)*11	65 to 131		242 to 485			294 to 588			368 to 736	
ဟ	Max. speed [mm/s]		900	450	225	1200	600	300	1000	500	250	
	Pushing speed [mm/		35 or less				30 or less			30 or less		
specification	Max. acceleration/deceleration/	ation [mm/s <sup>2</sup> ]		5000				50	00			
<u>:3</u>	Positioning	Basic type					±0.02					
등	repeatability [mm]	High-precision type		±0.01								
be	Lost motion [mm]*4	Basic type		0.1 or less								
		High-precision type		0.05 or less								
ctuator	Lead [mm] (including p		12	6	3	20	10	5	16	8	4	
Ę	Impact/Vibration resista	nce [m/s <sup>2</sup> ]*5		50/20				50/	/20			
Aci	Actuation type		Ball screw	+ Belt [1:1]		Ball so	crew + Belt [	1:1.25]		Ball screw		
_	Guide type				Sliding bear	ing (LEYG□	IM), Ball bus	shing bearing	j (LEYG□L)			
	Operating temperature		5 to 40				5 to	40				
	Operating humidity rai	nge [%RH]	90 or les	90 or less (No condensation) 90 or less (No condensation)								
	Regeneration option	1				depending on speed and work load (Refer to page 113.)						
S	Motor output/Size			100 W/□40		200 W/□60						
6	Motor type		AC servo motor (100/200 VAC) AC servo motor (100/200 VAC)									
specifications	Encoder		Motor type S2, S3: Incremental 17-bit encoder (Resolution: 131072 p/rev) Motor type S6, S7: Absolute 18-bit encoder (Resolution: 262144 p/rev) Motor type T6,T7: Absolute 22-bit encoder (Resolution: 4194304 p/rev)									
ğ	Power	Horizontal		45			65			65		
	consumption [W]*6	Vertical		145			175			175		
ectric	Standby power consumption	Horizontal		2			2			2		
Elec	when operating [W]*7	Vertical		8			8			8		
ш	Max. instantaneous power cons	sumption [W]*8		445			724			724		
it ons	Type*9		Non-	magnetising	lock			Non-magne	netising lock			
unit	Holding force [N]		131	255	485	157	157 308 588			385	736	
Si Si	Power consumption at	6.3				7.9			7.9			
ិន្ត Rated voltage [V]				24 VDC <sub>-10 %</sub>								

- \*1 This is the maximum value of the horizontal work load. An external guide is necessary to support the load. The actual work load changes according to the condition of the external
- support the load. The actual work load changes according to the condition of the external guide. Confirm the load using the actual device.

  \*2 The force setting range (set values for the driver) for the force control with the torque control mode. Set it with reference to "Force Conversion Graph" on page 114. When the control equivalent to the pushing operation of the controller LECP series is performed, select the LECSS driver and combine it with the Simple Motion (manufactured by Mischiel Electric Convertion). Mitsubishi Electric Corporation) which has a pushing operation function.

  \*3 The allowable collision speed for collision with the workpiece with the torque control mode
- \*4 A reference value for correcting an error in reciprocal operation
  \*5 Impact resistance: No malfunction occurred when the actuator was tested with a drop

Incremental encoder

tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)

1.84

Absolute encoder [S7]

Absolute encoder [T<sub>7</sub><sup>6</sup>]

2.05

Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead

- screw. (The test was performed with the actuator in the initial state.)

  \*6 The power consumption (including the driver) is for when the actuator is operating.

  \*7 The standby power consumption when operating (including the driver) is for when the actuator is stopped in the set position during operation.

  \*8 The maximum instantaneous power consumption (including the driver) is for when the
- \*9 Only when motor option "With lock" is selected
  \*10 For an actuator with lock, add the power consumption for the lock.
  \*11 For motor type T6 and T7, the set value is from 12 to 24 %.

5.08

5.02

5.0

4.66

4.60

4.6

5.58

5.52

5.5

5.98

5.92

5.9

#### Weight

	Weight: Motor Top Mounting Type [kg]														
	Series	LEYG25MS <sup>2</sup> /T6					LEYG32MS <sup>3</sup> /T7								
	Stroke [mm]	30	50	100	150	200	250	300	30	50	100	150	200	250	300
tor	Incremental encoder	1.80	1.99	2.31	2.73	3.07	3.41	3.67	3.24	3.50	4.05	4.80	5.35	5.83	6.28
Motor	Absolute encoder [S <sub>7</sub> ]	1.86	2.05	2.37	2.79	3.13	3.47	3.73	3.18	3.44	3.99	4.74	5.29	5.77	6.22
Σ÷	Absolute encoder [T <sub>7</sub> ]	1.8	2.0	2.4	2.8	3.1	3.5	3.7	3.2	3.4	4.0	4.7	5.3	5.7	6.2
	Series			LEY	G25LS	<sup>2</sup> /T6			LEYG32LS <sup>3</sup> /T7						
	Stroke [mm]	30	50	100	150	200	250	300	30	50	100	150	200	250	300
5 0	Incremental encoder	1.81	2.02	2.26	2.69	2.95	3.27	3.51	3.24	3.51	3.9	4.64	5.06	5.56	5.96
Motor	Absolute encoder [S <sub>7</sub> <sup>6</sup> ]	1.87	2.08	2.32	2.75	3.01	3.33	3.57	3.18	3.45	3.84	4.58	5.00	5.50	5.90
Σ÷	Absolute encoder [T7]	1.9	2.1	2.3	2.7	3.0	3.3	3.6	3.2	3.4	3.8	4.6	5.0	5.5	5.9

Weig	Weight: In-line Motor Type [kg]														
	Series	LEYG25MDS <sup>2</sup> /T6					LEYG32MDS <sup>3</sup> /T7								
	Stroke [mm]	30	50	100	150	200	250	300	30	50	100	150	200	250	300
e o	Incremental encoder	1.83	2.02	2.34	2.76	3.10	3.44	3.70	3.26	3.52	4.07	4.82	5.37	5.85	6.30
Mote	Absolute encoder [S <sup>6</sup> <sub>7</sub> ]	1.89	2.08	2.40	2.82	3.16	3.50	3.76	3.20	3.46	4.01	4.76	5.31	5.79	6.24
Σ÷	Absolute encoder [T <sub>7</sub> ]	1.9	2.1	2.4	2.8	3.1	3.5	3.7	3.2	3.4	4.0	4.7	5.3	5.8	6.2
	Series		LEYG25LDS <sub>6</sub> /T6					LEYG32LDS <sup>3</sup> /T7							
Stroke [mm]		30	50	100	150	200	250	300	30	50	100	150	200	250	300

3.30

3.54

3.26

3.53

3.92

2.98

j ģ ģ		coder [S <sup>6</sup> ]	1.90	2.11	2.35	2.78	3.04	3.36	3.60	3.20	3.47	3.86
Σ÷	Absolute er	coder [T <sup>6</sup> ]	1.9	2.1	2.3	2.8	3.0	3.3	3.6	3.2	3.4	3.8
Add	itional Weigh	t					[kg]					
	Size				25	3	2					
		Increme	ental en	coder	0.2	0 0.4	10					

0.30

0.3

2.29

2.72

0.66

0.7


Lock


AC Servo Motor

# Electric Actuator/Guide Rod Type LEYG Series AC Servo Motor


#### Construction







## **LEYG** M














#### When grease retaining function selected LEYG25/32M: 50st or less





LEYG25/32M: Over 50st




#### **LEYG** L







LEYG25/32L: Over 100st



#### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminium alloy	Anodised
2	Ball screw shaft	Alloy steel	
3	Ball screw nut	Synthetic resin/Alloy steel	
4	Piston	Aluminium alloy	
5	Piston rod	Stainless steel	Hard chrome plating
6	Rod cover	Aluminium alloy	
7	Bearing holder	Aluminium alloy	
8	Rotation stopper	POM	
9	Socket	Free cutting carbon steel	Nickel plating
10	Connected shaft	Free cutting carbon steel	Nickel plating
11	Bushing	Bearing alloy	
12	Bearing	_	
13	Return box	Aluminium die-cast	Coating
14	Return plate	Aluminium die-cast	Coating
15	Magnet	_	
16	Wear ring holder	Stainless steel	Stroke 101 mm or more
17	Wear ring	POM	Stroke 101 mm or more
18	Screw shaft pulley	Aluminium alloy	
19	Motor pulley	Aluminium alloy	
20	Belt	_	
21	Parallel pin	Stainless steel	
22	Seal	NBR	
23	Retaining ring	Steel for spring	Phosphate coated
24	Motor adapter	Aluminium alloy	Coating
25	Motor	_	
26	Motor block	Aluminium alloy	Coating

No.	Description	Material	Note
27	Hub	Aluminium alloy	
28	Spider	Urethane	
29	Guide attachment	Aluminium alloy	Anodised
30	Guide rod	Carbon steel	
31	Plate	Aluminium alloy	Anodised
32	Plate mounting cap screw	Carbon steel	Nickel plating
33	Guide cap screw	Carbon steel	Nickel plating
34	Sliding bearing	Bearing alloy	
35	Felt	Felt	
36	Holder	Synthetic resin	
37	Retaining ring	Steel for spring	Phosphate coated
38	Ball bushing	_	
39	Spacer	Aluminium alloy	Chromated

Size

25

#### Support Block

<u>oappo</u>	I C DIOOK
Size	Order no.
25	LEYG-S025
32	LEYG-S032

<sup>\*</sup> Two body mounting screws are included with the support block.

#### **Replacement Parts/Grease Pack**

Applied portion	Order no.						
Piston rod	GR-S-010 (10 g)						
Guide rod	GR-S-020 (20 g)						

	ack .
*	Apply grease on the piston rod
	periodically.
	Grease should be applied at 1
	million cycles or 200 km,

whichever comes first.


**Replacement Parts/Belt** 


Order no.

LE-D-2-2 LE-D-2-4



#### **Dimensions: Motor Top Mounting**






- \*1 Range within which the rod can move

  Make sure workpieces mounted on the rod do not interfere
  with the workpieces and facilities around the rod.
- \*2 The Z-phase first detecting position from the stroke end of the motor side
- \*3 Through holes cannot be used for size 32 with strokes of 50 mm or less.

#### **LEYG**□**L** (Ball bushing bearing) [mm]

Size	Stroke range [mm]	L	DB
	Up to 114	91	
25	115 to 190	115	10
	191 to 300	133	
	Up to 114	97.5	
32	115 to 190	116.5	13
	191 to 300	134	



B + Stroke

A + Stroke


0.5

FA<sub>.</sub>

С

FB

Υ



<del>(၂)</del> တ(တ

T

EΗ

LEY	G□M (Sliding bea	ring)	[mm]
Size	Stroke range [mm]	L	DB
	Up to 59	67.5	
25	60 to 185	100.5	12
	186 to 300	138	
	Up to 59	74	
32	60 to 185	107	16
	186 to 300	144	

#### **LEYG**□M, **LEYG**□L Common

			301111	11011																	[HIIII]
Size	Stroke range [mm]	Α	В	С	DA	EA	ЕВ	ЕН	EV	FA	FB	FC	G	GA	Н	J	K	M	NA	NB	NC
	Up to 39	141.5	116	50																	
	40 to 100	141.5	110	67.5																	
25	101 to 124			07.5	20	46	85	103	52.3	11	14.5	12.5	5.4	40.3	98.8	30.8	29	34	M5 x 0.8	8	6.5
	125 to 200	166.5	141	84.5																	
	201 to 300			102																	
	Up to 39	160.5	130	55																	
	40 to 100	100.5	130	68																	
32	101 to 124			00	25	60	101	123	63.8	12	18.5	16.5	5.4	50.3	125.3	38.3	30	40	M6 x 1.0	10	8.5
	125 to 200	190.5	160	85																	
	201 to 300			102																	
Size	Stroke range [mm]	ОА	ОВ	Р	Q	S	Т	U	V	WA	WB	wc	Х	XA	ХВ	Υ	Z				
	Up to 39									35	26	70									

	Op 10 39	]								33	20	70					
	40 to 100									50	33.5	/0					
25	101 to 124	M6 x 1.0	12	80	18	30	95	6.8	40	30	33.3		54	4	5	26.5	8.5
	125 to 200	]								70	43.5	95					
	201 to 300	]								85	51						
	Up to 39									40	28.5	75					
	40 to 100									50	33.5	/5					
32	101 to 124	M6 x 1.0	12	95	28	40	117	7.3	60	50	33.5		64	5	6	34	8.5
	125 to 200									70	43.5	105					
	201 to 300									85	51						

		Inc	crement	al enco	der			Abso	lute end	oder [S	6/S7]			Abso	lute end	coder [T	6/T7]	
Size	W	ithout lo	ck	\	Nith loc	<	Wi	ithout lo	ck	\	With lock	<	Wi	thout lo	ck	\	With lock	<
	VA	VB	VC	VA	VB	VC	VA	VB	VC	VA	VB	VC	VA	VB	VC	VA	VB	VC
25	120	87	14.1	156.9	123.9	15.8	115.4	82.4	14.1	156.5	123.5	15.8	115.4	82.4	14.1	156	123	15.8
32	128.2	88.2	17.1	156.8	116.8	17.1	116.6	76.6	17.1	156.1	116.1	17.1	116.6	76.6	17.1	153.4	113.4	17.1

Model Selection

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

LEY AC Servo Motor LEYG

25A-LEY | LEY-X5 Environment


LECA6 Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEC-G

LECP1 LECPA

LECS AC Servo Motor LECY

Specific Product Precautions

**Dimensions: In-line Motor** 



	Size	Stroke range [mm]	L	DB
		Up to 114	91	
	25	115 to 190	115	10
		191 to 300	133	
ĺ		Up to 114	97.5	
	32	115 to 190	116.5	13
		191 to 300	134	

i	,	-		0 0	
Δ,	×	Ø	5	0 0	
•		Ø DB	z,	0.5 4 x Ø G through  L + Stroke	_
			-	■ 1 Ollone	

LEYG□M (Sliding bearing) [mm] Size Stroke range [mm] DB Up to 59 67.5 25 60 to 185 100.5 12 186 to 300 138 74 Up to 59 32 60 to 185 107 16 144 186 to 300

LEY	G□M, LEYO	G□L (	Comn	non													[mm]
Size	Stroke range [mm]	В	С	DA	ЕВ	ЕН	EV	FA	FB	FC	G	GA	Н	J	K	NA	NC
	Up to 39	136.5	50														
	40 to 100	130.3	67.5														
25	101 to 124		07.5	20	85	103	52.3	11	14.5	12.5	5.4	40.3	53.3	30.8	29	M5 x 0.8	6.5
	125 to 200	161.5	84.5														
	201 to 300		102														
	Up to 39	156	55														
	40 to 100	100	68														
32	101 to 124			25	101	123	63.8	12	18.5	16.5	5.4	50.3	68.3	38.3	30	M6 x 1.0	8.5
	125 to 200	186	85														
	201 to 300		102														
Size	Stroke range [mm]	ОА	ОВ	Р	Q	S	Т	U	V	WA	WB	wc	Х	XA	ХВ	YD	Z
	Up to 39									35	26	70					
	40 to 100	M6 x								50	33.5	70					
25	101 to 124	1.0	12	80	18	30	95	6.8	40	50	33.5		54	4	5	47	8.5
	125 to 200	1.0								70	43.5	95					
	201 to 300									85	51						
	Up to 39									40	28.5	75					
	40 to 100	M6 x								50	33.5	/3					
32	101 to 124	1.0	12	95	28	40	117	7.3	60				64	5	6	60	8.5
	125 to 200	1.0	.0				' '	7.0		70	43.5	105					
	201 to 300									85	51						

	Chualia vanana		Inc	rement	al enco	der			Absol	lute end	oder [S	6/S7]			Abso	lute end	oder [T	6/T7]	
Size	Stroke range	Wi	thout lo	ck	٧	Vith loc	k	Wi	thout lo	ck	V	Vith lock	<	Wi	thout lo	ck	V	Vith loc	K
	[mm]	Α	VB	VC	Α	VB	VC	Α	VB	VC	Α	VB	VC	Α	VB	VC	Α	VB	VC
25	15 to 100	249	87	14.6	285.9	123.9	16.3	244.4	82.4	14.6	285.5	123.5	16.3	244.4	82.4	14.6	285	123	16.3
25	105 to 300	274	07	14.0	310.9	123.9	16.3	269.4	02.4	14.0	310.5	123.5	16.3	269.4	02.4	14.0	310	123	16.3
32	15 to 100	274.7	88.2	17.1	303.3	116.8	17.1	263.1	76.6	171	302.6	116.1	171	263.1	76.6	17.1	299.9	110 /	171
32	105 to 300	304.7	00.2	17.1	333.3	110.6	17.1	293.1	70.0	17.1	332.6	110.1	17.1	293.1	70.0	17.1	329.9	113.4	17.1





#### **Support Block**


#### Guide for support block application

When the stroke exceeds 100 mm and the mounting orientation is horizontal, the body will be bent. Mounting the support block is recommended. (Please order it separately from the models shown below.)

#### **Support Block Model**







#### **⚠** Caution

Do not install the body using only a support block. The support block should be used only for support.

										[mm]
Size	Model	Stroke range	EB	G	GA	OA	ОВ	ST	wc	Х
25	LEYG-S025	100st or less	85	5.4	40.3	M6 x 1.0	12	20	70	54
	LL1G-3023	101st or more, 300st or less	00	5.4	40.0	WO X 1.0	12	20	95	
32	LEYG-S032	100st or less	101	(5.4)	(50.3)	M6 x 1.0	12	22	75	64
32	LEYG-5032	101st or more, 300st or less	101	(5.4)	(50.3)	IVIO X 1.0	12	22	105	04

\* Two body mounting screws are included with the support block.

\* The through holes of the LEYG-S032 cannot be used for the motor top mounting type. Use taps on the bottom.

	QI/	
~	OIA	


# **Electric Actuator/ Guide Rod Type**

LEYG Series LEYG25, 32



LECS□ Series Pp. 135

#### **How to Order**



#### Accuracy

_	
_	Basic type
Н	High-precision type

2	Si	ze
	_	

9 312
25
32

#### **3** Bearing type

M	Sliding bearing	
L	Ball bushing bearing	

	N/I - 4	mounting	
47	Motor	mounting	position

	<u> </u>
_	Top mounting
D	In-line

**5** Motor type

Symbol	Туре	Output [W]	Actuator size	Compatible driver
V6*1	AC servo motor (Absolute encoder)	100	25	LECYM2-V5 LECYU2-V5
V7		200	32	LECYM2-V7 LECYU2-V7

\*1 For motor type V6, the compatible driver part number suffix is V5.

6 Lead [mm]

Symbol	LEYG25	LEYG32*1
Α	12	16 (20)
В	6	8 (10)
С	3	4 (5)

\*1 The values shown in () are the leads for the top mounting type. (Equivalent leads which include the pulley ratio [1.25:1])

Stroke [mm]


30	30
to	to
300	300

- \* For details, refer to the applicable stroke table below.
- \* There is a limit for mounting the size 3 2 top mounting type and strokes of 5 0 mm or less. Refer to the dimensions.

**8** Motor option

	Without option
В	With lock

When "With lock" is selected for the top mounting type, the motor body will stick out from the end of the body for size 25 with strokes of 30 mm or less. Check for interference with work-pieces before selecting a model.



9 Guide option

	_	Without option
	F	With grease retaining function

\* Only available for the sliding bearing

Cable type\*1

_	
_	Without cable
S	Standard cable
R	Robotic cable (Flexible cable)

\*1 The motor and encoder cables are included. The motor cable for lock option is included when the motor with lock option is selected. Cable length [m]\*1

<u> </u>	
_	Without cable
3	3
5	5
Α	10
С	20

\*1 The length of the motor and encoder cables are the same. (For with lock)

#### **Applicable Stroke Table**

Applicable Stroke Table 9: Standard										
Stroke [mm]	30	50	100	150	200	250	300	Manufacturable stroke range		
LEYG25	•	•	•	•	•	•	•	15 to 300		
LEYG32	•	•	•	•	•	•	•	20 to 300		

\* Please consult with SMC for non-standard strokes as they are produced as special orders.

For auto switches, refer to pages 101 to 103.





Motor mounting position: Top mounting

# 12 Driver type

	Compatible driver	Power supply voltage [V]		
_	Without driver	_		
M2	LECYM2-V□	200 to 230		
U2	LECYU2-V□	200 to 230		

\* When a driver type is selected, a cable is included.

Select the cable type and cable length.

# I/O cable length [m]\*1

_	Without cable
Н	Without cable (Connector only)
1	1.5

\*1 When "Without driver" is selected for driver type, only "-: Without cable" can be selected. Refer to page 278 if I/O cable is required. (Options are shown on page 278.)

#### Use of auto switches for the guide rod type LEYG series

- · Auto switches must be inserted from the front side with the rod (plate) sticking out.
- Auto switches cannot be fixed with the parts hidden behind the guide attachment (the side of the rod that sticks out).
- Please consult with SMC when using auto switches on the side of the rod that sticks out, as it is produced as a special order.

#### **Compatible Driver**

Driver type	MECHATROLINK-II type	MECHATROLINK-III type						
Series	LECYM	LECYU						
Applicable network	MECHATROLINK-II	MECHATROLINK-Ⅲ						
Control encoder		Absolute 20-bit encoder						
Communication device	USB communication,	RS-422 communication						
Power supply voltage [V]	200 to 230 VAC (50/60 Hz)							
Reference page	2	71						



# **Specifications**

Model		LEYG25 <sup>M</sup> V6 (Top mounting) LEYG25 <sup>M</sup> DV6 (In-line)			LEYG32	<sup>™</sup> V7 (Top n	nounting)	LEYG32 <sup>M</sup> DV7 (In-line)			
	Wayle land [leg]	Horizontal*1	18	50	50	30	60	60	30	60	60
	Work load [kg]	Vertical	7	15	29	7	17	35	10	22	44
	Force [N]*2 (Set value:	45 to 90 %)	65 to 131	127 to 255	242 to 485	79 to 157	154 to 308	294 to 588	98 to 197	192 to 385	368 to 736
	Max. speed [mm/s]		900	450	225	1200	600	300	1000	500	250
ns	Pushing speed [mm/	<b>/s]</b> *3		35 or less			30 or less			30 or less	
specifications	Max. acceleration/deceleration			5000				50	00		
<u>S</u>	Positioning	Basic type		±0.02				±0.	.02		
Ci.	repeatability [mm]	High-precision type		±0.01				±0.	.01		
be	Lost motion [mm]	Basic type		0.1 or less				0.1 o	r less		
	Lost motion [mm]	High-precision type		0.05 or less				0.05 c	r less		
Actuator	Lead [mm] (including p		12	6	3	20	10	5	16	8	4
Ę	Impact/Vibration resista	nce [m/s <sup>2</sup> ]*4		50/20 50/20							
Ac	Actuation type		Ball screw	+ Belt [1:1]		Ball screw + Belt [1:1.25] Ball screw					
	Guide type		Sliding bearing (LEYG□M), Ball bushing bearing (LEYG□L)								
	Operating temperature			5 to 40		5 to 40					
	Operating humidity ra		90 or les	s (No conde	ensation)	90 or less (No condensation)					
	Conditions for*5	Horizontal		Not required	ł	Not required					
	"Regenerative resistor" [kg]	Vertical		5 or more		2 or more					
Su	Motor output/Size			100 W/□40 200 W/□60							
≘	Motor type		AC servo motor (200 VAC)  AC servo motor (200 VAC)					C)			
specifications	Encoder				Absolute	e 20-bit enco		ition: 104857	'6 p/rev)		
eci	Power	Horizontal		45			65			65	
	consumption [W]*6	Vertical		145			175			175	
5	Standby power consumption			2			2			2	
Electric	when operating [W]*7	Vertical	8				8			8	
							724			724	
it	Type*9			magnetising	<u> </u>				netising lock		
k unit icatior	Holding force [N]		131	255	485	157	308	588	197	385	736
Lock	Power consumption at 2	20 °C [W]*10	5.5 6 6								
ds	Rated voltage [V]						24 VDC +10 %	0			

- \*1 This is the maximum value of the horizontal work load. An external guide is necessary to support the load. The actual work load changes according to the condition of the external guide. Confirm the load using the actual device.
- \*2 The force setting range (set values for the driver) for the force control with the torque control mode
  - Set it with reference to "Force Conversion Graph" on page 119.
- \*3 The allowable collision speed for collision with the workpiece with the torque control mode
- \*4 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.) Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
- \*5 The work load conditions which require "Regenerative resistor" when operating at the maximum speed (Duty ratio: 100 %)
  - Order the regenerative resistor separately. For details, refer to "Conditions for Regenerative Resistor (Guide)" on page 118.
- \*6 The power consumption (including the driver) is for when the actuator is operating.
- \*7 The standby power consumption when operating (including the driver) is for when the actuator is stopped in the set position during operation.
- \*8 The maximum instantaneous power consumption (including the driver) is for when the actuator is operating.
- \*9 Only when motor option "With lock" is selected
- \*10 For an actuator with lock, add the power consumption for the lock.

# Weight

Product Weight: Motor Top Mounting Type [kg]														
Series		LEYG25MV6								LE	YG32M	IV7		
Stroke [mm]	30	50	100	150	200	250	300	30	50	100	150	200	250	300
Weight [kg]	1.7	1.9	2.2	2.6	3.0	3.3	3.6	3.1	3.4	4.0	4.7	5.3	5.7	6.2
Series	Series LEYG25LV6 LEYG32LV7					LEYG25LV6								
Stroke [mm]	30	50	100	150	200	250	300	30	50	100	150	200	250	300
Weight [kg]	1.7	1.9	2.2	2.6	2.9	3.2	3.4	3.1	3.4	3.8	4.5	5.0	5.5	5.9

Product Weight: In-line Motor Type [kg]														
Series		LEYG25MDV6								LE,	YG32MI	DV7		
Stroke [mm]	30	50	100	150	200	250	300	30	50	100	150	200	250	300
Weight [kg]	1.7	1.9	2.2	2.6	3.0	3.3	3.6	3.2	3.4	4.0	4.7	5.3	5.8	6.2
Series		LEYG25LDV6								LE	YG32LI	DV7		
Stroke [mm]	30	50	100	150	200	250	300	30	50	100	150	200	250	300
Weight [kg]	17	2.0	22	2.6	29	3.2	3.4	3.2	3.4	3.8	4.6	5.0	5.5	5.9

Additional Weight [k						
Size	25	32				
Lock	0.3	0.6				





AC Servo Motor

Electric Actuator/Guide Rod Type LEYG Series
AC Servo Motor


# Construction

# Motor mounting position: Top mounting type






# **LEYG** M



# **LEYG** L



**Component Parts** 

No.	Description	Material	Note
1	Body	Aluminium alloy	Anodised
2	Ball screw shaft	Alloy steel	
3	Ball screw nut	_	
4	Piston	Aluminium alloy	
5	Piston rod	Stainless steel	Hard chrome plating
6	Rod cover	Aluminium alloy	
7	Bearing holder	Aluminium alloy	
8	Rotation stopper	POM	
9	Socket	Free cutting carbon steel	Nickel plating
10	Connected shaft	Free cutting carbon steel	Nickel plating
11	Bushing	Bearing alloy	
12	Bearing	_	
13	Return box	Aluminium die-cast	Coating
14	Return plate	Aluminium die-cast	Coating
15	Magnet	_	
16	Wear ring holder	Stainless steel	Stroke 101 mm or more
17	Wear ring	POM	Stroke 101 mm or more
18	Screw shaft pulley	Aluminium alloy	
		·	

**Support Block** 

Size	Order no.
25	LEYG-S025
32	LEYG-S032

Two body mounting screws are included with the support block.

No.	Description	Material	Note
19	Motor pulley	Aluminium alloy	
20	Belt	_	
21	Parallel pin	Stainless steel	
22	Seal	NBR	
23	Retaining ring	Steel for spring	Phosphate coated
24	Motor adapter	Aluminium alloy	Coating
25	Motor	-	
26	Motor block	Aluminium alloy	Coating
27	Hub	Aluminium alloy	
28	Spider	Urethane	
29	Guide attachment	Aluminium alloy	Anodised
30	Guide rod	Carbon steel	
31	Plate	Aluminium alloy	Anodised
32	Plate mounting cap screw	Carbon steel	Nickel plating
33	Guide cap screw	Carbon steel	Nickel plating
34	Sliding bearing	Bearing alloy	
35	Retaining ring	Steel for spring	Phosphate coated
36	Ball bushing	_	


#### Replacement Parts/Belt

Size	Order no.
25	LE-D-2-2
32	LE-D-2-4





# **Dimensions: Motor Top Mounting**



Size	Stroke range [mm]	L	DB
	15 to 110	91	
25	115 to 190	115	10
	195 to 300	133	
	20 to 110	97.5	
32	115 to 190	116.5	13
	195 to 300	134	

4 x Ø G through*3	LEY	G□M (Sliding bea	ring)	[mm]
	Size	Stroke range (mm)	L	DB
oke		15 to 55	67.5	
→ Ne	25	60 to 185	100.5	12
		190 to 300	138	
		20 to 55	74	
	32	60 to 185	107	16
		190 to 300	144	

[mm]

LEY	G□M, LEYC	à□L (	Comn	non
Size	Stroke range [mm]	Α	В	С

Size	Stroke range [mm]	Α	В	С	DA	EA	ЕВ	EH	EV	FA	FB	FC	G	GA	Н	J	K	М	NA	NB	NC
	15 to 35	141.5	116	50																	
	40 to 100	141.5	110	67.5																	
25	105 to 120			07.5	20	46	85	103	52.3	11	14.5	12.5	5.4	40.3	98.8	30.8	29	34	M5 x 0.8	8	6.5
	125 to 200	166.5	141	84.5																	
	205 to 300			102																	
	20 to 35	160.5	130	55																	
	40 to 100	100.0	100	68																	
32	105 to 120				25	60	101	123	63.8	12	18.5	16.5	5.4	50.3	125.3	38.3	30	40	M6 x 1.0	10	8.5
	125 to 200	190.5	160	85																	
	205 to 300			102																	
Size	Stroke range [mm]	ОА	ОВ	Р	Q	S	Т	U	٧	WA	WB	wc	Х	XA	ХВ	Υ	Z				
Size		ОА	ОВ	P	Q	S	Т	U	V	<b>WA</b> 35	<b>WB</b> 26		Х	XA	ХВ	Υ	Z				
Size	[mm]	OA	ОВ	Р	Q	S	Т	U	V	35	26	<b>WC</b> 70	Х	XA	ХВ	Υ	Z				
Size	[mm] 15 to 35	<b>OA</b> M6 x 1.0	<b>OB</b>	<b>P</b> 80	<b>Q</b> 18	<b>S</b>	<b>T</b> 95	<b>U</b> 6.8	<b>V</b>				<b>X</b> 54	<b>XA</b> 4	<b>XB</b> 5	<b>Y</b> 26.5	<b>Z</b> 8.5				
	[mm] 15 to 35 40 to 100									35	26					-					
	[mm] 15 to 35 40 to 100 105 to 120									35 50	26 33.5	70				-					
	[mm] 15 to 35 40 to 100 105 to 120 125 to 200									35 50 70	26 33.5 43.5	70				-					
	[mm] 15 to 35 40 to 100 105 to 120 125 to 200 205 to 300									35 50 70 85 40	26 33.5 43.5 51 28.5	70				-					
	[mm] 15 to 35 40 to 100 105 to 120 125 to 200 205 to 300 20 to 35									35 50 70 85	26 33.5 43.5 51	70				-					
25	[mm] 15 to 35 40 to 100 105 to 120 125 to 200 205 to 300 20 to 35 40 to 100	M6 x 1.0	12	80	18	30	95	6.8	40	35 50 70 85 40	26 33.5 43.5 51 28.5	70	54	4	5	26.5	8.5				

Size	W	ithout lo	ck	With lock				
SIZE	VA	VB	VC	VA	VB	VC		
25	115.5	82.5	11	160.5	127.5	11		
32	120	80	14	160	120	14		



Environment

190 to 300

20 to 55

60 to 185

190 to 300

32

138


74

16

107

144

# **Dimensions: In-line Motor**



. = > / 0 = > .	. =	_
LEYG□M.	LEYGUL	Common

195 to 300

20 to 110

115 to 190

195 to 300

32

133

97.5

116.5

134

13

LET	G⊔M, LEYC	7 L L	COIIIII	IIOII													[mm]
Size	Stroke range [mm]	В	С	DA	ЕВ	EH	EV	FA	FB	FC	G	GA	Н	J	K	NA	NC
	15 to 35	136.5	50														
	40 to 100	130.5	67.5														
25	105 to 120		07.3	20	85	103	52.3	11	14.5	12.5	5.4	40.3	53.3	30.8	29	M5 x 0.8	6.5
	125 to 200	161.5	84.5														
	205 to 300		102														
	20 to 35	156	55														
	40 to 100	130	68														
32	105 to 120			25	101	123	63.8	12	18.5	16.5	5.4	50.3	68.3	38.3	30	M6 x 1.0	8.5
	125 to 200	186	85														
	205 to 300		102														
Size	Stroke range [mm]	OA	ОВ	Р	Q	s	Т	U	V	WA	WB	wc	X	XA	ХВ	YD	Z
Size	_	OA	ОВ	P	Q	S	Т	U	V	<b>WA</b> 35	<b>WB</b> 26		X	ХА	ХВ	YD	Z
Size	[mm]		ОВ	Р	Q	S	Т	U	V	35	26	<b>WC</b> 70	х	XA	ХВ	YD	Z
Size 25	[mm] 15 to 35	M6 x	<b>OB</b>	<b>P</b> 80	<b>Q</b> 18	<b>S</b>	<b>T</b> 95	<b>U</b> 6.8	<b>V</b>				<b>X</b> 54	<b>XA</b> 4	<b>XB</b> 5	<b>YD</b> 47	<b>Z</b> 8.5
	[mm] 15 to 35 40 to 100			-					-	35	26						
	[mm] 15 to 35 40 to 100 105 to 120	M6 x		-					-	35 50	26 33.5	70					
	[mm] 15 to 35 40 to 100 105 to 120 125 to 200	M6 x		-					-	35 50 70	26 33.5 43.5	70					
	[mm] 15 to 35 40 to 100 105 to 120 125 to 200 205 to 300	M6 x 1.0		-					-	35 50 70 85 40	26 33.5 43.5 51 28.5	70					
	[mm] 15 to 35 40 to 100 105 to 120 125 to 200 205 to 300 20 to 35	M6 x 1.0		-					-	35 50 70 85	26 33.5 43.5 51	70					
25	[mm] 15 to 35 40 to 100 105 to 120 125 to 200 205 to 300 20 to 35 40 to 100	M6 x 1.0	12	80	18	30	95	6.8	40	35 50 70 85 40	26 33.5 43.5 51 28.5	70	54	4	5	47	8.5
25	[mm] 15 to 35 40 to 100 105 to 120 125 to 200 205 to 300 20 to 35 40 to 100 105 to 120	M6 x 1.0	12	80	18	30	95	6.8	40	35 50 70 85 40 50	26 33.5 43.5 51 28.5 33.5	70 95 75	54	4	5	47	8.5

L + Stroke

Size	Stroke range	W	ithout lo	ck	\	Nith loc	k
Size	[mm]	Α	VB	VC	Α	VB	VC
25	15 to 100	255.5	82.5	11.5	300.5	127.5	11.5
25	105 to 300	280.5	02.5	11.5	325.5	127.5	11.5
32	15 to 100	266.5	80	14	306.5	120	14
32	105 to 300	296.5	80	14	336.5	120	14







# **Support Block**


# •Guide for support block application

When the stroke exceeds 100 mm and the mounting orientation is horizontal, the body will be bent. Mounting the support block is recommended. (Please order it separately from the models shown below.)

# **Support Block Model**







#### **⚠** Caution

Do not install the body using only a support block. The support block should be used only for support.

										[mm]
Size	Model	Stroke range	EB	G	GA	OA	ОВ	ST	wc	X
25	LEYG-S025	15 to 100	85	5.4	40.3	M6 x 1.0	12	20	70	54
23	LE1G-3025	105 to 300	00	3.4	40.3	IVIO X 1.0	12	20	95	54
32	LEYG-S032	20 to 100	101	5.4	50.3	M6 x 1.0	12	22	75	64
32	LE 1 G-3032	105 to 300	101	3.4	50.5	IVIO X 1.0	12	22	105	04


\* Two body mounting screws are included with the support block.

\* The through holes of the LEYG-S032 cannot be used for the motor top mounting type. Use taps on the bottom.

# **Dust-tight/Water-jet-proof (IP65 Equivalent)**

- Enclosure: IP65 equivalent\*1
- Max. stroke: 500 mm\*2

\*2 For size 32



\*1 IP65 enclosure: The protection structure against solid foreign objects is dust-tight type and the protection structure against water is water-jet-proof type.

Dust-tight means that no dust can enter the inside of the equipment.

Water-jet-proof means that the product is not adversely affected by direct water jets from any direction. That is, even when direct water jets are applied to the product for 3 minutes by means of the pre-determined method, there is no water entry that hinders the correct operation inside the equipment. Be sure to take appropriate protective measures if the product is to be used in an environment where it will be constantly exposed to water or fluids other than water splash. In particular, the product cannot be used in environments where oils, such as cutting oil or cutting fluid, are present







# **Secondary Battery Compatible**

- ●Copper (Cu) and zinc (Zn) free<sup>\*1</sup>
  - \*1 Excludes motors, cables, controllers/drivers
- Compatible with dew points as low as -70 °C

Uses grease compatible with low dew points





\* Copper and zinc materials are used for the motors, cables, controllers/drivers.



Step Motor (Servo/24 VDC) Servo Motor (24 VDC)

**Electric Actuator/Rod Type** 

LEY-X5 Series Dust-tight/Water-jet-proof (IP65 Equivalent)

# **Model Selection**

LEY-X5 Series ▶p. 155

Speed–Work Load Graph (Guide) for Step Motor (Servo/24 VDC) LECP1, JXC□1



Lead 12: LEY25A

300

Speed [mm/s]


400

600


500

Refer to page 108 for the LECPA JXC $\square_3^2$  and page 109 for the LECA6.

#### Horizontal




#### Vertical




200





for acceleration/deceleration: 2000 mm/s<sup>2</sup>




#### LEY32□-X5


0

0


100



# Graph of Allowable Lateral Load on the Rod End (Guide)




[Stroke] = [Product stroke] + [Distance from the rod end to the centre of gravity of the workpiece]



# Rod Displacement: δ [mm]

Stroke Size	30	50	100	150	200	250	300	350	400	450	500
25	±0.3	±0.4	±0.7	±0.7	±0.9	±1.1	±1.3	±1.5	±1.7	_	_
32	±0.3	±0.4	±0.7	±0.6	±0.8	±1.0	±1.1	±1.3	±1.5	±1.7	±1.8

**SMC** 



LEY

LEYG

LEY

LEYG

LEY-X5

25A-LEY

LECA6

LEC-G

LECP1

LECPA

LECS

AC Servo Motor

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

Environment


AC Servo Motor

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)


# Speed–Work Load Graph (Guide) For Step Motor (Servo/24 VDC) LECPA, JXC□3

Refer to page 107 for the LECP1, JXC□1 and page 109 for the LECA6.


#### Horizontal













#### LEY32□-X5




# For Servo Motor (24 VDC) LECA6

#### Horizontal



#### Vertical




ecific Product

# **Force Conversion Graph**


#### Step Motor (Servo/24 VDC)

#### LEY25□-X5




Ambient temperature	Set value of pushing force*1 [%]	Duty ratio [%]	Continuous pushing time [minute]
40 °C or less	65 or less	100	_

#### LEY32□-X5



Ambient temperature	Set value of pushing force*1 [%]	Duty ratio [%]	Continuous pushing time [minute]
25 °C or less	85 or less	100	_
40 °C	65 or less	100	_
40 C	85	50	15

# Non-rotating Accuracy of Rod




Size	Non-rotating accuracy θ
25	±0.8°
32	±0.7°
32	

Avoid using the electric actuator in such a way that rotational torque would be applied to the piston rod.

This may cause the deformation of the non-rotating guide, abnormal auto switch responses, play in the internal guide, or an increase in the sliding resistance

# Servo Motor (24 VDC)

#### LEY25□A-X5



Ambient temperature	Set value of pushing force*1 [%]	Duty ratio [%]	Continuous pushing time [minute]
40 °C or less	95 or less	100	_

#### <Limit Values for Pushing Force and Trigger Level in Relation to Pushing Speed> Without Load

	Model	Lead	Pushing speed [mm/s]	Pushing force (Setting input value)	Model	Lead	Pushing speed [mm/s]	Pushing force (Setting input value)
	LEY25	A/B/C	21 to 35	50 to 65 %	LEY25□A	A/B/C	21 to 35	80 to 95 %
	LEY32	Α	24 to 30	60 to 85 %				
		B/C	21 to 30	00 10 05 %				

There is a limit to the pushing force in relation to the pushing speed. If the product is operated outside of the range (low pushing force), the completion signal [INP] may be output before the pushing operation has been completed (during the moving operation).

If operating with the pushing speed below the min. speed, please check for operating problems before using the product.

#### <Set Values for Vertical Upward Transfer Pushing Operations>

For vertical loads (upward), set the pushing force to the max. value shown below and operate at the work load or less.

Model	LEY25□		LEY32□			LEY25□A			
Lead	Α	A B C		Α	В	С	Α	В	С
Work load [kg]	2.5	5	10	4.5	9	18	1.2	2.5	5
Pushing force	65 %		85 %			95 %			

\*1 Set values for the controller

Specific Product Precautions

<b>SMC</b>
------------

# **Electric Actuator/** Rod Type Dust-tight/Water-jet-proof (IP65 Equivalent)


LEY-X5 (Made to Order) Series LEY25, 32

(RoHS)

Refer to page 151 for model selection.

#### **How to Order**





### 1 Size 25 32

# 2 Motor mounting position

_	Top mounting
D	In-line

# Motor type

Cumple of	Time	Si	ze	Commodible controller/duiver		
Symbol	Туре	25	32	Compatible controller/driver		
-	Step motor (Servo/24 VDC)	•	•	LECP1 JXCP1 LECPA JXCP1 LECPA JXCD1 JXCL1		
Α	Servo motor (24 VDC)	•	_	LECA6		

# 4 Lead [mm]

Rod end thread

Symbol	LEY25	LEY32
Α	12	16
В	6	8
С	3	4

# 5 Stroke [mm]

30	30
to	to
500	500

<sup>\*</sup> For details, refer to the applicable stroke table

# 6 Motor option\*2

_	Without option		
В	With lock		
	Motor		

# 8 Mounting\*3

_	Rod end female thread	Symbol	
М	Rod end male thread	Symbol	
IVI	(1 rod end nut is included.)		Ends
			botto
		_	

Symbol	Type	Motor mounting position		
Symbol	туре	Top mounting	In-line	
_	Ends tapped/Body bottom tapped*4	•	•	
L	Foot	•	_	
F	Rod flange*4	<b>●</b> *5	•	
G	Head flange*4	<b>*</b> 6	_	

# Actuator cable type/length

Robotic	[m]		
R1	1.5	RA	10* <sup>7</sup>
R3	3	RB	15* <sup>7</sup>
R5	5	RC	20*7
R8	8*7		

# Applicable Stroke Table\*1

•:	St	anc	lar	(

Stroke [mm]		50	100	150	200	250	300	350	400	450	500	Manufacturable stroke range
LEY25	•	•	•	•		•	•	•	•	_		15 to 400
LEY32	•	•	•	•	•	•	•	•	•	•	•	20 to 500

<sup>\*</sup> For auto switches, refer to page 176.

<sup>\* &</sup>quot;-X5" is not added to an actuator model with a controller/driver part number suffix. Example) "LEY25DB-100" for the LEY25DB-100BMU-R16N1D-X5


Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEC-G

LECPA

AC Servo Motor

pecific Product

Series (For details, refer to page 157.)



# Controller/Driver type\*8

_	Without controller/driv	er
6N	LECA6	NPN
6P	(Step data input type)	PNP
1N	LECP1*9	NPN
1P	(Programless type)	PNP
AN	LECPA*9 *11	NPN
AP	(Pulse input type)	PNP

# I/O cable length\*12, Communication plug

_	Without cable
1	1.5 m
3	3 m* <sup>13</sup>
5	5 m* <sup>13</sup>
S	Straight type communication plug connector
Т	T-branch type communication plug connector




# Controller/Driver mounting

_	Screw mounting
D	DIN rail*14

# JXC Series (For details, refer to page 157.



D



\*1 Please consult with SMC for non-standard strokes as they are

For single axis

- produced as special orders.
  When "With lock" is selected for the top mounting type, the motor body will stick out from the end of the body for strokes of 5 0 mm or less. Check for interference with workpieces before selecting a model.
- \*3 The mounting bracket is shipped together with the product but does not come assembled. \*4 For the horizontal cantilever mounting of the rod flange, head flange, or ends tapped types, use the actuator within the following stroke range. ·LEY25: 200 mm or less ·LEY32: 100 mm or less
- The rod flange type is not available for the LEY 25/32 with strokes of 50 mm or less and motor option "With lock.
- The head flange type is not available for the LEY32
- \*7 Produced upon receipt of order (Robotic cable only)
- \*8 For details on controllers/drivers and compatible motors, refer to the compatible controller/driver on the next page.

- \*9 Only available for the motor type "Step motor"
  - \*10 Not compliant with CE
- \*11 When pulse signals are open collector, order the current limiting
- resistor (LEC-PA-R-□) on page 220 separately. \*12 When "Without controller/driver" is selected for controller/driver types, I/O cable cannot be selected. Refer to page 199 (For LECA6), page 213 (For LECP1), or page 220 (For LECPA) if I/O cable is required.
- \*13 When "Pulse input type" is selected for controller/driver types, pulse input usable only with differential. Only 1.5 m cables usable with open collector
- \*14 The DIN rail is not included. Order it separately.
- \*15 Select "—" for anything other than DeviceNet™

# **⚠** Caution

#### [CE-compliant products]

DeviceNet™

IO-Link

- 1) EMC compliance was tested by combining the electric actuator LEY series and the controller LEC/JXC series.
  - The EMC depends on the configuration of the customer's control panel and the relationship with other electrical equipment and wiring. Therefore, compliance with the EMC directive cannot be certified for SMC components incorporated into the customer's equipment under actual operating conditions. As a result, it is necessary for the customer to verify compliance with the EMC directive for the machinery and equipment as a whole.
- 2 For the servo motor (24 VDC) specification, EMC compliance was tested by installing a noise filter set (LEC-NFA). Refer to page 199 for the noise filter set. Refer to the LECA series Operation Manual for installation.

#### [UL-compliant products (For the LEC series)]


When compliance with UL is required, the electric actuator and controller/ driver should be used with a UL1310 Class 2 power supply.

# The actuator and controller/driver are sold as a package.

Confirm that the combination of the controller/driver and actuator is correct.

# <Check the following before use.>

- 1 Check the actuator label for the model number. This number should match that of the controller/driver.
- 2 Check that the Parallel I/O configuration matches (NPN or PNP).



Refer to the Operation Manual for using the products. Please download it via our website, https://www.smc.eu

# **Compatible Controller/Driver**

# **LEC**□ Series

Туре	Step data input type	Programless type	Pulse input type
Series	LECA6	LECP1	LECPA
Features	Value (Step data) input Standard controller	Capable of setting up operation (step data) without using a PC or teaching box	Operation by pulse signals
Compatible motor	Servo motor (24 VDC)		motor 24 VDC)
Max. number of step data	64 points	14 points	_
Power supply voltage			
Reference page	191	207	214

# JXC□ Series

Туре	EtherCAT® direct input type	EtherNet/IP™ direct input type	PROFINET direct input type	DeviceNet <sup>TM</sup> direct input type	IO-Link direct input type
Series	JXCE1	JXC91	JXCP1	JXCD1	JXCL1
Features	EtherCAT® direct input	EtherNet/IP™ direct input	PROFINET direct input	DeviceNet™ direct input	IO-Link direct input
Compatible motor	anost mput	an ook input	Step motor (Servo/24 VDC)	anost input	an ook mput
Max. number of step data			64 points		
Power supply voltage			24 VDC		
Reference page			224		

# **Specifications**

Step Motor (Servo/24 VDC)

Work load   For   (3000 [mm/s²])   20   40   60   30   45	80								
Work load									
Work load [kg]*1	40								
IKG **   For LECPA	.0								
JXC□3 (2000 [mm/s²])   18   50   50   30   60	60								
Vertical*14   (3000 [mm/s²])   7   15   29   10   21	42								
Pushing force [N]*2 *3 *4 63 to 122 126 to 238 232 to 452 80 to 189 156 to 370 296	6 to 707								
Speed [mm/s]*4         18 to 400         9 to 200         5 to 100         24 to 400         12 to 200         6	to 100								
Max. acceleration/deceleration [mm/s <sup>2</sup> ] 3000									
Pushing speed [mm/s]*5 35 or less 30 or less									
Positioning repeatability [mm] $\pm 0.02$									
Lost motion [mm]*6 0.1 or less									
Screw lead [mm]         12         6         3         16         8	4								
Impact/Vibration resistance [m/s <sup>2</sup> ]* <sup>7</sup> 50/20									
Actuation type  Ball screw + Belt (LEY□) Ball screw (LEY□D)									
Guide type Sliding bushing (Piston rod)									
Enclosure*8 IP65 equivalent									
Operating temperature range [°C] 5 to 40									
Operating humidity range [%RH] 90 or less (No condensation)									
<b>2</b>   Motor size									
Motor type Step motor (Servo/24 VDC)									
Encoder Incremental A/B phase (800 pulse/rotation)									
Rated voltage [V] 24 VDC ±10 %									
Power consumption [W]*9 40 50									
Motor size									
Type*12 Non-magnetising lock									
Holding force [N] 78 157 294 108 216	421								
Power consumption [W]*13 5									
Rated voltage [V] 24 VDC ±10 %									

- \*1 Horizontal: The maximum value of the work load. An external guide is necessary to support the load. (Friction coefficient of guide: 0.1 or less) The actual work load and transfer speed change according to the condition of the external guide. Also, speed changes according to the work load. Check "Model Selection" on pages 151 and 152.
  - Vertical: Speed changes according to the work load. Check "Model Selection" on pages 151 and 152.
  - The values shown in ( ) are the acceleration/deceleration. Set these values to be 3000 [mm/s²] or less.
- \*2 Pushing force accuracy is ±20 % (F.S.).
- \*3 The thrust setting values for LEY25 is 38 % to 65 % and for LEY32 is 38 % to 85 %. The pushing force values change according to the duty ratio and pushing speed. Check "Model Selection" on page 153.
- \*4 The speed and force may change depending on the cable length, load, and mounting conditions. Furthermore, if the cable length exceeds 5 m, then it will decrease by up to 10 % for each 5 m. (At 15 m: Reduced by up to 20 %)
- \*5 The allowable speed for pushing operation. When push conveying a workpiece, operate at the vertical work load or less.
- \*6 A reference value for correcting an error in reciprocal operation
- \*7 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
  - Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
- \*8 Cannot be used in an environment where oil such as cutting oil splashes or it is constantly exposed to water
- Take appropriate protective measures. For details on enclosure, refer to "Enclosure" on page 188.
- \*9 The power consumption (including the controller) is for when the actuator is operating.
- \*10 The standby power consumption when operating (including the controller) is for when the actuator is stopped in the set position during the operation. Except during the pushing operation
- The maximum instantaneous power consumption (including the controller) is for when the actuator is operating. This value can be used for the selection of the power supply
- \*12 With lock only
- \*13 For an actuator with lock, add the power consumption for the lock.
- \*14 When mounting vertically and using the product facing upwards in an environment where water is present, take necessary measures to prevent water from splashing on the rod cover, because water will accumulate on the rod seal due to the structure of the product.



# **Specifications**

#### Servo Motor (24 VDC)

		Model			LEY25□A-X5					
	Work load	Horizontal	(3000 [mm/s <sup>2</sup> ])	7	15	30				
	[kg]*1	Vertical*13	(3000 [mm/s <sup>2</sup> ])	2	5	11				
	Pushing ford	e [N]*2 *3		18 to 35	37 to 72	66 to 130				
	Speed [mm/s	<b>s</b> ]		2 to 400	1 to 200	1 to 100				
S	Max. acceler	ation/decelera	ation [mm/s²]		3000					
ţi	Pushing spe	ed [mm/s]*4			35 or less					
fica	Positioning I	epeatability [	mm]		±0.02					
eci	Lost motion	[mm]* <sup>5</sup>			0.1 or less					
gs	Screw lead [	mm]		12	6	3				
ator	Impact/Vibra	tion resistand	e [m/s²]*6		50/20					
Actuator specifications	Actuation ty	oe		Ball screw + Belt (LEY□) Ball screw (LEY□D)						
	Guide type			Slidir	ng bushing (Pistor	n rod)				
	Enclosure*7				IP65 equivalent					
	Operating te	mperature rar	nge [°C]	5 to 40						
	Operating hu	ımidity range	[%RH]	90 or less (No condensation)						
Suc	Motor size			□42						
Electric specifications	Motor type			Servo motor (24 VDC)						
iji	Encoder			Incremental A/B	phase (800 pulse/i	rotation)/Z-phase				
bec	Rated voltag				24 VDC ±10 %					
ic s	Power consu	ımption [W]*8			86					
ectr			when operating [W]*9	4 (H	orizontal)/12 (Ver	tical)				
		neous power of	consumption [W]*10		96					
Lock unit specifications	Type*11			Non-magnetising lock						
catio	Holding forc			78 157 294						
Lock	Power consu	ımption [W]*1	2	5						
S	Rated voltag	e [V]			24 VDC ±10 %					

- \*1 Horizontal: The maximum value of the work load. An external guide is necessary to support the load. (Friction coefficient of guide: 0.1 or less) The actual work load and transfer speed change according to the condition of the external guide. Vertical: Speed changes according to the work load. Check "Model Selection" on page 152. The values shown in ( ) are the acceleration/ deceleration.
- Set these values to be 3000 [mm/s²] or less.
- \*2 Pushing force accuracy is ±20 % (F.S.).
  \*3 The thrust setting values for LEY25A□ is 75 % to 95 %. The pushing force values change according to the duty ratio and pushing speed. Check "Model Selection" on page 153.
- \*4 The allowable speed for pushing operation When push conveying a workpiece, operate at the vertical work load or less.
- \*5 A reference value for correcting an error in reciprocal operation
- \*6 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
  - Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
- \*7 Cannot be used in an environment where oil such as cutting oil splashes or it is constantly exposed to water
- Take appropriate protective measures. For details on enclosure, refer to "Enclosure" on page 188.
- \*8 The power consumption (including the controller) is for when the actuator is operating.
- \*9 The standby power consumption when operating (including the controller) is for when the actuator is stopped in the set position during the operation with the maximum work load. Except during the pushing operation
- \*10 The maximum instantaneous power consumption (including the controller) is for when the actuator is operating. This value can be used for the selection of the power supply.
- \*11 With lock only
- \*12 For an actuator with lock, add the power consumption for the lock.
- \*13 When mounting vertically and using the product facing upwards in an environment where water is present, take necessary measures to prevent water from splashing on the rod cover, because water will accumulate on the rod seal due to the structure of the product.

# Weight

Weight: Motor Top Mounting Type

	g																				
	Model		LEY25-X5									LEY32-X5									
<b>Stroke [mm]</b> 30 50 100 150 200 250 300					350	400	30 50 100 150 200 250 300 350 400 450 5						500								
Product	Step motor	1.45	1.52	1.69	1.95	2.13	2.30	2.48	2.65	2.83	2.48	2.59	2.88	3.35	3.64	3.91	4.21	4.49	4.76	5.04	5.32
weight [kg]	Servo motor	1.41	1.48	1.65	1.91	2.09	2.26	2.44	2.61	2.79	_	_	_	_	_	_	_	_	_	_	_

Weight: In-line Motor Type

	Model LEY25D-X5									LEY32D-X5											
Stroke [mm] 30 50 100 150 200 250 300 350 400 30 50 100 150							150	200	250	300	350	400	450	500							
Product	Step motor	1.46	1.53	1.70	1.96	2.14	2.31	2.49	2.66	2.84	2.49	2.60	2.89	3.36	3.65	3.92	4.22	4.50	4.77	5.05	5.33
weight [kg]	Servo motor	1.42	1.49	1.66	1.92	2.10	2.27	2.45	2.62	2.80	_	_	_	_	_	_	_	_	_	_	_

. . . . . . . .

Additional Weight			[kg]					
Siz	e	25	32					
Lock	ock							
Rod end male thread	Male thread	0.03	0.03					
nou enu maie uneau	Nut	0.02	0.02					
Foot bracket (2 sets inc	cluding mounting bolt)	0.08	0.14					
Rod flange (including n	Rod flange (including mounting bolt)							
Head flange (including	mounting bolt)	0.17	0.20					





Electric Actuator/Rod Type LEY-X5 Series


Step Motor (Servo/24 VDC) Servo Motor (24 VDC) Dust-tight/Water-jet-proof (IP65 Equivalent)

# Construction

Motor top mounting type: LEY<sub>32</sub><sup>25</sup>







**Component Parts** 

No.	Description	Material	Note
1	Body	Aluminium alloy	Anodised
2	Ball screw shaft	Alloy steel	
3	Ball screw nut	Synthetic resin/Alloy steel	
4	Piston	Aluminium alloy	
5	Piston rod	Stainless steel	Hard chrome plating
6	Rod cover	Aluminium alloy	
7	Bearing holder	Aluminium alloy	
8	Rotation stopper	POM	
9	Socket	Free cutting carbon steel	Nickel plating
10	Connected shaft	Free cutting carbon steel	Nickel plating
11	Bushing	Bearing alloy	
12	Bearing	_	
13	Return box	Aluminium die-cast	Coating
14	Return plate	Aluminium die-cast	Coating
15	Magnet	_	
16	Wear ring holder	Stainless steel	Stroke 101 mm or more
17	Wear ring	POM	Stroke 101 mm or more
18	Screw shaft pulley	Aluminium alloy	
19	Motor pulley	Aluminium alloy	

	·		
No.	Description	Material	Note
20	Belt	_	
21	Parallel pin	Stainless steel	
22	Scraper	Nylon	
23	Retaining ring	Steel for spring	Phosphate coated
24	Motor	_	
25	Lube-retainer	Felt	
26	O-ring	NBR	
27	Gasket	NBR	
28	Motor adapter	Aluminium alloy	Anodised
29	Motor cover	Aluminium alloy	Anodised
30	Seal connector	_	
31	End cover	Aluminium alloy	Anodised
32	Hub	Aluminium alloy	
33	Spider	NBR	
34	Motor block	Aluminium alloy	Anodised
35	Motor adapter	Aluminium alloy	LEY25 only
36	Socket (Male thread)	Free cutting carbon steel	Nickel plating
37	Nut	Alloy steel	Zinc chromated

#### Replacement Parts (Motor top mounting only)/Belt

	No.	Size	Order no.
	20	25	LE-D-2-2
		32	LE-D-2-3

**Replacement Parts/Grease Pack** 


Applied portion	Order no.
Piston rod	GR-S-010 (10 g) GR-S-020 (20 g)

Apply grease on the piston rod periodically. Grease should be applied at 1 million cycles or 200 km, whichever comes first.



# **Dimensions**

#### Motor top mounting type



Size	Stroke range [mm]	Α	В	С	D	EH	EV	FH	FV	GH	GV	Н	J	K	L	М	<b>O</b> 1
25	15 to 100	130.5	116	13	20	44	45.5	57.6	56.8	66.2	139.5	M8 x 1.25	24	17	14.5	34	M5 x 0.8
	101 to 400	155.5	141														
32	20 to 100	148.5	130	13	25	51	56.5	69.6	78.6	76.2	173.5	M8 x 1.25	31	22	18.5	40	M6 x 1.0
32	101 to 500	178.5	160			Ŭ.	00.0	00.0	, 5.0	, 5.2	1,0.0	1110 X 1.20			10.0	.0	1110 % 1.0

Size	Stroke	R	OA	ОВ	PA	РВ	_	6	т	- 11	PC	V	V	<u> </u>	X	v
Size	range [mm]	n	UA	ОВ	FA	PD	Q	3	'	0	PC	Without lock	With lock	Without lock	With lock	I
25	15 to 100	0	37	38	15 /	8.2	28	46	92	4	15.4	123	173	1.45	195	E-1
25	101 to 400	0	37	30	15.4	13.4 0.2	0.2   20	46	92	'	15.4	123	1/3	145	195	51
20	20 to 100	10	27	20	15 /	0.0	20	60	110	4	15.0	100	170	150	200	61
32	101 to 500	10	37	38	15.4	8.2	28	60	118	'	15.9	123	173	150	200	61

Body	Body Bottom Tapped [mm]											
Size	Stroke range [mm]	MA	МВ	МС	MD	МН	ML	МО	MR	XA	ХВ	
	15 to 39			24	32		50	M5 x 0.8		4		
	40 to 100			42	41		50		6.5			
25	101 to 124	20	46	42	71	29	75				5	
	125 to 200			59	49.5							
	201 to 400			76	58							
	20 to 39			22	36		50					
	40 to 100			36	43		50					
32	101 to 124	25	25 55 53 70	40	30		M6 x 1	8.5	5	6		
_	125 to 200			53	51.5		80					
	201 to 500			70	60							

- \*1 Range within which the rod can move when it returns to origin Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.
- \*2 Position after return to origin
- \*3 [ ] for when the direction of return to origin has changed
- \*4 The direction of rod end width across flats ( $\square K$ ) differs depending on the products.
- \*5 The vent hole is the port for releasing to atmosphere. Do not apply pressure to this hole. Attach tubing to the vent hole and place the end of the tubing so it is not exposed to dust or water.

For the rod end male thread, refer to page 67. For the mounting bracket dimensions, refer to page 97.



LEY


Environment

Electric Actuator/Rod Type LEY-X5 Series

Step Motor (Servo/24 VDC) Servo Motor (24 VDC) Dust-tight/Water-jet-proof (IP65 Equivalent)

# **Dimensions**

# In-line motor type



Size	Stroke		Α	В	С	D	EH	EV	FH	FV	G	н	J	К	L
	range [mm]	Without lock	With lock												
25	15 to 100	250	300	89.5	13	20	44	45.5	57.6	57.7	94.7	M8 x 1.25	24	17	14.5
25	101 to 400	275	325	114.5	13	20	20 44	45.5	37.0	37.7	34.7	1010 X 1.25	24	17	14.5
32	20 to 100	265.5	315.5	96	10	25	51	56.5	69.6	79.6	116.6	M8 x 1.25	31	22	18.5
32	101 to 500	295.5	345.5	126	13	25	31	30.3	09.0	79.0	110.0	1016 X 1.25	31	22	16.5
				_											

Size	Stroke range [mm]	М	<b>O</b> 1	R	OA	ОВ	PA	РВ	Q	U	РС	Without lock	With lock	Υ
25	15 to 100 101 to 400	34	M5 x 0.8	8	37	38	15.4	8.2	28	0.9	15.9	146	196	24.5
32	20 to 100 101 to 500	40	M6 x 1.0	10	37	38	15.4	8.2	28	1	15.9	151	201	27

Body	<b>Bottom T</b>	apped								[mm]
Size	Stroke range [mm]	MA	МС	MD	МН	ML	МО	MR	XA	ХВ
	15 to 39		24	32		50				
	40 to 100		42	41	29	50	M5 x 0.8	6.5	4	
25	101 to 124	20	42	41		75				5
	125 to 200		59	49.5						
	201 to 400		76	58						
	20 to 39		22	36		50				
	40 to 100		36	43		30				
32	101 to 124	25	30	43	30		M6 x 1	8.5	5	6
_	125 to 200		53	51.5		80				
	201 to 500		70	60						

- \*1 Range within which the rod can move when it returns to origin Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around
- \*2 Position after return to origin
- \*3 [ ] for when the direction of return to origin has changed
- \*4 The direction of rod end width across flats ( $\square K$ ) differs depending on the products.
- \*5 The vent hole is the port for releasing to atmosphere. Do not apply pressure to this hole. Attach tubing to the vent hole and place the end of the tubing so it is not exposed to dust or water.

For the rod end male thread, refer to page 67. For the mounting bracket dimensions, refer to page 97.



# **Electric Actuator/** Rod Type Dust-tight/Water-jet-proof (IP65 Equivalent)

LEY-X5 (Made to Order) Series LEY25, 32

Refer to page 41 for model selection.


Size 63 is available by selecting option P. Refer to page 79.





LECY□ Series > p. 169

#### **How to Order**



Accuracy

_	Basic type
Н	High-precision type

2 Size

Motor mounting position									
_	Top mounting								
D	In-line								

Lead [mm]

Symbol	LEY25□	LEY32□*1
Α	12	16 (20)
В	6	8 (10)
С	3	4 (5)

\*1 The values shown in ( ) are the equivalent leads which include the pulley ratio for the size 32 top mounting type. 4 Motor type

Symbol	Туре	Output [W]	Actuator size	Compatible driver
S2*1	AC servo motor	100	25	LECSA□-S1
S3	(Incremental encoder)	200	32	LECSA□-S3
S6*1	AC servo motor	100	25	LECSB□-S5 LECSC□-S5 LECSS□-S5
<b>S7</b>	(Absolute encoder)	200	32	LECSB□-S7 LECSC□-S7 LECSS□-S7
T6*2	AC servo motor	100	25	LECSS2-T5
T7	(Absolute encoder)	200	32	LECSS2-T7

- \*1 For motor type S2 and S6, the compatible driver part number suffixes are S1 and S5 respectively.
- \*2 For motor type T6, the compatible driver part number suffix is T5.

6 Stroke [mm]

30	30
to	to
500	500

For details, refer to the applicable stroke table below.

Motor option

_	Without option
В	With lock*1

\*1 When "With lock" is selected for the top mounting type, the motor body will stick out from the end of the body for size 25 with strokes of 30 mm or less. Check for interference with workpieces before selecting a model.



# Rod end thread

<ul> <li>Rod end female thread</li> </ul>					
М	Rod end male thread (1 rod end nut is included.)				

9 Mounting\*1

Symbol	Tuno	Motor mounting position				
Symbol	Туре	Top mounting	In-line			
_	Ends tapped/ Body bottom tapped *2	•	•			
L	Foot	•				
F	Rod flange*2	●*3	•			
G	Head flange*2	●*4	_			

- The mounting bracket is shipped together with the product but does not come assembled.
- \*2 For the horizontal cantilever mounting of the rod flange, head flange, or ends tapped types, use the actuator within the following stroke range.
  - LEY25: 200 mm or less
  - LEY32: 100 mm or less
- \*3 The rod flange type is not available for the LEY25 with a 30 mm stroke and motor option "With lock."
- \*4 The head flange type is not available for the LEY32.

Cable type\*1 \*2

	71
_	Without cable
S	Standard cable
R	Robotic cable (Flexible cable)

- The motor and encoder cables are included. (The lock cable is also included when the motor with lock option is selected.)
- \*2 Standard cable entry direction is
  - Top mounting: (A) Axis side
  - In-line: (B) Counter axis side (Refer to page 264 for details.)

13 I/O cable length [m]\*1

<b>P</b> "	oasio iorigai [iii]
I	Without cable
Н	Without cable (Connector only)
1	1.5

\*1 When "Without driver" is selected for driver type, only "-: Without cable" can be selected. Refer to page 265 if I/O cable is required. (Options are shown on page 265.)

Cable length [m]\*1

<b>U</b> Ou	
_	Without cable
2	2
5	5
Α	10

\*1 The length of the encoder, motor, and lock cables are the same.

Driver type\*1

<b>W</b> Dri	ver type	
	Compatible driver	Power supply voltage [V]
-	Without driver	
A1	LECSA1-S□	100 to 120
A2	LECSA2-S□	200 to 230
B1	LECSB1-S□	100 to 120
B2	LECSB2-S□	200 to 230
C1	LECSC1-S□	100 to 120
C2	LECSC2-S□	200 to 230
S1	LECSS1-S□	100 to 120
S2	LECSS2-S□	200 to 230
32	LECSS2-T□	200 to 240

\*1 When a driver type is selected, a cable is included. Select the cable type and cable length.

Example) S2S2: Standard cable (2 m) + Driver (LECSS2)

: Standard cable (2 m) : Without cable and driver

\* For auto switches, refer to page 176.

A ...... Table Ottonia Table

Applicable Stroke Table •: Standard												
Stroke Model	30	50	100	150	200	250	300	350	400	450	500	Manufacturable stroke range [mm]
LEY25	•	•	•	•	•	•	•	•	•	-	_	15 to 400
LFV32												20 to 500

Please consult with SMC for non-standard strokes as they are produced as special orders.

163



# Specifications: LECSA/LECSB/LECSC/LECSS

Model				LEY25S <sub>6</sub> <sup>2</sup> /1	76-X5 /LEY25	DS <sub>6</sub> <sup>2</sup> /T6-X5	LEY32S <sub>7</sub> /	Т7-Х5 (Тор	mounting)	LEY32	LEY32DS <sub>7</sub> <sup>3</sup> /T7-X5 (In-line)		
	Work load	Horizon	ıtal*1	18	50	50	30	60	60	30	60	60	
	[kg]	Vertical*	:8	8	16	30	9	19	37	12	24	46	
	Force [N]*	<sup>2</sup> (Set value: 1	5 to 30%)*15	65 to 131	127 to 255	242 to 485	79 to 157	154 to 308	294 to 588	98 to 197	192 to 385	368 to 736	
	Max. Stroke range	Chualca	Up to 300	900	450	225	1200	600	300	1000	500	250	
		d	305 to 400	600	300	150	1200	600	300	1000	500	250	
က္ခ	[mm/s]*3	Ū	405 to 500	_	_	_	800	400	200	640	320	160	
specifications	Pushing s	speed [mm/s	]*4		35 or less			30 or less			30 or less		
ati	Max. accele	ration/decelera	ntion [mm/s²]		5000				50	00			
lij	Positionii	ng	Basic type					±0.02					
မ	repeatabi	lity [mm]	High-precision type					±0.01					
Sp	Last mati	ion [mm]*5	Basic type					0.1 or less					
5	LUST IIIUTI	ion [iiiii]	High-precision type					0.05 or less					
nat	Lead [mm			12	6	3	20	10	5	16	8	4	
Actuator		ration resista	nce [m/s²]*6		50/20 50/20								
⋖	Actuation				rew + Belt/Ba		Ball screw + Belt [1.25:1] Ball screw						
	Guide type			Sliding bushing (Piston rod) Sliding bushing (Piston rod)									
	Enclosure			IP65 equivalent									
		temperature			5 to 40		5 to 40						
	. ,	g humidity ra	inge [%RH]	90 or less (No condensation) 90 or less (No condensation)									
		tion option		May be required depending on speed and work load (Refer to pages 45 and 46.)									
ဟ		tput/Size		100 W/□40 200 W/□60									
S .	Motor typ	ре		AC servo motor (100/200 VAC) AC servo motor (100/200 VAC)									
specifications	Encoder			Motor type S2, S3: Incremental 17-bit encoder (Resolution: 131072 p/rev) Motor type S6, S7: Absolute 18-bit encoder (Resolution: 262144 p/rev) Motor type T6, T7: Absolute 22-bit encoder (Resolution: 4194304 p/rev)									
sp	Power		Horizontal		45			65			65		
<u>.</u> 2	consump	tion [W]*9	Vertical		145			175			175		
Electric		er consumption			2			2			2		
	when operati	<b>v</b> · · ·	Vertical		8			8		8			
		neous power cons	sumption [W]*11		445			724			724		
iit	Type*12							-magnetizing					
ock unit	Holding f			131	255	485	157	308	588	197	385	736	
Loc		sumption [W	] at 20°C*13	6.3 7.9 7.9									
ds	Rated vol	tage [V]		24 VDC -00 %									

- \*1 This is the maximum value of the horizontal work load. An external guide is necessary to support the load. The actual work load changes according to the condition of the external guide. Confirm the load using the actual device.
- \*2 The force setting range (set values for the driver) for the force control with the torque control mode Set it with reference to "Force Conversion Graph" on pages 45 and 46. When the control equivalent to the pushing operation of the controller LECP6 series is performed, combine the Simple Motion module (manufactured by Mitsubishi Electric Corporation) which has a pushing operation function.
- \*3 The allowable speed changes according to the stroke.
- \*4 The allowable collision speed for collision with the workpiece with the torque control mode
- \*5 A reference value for correcting an error in reciprocal operation
- \*6 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.) Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)
- \*7 Cannot be used in an environment where oil such as cutting oil splashes or it is constantly exposed to water Take appropriate protective measures. For details on enclosure, refer to "Enclosure" on page 188.
- \*8 When mounting vertically and using the product facing upwards in an environment where water is present, take necessary measures to prevent water from splashing on the rod cover, because water will accumulate on the rod seal due to the structure of the product.
- \*9 The power consumption (including the driver) is for when the actuator is operating.
- \*10 The standby power consumption when operating (including the driver) is for when the actuator is stopped in the set position during the operation.
- \*11 The maximum instantaneous power consumption (including the driver) is for when the actuator is operating.
- \*12 Only when motor option "With lock" is selected
- \*13 For an actuator with lock, add the power consumption for the lock.
- \*14 The resolution will change depending on the driver type.
- \*15 For motor type T6 and T7, the set value is from 12 to 24 %.

#### Weight

### Product Weight

FIOU	uct weight																					
	Series		LEY2	25S <sub>6</sub> /T	6-X5 (I	Motor n	nountir	ng posi	tion: To	p mou	nting)	LE'	Y32S	<sup>3</sup> / <b>T7-)</b>	<b>(</b> 5 (Mc	otor m	ounti	ng pos	sition:	Top r	nount	ing)
	Stroke [mm]		30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500
5 0	Incremental en	coder	1.31	1.38	1.55	1.81	1.99	2.16	2.34	2.51	2.69	2.42	2.53	2.82	3.29	3.57	3.85	4.14	4.42	4.70	4.98	5.26
Mote	Absolute	S6/S7	1.37	1.44	1.61	1.87	2.05	2.22	2.40	2.57	2.75	2.36	2.47	2.76	3.23	3.51	3.79	4.08	4.36	4.64	4.92	5.20
≥ ₽	encoder	T6/T7	1.4	1.5	1.6	1.9	2.0	2.2	2.4	2.6	2.7	2.3	2.4	2.7	3.2	3.5	3.8	4.1	4.3	4.6	4.9	5.2


	Series		LEY2	25DS <sub>6</sub>	/T6-X	5 (Mo	tor mo	unting	g posit	ion: Ir	n-line)	L	EY32	2DS <sub>7</sub> /	/T7-X	5 (Mot	or mo	untin	g posi	tion: I	n-line	)
	Stroke [mm]		30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500
5 0	Incremental en	coder	1.34	1.41	1.58	1.84	2.02	2.19	2.37	2.54	2.72	2.44	2.55	2.84	3.31	3.59	3.87	4.16	4.44	4.72	5.00	5.28
Moto	Absolute	S6/S7	1.40	1.47	1.64	1.90	2.08	2.25	2.43	2.60	2.78	2.38	2.49	2.78	3.25	3.53	3.81	4.10	4.38	4.66	4.94	5.22
≥ ₽	encoder	T6/T7	1.4	1.5	1.6	1.9	2.1	2.2	2.4	2.6	2.8	2.4	2.5	2.8	3.2	3.5	3.8	4.1	4.4	4.6	4.9	5.2

<b>Additional Weigh</b>	t		[kg
	Size	25	32
Lock	Incremental encoder	0.20	0.40
LOCK	Absolute encoder	0.30	0.66
Rod end male thread	Male thread	0.03	0.03
nou enu maie inreau	Nut	0.02	0.02
Foot bracket (2 se	ts including mounting bolt)	0.08	0.14
Rod flange (includ	ing mounting bolt)	0.17	0.20
Head flange (inclu	ding mounting bolt)	0.17	0.20
Double clevis (including	pin, retaining ring, and mounting bolt)	0.16	0.22





# Construction

# Motor top mounting type: LEY<sub>32</sub><sup>25</sup>



# In-line motor type: $LEY_{32}^{25}D$





#### **Component Parts**

No.	Description	Material	Note
1	Body	Aluminium alloy	Anodised
2	Ball screw shaft	Alloy steel	
3	Ball screw nut	Synthetic resin/Alloy steel	
4	Piston	Aluminium alloy	
5	Piston rod	Stainless steel	Hard chrome plating
6	Rod cover	Aluminium alloy	
7	Bearing holder	Aluminium alloy	
8	Rotation stopper	POM	
9	Socket	Free cutting carbon steel	Nickel plating
10	Connected shaft	Free cutting carbon steel	Nickel plating
11	Bushing	Bearing alloy	
12	Bearing	_	
13	Return box	Aluminium die-cast	Coating
14	Return plate	Aluminium die-cast	Coating
15	Magnet	_	
16	Wear ring holder	Stainless steel	Stroke 101 mm or more
17	Wear ring	POM	Stroke 101 mm or more

No.	Description	Material	Note
18	Screw shaft pulley	Aluminium alloy	
19	Motor pulley	Aluminium alloy	
20	Belt	_	
21	Parallel pin	Stainless steel	
22	Scraper	Nylon	
23	Retaining ring	Steel for spring	Phosphate coated
24	Motor adapter	Aluminium alloy	Coating
25	Motor	_	
26	Lube-retainer	Felt	
27	O-ring	NBR	
28	Gasket	NBR	
29	O-ring	NBR	
30	Motor block	Aluminium alloy	Coating
31	Hub	Aluminium alloy	
32	Spider	Urethane	
33	Socket (Male thread)	Free cutting carbon steel	Nickel plating
34	Nut	Alloy steel	Trivalent chromated

#### Replacement Parts (Motor top mounting only)/Belt

No.	Size	Order no.
20	25	LE-D-2-2
20	32	LE-D-2-4

#### **Replacement Parts/Grease Pack**

Applied portion	Order no.
Piston rod	GR-S-010 (10 g) GR-S-020 (20 g)

Apply grease on the piston rod periodically.
 Grease should be applied at 1 million cycles or 200 km, whichever comes first.




LECA6

AC Servo Motor

# Electric Actuator/Rod Type LEY-X5 Series AC Servo Motor Dust-tight/Water-jet-proof (IP65 Equivalent)

# **Dimensions**

Motor top mounting type: LEY<sub>32</sub><sup>25</sup>



							,	,													[mm]
Size	Stroke range [mm]	Α	В	С	D	ЕН	EV	н		J	K	L	M	<b>O</b> 1	R	PA	РВ	V	s	т	U
25	15 to 100	130.5	116	13	20	44	45.5	M8 x	1.05	24	17	14.5	34	M5 x 0.8	3 8	15.4	8.2	40	46	92	4
25	101 to 400	155.5	141	13	20	44	45.5	IVIO X	1.25	24	17	14.5	34	IVIO X U.G	0	15.4	0.2	40	40	92	'
32	20 to 100	148.5	130	13	25	51	56.5	M8 x	1 05	31	22	18.5	40	M6 x 1.0	10	15.4	8.2	60	60	118	4
32	101 to 500	178.5	160	13	25	31	30.3	IVIO X	1.25	31	22	10.5	40	IVIO X 1.0	10	15.4	0.2	00	00	110	'
				Incr	ement	al enco	der			Abso	lute er	coder	[S6/S	7]		Absolu	ite enc	oder [7	6/T7]		
Size	Stroke range	PC	Wit	hout lo	ck	٧	Vith loc	k	W	ithout	lock		With I	ock	Wit	hout lo	ck	V	ith loc	k	Υ
	[mm]		W	Х	Z	W	Х	Z	W	X	Z	W	X	Z	W	Х	Z	W	Х	Z	
	451 400																				

	Ctroke renge			11101	CITICITE	ai ericc	Juei			ADSOIL	ate ent	Joues [	30/07]			ADSOIL	ate ent	Jouei [	10/1/]		i e
Size	Stroke range [mm]	PC	Wi	thout lo	ock	V	Vith loc	k	Wi	thout lo	ock	V	Vith loc	k	Wi	thout lo	ck	V	Vith loc	k	Υ
	[111111]		W	X	Z	W	X	Z	W	X	Z	W	X	Z	W	X	Z	W	X	Z	
25	15 to 100	15.4	87	120	14.1	122.0	156.9	15.8	00.4	115.4	1/11	100 5	1565	15.8	00.4	115.4	14.1	100	156	15.8	51
25	101 to 400	15.4	07	120	14.1	123.9	150.9	13.6	02.4	115.4	14.1	123.5	130.3	15.6	02.4	115.4	14.1	123	150	15.6	31
32	20 to 100	15.9	00 2	120.2	171	1160	156.8	17 1	76.6	116.6	171	1161	156 1	171	76.6	1166	171	110 /	152 /	17.1	61
32	101 to 500	15.9	00.2	120.2	17.1	110.0	150.6	17.1	70.0	110.0	17.1	110.1	130.1	17.1	70.0	110.0	17.1	113.4	155.4	17.1	01

Body	<b>Bottom T</b>	apped									[mm]
Size	Stroke range [mm]	MA	МВ	МС	MD	МН	ML	МО	MR	XA	ХВ
	15 to 39			24	32		50				
	40 to 100			42	41		30				
25	101 to 124	20	46	42	41	29		M5 x 0.8	6.5	4	5
	125 to 200			59	49.5		75				
	201 to 400			76	58						
	20 to 39			22	36		50				
	40 to 100			36	43						
32	101 to 124	25	55	30	40	30		M6 x 1	8.5	5	6
	125 to 200			53	51.5		80				
	201 to 500			70	60						

<sup>\*1</sup> Range within which the rod can move Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.

For the rod end male thread, refer to page 77. For the mounting bracket dimensions, refer to page 97.




<sup>\*2</sup> The direction of rod end width across flats ( $\square K$ ) differs depending on the products.

<sup>\*3</sup> The vent hole is the port for releasing to atmosphere. Do not apply pressure to this hole. Attach tubing to the vent hole and place the end of the tubing so it is not exposed to dust or water.

# **Dimensions**

# In-line motor type: LEY<sub>32</sub>D



																					[mm]
	Chualta namana		Inc	cremer	ntal end	coder			Absolu	ıte enc	oder [S	6/S7]			Abs	solute	e enc	oder [T	6/T7]		
Size	Stroke range	Wi	thout I	ock		With lock		Wit	hout lo	ck	V	Vith loc	ck	V	Vithou	t lock	(	W	ith lock	(	В
	[mm]	Α	W	Z	Α	W	Z	Α	W	Z	Α	W	Z	Α	VE	3 \	VC	Α	VB	VC	
25	15 to 100	238	87	14.6	274.	9 123.9	16.3	233.4	82.4	14.6	274.5	123.5	16.3	233.4	82.	4 4	4.6	274	123	16.3	136.5
25	101 to 400	263	07	14.0	299.	9 123.9	10.3	258.4	02.4	14.0	299.5	123.5	10.3	258.4	1 02.	4   1	4.6	299	123	16.3	161.5
32	20 to 100	262.7	88.2	17.1	291.	3 116.8	17.1	251.1	76.6	17.1	290.6	116.1	17.1	251.	76.	6 1	7.1	287.9	110 4	17.1	156
32	101 to 500	292.7	00.2	17.1	321.	3 110.0	17.1	281.1	70.0	17.1	320.6	110.1	17.1	281.	1 /6.	0 1	7.1	317.9	113.4	17.1	186
Size	Stroke range	С	D	EH	EV	н	J	ΙK	L	М	0	1	R	PA	РВ	V	S	Т	U	PC	Y
	[mm]																				
	15 to 100																1	40.	T		
25	101 to 400	13	20	44	45.5	M8 x 1.2	5 24	4   17	14.5	34	M5 x	8.0	8	15.4	8.2	40	45	46.5	1.5	15.9	71.5
	20 to 100	40	0.5	F.4	50.5	140 4.0	-   0.		40.5	40	140	4.0	40	45.4	0.0	00		0.4		45.0	07
32	101 to 500	13	25	51	56.5	M8 x 1.2	5   3	1 22	18.5	40	M6 x	1.0	10	15.4	8.2	60	60	61	1	15.9	87

Body	<b>Bottom T</b>	apped								[mm]
Size	Stroke range [mm]	MA	МС	MD	МН	ML	МО	MR	XA	ХВ
	15 to 39		24	32		50				
	40 to 100		42	41		50				
25	101 to 124	20	42	41	29		M5 x 0.8	6.5	4	5
	125 to 200		59	49.5		75				
	201 to 400		76	58						
	20 to 39		22	36		50				
	40 to 100		36	43		30				
32	101 to 124	25	30	40	30		M6 x 1	8.5	5	6
	125 to 200		53	51.5		80				
	201 to 500		70	60						

<sup>\*1</sup> Range within which the rod can move Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.

For the rod end male thread, refer to page 77. For the mounting bracket dimensions, refer to page 97.



<sup>\*2</sup> The direction of rod end width across flats (□K) differs depending on the products.
\*3 The vent hole is the port for releasing to atmosphere. Do not apply pressure to this hole. Attach tubing to the vent hole and place the end of the tubing so it is not exposed to dust or water.

Specific Product Precautions

# **Electric Actuator/** Rod Type Dust-tight/Water-jet-proof (IP65 Equivalent)

LEY-X5 (Made to Order) Series LEY25, 32


Refer to page 48 for model selection. || Size 63 is available by selecting option P. Refer to page 87.





LECS□ Series ▶ p. 163

# **How to Order**



# Accuracy

Accuracy					
_	Basic type				
Н	High-precision type				

2	Size	9
2	5	

25 32

3	Mo	tor mounting pos	itior
_	_	Top mounting	

In-line

# 4 Motor type

	10. 1)   0			
Symbol	Туре	Output [W]	Size	Compatible driver
V6*1	AC servo motor	100	25	LECYM2-V5 LECYU2-V5
V7	(Absolute encoder)	200	32	LECYM2-V7 LECYU2-V7

<sup>\*1</sup> For motor type V6, the compatible driver part number suffix is V5.

#### Lead [mm]

Symbol	LEY25	LEY32
Α	12	16 (20)
В	6	8 (10)
С	3	4 (5)

\* The values shown in ( ) are the leads for the top mounting type. (Equivalent leads which include the pulley ratio [1.25:1])

# 6 Stroke [mm]

O Stroke [mm]					
30	30				
to	to				
500	500				

For details, refer to the applicable stroke table below.

# **Motor option**

	101 0 0 11011
_	Without option
В	With lock

\* When "With lock" is selected for the top mounting type, the motor body will stick out from the end of the body for size 25 with strokes of 30 mm or less.

Check for interference with workpieces before selecting a model.



#### 8 Rod end thread

_	Rod end female thread
М	Rod end male thread (1 rod end nut is included.)

# nlicable Stroke Table

Applicable Stroke Table •: Standard												
Stroke [mm]	30	50	100	150	200	250	300	350	400	450	500	Manufacturable stroke range
LEY25	•	•	•	•	•	•	•	•	•	_	_	15 to 400
LEY32	•	•	•	•	•	•	•	•	•	•	•	20 to 500

Please consult with SMC for non-standard strokes as they are produced as special orders.

AC Servo Motor

Electric Actuator/Rod Type LEY-X5 Series

AC Servo Motor Size 25, 32





Motor mounting position: Top mounting

Motor mounting position: In-line

9 Mounting\*1

<u> </u>	ounting				
Cumbal	Typo	Motor mounting position			
Symbol	Type	Top mounting	In-line		
_	Ends tapped/ Body bottom tapped*2	•	•		
L	Foot	•	_		
F	Rod flange*2	●*3	•		
G	Head flange*2	●*4	_		

- \*1 The mounting bracket is shipped together with the product but does not come assembled.
- \*2 For the horizontal cantilever mounting of the ends tapped, rod flange, or head flange types, use the actuator within the following stroke range.
  - · LEY25: 200 mm or less · LEY32: 100 mm or less
- \*3 The rod flange type is not available for the LEY25 with a 30 mm stroke and motor option "With lock."
- \*4 The head flange type is not available for the LEY32.

Cable type\*1

_	Without cable
S	Standard cable
R	Robotic cable (Flexible cable)

\*1 The motor and encoder cables are included. The motor cable for lock option is included when the motor with lock option is selected.

Cable length [m]\*1

• casic iongin [m]					
	_	Without cable			
	3	3			
	5	5			
	Α	10			
	С	20			

The length of the motor and encoder cables are the same. (For with lock)

12 Driver type

_	. 71.	
	Compatible driver	Power supply voltage [V]
_	Without driver	_
M2	LECYM2-V□	200 to 230
U2	LECYU2-V□	200 to 230


When a driver type is selected, a cable is included. Select the cable type and cable length.

I/O cable length [m]\*1

	3 L 1
	Without cable
Н	Without cable (Connector only)
1	1.5

When "Without driver" is selected for driver type, only "-: Without cable" can be selected. Refer to page 278 if I/O cable is required. (Options are shown on page 278.)

**Compatible Driver** 





# Specifications: LECY

		Model		LEY25V	6-X5/LEY2	5DV6-X5	LEY32V	7-X5 (Top n	nounting)	LEY3	2DV7-X5 (I	n-line)	
	Work los	al Fleat	Horizontal*1	18	50	50	30	60	60	30	60	60	
	Work loa	a [kg]	Vertical*9	8	16	30	9	19	37	12	24	46	
	Force [N]	*2 (Set value:	45 to 90 %)	65 to 131	127 to 255	242 to 485	79 to 157	154 to 308	294 to 588	98 to 197	192 to 385	368 to 736	
	Max.*3	Stroke	Up to 300	900	450	225	1200	600	300	1000	500	250	
	speed	range	305 to 400	600	300	150	1200	000	300	1000	300	250	
	[mm/s]	range	405 to 500	_	_	_	800	400	200	640	320	160	
ns	Pushing	speed [mm/	/s]* <sup>4</sup>		35 or less			30 or less			30 or less		
specifications	Max. accele	eration/decelera	ation [mm/s <sup>2</sup> ]		5000				50	00			
ca	Positioni	ing	Basic type		±0.02				±0.	.02			
15	repeatab	ility [mm]	High-precision type		±0.01				±0.	.01			
be	Lost mot	tion [mm]*5	Basic type		0.1 or less				0.1 o	r less			
			mign-precision type		0.05 or less				0.05 c				
Actuator		ı] (including p		12	6	3	20*6	10*6	5* <sup>6</sup>	16	8	4	
Ĕ	Impact/Vib	ration resista	nce [m/s <sup>2</sup> ]*7		50/20				50/	20			
Ac	Actuatio	n type		Ball screw + Be	elt (LEY□)/Ball s	screw (LEY□D)	Ball so	crew + Belt [	1.25:1]		Ball screw		
	Guide ty	pe		Sliding	bushing (Pis	ton rod)			liding bushin	g (Piston ro	d)		
	Enclosu						IP65 equivalent						
		j temperature			5 to 40		5 to 40						
		g humidity ra	<u> </u>		ss (No conde	,	90 or less (No condensation)						
	Conditions 1		Horizontal		Not required	l	Not required						
		ve resistor" [kg]	Vertical		6 or more		4 or more						
ns.		tput/Size			100 W/□40				200 V				
specifications	Motor ty			AC ser	vo motor (20				C servo mo		C)		
Ę	Encoder					Absolute	20-bit enco	oder (Resolu	tion: 104857	'6 p/rev)			
ec.	Power		Horizontal		45			65			65		
		ion [W]*11	Vertical		145			175			175		
댪	Standby pov	ver consumption			2			2			2		
Electric	when operat		Vertical		8			8			8		
Ш	Max. instanta	neous power consu	umption [W]*13		445			724			724		
iit	Type*14				ı			magnetising					
k unit	Holding			131	255	485	35 157 308 588 197 385					736	
Lock		nsumption [W	] at 20 °C*15	C*15 5.5 6 6									
SD	Rated vo	Itage [V]						24 VDC +10 %	•				

- \*1 This is the maximum value of the horizontal work load. An external guide is necessary to support the load. The actual work load changes according to the condition of the external guide. Confirm the load using the actual device.
- \*2 The force setting range (set values for the driver) for the force control with the torque control mode
  - Set it with reference to "Force Conversion Graph (Guide)" on page 52.
- \*3 The allowable speed changes according to the stroke.
- \*4 The allowable collision speed for collision with the workpiece with the torque control mode
- $*5\,$  A reference value for correcting an error in reciprocal operation
- \*6 Equivalent leads which include the pulley ratio [1.25:1]
- \*7 Impact resistance: No malfunction occurred when the actuator was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)

Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. The test was performed in both an axial direction and a perpendicular direction to the lead screw. (The test was performed with the actuator in the initial state.)

- \*8 Cannot be used in an environment where oil such as cutting oil splashes or it is constantly exposed to water Take appropriate protective measures. For details on enclosure, refer to "Enclosure" on page 188.
- \*9 When mounting vertically and using the product facing upwards in an environment where water is present, take necessary measures to prevent water from splashing on the rod cover, because water will accumulate on the rod seal due to the structure of the product.
- \*10 The work load conditions which require "Regenerative resistor" when operating at the maximum speed (Duty ratio: 100 %)

  Order the regenerative resistor constraint. For details, refer to "Conditions for Regenerative
  - Order the regenerative resistor separately. For details, refer to "Conditions for Regenerative Resistor (Guide)" on pages 51 and 52.
- \*11 The power consumption (including the driver) is for when the actuator is operating.
- \*12 The standby power consumption when operating (including the driver) is for when the actuator is stopped in the set position during the operation.
- \*13 The maximum instantaneous power consumption (including the driver) is for when the actuator is operating.
- \*14 Only when motor option "With lock" is selected
- \*15 For an actuator with lock, add the power consumption for the lock.

#### Weight

Product Weight																				[kg]
Series	LEY	25V6	(Motor	mour	nting p	ositio	n: Top	mou	nting)	L	EY32	2V7 (I	Motor	mour	ting p	ositio	n: To	p moı	unting	1)
Stroke [mm]	30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500
Weight [kg]	1.2	1.3	1.6	1.7	1.9	2.1	2.2	2.4	2.6	2.3	2.4	2.7	3.2	3.5	3.8	4.0	4.3	4.6	4.9	5.2
Series	LE	Y25D	V6 (N	lotor r	nount	ing p	ositio	n: In-l	ine)		LE'	Y32D	V7 (N	lotor r	nount	ing p	ositio	n: In-li	ine)	
Stroke [mm]	30	50	100	150	200	250	300	350	400	30	50	100	150	200	250	300	350	400	450	500
Weight [kg]	1.2	1.3	1.5	1.7	1.9	2.1	2.3	2.4	2.6	2.3	2.4	2.7	3.2	3.5	3.8	4.1	4.3	4.6	4.9	5.2

Additional Weigh	t		[kg
	Size	25	32
Lock		0.30	0.60
Rod end male thread	Male thread	0.03	0.03
nou enu male umeau	Nut	0.02	0.02
Foot bracket (2 se	ts including mounting bolt)	0.08	0.14
Rod flange (includ	ing mounting bolt)	0.17	0.20
Head flange (inclu	ding mounting bolt)	0.17	0.20



LEYG

AC Servo Motor


Electric Actuator/Rod Type LEY-X5 Series

AC Servo Motor Dust-tight/Water-jet-proof (IP65 Equivalent)

EΗ

#### **Dimensions**

# Motor top mounting type: LEY<sub>32</sub><sup>25</sup>



																		[mm]
Size	Stroke range [mm]	A	В	С	D	ЕН	EV	ŀ	1	J	K	L	M	<b>O</b> 1	R	PA	РВ	٧
25	15 to 100	130.5	116	13	20	44	45.5	M8 x	1 25	24	17	14.5	34	M5 x 0.8	8	15.4	8.2	40
25	101 to 400	155.5	141	13	20	44	45.5	IVIO A	1.23	24	17	14.5	34	IVIS X 0.0	0	13.4	0.2	40
32	20 to 100	148.5	130	13	25	51	56.5	M8 x	1.05	31	22	18.5	40	M6 x 1.0	10	15.4	8.2	60
32	101 to 500	178.5	160	13	25	51	36.3	IVIO X	1.25	31	22	10.5	40	IVIO X 1.0	10	15.4	0.2	60
01	Stroke		_			W	ithout lo	ck	١	Nith loc	k	v						
Size	range [mm]	S	ı	U	PC	W	Х	Z	W	Х	Z	Y						
	15 to 100																	

A + Stroke

	10110300	170.5	100									
Size	Stroke	6	S T		РС	W	ithout lo	ck	١ ١	Vith loc	k	v
Size	range [mm]	3	'	U	PC	W	Х	Z	W	X	Z	ı
25	15 to 100	46	92	-1	15.4	82.5	115.5	11	127.5	160.5	11	51
25	101 to 400	40	92	'	15.4	02.5	115.5	11	127.5	100.5	11	31
32	20 to 100	60	118	-1	15.9	80	120	14	120	160	14	61
32	101 to 500	00	110	'	15.9	80	120	14	120	100	14	01

Body Bottom Tapped [mm]														
Size	Stroke range [mm]	MA	МВ	МС	MD	МН	ML	МО	MR	XA	ХВ			
	15 to 39			24	32		50							
	40 to 100			42	41		50							
25	101 to 124	20	46	42	41	29		M5 x 0.8	6.5	4	5			
	125 to 200			59	49.5		75							
	201 to 400			76	58									
	20 to 39			22	36		50							
	40 to 100			36	43		30							
32	101 to 124	25	55	30	43	30		M6 x 1	8.5	5	6			
	125 to 200			53	51.5		80							
	201 to 500			70	60									

<sup>\*1</sup> Range within which the rod can move Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around

For the rod end male thread, refer to page 77. For the mounting bracket dimensions, refer to page 97.




<sup>\*2</sup> The direction of rod end width across flats (□K) differs depending on the products.

<sup>\*3</sup> The vent hole is the port for releasing to atmosphere. Do not apply pressure to this hole. Attach tubing to the vent hole and place the end of the tubing so it is not exposed to dust or water.

# **Dimensions**

# In-line motor type: LEY<sub>32</sub>D



												[mm]						
Size	Stroke	Wi	ithout lo	ck	V	Vith loc	k	В	С	D	EH	EV						
SIZE	range [mm]	Α	W	Z	Α	W	Z	0	C	D	LII	LV						
25	15 to 100	233.5	82.5	11.5	278.5	127.5	11.5	136.5	13	20	44	45.5						
25	101 to 400	258.5	02.5	11.5	303.5	127.5	11.5	161.5	13	20	44	45.5						
32	20 to 100	254.5	80	14	294.5	120	14	156	13	25	51	56.5						
32	101 to 500	284.5	00	14	324.5	120	14	186	13	25	51	36.3						
Size	Stroke range [mm]	ŀ	1	J	К	L	М	0	1	R	PA	РВ	٧	s	т	U	РС	Υ
Size		<b>Н</b>		<b>J</b> 24	<b>K</b>	<b>L</b> 14.5	<b>M</b>	<b>O</b> M5 x		<b>R</b> 8	<b>PA</b> 15.4	<b>PB</b> 8.2	<b>V</b>	<b>S</b>	<b>T</b> 46.5	1.5	<b>PC</b> 15.9	<b>Y</b> 71.5

Body	Body Bottom Tapped [mm]														
Size	Stroke range [mm]	MA	МС	MD	МН	ML	МО	MR	XA	ХВ					
	15 to 39		24	32		50									
	40 to 100		42	41		30									
25	101 to 124	20	42	41	29		M5 x 0.8	6.5	4	5					
	125 to 200		59	59 49.5 75		75									
	201 to 400		76	58											
	20 to 39		22	36		50									
	40 to 100		36	43		50									
32	101 to 124	25	30	40	30		M6 x 1	8.5	5	6					
	125 to 200		53	51.5		80									
	201 to 500		70	60											

<sup>\*1</sup> Range within which the rod can move Make sure workpieces mounted on the rod do not interfere with the workpieces and facilities around the rod.

For the rod end male thread, refer to page 77. For the mounting bracket dimensions, refer to page 97.



<sup>\*2</sup> The direction of rod end width across flats (□K) differs depending on the products.

<sup>\*3</sup> The vent hole is the port for releasing to atmosphere. Do not apply pressure to this hole.

Attach tubing to the vent hole and place the end of the tubing so it is not exposed to dust or water.


Specific Product Precautions


**SMC** 

# LEY-X5 Series Auto Switch Mounting

# **Proper Auto Switch Mounting Position**

Applicable auto switches: D-M9□A(V)






					-
г	-	_	×		٠1
- 1	П	П	ı	ı	н

			Auto swite	ch position		Return to origin	Operating range
Size	Stroke range	Mounting:	Left facing	Mounting: I	Right facing	distance	Operating range
		Α	В	С	D	E	_
25	15 to 100	27	62.5	39	50.5	(0)	4.2
25	105 to 400	52	02.5	64	50.5	(2)	4.2
32	20 to 100	30.5	OF F	42.5	53.5	(0)	4.0
32	105 to 500	90.5	85.5	102.5	53.5	(2)	4.9

- \*1 Figures in the table above are used as a reference when mounting the auto switches for stroke end detection. Adjust the auto switch after confirming the operating condition in the actual setting.
- \*2 Switches cannot be mounted on the motor mounting side surface.
- \*3 For the LEYG with a guide, switches cannot be mounted on the guide attachment side (rod side).
- \*4 Since the operating range is provided as a guideline including hysteresis, it cannot be guaranteed (assuming approximately ±30 % dispersion). It may change substantially depending on the ambient environment.

# **Auto Switch Mounting**



# Auto Switch Mounting Screw

 Tightening Torque
 N⋅m

 Auto switch model
 Tightening torque

 D-M9□A(V)
 0.05 to 0.10

 When tightening the auto switch mounting screw (included with auto switch), use a watchmaker's screwdriver with a handle diameter of about 5 to 6 mm.



[mm]

AC Servo Motor

# **Water Resistant 2-Colour Indicator** Solid State Auto Switch: Direct Mounting Type D-M9NA(V)/D-M9PA(V)/D-M9BA(V) ( $\epsilon$

#### Grommet

- Water (coolant) resistant type
- 2-wire load current is reduced (2.5 to 40 mA).
- The proper operating range can be determined by the colour of the light. (Red  $\rightarrow$  Green  $\leftarrow$  Red)
- Using flexible cable as standard spec.



#### **∆**Caution

#### **Precautions**

Fix the auto switch with the existing screw installed on the auto switch body. The auto switch may be damaged if a screw other than the one supplied is used.

Please consult with SMC if using coolant liquid other than water based solution.

# Weight

[g]

	Auto switch model		D-M9NA(V) D-M9PA(V)	D-M9BA(V)
		0.5 m ( <del></del> )	8	7
١	Lead wire	1 m ( <b>M</b> )	14	13
	length	3 m ( <b>L</b> )	41	38
	.cgui	5 m ( <b>Z</b> )	68	63

# **Auto Switch Specifications**

PLC: Programmable Logic Controller


D-M9□A, D-M9	D-M9□A, D-M9□AV (With indicator light)						
Auto switch model	D-M9NA	D-M9NAV	D-M9PA	D-M9PAV	D-M9BA	D-M9BAV	
Electrical entry direction	In-line	Perpendicular	In-line	Perpendicular	In-line Perpendicular		
Wiring type		3-v	vire		2-v	2-wire	
Output type	N	PN	PI	NP	_	_	
Applicable load		IC circuit, Relay, PLC			24 VDC relay, PLC		
Power supply voltage	oly voltage 5, 1		, 12, 24 VDC (4.5 to 28 V)			_	
<b>Current consumption</b>	10 mA or less		_				
Load voltage	28 VDC or less —		24 VDC (10 to 28 VDC)				
Load current		40 mA	or less		2.5 to 40 mA		
Internal voltage drop	0.8 V or l	ess at 10 mA	(2 V or less	at 40 mA)	4 V or less		
Leakage current	100 μA or less at 24 VDC 0.8 m			0.8 mA	or less		
Indicator light	Operating range Red LED illumin Proper operating range Green LE					S.	
Standard	CE marking (EMC directive/RoHS directive)						

Oilproof Flexible Heavy-duty Lead Wire Specifications


Auto switch model		D-M9NA□   D-M9NAV□   D-M9PA□   D-M9PAV□   D-M9BA□   D-	M9BAV□
Sheath	Outside diameter [mm]	2.6	
Insulator	Number of cores	3 cores (Brown/Blue/Black) 2 cores (Brown	wn/Blue)
Insulator	Outside diameter [mm]	0.88	
Conductor	Effective area [mm²]	0.15	
Conductor	Strand diameter [mm]	0.05	
Minimum bend	ling radius [mm]	17	

- \* Refer to the **Web Catalogue** for solid state auto switch common specifications.
- \* Refer to the Web Catalogue for lead wire lengths.

# **Dimensions**







# **Electric Actuator/** Rod Type Secondary Battery Compatible

(RoHS)

**25A-LEY Series** LEY16, 25, 32, 40


Dust -tight/Water-jet-proof▶p. 151

**How to Order** 



Motor mounting position: Top/Parallel

Motor mounting position: In-line



# 1 Size

16	
25	
32	
40	

# 2 Motor mounting position

_	Top mounting
R	Right side parallel
L	Left side parallel
D	In-line

# **3** Motor type

Symbol	Tuno	Applicable size			Compatible	
Symbol	Type	LEY16	LEY25	LEY32/40	controll	er/driver
	Step motor (Servo/24 VDC)	•	•	•	LECP1 LECPA	JXCE1 JXC91 JXCP1 JXCD1 JXCL1
Α	Servo motor (24 VDC)	•	•	_	LE	CA6

#### 4 Lead [mm]

Symbol	LEY16	LEY25	LEY32/40
Α	10	12	16
В	5	6	8
С	2.5	3	4

# Rod end thread

_	Rod end female thread
М	Rod end male thread (1 rod end nut is included.)

#### 5 Stroke [mm]

30	30
to	to
500	500

\* For details, refer to the applicable stroke table below.

#### 6 Motor option\*2

_	Without option
С	With motor cover
W	With lock/motor cover

#### 8 Mounting\*5

Cumbal	Tyroo	Motor mounting position		
Symbol	Туре	Top/Parallel	In-line	
	Ends tapped/Body			
	bottom tapped*6			
L	Foot	•	_	
F	F Rod flange*6 G Head flange*6 D Double clevis*7		•	
G			_	
D			_	

#### Actuator cable type/length\*11

Standard cable [m]		
_	None	
S1	1.5*12	
S3	3*12	
S5	5*12	

Roboti	[m]		
R1	1.5	RA	10* <sup>10</sup>
R3	3	RB	15*10
R5	5	RC	20*10
R8	8*10		

#### Mounting Bracket Part Nos. for the 25A- Series\*4

Applicable size	Foot*3	Flange	Double clevis			
16	25-LEY-L016	25-LEY-F016	25-LEY-D016			
25	25-LEY-L025	25-LEY-F025	25-LEY-D025			
32, 40	25-LEY-L032	25-LEY-F032	25-LEY-D032			
Surface treatment	RAYDENT®	RAYDENT®	Coating (Size 16: Electroless nickel plating)			

Solid state auto switches should be ordered separately. For details on auto switches, refer to the Web Catalogue.

#### Applicable auto switches

D-M9N(V)-900, D-M9P(V)-900, D-M9B(V)-900 D-M9NW(V)-900, D-M9PW(V)-900, D-M9BW(V)-900

#### 


P	Applicable Stroke Table*  •: Standard												
١	Stroke [mm]	30	50	100	150	200	250	300	350	400	450	500	Manufacturable stroke range
	25A-LEY16	•	•		•	•	•	•				_	10 to 300
	25A-LEY25	•	•	•	•	•	•	•	•	•	_	_	15 to 400
	25A-LEY32/40	•	•							•	•		20 to 500

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

Electric Actuator/Rod Type 25A-LEY Series

Step Motor (Servo/24 VDC) Servo Motor (24 VDC) Secondary Battery Compatible

Series (For details, refer to page 179.)



# Controller/Driver type\*12

_	Without controller/driver					
6N	LECA6 NPI					
6P	(Step data input type)	PNP				
1N	LECP1*13	NPN				
1P	(Programless type)	PNP				
AN	LECPA*13 *15	NPN				
AP	(Pulse input type)	PNP				

# I/O cable length\*16, Communication plug

_	Without cable (Without communication plug connector)			
1	1.5 m			
3	3 m* <sup>17</sup>			
5	5 m* <sup>17</sup>			
S	Straight type communication plug connector			
T	T-branch type communication plug connector			

#### Controller/Driver mounting Screw mounting DIN rail\*18

# JXC Series (For details, refer to page 179.




Р

D

PROFINET

DeviceNet™

IO-Link



\*1 Please consult with SMC for non-standard strokes as they are produced as special orders.

For single axis

- When "With lock" or "With lock/motor cover" is selected for the top mounting and right/left side parallel types, the motor body will stick out from the end of the body for size 16/40 with strokes of 30 mm or less. Check for interference with workpieces before selecting a model.
- \*3 When ordering foot brackets, order 2 pieces per actuator.
- \*4 Parts belonging to each bracket are as follows.
  Foot, Flange: Body mounting bolt, Double clevis: Clevis pin, Type C
- retaining ring for axis, Body mounting bolt
  \*5 The mounting bracket is shipped together with the product but does not come assembled.
- \*6 For the horizontal cantilever mounting of the rod flange, head flange, or ends tapped types, use the actuator within the following stroke range. LEY25: 200 mm or less LEY32/40: 100 mm or less
- For the mounting of the double clevis type, use the actuator within the following stroke range LEY16: 100 mm or less LEY25: 200 mm or less LEY32/40: 200 mm or less
- \*8 The rod flange type is not available for the LEY 1 6/4 0 with a 30 mm stroke and motor option "With lock," "With lock/motor cover."

- \*9 The head flange type is not available for the LEY32/40.
- \*10 Produced upon receipt of order (Robotic cable only)
  \*11 The standard cable should only be used on fixed parts. or use on moving parts, select the robotic cable
- For details on controllers/drivers and compatible motors, refer to the
- compatible controller/driver on the next page. Only available for the motor type "Step motor"
- \*14 Not compliant with CE
- \*15 When pulse signals are open collector, order the current limiting resistor (LEC-PA-R-□) on page 220 separately.
  \*16 When "Without controller/driver" is selected for controller/driver types,
- \*16 When "without controller/driver" is selected for controller/driver types, I/O cable cannot be selected. Refer to page 1 9 9 (For LECA 6), page 213(For LECP1), or page 220 (For LECPA) if I/O cable is required.

  \*17 When "Pulse input type" is selected for controller/driver types, pulse input usable only with differential. Only 1.5 m cables usable with open collector

  \*18 The DIN rail is not included. Order it separately.

  \*19 Select "—" for anything other than DeviceNet™.

# 

#### [CE-compliant products]

① EMC compliance was tested by combining the electric actuator LEY series and the controller LEC/JXC series.

The EMC depends on the configuration of the customer's control panel and the relationship with other electrical equipment and wiring. Therefore, compliance with the EMC directive cannot be certified for SMC components incorporated into the customer's equipment under actual operating conditions. As a result, it is necessary for the customer to verify compliance with the EMC directive for the machinery and equipment as a whole.

2 For the servo motor (24 VDC) specification, EMC compliance was tested by installing a noise filter set (LEC-NFA). Refer to page 199 for the noise filter set. Refer to the LECA series Operation Manual for installation.

#### [UL-compliant products (For the LEC series)]


When compliance with UL is required, the electric actuator and controller/ driver should be used with a UL1310 Class 2 power supply.

#### The actuator and controller/driver are sold as a package.

Confirm that the combination of the controller/driver and actuator is correct.

#### <Check the following before use.>

- 1 Check the actuator label for the model number (after "25A-"). This number should match that of the controller/driver.
- 2 Check that the Parallel I/O configuration matches (NPN or PNP).



Refer to the Operation Manual for using the products. Please download it via our website, https://www.smc.eu



# **Compatible Controller/Driver**

# **LEC**□ Series

Туре	Step data input type	Programless type	Pulse input type	
Series	LECA6	LECP1	LECPA	
Features	Value (Step data) input Standard controller	Capable of setting up operation (step data) without using a PC or teaching box	Operation by pulse signals	
Compatible motor	Servo motor (24 VDC)	Step motor (Servo/24 VDC)		
Max. number of step data	64 points	14 points	_	
Power supply voltage				
Reference page	191	207	214	

# JXC□ Series

Туре	EtherCAT® direct input type	EtherNet/IP™ direct input type	PROFINET direct input type	DeviceNet <sup>TM</sup> direct input type	IO-Link direct input type			
Series	JXCE1	JXC91	JXCP1	JXCD1	JXCL1			
Features	EtherCAT® direct input	EtherNet/IP™ direct input	PROFINET direct input	DeviceNet™ direct input	IO-Link direct input			
Compatible motor	Step motor (Servo/24 VDC)							
Max. number of step data	64 points							
Power supply voltage	24 VDC							
Reference page			224		_			

Specific Product Precautions

## **Electric Actuator/** Rod Type Secondary Battery Compatible

25A-LEY Series LEY25, 32 Size


25, 32



LECY□ Series ▶ p. 183

Refer to page 41 for model selection.

#### How to Order



Accuracy

Basic type High-precision type

2 Size 32

Motor mounting position

_	Top mounting
R	Right side parallel
L	Left side parallel
D	In-line

Motor type

	motor type								
Symbol	Туре	Output [W]	Actuator size	Compatible driver*3	UL- compliant				
S2*1	AC servo motor	100	25	LECSA□-S1	_				
S3	(Incremental encoder)	200	32	LECSA□-S3	_				
S6*1	AC servo motor (Absolute encoder)	100	25	LECSB□-S5 LECSC□-S5 LECSS□-S5					
<b>S</b> 7		200	32	LECSB□-S7 LECSC□-S7 LECSS□-S7	_				
T6*2	AC servo motor	100	25	LECSS2-T5	•				
T7	(Absolute encoder)	200	32	LECSS2-T7	•				

5 Lead [mm]

Symbol	LEY25	LEY32*1		
Α	12	16 (20)		
В	6	8 (10)		
С	3	4 (5)		

to to 500 500 For details, refer to the applicable stroke table

6 Stroke [mm]

30

below.

- \*1 The values shown in ( ) are the leads for the size 32 top mounting. right/left side parallel types. (Equivalent leads which include the pulley ratio [1.25:1])
- \*1 For motor type S2 and S6, the compatible driver part number suffixes are S1 and S5 respectively.
- \*2 For motor type T6, the compatible driver part number suffix is T5.
- \*3 For details on the driver, refer to the Web Catalogue

✓ Motor option				
_	Without option			
В	With lock*1			

\*1 When "With lock" is selected for the top mounting and right/left side parallel types, the motor body will stick out from the end of the body for size 25 with strokes of 30 mm or less. Check for interference with workpieces before selecting a model.



#### 8 Rod end thread

_	Rod end female thread
М	Rod end male thread (1 rod end nut is included.)

## 9 Mounting\*1

Symbol	Typo	Motor mounting position			
Syllibol	Type	Top/Parallel	In-line		
	Ends tapped/ Body bottom tapped *2	•	•		
L	Foot		_		
F	Rod flange*2	*4			
G	Head flange*2	*5	_		
D	Double clevis*3		_		

- \*1 The mounting bracket is shipped together with the product but does not come assembled.
- \*2 For the horizontal cantilever mounting of the rod flange, head flange, or ends tapped types, use the actuator within the following stroke range.
  - · 25A-LEY25: 200 mm or less
  - 25A-LEY32: 100 mm or less
- \*3 For the mounting of the double clevis type, use the actuator within the following stroke range.
  - · 25A-LEY25: 200 mm or less
  - · 25A-LEY32: 200 mm or less
- \*4 The rod flange type is not available for the 25A-LEY25 with a 30 mm stroke and motor option 'With lock.'
- \*5 The head flange type is not available for the 25A-LEY32.

Solid state auto switches should be ordered separately. For details on auto switches, refer to the Web Catalogue.

#### Applicable auto switches

D-M9N(V)-900, D-M9P(V)-900, D-M9B(V)-900 D-M9NW(V)-900, D-M9PW(V)-900, D-M9BW(V)-900

#### Mounting Bracket Part Nos. for the 25A- Series

Applicable size	Foot*1	Flange	Double clevis		
25	25-LEY-L025	25-LEY-F025	25-LEY-D025		
32	25-LEY-L032	25-LEY-F032	25-LEY-D032		
Surface treatment	RAYDENT®	RAYDENT®	Coating (Size 16: Electroless nickel plating)		

- \*1 When ordering foot brackets, order 2 pieces per actuator.
- \* Parts belonging to each bracket are as follows. Foot, Flange: Body mounting bolt, Double clevis: Clevis pin, Type C retaining ring for axis, Body mounting bolt

Applicable Stroke Table   Standard												
Stroke	30	50	100	150	200	250	300	250	400	450	500	Manufacturable
Model [mm]	30	30	100 150		200 250		300 330		400	450	500	stroke range [mm]
25A-LEY25										_	_	15 to 400
25A-LEY32												20 to 500

\* Please consult with SMC for non-standard strokes as they are produced as special orders.

ĒΥ

Environment

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

Electric Actuator/Rod Type 25A-LEY Series

AC Servo Motor Size 25, 32 Secondary Battery Compatible



Motor mounting position: Top/Parallel



Motor mounting position: In-line

## Cable type\*1 \*2

_	Without cable
S	Standard cable
R	Robotic cable (Flexible cable)

\*1 The motor and encoder cables are included. (The lock cable is also included when the motor with lock option is selected.)

Without cable

Without cable (Connector only)

1.5

When "Without driver" is selected for driver type,

only "-: Without cable" can be selected.

Refer to page 265 if I/O cable is required.

- \*2 Standard cable entry direction is
  - · Top/Parallel: (A) Axis side

I/O cable length [m]\*1

Н

1

· In-line: (B) Counter axis side

## Cable length\*1 [m]

_	Without cable
2	2
5	5
Α	10

\*1 The length of the encoder, motor, and lock cables are the same.

Driver type\*1

	Compatible driver	Power supply voltage [V]	UL-compliant
_	Without driver		
A1	LECSA1-S□	100 to 120	
A2	LECSA2-S□	200 to 230	_
B1	LECSB1-S□	100 to 120	_
B2	LECSB2-S□	200 to 230	_
C1	LECSC1-S□	100 to 120	_
C2	LECSC2-S□	200 to 230	
S1	LECSS1-S□	100 to 120	
S2	LECSS2-S□	200 to 230	
32	LECSS2-T□	200 to 240	
4 14/1	1.1		

\*1 When a driver type is selected, a cable is included. Select the cable type and cable length. Example)

S2S2: Standard cable (2 m) + Driver (LECSS2)

: Standard cable (2 m) S2 : Without cable and driver

\* The 25A- series specifications and dimensions are the same as those of the standard model.

Compatible Driv	er								
Driver type	Pulse input type/ Positioning type  Pulse input type		CC-Link direct input type	SSCNETIII type	SSCNETIII/H type				
Series	LECSA	LECSB	LECSC	LECSS	LECSS-T				
Number of point tables	Up to 7	_	Up to 255 (2 stations occupied)	_	_				
Pulse input	0	0	_	_	_				
Applicable network	_	_	CC-Link	SSCNETⅢ	SSCNET III/H				
Control encoder	Incremental 17-bit encoder	Absolute 18-bit encoder	Absolute 18-bit encoder	Absolute 18-bit encoder	Absolute 22-bit encoder				
Communication function	USB communication	USB communication,	RS422 communication	USB com	munication				
Power supply voltage [V]	10	100 to 120 VAC (50/60 Hz), 200 to 230 VAC (50/60 Hz) 200 to 240 VAC (50/60 Hz)							
Reference page	246								

<sup>\*</sup> Copper and zinc materials are used for the motors, cables, controllers/drivers.



## **Electric Actuator/** Rod Type Secondary Battery Compatible


25A-LEY Series LEY25, 32 Size



LECS□ Series ▶ p. 181

Refer to page 48 for model selection.

#### How to Order



Accuracy Basic type

High-precision type

2 Size 25 32

Motor mounting position

_	Top mounting			
R	Right side parallel			
L	Left side parallel			
D	In-line			

4 Motor type

Symbol	Туре	Output [W]	Size	Compatible driver
V6*1	AC servo motor	100	25	LECYM2-V5 LECYU2-V5
V7	(Absolute encoder)	200	32	LECYM2-V7 LECYU2-V7

<sup>\*1</sup> For motor type V6, the compatible driver part number suffix is V5.

5 Lead [mm]

Symbol	25A-LEY25	25A-LEY32*1
Α	12	16 (20)
В	6	8 (10)
С	3	4 (5)

\*1 The values shown in ( ) are the leads for the size 32 top mounting, right/left side parallel types. (Equivalent leads which include the pulley ratio [1.25:1])

6 Stroke [mm]

30	30
to	to
500	500

For details, refer to the applicable stroke table below.

Motor option

_	Without option
В	With lock*1

\*1 When "With lock" is selected for the top mounting and right/left side parallel types, the motor body will stick out from the end of the body for size 25 with strokes of 30 mm or less. Check for interference with workpieces before selecting a model.

Motor

8 Rod end thread

_	Rod end female thread			
М	Rod end male thread			
IVI	(1 rod end nut is included.)			

9 Mounting\*1

Cumbal	Tymo	Motor mounting position				
Symbol	Туре	Top/Parallel	In-line			
_	Ends tapped/ Body bottom tapped *2	•	•			
L	Foot	•	_			
F	Rod flange*2	*4	•			
G	Head flange*2	*5	_			
D	Double clevis*3		_			

\*1 The mounting bracket is shipped together with the product but does not come assembled.

\*2 For the horizontal cantilever mounting of the rod flange, head flange, or ends tapped types, use the actuator within the following stroke range.

· LEY25: 200 mm or less · LEY32: 100 mm or less \*3 For the mounting of the double clevis type, use the actuator within the following stroke range.

· LEY25: 200 mm or less · LEY32: 200 mm or less \*4 The rod flange type is not available for the LEY25 with a 30 mm stroke and motor option "With lock."

\*5 The head flange type is not available for the

#### Mounting Bracket Part Nos. for the 25A- Series

Applicable size	Foot*1	Flange	Double clevis
25	25-LEY-L025	25-LEY-F025	25-LEY-D025
32	25-LEY-L032	25-LEY-F032	25-LEY-D032
Surface treatment	RAYDENT®	RAYDENT®	Coating (Size 16: Electroless nickel plating)

\*1 When ordering foot brackets, order 2 pieces per actuator.

\* Parts belonging to each bracket are as follows. Foot, Flange: Body mounting bolt, Double clevis: Clevis pin, Type C retaining ring for axis, D-M9NW(V)-900, D-M9PW(V)-900, D-M9PW(V)-900 Body mounting bolt

Solid state auto switches should be ordered separately. For details on auto switches, refer to the Web Catalogue.

#### Applicable auto switches

D-M9N(V)-900, D-M9P(V)-900, D-M9B(V)-900

Applicable Stroke Table												: Standard
Stroke	30	50	100	150	200	250	300	350	400	450	500	Manufacturable
Model [mm]	30	30	100	130	200	230	300	330	400	430	300	stroke range [mm]
25A-LEY25			•							_	_	15 to 400
25A-LEY32												20 to 500

Please consult with SMC for non-standard strokes as they are produced as special orders.

Electric Actuator/Rod Type 25A-LEY Series

AC Servo Motor Size 25, 32 Secondary Battery Compatible





Motor mounting position: Top/Parallel

Motor mounting position: In-line

Cable type\*1 \*2

_	— Without cable				
S	Standard cable				
R Robotic cable (Flexible cab					

- \*1 The motor and encoder cables are included. (The lock cable is also included when the motor with lock option is selected.)
- \*2 Standard cable entry direction is
  - · Top/Parallel: (A) Axis side
  - · In-line: (B) Counter axis side

Cable length [m]\*1

_	Without cable
3	3
5	5
Α	10
С	20

\*1 The length of the motor and encoder cables are the same. (For with lock)

Driver type

	Compatible driver	Power supply voltage [V			
_	Without driver	_			
M2	LECYM2-V□	200 to 230			
U2	LECYU2-V□	200 to 230			

\* When a driver type is selected, a cable is included. Select the cable type and cable length.

I/O cable length [m]\*1

_	Without cable
Н	Without cable (Connector only)
1	1.5

\*1 When "Without driver" is selected for driver type, only "-: Without cable" can be selected. Refer to page 278 if I/O cable is required.

> \* The 25A- series specifications and dimensions are the same as those of the standard model.

Compatible Driver

Compatible Driver		
Driver type	MECHATROLINK-II type	MECHATROLINK-III type
Series	LECYM	LECYU
Applicable network	MECHATROLINK-Ⅱ	MECHATROLINK-Ⅲ
Control encoder		olute encoder
Communication device	USB communication, F	RS-422 communication
Power supply voltage [V]	200 to 230 V	AC (50/60 Hz)
Reference page	2	71

<sup>\*</sup> Copper and zinc materials are used for the motors, cables, controllers/drivers.





# LEY/LEYG Series Electric Actuators Specific Product Precautions 1

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For electric actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

#### **Design/Selection**

## 

1. Do not apply a load in excess of the specification limits.

Select a suitable actuator by work load and allowable lateral load on the rod end. If a load in excess of the specification limits is applied to the piston rod, the generation of play in the piston rod sliding parts, reduced accuracy, etc., may occur and adversely affect the operation and service life of the product.

2. Do not use the product in applications where excessive external force or impact force is applied to it.

This can cause a malfunction.

- 3. When used as a stopper, select the LEYG series "Sliding bearing" for strokes of 30 mm or less.
- 4. When used as a stopper, fix the main body with a guide attachment ("Top mounting" or "Bottom mounting").

If the end of the actuator is used to fix the main body (end mounting), the excessive load acts on the actuator, which may adversely affect the operation and service life of the product.

#### Handling

## **⚠** Caution

- 1. INP output signal
  - 1) Positioning operation

When the product comes within the set range of the step data [In position], the INP output signal will turn ON. Initial value: Set to [0.50] or higher.

2) Pushing operation

When the effective force exceeds the step data [Trigger LV], the INP output signal will turn ON.

Use the product within the specified range of the [Pushing force] and [Trigger LV].

- a) To ensure that the actuator pushes the workpieces with the set [Pushing force], it is recommended that the [Trigger LV] be set to the same value as the [Pushing force].
- b) When the [Pushing force] and the [Trigger LV] are set below the specified range, the INP output signal will turn ON from the pushing start position.

#### <Limit Values for Pushing Force and Trigger Level in Relation to Pushing Speed> Without Load

Model	Lead	Pushing speed [mm/s]	Pushing force (Setting input value)	Model	Lead	Pushing speed [mm/s]	Pushing force (Setting input value)
LEY□16□	A/B/C	21 to 50	60 to 85 %	LEY□16□A	A/B/C	21 to 50	80 to 95 %
LEY□25□	A/B/C	21 to 35	50 to 65 %	LEY□25□A	A/B/C	21 to 35	80 to 95 %
LEY□32□	Α	24 to 30	60 to 85 %				
LETUSZU	B/C	21 to 30	00 10 05 %				
LEY□40□	Α	24 to 30	50 to 65 %				
LEY_4U_	B/C	21 to 30	50 10 65 %				

There is a limit to the pushing force in relation to the pushing speed. If the product is operated outside of the range (low pushing force), the completion signal [INP] may be output before the pushing operation has been completed (during the moving operation). If operating with the pushing speed below the min. speed, please check for operating problems before using the product.

#### Handling

## **⚠** Caution

<Set Values for Vertical Upward Transfer Pushing Operations>

For vertical loads (upward), set the pushing force to the max. value shown below and operate at the work load or less.

Model	LE	Y16		LE	Y25	<u> </u>	LE	Y32	2□	LE	Y40	
Lead	Α	В	С	Α	В	С	Α	В	С	Α	В	С
Work load [kg]	1	1.5	3	2.5	5	10	4.5	9	18	7	14	28
Pushing force		85 %			65 %	)		85 %	,		65 %	
Model	LE	Y16[	□Α	LE	Y25	□A	]					
Lead	Α	В	С	Λ	В	^	1					
Load	^	D	C	Α	В	С						
Work load [kg]	1	1.5	3	1.2	2.5	5						

Model	LE)	/G16	6 <u>M</u> □	LE	/G2	<b>5</b> M□	LE\	/G32	2월□	LE	<b>YG4</b> (	O <sub>L</sub> M
Lead	Α	В	С	Α	В	С	Α	В	С	Α	В	С
Work load [kg]	0.5	1	2.5	1.5	4	9	2.5	7	16	5	12	26
Pushing force		85 %	,		65 %	,	-	85 %	,		65 %	,
Model	LEY	'G16	^□A	LEY	'G25	′□A						
Model Lead	LEY A	'G16  B	<sup>l</sup> □A C	LEY A	G25  B	<sup>l</sup> □A C						
			_	<b>A</b> 0.5		_						

2. To conduct a pushing operation, be sure to set the product to [Pushing operation].

Also, refrain from bumping the workpiece during a positioning operation or when in the range of the positioning operation. Failure to do so may result in a malfunction.

3. Use the product within the specified pushing speed range for the pushing operation.

Failure to do so may result in damage or malfunction.

4. The moving force should be the initial value (LEY16 □/25□/32□/40□: 100 %, LEY16A□: 150 %, and LEY25A□: 200 %).

If the moving force is set below the initial value, it may cause the generation of an alarm.

5. The actual speed of this actuator is affected by the load.

Check the model selection section of the catalogue.

6. Do not apply a load, impact, or resistance in addition to the transferred load during return to origin.

Additional force will cause the displacement of the origin position since it is based on the detected motor torque.

7. For pushing operations, set the product to a position at least 2 mm away from a workpiece. (This position is referred to as the pushing start position.)

The following alarms may be generated and operation may become unstable if setting is not done correctly.

a. "Posn failed"

The product cannot reach the pushing start position due to variations in the target positions.

b. "Pushing ALM"

The product is pushed back from the pushing start position after starting to push.



Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

AC Servo Motor



LEY/LEYG Series

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For electric actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

#### Handling

## **<b>⚠** Caution

8. Do not scratch or dent the sliding parts of the piston rod by bumping them or placing objects on them.

The piston rod and guide rod are manufactured to precise tolerances, so even a slight deformation may cause a malfunction.

9. When an external guide is used, connect it in such a way that no impact or load is applied to it.

Use a freely moving connector (such as a floating joint).

10. Do not operate by fixing the piston rod and moving the actuator body.

Excessive load will be applied to the piston rod, resulting in damage to the actuator and a reduced service life of the product.

11. When an actuator is operated with one end fixed and the other free (ends tapped or flange), a bending moment may act on the actuator due to vibration generated at the stroke end, which can damage the actuator. In such cases, install a mounting bracket to suppress the vibration of the actuator body or reduce the speed so that the actuator does not vibrate at the stroke end.

Also, use a mounting bracket when moving the actuator body or when a long stroke actuator is mounted horizontally and fixed at one end.


12. Avoid using the electric actuator in such a way that rotational torque would be applied to the piston rod.

This may cause the deformation of the non-rotating guide, abnormal auto switch responses, play in the internal guide, or an increase in the sliding resistance.

Refer to the table below for the approximate values of the allowable range of rotational torque.

Allowable rotational	LEY16□□	LEY25□□	LEY32/40□□	LEY63
torque [N·m] or less	0.8	1.1	1.4	2.8

When screwing a bracket or nut into the piston rod end, hold the flats of the end of the "socket" with a wrench (the piston rod should be fully retracted). Do not apply tightening torque to the non-rotating mechanism.



13. When rotational torque is applied to the end of the plate, use it within the allowable range. [LEYG series]

Failure to do so may cause the deformation of the guide rod and bushing, play in the guide, or an increase in the sliding resistance

#### 14. For pushing operations, use the product within the duty ratio range below.

The duty ratio is the fraction of time that the product can keep pushing.

#### Step motor (Servo/24 VDC)

LEY16□					
Duching	Ambient temperat	ture: 25 °C or less	Ambient temperature: 40 °C		
Pushing force [%]	Duty ratio	Continuous pushing	Duty ratio	Continuous pushing	
Torce [%]	[%]	time [minute]	[%]	time [minute]	
40 or less			100	_	
50	100		70	12	
70	100	_	20	1.3	
85			15	0.8	

LL I ZJ	/ <del>1</del> 0□				
Pushing	Ambient temperat	ture: 25 °C or less	Ambient temperature: 40 °C		
	Duty ratio	Continuous pushing	Duty ratio	Continuous pushing	
force [%]	[%]	time [minute]	[%]	time [minute]	

force [%]	[%]	time [minute]	[%]	time [minute]		
65 or less	100	_	100	_		
LEY32□						

Duahina	Ambient temperat	ture: 25 °C or less	Ambient temp	erature: 40 °C
Pushing force [%]	Duty ratio [%]	Continuous pushing time [minute]	Duty ratio [%]	Continuous pushing time [minute]
65 or less	100		100	_
85	100	_	50	15


#### Servo motor (24 VDC)

LEV25 //O

LEY16A				
Pushing	Ambient temperat	ture: 25 °C or less	Ambient temp	erature: 40 °C
force [%]	,	Continuous pushing	,	Continuous pushing
10100 [70]	[%]	time [minute]	[%]	time [minute]
95 or less	100	_	100	_

LEY25A				
Pushing	Ambient temperat	ture: 25 °C or less	Ambient temp	erature: 40 °C
"	Duty ratio	Continuous pushing	Duty ratio	Continuous pushing
force [%]	[%]	time [minute]	[%]	time [minute]
95 or less	100	_	100	_

#### 15. When mounting the product, secure a space of 40 mm or more to allow for bends in the cable.



16. When mounting a bolt, workpiece, or jig, hold the flats of the piston rod end with a wrench so that the piston rod does not rotate. The bolt should be tightened within the specified torque range.

Failure to do so may cause abnormal auto switch responses, play in the internal guide, or an increase in the sliding resistance.





# LEY/LEYG Series Electric Actuators Specific Product Precautions 3

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For electric actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

#### Handling

## **⚠** Caution

17. When mounting the product and/or a workpiece, tighten the mounting screws within the specified torque range.

Tightening the screws with a higher torque than recommended may cause a malfunction, while tightening with a lower torque can cause the displacement of the mounting position or, in extreme conditions, the actuator could become detached from its mounting position.


#### <LEY series>

#### Workpiece fixed/Rod end female thread



Model	Screw size	Max. tightening torque [N⋅m]	Max. screw-in depth [mm]	
LEY16	M5 x 0.8	3.0	10	14
LEY25	M8 x 1.25	12.5	13	17
LEY32/40	M8 x 1.25	12.5	13	22
LEY63	M16 x 2	106	21	36

#### Workpiece fixed/Rod end male thread (When "Rod end male thread" is selected)



Model	Thread size	Max. tightening torque [N·m]	Effective thread length [mm]	End socket width across flats [mm]
LEY16	M8 x 1.25	12.5	12	14
LEY25	M14 x 1.5	65.0	20.5	17
	M14 x 1.5		20.5	22
LEY63	M18 x 1.5	97.0	26	36
	Pod and nut		Food broadcas	

Model	Rod e	End bracket	
Model	Width across flats [mm]	Length [mm]	screw-in depth [mm]
LEY16	13	5	5 or more
LEY25	22	8	8 or more
LEY32/40	22	8	8 or more
LEY63	27	11	18


<sup>\*</sup> The rod end nut is an accessary.

#### Body fixed/Body bottom tapped type (When "Body bottom tapped" is selected)




Model	Screw size	Max. tightening torque [N·m]	Max. screw-in depth [mm]
LEY16	M4 x 0.7	1.5	5.5
LEY25	M5 x 0.8	3.0	6.5
LEY32/40	M6 x 1.0	5.2	8.8
LEY63	M8 x 1.25	12.5	10

### Body fixed/Rod side/Head side tapped type




1	Model			Max. screw-in
	Wiodoi	size	torque [N·m]	depth [mm]
	LEY16	M4 x 0.7	1.5	7
	LEY25	M5 x 0.8	3.0	8
	LEY32/40	M6 x 1.0	5.2	10
	LEY63	M8 x 1.25	12.5	16
				,

## <LEYG series> Workpiece fixed/Plate tapped type




Model	Screw size	Max. tightening torque [N·m]	Max. screw-in depth [mm]
LEYG16 <sup>™</sup>	M5 x 0.8	3.0	8
LEYG25 <sup>M</sup>	M6 x 1.0	5.2	11
I FYG32M	M6 x 1 0	5.2	12

#### **Body fixed/Top mounting**




Model	Screw size	Max. tightening torque [N·m]	Length: L [mm]
LEYG16 <sup>™</sup>	M4 x 0.7	1.5	32
LEYG25 <sup>M</sup>	M5 x 0.8	3.0	40.3
LEYG <sub>40L</sub>	M5 x 0.8	3.0	50.3

#### **Body fixed/Bottom mounting**



Model	Screw size	Max. tightening torque [N·m]	Max. screw-in depth [mm]
LEYG16 <sup>™</sup>	M5 x 0.8	3.0	10
LEYG25 <sup>M</sup>	M6 x 1.0	5.2	12
LEYG <sub>40L</sub>	M6 x 1.0	5.2	12

#### Body fixed/Head side tapped type



Model	Screw size	Max. tightening torque [N·m]	Max. screw-ir depth [mm]
LEYG16 <sup>™</sup>	M4 x 0.7	1.5	7
LEYG25 <sup>M</sup>	M5 x 0.8	3.0	8
LEYG <sub>40L</sub>	M6 x 1.0	5.2	10

18. Keep the flatness of the mounting surface within the following ranges when mounting the actuator body and workpiece.

Mounting the product on an uneven workpiece or base may cause an increase in the sliding resistance.

M	odel	Mounting po	osition	Flatness			
LE	ΕY□	Body/Body bottom		0.1 mm or less			
	VC -	Top mounting/Bottom moun	nting	0.02 mm or less			
LE	YG□	Workpiece/Plate mounting		0.02 mm or less			

- 19. When using auto switches with the guide rod type LEYG series, the following limits apply. Please consider the following before selecting the product.
  - Auto switches must be inserted from the front side with the rod (plate) sticking out.
  - Auto switches with perpendicular electrical entries cannot be used
  - Auto switches cannot be fixed with the parts hidden behind the guide attachment (the side of the rod that sticks out).
  - Please consult with SMC when using auto switches on the side of the rod that sticks out.



LEYG



## LEY/LEYG Series **Electric Actuators Specific Product Precautions 4**

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For electric actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

#### Handling


## **⚠** Caution

- 20. When using the product with the IP65 or equivalent specifications, be sure to mount the tubing to the vent hole, and then place the end of the tubing in an area where it is not exposed to dust or water. When the actuator is used without mounting the fitting and tubing to the vent hole, water or dust may enter the inside of the actuator, causing a malfunction.
- 21. When fluctuations in the load are caused during operation, malfunction, noise, or alarm generation may occur. (In the case of the AC servo motor)

The gain tuning may not be suitable for fluctuating loads.

Adjust the gain properly by following the instructions in the driver manual.

#### **Enclosure**



#### • First Digit:

#### Degree of protection against solid foreign objects

0	Not protected
1	Protected against solid foreign objects of 50 mmØ and larger
2	Protected against solid foreign objects of 12 mmØ and larger
3	Protected against solid foreign objects of 2.5 mmØ and larger
4	Protected against solid foreign objects of 1.0 mmØ and larger
5	Dust protected
6	Dust-tight

#### Second Digit:

#### Degree of protection against water

0	Not protected	_
1	Protected against vertically falling water droplets	Dripproof type 1
2	Protected against vertically falling water droplets when enclosure is tilted up to 15°	Dripproof type 2
3	Protected against rainfall when enclosure is tilted up to 60°	Rainproof type
4	Protected against splashing water	Splashproof type
5	Protected against water jets	Water-jet- proof type
6	Protected against powerful water jets	Powerful water- jet-proof type
7	Protected against the effects of temporary immersion in water	Immersible type
8	Protected against the effects of continuous immersion in water	Submersible type

Example) IP65: Dust-tight, Water-jet-proof type

"Water-jet-proof" means that no water enters the equipment that could hinder it from operating normally when water is applied for 3 minutes in the prescribed manner. Take appropriate protective measures as the device is not usable in environments where droplets of water are splashed constantly.

#### **Maintenance**

## **⚠** Warning

- 1. Ensure that the power supply is stopped and the workpiece is removed before starting maintenance work or replacing the product.
- Maintenance frequency

Perform maintenance according to the table below.

Frequency	Appearance check	Belt check
Inspection before daily operation	0	_
Inspection every 6 months/ 250 km/5 million cycles*1	0	0

- \*1 Select whichever comes first.
- Items for visual appearance check
  - 1. Loose set screws, Abnormal amount of dirt, etc.
  - 2. Check for visible damage, Check of cable joint
  - 3. Vibration, Noise

#### • Items for belt check

Stop operation immediately and replace the belt when any of the following occur. In addition, ensure your operating environment and conditions satisfy the requirements specified for the product.

a. Tooth shape canvas is worn out

Canvas fiber becomes fuzzy, Rubber is coming off and the fiber has become whitish, Lines of fibers have become unclear

b. Peeling off or wearing of the side of the belt

Belt corner has become rounded and frayed threads stick

c. Belt is partially cut

Belt is partially cut, Foreign matter caught in the teeth of other parts is causing damage

d. A vertical line on belt teeth is visible

Damage which is made when the belt runs on the flange

- e. Rubber back of the belt is softened and sticky
- f. Cracks on the back of the belt are visible

	C	SIV	
--	---	-----	--

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

## **Controller/Driver** LEC□/JXC□ Series

## <Single Axis Controllers>

Step Data Input Type ...... p. 191

Gateway Unit .....p. 203

**LEC-G** Series



Programless Type ..... p. 207

**Servo Motor** 

(24 VDC) **LECA6** Series

Pulse Input Type ....

.... p. 214

**Step Motor** (Servo/24 VDC) **LECP1** Series



**Step Motor** (Servo/24 VDC) **LECPA** Series



#### EtherCAT®/EtherNet/IP™/PROFINET/DeviceNet™/IO-Link Direct Input Type

p. **2224** 

JXC Series

Ether CAT.



EtherNet/IP



**PROFO**® NET

Device Net



**IO**-Link

## <Multi-Axis Controllers>

EtherNet/IP™ Direct Input Type ..... p. 233



For 4 axes

Parallel I/O/EtherNet/IP™ Direct Input Type ...... p. 235



JXC73 Series **JXC83** Series



JXC93 Series EtherNet/IP



## **Controller (Step Data Input Type)** Servo Motor (24 VDC)

**LECA6** Series




**LECA6** Series

( E CRU'US ROHS




## **How to Order**



When controller equipped type is selected when ordering the LE series, you do not need to order this controller.

5



#### Refer to the operation manual for using the products. Please download it via our website, https://www.smc.eu

#### Precautions for blank controllers $(LEC \Box 6 \Box \Box -BC)$

A blank controller is a controller to which the customer can write the data of the actuator it is to be combined and used with. Use the dedicated software (LEC-BCW) for data writing.

- Please download the dedicated software (LEC-BCW) via our website.
- · Order the communication cable for controller setting (LEC-W2A-C) separately to use this software.

SMC website https://www.smc.eu

## **Specifications**

[UL-compliant products]

When compliance with UL is required, the electric actuator and controller should be

used with a UL1310 Class 2 power supply.

Basic Specificati	ons					
Item	LECA6					
Compatible motor	Servo motor (24 VDC)					
Power supply*1	Power voltage: 24 VDC ±10 %*2					
rower supply	[Including motor drive power, control power, stop, lock release]					
Parallel input	11 inputs (Photo-coupler isolation)					
Parallel output	13 outputs (Photo-coupler isolation)					
Compatible encoder	Incremental A/B phase (800 pulse/rotation) Incremental A/B (800 pulse/rotation)/Z phase					
Serial communication	RS485 (Modbus protocol compliant)					
Memory	EEPROM					
LED indicator	LED (Green/Red) one of each					
Lock control	Forced-lock release terminal*3					
Cable length [m]	I/O cable: 5 or less, Actuator cable: 20 or less					
Cooling system	Natural air cooling					
Operating temperature range [°C]	0 to 40 (No freezing)					
Operating humidity range [%RH]	90 or less (No condensation)					
Storage temperature range [°C]	-10 to 60 (No freezing)					
Storage humidity range [%RH]	90 or less (No condensation)					
Insulation resistance [MΩ]	Between the housing and SG terminal: 50 (500 VDC)					
Weight [g]	150 (Screw mounting), 170 (DIN rail mounting)					


- \*1 Do not use the power supply of "inrush current prevention type" for the controller power supply. When compliance with UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.
- \*2 The power consumption changes depending on the actuator model. Refer to the specifications of actuator for more details
- \*3 Applicable to non-magnetising locks





DIN rail mounting adapter

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

#### **How to Mount**








Hook the controller on the DIN rail and press the lever of section **A** in the arrow direction to lock it.

\* When size 25 or more of the LE series are used, the space between the controllers should be 10 mm or more.

## DIN rail AXT100-DR-□

\* For □, enter a number from the No. line in the table below. Refer to the dimension drawings on page 193 for the mounting dimensions.



D:	ensions	F 7
_ I JIME	ensions	ımmı

	iiiieii	SIONS	» [1111111]																		
1	No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
	L	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
1	No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
	L	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5

## DIN rail mounting adapter


LEC-D0 (with 2 mounting screws)


This should be used when the DIN rail mounting adapter is mounted onto a screw mounting type controller afterward.

## LECP6 Series LECA6 Series


#### **Dimensions**


### a) Screw mounting (LEC□6□□-□)





### b) DIN rail mounting (LEC□6□□D-□)





Щ

LECA6

## Wiring Example 1

Power Supply Connector: CN1


\* The power supply plug is an accessory. < Applicable cable size > AWG20 (0.5 mm²), cover diameter 2.0 mm or less

Controller (Step Data Input Type)/Step Motor (Servo/24 VDC) LECP6 Series

Controller (Step Data Input Type)/Servo Motor (24 VDC) LECA6 Series

#### CN1 Power Supply Connector Terminal for LECA6 (PHOENIX CONTACT FK-MC0.5/7-ST-2.5)

Terminal name	Function	Details
0V	Common supply (-)	M 24V terminal/C 24V terminal/EMG terminal/BK RLS terminal are common (–).
M 24V	Motor power supply (+)	Motor power supply (+) supplied to the controller
C 24V	Control power supply (+)	Control power supply (+) supplied to the controller
EMG	Stop (+)	Input (+) for releasing the stop
BK RLS	Lock release (+)	Input (+) for releasing the lock
RG+	Regenerative output 1	Regenerative output terminals for external connection
RG-	Regenerative output 2	(Not necessary to connect them in the combination with the LE series standard specifications.)



## Wiring Example 2

\* When you connect a PLC to the CN5 parallel I/O connector, use the I/O cable (LEC-CN5- $\square$ ). Parallel I/O Connector: CN5

\* The wiring changes depending on the type of parallel I/O (NPN or PNP).

#### Wiring diagram

<b>(</b> l	NPN)		Davis and by 04 MDO
_	CN5		Power supply 24 VDC for I/O signal
	COM+	A1	
	COM-	A2	<b>———</b>
	IN0	A3	
	IN1	A4	<del>-</del>
	IN2	A5	<del>-</del>
	IN3	A6	
	IN4	A7	<del>-</del>
	IN5	A8	
	SETUP	A9	
	HOLD	A10	<del>-</del>
	DRIVE	A11	
	RESET	A12	<del>-</del>
	SVON	A13	<del></del>
	OUT0	B1	Load
	OUT1	B2	Load
	OUT2	В3	Load
	OUT3	B4	Load
	OUT4	B5	Load
	OUT5	В6	Load
	BUSY	B7	Load
	AREA	B8	Load
	SETON	B9	Load
	INP	B10	Load
	SVRE	B11	Load
	*ESTOP	B12	Load
	*ALARM	B13	Load

ln	put	Signal

Name	Details
COM+	Connects the power supply 24 V for input/output signal
COM-	Connects the power supply 0 V for input/output signal
IN0 to IN5	Step data specified bit no. (Input is instructed by combining IN0 to 5.)
SETUP	Instruction to return to origin
HOLD	Temporarily stops operation
DRIVE	Instruction to drive
RESET	Resets alarm and interrupts operation
SVON	Servo ON instruction

#### LEC□6P□□-□ (PNP)

١.	,		Power supply 24 VDC
_	CN5		for I/O signal
	COM+	A1	<b>├</b>
	COM-	A2	<del>                                     </del>
	IN0	A3	
	IN1	A4	
	IN2	A5	
	IN3	A6	
	IN4	A7	
	IN5	A8	
	SETUP	A9	
	HOLD	A10	
	DRIVE	A11	
	RESET	A12	
	SVON	A13	
	OUT0	B1	Load
	OUT1	B2	Load
	OUT2	В3	Load
	OUT3	B4	Load
	OUT4	B5	Load
	OUT5	B6	Load
	BUSY	B7	Load
	AREA	B8	Load
	SETON	B9	Load
	INP	B10	Load
	SVRE	B11	Load
	*ESTOP	B12	Load
	*ALARM	B13	Load
_			<del>-</del>

#### Outnut Signal

Output Signa	.l
Name	Details
OUT0 to OUT5	Outputs the step data no. during operation
BUSY	Outputs when the actuator is moving
AREA	Outputs within the step data area output setting range
SETON	Outputs when returning to origin
INP	Outputs when target position or target force is reached (Turns on when the positioning or pushing is completed.)
SVRE	Outputs when servo is on
*ESTOP*1	OFF when EMG stop is instructed
*ALARM*1	OFF when alarm is generated

<sup>\*1</sup> Signal of negative-logic circuit (N.C.)




## **LECA6** Series

#### Step Data Setting

#### 1. Step data setting for positioning

In this setting, the actuator moves toward and stops at the target position.

The following diagram shows the setting items and operation. The setting items and set values for this operation are stated



: Need to be set.

○: Need to be adjusted as required.


Setting is not required.

#### Step Data (Positioning) Details Necessit Item When the absolute position is required, set 0 Movement MOD Absolute. When the relative position is required, set Relative. Transfer speed to the target position $\bigcirc$ Speed $\bigcirc$ Position Target position Parameter which defines how rapidly the actuator reaches the speed set. The Acceleration $\bigcirc$ higher the set value, the faster it reaches the speed set. Parameter which defines how rapidly the 0 Deceleration actuator comes to stop. The higher the set value, the quicker it stops. Set 0. 0 Pushing force (If values 1 to 100 are set, the operation will be changed to the pushing operation.) Trigger LV Setting is not required. Pushing speed Setting is not required. Max. torque during the positioning operation 0 Moving force (No specific change is required.) Condition that turns on the AREA output $\bigcirc$ Area 1, Area 2 signal. Condition that turns on the INP output signal. When the actuator enters the range of [in position], the INP output signal turns on. (It is unnecessary to change this from In position the initial value.) When it is necessary to output the arrival signal before the operation is completed, make the value larger.

#### 2. Step data setting for pushing

The actuator moves toward the pushing start position, and when it reaches that position, it starts pushing with the set force or less.

The following diagram shows the setting items and operation. The setting items and set values for this operation are stated below.




#### Step Data (Pushing)

©: Need to be set.


○: Need to be adjusted as required.

	<b>–</b> a.a. (. a.cg)	O : 11000 to be dejusted de required
Necessity	Item	Details
0	Movement MOD	When the absolute position is required, set Absolute. When the relative position is required, set Relative.
0	Speed	Transfer speed to the pushing start position
0	Position	Pushing start position
0	Acceleration	Parameter which defines how rapidly the actuator reaches the speed set. The higher the set value, the faster it reaches the speed set.
0	Deceleration	Parameter which defines how rapidly the actuator comes to stop. The higher the set value, the quicker it stops.
0	Pushing force	Pushing force ratio is defined. The setting range differs depending on the electric actuator type. Refer to the operation manual for the electric actuator.
0	Trigger LV	Condition that turns on the INP output signal. The INP output signal turns on when the generated force exceeds the value. Trigger level should be the pushing force or less.
0	Pushing speed	Pushing speed during pushing. When the speed is set fast, the electric actuator and workpieces might be damaged due to the impact when they hit the end, so this set value should be smaller. Refer to the operation manual for the electric actuator.
0	Moving force	Max. torque during the positioning operation (No specific change is required.)
0	Area 1, Area 2	Condition that turns on the AREA output signal.
0	In position	Transfer distance during pushing. If the transferred distance exceeds the setting, it stops even if it is not pushing. If the transfer distance is exceeded, the INP output signal will not turn on.

## Signal Timing



"\*ALARM" and "\*ESTOP" are expressed as negative-logic circuits.





"OUT" is output when "DRIVE" is changed from ON to OFF Refer to the operation manual for details on the controller for the LEM series. (When power supply is applied, "DRIVE" or "RESET" is turned ON or \*ESTOP" is turned OFF, all of the "OUT" outputs are OFF.)

#### **HOLD** ON Input HOLD OFF ON Output BUSY OFF Slow-down Speed 0 mm/s starting **HOLD** during the operation

When the actuator is within the "In position" range in the pushing operation, it does not stop even if HOLD signal is input.

point





of OUT signals when the alarm is generated.

"\*ALARM" is expressed as a negative-logic circuit.



LEY

Model Selection

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEYG

Ē AC Servo Motor EYG.

LEY-X5 Environment

25A-LEY


LECA6 Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEC-G LECP1

LECPA


LECS AC Servo Motor LECY

## **LECA6** Series

## **Options: Actuator Cable**




[Robotic cable, standard cable with lock and sensor for step motor (Servo/24 VDC)]



## Controller (Step Data Input Type)/Servo Motor (24 VDC) LECA6 Series


## [Robotic cable for servo motor (24 VDC)]




Produced upon receipt of order

#### Controller side LE-CA-□ Actuator side (10.5)Connector C (14.2)(Terminal no.) (Terminal no.) (23.7)Connector A (16.6)(ø7. 321 (13.5)(06.7) AB (14.7)15 (30.7)(11) (10)Connector D Connector B

Weight				
Product no.	Weight [g]			
LE-CA-1	220			
LE-CA-3	420			
LE-CA-5	700			
LE-CA-8	1100			
LE-CA-A	1370			
LE-CA-B	2050			
LE-CA-C	2720			




### [Robotic cable with lock and sensor for servo motor (24 VDC)]



Produced upon receipt

With lock and sensor

LE-CA-□-B Actuator side



#### Weight

Product no.	Weight [g]
LE-CA-1-B	270
LE-CA-3-B	520
LE-CA-5-B	870
LE-CA-8-B	1370
LE-CA-A-B	1710
<b>LE-CA-B-B</b> 2560	
LE-CA-C-B	3400

Signal U	Connector A1 terminal no.		Cable color	Connector C terminal no.
V	2 '		White	2
W	3 '		Black	3
Signal	Connector A2 terminal no.	Shield	Cable color	Connector D terminal no.
Vcc	B-1 •		Brown	12
GND	A-1		Black	13
Ā	B-2 •		Red	7
Α	A-2		Black	6
B	B-3		Orange	9
В	A-3		Black	8
Z	B-4 '		Yellow	11
Z	A-4	\	Black	10
	Connector B	· · · · · · · · · · · · · · · · · · ·	_	3
Signal	terminal no.	Connection of shield material		
Lock (+)	B-1 •		Red	4
Lock (-)	A-1 •		Black	5
Sensor (+)	B-3		Brown	1
Sensor (-)	A-3		Black	2

Model Selection Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

LEY AC Servo Motor LEYG

25A-LEY LEY-X5 Environment


> LECA6 LEC-G

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECP1 LECPA

LECS AC Servo Motor LECY

## **LECA6** Series

## Option: I/O Cable



\* Conductor size: AWG28

Connector	Insulation	Dot	Dot
pin no.	colour	mark	colour
A1	Light brown		Black
A2	Light brown		Red
A3	Yellow		Black
A4	Yellow		Red
A5	Light green		Black
A6	Light green		Red
A7	Gray		Black
A8	Gray		Red
A9	White		Black
A10	White		Red
A11	Light brown		Black
A12	Light brown		Red
A13	Yellow		Black

Connector	Insulation	Dot	Dot
pin no.	colour	mark	colour
B1	Yellow		Red
B2	Light green		Black
B3	Light green		Red
B4	Gray		Black
B5	Gray		Red
B6	White		Black
B7	White		Red
B8	Light brown		Black
B9	Light brown		Red
B10	Yellow		Black
B11	Yellow		Red
B12	Light green		Black
B13	Light green		Red
_		Shield	


### Weight

Product no.	Weight [g]
LEC-CN5-1	170
LEC-CN5-3	320
LEC-CN5-5	520

Option: Noise Filter Set for Servo Motor (24 VDC)

## LEC-NFA

Contents of the set: 2 noise filters (Manufactured by WURTH ELEKTRONIK: 74271222)



\* Refer to the LECA6 series Operation Manual for installation.

## **Communication Cable for Controller Setting/LEC-W2A-**□

PC Communication cable (LEC-W2A-C) USB cable (LEC-W2-U) Controller setting software · USB driver Download from SMC's website https://www.smc.eu

**How to Order** 

LEC-W2A-C Communication cable

LEC-W2-U **USB** cable

## **Compatible Controller/Driver**

Step data input type **LECA6** Series **LECPA** Series Pulse input type

**Step Motor Controller** JXCE1/91/P1/D1/L1 Series

\* When connecting to a JXCE1/91/P1/D1/L1 series product, use a conversion cable (P5062-5) as a relay.


### **Hardware Requirements**

OS	Windows <sup>®</sup> 7, Windows <sup>®</sup> 8.1, Windows <sup>®</sup> 10
Communication interface	USB 1.1 or USB 2.0 ports
Display	1024 x 768 or more

<sup>\*</sup> Windows®7, Windows®8.1 and Windows®10 are registered trademarks of Microsoft Corporation in the United States.

## Screen Example


#### Easy mode screen example



#### Easy operation and simple setting

- Allowing to set and display actuator step data such as position, speed, force, etc.
- Setting of step data and test drive can be performed on the same page.
- Can be used to jog and move at a constant rate

#### Normal mode screen example



#### **Detailed setting**

- Step data can be set in detail.
- Signals and terminal status can be monitored.
- Parameters can be set.
- JOG and constant rate movement, return to origin, test drive and testing of forced output can be performed.



Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

Ē AC Servo Motor

LEYG

LEY-X5 25A-LEY

LECA6 LEC-G

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECP1 LECPA


## LEC Series **Teaching Box/LEC-T1**





#### **How to Order**





#### The displayed language can be changed to English or Japanese.

#### **Specifications**

#### Standard functions

- Chinese character display
- Stop switch is provided.

### **Option**

• Enable switch is provided.

Item	Description
Switch	Stop switch, Enable switch (Option)
Cable length [m]	3
Enclosure	IP64 (Except connector)
Operating temperature range [°C]	5 to 50
Operating humidity range [%RH]	90 or less (No condensation)
Weight [g]	350 (Except cable)

#### [CE-compliant products]

The EMC compliance of the teaching box was tested with a step motor controller (servo/24 VDC) and an applicable actuator.

#### [UL-compliant products]

When compliance with UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.

### **Easy Mode**

Function	Details
Step data	Setting of step data
Jog	Jog operation     Return to origin
Test	1 step operation     Return to origin
Monitor	<ul> <li>Display of axis and step data no.</li> <li>Display of two items selected from Position, Speed, Force.</li> </ul>
ALM	Active alarm display     Alarm reset
TB setting	Reconnection of axis (Ver. 1.**)     Displayed language setting (Ver. 2.**)     Setting of easy/normal mode     Setting step data and selection of items from easy mode monitor

#### Menu Operations Flowchart


Menu Operatio	113 1 10	WCHart	
Menu		Data	
Data Monitor Jog Test ALM TB setting		Step data no. Setting of two items selected below Ver. 1.**: Position, Speed, Force, Acceleration, Deceleration Ver. 2.**: Position, Speed, Pushing force, Acceleration, Deceleration, Movement MOD, Trigger LV, Pushing speed, Moving force, Area 1, Area 2, In position	
		Monitor	
		Display of step no. Display of two items se (Position, Speed, For	
		Jog	
		Return to origin Jog operation	
		Test	
		1 step operation	
		Active alarm display Alarm reset	
		TB setting	
		Reconnect (Ver. 1.**) Japanese/English (Ve Easy/Normal Set item	,




## Teaching Box LEC Series

#### **Normal Mode**

Function	Details
Step data	Step data setting
Parameter	Parameters setting
Test	Jog operation/Constant rate movement     Return to origin     Test drive     (Specify a maximum of 5 step data and operate.)     Forced output     (Forced signal output, Forced terminal output)
Monitor	<ul> <li>Drive monitor</li> <li>Output signal monitor</li> <li>Input signal monitor</li> <li>Output terminal monitor</li> <li>Input terminal monitor</li> </ul>
ALM	<ul><li>Active alarm display (Alarm reset)</li><li>Alarm log record display</li></ul>
File	Data saving     Save the step data and parameters of the controller which is being used for communication (it is possible to save four files, with one set of step data and parameters defined as one file).      Load to controller     Loads the data which is saved in the teaching box to the controller which is being used for communication.      Delete the saved data.      File protection (Ver. 2.**)
TB setting	Display setting     (Easy/Normal mode)     Language setting     (Japanese/English)     Backlight setting     LCD contrast setting     Beep sound setting     Max. connection axis     Distance unit (mm/inch)
Reconnect	Reconnection of axis



## **Dimensions**



No.	Description	Function
1	LCD	A screen of liquid crystal display (with backlight)
2	Ring	A ring for hanging the teaching box
3	Stop switch	When switch is pushed in, the switch locks and stops. The lock is released when it is turned to the right.
4	Stop switch guard	A guard for the stop switch
5	Enable switch (Option)	Prevents unintentional operation (unexpected operation) of the jog test function.  Other functions such as data change are not covered.
6	Key switch	Switch for each input
7	Cable	Length: 3 meters
8	Connector	A connector connected to CN4 of the controller



LECS

AC Servo Motor LECY

## Gateway Unit

LEC-G Series



#### **How to Order**

#### LEC-GMJ2 **⚠** Caution Gateway unit [CE-compliant products] EMC compliance was tested by Applicable Fieldbus protocols combining the electric actuator LE MJ2 CC-Link Ver. 2.0 series and the controller LEC series. The EMC depends on the Mounting 4 DN1 DeviceNet™ configuration of the customer's PR1 PROFIBUS DP Screw mounting control panel and the relationship EtherNet/IP™ DIN rail EN1 with other electrical equipment \*1 The DIN rail is not included. and wiring. Therefore, compliance CC-Link V2 Device Net eggegg<sup>®</sup> Ethen\\et/IP Order it separately. with the EMC directive cannot be certified for SMC components incorporated into the customer's LEC-CG Cable equipment under actual operating conditions. As a result, it is necessary for the customer to Cable type ● verify compliance with the EMC Cable length Communication cable directive for the machinery and Communication cable 2 Cable between branches K 0.3 m equipment as a whole. 0.5 m [UL-compliant products] 1 m When compliance with UL is required, the electric actuator and LEC-CGD controller should be used with a **Branch connector** UL1310 Class 2 power supply. Cable between branches Branch connector

LEC-CGR

## **Specifications**

	Model		LEC-	GMJ2□	LEC-GDN1□	LEC-GPR1□	LEC-GEN1□			
	Annlicable avetem	Fieldbus	CC	:-Link	DeviceNet™	PROFIBUS DP	EtherNet/IP™			
	Applicable system	Version*1	Ver. 2.0		Release 2.0	V1	Release 1.0			
	Communication speed [bps]		156 k/625 k/2.5 M /5 M/10 M		125 k/250 k/500 k	9.6 k/19.2 k/45.45 k/ 93.75 k/187.5 k/500 k/ 1.5 M/3 M/6 M/12 M	10 M/100 M			
	Configuratio	n file*2		_	EDS file	GSD file	EDS file			
Communication specifications	I/O occupation	on area	4 stations occupied (8 times setting)	Input 896 points 108 words Output 896 points 108 words	Input 200 bytes Output 200 bytes	Input 57 words Output 57 words	Input 256 bytes Output 256 bytes			
	Power supply for	Power supply for Power supply voltage [V]*6		_	11 to 25 VDC	_	_			
	communication	Internal current consumption [mA]	_		100	_	_			
	Communication	connector specifications	Connector (Accessory)		Connector (Accessory)	D-sub	RJ45			
	Terminating	resistor	Not included		Not included	Not included	Not included			
Power supply voltage	ge [V]* <sup>6</sup>				24 VDC	±10 %				
Current	Not connecte	ed to teaching box	200							
consumption [mA]	Connected to	teaching box	300							
EMG output termina	1		30 VDC 1 A							
Controller	Applicable c		LECA6 Series							
specifications		ion speed [bps]*3			115.2 k/					
opodinoution:	Max. number of o	onnectable controllers*4		12	8* <sup>5</sup>	5	12			
Accessories			Power supply connector, communication connector Power supply connector							
Operating temperat			0 to 40 (No freezing)							
Operating humidity	<u> </u>		90 or less (No condensation)							
Storage temperature range [°C] Storage humidity range [%RH] Weight [g]			-10 to 60 (No freezing)							
			90 or less (No condensation)							
			200 (Screw mounting), 220 (DIN rail mounting)							

- \*1 Please note that versions are subject to change.
- \*2 Each file can be downloaded from the SMC website.
- \*3 When using a teaching box (LEC-T1-□), set the communication speed to 115.2 kbps.


**Terminating resistor** 

- \*4 A communication response time for 1 controller is approximately 30 ms.
- Refer to "Communication Response Time Guideline" for response times when several controllers are connected.
- \*5 For step data input, up to 12 controllers connectable.
- \*6 When compliance with UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.



## **Communication Response Time Guideline**

Response time between gateway unit and controllers depends on the number of controllers connected to the gateway unit. For response time, refer to the graph below.




This graph shows delay times between gateway unit and controllers. Fieldbus network delay time is not included.


#### **Dimensions**

## Screw mounting (LEC-G□□□)


### Applicable Fieldbus protocol: CC-Link Ver. 2.0




#### Applicable Fieldbus protocol: DeviceNet™



#### Applicable Fieldbus protocol: PROFIBUS DP



#### Applicable Fieldbus protocol: EtherNet/IP™




<sup>■</sup>Trademark DeviceNet™ is a trademark of ODVA. EtherNet/IP™ is a trademark of ODVA.

## Gateway Unit **LEC-G** Series


#### **Dimensions**

#### DIN rail mounting (LEC-G□□□D)


#### Applicable Fieldbus protocol: CC-Link Ver. 2.0




#### Applicable Fieldbus protocol: DeviceNet™



#### Applicable Fieldbus protocol: PROFIBUS DP




#### Applicable Fieldbus protocol: EtherNet/IP™



## DIN rail AXT100-DR-□

\* For □, enter a number from the No. line in the table below.
 Refer to the dimension drawings above for the mounting dimensions.



L Dime	nsions	[mm]
NIa	- 4	

No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
L	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5



AC Servo Motor


LEY

## **Wiring Example**

\* The power supply plug is an accessory. Power Supply Connector: CN1 <Applicable cable size> AWG20 (0.5 mm²), cover diameter 2.0 mm or less

CN1 Power Supply Connector Terminal for LEC-G (PHOENIX CONTACT FK-MC0.5/5-ST-2.5)

		,
Terminal name	Function	Details
EMG +	EMG signal output +	Output terminal of the emergency stop switch of the teaching box
EMG -	EMG signal output -	Output terminal of the emergency stop switch of the teaching box
24V	Power supply + terminal	Power supply terminal of the Gateway unit (Power to the teaching
0V	Power supply – terminal	box is supplied from this terminal)
FG	FG terminal	Grounding terminal




## **Programless Controller**

## **LECP1** Series





### **How to Order**



### **A** Caution

#### [CE-compliant products]

EMC compliance was tested by combining the electric actuator LE series and the controller LEC series. The EMC depends on the configuration of the customer's control panel and the relationship with other electrical equipment and wiring. Therefore, compliance with the EMC directive cannot be certified for SMC components incorporated into the customer's equipment under actual operating conditions. As a result, it is necessary for the customer to verify compliance with the EMC directive for the machinery and equipment as a whole.

[UL-compliant products]

When compliance with UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.

## The controller is sold as single unit after the compatible actuator is set.

Confirm that the combination of the controller and actuator is correct.

Refer to the operation manual for using the products. Please download it via our website, https://www.smc.eu

## **Specifications**

**Basic Specifications** 

Item	LECP1
Compatible motor	Step motor (Servo/24 VDC)
Power supply*1	Power supply voltage: 24 VDC ±10 %*2
Power supply	[Including the motor drive power, control power supply, stop, lock release]
Parallel input	6 inputs (Photo-coupler isolation)
Parallel output	6 outputs (Photo-coupler isolation)
Stop points	14 points (Position number 1 to 14(E))
Compatible encoder	Incremental A/B phase (800 pulse/rotation)
Memory	EEPROM
LED indicator	LED (Green/Red) one of each
7-segment LED display*3	1 digit, 7-segment display (Red) Figures are expressed in hexadecimal ("10" to "15" in decimal number are expressed as "A" to "F")
Lock control	Forced-lock release terminal*4
Cable length [m]	I/O cable: 5 or less, Actuator cable: 20 or less
Cooling system	Natural air cooling
Operating temperature range [°C]	0 to 40 (No freezing)
Operating humidity range [%RH]	90 or less (No condensation)
Storage temperature range [°C]	−10 to 60 (No freezing)
Storage humidity range [%RH]	90 or less (No condensation)
Insulation resistance [M $\Omega$ ]	Between the housing and SG terminal: 50 (500 VDC)
Weight [g]	130 (Screw mounting), 150 (DIN rail mounting)

- \*1 Do not use the power supply of "inrush current prevention type" for the controller input power supply. When compliance with UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.
- \*2 The power consumption changes depending on the actuator model. Refer to the each actuator's operation manual, etc., for details.
- \*3 "10" to "15" in decimal number are displayed as follows in the 7-segment LED.



\*4 Applicable to non-magnetising locks


207



E

AC Servo Motor

### **Controller Details**




No.	Display	Description	Details					
1	PWR	Power supply LED	Power supply ON/Servo ON: Green turns on Power supply ON/Servo OFF: Green flashes					
2	ALM	Alarm LED	With alarm : Red turns on Parameter setting : Red flashes					
3	_	Cover	Change and protection of the mode switch (Close the cover after changing switch)					
4	_	FG	Frame ground (Tighten the screw with the washer when mounting the controller. Connect the ground wire.)					
(5)	_	Mode switch	Switch the mode between manual and auto.					
6	_	7-segment LED	Stop position, the value set by $\ensuremath{\$}$ and alarm information are displayed.					
7	SET	Set button	Decide the settings or drive operation in Manual mode.					
8	_	Position selecting switch	Assign the position to drive (1 to 14), and the origin position (15).					
9	MANUAL	Manual forward button	Perform forward jog and inching.					
10	WANGAL	Manual reverse button	Perform reverse jog and inching.					
11)	SPEED	Forward speed switch	16 forward speeds are available.					
12	SFLLD	Reverse speed switch	16 reverse speeds are available.					
13	ACCEL	Forward acceleration switch	16 forward acceleration steps are available.					
14)	ACCLL	Reverse acceleration switch	16 reverse acceleration steps are available.					
15	CN1 Power supply connector		Connect the power supply cable.					
16	CN2 Motor connector		Connect the motor connector.					
17)	① CN3 Encoder connector Connect the encoder connector.							
18	B CN4 I/O connector Connect I/O cable.							

## **How to Mount**


Controller mounting shown below.

1. Mounting screw (LECP1□□-□)



#### 2. Grounding

Tighten the screw with the washer when mounting the ground wire as shown below.




\* When size 25 or more of the LE series are used, the space between the controllers should be 10 mm or more.


## **⚠** Caution

- M4 screws, cable with crimping terminal and tooth lock washer are not included. Be sure to carry out grounding earth in order to ensure the noise tolerance.
- Use a watchmaker's screwdriver of the size shown below when changing position switch (8) and the set value of the speed/acceleration switch (1) to (14).

#### Size

End width L: 2.0 to 2.4 [mm] End thickness W: 0.5 to 0.6 [mm]







## Programless Controller LECP1 Series


### **Dimensions**

#### Screw mounting (LEC□1□□-□)



### DIN rail mounting (LEC□1□□D-□)





## DIN rail AXT100-DR-□

\* For  $\square$ , enter a number from the No. line in the table below.

Refer to the dimension drawings above for the mounting dimensions.

L	J	
12.5 (Pitch)	5.25	7.5
+++++++++++++++++++++++++++++++++++++++	5.5	(35)
+	1.25	<del></del>

### L Dimensions [mm]

No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14
L	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5
No.	15	16	17	18	19	20	21	22	23	24	25	26	27	28
L	198	210.5	223	235.5	248	260.5	273	285.5	298	310.5	323	335.5	348	360.5
No.	29	30	31	32	33	34	35	36	37	38	39	40		
L	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5		

#### **DIN rail mounting adapter**

LEC-1-D0 (with 2 mounting screws)

This should be used when the DIN rail mounting adapter is mounted onto a screw mounting type controller afterward.



LEY

## Wiring Example 1

 $\ast\,$  When you connect a CN1 power supply connector, use the power supply cable (LEC-CK1-1).  $\ast\,$  The power supply cable (LEC-CK1-1) is an accessory. **Power Supply Connector: CN1** 

#### **CN1 Power Supply Connector Terminal for LECP1**

	Terminal name Cable colour		Function	Details					
	0V	Blue	Common supply (–)	M 24V terminal/C 24V terminal/BK RLS terminal are common (–).					
	C 24V Brown Control supply		Motor power supply (+)	Motor power supply (+) supplied to the controller					
			Control power supply (+)	Control power supply (+) supplied to the controller					
			Lock release (+)	Input (+) for releasing the lock					

### Power supply cable for LECP1 (LEC-CK1-1)



### Wiring Example 2

When you connect a PLC to the CN4 parallel I/O connector, use the I/O cable (LEC-CK4-□). Parallel I/O Connector: CN4 The wiring changes depending on the type of parallel I/O (NPN or PNP).

#### **■**NPN

		Power supply 24 VDC
CN4		for I/O signal
COM+	1	<u></u>
COM-	2	<del>                                     </del>
OUT0	3	Load
OUT1	4	Load
OUT2	5	Load
OUT3	6	Load
BUSY	7	Load
ALARM	8	Load
IN0	9	<b>├</b> /
IN1	10	<b>⊢</b> ´∕−− <b>→</b>
IN2	11	H
IN3	12	<b>⊢</b> ∕
RESET	13	<b>⊢</b> ∕
STOP	14	⊬ <i>∕</i>
		, /

CN4		Power supply 24 VDC for I/O signal
COM+	1	→ ⊢
COM-	2	<b>———</b>
OUT0	3	Load
OUT1	4	Load
OUT2	5	Load
OUT3	6	Load
BUSY	7	Load
ALARM	8	Load
IN0	9	$\vdash$
IN1	10	H
IN2	11	H
IN3	12	H
RESET	13	<del>-</del>
STOP	14	H
		- /

Input Signal

iliput Signai										
Name		Details								
COM+	Conne	Connects the power supply 24 V for input/output signal								
COM-	Conne	cts the powe	er supply 0 V	for input/ou	ıtput signal					
IN0 to IN3	• Instru	Instruction to drive (input as a combination of IN0 to IN3)     Instruction to return to origin (IN0 to IN3 all ON simultaneously)     Example - (instruction to drive for position no. 5)								
		IN3 OFF	IN2 ON	IN1 OFF	IN0 ON					
RESET	Alarm reset and operation interruption  During operation: deceleration stop from position at which signal is input (servo ON maintained)  While alarm is active: alarm reset									
STOP	Instructi	on to stop (afte	er maximum de	eceleration sto	p, servo OFF)					

**Output Signal** 

Name	Details					
OUT0 to OUT3	Turns on when the positioning or pushing is completed. (Output is instructed in the combination of OUT0 to 3.)  Example - (operation complete for position no. 3)					
		OUT3 OFF	OUT2 OFF	OUT1 ON	OUT0 ON	
BUSY	Outputs when the actuator is moving					
*ALARM*1	Not output when alarm is active or servo OFF					
4.0: 1.6			٥,			

<sup>\*1</sup> Signal of negative-logic circuit (N.C.)

#### Input Signal [IN0 - IN3] Position Number Chart O: OFF ●: ON

Position number	IN3	IN2	IN1	IN0
1 Osition number	1110	11142	1111	1110
1	O	0	0	
2	0	0	•	0
3	0	0	•	
4	0	•	0	0
5	0	•	0	•
6	0	•	•	0
7	0	•	•	•
8	•	0	0	0
9	•	0	0	•
10 (A)	•	0	•	0
11 (B)	•	0	•	•
12 (C)	•	•	0	0
13 (D)	•	•	0	
14 (E)	•	•	•	0
Return to origin	•	•	•	


Output Signal [OUT0 - OU	T31 Position Number Chart	O: OFF ●: ON

Output Signal [OUTO - OUT3] Position Number Chart O: OFF •: C					
Position number	OUT3	OUT2	OUT1	OUT0	
1	0	0	0		
2	0	0	•	0	
3	0	0	•		
4	0	•	0	0	
5	0	•	0	•	
6	0	•	•	0	
7	0	•	•		
8	•	0	0	0	
9	•	0	0	•	
10 (A)	•	0	•	0	
11 (B)	•	0	•	•	
12 (C)	•	•	0	0	
13 (D)	•	•	0	•	
14 (E)	•	•	•	0	
Return to origin	•	•	•	•	

## Programless Controller LECP1 Series


## **Signal Timing**






\* "\*ALARM" is expressed as a negative-logic circuit.

(2) Positioning Operation







211



#### (4) Stop by the STOP Signal




### (5) Alarm Reset





\* "\*ALARM" is expressed as a negative-logic circuit.

AC Servo Motor

**Options: Actuator Cable** 









Robotic cable

(Flexible cable)


Standard cable

S






Weight		
Product no.	Weight [g]	Note
LE-CP-1-S	190	
LE-CP-3-S	280	Standard cable
LE-CP-5-S	460	
LE-CP-1	140	
LE-CP-3	260	
LE-CP-5	420	
LE-CP-8	790	Robotic cable
LE-CP-A	980	
LE-CP-B	1460	
LE-CP-C	1940	



[Robotic cable, standard cable with lock and sensor for step motor (Servo/24 VDC)]




With lock and sensor

	Oubic type •
_	Robotic cable (Flexible cable)
S	Standard cable

W	/ei	a	ht

Product no.	Weight [g]	Note
LE-CP-1-B-S	240	
LE-CP-3-B-S	380	Standard cable
LE-CP-5-B-S	630	
LE-CP-1-B	190	
LE-CP-3-B	360	
LE-CP-5-B	590	
LE-CP-8-B	1060	Robotic cable
LE-CP-A-B	1320	
LE-CP-B-B	1920	
LE-CP-C-B	2620	




Signal	Connector A terminal no.		Cable color	Connector C terminal no.
A	B-1 <sup>4</sup>		Brown	2
Ā	A-1 '		Red	1
В	B-2 '		Orange	6
B	A-2		Yellow	5
COM-A/COM	B-3 ·		Green	3
COM-B/—	A-3		Blue	4
		Shield	Cable color	Connector D terminal no.
Vcc	B-4		Brown	12
GND	A-4		Black	13
Ā	B-5		Red	7
Α	A-5		Black	6
B	B-6		Orange	9
В	A-6	· · · · · · · · · · · · · · · · · · ·	Black	8
	Connector B	~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~	_	3
Signal	terminal no.			
Lock (+)	B-1 <sup>4</sup>		Red	4
Lock (-)	A-1 '		Black	5
Sensor (+)	B-3 '		Brown	1
Sensor (-)	A-3		Blue	2

## Programless Controller LECP1 Series

## **Options**

## [Power supply cable]

## LEC-CK1-1




Terminal name	Covered colour	Function
0V	Blue	Common supply (-)
M 24V	White	Motor power supply (+)
C 24V	Brown	Control power supply (+)
BK RLS	Black	Lock release (+)

\* Conductor size: AWG20

Weight: 90 g

### [I/O cable]



Controller side			PLC side	
(11) (30)	(6.7.9)	<i>a</i>	(60)	(10)

(L)

Terminal no.	Insulation colour	Dot mark	Dot colour	Function
1	Light brown	•	Black	COM+
2	Light brown		Red	COM-
3	Yellow		Black	OUT0
4	Yellow		Red	OUT1
5	Light green		Black	OUT2
6	Light green		Red	OUT3
7	Gray		Black	BUSY
8	Gray		Red	ALARM
9	White		Black	IN0
10	White		Red	IN1
11	Light brown		Black	IN2
12	Light brown		Red	IN3
13	Yellow		Black	RESET
14	Yellow		Red	STOP

<sup>\*</sup> Conductor size: AWG26

Weight								
Product no.	Weight [g]							
LEC-CK4-1	100							
LEC-CK4-3	200							
LEC-CK4-5	330							

<sup>\*</sup> Parallel I/O signal is valid in auto mode. While the test function operates at manual mode, only the output is valid.

AC Servo Motor

## **Step Motor Driver** LECPA Series





#### How to Order

#### **⚠** Caution

#### [CE-compliant products]

- 1 EMC compliance was tested by combining the electric actuator LE series and the LECPA series. The EMC depends on the configuration of the customer's control panel and the relationship with other electrical equipment and wiring. Therefore, compliance with the EMC directive cannot be certified for SMC components incorporated into the customer's equipment under actual operating conditions. As a result, it is necessary for the customer to verify compliance with the EMC directive for the machinery and equipment as a whole.
- 2 For the LECPA series (step motor driver), EMC compliance was tested by installing a noise filter set (LEC-NFA).
  - Refer to page 220 for the noise filter set. Refer to the LECPA Operation Manual for installation.

#### [UL-compliant products]

When compliance with UL is required, the electric actuator and driver should be used with a UL1310 Class 2 power supply.

## LECP AP **Driver type**

#### Pulse input type (NPN) Pulse input type (PNP)

#### I/O cable length [m]

_	None
1	1.5
3	3*1
5	5* <sup>1</sup>

Pulse input usable only with differential. Only 1.5 m cables usable with open collector.

Driver inounting								
_	Screw mounting							
<b>D</b> *1	DIN rail							

The DIN rail is not included. Order it separately.

#### Actuator part number

EY16B-100

Without cable specifications and actuator options Example: Enter "LEY16B-100" for the LEY16B-100B-R16N1

Blank controller\*1

\*1 Requires dedicated software (LEC-BCW)


- When controller equipped type is selected when ordering the LE series, you do not need to order this driver.
- \* When pulse signals are open collector, order the current limiting resistor (LEC-PA-R
  ) separately.

## The driver is sold as single unit after the compatible actuator is set.

Confirm that the combination of the driver and actuator is correct.

#### <Check the following before use.>

- 1) Check the actuator label for the model number. This number should match that of the driver.
- 2 Check that the Parallel I/O configuration matches (NPN or PNP).



Refer to the operation manual for using the products. Please download it via our website,

#### Precautions for blank controllers (LECPA□□-BC)

A blank controller is a controller to which the customer can write the data of the actuator it is to be combined and used with. Use the dedicated software (LEC-BCW) for data writing.

- · Please download the dedicated software (LEC-BCW) via our website.
- Order the communication cable for controller setting (LEC-W2A-C) separately to use this software.

SMC website https://www.smc.eu

## **Specifications**

Item	LECPA							
Compatible motor	Step motor (Servo/24 VDC)							
	Power voltage: 24 VDC ±10 %*2							
Power supply*1	[Including motor drive power, control power, stop, lock release]							
Parallel input	5 inputs (Except photo-coupler isolation, pulse input terminal, COM terminal)							
Parallel output	9 outputs (Photo-coupler isolation)							
Dulas signal input	Maximum frequency: 60 kpps (Open collector), 200 kpps (Differential)							
Pulse signal input	Input method: 1 pulse mode (Pulse input in direction), 2 pulse mode (Pulse input in differing directions)							
Compatible encoder	Incremental A/B phase (Encoder resolution: 800 pulse/rotation)							
Serial communication	RS485 (Modbus protocol compliant)							
Memory	EEPROM							
LED indicator	LED (Green/Red) one of each							
Lock control	Forced-lock release terminal*3							
Cable length [m]	I/O cable: 1.5 or less (Open collector), 5 or less (Differential), Actuator cable: 20 or less							
Cooling system	Natural air cooling							
Operating temperature range [°C]	0 to 40 (No freezing)							
Operating humidity range [%RH]	90 or less (No condensation)							
Storage temperature range [°C]	-10 to 60 (No freezing)							
Storage humidity range [%RH]	90 or less (No condensation)							
Insulation resistance [MΩ]	Between the housing and SG terminal: 50 (500 VDC)							
Weight [q]	120 (Screw mounting), 140 (DIN rail mounting)							


- Do not use the power supply of "inrush current prevention type" for the driver power supply. When compliance with UL is required, the electric actuator and driver should be used with a UL1310 Class 2 power supply.
- \*2 The power consumption changes depending on the actuator model. Refer to the specifications of actuator for more details
- \*3 Applicable to non-magnetising locks




## **LECPA** Series

#### **How to Mount**

a) Screw mounting (LECPA□□-□) (Installation with two M4 screws)




b) DIN rail mounting (LECPA D-D) (Installation with the DIN rail)



\* The space between the drivers should be 10 mm or more.

## DIN rail AXT100-DR-□

For □, enter a number from the No. line in the table below.
 Refer to the dimension drawings on page 216 for the mounting dimensions.



#### L Dimensions [mm]

No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
	1										01	02	00		- 00	00	0,	00	- 00	


### **DIN rail mounting adapter**

#### LEC-2-D0 (with 2 mounting screws)


This should be used when the DIN rail mounting adapter is mounted onto a screw mounting type driver afterward.


#### **Dimensions**

#### a) Screw mounting (LECPA□□-□)



#### b) DIN rail mounting (LECPA□□D-□)






#### Wiring Example 1

\* The power supply plug is an accessory. Power Supply Connector: CN1 <Applicable cable size> AWG20 (0.5 mm²), cover diameter 2.0 mm or less

#### CN1 Power Supply Connector Terminal for LECPA (PHOENIX CONTACT FK-MC0.5/5-ST-2.5)


Terminal name	Function	Details
0V	Common supply (-)	M 24V terminal/C 24V terminal/EMG terminal/BK RLS terminal are common (–).
M 24V	Motor power supply (+)	Motor power supply (+) supplied to the driver
C 24V	Control power supply (+)	Control power supply (+) supplied to the driver
EMG	Stop (+)	Input (+) for releasing the stop
BK RLS	Lock release (+)	Input (+) for releasing the lock



# **LECPA** Series

#### Wiring Example 2

#### LECPAN□□-□ (NPN)



- \*1 For pulse signal wiring method, refer to "Pulse Signal Wiring Details".
- \*2 Output when the power supply of the driver is ON. (N.C.)

#### Input Signal

input Oignai				
Name	Details			
COM+	Connects the power supply 24 V for input/output signal			
COM-	Connects the power supply 0 V for input/output signal			
SETUP	Instruction to return to origin			
RESET	Alarm reset			
SVON	Servo ON instruction			
CLR	Deviation reset			
TL	Instruction to pushing operation			

#### LECPAP□□-□ (PNP)

	CN5									Power su	
Terminal name	Function	Pin no.	(*)			ς.				for I/O sig	
COM+	24 V	1	+		$\vdash$	+				<del></del>	- ٦
COM-	0 V	2	+		+	+					+
NP+	Pulse signal	3	-		$\cap$	-	— )				
NP-	Pulse signal	4	+		-	+	- [	*1			
PP+	Pulse signal	5	+	-	$\leftarrow$	+	- [	*1			
PP-	Pulse signal	6	+		+	+	_				
SETUP	Input	7	+	-	$\leftarrow$	+					
RESET	Input	8	+		-	+				-	
SVON	Input	9	÷		$\leftarrow$	+					
CLR	Input	10	+		+	+					
TL	Input	11	+			+					
TLOUT	Output	12	+		$\vdash$	+			Load	d	+
WAREA	Output	13	+	:	$\leftarrow$	÷			Load	d	+
BUSY	Output	14	÷		H	+			Load	d	+
SETON	Output	15	+	-	$\leftarrow$	+			Load	d	+
INP	Output	16				-			Load	d ———	ł
SVRE	Output	17	÷		$\vdash$	÷			Load	d	+
*ESTOP*2	Output	18	+		-	+			Load	b	+
*ALARM*2	Output	19	+		$\leftarrow$	+			Load	b	+
AREA	Output	20	÷	-	H	1			Load	d	J
	FG	Round terminal 0.5-5	7								


#### **Output Signal**

<u> </u>			
Name	Details		
BUSY	Outputs when the actuator is operating		
SETON	Outputs when returning to origin		
INP	Outputs when target position is reached		
SVRE	Outputs when servo is on		
*ESTOP*3	Not output when EMG stop is instructed		
*ALARM*3 Not output when alarm is generated			
AREA Outputs within the area output setting rang			
WAREA	Outputs within W-AREA output setting range		
TLOUT	Outputs during pushing operation		
O Cinnel of the method lends of the CN (N.C.)			


<sup>\*3</sup> Signal of negative-logic circuit ON (N.C.)

#### **Pulse Signal Wiring Details**

#### • Pulse signal output of positioning unit is differential output



#### • Pulse signal output of positioning unit is open collector output



\*1 Connect the current limiting resistor R in series to correspond to the pulse signal voltage.

Pulse signal power supply voltage	Current limiting resistor R specifications	Current limiting resistor part no.
24 VDC ±10 %	3.3 kΩ ±5 % (0.5 W or more)	LEC-PA-R-332
5 VDC ±5 %	390 Ω ±5 % (0.1 W or more)	LEC-PA-R-391



Model Selection

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

LEY AC Servo Motor

LEYG


25A-LEY LEY-X5 Environment

LECA6 LEC-G

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECP1 LECPA


LECS AC Servo Motor LECY

**Signal Timing** 




"\*ALARM" and "\*ESTOP" are expressed as negative-logic circuits.

**Positioning Operation** 




#### **Alarm Reset**



\* "\*ALARM" is expressed as a negative-logic circuit.

**Pushing Operation** 





\* If pushing operation is stopped when there is no pulse deviation, the moving part of the actuator may pulsate.

#### **LECPA** Series

#### **Options: Actuator Cable**









AC Servo Motor

#### [I/O cable]

**Options** 



Pulse input usable only with differential. Only 1.5 m cables usable with open collector



Pin	Insulation	Dot	Dot
no.	colour	mark	colour
1	Light brown		Black
2	Light brown		Red
3	Yellow		Black
4	Yellow		Red
5	Light green		Black
6	Light green		Red
7	Gray		Black
8	Gray		Red
9	White		Black
10	White		Red
11	Light brown		Black

Pin	Insulation	Dot	Dot
no.	colour	colour mark colo	
12	Light brown ■■ Red		Red
13	Yellow		Black
14	Yellow		Red
15	Light green		Black
16	Light green ■■ Red		Red
17	Gray ■■ Black		Black
18	Gray		Red
19	White		Black
20	White ■■ Red		Red
Round terminal 0.5-5	Green		


#### Weight


Product no.	Weight [g]
LEC-CL5-1	190
LEC-CL5-3	370
LEC-CL5-5	610

#### [Noise filter set] **Step Motor Driver (Pulse Input Type)**

# LEC-NFA

Contents of the set: 2 noise filters (Manufactured by WURTH ELEKTRONIK: 74271222)





\* Refer to the LECPA series Operation Manual for installation.

#### [Current limiting resistor]

This optional resistor (LEC-PA-R-□) is used when the pulse signal output of the positioning unit is open collector output.

# LEC-PA-R-


#### **Current limiting resistor**

Symbol	Resistance	Pulse signal			
Symbol	nesisiance	power supply voltage			
332	3.3 kΩ ±5 %	24 VDC ±10 %			
391	390 Ω ±5 %	5 VDC ±5 %			

- Select a current limiting resistor that corresponds to the pulse signal power supply voltage.
- For the LEC-PA-R-□, two pieces are shipped as a set.
- For pulse signal wiring details, refer to page 217.

## **LEC** Series

# **Communication Cable for Controller Setting/LEC-W2A-**□



# LEC-W2A-C Communication cable LEC-W2-U USB cable

#### **Compatible Controller/Driver**

Step data input type PLECA6 Series
Pulse input type LECPA Series

PStep Motor Controller JXCE1/91/P1/D1/L1 Series

\* When connecting to a JXCE1/91/P1/D1/L1 series product, use a conversion cable (P5062-5) as a relay.


#### **Hardware Requirements**

OS	Windows <sup>®</sup> 7, Windows <sup>®</sup> 8.1, Windows <sup>®</sup> 10
Communication interface	USB 1.1 or USB 2.0 ports
Display	1024 x 768 or more

<sup>\*</sup> Windows®7, Windows®8.1 and Windows®10 are registered trademarks of Microsoft Corporation in the United States.

#### Screen Example


#### Easy mode screen example



#### Easy operation and simple setting

- Allowing to set and display actuator step data such as position, speed, force, etc.
- Setting of step data and test drive can be performed on the same page.
- Can be used to jog and move at a constant rate

#### Normal mode screen example



#### **Detailed setting**

- Step data can be set in detail.
- Signals and terminal status can be monitored.
- Parameters can be set.
- JOG and constant rate movement, return to origin, test drive and testing of forced output can be performed.






LEY

AC Servo Motor

# **Teaching Box/LEC-T1**



#### **How to Order**



#### **Specifications**

Item	Description
Switch	Stop switch, Enable switch (Option)
Cable length [m]	3
Enclosure	IP64 (Except connector)
Operating temperature range [°C]	5 to 50
Operating humidity range [%RH]	90 or less (No condensation)
Weight [a]	350 (Except cable)

#### [CE-compliant products]

The EMC compliance of the teaching box was tested with a step motor controller (servo/24 VDC) and an

#### [UL-compliant products]

When compliance with UL is required, the electric actuator and driver should be used with a UL1310 Class 2 power supply.

#### **Easy Mode**

**Option** 

Standard functions

 Chinese character display • Stop switch is provided.

• Enable switch is provided.

Function	Details
Step data	Setting of step data
Otop data	
Jog	Jog operation     Return to origin
Test	<ul> <li>1 step operation*<sup>1</sup></li> <li>Return to origin</li> </ul>
Monitor	<ul><li>Display of axis and step data no.</li><li>Display of two items selected from Position, Speed, Force.</li></ul>
ALM	<ul><li>Active alarm display</li><li>Alarm reset</li></ul>
TB setting	Reconnection of axis (Ver. 1.**)     Displayed language setting (Ver. 2.**)     Setting of easy/normal mode     Setting step data and selection of items from easy mode monitor


#### Menu Operations Flowchart

	Menu Operatio	ns Flo	wchart
	Menu		Data
	Data		Step data no.
	Monitor		Setting of two items selected below
	Jog		Ver. 1.**:
	Test		Position, Speed, Force, Acceleration, Deceleration
	ALM		Ver. 2.**:
data no. selected	TB setting		Position, Speed, Pushing force, Acceleration, Deceleration, Movement MOD, Trigger LV, Pushing speed, Moving force, Area 1, Area 2, In position
orce.			Monitor
		$\vdash$	Display of step no.
			Display of two items selected below
er. 1.**)			(Position, Speed, Force)
ing			Jog
2000		<u> </u>	Return to origin
node selection			Jog operation
monitor			
7 1110111101			Test*1
			1 step operation
			AL M
			ALM
			Active alarm display
			Alarm reset
			TB setting
			Reconnect (Ver. 1.**)
			Japanese/English (Ver. 2.**)
*1 Not co	ompatible with the LECPA		Easy/Normal Set item
* 1 INOL CC	impatible with the LLOI A		Section


# **LEC** Series

#### **Normal Mode**

Function	Details
Step data	Step data setting
Parameter	Parameters setting
Test	Jog operation/Constant rate movement     Return to origin     Test drive*1     (Specify a maximum of 5 step data and operate.)     Forced output     (Forced signal output, Forced terminal output)*2
Monitor	Drive monitor     Output signal monitor*2     Input signal monitor*2     Output terminal monitor     Input terminal monitor
ALM	Active alarm display     (Alarm reset)     Alarm log record display
File	<ul> <li>Data saving Save the step data and parameters of the driver which is being used for communication (it is possible to save four files, with one set of step data and parameters defined as one file).</li> <li>Load to driver Loads the data which is saved in the teaching box to the driver which is being used for communication.</li> <li>Delete the saved data.</li> <li>File protection (Ver. 2.**)</li> </ul>
TB setting	Display setting     (Easy/Normal mode)     Language setting     (Japanese/English)     Backlight setting     LCD contrast setting     Beep sound setting     Max. connection axis     Distance unit (mm/inch)
Reconnect	Reconnection of axis



#### **Dimensions**



No.	Description	Function			
1	LCD	A screen of liquid crystal display (with backlight)			
2	Ring	A ring for hanging the teaching box			
3	Stop switch	When switch is pushed in, the switch locks and stops. The lock is released when it is turned to the right.			
4	Stop switch guard	A guard for the stop switch			
5	Enable switch (Option)	Prevents unintentional operation (unexpected operation) of the jog test function.  Other functions such as data change are not covered.			
6	Key switch	Switch for each input			
7	Cable	Length: 3 meters			
8	Connector	A connector connected to CN4 of the driver			




# **Step Motor Controller**

JXCE1/91/P1/D1/L1 Series ( E ROHS)





#### **How to Order**



**Option** 

_	Without option
S	With straight type DeviceNet <sup>™</sup> communication plug for JXCD1
Т	With T-branch type DeviceNet™ communication plug for JXCD1

\* Select "--" for anything other than JXCD1.

#### Actuator part number


Without cable specifications and actuator options Example: Enter "LEY16B-100" for the LEY16B-100B-R16N1. Blank controller\*1

\*1 Requires dedicated software (JXC-BCW)

#### The controller is sold as single unit after the compatible actuator is set.

Confirm that the combination of the controller and actuator is correct.

(1) Check the actuator label for the model number. This number should match that of the controller.



Refer to the operation manual for using the products. Please download it via our website, https://www.smc.eu

#### **Precautions for blank controllers (JXC**□1□□-BC)

A blank controller is a controller to which the customer can write the data of the actuator it is to be combined and used with. Use the dedicated software (JXC-BCW) for data writing.

- Please download the dedicated software (JXC-BCW) via our website.
- Order the controller setting kit (JXC-W2) separately to use this software.

SMC website: https://www.smc.eu



## JXCE1/91/P1/D1/L1 Series

#### **Specifications**

	M	odel	JXCE1	JXC91	JXCP1	JXCD1	JXCL1				
Network			EtherCAT®	EtherNet/IP™	PROFINET	DeviceNet™	IO-Link				
Co	ompatible i	notor		S	tep motor (Servo/24 VD0	C)					
Po	wer suppl	у		Pov	wer voltage: 24 VDC $\pm$ 10	) %					
Cu	rrent consun	nption (Controller)	200 mA or less	130 mA or less	200 mA or less	100 mA or less	100 mA or less				
Co	ompatible e	encoder		Incremen	tal A/B phase (800 pulse	e/rotation)					
Suc	Applicable	Protocol	EtherCAT®*2	EtherNet/IP <sup>TM*2</sup>	PROFINET*2	DeviceNet™	IO-Link				
ificatio	system	Version*1	Conformance Test Record V.1.2.6	Volume 1 (Edition 3.14) Volume 2 (Edition 1.15)	Specification Version 2.32	Volume 1 (Edition 3.14) Volume 3 (Edition 1.13)	Version 1.1 Port Class A				
Communication specifications	Communication speed		100 Mbps*2	10/100 Mbps*2 (Automatic negotiation)	100 Mbps*2	125/250/500 kbps	230.4 kbps (COM3)				
cati	र्ह्हे Configuration file*3		ESI file	EDS file	GSDML file	EDS file	IODD file				
nmuni	I/O occupation area		Input 20 bytes Output 36 bytes	Input 36 bytes Output 36 bytes	Input 36 bytes Output 36 bytes	Input 4, 10, 20 bytes Output 4, 12, 20, 36 bytes	Input 14 bytes Output 22 bytes				
ខ	Terminati	ng resistor	Not included								
Me	emory		EEPROM								
LE	D indicate	r	PWR, RUN, ALM, ERR	PWR, ALM, MS, NS	PWR, ALM, SF, BF	PWR, ALM, MS, NS	PWR, ALM, COM				
Ca	able length	[m]	Actuator cable: 20 or less								
Co	ooling syst	em	Natural air cooling								
<u> </u>		erature range [°C]	0 to 40 (No freezing)								
Op	erating hum	idity range [%RH]	90 or less (No condensation)								
In	sulation re	sistance [M $\Omega$ ]		Between all exter	nal terminals and the ca						
W	eight [g]		220 (Screw mounting) 240 (DIN rail mounting)	210 (Screw mounting) 230 (DIN rail mounting)	220 (Screw mounting) 240 (DIN rail mounting)	210 (Screw mounting) 230 (DIN rail mounting)	190 (Screw mounting) 210 (DIN rail mounting)				

- \*1 Please note that versions are subject to change.
- \*2 Use a shielded communication cable with CAT5 or higher for the PROFINET, EtherNet/IP™, and EtherCAT®.
- \*3 The files can be downloaded from the SMC website.

#### ■Trademark

EtherNet/IP™ is a trademark of ODVA.

DeviceNet™ is a trademark of ODVA.

EtherCAT® is registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany.

#### **Example of Operation Command**

In addition to the step data input of 64 points maximum in each communication protocol, the changing of each parameter can be performed in real time via numerical data defined operation.

\* Numerical values other than "Moving force," "Area 1," and "Area 2" can be used to perform operation under numerical instructions from JXCL1.

#### <Application example> Movement between 2 points

	No.	Movement mode	Speed	Position	Acceleration	Deceleration	Pushing force	Trigger LV	Pushing speed	Moving force	Area 1	Area 2	In position
	0	1: Absolute	100	10	3000	3000	0	0	0	100	0	0	0.50
[	1	1: Absolute	100	100	3000	3000	0	0	0	100	0	0	0.50

#### <Step no. defined operation>

Sequence 1: Servo ON instruction

Sequence 2: Instruction to return to origin

Sequence 3: Specify step data No. 0 to input the DRIVE signal.

Sequence 4: Specify step data No. 1 after the DRIVE signal has been temporarily turned OFF to input the DRIVE signal.

#### <Numerical data defined operation>


Sequence 1: Servo ON instruction

Sequence 2: Instruction to return to origin

Sequence 3: Specify step data No. 0 and turn ON the input instruction flag (position). Input 10 in the target position. Subsequently the start flag turns ON.

Sequence 4: Turn ON step data No. 0 and the input instruction flag (position) to change the target position to 100 while the start flag is ON.


The same operation can be performed with any operation command.






# Step Motor Controller JXCE1/91/P1/D1/L1 Series

#### **Dimensions**







Model Selection

LEY

LEYG

LEY

LEYG

25A-LEY LEY-X5

LECA6

LEC-G

LECP1

LECPA

□XC

LECS

LECY


Specific Product Precautions


AC Servo Motor


Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

# JXCE1/91/P1/D1/L1 Series

#### **Dimensions**









L Dimensions [mm]

No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5



# Step Motor Controller JXCE1/91/P1/D1/L1 Series





weignt		
Product no.	Weight [g]	Note
LE-CP-1-B-S	240	
LE-CP-3-B-S	380	Standard cable
LE-CP-5-B-S	630	
LE-CP-1-B	190	
LE-CP-3-B	360	
LE-CP-5-B	590	
LE-CP-8-B	1060	Robotic cable
LE-CP-A-B	1320	
LE-CP-B-B	1920	
LE-CP-C-B	2620	

Wainbi

Signal  A A B B COM-A/COM COM-B/—	Connector A terminal no.  B-1 A-1 B-2 A-2 B-3 A-3		Cable color Brown Red Orange Yellow Green Blue	Connector C terminal no.  2 1 6 5 3 4
Vcc GND Ā A B B	B-4 A-4 B-5 A-5 B-6 A-6	Shield	Cable color Brown Black Red Black Orange Black	Connector D terminal no. 12 13 7 6 9 8
Signal  Lock (+)  Lock (-)  Sensor (+)  Sensor (-)	Connector B terminal no.  B-1  A-1  B-3  A-3		Red Black Brown Blue	3 4 5 1 2

Model Selection

LEY

LEYG

Ē

LEYG

LEY-X5

25A-LEY

LECA6

LEC-G

LECP1

LECPA

JXC

LECS

LECY

AC Servo Motor

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

Environment

AC Servo Motor

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)


# JXCE1/91/P1/D1/L1 Series

#### **Options**

#### ■ Controller setting kit JXC-W2


#### [Contents

- (1) Communication cable
- 2 USB cable
- 3 Controller setting software
- \* A conversion cable (P5062-5) is not required.




_	A kit includes:  Communication cable, USB cable, Controller setting software
С	Communication cable
U	USB cable
S	Controller setting software (CD-ROM)

#### 1 Communication cable JXC-W2-C




\* It can be connected to the controller directly.

#### 2 USB cable JXC-W2-U



#### ③ Controller setting software (CD-ROM) JXC-W2-S



#### ■ DIN rail mounting adapter LEC-3-D0

\* With 2 mounting screws


This should be used when the DIN rail mounting adapter is mounted onto a screw mounting type controller afterward.

#### ■ DIN rail AXT100-DR-□

\* For □, enter a number from the No. line in the table on page 227. Refer to the dimension drawings on pages 226 and 227 for the mounting dimensions.

#### **■**Power supply plug JXC-CPW

\* The power supply plug is an accessory.



000
(6)(5)(4)
$\bigcirc$
(3)(2)(1)

① C24V ④ 0V

② M24V ③ EMG

M24V ⑤ N.C. EMG ⑥ LK RLS

Power supply plug

ower cappry plag								
Terminal name	Function	Details						
0V	Common supply (-)	M24V terminal/C24V terminal/EMG terminal/LK RLS terminal are common (-).						
M24V	Motor power supply (+)	Motor power supply (+) of the controller						
C24V	Control power supply (+)	Control power supply (+) of the controller						
EMG	Stop (+)	Connection terminal of the external stop circuit						
LK RLS	Lock release (+)	Connection terminal of the lock release switch						

#### **■**Communication plug connector

#### For DeviceNet™

Straight type JXC-CD-S

T-branch type JXC-CD-T






#### Communication plug connector for DeviceNet™

- communication progression for Economic		
Terminal name	Details	
V+	Power supply (+) for DeviceNet™	
CAN_H	Communication wire (High)	
Drain	Grounding wire/Shielded wire	
CAN_L	Communication wire (Low)	
V–	Power supply (–) for DeviceNet™	

#### For IO-Link Straight type JXC-CL-S

 The communication plug connector for IO-Link is an accessory.



#### Communication plug connector for IO-Link

<u> </u>				
Terminal no.	Terminal name	Details		
1	L+	+24 V		
2	NC	N/A		
3	L-	0 V		
4	C/Q	IO-Link signal		

#### ■ Conversion cable P5062-5 (Cable length: 300 mm)



\* To connect the teaching box (LEC-T1-3□G□) or controller setting kit (LEC-W2) to the controller, a conversion cable is required.



# JXCE1/91/P1/D1/L1 Series **Precautions Related to Differences in Controller Versions**

LEY

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

LEYG

LEY AC Servo Motor

LEYG

25A-LEY LEY-X5

Environment

LECA6 LECP1 LEC-G

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECPA

□XC

LECY□ | LECS□ AC Servo Motor


As the controller version of the JXC series differs, the internal parameters are not compatible.


- If using the JXC□1□-BC, please use the latest version of the JXC-BCW (parameter writing tool).
- ■There are currently 3 versions available: version 1 products (V1.□ or S1.□), version 2 products (V2.□ or S2.□), and version 3 products (V3.□ or S3.□). Keep in mind that in order to write a backup file (.bkp) to another controller with the JXC-BCW, it needs to be the same version as the controller that created the file. (For example, a backup file created by a version 1 product can only be written to another version 1 product, and so on.)

#### Identifying Version Symbols




#### JXC□1 Series Version V3.□ or S3.□ Products







#### JXC□1 Series Version V2.□ or S2.□ Products





#### JXC□1 Series Version V1.□ or S1.□ Products






# LEC Series **Teaching Box/LEC-T1**





#### **How to Order**





The displayed language can be changed to English or Japanese.

#### **Specifications**

#### Standard functions

- Chinese character display
- Stop switch is provided.

#### **Option**

• Enable switch is provided.

Item	Description
Switch	Stop switch, Enable switch (Option)
Cable length [m]	3
Enclosure	IP64 (Except connector)
Operating temperature range [°C]	5 to 50
Operating humidity range [%RH]	90 or less (No condensation)
Weight [g]	350 (Except cable)

#### [CE-compliant products]

The EMC compliance of the teaching box was tested with a step motor controller (servo/24 VDC) and an applicable actuator.

#### [UL-compliant products]

When compliance with UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.

#### **Easy Mode**

Function	Details
Step data	Setting of step data
Jog	<ul><li>Jog operation</li><li>Return to origin</li></ul>
Test	1 step operation     Return to origin
Monitor	<ul> <li>Display of axis and step data no.</li> <li>Display of two items selected from Position, Speed, Force.</li> </ul>
ALM	Active alarm display     Alarm reset
TB setting	Reconnection of axis (Ver. 1.**)     Displayed language setting (Ver. 2.**)     Setting of easy/normal mode     Setting step data and selection of items from easy mode monitor

#### **Menu Operations Flowchart**


Menu		Data
Data		Step data no.
Monitor		Setting of two items selected below
Jog		Ver. 1.**:
Test		Position, Speed, Force, Acceleration, Deceleration
ALM		Ver. 2.**:
TB setting		Position, Speed, Pushing force, Acceleration, Deceleration, Movement MOD,
		Trigger LV, Pushing speed, Moving force, Area 1, Area 2, In position
		Monitor
	L	Display of step no.
		Display of two items selected below
		(Position, Speed, Force)
		lon
		Jog
		Return to origin
		Jog operation
		Test
		1 step operation
		ALM
	⊢	Active alarm display
		Alarm reset
		TB setting
		Reconnect (Ver. 1.**)
		Japanese/English (Ver. 2.**)
		Easy/Normal
		Set item




# Teaching Box LEC Series

#### **Normal Mode**

Function	Details
Step data	Step data setting
Parameter	Parameters setting
Test	<ul> <li>Jog operation/Constant rate movement</li> <li>Return to origin</li> <li>Test drive (Specify a maximum of 5 step data and operate.)</li> <li>Forced output (Forced signal output, Forced terminal output)</li> </ul>
Monitor	<ul> <li>Drive monitor</li> <li>Output signal monitor</li> <li>Input signal monitor</li> <li>Output terminal monitor</li> <li>Input terminal monitor</li> </ul>
ALM	<ul><li>Active alarm display (Alarm reset)</li><li>Alarm log record display</li></ul>
File	<ul> <li>Data saving         Save the step data and parameters         of the controller which is being         used for communication (it is         possible to save four files, with one         set of step data and parameters         defined as one file).</li> <li>Load to controller         Loads the data which is saved in the         teaching box to the controller which         is being used for communication.</li> <li>Delete the saved data.</li> <li>File protection (Ver. 2.**)</li> </ul>
TB setting	Display setting     (Easy/Normal mode)     Language setting     (Japanese/English)     Backlight setting     LCD contrast setting     Beep sound setting     Max. connection axis     Distance unit (mm/inch)
Reconnect	Reconnection of axis



#### **Dimensions**



No.	Description	Function	
1	LCD	A screen of liquid crystal display (with backlight)	
2	Ring	A ring for hanging the teaching box	
3	Stop switch	When switch is pushed in, the switch locks and stops. The lock is released when it is turned to the right.	
4	Stop switch guard	A guard for the stop switch	
5	Enable switch (Option)	Prevents unintentional operation (unexpected operation) of the jog test function.  Other functions such as data change are not covered.	
6	Key switch Switch for each input		
7	Cable Length: 3 meters		
8	Connector	A connector connected to CN4 of the controller	



LECS

AC Servo Motor LECY

# 3-Axis Step Motor Controller (EtherNet/IP Type)

# JXC92 Series




#### **How to Order**

#### ■ EtherNet/IP<sup>™</sup> Type (JXC92)

#### Controller





- Order the actuator separately, including the actuator cable. (Example: LEY16B-100-S1)
- \* For the "Speed-Work Load" graph of the actuator, refer to page 38.

#### **Specifications**

For the setting of functions and operation methods, refer to the operation manual on the SMC website. (Documents/Download --> Instruction Manuals)


#### EtherNet/IP™ Type (JXC92)


Item		Specifications	
Number of axes		Max. 3 axes	
Compatible motor Step motor (Servo/24 VDC)		Step motor (Servo/24 VDC)	
Compatible encoder Incremental A/B phase (Encoder resolution: 800 pulse/rotation)		Incremental A/B phase (Encoder resolution: 800 pulse/rotation)	
Power supply*1		Control power supply Power voltage: 24 VDC $\pm$ 10 % Max. current consumption: 500 mA Motor power supply Power voltage: 24 VDC $\pm$ 10 % Max. current consumption: Based on the connected actuator* <sup>2</sup>	
	Protocol	EtherNet/IP <sup>TM*3</sup>	
_	Communication speed	10 Mbps/100 Mbps (automatic negotiation)	
엹	Communication method	Full duplex/Half duplex (automatic negotiation)	
Communication	Configuration file	EDS file	
占	Occupied area	Input 16 bytes/Output 16 bytes	
Е	IP address setting range	Manual setting by switches: From 192.168.1.1 to 254, Via DHCP server: Arbitrary address	
l o	Vendor ID	7 h (SMC Corporation)	
0	Product type	2 Bh (Generic Device)	
	Product code	DEh	
Seria	al communication	USB2.0 (Full Speed 12 Mbps)	
Mem	ory	Flash-ROM	
LED	indicator	PWR, RUN, USB, ALM, NS, MS, L/A, 100	
Lock	control	Forced-lock release terminal*4	
Cabl	e length	Actuator cable: 20 m or less	
Cool	ing system	Natural air cooling	
Operating temperature range		0 °C to 40 °C (No freezing)	
Operating humidity range		90 % RH or less (No condensation)	
Stor	age temperature range	-10 °C to 60 °C (No freezing)	
	age humidity range	90 % RH or less (No condensation)	
	lation resistance	Between all external terminals and the case: 50 M $\Omega$ (500 VDC)	
Weig	jht	600 g (Screw mounting), 650 g (DIN rail mounting)	

- \*1 Do not use a power supply with inrush current protection for the motor drive power supply.
- \*2 Power consumption depends on the actuator connected. Refer to the actuator specifications for further details.
- \*3 EtherNet/IP™ is a trademark of ODVA.
- \*4 Applicable to non-magnetising locks




#### EtherNet/IP™ Type JXC92 **Screw mounting**






#### **DIN** rail mounting



#### **Controller Details**

EtherNet/IP™ Type JXC92



No.	Name	Description	Details
1	P1, P2	EtherNet/IP™ communication connector	Connect Ethernet cable.
2	NS, MS	Communication status LED	Displays the status of the EtherNet/IP™ communication
3	X100 X10 X1	IP address setting switches	Switch to set the 4th byte of the IP address by X1, X10 and X100.
4	PWR	Power supply LED (Green)	Power supply ON: Green turns on Power supply OFF: Green turns off
(5)	RUN	Operation LED (Green)	Running in EtherNet/IP™: Green turns on Running via USB communication: Green flashes Stopped: Green turns off
6	USB	USB connection LED (Green)	USB connected: Green turns on USB not connected: Green turns off
7	ALM	Alarm LED (Red)	With alarm: Red turns on Without alarm: Red turns off
8	USB	Serial communication connector	Connect to a PC via the USB cable.
9	ENC 1	Encoder connector (16 pins)	Axis 1: Connect the actuator cable.
10	MOT 1	Motor power connector (6 pins)	Axis 1. Connect the actuator cable.
11)	ENC 2	Encoder connector (16 pins)	Axis 2: Connect the actuator cable.
12	MOT 2	Motor power connector (6 pins)	Axis 2. Connect the actuator cable.
13	ENC 3	Encoder connector (16 pins)	Avia 2. Connect the actuator cable
14)	MOT 3	Motor power connector (6 pins)	Axis 3: Connect the actuator cable.
15	CI	Control power supply connector*1	Control power supply (+), All axes stop (+), Axis 1 lock release (+), Axis 2 lock release (+), Axis 3 lock release (+), Common (-)
16	M PWR	Motor power supply connector*1	Motor power supply (+), Motor power supply (-)

<sup>\*1</sup> Connectors are included. (Refer to page 239.)



Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

Model Selection

LEYG

LEY AC Servo Motor LEYG

25A-LEY LEY-X5 Environment

LECA6 LEC-G Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

LECP1 LECPA

JXC

LECS AC Servo Motor LECY

# 4-Axis Step Motor Controller (Parallel I/O/EtherNet/IP Type)

**JXC73/83/93** Series




#### **How to Order**

#### ■ Parallel I/O (JXC73/83)

Controller






<sup>\*</sup> Two I/O cables are included

#### ■ EtherNet/IP<sup>™</sup> Type (JXC93)







- Order the actuator separately, including the actuator cable. (Example: LEY16B-100-S1)
- \* For the "Speed-Work Load" graph of the actuator, refer to page 38.

#### **Specifications**

For the setting of functions and operation methods, refer to the operation manual on the SMC website. (Documents/Download --> Instruction Manuals)

#### Parallel I/O (JXC73/83)

Item	Specifications	
Number of axes	Max. 4 axes	
Compatible motor	Step motor (Servo/24 VDC)	
Compatible encoder Incremental A/B phase (Encoder resolution: 800 pulse/rotation)		
	Main control power supply Power voltage: 24 VDC ±10 %	
	Max. current consumption: 300 mA	
Power supply*1	Motor power supply, Motor control power supply (Common)	
	Power voltage: 24 VDC ±10 %	
	Max. current consumption: Based on the connected actuator*2	
Parallel input	16 inputs (Photo-coupler isolation)	
Parallel output	32 outputs (Photo-coupler isolation)	
Serial communication	USB2.0 (Full Speed 12 Mbps)	
Memory	Flash-ROM/EEPROM	
LED indicator PWR, RUN, USB, ALM		
Lock control Forced-lock release terminal*3		
Cable length	I/O cable: 5 m or less, Actuator cable: 20 m or less	
Cooling system	Natural air cooling	
Operating temperature range	0 °C to 40 °C (No freezing)	
Operating humidity range	90 % RH or less (No condensation)	
Storage temperature range	−10 °C to 60 °C (No freezing)	
Storage humidity range	90 % RH or less (No condensation)	
Insulation resistance	Between all external terminals and the case: 50 MΩ (500 VDC)	
Weight	1050 g (Screw mounting), 1100 g (DIN rail mounting)	

- \*1 Do not use a power supply with inrush current protection for the motor drive power and motor control power supply.
- \*2 Power consumption depends on the actuator connected. Refer to the actuator specifications for further details.
- \*3 Applicable to non-magnetising locks

For the setting of functions and operation methods, refer to the operation manual on the SMC website. (Documents/Download --> Instruction Manuals)

#### EtherNet/IP™ Type (JXC93)

	Net/IP Type (JAC93)				
Item		Specifications			
Number of axes		Max. 4 axes			
Compatible motor		Step motor (Servo/24 VDC)			
Compatible encoder		Incremental A/B phase (Encoder resolution: 800 pulse/rotation)			
Power supply*1		Main control power supply Power voltage: 24 VDC ±10 %			
	Protocol	EtherNet/IP™*4			
_	Communication speed	10 Mbps/100 Mbps (automatic negotiation)			
Communication	Communication method	Full duplex/Half duplex (automatic negotiation)			
ca	Configuration file	EDS file			
n	Occupied area	Input 16 bytes/Output 16 bytes			
שר	IP address setting range	Manual setting by switches: From 192.168.1.1 to 254, Via DHCP server: Arbitrary address			
ou	Vendor ID	7 h (SMC Corporation)			
0	Product type	2 Bh (Generic Device)			
	Product code	DCh			
Seria	I communication	USB2.0 (Full Speed 12 Mbps)			
Mem	ory	Flash-ROM/EEPROM			
LED	indicator	PWR, RUN, USB, ALM, NS, MS, L/A, 100			
Lock	control	Forced-lock release terminal*3			
Cable	e length	Actuator cable: 20 m or less			
Cool	ing system	Natural air cooling			
Operating temperature range		0 °C to 40 °C (No freezing)			
Oper	ating humidity range	90 % RH or less (No condensation)			
Storage temperature range		-10 °C to 60 °C (No freezing)			
Stora	ge humidity range	90 % RH or less (No condensation)			
Insul	ation resistance	Between all external terminals and the case: 50 M $\Omega$ (500 VDC)			
Weig	ht	1050 g (Screw mounting), 1100 g (DIN rail mounting)			

- \*1 Do not use a power supply with inrush current protection for the motor drive power and motor control power supply.

  \*2 Power consumption depends on the actuator connected. Refer to the actuator specifications for further details.

  \*3 Applicable to non-magnetising locks

  \*4 EtherNet/IP™ is a trademark of ODVA.





# **JXC73/83/93** Series

#### **Dimensions**


#### Parallel I/O JXC73/83

#### **Screw mounting**







#### **DIN** rail mounting




# EtherNet/IP™ Type JXC93 Screw mounting






#### **DIN rail mounting**



LEYG

### **Controller Details**


#### Parallel I/O JXC73/83



No.	Name	Description	Details
1	PWR Power supply LED (Green)		Power supply ON: Green turns on Power supply OFF: Green turns off
2	RUN	Operation LED (Green)	Running in parallel I/O: Green turns on Running via USB communication: Green flashes Stopped: Green turns off
3	USB	USB connection LED (Green)	USB connected: Green turns on USB not connected: Green turns off
4	ALM	Alarm LED (Red)	With alarm: Red turns on Without alarm: Red turns off
(5)	USB	Serial communication	Connect to a PC via the USB cable.
6	C PWR	Main control power supply connector (2 pins)*1	Main control power supply (+) (-)
7	I/O 1	Parallel I/O connector (40 pins)	Connect to a PLC via the I/O cable.
8	I/O 2	Parallel I/O connector (40 pins)	Connect to a PLC via the I/O cable.
9	ENC 1	Encoder connector (16 pins)	Axis 1: Connect the actuator cable.
10	MOT 1	Motor power connector (6 pins)	Axis 1. Connect the actuator cable.
11)	ENC 2	Encoder connector (16 pins)	Axis 2: Connect the actuator cable.
12	MOT 2	Motor power connector (6 pins)	Axis 2. Connect the actuator cable.
13	CI12	Motor control power supply connector*1	Motor control power supply (+), Axis 1 stop (+), Axis 1 lock release (+), Axis 2 stop (+), Axis 2 lock release (+)
14)	M PWR 1 2	Motor power supply connector*1	For Axis 1, 2. Motor power supply (+), Common (-)
15)	ENC 3	Encoder connector (16 pins)	Axis 3: Connect the actuator cable.
16	MOT 3	Motor power connector (6 pins)	Axis 5. Connect the actuator cable.
17)	ENC 4	Encoder connector (16 pins)	Axis 4: Connect the actuator cable.
18	MOT 4	Motor power connector (6 pins)	AND 4. Confident the actuator capie.
19	CI 3 4	Motor control power supply connector*1	Motor control power supply (+), Axis 3 stop (+), Axis 3 lock release (+), Axis 4 stop (+), Axis 4 lock release (+)
20	M PWR 3 4	Motor power supply connector*1	For Axis 3, 4. Motor power supply (+), Common (-)

<sup>\*1</sup> Connectors are included. (Refer to page 239.)

#### EtherNet/IP™ Type JXC93



No.	Name	Description	Details
1	PWR	Power supply LED (Green)	Power supply ON: Green turns on Power supply OFF: Green turns off
2	RUN	Operation LED (Green)	Running in EtherNet/IP™: Green turns on Running via USB communication: Green flashes Stopped: Green turns off
3	USB	USB connection LED (Green)	USB connected: Green turns on USB not connected: Green turns off
4	ALM	Alarm LED (Red)	With alarm: Red turns on Without alarm: Red turns off
(5)	USB	Serial communication	Connect to a PC via the USB cable.
6	C PWR	Main control power supply connector (2 pins)* $^{1}$	Main control power supply (+) (-)
7	x100 x10 x1	IP address setting switches	Switch to set the 4th byte of the IP address by X1, X10 and X100.
8	MS, NS	Communication status LED	Displays the status of the EtherNet/IP™ communication
9	ENC 1	Encoder connector (16 pins)	Axis 1: Connect the actuator cable.
10	MOT 1	Motor power connector (6 pins)	Axis 1. Connect the actuator cable.
11)	ENC 2	Encoder connector (16 pins)	Axis 2: Connect the actuator cable.
12	MOT 2	Motor power connector (6 pins)	Axis 2. Connect the actuator cable.
13	CI 1 2	Motor control power supply connector*1	Motor control power supply (+), Axis 1 stop (+), Axis 1 lock release (+), Axis 2 stop (+), Axis 2 lock release (+)
14)	M PWR 1 2	Motor power supply connector*1	For Axis 1, 2. Motor power supply (+), Common (–)
15)	ENC 3	Encoder connector (16 pins)	Axis 3: Connect the actuator cable.
16	MOT 3	Motor power connector (6 pins)	Axis 5. Confident tile actuator cable.
17)	ENC 4	Encoder connector (16 pins)	Axis 4: Connect the actuator cable.
18	MOT 4	Motor power connector (6 pins)	Axis 4. Confident the actuator capie.
19	CI34	Motor control power supply connector*1	Motor control power supply (+), Axis 3 stop (+), Axis 3 lock release (+), Axis 4 stop (+), Axis 4 lock release (+)
20	M PWR 3 4	Motor power supply connector*1	For Axis 3, 4. Motor power supply (+), Common (-)
21)	P1, P2	EtherNet/IP™ communication connector	Connect Ethernet cable.

<sup>\*1</sup> Connectors are included. (Refer to page 239.)



# JXC73/83/93 Series

#### Wiring Example 1

#### Cable with Main Control Power Supply Connector (For 4 Axes)\*1: C PWR

1 pc.

For 4 Axes JXC73/83/93

Terminal name	Function	Details
+24V	Main control power supply (+)	Power supply (+) supplied to the main control
24-0V	Main control power supply (-)	Power supply (-) supplied to the main control

<sup>\*1</sup> Part no.: JXC-C1 (Cable length: 1.5 m)

Cable with main control power supply connector

Cable color: Blue (0V)

Cable color: Brown (24V)

#### Motor Power Supply Connector (For 3/4 Axes)\*2: M PWR 2 pcs.\*3

JXC92 JXC73/83/93

Terminal name	Function	Details	Note
0V	Motor power cumply ( )	Power supply (–) supplied to the motor power	For 3 axes JXC92
OV.	Motor power supply (–)	The M 24V terminal, C 24V terminal, EMG	For 4 axes
		terminal, and LKRLS terminal are common (-).	JXC73/83/93
M 24V	Motor power supply (+)	Power supply (+) supplied to the motor power	

<sup>\*2</sup> Manufactured by PHOENIX CONTACT (Part no.: MSTB2, 5/2-STF-5, 08)

#### Motor power supply connector




Motor Control Power Supply Connector (For 4 Axes)\*4: CI 2 pcs.

For 4 Axes

Terminal name	Function	Details
C 24V	Motor control power supply (+)	Power supply (+) supplied to the motor control
EMG1/EMG3	Stop (+)	Axis 1/Axis 3: Input (+) for releasing the stop
EMG2/EMG4	Stop (+)	Axis 2/Axis 4: Input (+) for releasing the stop
LKRLS1/LKRLS3	Lock release (+)	Axis 1/Axis 3: Input (+) for releasing the lock
LKRLS2/LKRLS4	Lock release (+)	Axis 2/Axis 4: Input (+) for releasing the lock

<sup>\*4</sup> Manufactured by PHOENIX CONTACT (Part no.: FK-MC0, 5/5-ST-2, 5)

#### Motor control power supply connector




#### Control Power Supply Connector (For 3 Axes)\*5: CI 1 pc.

For 3 Axes

Terminal name	Function	Details
0V	Control power supply (–)	The C 24V terminal, LKRLS terminal, and EMG terminal are common (–).
C 24V	Control power supply (+)	Power supply (+) supplied to the control
LKRLS3	Lock release (+)	Axis 3: Input (+) for releasing the lock
LKRLS2	Lock release (+)	Axis 2: Input (+) for releasing the lock
LKRLS1	Lock release (+)	Axis 1: Input (+) for releasing the lock
EMG	Stop (+)	All axes: Input (+) for releasing the stop

<sup>\*5</sup> Manufactured by PHOENIX CONTACT (Part no.: FK-MC0, 5/6-ST-2, 5)

#### Control power supply connector







<sup>\*3 1</sup> pc. for 3 axes (JXC92)


# 4-Axis Step Motor Controller JXC73/83/93 Series

#### Wiring Example 2


Parallel I/O Connector

- When you connect a PLC to the I/O 1 or I/O 2 parallel I/O connector, use the I/O cable (JXC-C2-\( \subseteq \)).
- The wiring changes depending on the type of parallel I/O (NPN or PNP).

#### I/O 1 Wiring example **NPN JXC73**



#### **PNP JXC83**



OUT0	10	Load
OUT1	30	Load
OUT2	11	Load
OUT3	31	Load
OUT4	12	Load
OUT5	32	Load
OUT6	13	Load
OUT7	33	Load
OUT8	14	Load
BUSY	34	Load
(OUT9)	04	Loau
AREA	15	Load
(OUT10)	13	Loau
SETON	35	Load
INP	16	Load
SVRE	36	Load
*ESTOP	17	Load
*ALARM	37	Load
-COM1	18	
-COM1	19	
-COM1	38	
-COM2	20	
-COM2	39	
-COM2	40	

I/O 1 Input Signal

Name	Details
+COM1 +COM2	Connects the power supply 24 V for input/output signal
IN0 to IN8	Step data specified bit no. (Standard: When 512 points are used)
IN9 IN10	Step data specified extension bit no. (Extension: When 2048 points are used)
SETUP	Instruction to return to origin
HOLD	Temporarily stops operation
DRIVE	Instruction to drive
RESET	Resets alarm and interrupts operation
SVON	Servo ON instruction

I/O 1 Output Signal

Name	Details
IVAIIIC	Details
OUT0 to OUT8	Outputs the step data no. during operation
BUSY (OUT9)	Outputs when the operation of the actuator is in progress
AREA (OUT10)	Outputs when all actuators are within the area output range
SETON	Outputs when the return to origin of all actuators is completed
INP	Outputs when the positioning or pushing of all actuators is completed
SVRE	Outputs when servo is ON
*ESTOP*1	OFF when EMG stop is instructed
*ALARM*1	OFF when alarm is generated
-COM1 -COM2	Connects the power supply 0 V for input/output signal

<sup>\*1</sup> Negative-logic circuit signal

240

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

Model Selection

LEYG

LEY AC Servo Motor

LEYG

25A-LEY LEY-X5 Environment

> LECA6 LEC-G

LECP1 LECPA

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

□XC

LECY□ | LECS□ AC Servo Motor


# **JXC73/83/93** Series

#### Wiring Example 2


Parallel I/O Connector

- \* When you connect a PLC to the I/O 1 or I/O 2 parallel I/O connector, use the I/O cable (JXC-C2-\( \subseteq \)).
- \* The wiring changes depending on the type of parallel I/O (NPN or PNP).

# I/O 2 Wiring example NPN JXC73



#### **PNP JXC83**



BUSY1	10	Load
BUSY2	30	Load
BUSY3	11	Load
BUSY4	31	Load
AREA1	12	Load
AREA2	32	Load
AREA3	13	Load
AREA4	33	Load
INP1	14	Load
INP2	34	Load
INP3	15	Load
INP4	35	Load
*ALARM1	16	Load
*ALARM2	36	Load
*ALARM3	17	Load
*ALARM4	37	Load
-СОМЗ	18	
-СОМЗ	19	
-СОМЗ	38	
-COM4	20	
-COM4	39	
-COM4	40	

I/O 2 Input Signal

"O = mpace	, ignai
Name	Details
+COM3 +COM4	Connects the power supply 24 V for input/output signal
N.C.	Cannot be connected

I/O 2 Output Signal

Details Busy signal for axis 1 Busy signal for axis 2 Busy signal for axis 3 Busy signal for axis 4 Area signal for axis 1 Area signal for axis 2 Area signal for axis 3
Busy signal for axis 2 Busy signal for axis 3 Busy signal for axis 4 Area signal for axis 1 Area signal for axis 2
Busy signal for axis 3 Busy signal for axis 4 Area signal for axis 1 Area signal for axis 2
Busy signal for axis 4 Area signal for axis 1 Area signal for axis 2
Area signal for axis 1 Area signal for axis 2
Area signal for axis 2
Ÿ
Area signal for axis 3
Area signal for axis 4
Positioning or pushing completion signal for axis 1
Positioning or pushing completion signal for axis 2
Positioning or pushing completion signal for axis 3
Positioning or pushing completion signal for axis 4
Alarm signal for axis 1
Alarm signal for axis 2
Alarm signal for axis 3
Alarm signal for axis 4
Connects the power supply 0 V for input/output signal

<sup>\*2</sup> Negative-logic circuit signal



# 4-Axis Step Motor Controller JXC73/83/93 Series

**Options** 


Cable with main control power supply connector

JXC-C1

Cable length: 1.5 m (Accessory)

Number of cores	2
AWG size	AWG20






Number of cores	40
AWG size	AWG28

#### Weight


Product no.	Weight [g]
JXC-C2-1	160
JXC-C2-3	300
JXC-C2-5	480



Pin no.	Wire colour	Pin no.	Wire colour	Pin no.	Wire colour	Pin no.	Wire colour
1	Orange (Black 1)	6	Orange (Black 2)	11	Orange (Black 3)	16	Orange (Black 4)
21	Orange (Red 1)	26	Orange (Red 2)	31	Orange (Red 3)	36	Orange (Red 4)
2	Gray (Black 1)	7	Gray (Black 2)	12	Gray (Black 3)	17	Gray (Black 4)
22	Gray (Red 1)	27	Gray (Red 2)	32	Gray (Red 3)	37	Gray (Red 4)
3	White (Black 1)	8	White (Black 2)	13	White (Black 3)	18	White (Black 4)
23	White (Red 1)	28	White (Red 2)	33	White (Red 3)	38	White (Red 4)
4	Yellow (Black 1)	9	Yellow (Black 2)	14	Yellow (Black 3)	19	Yellow (Black 4)
24	Yellow (Red 1)	29	Yellow (Red 2)	34	Yellow (Red 3)	39	Yellow (Red 4)
5	Pink (Black 1)	10	Pink (Black 2)	15	Pink (Black 3)	20	Pink (Black 4)
25	Pink (Red 1)	30	Pink (Red 2)	35	Pink (Red 3)	40	Pink (Red 4)

#### **DIN** rail For 4 Axes JXC92 JXC73/83/93 **AXT100 - DR**

\* For , enter a number from the No. line in the table below. Refer to the dimension drawings on pages 234 and 237 for the mounting dimensions.



	L Dimensions												<u>►                                    </u>			<u>►  -/</u>	1.0)				
	No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
	L	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
Ī	No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
	L	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5

DIN rail mounting bracket (with 6 mounting screws) For 3 Axes For 4 Axes

JXC92 JXC73/83/93

### JXC-Z1

This should be used when the DIN rail mounting bracket is mounted onto a screw mounting type controller afterward.

**SMC** 

Model Selection

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

LEY AC Servo Motor LEYG

25A-LEY LEY-X5


LECA6

LEC-G Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECP1

## **JXC73/83/93** Series

#### **Options**





#### **Contents**

- **1) Controller setting software (CD-ROM)**
- 2 USB cable (Cable length: 3 m)

		Description	Model		
ı	1	Controller setting software	JXC-W1-1		
	2	USB cable	JXC-W1-2 (The same cable as the JXC-MA1-2)		


\* Can be ordered separately

#### **Hardware Requirements**

PC/AT compatible machine with Windows 7 or Windows 8.1 and USB1.1 or USB2.0 port

 Windows® is a registered trademark of Microsoft Corporation in the United States.





#### **Contents**

- ①Controller setting software (CD-ROM)\*1
- 2 USB cable (Cable length: 3 m)

	Description	Model			
1	Controller setting software	JXC-MA1-1			
2	USB cable	JXC-MA1-2 (The same cable as the JXC-W1-2)			

\* Can be ordered separately

#### **Hardware Requirements**

PC/AT compatible machine with Windows 7 or Windows 8.1 and USB1.1 or USB2.0 port


- \*1 The controller setting software also includes software dedicated for 4 axes.
- $\ast$  Windows® is a registered trademark of Microsoft Corporation in the United States.

# 4-Axis Step Motor Controller JXC73/83/93 Series










[Robotic cable, standard cable with lock and sensor for step motor (Servo/24 VDC)]



۱Λ	1_		<b>L</b> +
V١	ıе	ıa	nτ

Product no.	Weight [g]	Note
LE-CP-1-B-S	240	
LE-CP-3-B-S	380	Standard cable
LE-CP-5-B-S	630	
LE-CP-1-B	190	
LE-CP-3-B	360	
LE-CP-5-B	590	
LE-CP-8-B	1060	Robotic cable
LE-CP-A-B	1320	
LE-CP-B-B	1920	
LE-CP-C-B	2620	

Signal	Connector A terminal no.		Cable colour	Connector C terminal no.
Α	B-1 •		Brown	2
Ā	A-1		Red	1
В	B-2		Orange	6
B	A-2		Yellow	5
COM-A/COM	B-3 •		Green	3
COM-B/—	A-3		Blue	4
		Shield	Cable colour	Connector D terminal no.
Vcc	B-4 •		Brown	12
GND	A-4		Black	13
Ā	B-5		Red	7
Α	A-5	+ + ~ ~ + + + + + + + + + + + + + + + +	Black	6
B	B-6		Orange	9
В	A-6		Black	8
	Connector B	~\ <u>-</u>	_	3
Signal	terminal no.			
Lock (+)	B-1 <sup>4</sup>		Red	4
Lock (-)	A-1 '		Black	5
Sensor (+)	B-3 •		Brown	1
Sensor (-)	A-3		Blue	2

**SMC** 

LEY

Model Selection

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEYG

E AC Servo Motor

LEYG

LEY-X5 Environment 25A-LEY

> LECA6 LEC-G

LECP1 LECPA JXC

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECS AC Servo Motor LECY

# AC Servo Motor Driver LECS / LECY Series

#### **Pulse Input Type/Positioning Type**

# Incremental Type LECSA Series



#### **Pulse Input Type**

Absolute Type LECSB Series



#### **CC-Link Direct Input Type**

Absolute Type LECSC Series



#### SSCNET **II** Type

Absolute Type LECSS Series



#### SSCNET II/H Type

Absolute Type LECSS-T Series



#### MECHATROLINK-II Type

Absolute Type LECYM Series



#### MECHATROLINK-Ⅲ Type

Absolute Type LECYU Series



### **AC Servo Motor Driver**

**LECS** Series

Power supply voltage

100 to 120 VAC 200 to 230 VAC

**Motor capacity** 

100/200/400 W

Incremental Type

#### LECSA Series (Pulse input type/Positioning type)



• Up to 7 positioning points by point table

• Input type: Pulse input

• Control encoder: Incremental 17-bit encoder (Resolution: 131072 p/rev)

Parallel input: 6 inputsoutput: 4 outputs

#### LECSB Series (Pulse input type)



• Input type: Pulse input

• Control encoder: Absolute 18-bit encoder (Resolution: 262144 p/rev)

 Parallel input: 10 inputs output: 6 outputs

#### LECSC Series (CC-Link direct input type)



• Position data/speed data setting and operation start/stop



- Positioning by up to 255 point tables (when 2 stations are occupied)
- Up to 32 drivers can be connected (when 2 stations are occupied) with CC-Link communication.
- Applicable Fieldbus protocol: CC-Link (Ver. 1.10, Max. communication speed: 10 Mbps)
- Control encoder: Absolute 18-bit encoder (Resolution: 262144 p/rev)

#### LECSS Series (SSCNET III type)



- Compatible with Mitsubishi Electric's servo system controller network
- Reduced wiring and SSCNET III optical cable for one-touch connection
- The SSCNET III optical cable provides enhanced noise resistance.
- Up to 16 drivers can be connected with SSCNET III communication.
- Control encoder: Absolute 18-bit encoder (Resolution: 262144 p/rev)





**Absolute Type** 

LEY


**AC Servo Motor Driver** LECSS-T Series

**Motor capacity** 

Power supply voltage

100/200/400 W


200 to 230 VAC



SSCNET III/H and SSCNET III products are compatible.

SSCNET II/H compatible products can be added to existing SSCNET II systems for system expansion. Reassembly of the system (new installation of master PLC) is not required.

\* Note that the communication speed is that of SSCNET I (50 Mbps).



- Improved noise resistance STO (Safe Torque Off) safety function available
- Control encoder: Absolute 22-bit encoder (Resolution: 4194304 p/rev)

#### LECSS-T Series (SSCNET II/H type)



**Absolute Type** 

- Applicable Fieldbus protocol: 
   SSCNETIII/H
   SHOW SYSTEM CONTROLLED THE PROTOCOL
  - (High-speed optical communication, max. bidirectional communication speed: 150 Mbps)
- Bidirectional communication speed: 3 times
- SSCNET II/H and SSCNET III products are compatible.
- Improved noise resistance
- STO (Safe Torque Off) safety function available
- Control encoder: Absolute 22-bit encoder (Resolution: 4194304 p/rev)



Power supply voltage

200 to 230 VAC

**Motor capacity** 

100/200/400 W

#### **LECYM Series** (MECHATROLINK-II type)





- Applicable Fieldbus protocol: 

  MECHATROLINK-II
- Number of connectable drivers: 30 units (Transmission distance: Max. 50 m in total)
- Max. transmission speed: 10 Mbps
- Min. transmission cycle: 250 μs
- Control encoder: Absolute 20-bit encoder (Resolution: 1048576 p/rev)
- STO (Safe Torque Off) safety function available
- Compliant with the SEMI F47 Standard (Torque limit for low DC power supply voltage for main circuit)

#### LECYU Series (MECHATROLINK-III type)





- Number of connectable drivers: 62 units (Transmission distance: Max. 75 m between stations)
- Max. transmission speed: 100 Mbps
- Min. transmission cycle: 125 μs
- Control encoder: Absolute 20-bit encoder (Resolution: 1048576 p/rev)
- STO (Safe Torque Off) safety function available
- Compliant with the SEMI F47 Standard (Torque limit for low DC power supply voltage for main circuit)

# **AC Servo Motor Driver**

# **Incremental Type**

LECSA Series (Pulse Input Type/Positioning Type)

# **Absolute Type**

LECSB (Pulse Input Type) / LECSC (CC-Link Direct Input Type)

LECSS (SSCNET III Type)/LECSS-T (SSCNET III/H Type) Series












#### **How to Order**

#### LECSA/LECSB/LECSC/LECSS



Power supply voltage

Driver type

Power supply voltage 200 to 240 VAC, 50/60 Hz

SSCNET II/H type

(For absolute encoder)

S

	i olici ouppiy voltuge
1	100 to 120 VAC, 50/60 Hz
2	200 to 230 VAC 50/60 Hz

- If an I/O connector (CN1) is required, order the part number "LE-CSN□" separately.
- \* If an I/O cable (CN1) is required, order the part number "LEC-CSN□-1" separately. (Since the electric actuator will not operate without emergency stop (EMG) wiring for the LECSB, an I/O connector or an I/O cable is required.)

#### Compatible motor type

Symbol	Туре	Capacity	Encoder
S1	AC servo motor (S2*1)	100 W	
S3	AC servo motor (S3*1)	200 W	Incremental
S4	AC servo motor (S4*1)*2	400 W	
S5	AC servo motor (S6*1)	100 W	
S7	AC servo motor (S7*1)	200 W	Absolute
S8	AC servo motor (S8*1)*2	400 W	

- \*1 The symbol shows the motor type (actuator).
- \*2 Only available for power supply voltage "200 to 230 VAC"

#### **LECSS-T**



- \* If an I/O connector (CN1) is required, order the part number "LE-CSNS" separately.
- If an I/O cable (CN1) is required, order the part number "LEC-CSNS-1" separately.

#### Compatible motor type

Symbol	Туре	Capacity	Encoder
T5	AC servo motor (T6*1)	100 W	
T7	AC servo motor (T7*1)	200 W	Absolute
T8	AC servo motor (T8*1)	400 W	

\*1 The symbol shows the motor type (actuator).



Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

LEY

LEYG

AC Servo Motor

25A-LEY | LEY-X5 Environment

LECA6 Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

LEC-G LECP1


LECPA


AC Servo Motor

# LECS /LECSS-T Series

#### **Dimensions**


#### **LECSA**






Connector name	Description
CN1	I/O signal connector
CN2	Encoder connector
CN3	USB communication connector
CNP1	Main circuit power supply connector
CNP2	Control circuit power supply connector

#### **LECSB**



\*1 Battery included





Connector name	Description
CN1	I/O signal connector
CN2	Encoder connector
CN3	RS-422 communication connector
CN4	Battery connector
CN5	USB communication connector
CN6	Analogueue monitor connector
CNP1	Main circuit power supply connector
CNP2	Control circuit power supply connector
CNP3	Servo motor power connector

### AC Servo Motor Driver LECS /LECS-T Series

### **Dimensions**


### **LECSC**






Connector name	Description
CN1	CC-Link connector
CN2	Encoder connector
CN3	RS-422 communication connector
CN4	Battery connector
CN5	USB communication connector
CN6	I/O signal connector
CNP1	Main circuit power supply connector
CNP2	Control circuit power supply connector
CNP3	Servo motor power connector


### **LECSS**







Connector name	Description
CN1A	Front axis connector for SSCNET II optical cable
CN1B	Rear axis connector for SSCNET II optical cable
CN2	Encoder connector
CN3	I/O signal connector
CN4	Battery connector
CN5	USB communication connector
CNP1	Main circuit power supply connector
CNP2	Control circuit power supply connector
CNP3	Servo motor power connector


### LECSS2-T□





\* Battery included





Connector name	Description
CN1A	Front axis connector for SSCNET III/H
CN1B	Rear axis connector for SSCNET III/H
CN2	Encoder connector
CN3	I/O signal connector
CN4	Battery connector
CN5	USB communication connector
CN8	STO input signal connector
CNP1	Main circuit power supply connector
CNP2	Control circuit power supply connector
CNP3	Servo motor power connector

<b>Dimensions</b> [mm]						
Model	W	L	D	M		
LECSS2-T5		135				
LECSS2-T7	40	133	4	6		
LECSS2-T8		170	5			

252

Model Selection

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

AC Servo Motor LEYG

LEY

LEY-X5 Environment 25A-LEY

LECA6 LEC-G Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECP1

LECPA 

LECS AC Servo Motor LECY

Specific Product Precautions

### **Specifications**

### **LECSA Series**

	Model	LECSA1-S1	LECSA1-S3	LECSA2-S1	LECSA2-S3	LECSA2-S4
Compatil	ole motor capacity [W]	100 200		100	200	400
Compatil	ole encoder		Incremental 17-bi	t encoder (Resolution	on: 131072 p/rev)	
Main	Power voltage [V]	Single phase 100 to	120 VAC (50/60 Hz)	Single pha	se 200 to 230 VAC	(50/60 Hz)
power	Allowable voltage fluctuation [V]	Single phase 8	35 to 132 VAC	Singl	e phase 170 to 253	VAC
supply	Rated current [A]	3.0	5.0	1.5	2.4	4.5
Control	Control power supply voltage [V]			24 VDC		
power	Allowable voltage fluctuation [V]			21.6 to 26.4 VDC		
supply	Rated current [A]			0.5		
Parallel i	nput	6 inputs				
Parallel o	output	4 outputs				
Max. inp	ut pulse frequency [pps]	1 M (for differential receiver), 200 k (for open collector)*2				
	In-position range setting [pulse]	0 to ±65535 (Command pulse unit)				
Function	Error excessive	±3 rotations				
runction	Torque limit	Parameter setting				
	Communication	USB communication				
Operatin	g temperature range [°C]		(	to 55 (No freezing	)	
Operatin	g humidity range [%RH]	90 or less (No condensation)				
Storage t	temperature range [°C]	-20 to 65 (No freezing)				
Storage I	numidity range [%RH]	90 or less (No condensation)				
Insulatio	n resistance [MΩ]		Between the	housing and SG: 1	0 (500 VDC)	
Weight [	<u></u>		60	00		700

### **LECSB Series**

	Model	LECSB1-S5	LECSB1-S7	LECSB2-S5	LECSB2-S7	LECSB2-S8
Compatil	ole motor capacity [W]	100	200	100	200	400
Compatil	ble encoder		Absolute 18-bit	encoder (Resolution	n: 262144 p/rev)	
Main	Power voltage [V]	Single phase 100 to	120 VAC (50/60 Hz)		se 200 to 230 VAC se 200 to 230 VAC	
power supply	Allowable voltage fluctuation [V]	Single phase 8	85 to 132 VAC		e phase 170 to 253 le phase 170 to 253	
	Rated current [A]	3.0	5.0	0.9	1.5	2.6
Control	Control power supply voltage [V]	Single phase 100 to	120 VAC (50/60 Hz)	Single pha	se 200 to 230 VAC	(50/60 Hz)
power	Allowable voltage fluctuation [V]	Single phase 8	85 to 132 VAC	Singl	e phase 170 to 253	VAC
supply	Rated current [A]	0.4 0.2				
Parallel i	nput	10 inputs				
Parallel c	output	6 outputs				
Max. inpu	ut pulse frequency [pps]		1 M (for differentia	l receiver), 200 k (fo	or open collector)*2	
	In-position range setting [pulse]		0 to ±10	0000 (Command pu	lse unit)	
Function	Error excessive			±3 rotations		
i unction	Torque limit	Par	ameter setting or ex	ternal analogue inp	ut setting (0 to 10 V	DC)
	Communication	USB communication, RS422 communication*1				
Operating	g temperature range [°C]	0 to 55 (No freezing)				
Operating	g humidity range [%RH]	90 or less (No condensation)				
Storage t	temperature range [°C]	–20 to 65 (No freezing)				
Storage I	humidity range [%RH]	90 or less (No condensation)				
Insulatio	n resistance [MΩ]	Between the housing and SG: 10 (500 VDC)				
Weight [	a]		80	00		1000

<sup>\*1</sup> USB communication and RS422 communication cannot be performed at the same time.



<sup>\*2</sup> If the command pulse input is open collector method, it supports only the sink (NPN) type interface. It does not correspond to the source (PNP) type interface.

### AC Servo Motor Driver LECS /LECS-T Series

### **Specifications**

### **LECSC Series**

Mod	del	LECSC1-S5	LECSC1-S7	LECSC2-S5	LECSC2-S7	LECSC2-S8	
Compatible motor capacity [W]         100         200         100         200			400				
Compatible encoder			Absolute 18-bit	encoder (Resolution	n: 262144 p/rev)		
Power voltag	Allowable voltage fluctuation [1/]		Single phase 100 to 120 VAC Three phase 200 to 230 VAC (50/60 (50/60 Hz) Single phase 200 to 230 VAC (50/60			(	
power supply Allowable vo			35 to 132 VAC		e phase 170 to 253 e phase 170 to 253		
Rated curren	it [A]	3.0	5.0	0.9	1.5	2.6	
Control power	er supply voltage [V]	Single phase 1 (50/6			e phase 200 to 230 (50/60 Hz)		
supply Allowable vo	Itage fluctuation [V]	Single phase 8	35 to 132 VAC	Single	e phase 170 to 253	VAC	
Rated curren		0.			0.2		
	eldbus protocol (Version)			communication (V			
Connection of	cable	CC-Link	Ver. 1.10 complia	nt cable (Shielded :	3-core twisted pair	cable)*1	
Remote stati	on number			1 to 64			
Cable	Communication speed [bps]	16 k	625 k	2.5 M	5 M	10 M	
Communication	Maximum overall cable length [m]	1200	900	400	160	100	
specifications	Cable length between stations [m]	0.2 or more					
I/O occupation (Inputs/Outputs/		1 station occupied (Remote I/O 32 points/32 points)/(Remote register 4 words/4 words) 2 stations occupied (Remote I/O 64 points/64 points)/(Remote register 8 words/8 words)					
Number of co	onnectable drivers	Up to 42 (when 1 station is occupied by 1 driver), Up to 32 (when 2 stations are occupied by 1 driver), when there are only remote device stations.					
Remote regis	ster input	Available with CC-Link communication (2 stations occupied)					
Command method	table No. input  Available with CC-Link communication, RS422 communication CC-Link communication (1 station occupied): 31 points CC-Link communication (2 stations occupied): 255 points RS422 communication: 255 points						
Indexer posit	tioning input	Available with CC-Link communication CC-Link communication (1 station occupied): 31 points CC-Link communication (2 stations occupied): 255 points					
Communication function	on		USB commun	ication, RS-422 cor	mmunication*2		
Operating temperature	range [°C]		(	to 55 (No freezing	)		
Operating humidity ran	ge [%RH]	90 or less (No condensation)					
Storage temperature ra	nge [°C]		-2	20 to 65 (No freezin	g)		
Storage humidity range	e [%RH]	90 or less (No condensation)					
In a collection we also as a collection of	MO1	Between the housing and SG: 10 (500 VDC)					
Insulation resistance [N	VIS2]		DCtwccii tiic	riousing and od. 1	0 (300 VDO)		

<sup>\*1</sup> If the system comprises of both CC-Link Ver. 1.00 and Ver. 1.10 compliant cables, Ver. 1.00 specifications are applied to the overall cable length and the cable length between stations.

#### **LECSS Series**

	3CI IC3					
	Model	LECSS1-S5	LECSS1-S7	LECSS2-S5	LECSS2-S7	LECSS2-S8
Compati	ole motor capacity [W]	100	200	100	200	400
Compati	ole encoder	Absolute 18-bit encoder (Resolution: 262144 p/rev)				
Main	Power voltage [V]		00 to 120 VAC 0 Hz)		se 200 to 230 VAC se 200 to 230 VAC	' '
power supply	Allowable voltage fluctuation [V]	Single phase 8	35 to 132 VAC		e phase 170 to 253 e phase 170 to 253	I
	Rated current [A]	3.0	5.0	0.9	1.5	2.6
Control	Control power supply voltage [V]	Single phase 100 to 120 VAC (50/60 Hz)		Single phase 200 to 230 VAC (50/60 Hz)		
power supply	Allowable voltage fluctuation [V]	Single phase 85 to 132 VAC		Single phase 170 to 253 VAC		
	Rated current [A]	0.4		0.2		
Applicab	le Fieldbus protocol		SSCNET II (H	igh-speed optical c	ommunication)	
Commun	ication function		l	JSB communication	า	
Operatin	g temperature range [°C]		(	to 55 (No freezing	)	
Operatin	g humidity range [%RH]	90 or less (No condensation)				
Storage	Storage temperature range [°C] —20 to 65 (No freezing)					
Storage humidity range [%RH] 90 or less (No condensation)			ation)			
Insulatio	n resistance [MΩ]		Between the	housing and SG: 1	0 (500 VDC)	
Weight [	al		80	00		1000

<sup>\*2</sup> USB communication and RS422 communication cannot be performed at the same time.

### **Specifications**


### **LECSS-T Series**

	Model	LECSS2-T5 LECSS2-T7 LECSS2-T					
Compatil	ble motor capacity [W]	100 200 400					
Compatil	ble encoder	Absolute 22-bit encoder (Resolution: 4194304 p/rev)					
Main	Power voltage [V]	Three phase 200 to 24	10 VAC (50/60 Hz), Single phase 200	to 240 VAC (50/60 Hz)			
power	Allowable voltage fluctuation [V]	Three phase 170 to 26	64 VAC (50/60 Hz), Single phase 170	to 264 VAC (50/60 Hz)			
supply	Rated current [A]	0.9	1.5	2.6			
Control	Control power supply voltage [V]	S	Single phase 200 to 240 VAC (50/60 Hz)				
power	Allowable voltage fluctuation [V]	Single phase 170 to 264 VAC					
supply	supply Rated current [A] 0.2						
Applicab	le Fieldbus protocol	SSCNET II/H (High-speed optical communication)					
Commun	ication function		USB communication				
Operatin	g temperature range [°C]		0 to 55 (No freezing)				
Operatin	g humidity range [%RH]		90 or less (No condensation)				
Storage t	temperature range [°C]	-20 to 65 (No freezing)					
Storage I	humidity range [%RH]	90 or less (No condensation)					
Insulatio	n resistance [MΩ]	Between the housing and SG: 10 (500 VDC)					
Weight [g	9]	80	00	1000			

### AC Servo Motor Driver LECS /LECSS-T Series

**Power Supply Wiring Example: LECSA** 

### LECSA□-□




#### Main Circuit Power Supply Connector: CNP1 \* Accessory

Terminal name	Function	Details
	Protective earth (PE)	Should be grounded by connecting the servo motor's earth terminal and the control panel's protective earth (PE)
L <sub>1</sub>	Main circuit	Connect the main circuit power supply. LECSA1: Single phase 100 to 120 VAC, 50/60 Hz
L2	power supply	LECSA2: Single phase 200 to 230 VAC, 50/60 Hz
Р	Regeneration option	Terminal to connect regeneration option LECSA□-S1: Not connected at time of shipping LECSA□-S3, S4: Connected at time of shipping
С	negeneration option	* If regeneration option is required for "Model Selection," connect to this terminal.
U	Servo motor power (U)	
V	Servo motor power (V)	Connect to motor cable (U, V, W).
W	Servo motor power (W)	

### Control Circuit Power Supply Connector: CNP2 | \* Accessory

Terminal name	Function	Details
24V	Control circuit power supply (24 V)	24 V side of the control circuit power supply (24 VDC) supplied to the driver
0V	Control circuit power supply (0 V)	0 V side of the control circuit power supply (24 VDC) supplied to the driver



LEY

Model Selection

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEYG

LEY AC Servo Motor

LEYG

25A-LEY LEY-X5 Environment


LECA6 LEC-G

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECP1 LECPA


JXC □SO∃T AC Servo Motor 

Specific Product Precautions


### Power Supply Wiring Example: LECSB, LECSC, LECSS



### For single phase 200 VAC



#### For three phase 200 VAC



\* For single phase 200 to 230 VAC, power supply should be connected to L1 and L2 terminals, with nothing connected to L3.

### Main Circuit Power Supply Connector: CNP1 \* Accessory


Terminal name	Function	Details		
L <sub>1</sub>		Connect the main circuit power supply.		
L2	Main circuit power supply	LECSB1/LECSC1/LECSS1: Single phase 100 to 120 VAC, 50/60 Hz Connection terminal: L1, L2 LECSB2/LECSC2/LECSS2: Single phase 200 to 230 VAC, 50/60 Hz Connection terminal: L1, L2		
Lз	p	Three phase 200 to 230 VAC, 50/60 Hz Connection terminal: L <sub>1</sub> , L <sub>2</sub> , L <sub>3</sub>		
N	Do not connect.			
P <sub>1</sub>	Connect between Dr and De (Connected at time of abinning)			
P <sub>2</sub>	Connect between P <sub>1</sub> and P <sub>2</sub> . (Connected at time of shipping)			

### Control Circuit Power Supply Connector: CNP2 \* Accessory

Terminal name	Function	Details		
Р	Regeneration	Connect between P and D. (Connected at time of shipping)  * If regeneration option is required for "Model Selection," connect to this terminal.		
С	option			
D	орион			
L <sub>11</sub>	Connect the control circuit power supply.  Control circuit LECSB1/LECSC1/LECSS1: Single phase 100 to 120 VAC, 50/60 Hz Connection			
L21	power supply	LECSB2/LECSC2/LECSS2: Single phase 200 to 230 VAC, 50/60 Hz Connection terminal: L11, L21  Three phase 200 to 230 VAC, 50/60 Hz Connection terminal: L11, L21		

### Motor Connector: CNP3 \* Accessory


Terminal name	Function	Details
U	Servo motor power (U)	
V	Servo motor power (V)	Connect to motor cable (U, V, W).
W	Servo motor power (W)	






### AC Servo Motor Driver LECS /LECS-T Series

### Power Supply Wiring Example: LECSS2-T□



#### For three phase 200 VAC



\* For single phase 200 to 240 VAC, power supply should be connected to L1 and L3 terminals, with nothing connected to L2. Please note that the wiring locations differ from the LECS.

### Main Circuit Power Supply Connector: CNP1


Terminal name	Function	Details	
L <sub>1</sub>	Main ainerit	Connect the main circuit power supply.	
L2	Main circuit	LECSS2: Single phase 200 to 240 VAC, 50/60 Hz Connection terminal: L1, L3	
Lз	power supply	Three phase 200 to 240 VAC, 50/60 Hz Connection terminal: L1, L2, L3	
N(-)	Do not connect.		
Рз	Connect between P <sub>3</sub> and P <sub>4</sub> . (Connected at time of shipping)		
P4	Connect between F3 and F4. (Connected at time of Shipping)		

### Control Circuit Power Supply Connector: CNP2 | \* Accessory

Terminal name	Function	Details
P(+) C D	Regeneration option	Connect between P(+) and D. (Connected at time of shipping)  * If regeneration option is required for "Model Selection," connect to this terminal.
L <sub>11</sub>	Control circuit	Connect the control circuit power supply.  LECSS2: Single phase 200 to 240 VAC, 50/60 Hz Connection terminal: L11, L21
L21	power supply	Three phase 200 to 240 VAC, 50/60 Hz Connection terminal: L11, L21

#### Motor Connector: CNP3 \* Accessory

Terminal name	Function	Details
U	Servo motor power (U)	
V	Servo motor power (V)	Connect to motor cable (U, V, W).
W	Servo motor power (W)	



LEY AC Servo Motor

Model Selection

LEY

LEYG

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

LEYG

LEY-X5


Environment 25A-LEY LECA6

LEC-G Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECP1 LECPA

### **Control Signal Wiring Example: LECSA**

#### LECSA□-□


This wiring example shows connection with a PLC (FX3U- $\square\square$ MT/ES) manufactured by Mitsubishi Electric Corporation as when used in position control mode. Refer to the LECSA series Operation Manual and any technical literature or operation manuals for your PLC and positioning unit before connecting to another PLC or positioning unit.



- \*1 For preventing electric shock, be sure to connect the driver main circuit power supply connector (CNP1)'s protective earth (PE) terminal (marked 🏐) to the control panel's protective earth (PE).
- \*2 For interface use, supply 24 VDC ±10 % 200 mA using an external source. 200 mA is the value when all I/O command signals are being used. In addition, reducing the number of inputs/outputs can decrease the current capacity. Refer to the Operation Manual for required current for interface.
- \*3 The failure (ALM) is normally ON. When it is OFF (alarm occurs), stop the PLC signal using the sequence program.
- \*4 Signals of the same name are connected inside the driver.
- \*5 For command pulse input with an open collector method. When a positioning unit loaded with a differential line driver method is used, it is 10 m or less.
- \*6 If the command pulse input is open collector method, it supports only the sink (NPN) type interface. It does not correspond to the source (PNP) type interface.



This wiring example shows connection with a positioning unit (QD75D) manufactured by Mitsubishi Electric Corporation as when used in position control mode. Refer to the LECSB series Operation Manual and any technical literature or operation manuals for your PLC and positioning unit before connecting to another PLC or positioning unit.



- \*1 For preventing electric shock, be sure to connect the driver's protective earth (PE) terminal (marked 🏐) to the control panel's protective earth (PE).
- \*2 For interface use, supply 24 VDC ±10 % 300 mA using an external source.
- \*3 The failure (ALM) is normally ON. When it is OFF (alarm occurs), stop the PLC signal using the sequence program.
- \*4 Signals of the same name are connected inside the driver.
- \*5 For command pulse input with a differential line driver method. For open collector method, it is 2 m or less.
- \*6 If the command pulse input is open collector method, it supports only the sink (NPN) type interface. It does not correspond to the source (PNP) type interface.



Model Selection

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

Ē AC Servo Motor EYG.

LEY-X5 Environment 25A-LEY


LECA6 LEC-G Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECP1

LECPA 

LECS AC Servo Motor LECY

pecific Product

### **Control Signal Wiring Example: LECSC**




<sup>\*1</sup> For preventing electric shock, be sure to connect the driver's protective earth (PE) terminal (marked 🏐) to the control panel's protective earth (PE).

<sup>\*2</sup> For interface use, supply 24 VDC ±10 % 150 mA using an external source.

<sup>\*3</sup> The failure (ALM) is normally ON. When it is OFF (alarm occurs), stop the PLC signal using the sequence program.

### AC Servo Motor Driver LECS /LECS-T Series

### **Control Signal Wiring Example: LECSS**



- occurs), stop the PLC signal using the sequence program.
- \*4 Signals of the same name are connected inside the driver.
- \*5 Use the following SSCNET II optical cables. Refer to "SSCNET III optical cable" on page 265 for cable product numbers.

Cable	Product no.	Cable length
SSCNET <b>I</b> II optical cable	LE-CSS-□	0.15 m to 3 m

- \*6 Connections from Axis 2 onward are omitted.
- \*7 Up to 16 axes can be set.
- \*8 Be sure to place a cap on unused CN1A/CN1B.



SW2

1 2

Cap\*8

262

Model Selection

LEY

LEYG

Щ

LEYG

LEY-X5

25A-LEY

LECA6

LEC-G

LECP1

LECPA

LECS

LECY

Specific Product

AC Servo Motor


Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

Environment

AC Servo Motor

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

### Control Signal Wiring Example: LECSS2-T□



- \*1 For preventing electric shock, be sure to connect the driver's protective earth (PE) terminal (marked (1)) to the
- \*2 For interface use, supply 24 VDC ±10 % using an external
- \*3 The failure (ALM) is normally ON. When it is OFF (alarm occurs), stop the master PLC signal using the master PLC
- \*4 Signals of the same name are connected inside the driver.
- Refer to "SSCNET III optical cable" on page 265 for cable

Cable	Product no.	Cable length
SSCNET <b>I</b> optical cable	LE-CSS-□	0.15 m to 3 m

- \*6 Connections from Axis 2 onward are omitted.
- Up to 64 axes can be set for the axis selection rotary switch (SW1) and auxiliary axis number setting switches (SW2-3, SW2-4) in combination. Note that the number of connection axes depends on the specifications of the master PLC
- \*8 Be sure to place a cap on unused CN1A/CN1B.
- When not using the STO function, use the driver with the shortcircuit connector (provided as an accessory) inserted.
- \*10 Configure a circuit to turn off EM2 when the main circuit power is turned off to prevent any unexpected restarts of the driver.





1234

Cap\*8

### **Options**


Motor cable, Lock cable, Encoder cable (LECS□, LECSS-T common)





Α

10



Product no.	ØD
LE-CSB-S□A	4.7
LE-CSB-S□B	4.7
LE-CSB-R□A	4.5
LE-CSB-R□B	4.5

Product no.	שש
LE-CSM-S□A	6.2
LE-CSM-S□B	0.2
LE-CSM-R□A	5.7
LE-CSM-R□B	5.7

### Weight

Product no.	Length [m]	Weight [g]
LE-CSM-S2□	2	180
LE-CSM-S5□	5	400
LE-CSM-SA□	10	800
LE-CSM-R2□	2	180
LE-CSM-R5□	5	400
LE-CSM-RA□	10	800

### Weight

Product no.	Length [m]	Weight [g]
LE-CSB-S2□	2	80
LE-CSB-S5□	5	200
LE-CSB-SA□	10	400
LE-CSB-R2□	2	80
LE-CSB-R5□	5	200
LE-CSB-RA□	10	400

#### Weight

Product no.	Length [m]	Weight [g]
LE-CSE-S2□	2	220
LE-CSE-S5□	5	600
LE-CSE-SA□	10	1200
LE-CSE-R2□	2	220
LE-CSE-R5□	5	600
LE-CSE-RA□	10	1200

### LE-CSE-□□: Encoder cable


(29.6)

LE-CSB-□□: Lock cable\*1



\*1 If using an actuator with a lock, a lock cable is required.

### I/O connector (Without cable, Connector only)



\* LE-CSNA: 10126-



**LE-CSNA** 

LE-CSNA: 10126-3000PE (connector)/10326-52F0-008 (shell kit)
manufactured by 3M Japan Limited or equivalent
LE-CSNB: 10150-3000PE (connector)/10350-52F0-008 (shell kit)
manufactured by 3M Japan Limited or equivalent
LE-CSNS: 10120-3000PE (connector)/10320-52F0-008 (shell kit)
manufactured by 3M Japan Limited or equivalent

#### **LE-CSNB**






**LE-CSNS** 

Weight				
Product no.	Weight [g			
LE-CSNA	25			
LE-CSNB	30			
LE-CSNS	16			

- Applicable conductor size: AWG24 to 30
  - If using the LECSB, emergency stop (EMG) wiring is required in all cases. (The electric actuator will not operate without the wiring.) Prepare an I/O connector or an I/O cable in advance.

### **Options**

SSCNET III optical cable (LECSS□-S□, LECSS2-T□)





 \* LE-CSS-□ is MR-J3BUS□M manufactured by Mitsubishi Electric Corporation.

#### Weight

Product no.	Length [m]	Weight [g]
LE-CSS-L	0.15	100
LE-CSS-K	0.3	100
LE-CSS-J	0.5	200
LE-CSS-1	1	200
LE-CSS-3	3	200

#### I/O cable





- \* LEC-CSNA-1: 10126-3000PE (connector)/10326-52F0-008 (shell kit) manufactured by 3M Japan Limited or equivalent LEC-CSNB-1: 10150-3000PE (connector)/10350-52F0-008 (shell kit) manufactured by 3M Japan Limited or equivalent LEC-CSNS-1: 10120-3000PE (connector)/10320-52F0-008 (shell kit) manufactured by 3M Japan Limited or equivalent
- \* Conductor size: AWG24
- If using the LECSB, emergency stop (EMG) wiring is required in all cases. (The electric actuator will not operate without the wiring.) Prepare an I/O connector or an I/O cable in advance.

#### Cable O.D.

Product no.	ØD
LEC-CSNA-1	11.1
LEC-CSNB-1	13.8
LEC-CSNS-1	9.1

#### Dimensions/Pin Nos.

Product no.	W	Н	Т	U	Pin no. n
LEC-CSNA-1		37.2		14	14
LEC-CSNB-1	39	52.4	12.7	18	26
LEC-CSNS-1		33.3		14	21

### Wiring

LEC-CSNA-1: Pin nos. 1 to 26 LEC-CSNB-1: Pin nos. 1 to 50 LEC-CSNS-1: Pin nos. 1 to 20

	nector no.	Pair no. of wire	Insulation colour	Dot mark	Dot colour
	1	4	0		Red
	2	1	Orange		Black
	3	2	Light		Red
	4		gray		Black
	5	3	White	_	Red
	6	3	vviile		Black
	7	4	Yellow		Red
	8	4	reliow		Black
A side	9	5	Pink		Red
A	10	5			Black
	11	6	Orange		Red
	12	0	Orange		Black
	13	7	Light		Red
	14	′	gray		Black
	15	0	White		Red
	16	8	vville		Black
	17	9	O Vallani		Red
	18	9	Yellow		Black

Cor	nector	Pair no.	Insulation	Dot mark	Dot
pi	n no.	of wire	colour	Dollilark	colour
	19	10	Pink		Red
	20	10	FILIK		Black
	21	11			Red
	22	11	Orange		Black
	23	12	Light		Red
	24	12	gray		Black
4	25	13	White		Red
A side	26				Black
8	27	14	Yellow		Red
~	28	14	reliow		Black
	29 15	Pink		Red	
	30	15	FILIK		Black
	31	16	16 Orongo		Red
	32		Orange		Black
	33	17	Light		Red
	34	'/	gray		Black

_					
Connector			Insulation	Dot mark	Dot
pir	no.	of wire	colour	Dot mark	colour
	35	18	White		Red
	36	10	vviile		Black
	37	10	Vallann		Red
	38	19	Yellow		Black
	39	00	Pink		Red
	40	20	PINK		Black
	41	0.4	Orange		Red
ide	42	21			Black
A side	43	22	Light		Red
	44	22	gray		Black
	45	00	\		Red
	46	23	White		Black
	47	24	Vallann		Red
	48		Yellow		Black
	49	0.5	Divil		Red
	50 25	Pink		Black	

### AC Servo Motor Driver LECS /LECS-T Series

**Options** 

Regeneration option (LECS□, LECSS-T common)




### Regeneration option type

032		Allowable regenerative power 30 W
	12	Allowable regenerative power 100 W

Confirm regeneration option to be used in "Model Selection.'


#### LEC-MR-RB-032



### Weight

Product no.	Weight [kg]
LEC-MR-RB-032	0.5

\* MR-RB032 manufactured by Mitsubishi **Electric Corporation** 



#### Weight

Product no.	Weight [kg]
LEC-MR-RB-12	1.1

\* MR-RB12 manufactured by Mitsubishi Electric Corporation

**SMC** 

Model Selection

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LEY

LEYG

LEY AC Servo Motor

LEYG

25A-LEY | LEY-X5 Environment

LECA6 LEC-G

Step Motor (Servo/24 VDC)/Servo Motor (24 VDC) LECP1 LECPA


LECS

AC Servo Motor 

### **Options**







(MR Configurator2™)

### Setup software (MR Configurator2™) (LECSA, LECSB, LECSC, LECSS, LECSS-T common)

LEC-MRC2

_	Japanese version		
Е	English version		
C	Chinese version		

\* SW1DNC-MRC2- manufactured by Mitsubishi Electric Corporation Refer to Mitsubishi Electric Corporation's website for operating environment and version upgrade information.

MR Configurator2<sup>™</sup> is a registered trademark or trademark of Mitsubishi Electric Corporation.

### Adjustment, waveform display, diagnostics, parameter read/write, and test operation can be performed upon a PC. Compatible PC

When using setup software (MR Configurator2™), use an IBM PC/AT compatible PC that meets the following operating conditions.

### **Hardware Requirements**

Equ	uipment	Setup software (MR Configurator2™) <b>LEC-MRC2</b> □	
*1, 2, 3, 4, 5, 6, 7, 8, 9, 10 PC	os	Microsoft® Windows® 10 Edition Microsoft® Windows® 10 Enterprise Microsoft® Windows® 10 Pro Microsoft® Windows® 10 Home Microsoft® Windows® 8.1 Enterprise Microsoft® Windows® 8.1 Pro Microsoft® Windows® 8.1 Pro Microsoft® Windows® 8.1 Microsoft® Windows® 8 Enterprise Microsoft® Windows® 8 Pro Microsoft® Windows® 8 Pro Microsoft® Windows® 7 Ultimate Microsoft® Windows® 7 Fenterprise Microsoft® Windows® 7 Fenterprise Microsoft® Windows® 7 Fenterprise Microsoft® Windows® 7 Fenterprise Microsoft® Windows® 7 Fenterprise Microsoft® Windows® 7 Starter Microsoft® Windows® 7 Starter Microsoft® Windows Vista® Ultimate Microsoft® Windows Vista® Enterprise Microsoft® Windows Vista® Business Microsoft® Windows Vista® Home Premium Microsoft® Windows Vista® Home Premium Microsoft® Windows Vista® Home Basic Microsoft® Windows® XP Professional, Service Pack 3 or later Microsoft® Windows® XP Professional, Service Pack 3 or later	
	Hard disk	1 GB or more of free space	1
	Communication interface	Use USB port.	١
Display		Resolution 1024 x 768 or more Must be capable of high colour (16-bit) display. Connectable with the PC above	
Keyboar	d	Connectable with the PC above	]
Mouse		Connectable with the PC above	]
Printer		Connectable with the PC above	1
USB cat	ole*11	LEC-MR-J3USB	

### **Setup Software Compatible Drivers**

	Setup software				
Compatible driver	MR Configurator™	MR Configurator2™			
divei	LEC-MR-SETUP221□	LEC-MRC2□			
LECSA	0	0			
LECSB	0	0			
LECSC	0	0			
LECSS□-S□	0	0			
LECSS2-T□	_	0			

- \*1 Before using a PC for setting LECSA point table method/program operation method, upgrade to version 1.18U (Japanese version)/ version 1.19V (English version) or later. Refer to Mitsubishi Electric Corporation's website for version upgrade information.
- \*2 Windows® and Windows Vista® are registered trademarks of Microsoft Corporation in the United States and other countries.
- \*3 On some PCs, setup software (MR Configurator2™) may not run properly.
- The following functions cannot be used. If any of the following functions is used, this product may not oper-
  - · Start of application in Windows® compatible mode
  - · Fast User Switching
  - · Remote Desktop
  - · Windows XP Mode
  - · Windows Touch or Touch
  - · Modern UI
  - · Client Hyper-V
  - · Tablet Mode
  - · Virtual desktop
  - · 6 4 -bit OSs are not supported, except for Microsoft® Windows®7 or later.
- \*5 Multi-display is set, the screen of this product may not operate normally.
- \*6 The size of the text or other items on the screen is not changed to the specified value (96 DPI, 100 %, 9 pt, etc.), the screen of this product may not operate normally.
- \*7 Changed the resolution of the screen during operating, the screen of this product may not operate normally.
- Please use by "Standard User," "Administrator" in Windows Vista® or later.
- \*9 Using a PC for setting Windows® 10, upgrade to version 1.52E or later.
  - Using a PC for setting Windows® 8.1, upgrade to version 1.25B or later Using a PC for setting Windows®8, upgrade to version
  - 1.20W or later. Refer to Mitsubishi Electric Corporation's website for
- version upgrade information.
- \*10 If .NET Framework 3.5 (including .NET 2.0 and 3.0) have been disabled in Windows® 7 or later, it is necessary to enable it.
- \*11 Order USB cable separately.
  - This cable is compatible with the setup software (MR Configurator™: LEC-MR-SETUP221□).



### **Options**

USB cable (3 m)

(LECSA, LECSB, LECSC, LECSS, LECSS-T common)

### LEC-MR-J3USB

\* MR-J3USBCBL3M manufactured by Mitsubishi Electric Corporation

Weight: 140 a

Cable for connecting PC and driver when using the setup software (MR Configurator2™)

Do not use any cable other than this cable.

### Battery (Only for LECSB, LECSC, and LECSS) LEC-MR-J3BAT

\* MR-J3BAT manufactured by Mitsubishi Electric Corporation

Battery for replacement

Absolute position data is maintained by installing the battery to the driver.



Weight: 30 g

### Battery (Only for LECSS2-T□)

### LEC-MR-BAT6V1SET

\* MR-BAT6V1SET manufactured by Mitsubishi Electric Corporation

Battery for replacement

Absolute position data is maintained by installing the battery to the driver.




### STO cable (3 m) (Only for LECSS2-T□) LEC-MR-D05UDL3M

\* MR-D05UDL3M manufactured by Mitsubishi Electric Corporation

Cable for connecting the driver and device, when using the safety function

Do not use any cable other than this cable.



Weight: 500 g

SMC

\* The LEC-MR-J 3 BAT is a single battery that uses lithium metal battery FR6V

When transporting lithium metal batteries and devices with built-in lithium metal batteries by a method subject to UN regulations, it is necessary to apply measures according to the regulations stipulated in the United Nations Recommendations on the Transport of Dangerous Goods, the Technical Instructions (ICAO-TI) of the International Civil Aviation Organisation (ICAO), and the International Maritime Dangerous Goods Code (IMDG CODE) of the International Maritime Organisation (IMO). If a customer is transporting products such as shown above, it is necessary to confirm the latest regulations, or the laws and regulations of the country of transport on your own, in order to apply the proper measures. Please contact SMC sales representative for details.

The LEC-MR-BAT6V1SET is an assembled battery that uses lithium metal battery 2CR17335A.

When transporting lithium metal batteries and devices with built-in lithium metal batteries by a method subject to UN regulations, it is necessary to apply measures according to the regulations stipulated in the United Nations Recommendations on the Transport of Dangerous Goods, the Technical Instructions (ICAO-TI) of the International Civil Aviation Organisation (ICAO), and the International Maritime Dangerous Goods Code (IMDG CODE) of the International Maritime Organisation (IMO). If a customer is transporting products such as shown above, it is necessary to confirm the latest regulations, or the laws and regulations of the country of transport on your own, in order to apply the proper measures. Please contact SMC sales representative for details.



### LECS Series

### **Specific Product Precautions 1**

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For electric actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

#### **Design / Selection**

### **⚠** Warning

1. Be sure to apply the specified voltage.

Otherwise, malfunction or breakage may occur. If the applied voltage is lower than the specified voltage, it is possible that the load will not be able to be moved due to an internal voltage drop of the driver. Please check the operating voltage before use.

2. Do not operate the product beyond the specifications.

Otherwise, a fire, malfunction, or actuator damage may result. Please check the specifications before use.

3. Install an emergency stop circuit.

Please install an emergency stop outside of the enclosure so that the system operation can be stopped immediately and the power supply can be intercepted.

- 4. In order to prevent any damage caused by the breakdown or malfunction of the driver and its peripheral devices, a backup system should be established in advance by giving a multiple-layered structure or a failsafe design to the equipment, etc.
- 5. If a danger of human injury is expected due to abnormal heat generation, smoking, ignition, etc., of the driver and its peripheral devices, cut off the power supply of the product and the system immediately.
- 6. The parameters of the driver are set to initial values. Please change the parameters according to the specifications of the customer's equipment before use. Refer to the operation manual for parameter details.

#### Handling

### **Marning**

 Do not touch the inside of the driver and its peripheral devices.

Doing so may cause an electric shock or damage to the driver.

2. Do not perform the operation or setting of the product with wet hands.

Doing so may cause an electric shock.

Products with damage or those missing any components should not be used.

An electric shock, fire, or injury may result.

4. Use only the specified combination between the electric actuator and driver.

Failure to do so may cause damage to the actuator or the driver.

Be careful not to be hit by workpieces while the actuator is moving.

It may cause an injury.

Do not connect the power supply or power on the product before confirming the area to which the workpiece moves is safe.

The movement of the workpiece may cause an accident.

Do not touch the product when it is energised and for some time after power has been disconnected, as it is very hot.

Doing so may lead to a burn due to the high temperature.

Before installation, wiring, and maintenance, the voltage should be checked with a tester 5 minutes after the power supply has been turned off.

Otherwise, an electric shock, fire, or injury may result.

#### Handling

### **Marning**

Static electricity may cause malfunction or break the driver. Do not touch the driver while power is supplied.

When touching the driver for maintenance, take sufficient measures to eliminate static electricity.

10. Do not use the product in an area where dust, powder dust, water, chemicals, or oil is in the air.

It will cause failure or malfunction.

11. Do not use the product in an area where a magnetic field is generated.

It will cause failure or malfunction.

- Do not install the product in an environment containing flammable gas, explosive gas, or corrosive gas. It could lead to fire, explosion, or corrosion.
- Radiant heat from strong heat sources, such as a furnace, direct sunlight, etc., should not be applied to the product.

It will cause failure of the driver or its peripheral devices.

 Do not use the product in an environment subject to a temperature cycle.

It will cause failure of the driver or its peripheral devices.

15. Do not use the product in a place where surges are generated.

When there are units that generate a large amount of surge around the product (e.g. solenoid type lifters, high-frequency induction furnaces, motors, etc.), this may cause deterioration or damage to the product's internal circuit. Avoid sources of surge generation and crossed lines.

16. Do not install the product in an environment under the effect of vibrations and impacts.

It will cause failure or malfunction.

17. When a surge-generating load, such as a relay or solenoid valve, is driven directly, use a product that incorporates a surge absorption element.

#### Installation

### **⚠** Warning

 Install the driver and its peripheral devices on a fireproof material.

Direct installation on or near a flammable material may cause a

2. Do not install the product in a place subject to vibrations and impacts.

It will cause failure or malfunction.

- The driver should be mounted on a vertical wall in a vertical direction. Also, be sure not to cover the driver's suction/exhaust ports.
- 4. Install the driver and its peripheral devices on a flat surface.

If the mounting surface is distorted or uneven, an unacceptable force may be added to the housing, etc., causing problems.



₩

LECA6



### **LECS** Series **Specific Product Precautions 2**

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For electric actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

### **Power Supply**

### **⚠** Caution

1. Use a power supply that has low noise between lines and between the power and ground.

In cases where noise is high, an isolation transformer should be used

2. To prevent lightning surges, appropriate measures should be taken. Ground the surge absorber for lightning separately from the grounding of the driver and its peripheral devices.

#### Wiring


### **⚠** Warning

- 1. The driver will be damaged if a commercial power supply (100/200 V) is added to the driver's servo motor power (U, V, and W). Be sure to check wiring for mistakes when the power supply is turned on.
- 2. Connect the ends of the U, V, and W wires of the motor cable correctly to the phases (U, V, and W) of the servo motor power. If these wires do not match up, the servo motor cannot be controlled.

#### Grounding

### ⚠ Warning

1. For grounding the actuator, connect the copper wire of the actuator to the driver's protective earth (PE) terminal and connect the copper wire of the driver to the earth via the control panel's protective earth (PE) terminal. Do not connect them directly to the control panel's protective earth (PE) terminal.



2. In the unlikely event that a malfunction is caused by the ground, please disconnect it.

#### Maintenance

### 

- 1. Perform a maintenance and inspection periodically. Confirm wiring and screws are not loose. Loose screws or wires may cause unintentional malfunction.
- 2. Conduct an appropriate functional inspection after completing the maintenance and inspection.

At times where the equipment or machinery does not operate properly, conduct an emergency stop of the system. Otherwise, an unexpected malfunction may occur and it will become impossible to ensure safety. Conduct a test of the emergency stop in order to confirm the safety of the equipment.

- 3. Do not disassemble, modify, or repair the driver and its peripheral devices.
- 4. Do not put anything conductive or flammable inside the driver.

It may cause a fire.

- 5. Do not conduct an insulation resistance test or withstand voltage test on this product.
- 6. Ensure sufficient space for maintenance activities. Design the system allowing the required space for maintenance and inspection.



### MECHATROLINK Compatible

### **AC Servo Motor Driver Absolute Type**

### LECYM/LECYU Series


( MECHATROLINK-III Type)







### **How to Order**



Power supply voltage 200 to 230 VAC, 50/60 Hz

- \* If an I/O connector (CN1) is required, order the part number "LE-CYNA" separately.
- \* If an I/O cable (CN1) is required, order the part number "LEC-CSNA-1" separately.


Compatible motor type


Symbol	Туре	Capacity	Encoder
V5	AC servo motor (V6*1)	100 W	
V7	AC servo motor (V7*1)	200 W	Absolute
V8	AC servo motor (V8*1)	400 W	

\*1 The symbol shows the motor type (actuator).

### **Dimensions**

MECHATROLINK-II type






Connector name	Description
CN1	I/O signal connector
CN2	Encoder connector
CN3*1	Digital operator connector
CN6A	MECHATROLINK- I communication connector
CN6B	MECHATROLINK- II communication connector
CN7	PC connector
CN8	Safety connector


Digital operator is JUSP-OP05A-1-E manufactured by YASKAWA Electric Corporation. When using the digital operator, it should be provided by the customer.

Motor	Hole	Mou	nting o	dimens	sions	Mounting
capacity	position	Α	В	С	D	hole
<b>V5</b> (100 W)	12	5	_	5	5	
<b>V7</b> (200 W)	12	5	_	5	5	Ø 5
<b>V8</b> (400 W)	23	5	5	5	5	

The mounting hole position varies depending on the motor capacity.

### MECHATROLINK-III type **LECYU2-V**□





Connector name	Description
CN1	I/O signal connector
CN2	Encoder connector
CN3*1	Digital operator connector
CN6A	MECHATROLINK- II communication connector
CN6B	MECHATROLINK- II communication connector
CN7	PC connector
CN8	Safety connector

Digital operator is JUSP-OP05A-1-E manufactured by YASKAWA Electric Corporation. When using the digital operator, it should be provided by the customer.

Motor	Hole	Mou	nting o	dimens	sions	Mounting
capacity	position	Α	В	С	D	hole
<b>V5</b> (100 W)	12	5	_	5	5	
<b>V7</b> (200 W)	12	5	_	5	5	Ø 5
<b>V8</b> (400 W)	23	5	5	5	5	

 The mounting hole position varies depending on the motor capacity.



LEY

### AC Servo Motor Driver $LECY_U^M$ Series

### **Specifications**

MECHATROLINK-II	Type
-----------------	------

Model			LECYM2-V5 LECYM	12-V7 LE	CYM2-V8	
Compatible motor capa	city [W]		100 20	)	400	
Compatible encoder			Absolute 20-bit encoder (R	esolution: 1048576 p/rev)		
Main circuit power	Power voltage [\	/]	Three phase 200 to 2	30 VAC (50/60 Hz)		
supply	Allowable voltage fluctuation [V]		Three phase 17	0 to 253 VAC		
	Power voltage [V]		Single phase 200 to 2	30 VAC (50/60 Hz)		
Control power supply  Allowable voltage fluc		ctuation [V]	Single phase 1	0 to 253 VAC		
Power supply capacity	(at rated output) [	A]	0.91	;	2.8	
Input circuit	· /-		NPN (Sink circuit)/P	NP (Source circuit)		
Parallel input (7 inputs)	Number of 7 optional inputs		[Initial allocation]     Homing deceleration switch (/DEC)     External latch (/EXT 1 to 3)     Forward run prohibited (P-OT), reverse run pro [Can be allocated by setting the parameters]     Forward external torque limit (/P-CL), reverse of signal allocations can be performed, and positive	external torque limit (/N-CL)	changed.	
	Number of fixed allocations	1 output	· Servo alarm (ALM)			
Parallel output (4 outputs)	Number of optional allocations	3 outputs	[Initial allocation]     Lock (/BK)  [Can be allocated by setting the parameters]     Positioning completion (/COIN)     Speed limit detection (/VLT)     Speed coincidence detection (/V-CMP)     Rotation detection (/TGON)     Warning (/WARN)     Servo ready (/S-RDY)     Near (/NEAR)     Torque limit detection (/CLT)  Signal allocations can be performed, and positive	k (/BK)  be allocated by setting the parameters]  citioning completion (/COIN)  bed limit detection (/VLT)  bed coincidence detection (/V-CMP)  ation detection (/TGON)  rrning (/WARN)  vo ready (/S-RDY)  ar (/NEAR)		
	Communication protocol		MECHATR	OLINK-II		
	Station address		41H to 5FH			
	Transmission speed		10 Mbps			
MECHATROLINK	Transmission cy	/cle	250 μs, 0.5 ms to 4 ms (Multiples of 0.5 ms)			
communication	Number of transmission bytes		17 bytes, 32 bytes			
	Number of transmis	SSION DYLES	17 Dytes,			
	Max. number of		30 31 display 17 bytes,	32 bytes		
	Max. number of		30	32 bytes	0.5 m or more	
			Overall cable length: 50 m or less, Cable le	32 bytes ngth between the stations: 0		
Command method	Max. number of Cable length	stations	30	32 bytes  ngth between the stations: 0  MECHATROLINK-Ⅱ commu  K-Ⅱ command		
Command method	Max. number of Cable length	stations	30 Overall cable length: 50 m or less, Cable le Position, speed, or torque control with MECHATROLIN	ngth between the stations: 0 MECHATROLINK- II commod  -II command nitoring, or adjustment)	unication	
Command method	Max. number of Cable length Control method Command input	stations	30 Overall cable length: 50 m or less, Cable le Position, speed, or torque control with MECHATROLIN (Motion, data setting, mo	age bytes  Ingth between the stations: 0  MECHATROLINK- I community  (- I command initoring, or adjustment)  Ining/One-parameter tuning	unication	
Command method	Max. number of Cable length Control method Command input	stations	Overall cable length: 50 m or less, Cable le Position, speed, or torque control with MECHATROLIN (Motion, data setting, mo	age bytes  Ingth between the stations: 0  MECHATROLINK- I community  (- I command nitoring, or adjustment)  Ining/One-parameter tuning  S-422 communication	unication	
	Max. number of Cable length Control method Command input Gain adjustment Communication	stations	Overall cable length: 50 m or less, Cable le Position, speed, or torque control with MECHATROLIN (Motion, data setting, mo Tuning-less/Advanced auto tr USB communication, R	ngth between the stations: 0 MECHATROLINK- II commu K- II command nitoring, or adjustment) Ining/One-parameter tuning S-422 communication and torque limit by analogue	unication	
	Max. number of Cable length Control method Command input Gain adjustment Communication Torque limit	stations	Overall cable length: 50 m or less, Cable le Position, speed, or torque control with MECHATROLIN (Motion, data setting, mo Tuning-less/Advanced auto tr USB communication, R Internal torque limit, external torque limit,	ngth between the stations: 0 MECHATROLINK- II commod  K- II command nitoring, or adjustment) Ining/One-parameter tuning S-422 communication and torque limit by analogue the driver output	unication	
	Max. number of Cable length Control method Command input Gain adjustment Communication Torque limit Encoder output	stations	Overall cable length: 50 m or less, Cable le Position, speed, or torque control with  MECHATROLIN (Motion, data setting, mo Tuning-less/Advanced auto tr  USB communication, R Internal torque limit, external torque limit, Phase A, B, Z: Li	ngth between the stations: 0 MECHATROLINK- II commod  K-II command nitoring, or adjustment) Ining/One-parameter tuning S-422 communication and torque limit by analogue the driver output In function	unication e command	
	Max. number of Cable length Control method Command input Gain adjustment Communication Torque limit Encoder output Emergency stop	stations	Overall cable length: 50 m or less, Cable le Position, speed, or torque control with MECHATROLIN (Motion, data setting, mo Tuning-less/Advanced auto to USB communication, R Internal torque limit, external torque limit, Phase A, B, Z: Li CN8 Safet Dynamic brake stop, deceleration to a sto	angth between the stations: 0 MECHATROLINK- II commod  A-II command intoring, or adjustment) uning/One-parameter tuning S-422 communication and torque limit by analogue and torque limit by analogue and torque limit by analogue and torque limit by analogue and torque limit by analogue and torque limit by analogue and torque limit by analogue and torque limit by analogue and torque limit by analogue and torque limit by analogue and torque limit by analogue	unication e command	
Function	Max. number of Cable length Control method Command input Gain adjustment Communication Torque limit Encoder output Emergency stop Overtravel Alarm	stations	Overall cable length: 50 m or less, Cable le Position, speed, or torque control with  MECHATROLIN (Motion, data setting, mo Tuning-less/Advanced auto to USB communication, R Internal torque limit, external torque limit, Phase A, B, Z: Li CN8 Safet	angth between the stations: 0 MECHATROLINK- II common  K- II command nitoring, or adjustment) uning/One-parameter tuning S-422 communication and torque limit by analogue ne driver output function p, or free run to a stop at P-t ROLINK- II command	unication e command	
Function  Operating temperature	Max. number of Cable length Control method Command input Gain adjustment Communication Torque limit Encoder output Emergency stop Overtravel Alarm range [°C]	stations	Overall cable length: 50 m or less, Cable le Position, speed, or torque control with MECHATROLIN (Motion, data setting, mo Tuning-less/Advanced auto to USB communication, R Internal torque limit, external torque limit, Phase A, B, Z: Li CN8 Safet Dynamic brake stop, deceleration to a sto	angth between the stations: 0 MECHATROLINK- II common K- II command nitoring, or adjustment) uning/One-parameter tuning S-422 communication and torque limit by analogue ne driver output function p, or free run to a stop at P-1 ROLINK- II command freezing)	unication e command	
Function  Operating temperature Operating humidity ran	Max. number of Cable length Control method Command input Gain adjustment Communication Torque limit Encoder output Emergency stop Overtravel Alarm range [°C] ge [%RH]	stations	Overall cable length: 50 m or less, Cable le Position, speed, or torque control with MECHATROLIN (Motion, data setting, mo Tuning-less/Advanced auto to USB communication, R Internal torque limit, external torque limit, Phase A, B, Z: Li CN8 Safet Dynamic brake stop, deceleration to a sto Alarm signal, MECHAT 0 to 55 (No	angth between the stations: 0 MECHATROLINK- II common K-II command mitoring, or adjustment) uning/One-parameter tuning S-422 communication and torque limit by analogue ne driver output function p, or free run to a stop at P-0 ROLINK- II command freezing) condensation)	unication e command	
Function  Operating temperature Operating humidity ran Storage temperature ra	Max. number of Cable length Control method Command input Gain adjustment Communication Torque limit Encoder output Emergency stop Overtravel Alarm range [°C] ge [%RH] nge [°C]	stations	Overall cable length: 50 m or less, Cable le Position, speed, or torque control with MECHATROLIN (Motion, data setting, mo Tuning-less/Advanced auto to USB communication, R Internal torque limit, external torque limit, Phase A, B, Z: Li CN8 Safet Dynamic brake stop, deceleration to a sto Alarm signal, MECHAT 0 to 55 (No 90 or less (No -20 to 85 (No	angth between the stations: 0 MECHATROLINK- II common K-II command nitoring, or adjustment) uning/One-parameter tuning S-422 communication and torque limit by analogue ne driver output function p, or free run to a stop at P-0 ROLINK- II command freezing) condensation) or freezing)	unication e command	
Function  Operating temperature  Operating humidity ran	Max. number of Cable length Control method Command input Gain adjustment Communication Torque limit Encoder output Emergency stop Overtravel Alarm range [°C] ge [%RH]	stations	Overall cable length: 50 m or less, Cable le Position, speed, or torque control with MECHATROLIN (Motion, data setting, mo Tuning-less/Advanced auto to USB communication, R Internal torque limit, external torque limit, Phase A, B, Z: Li CN8 Safet Dynamic brake stop, deceleration to a sto Alarm signal, MECHAT 0 to 55 (No	angth between the stations: 0 MECHATROLINK-II common K-II command nitoring, or adjustment) Ining/One-parameter tuning S-422 communication and torque limit by analogue the driver output If function p, or free run to a stop at P-I ROLINK-II command freezing) Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/One-parameter tuning Ining/O	unication e command	



### $LECY_U^M$ Series


### **Specifications**

### ₩ MECHATROLINK-III Type

Model			LECYU2-V5	LECYU2-V7	LECYU2-V8		
Compatible motor cap	acity [W]		100	200	400		
Compatible encoder			Absolute	20-bit encoder (Resolution: 1048	576 p/rev)		
Main circuit power	Power voltage [\	<b>V</b> ]	Three phase 200 to 230 VAC (50/60 Hz)				
supply	Allowable voltage flu	uctuation [V]	Three phase 170 to 253 VAC				
Power voltage [V]		Sin	ngle phase 200 to 230 VAC (50/60	Hz)			
Control power supply  Allowable voltage fluctuation [V]				Single phase 170 to 253 VAC	•		
Power supply capacity	/ (at rated output) [	A1	0.91	1.6	2.8		
Input circuit		-	NI	PN (Sink circuit)/PNP (Source circ	cuit)		
Parallel input (7 inputs)	Number of optional allocations	7 inputs	[Can be allocated by setting the Forward external torque limit	T), reverse run prohibited (N-OT)	, ,		
	Number of fixed allocations	1 output	· Servo alarm (ALM)	<u>_</u>	<u> </u>		
Parallel output (4 outputs)	Number of optional allocations	3 outputs	[Initial allocation]     Lock (/BK)  [Can be allocated by setting the parameters]     Positioning completion (/COIN)     Speed limit detection (/VLT)     Speed coincidence detection (/V-CMP)     Rotation detection (/TGON)     Warning (/WARN)     Servo ready (/S-RDY)     Near (/NEAR)     Torque limit detection (/CLT)  Signal allocations can be performed, and positive and negative logic can be changed.				
	Communication protocol		MECHATROLINK-Ⅲ				
	Station address		03H to EFH				
	Transmission speed		100 Mbps				
MECHATROLINK	Transmission cycle		125 μs, 250 μs, 500 μs, 750 μs, 1 ms to 4 ms (Multiples of 0.5 ms)				
communication	Number of transmis		16 bytes, 32 bytes, 48 bytes				
	Max. number of		62				
	Cable length		Cable length between the stations: 0.5 m or more, 75 m or less				
	Control method		Position, speed, or torque control with MECHATROLINK-III communication				
Command method	Command input		MECHATROLINK-Ⅲ command (Motion, data setting, monitoring, or adjustment)				
	Gain adjustment	t	Tuning-less	s/Advanced auto tuning/One-para	meter tuning		
	Communication	setting	USB	communication, RS-422 commun	ication		
	Torque limit		Internal torque limit, ex	ternal torque limit, and torque lim	it by analogue command		
Function	Encoder output		Phase A, B, Z: Line driver output				
	Emergency stop		CN8 Safety function				
	Overtravel		Dynamic brake stop, deceleration to a stop, or free run to a stop at P-OT or N-OT				
Alarm		Alarm signal, MECHATROLINK-Ⅲ command					
Operating temperature	range [°C]		0 to 55 (No freezing)				
Operating humidity ra			90 or less (No condensation)				
Storage temperature r			-20 to 85 (No freezing)				
Storage humidity rang			90 or less (No condensation)				
				· · · · · · · · · · · · · · · · · · ·			
Insulation resistance [	[ <b>Μ</b> Ω]			10 MΩ (500 VDC)			

**Power Supply Wiring Example: LECY**□

#### ■Three phase 200 V LECYM2-□ LECYU2-□



1QF: Molded-case circuit breaker

1FLT: Noise filter

1KM: Magnetic contactor (for control power supply) 2KM : Magnetic contactor (for main circuit power supply)

\*1 For the LECY 2-V5, LECY 2-V7 and LECY 2-V8, terminals B2 and B3 are not short-circuited. Do not short-circuit these terminals.

### Main Circuit Power Supply Connector \* Accessory


Terminal name	Function	Details
L1	IVIAIN CIRCUIT NOWER	Connect the main circuit power supply.
L2		Single phase 200 to 230 VAC, 50/60 Hz Connection terminal: L1, L2
L3	Supply	Three phase 200 to 230 VAC, 50/60 Hz Connection terminal: L1, L2, L3
L1C	Control power supply	Connect the control power supply.
L2C		Single phase 200 to 230 VAC, 50/60 Hz Connection terminal: L1C, L2C
B1/⊕	External regenerative	When the regenerative resistor is required, connect it
B2	resistor	between terminals B1(+) and B2.
В3	connection terminal	Detween terminals DIT and DZ.
⊝1	Main circuit negative	
⊝2	terminal	Tanu -2 are connected at shipment.

Motor Connector \* Accessory

The constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant of the constant o					
	Terminal name	Function	Details		
	U	Servo motor power (U)			
	V	Servo motor power (V)	Connect to motor cable (U, V, W).		
	۱۸/	Serve motor newer (M)			


**Power Supply Wire Specifications** 

- cuel cappi, tine opecinications					
Item	Specifications				
Applicable	L1, L2, L3, L1C, L2C				
wire size	Single wire, Twisted wire, AWG14 (2.0 mm²)				
Stripped wire length	8 to 9 mm				




2SA: Surge absorber 3SA: Surge absorber

1D : Flywheel diode



### **LECY**<sup>M</sup> Series

### **Control Signal Wiring Example: LECYM**



<sup>\*1 \$\</sup>neq\$ shows twisted-pair wires.

<sup>\*2</sup> The 24 VDC power supply is not included. Use a 24 VDC power supply with double insulation or reinforced insulation.


<sup>\*3</sup> When using the safety function, a safety function device must be connected to the wiring that is necessary to activate the safety function. Otherwise, the servo motor is not turned ON. When not using the safety function, use the driver with the Safety Jumper Connector (provided as an accessory) inserted into the CN8.

<sup>\*4</sup> Always use line receivers to receive the output signals.

<sup>\*\*</sup> The functions allocated to the input signals /DEC, P-OT, N-OT, /EXT 1 , /EXT 2 and /EXT 3 , and the output signals /SO 1 , /SO 2 and /SO 3 can be changed by setting the parameters.

<sup>\*5</sup> It is a safety function equivalent to the STO function (IEC 61800-5-2) using the hard wire base block function (HWBB).

### Control Signal Wiring Example: LECYU



- \*1 \$\neq\$ shows twisted-pair wires.
- \*2 The 24 VDC power supply is not included. Use a 24 VDC power supply with double insulation or reinforced insulation.
- \*3 When using the safety function, a safety function device must be connected to the wiring that is necessary to activate the safety function. Otherwise, the servo motor is not turned ON. When not using the safety function, use the driver with the Safety Jumper Connector (provided as an accessory) inserted into the CN8.
- \*4 Always use line receivers to receive the output signals.
  - The functions allocated to the input signals /DEC, P-OT, N-OT, /EXT 1, /EXT 2 and /EXT 3, and the output signals /SO 1, /SO 2 and /SO 3 can be changed by setting the parameters.
- \*5 It is a safety function equivalent to the STO function (IEC 61800-5-2) using the hard wire base block function (HWBB).




### **LECY**<sup>M</sup> Series

### **Options**


Motor cable, Motor cable for lock option, Encoder cable (LECYM/LECYU common)

5

10 20




### LE-CYM-□□A-□: Motor cable




3 5

A

### LE-CYB-□□A-□: Motor cable for lock option



#### LE-CYE-□□A: Encoder cable



### Weight

Weight				
Product no.	Length [m]	Weight [g]	Note	
LE-CYM-S3A-5	3	250		
LE-CYM-S5A-5	5	390	100 W	
LE-CYM-SAA-5	10	750	100 00	
LE-CYM-SCA-5	20	1500		
LE-CYM-S3A-7	3	250		
LE-CYM-S5A-7	5	390	200/	
LE-CYM-SAA-7	10	750	400 W	
LE-CYM-SCA-7	20	1500		
LE-CYM-R3A-5	3	220		
LE-CYM-R5A-5	5	350	100 W	
LE-CYM-RAA-5	10	670	100 00	
LE-CYM-RCA-5	20	1300		
LE-CYM-R3A-7	3	220		
LE-CYM-R5A-7	5	350	200/	
LE-CYM-RAA-7	10	670	400 W	
LE-CYM-RCA-7	20	1300		

#### Weight

Weight	1911					
Product no.	Length [m]	Weight [g]	Note			
LE-CYB-S3A-5	3	240				
LE-CYB-S5A-5	5	390	100 W			
LE-CYB-SAA-5	10	750	100 00			
LE-CYB-SCA-5	20	1490				
LE-CYB-S3A-7	3	240				
LE-CYB-S5A-7	5	390	200/			
LE-CYB-SAA-7	10	750	400 W			
LE-CYB-SCA-7	20	1490				
LE-CYB-R3A-5	3	220				
LE-CYB-R5A-5	5	350	100 W			
LE-CYB-RAA-5	10	670	100 00			
LE-CYB-RCA-5	20	1300				
LE-CYB-R3A-7	3	220				
LE-CYB-R5A-7	5	350	200/			
LE-CYB-RAA-7	10	670	400 W			
LE-CYB-RCA-7	20	1300				


#### Weight

Length [m]	Weight [g]
3	230
5	360
10	680
20	1250
3	220
5	330
10	660
20	1240
	3 5 10 20 3 5 10

<sup>\*</sup> LE-CYM-S□A-□ is JZSP-CSM0□-□□-E manufactured by YASKAWA CONTROLS CO., LTD. LE-CYB-S□A-□ is JZSP-CSM1□-□□-E manufactured by YASKAWA CONTROLS CO., LTD. LE-CYE-S□A is JZSP-CSP05-□□-E manufactured by YASKAWA CONTROLS CO., LTD.


**Options** 


I/O connector (Without cable, Connector only)



- \* LE-CYNA: 10126-3000PE (connector)/10326-52F0-008 (shell kit) manufactured by 3M Japan Limited or equivalent
- \* Conductor size: AWG24 to 30

#### I/O cable





- \* LEC-CSNA-1: 10126-3000PE (connector)/10326-52F0-008 (shell kit) manufactured by 3M Japan Limited or equivalent
- \* Conductor size: AWG24

#### Wiring

LEC-CSNA-1: Pin nos. 1 to 26

Connector pin no.		Pair no. of wire	Insulation colour	Dot mark	Dot colour
	1	4	0		Red
	2		Orange		Black
	3	2	Light		Red
	4		gray		Black
ide	5	2	3 White		Red
A side	6	3	vviile		Black
_	7	4	Yellow		Red
	8	4	reliow		Black
	9 5	Diale	Pink		Red
	10	5	FILIK		Black

Connector pin no.		Pair no. of wire	Insulation colour	Dot mark	Dot colour
	11	6	0		Red
	12	0	Orange		Black
	13	7	Light		Red
	14	_ ′	gray		Black
A side	15	8	White		Red
AS	16	0	vvriite		Black
	17	9	Yellow		Red
	18	9	reliow		Black
	19	10	Pink		Red
	20	10	FILIK		Black

	nector n no.	Pair no. of wire	Insulation colour	Dot mark	Dot colour
	21	11	Orongo		Red
	22	11	Orange		Black
A side	23	12	Light		Red
S	24	12	gray		Black
	25	13	White		Red
	26	13	vviille		Black


Product no.	Ø D
LEC-CSNA-1	11.1

#### Dimensions/Pin No.

Product no.	W	Н	Т	U	Pin no. n
LEC-CSNA-1	39	37.2	12.7	14	14


### **LECY**<sup>M</sup> Series

### **Options**



- \* LEC-CYM-□ is JEPMC-W6002-□□-E manufactured by YASKAWA CONTROLS CO., LTD.
- \* LEC-CYU- $\square$  is JEPMC-W6012- $\square$ -E manufactured by YASKAWA CONTROLS CO., LTD.


### ₩ MECHATROLINK-II cable



#### Weight

Product no.	Length [m]	Weight [g]
LE-CYM-J	0.5	50
LE-CYM-1	1	80
LE-CYM-3	3	200

### **™**MECHATROLINK-**II** cable




#### Weight

Product no.	Length [m]	Weight [g]
LE-CYU-L	0.2	21
LE-CYU-J	0.5	41
LE-CYU-1	1	75
LE-CYU-3	3	205

### Terminating connector for ₩MECHATROLINK-II

### LEC-CYRM

\* LEC-CYRM is JEPMC-W6022-E manufactured by YASKAWA CONTROLS CO., LTD.



Weight: 10 g


Step Motor (Servo/24 VDC)/Servo Motor (24 VDC)

### **Options**





Drivers



### Setup software (SigmaWin+™) (LECYM/LECYU common)

\* Please download the SigmaWin+™ via our website. SigmaWin+™ is a registered trademark or trademark of YASKAWA Electric Corporation.

### Adjustment, waveform display, parameter read/write, and test operation can be performed upon a PC. Compatible PC

When using setup software (SigmaWin+TM), use an IBM PC/AT compatible PC that meets the following operating conditions.

#### **Hardware Requirements**

Equipment		Setup software (SigmaWin+™)	
*1, 2, 3, 4 PC	OS	Windows® XP*5, Windows Vista®, Windows® 7 (32-bit/64-bit)	
	Available HD space	350 MB or more (When the software is installed, 400 MB or more is recommended.)	
	Communication interface	Use USB port.	
Display		XVGA monitor (1024 x 768 or more, "The small font is used.") 256 colour or more (65536 colour or more is recommended.)	
		Connectable with the PC above	
Keyboard		Connectable with the PC above	
Mouse		Connectable with the PC above	
Printer		Connectable with the PC above	
USB cable		LEC-JZ-CVUSB*6	
Other		Adobe Reader Ver. 5.0 or higher (* Except Ver. 6.0)	


- \*1 Windows, Windows Vista®, Windows® 7 are registered trademarks of Microsoft Corporation in the United States and/or other countries.
- \*2 On some PCs, this software may not run properly.
- \*3 Not compatible with 64-bit Windows® XP and 64-bit Windows Vista®
- \*4 For Windows® XP, please use it by the administrator authority (When installing and using it.).
- \*5 In PC that uses the program to correct the problem of HotfixQ328310, it is likely to fail in the installation. In that case, please use the program to correct the problem of HotfixQ329623.
- \*6 Order USB cable separately.

### **Battery (LECYM/LECYU common)** LEC-JZ-CVBAT

\* JZSP-BA01 manufactured by YASKAWA CONTROLS CO., LTD.

Battery for replacement

Absolute position data is maintained by installing the battery to the battery case of the encoder cable.




#### USB cable (2.5 m)

### LEC-JZ-CVUSB

\* JZSP-CVS06-02-E manufactured by YASKAWA CONTROLS CO., LTD.

Cable for connecting PC and driver when using the setup software (SigmaWin+™)

Do not use any cable other than this cable.



\* The LEC-JZ-CVBAT is a single battery that uses lithium metal battery ER3V.

When transporting lithium metal batteries and devices with built-in lithium metal batteries by a method subject to UN regulations, it is necessary to apply measures according to the regulations stipulated in the United Nations Recommendations on the Transport of Dangerous Goods, the Technical Instructions (ICAO-TI) of the International Civil Aviation Organisation (ICAO), and the International Maritime Dangerous Goods Code (IMDG CODE) of the International Maritime Organisation (IMO). If a customer is transporting products such as shown above, it is necessary to confirm the latest regulations, or the laws and regulations of the country of transport on your own, in order to apply the proper measures. Please contact SMC sales representative for details.


### Cable for safety function device (3 m)

### LEC-JZ-CVSAF

\* JZSP-CVH03-03-E manufactured by YASKAWA CONTROLS CO., LTD.

Cable for connecting the driver and device when using the safety function

Do not use any cable other than this cable.



Weight: 160 g



Weight: 150 g



# LECYM/LECYU Series AC Servo Motor Driver Specific Product Precautions 1

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For electric actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

#### **Design / Selection**

### **⚠** Warning

1. Be sure to apply the specified voltage.

Otherwise, malfunction or breakage may occur. If the applied voltage is lower than the specified voltage, it is possible that the load will not be able to be moved due to an internal voltage drop of the driver. Please check the operating voltage before use.

2. Do not operate the product beyond the specifications.

Otherwise, a fire, malfunction, or actuator damage may result. Please check the specifications before use.

3. Install an emergency stop circuit.

Please install an emergency stop outside of the enclosure so that the system operation can be stopped immediately and the power supply can be intercepted.

- 4. In order to prevent any damage caused by the breakdown or malfunction of the driver and its peripheral devices, a backup system should be established in advance by giving a multiple-layered structure or a failsafe design to the equipment, etc.
- 5. If a danger of human injury is expected due to abnormal heat generation, smoking, ignition, etc., of the driver and its peripheral devices, cut off the power supply of the product and the system immediately.

#### Handling

### **⚠** Warning

1. Do not touch the inside of the driver and its peripheral devices.

Doing so may cause an electric shock or damage to the driver.

2. Do not perform the operation or setting of the product with wet hands.

Doing so may cause an electric shock.

Products with damage or those missing any components should not be used.

An electric shock, fire, or injury may result.

4. Use only the specified combination between the electric actuator and driver.

Failure to do so may cause damage to the actuator or the driver.

Be careful not to be hit by workpieces while the actuator is moving.

It may cause an injury.

Do not connect the power supply or power on the product before confirming the area to which the workpiece moves is safe.

The movement of the workpiece may cause an accident.

Do not touch the product when it is energised and for some time after power has been disconnected, as it is very hot.

Doing so may lead to a burn due to the high temperature.

8. Before installation, wiring, and maintenance, the voltage should be checked with a tester 5 minutes after the power supply has been turned off.

Otherwise, an electric shock, fire, or injury may result.

#### Handling

### **Marning**

Static electricity may cause malfunction or break the driver. Do not touch the driver while power is supplied.

When touching the driver for maintenance, take sufficient measures to eliminate static electricity.

Do not use the product in an area where dust, powder dust, water, chemicals, or oil is in the air.

It will cause failure or malfunction.

11. Do not use the product in an area where a magnetic field is generated.

It will cause failure or malfunction.

- 12. Do not install the product in an environment containing flammable gas, explosive gas, or corrosive gas. It could lead to fire, explosion, or corrosion.
- Radiant heat from strong heat sources, such as a furnace, direct sunlight, etc., should not be applied to the product.

It will cause failure of the driver or its peripheral devices.

14. Do not use the product in an environment subject to a temperature cycle.

It will cause failure of the driver or its peripheral devices.

Do not use the product in a place where surges are generated.

When there are units that generate a large amount of surge around the product (e.g. solenoid type lifters, high-frequency induction furnaces, motors, etc.), this may cause deterioration or damage to the product's internal circuit. Avoid sources of surge generation and crossed lines.

16. Do not install the product in an environment under the effect of vibrations and impacts.

It will cause failure or malfunction.

17. When a surge-generating load, such as a relay or solenoid valve, is driven directly, use a product that incorporates a surge absorption element.

#### Installation

### **Marning**

 Install the driver and its peripheral devices on a fireproof material.

Direct installation on or near a flammable material may cause a fire.

2. Do not install the product in a place subject to vibrations and impacts.

It will cause failure or malfunction.

- The driver should be mounted on a vertical wall in a vertical direction. Also, be sure not to cover the driver's suction/exhaust ports.
- Install the driver and its peripheral devices on a flat surface.

If the mounting surface is distorted or uneven, an unacceptable force may be added to the housing, etc., causing problems.



Ē

AC Servo Motor



### LECYM/LECYU Series **AC Servo Motor Driver Specific Product Precautions 2**

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For electric actuator and auto switch precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: https://www.smc.eu

### **Power Supply**

### **⚠** Caution

1. Use a power supply that has low noise between lines and between the power and ground.

In cases where noise is high, an isolation transformer should be used

2. To prevent lightning surges, appropriate measures should be taken. Ground the surge absorber for lightning separately from the grounding of the driver and its peripheral devices.

#### Wiring


### **⚠** Warning

- 1. The driver will be damaged if a commercial power supply (100/200 V) is added to the driver's servo motor power (U, V, and W). Be sure to check wiring for mistakes when the power supply is turned on.
- 2. Connect the ends of the U, V, and W wires of the motor cable correctly to the phases (U, V, and W) of the servo motor power. If these wires do not match up, the servo motor cannot be controlled.

### Grounding

### **⚠** Warning

1. For grounding the actuator, connect the copper wire of the actuator to the driver's protective earth (PE) terminal and connect the copper wire of the driver to the earth via the control panel's protective earth (PE) terminal. Do not connect them directly to the control panel's protective earth (PE) terminal.



2. In the unlikely event that a malfunction is caused by the ground, please disconnect it.

#### Maintenance

### 

- 1. Perform a maintenance and inspection periodically. Confirm wiring and screws are not loose. Loose screws or wires may cause unintentional malfunction.
- 2. Conduct an appropriate functional inspection after completing the maintenance and inspection.

At times where the equipment or machinery does not operate properly, conduct an emergency stop of the system. Otherwise, an unexpected malfunction may occur and it will become impossible to ensure safety. Conduct a test of the emergency stop in order to confirm the safety of the equipment.

- 3. Do not disassemble, modify, or repair the driver and its peripheral devices.
- 4. Do not put anything conductive or flammable inside the driver.

It may cause a fire.

- 5. Do not conduct an insulation resistance test or withstand voltage test on this product.
- 6. Ensure sufficient space for maintenance activities. Design the system allowing the required space for maintenance and inspection.



### **△** Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC) 1, and other safety regulations.

Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate

injury.

Warning indicates a hazard with a medium level of risk
 Warning: which, if not avoided, could result in death or serious

njury.

Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious

njury.

ISO 4414: Pneumatic fluid power – General rules relating to systems.
 ISO 4413: Hydraulic fluid power – General rules relating to systems.
 IEC 60204-1: Safety of machinery – Electrical equipment of machines.
 (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots - Safety.

### 

### 1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalogue information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

### 2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

#### Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.

- The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
- When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
- 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

#### Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.

- Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
- 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalogue.
- An application which could have negative effects on people, property, or animals requiring special safety analysis.
- 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

### **↑** Caution

#### 1. The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing industries.

If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary. If anything is unclear, contact your nearest sales branch.

## Limited warranty and Disclaimer/Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements". Read and accept them before using the product.

#### **Limited warranty and Disclaimer**

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first. <sup>2)</sup> Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalogue for the particular products.
- 2) Vacuum pads are excluded from this 1 year warranty. A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

#### **Compliance Requirements**

- The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

### **∧** Caution

### SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country.

Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

#### **Revision History**

#### **Edition C**

- The in-line motor type LEYD series has been added.
- The guide rod type LEYG series has been added.
- The guide rod type/in-line motor type LEYGD series has been added
- The LECP1 series programless controller has been added.
- A standard cable has been added to the actuator cable types.
   The AC servo motor (100/200 W) type LEYS series has
- The AC servo motor (100/200 W) type LEYS series has been added.
- The LECSA/LECSB series AC servo motor driver has been added.
- Number of pages has been increased from 38 to 94.

#### **Edition D**

- Size 40 has been added to the LEY/LEYG series step motor (servo/24 VDC).
- Size 63 has been added to the AC servo motor rod type LEY series.
- The dust-tight/water-jet-proof specification has been added to the rod type.
- Sizes 25 and 32 have been added to the AC servo motor guide rod type LEYG series.
- The LECPA series step motor driver has been added. - The LEC-G series gateway unit has been added.
- The LECSC/LECSS series AC servo motor driver has
- been added.
- UL-compliant products have been added.
- The controller setting kit (LEC-W2) has been changed.

YR

- Number of pages has been increased from 94 to 160.

#### Edition E

- Intermediate strokes have been added to the LEY63.
- Normally-closed solid state auto switches have been added.
  The JXC series step motor controller has been added.
- The controller setting kit has been changed to the
- communication cable for controller setting (LEC-W2A).
- Errors in text have been corrected.
- Number of pages has been increased from 160 to 286.

### **SMC Corporation (Europe)**

Δustria +43 (0)2262622800 www.smc.at office@smc.at Belgium +32 (0)33551464 www.smc.be info@smc.be Bulgaria +359 (0)2807670 office@smc.bg www.smc.bg Croatia +385 (0)13707288 www.smc.hr office@smc.hr **Czech Republic** +420 541424611 office@smc.cz www.smc.cz Denmark +45 70252900 www.smcdk.com smc@smcdk.com Estonia +372 6510370 www.smcpneumatics.ee info@smcee.ee Finland +358 207513513 smcfi@smc.fi www.smc.fi France +33 (0)164761000 www.smc-france.fr info@smc-france.fr Germany +49 (0)61034020 info@smc.de www.smc.de www.smchellas.gr Greece +30 210 2717265 sales@smchellas.gr Hungary +36 23513000 www.smc.hu office@smc.hu Ireland +353 (0)14039000 www.smcautomation.ie sales@smcautomation.ie +39 03990691 www.smcitalia.it mailbox@smcitalia.it Italy +371 67817700 Latvia info@smc.lv www.smc.lv

Lithuania	+370 5 2308118	www.smclt.lt	info@smclt.lt
Netherlands	+31 (0)205318888	www.smc.nl	info@smc.nl
Norway	+47 67129020	www.smc-norge.no	post@smc-norge.no
Poland	+48 222119600	www.smc.pl	office@smc.pl
Portugal	+351 214724500	www.smc.eu	apoioclientept@smc.smces.es
Romania	+40 213205111	www.smcromania.ro	smcromania@smcromania.ro
Russia	+7 8123036600	www.smc.eu	sales@smcru.com
Slovakia	+421 (0)413213212	www.smc.sk	office@smc.sk
Slovenia	+386 (0)73885412	www.smc.si	office@smc.si
Spain	+34 945184100	www.smc.eu	post@smc.smces.es
Sweden	+46 (0)86031200	www.smc.nu	smc@smc.nu
Switzerland	+41 (0)523963131	www.smc.ch	helpcentre@smc.ch
Turkey	+90 212 489 0 440	www.smcpnomatik.com.tr	info@smcpnomatik.com.tr
UK	+44 (0)845 121 5122	www.smc.uk	sales@smc.uk