


Proposal for Energy Saving in Factories

Helping you optimize your air pressure



Eco-Management

SMC Group Code of Conduct

We recognize that the preservation of global environment is an essential condition for our company's existence and activities as well as a common issue for all humanity. We will work on preserving and improving the environment where people can live safely with rich nature.

- 1 We will strive to develop and supply environment-friendly products.
- 2 We will consider protection of environment throughout the whole process of business operation.
 - We will comply with regulations on banned substances.
 - We will ensure proper treatment of wastewater and air exhaustion, and disposal of waste, and will work on reducing waste.
 - We will be thorough in our effort to save natural resources and energy.

Environmental Policy

- 1 We will identify the environmental impacts of our business activities, products and services and strive to reduce environmental burden and prevent pollution, and to make continual improvement of our environmental management system.
- 2 We will comply with all environment-related laws, regulations and agreements, and enhance collaboration with our customers, neighbors and local communities.
- 3 We will minimize the environmental impacts from our design, development and production activities.
 - (1) We will promote the development of environment-friendly products.
 - (2) We will use energy efficiently to prevent global warming.
 - (3) We will promote the reduction and recycling of waste.
- 4 We will ensure that the action plans are implemented properly to achieve the environmental objectives and goals.
- 5 We will make this policy known to all as well as release it to the general public.



This is a logo of SMC's environmental preservation activities. It is a heart-shaped design with a blue earth and a young leaf. The mark appears on our Environmental Policy as well as on documents and bulletins to enhance awareness among our employees.

CSR Promotion System

SMC has established a CSR Committee chaired by the President and has been taking initiatives in responding to customer requests and inquiries on CSR-related issues.

Main Tasks of the CSR Committee

- 1 To plan, develop and manage policies related to CSR and other matters.
- 2 To respond to questionnaires on CSR, etc., from users and corresponding to audits (site visits).
- 3 To conduct audits on the progress of implementation of policies related to CSR, etc.
- 4 To take necessary measures based on the progress of implementation of policies and audit results related to CSR, etc.

Environmental Training

SMC offers educational seminars and practical training on environmental issues for its employees, and also provides environmental training for environment-related partner companies. In addition, employees who hold their country's qualifications continuously attend follow-up training to enhance the quality of their knowledge and technical abilities.

Training conducted in FY2020

Environmental training for employees	7,319 attendees
Emergency response training	85 attendees
Training for front-line workers	504 attendees
Participation in external environment-related training sessions	22 attendees
Environmental training for environment-related partner companies	150 companies

Environmental Objectives, FY2020 Results and Evaluation

As part of its initiatives under the Environmental Management System (EMS) which adheres to ISO 14001, SMC defines a set of “Medium-Term Environmental Targets” to be achieved over a period of three years and “Environmental Targets” for each fiscal year, and manages and evaluates these progresses.


In FY2020, out of the “Environmental Targets” described below, SMC did not achieve “Prevention of global warming” and “Saving of resources”. The main reasons: with regard to “Prevention of global warming”, the production amount decreased but the air-conditioning energy use was significantly increased due to boosted ventilation to prevent infection by COVID-19, and, with regard to “Saving of resources”, a large equipment to improve productivity was disposed but the use of wooden pallets and wooden crate packaging in imports increased.

The main initiatives for FY2020 were as follows:


- 1 SMC conducted product assessments for designing and developing environmentally friendly products.
- 2 SMC recorded a 3.4% increase in CO₂ emissions per unit of production compared to the 7th Term (FY2017–2019) average. Waste discharged per unit of production increased 3.7% compared to the 7th Term (FY2017–2019) average.
- 3 All regional groups consisting of SMC’s major production facilities participated in climate change countermeasures organized by local governments and industry groups. They also were involved in community beautification activities and programs to build employee awareness.

	Environmental Targets		Results	Evaluation
		Medium-Term (To achieve in 3-year period of FY2020-2022)		
Product assessments (Environmental compatibility)	Design and develop environmentally friendly products - conduct assessments using score evaluation of current status		36 models 460 points	Achieved
	75 models or more 900 points or higher	25 models or more 300 points or higher		
Business activities (Environmental conservation)	Promote energy-saving, resource-saving and reduction of environmental burden through beneficial environmental activities in business activities (per unit of production)		—	
	Prevention of global warming - Reduction of CO2 emission vs previous term's average		3.4% increased	Not achieved
	Reduce 3% or more			
	Saving of resource - Reduction of waste discharge		3.7% increased	Not achieved
Reduce 3% or more				
Communication (Coexistence with society)	Social contribution activities - Community beautification activities		All regional groups conducted generally as planned	Mostly achieved
	Promotion of climate change actions		All regional groups conducted generally as planned	Mostly achieved
Participation in initiatives organized by local governments and industry groups. Implement awareness building programs.				

ISO 14001 Framework



Proposal for Energy-saving, Compact, and



First, figure out how much air is currently being used.

1

Plan piping in a way that saves energy.

3

4

5

Don't let any pressure go to waste! A few minor revisions → energy savings!

4

Are you replacing your elements?

4

1 Air consumption calculation

p. 7 ▶ 10

- Flow rate measurement
- Air blow measurement
- Pressure measurement



2 Air blow efficiency

p. 11 ▶ 17

Nozzles for blowing


Impact blow gun



3 Reduce air leakage

p. 18 ▶ 20

Air leakage from the One-touch fitting



Installation of a solenoid valve



4 Reduce pressure loss

p. 21 ▶ 26


Air filter clogging



7 Energy-saving circuit


p. 48 ▶ 52

Optimized cylinder driving system



8 Compact and lightweight products

p. 53 ▶ 75



Lightweight Air Systems

Pressure sensor devices Flow sensor devices

- Flow switch
- Pressure switch



Are your
operating
conditions ideal?

5

Air blow
adjustments
can lead to large
energy savings!

2

Search for air-
saving themes for
each device.

6

5

Air pressure source efficiency

p. 27 ▶ 30

- Reduce specific power
- Improve operation efficiency

Compressor



6

Air/Power saving equipment

p. 31 ▶ 46

Speed controller



Actuators



Solenoid valve




Directional control valve

Solenoid valve



Air consuming devices, Blow guns, Actuators, Flow control equipment, Vacuum equipment, etc.


Nozzle



Solenoid valve




Air cylinder



Solenoid valve




Gap checker



Vacuum equipment



Adsorption pad




9


Technical data

p. 76 ▶ 83

Energy-saving mindset



Changes in upstream conductance pressure loss



We will help you save energy.


Success stories of companies that implemented measures for energy saving

Company A performance		Company B performance	
Electricity consumption	3000 kW → 1400 kW	Electricity consumption	10000 kW → 7000 kW
CO ₂ emissions	1900 t reduction/year	CO ₂ emissions	3500 t reduction/year
Cost	JPY 48 million reduction/year	Cost	JPY 90 million reduction/year

* Companies in Japan. Amounts in Japanese yen. Electricity unit cost 15 JPY/kWh. Operating hour 2000 h/year. Electricity - CO₂ emissions conversion factor 0.587 kg - CO₂/kWh * SMC research

- We will help you to improve and standardize your equipment and adopt new equipment.
- We also proactively promote activities through official organizations, such as holding seminars at the Energy Conservation Center.

For energy saving in pneumatic systems, implement a **PDCA** cycle such as the one below. When following a PDCA cycle, the measuring of the usage amount before and after implementation is very important.



1

Air consumption calculation

Figuring out the cost of compressed air	p. 8
Calculation of compressed air energy	p. 9
Pressure and flow rate control	p. 10

As compressed air cannot be seen by the naked eye and can be released to the atmosphere without causing any harm, it's easy to remain unaware of how much it's costing. By figuring out the cost of compressed air (per unit), it is possible to calculate the annual cost of the compressed air being used in your pneumatic system. The following equation is the standard calculation method for finding the cost of compressed air.

Cost of compressed air [JPY/m³ (ANR)]

$$= \frac{\text{Electric power consumption [JPY/year]} + \text{Operating costs [JPY/year]} + \text{Maintenance costs [JPY/year]} + \text{Cost of equipment [JPY/year]}}{\text{Amount of air used for compressed air [m}^3 \text{ (ANR)]}}$$

The cost of compressed air can be calculated using the actual values of combined total costs and the amount of compressed air used.

Calculation method


The following equation is a simple calculation method for figuring out the cost of compressed air.

Calculation method ①...Calculating from the specific power

- The specific power can be found using the compressor rated output and discharge amount.
- The combined total of operating costs, maintenance costs, and the cost of equipment can be estimated to make up 25% of the cost.

Calculation method ②...When the amount of air and costs other than the cost of electricity are unknown

- The amount of air being used can be estimated as follows: operating hours x rated air discharge amount
- The combined total of operating costs, maintenance costs, and the cost of equipment can be estimated to be 25% of the cost of electricity.




Graph 1 Calculation method 1

Calculation example

When the compressor has a 15 kW output, a 3 m³/min (ANR) discharge flow, and the cost of electricity is 15 JPY/kWh

- ① Go up in a vertical line from the point of intersection of 3 m³/min (ANR) discharge flow and 15 kW compressor output.
- ② If you look to the left of the point of intersection with 15 JPY/kWh as the cost of electricity, you'll see that the cost of compressed air is 1.6 JPY/m³ (ANR).




Graph 2 Calculation method 2

Calculation example

When the compressor is operated for 3,000 hours/year, has a 20 m³/min (ANR) discharge flow, and electricity costs 10 million JPY/year to operate it

- ① Go up in a vertical line from the point of intersection of 20 m³/min (ANR) discharge flow and 3,000 hours of operation/year.
- ② If you look to the left of the point of intersection with 10 million JPY/year as the cost of electricity, you'll see that the cost of compressed air is 3.5 JPY/m³ (ANR).


To calculate the amount of compressed air per unit, the amount of electricity consumption, CO₂, calories, and crude oil are used.



Conversion factor

- Calculated with the specific power = 6 [kW/(m³/min (ANR))]
- Amount of electricity consumption → CO₂ conversion factor
Quote: The Ministry of Environment of Japan's website
Emission factors of electricity business operators (For the calculation of greenhouse gas emission amounts of specified businesses) — 2015 fiscal year results — Officially announced on December 27, 2016: (Substitute values)
- Amount of electricity consumption → Calorie conversion factor
Quote: The Agency for Natural Resources and Energy of Japan's website
Based on the annual reports of energy consumption in accordance with Article 15 and Article 19 (2) of the Act on Rationalizing Energy Use — February 7, 2017 revision: Use of daytime power purchase
- Calories → Crude oil conversion factor
Quote: Same as above

In order to figure out how much air is currently being used in your pneumatic system and to measure the effectiveness of the implemented measures, it is necessary to measure the flow rate and pressure. In addition, measuring the flow rate and pressure is also necessary in order to monitor the effectiveness and further improve upon the measures.



Measure the flow rate of the main line and of each device.

Measure the flow rate of each device and of the factory as a whole in order to figure out how much air is currently being used as well as to measure the effectiveness of the implemented measures.

1 Flow switch



Measure the air blow impact pressure.

In order to improve air blow, measure the impact pressure.

2 Manometer



Measure the pressure at each device.

Monitor pressure drops between the compressor and the devices.

3 Pressure switch




2

Air blow efficiency


Nozzles for Blowing KN Series 1	p. 12
Nozzles for Blowing KN Series 2	p. 13
Blow Gun VMG Series	p. 14
Impact Blow Gun IBG Series	p. 15
Impact Blow Valve IBV10-X5	p. 16
Pulse Blowing Valve AXTS Series	p. 17

CO₂ emissions
(Air consumption)**61%
reduction**

Comparison of Blow Effectiveness (Impact Pressure) Note: Fixed distance



Install a suitable nozzle where soft copper piping, etc., is cut and used as is to conduct blow.




By installing a suitable nozzle, the pressure right before the nozzle will rise immediately (①), resulting in improved blow efficiency. When the same operation is performed (②), air consumption can be reduced.

Nozzle with self-align fitting/
KNNozzle with male thread/
KN

Energy-saving Model

Supply pressure:

0.3 MPa



Collective piping: TU0805, 2 m
Intermediate and end piping:
TU0604, 0.5 m each
Distance: 100 mm

Air consumption per nozzle:
74 L/min (ANR)

Blow time: 2 sec.
Annual operating cycles:
900000

4464 m³/year (ANR) **61% reduction**CO₂ emissions: **261 kg/year****414 kg reduction in annual CO₂ emissions**

(¥6696/year)

(¥10584/year reduction)


Energy-saving Model

Effects of
Energy
Saving

Existing Model

Supply pressure:

0.3 MPa



Collective piping: TU0805, 2 m
Intermediate and end piping:
TU0604, 0.5 m each
Distance: 100 mm

Air consumption per copper tube:
192 L/min (ANR)

Blow time: 2 sec.
Annual operating cycles:
900000

11520 m³/year (ANR)CO₂ emissions: **675 kg/year**


(¥17280/year)

Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)**40%
reduction****Overall improvements can be seen by installing nozzles and revising piping and blow positioning.**

- Shorter copper pipes/Improved pipe branching
- Examination of blow position/Examination of number of blow operations
- Examination of hours of blow operation

**Energy-saving Model**

Reduced length and number of bends in copper pipes
Attachment of a nozzle (ø2) at the end of copper pipes

Flow rate per nozzle:

171 L/min (ANR)

Blow time: 2 sec.

Annual operating cycles: 900000

5130 m³/year (ANR) reductionCO₂ emissions: **301 kg/year****200 kg reduction in annual CO₂ emissions**

(¥7700/year)

(¥5130/year reduction)**40%****Energy-saving Model****Effects of
Energy
Saving****Existing Model**

Copper pipes with a lot of bends
Air blow directly from copper pipes

Flow rate per copper tube:

285 L/min (ANR)

Blow time: 2 sec.

Annual operating cycles: 900000

8550 m³/year (ANR)CO₂ emissions: **501 kg/year****(¥12830/year)****Existing Model**Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

* Refer to the "Energy Saving Program" on the SMC website for further details.

Related Products

Use to measure workpiece collision pressure.

Standard sensing head/**KNP**Needle sensing head/**KNP**

Standard sensing head



Needle sensing head





**Compact manometer
PPA series**

CO₂ emissions
(Power consumption)**20%
reduction****Power consumption can be reduced by 20% with the SMC blow gun + S coupler + coil tube combination.**

* 10% reduction with only the blow gun (VMG)

Pressure loss of **1% or less****Example of Improvement**

Review the blow work and change to the SMC blow gun, S coupler, and coil tube combination to create a larger effective area.

After improvement**Before improvement****Energy-saving Model**

Impact pressure: 0.011 MPa (Distance: 100 mm)
 Blow time: 10 s (Frequency: 12 times/h)
 Working hours: 10 h/day (250 days/year)
 Total working hours: 8300 h
 Compressor pressure: **0.5 MPa**
 Air consumption: **257 L/min (ANR)**

Power consumption by compressor:

1.25 kWCO₂ emissions: **6090 kg/year****1511 kg reduction in annual CO₂ emissions**

(¥155625/year)

(¥38595/year reduction)

**20%
reduction****Energy-saving Model****Effects of
Energy
Saving****Existing Model**

Impact pressure: 0.011 MPa
 (Distance: 100 mm)
 Blow time: 10 s
 (Frequency: 12 times/h)
 Working hours: 10 h/day
 (250 days/year)
 Total working hours: 8300 h
 Compressor pressure: 0.6 MPa
 Air consumption: 287 L/min (ANR)

Power consumption by compressor:

1.56 kWCO₂ emissions: **7601 kg/year**

(¥194220/year)

Existing ModelCorresponding value: Electricity unit ¥15/kWh, Power consumption – CO₂ conversion factor 0.587 kg - CO₂/kWh

High peak pressure

**3 times
or more**^{*1}
(Compared with
the existing model)


CO₂ emissions
(Air consumption)

**87%
reduction**^{*2}

**Increased impact
force due to higher
peak pressure
Drastic reduction in
air consumption and
labor time**



*1 According to blow requirements
*2 Pressure: 0.5 MPa
(Based on SMC's specific testing conditions)



Energy-saving Model

Effects of
Energy
Saving

Existing Model

Application examples:
Cutting chip removal
Pressure: 0.5 MPa^{*1}
Nozzle size: ø10
Removal time (1 operation):
0.1 s
Air consumption:
0.8 L (ANR)



*1 The removal of cutting chips
adhered to the clamping unit

When operating for 2500 hours/year,
120 removal operations/hour

240 m³/year (ANR)

CO₂ emissions: 14 kg/year

96 kg reduction in annual CO₂ emissions

(¥360/year)

(¥2475/year reduction)

**87%
reduction**

Energy-saving Model

Application examples:
Cutting chip removal
Pressure: 0.5 MPa^{*1}
Nozzle size: ø2
Removal time (1 operation):
3.1 s
Air consumption:
6.3 L (ANR)



*1 The removal of cutting chips
adhered to the clamping unit

When operating for 2500 hours/year,
120 removal operations/hour


1890 m³/year (ANR)

CO₂ emissions: 110 kg/year

(¥2835/year)


Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)



Increased impact force due to higher peak pressure
Drastic reduction in air consumption and labor time

Solenoid Type/IBV10-X5



^{*1} According to blow requirements When the piping volume is 100 cc (Piping I.D. ø13, 800 mm)

^{*2} Pressure: 0.5 MPa (Based on SMC's specific testing conditions)

Energy-saving Model

Application examples:

Cutting chip removal

Pressure: 0.5 MPa^{*1}

Nozzle size: ø10

Removal time (1 operation): 0.1 s

Air consumption: 0.6 L (ANR)

^{*1} The removal of cutting chips caught up in the blades

When operating for 2500 hours/year,
60 removal operations/hour


90 m³/year (ANR)

CO₂ emissions: **5 kg/year**

65 kg reduction in annual CO₂ emissions

(¥135/year)

(¥1665/year reduction)



Effects of Energy Saving

Existing Model

Application examples:

Cutting chip removal

Pressure: 0.5 MPa^{*1}

Nozzle size: ø2

Removal time (1 operation): 4 s

Air consumption: 8 L (ANR)

^{*1} The removal of cutting chips caught up in the blades

When operating for 2500 hours/year,
60 removal operations/hour

1200 m³/year (ANR)



CO₂ emissions: **70 kg/year**

(¥1800/year)





Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)**50%
reduction****Proposal for air-saving air blow by changing from continuous blow to intermittent blow**

Control for pulse generation is not required. Pulse blow can be used by simply supplying air.



Long service life (200 million cycles or more)

ON/OFF time adjustable individually

Flow rate characteristics

Operating pressure range: 0.2 to 1.0 MPa


Type of actuation	C [dm ³ /(s·bar)]	b	Cv
External pilot	14	0.18	3.4
Internal pilot	12	0.14	2.9

Energy-saving Model

Changing to pulse air blow

Flow rate per nozzle:
142.5 L/min (ANR)Blow time: 2 sec. (Duty 50%)
Annual operating cycles: 900000**4275 m³/year (ANR)**CO₂ emissions: **251 kg/year****250 kg reduction in annual CO₂ emissions**(**¥6413/year**)(**¥6413/year reduction**)

* Per nozzle

**Effects of
Energy
Saving****Existing Model**

Air blow accounts for 50% of all air consumption

Flow rate per nozzle:
285 L/min (ANR)Blow time: 2 sec
Annual operating cycles: 900000**8550 m³/year (ANR)**CO₂ emissions: **501 kg/year**(**¥12825/year**)Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

3 Reduce air leakage

Air leakage	p. 19
Reducing leakage and purge during non-operating hours	p. 20


Stops leakage from piping equipment

Before improvement

Leaked air actually accounts for 20 to 50% of all consumed air.

Regardless of whether equipment is being operated or not, as the compressor is continually operated, a certain amount of air is consumed and leaked from piping equipment.


Compressor operating status



Air usage


Tubing, Fittings	20%
Coupling fittings	25%
Rubber hose	30%
Others	25%

Air leakage accounts for 20 to 50%.




Air leakage examples


Air leakage from One-touch fittings due to poorly cut tubes



Air leakage from coupling fittings due to poor sealing




Air leakage from tubes due to cutting chips, wear, spatter, etc.



After improvement

① Selection of equipment with minimal leakage

S Coupler
KK Series


Effects of
Energy
Saving

Air consumption
↓
**100%
reduction**


Energy-saving Model

Existing Model

② Adjustment of tube cut surfaces with a dedicated tool

Tube Cutter
TK SeriesDouble Layer Tube Stripper
TKS Series

③ Adoption of double layer tubing to prevent tube damage due to cutting chips, spatter, and wear


Double Layer Tubing
TRB/TRBU Series

Sectional view of FR double layer tubing

Reducing air leakage and amount of air used for air purge during non-operating hours of equipment


Before improvement

As the compressor is continually operated even during non-operating hours of equipment, it continues to consume air through air leakage, air purge, etc.



After improvement

Stop the supply of air during non-operating hours of equipment.



Installation of a solenoid valve in each line and for each piece of equipment

Pilot Operated 2-Port
Solenoid Valve
VXD21/22/23 Series



Pilot Operated 3-Port
Solenoid Valve
VG342 Series



Pilot Operated 3-Port
Solenoid Valve
VP3145/3165/3185 Series



Effects of
Energy
Saving

Air consumption
↓
**100%
reduction**

After improvement

Before improvement

4


Reduce pressure loss

Monitoring of air filter clogging.....	p. 22
For reducing pressure loss in lines S Couplers KK130 Series	p. 23
Main Line Filter AFF Series	p. 24
Modular Connection Type Micro Mist Separator AMD Series	p. 25
Leveling of the line pressure	p. 26

As the air filter processes the compressed air, the element will gradually become clogged, resulting in a pressure drop. Failure to rectify the situation will result in energy loss and reduced actuator output. Therefore, be sure to periodically replace the air filter element before it becomes clogged.


Clogging indicator

The air filter element needs to be replaced every 2 years or before the pressure drop reaches 0.1 MPa. Confirm the pressure drop due to clogging with the element service indicator, a differential pressure switch, or a differential pressure gauge.




Replace the element

when **the red indicator reaches the top.**




When the differential air is 0.05 MPa → When the differential air is **0.1 MPa**



- Confirm the differential pressure by **electrical signal.**
- With an indicator for easy **visual confirmation**



Differential pressure gauge




Replace the element

when **the needle enters the red zone**
(Differential pressure of **0.1 MPa** or more).



4

Reduce
pressure lossFor reducing pressure loss in lines
S Couplers *KK130 Series*CO₂ emissions
(Pressure loss)**4%**
reductionThe built-in valve is of a special shape, resulting
in reduced pressure loss.**Energy-saving Model**

Operating pressure at the outlet: 0.5 MPa
Compressor efficiency: 0.7
Annual operating time: 2500 hours
Flow rate: 1.2 m³/min (ANR)

Inlet pressure:
0.54 MPa

Power consumption by compressor:

CO₂ emissions: **10258 kg/year**

425 kg reduction in annual CO₂ emissions

(¥262000/year)

(¥11000/year reduction)

4%
reduction

Energy-saving Model

**Effects of
Energy
Saving****Existing Model**

Operating pressure at the outlet: 0.5 MPa
Compressor efficiency: 0.7
Annual operating time: 2500 hours
Flow rate: 1.2 m³/min (ANR)

Inlet pressure:
0.58 MPa

Power consumption by compressor:

CO₂ emissions: **10683 kg/year**

(¥273000/year)

Existing Model

Corresponding value: Electricity unit ¥15/kWh, Power consumption – CO₂ conversion factor 0.587 kg – CO₂/kWh


4

Reduce
pressure lossMain Line Filter *AFF Series*


Flow Capacity

20%
increase

Flow capacity: 14.5 m³/min (ANR)
Pressure drop: 5 kPa or less



Reduction in
pressure drops!
Increased air flow
capacity!

Size	Filtration	Port size	Flow capacity m³/min (ANR)			
 AFF70D AFF80D AFF90D	1 μm*1	1, 1 1/2	<div><div>7.0</div><div>6.0</div></div> AFF37B (Existing model)			
		1 1/2	11.0			
		1 1/2, 2	<div><div>14.5</div><div>12.0</div></div> AFF75B (Existing model)			

*1 ISO 8573-4: 2010 compliant

4

Reduce
pressure loss

Modular Connection Type


Micro Mist Separator *AMD Series*

Flow Capacity

**50%
increase**

Flow capacity: 1.5 m³/min (ANR)
Pressure drop: 6.8 kPa or less

AMD40: 6.8 kPa
 (Existing model AMD350C: 13.6 kPa)




**Reduction in
pressure drops!
Increased air flow
capacity!**

Size	Filtration	Port size	Flow capacity m³/min (ANR)									
AMD20	0.01 μm*1	1/8, 1/4	<div><div></div><div>0.3</div></div>									
			<div><div></div><div>0.2</div><div>AMD150C (Existing model)</div></div>									
AMD30		1/4, 3/8	<div><div></div><div>0.75</div></div>									
			<div><div></div><div>0.5</div><div>AMD250C (Existing model)</div></div>									
AMD40		1/4, 3/8, 1/2	<div><div></div><div>1.5</div></div>									
			<div><div></div><div>1.0</div><div>AMD350C (Existing model)</div></div>									

*1 ISO 8573-4: 2010 compliant

Uneven terminal pressure in branch piping can be leveled by adopting loop piping, resulting in a reduction in pressure drops.




Air can be supplied from both sides with loop piping.

Terminal pressure is leveled.

The discharge pressure setting can be lowered.

An unbalanced consumption flow rate can lead to a large pressure drop in the line on one side.

Set the discharge pressure high.



Corresponding value: Electricity unit ¥15/kWh, Power consumption – CO₂ conversion factor 0.587 kg - CO₂/kWh

5

Air pressure source efficiency

Reducing the specific power of the compressor	p. 28
More efficient compressor operation	p. 29
Booster circuit.....	p. 30

CO₂ emissions
(Power consumption)**8%**
reduction**Power consumption can be reduced by reducing the discharge pressure, intake resistance, and intake temperature.**

The discharge pressure, intake pressure, and intake temperature, as well as the number of compression stages, etc., all have an effect on the compressor's specific power. Therefore, in order to reduce the compressor's specific power, the discharge pressure, intake resistance, and intake temperature must all be reduced as well.

Calculating the specific power of the compressor

The specific power can be calculated from the theoretical shaft power as shown in the equation on the right.

For the specific power, the smaller the value, the greater the efficiency.


L : theoretical shaft power [kW], r : specific power [kW/(m³/min (ANR))], Q : discharge flow [m³/min (ANR)], p_s : intake pressure [MPa], p_d : discharge pressure [MPa], T : intake temperature [°C], η : efficiency, m : number of compression stages, and κ : specific heat ratio (air = 1.4)

$$L = \frac{m\kappa}{\kappa-1} \cdot \frac{0.1Q}{0.06\eta} \cdot \frac{273+T}{293} \times \left\{ \left[\frac{p_d+0.1}{p_s+0.1} \right]^{\frac{\kappa-1}{m\kappa}} - 1 \right\}$$


$$r = \frac{L}{Q}$$

Effects of the discharge pressure on the specific power


By reducing the discharge pressure from 0.7 MPa to 0.6 MPa, the specific power can be reduced by 8%.

**Effects of the intake pressure on the specific power**

By increasing the intake pressure from -20 kPa to -10 kPa, the specific power can be reduced by 7%.

**Effects of the intake temperature on the specific power**

By reducing the intake temperature from 45°C to 30°C, the specific power can be reduced by 5%.




Corresponding value: Power consumption – CO₂ conversion factor 0.587 kg - CO₂/kWh

CO₂ emissions
(Power consumption)**38%
reduction**

Power consumption can be reduced by selecting an optimal operation to deal with load fluctuations.


Increased energy efficiency can be realized when the operation selected to deal with and control compressor load (flow rate) fluctuations is optimal.



Fluctuations in factory air consumption flow rates


The factory air consumption flow rate (= load) changes depending on the operating state of the equipment. By using inverter control or control for multiple compressors to deal with consumption flow rate fluctuations, compressor energy efficiency can be increased.

Suitable operation



Inverter control for the control of consumption flow rate fluctuations when multiple compressors are operated

Before improvement



Open/close control for the control of consumption flow rate fluctuations when 1 compressor is operated

Suitable Operation

Base compressor (Screw type)
110 kW, Discharge flow 19 m³/min (ANR)
+
Fluctuation-absorbing compressor (Screw type, Inverter control)
110 kW, Discharge flow 19 m³/min (ANR)
Days of operation per year: 250 days

Annual cost of electricity
12.32 million JPY/year
CO₂ emissions: **482162 kg/year**
292678 kg reduction in annual CO₂ emissions
(¥7480000/year reduction)

Suitable operation

Effects of Energy Saving

Before Improvement

Compressor (Screw type, Suction restriction control)
220 kW, Discharge flow 40 m³/min (ANR)
Days of operation per year: 250 days

Annual cost of electricity
19.80 million JPY/year
CO₂ emissions: **774840 kg/year**


Before improvement

Corresponding value: Electricity unit ¥15/kWh, Power consumption – CO₂ conversion factor 0.587 kg – CO₂/kWh


CO₂ emissions
(Air consumption)**33%**
reductionAir consumption can be
reduced by **33%** due to
the optimization of the
booster circuit.**Boost an insufficiently powered portion with a booster regulator**

- Optimized booster circuit: Now with a space-saving booster circuit

Example of a one-side booster circuit
(Boosting pressure on the operating stroke only)



Example of a two-side booster circuit

**Energy-saving Circuit**

When boosting pressure is on the
extension side only
Retraction: 0.4 MPa
Extension: 0.8 MPa (Boosting pressure)

Air consumption:
8.7 L (ANR)/cycle

When it is operated
900000 times/year

7830 m³/year (ANR) **33% reduction**
CO₂ emissions: **459 kg/year**
227 kg reduction in annual CO₂ emissions

(¥11750/year)
(¥5800/year reduction)

Energy-saving Circuit

Effects of
Energy
Saving**Existing Circuit**

Bore size: ø50
Stroke: 200 mm
Pressure: 0.4 MPa
Boosting pressure: 0.8 MPa

Air consumption:
13 L (ANR)/cycle

When it is operated
900000 times/year

11700 m³/year (ANR)
CO₂ emissions: **686 kg/year**

(¥17550/year)

Existing Circuit

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

6


Air/Power saving equipment

Low Wattage 3/4/5-Port Solenoid Valve	p. 32
Air Cylinder (Intermediary Bore Size) JMB Series	p. 33
Double Power Cylinder MGZ Series	p. 34
Compact Cylinder with Solenoid Valve CVQ Series	p. 35
Compact Cylinder/Air Saving Type CDQ2B-X3150	p. 36
End Power Cylinder CDQ2A-X3260	p. 37
Vacuum Ejector ZK2□A Series	p. 38
Multistage Ejector ZL3 Series	p. 39
Booster Regulator VBA-X3145	p. 40
Air Consumption-reducing Precision Regulator	p. 41
Air Saving Speed Controller AS-R Series	p. 42
Digital Gap Checker ISA3 Series	p. 43
Intermittent Blow Circuit IZE110-X238	p. 44
Pulse Valve Valve for Dust Collector JSXFA Series	p. 45
Refrigerated Air Dryer IDF□FS Series	p. 46

CO₂ emissions
(Power consumption)**75%**
reduction


The power-saving circuit can reduce the consumption of electric power when the device is energized.

SY Series




JSY Series

Plug-in Type



Non Plug-in Type

SY Series
Plug-in type


VP Series



- Reduces power consumption when energized

Power consumption can be reduced by approx. 1/4 by reducing the wattage required to hold the valve in an energized state. (Effective energizing time is over 62 ms*1 at 24 VDC.) Refer to the electrical power waveform as shown below.

Electrical power waveform with power-saving circuit



*1 SY/SYJ series

Low Wattage Valve

Energy-saving Product

Type	Model	Power consumption W*2	
		Standard	With power-saving circuit
4/5-port	SJ1000/2000	0.55	0.23
	SJ3000	0.4	0.15
	New SY3000/5000/7000	0.4	0.1
	SY3000/5000/7000	0.4	0.1
	JSY1000	—	0.2
	JSY3000/5000	0.4	0.1
	SYJ3000/5000/7000	0.4	0.1
3-port	V100	0.4	0.1
	SYJ300/500/700	0.4	0.1
	VP300/500	0.4	—
	VP700	1.55	0.55

*2 With DC light

Energy-saving Model

SY: 0.1 W

When the energizing time is 8 hours/day,
365 days/year

Power consumption per valve:

292 Wh/yearCO₂ emissions: **0.17 kg/year****0.52 kg reduction in annual CO₂ emissions**

(¥4.3/year)

(¥13.2/year reduction)



Energy-saving Model

Effects of
Energy
Saving

Existing Model

SY: 0.4 W

When the energizing time is 8 hours/day,
365 days/year

Power consumption per valve:

1168 Wh/yearCO₂ emissions: **0.69 kg/year**

(¥17.5/year)

Existing Model

Corresponding value: Electricity unit ¥15/kWh, Power consumption – CO₂ conversion factor 0.587 kg - CO₂/kWh

CO₂ emissions
(Air consumption)**29%**
reductionAir consumption can be reduced by
selecting an optimal size
air cylinder.

Intermediary Bore Sizes

Air consumption can be reduced by up to **29%**

Bore size (mm)	ø40	ø45	ø50	ø56	ø63	ø67	ø80	ø85	ø100
Air consumption L/min (ANR)	1.4	1.8	2.2	2.8	3.6	4.1	5.8	6.6	9.1

Conditions/Supply pressure: 0.5 MPa
Load factor: 50%, At 100 mm stroke**18% reduction****22% reduction****29% reduction****27% reduction****Example** Bore size for 85 kg workpieces

Conditions/Supply pressure: 0.5 MPa, Load factor: 50%

Bore size (mm)	Theoretical output (N)	Output for load factor of 50% (kg)	Judgment
ø63	1559	79.5	Not acceptable (Insufficient)
ø80	2513	128.2	Acceptable (Excessive)

When intermediary bore size ø67 is used

ø67	1763	89.9	OK
-----	------	------	----

Existing size: ø80

Could be switched to
intermediary bore size **ø67**

Energy-saving Model

Bore size: ø67
Stroke: 100 mm
Pressure: 0.5 MPa
Load factor: 50%Air consumption:
4.1 L (ANR)/cycleWhen it is operated
1000000 times/year**4100 m³/year (ANR)** **29% reduction**CO₂ emissions: **240 kg/year****100 kg reduction in annual CO₂ emissions**

(¥6150/year)

(¥2550/year reduction)

Energy-saving Model

Effects of
Energy
Saving

Existing Model

Bore size: ø80
Stroke: 100 mm
Pressure: 0.5 MPa
Load factor: 50%Air consumption:
5.8 L (ANR)/cycleWhen it is operated
1000000 times/year**5800 m³/year (ANR)**CO₂ emissions: **340 kg/year**

(¥8700/year)

Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)


CO₂ emissions
(Air consumption)**14%
reduction****Air consumption can be reduced by 14%
due to the reduced cylinder size.**

It is possible to reduce air consumption in the retracting direction, compared with a standard cylinder with equivalent output in the extending direction, due to the doubled piston area in the extending direction.



**Double extension output power!**

SMC's unique cylinder construction doubles the piston area in the extending direction. This is an ideal air cylinder for lifting and press applications.

Air pressure supplied from A operates on both surfaces ① and ②. (Extension)



Air pressure supplied from B operates on surface ③. (Retraction)




ø63

Piston area
Extension: 5945 mm²
Retraction: 2313 mm²

Increased energy saving and space saving
Reduced cylinder size

Size reduction
ø63 ← ø80



ø80

Piston area
Extension: 5030 mm²
Retraction: 4540 mm²

Energy-saving Model

Bore size: ø63

Stroke: 200 mm

Pressure on the extension side: 0.5 MPa

Theoretical output (Extension side): 2973 N

Air consumption:

9.9 L (ANR)/cycle

When it is operated
900000 times/year

8910 m³/year (ANR) **14% reduction**CO₂ emissions: **522 kg/year****85 kg reduction in annual CO₂ emissions**

(¥13370/year)

(¥2160/year reduction)**Energy-saving Model****Effects of
Energy
Saving****Existing Model**

Bore size: ø80

Stroke: 200 mm

Pressure: 0.5 MPa

Theoretical output (Extension side): 2520 N

Air consumption:

11.5 L (ANR)/cycle

When it is operated
900000 times/year

10350 m³/year (ANR)CO₂ emissions: **607 kg/year**



(¥15530/year)

Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)**50%**
reduction

Energy Saving

Air consumption between the valve and cylinder can be reduced by approximately **50%**.**Valve and compact cylinder integrated for compactness**

Energy-saving Model

Bore size: $\phi 32$
 Stroke: 30 mm
 No piping between the valve and the cylinder
 Supply pressure: 0.5 MPa

Air consumption:
0.25 L (ANR)/cycle

When it is operated
 900000 times/year


228 m³/year (ANR)

CO₂ emissions: **13 kg/year**

13 kg reduction in annual CO₂ emissions

(¥342/year)

(¥341/year reduction)



Energy-saving Model

Existing Model



Bore size: $\phi 32$
 Stroke: 30 mm
 Piping bore: 4 mm
 Piping length: 2 m
 (Between the valve and the cylinder)
 Supply pressure: 0.5 MPa

Air consumption:
0.51 L (ANR)/cycle

When it is operated
 900000 times/year


455 m³/year (ANR)

CO₂ emissions: **26 kg/year**

(¥683/year)

Existing Model


Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)Max. **46%**
reductionReduced air consumption
due to the built-in exhaust return circuit


Built-in exhaust return circuit

- Built-in check valve and throttle valve
- With centralized piping

Uses the air exhausted from the working side to supply the non-working side, thus reusing the air

Reduce air consumption just
by piping to the product

Circuit Diagram



Energy-saving Model

Bore size: $\phi 50$
Stroke: 100 mm
Pressure: 0.5 MPa

Air consumption per cycle
1.2 L (ANR)

When it is operated
1000000 times/year

1200 m³/year (ANR) **46% reduction**

CO₂ emissions: **70 kg/year**

59 kg reduction in annual CO₂ emissions

(¥1800/year)

(¥1500/year reduction)

Energy-saving Model

Effects of
Energy
Saving

Existing Model

Bore size: $\phi 50$
Stroke: 100 mm
Pressure: 0.5 MPa

Air consumption per cycle
2.2 L (ANR)

When it is operated
1000000 times/year

2200 m³/year (ANR)

CO₂ emissions: **129 kg/year**


(¥3300/year)

Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)**73%**
reduction


Energy saving can be achieved by using the assist cylinder to reach the output stroke position.



Output working principle


Extending operation in progress

Since the air passage ① is open while the assist cylinder is operating, the output cylinder is acting as a tank. (Air is not being consumed.)



When output is generated

When the piston of the output cylinder reaches the output stroke, the air passage ① is closed, the output port ② opens, causing a pressure differential, and cylinder output force is generated.



Energy-saving Model

Bore size: ø50
Stroke: 200 mm
Pressure: 0.5 MPa

Air consumption per cycle
1.2 L(ANR)

When it is operated
1000000 times/year

1200 m³/year (ANR)

CO₂ emissions: **70 kg/year**

182 kg reduction in annual CO₂ emissions

(¥1800/year)

(¥4700/year reduction)

73%
reduction

Energy-saving Model

Effects of Energy Saving

Existing Model

Bore size: ø50
Stroke: 200 mm
Pressure: 0.5 MPa

Air consumption per cycle
4.3 L(ANR)

When it is operated
1000000 times/year

4300 m³/year (ANR)

CO₂ emissions: **252 kg/year**

(¥6500/year)

Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

A digital pressure switch for vacuum with an energy-saving function and a more efficient ejector

CO₂ emissions
(Air consumption)

**93%
reduction***1

*1 Based on SMC's measuring conditions

Cuts off supply air when the pressure reaches the desired vacuum

Energy saving ejector

The digital pressure switch with energy-saving function can reduce

Air consumption 90% reduction*2




*2 Based on SMC's measuring conditions

While the suction signal is ON, the ON/OFF operation of the supply valve is also performed automatically within the set value.

More efficient ejector

Air consumption 30% reduction

(Compared to other SMC single stage ejectors)



Energy-saving Model

- Air consumption: 58 L/min (ANR)
- Vacuum suction flow rate: 61 L/min (ANR)
- Vacuum generation time: 0.6 s/cycle
(Vacuum is continuously generated and air is consumed for 6 s (1 cycle))
- Annual operating cycles: 1100000
(450 cycles/h, 10 h/day, 250 days/year)

Air consumption (When placed):

58 L/min (ANR)

638 m³/year (ANR)

CO₂ emissions: **37 kg/year**

511 kg reduction in annual CO₂ emissions

(¥957/year)

(¥13070/year reduction)

**93%
reduction**

Energy-saving Model

Effects of Energy Saving

Existing Model

- Air consumption: 85 L/min (ANR)
- Vacuum suction flow rate: 44 L/min (ANR)
- Vacuum generation time: 6 s/cycle
(Vacuum is continuously generated and air is consumed for 6 s (1 cycle))
- Annual operating cycles: 1100000
(450 cycles/h, 10 h/day, 250 days/year)

Air consumption (When placed):

85 L/min (ANR)


9350 m³/year (ANR)

CO₂ emissions: **548 kg/year**

(¥14025/year)


Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)**91%
reduction***1*1 Based on SMC's measurement conditions
When equipped with a pressure switch for
vacuum with energy saving function (ZL3)Pressure switch for
vacuum with energy
saving functionAir consumption
90% reduction

More efficient ejector

Air consumption

10% reduction
(Compared to ZL212)**Energy saving is possible due to the pressure switch
for vacuum with energy saving function.**Even when the suction signal is ON, the ON/OFF operation of the supply
valve is performed automatically within the set value.**Effects of
Energy
Saving****Energy-saving Model**

- Air consumption: 135 L/min (ANR)
Vacuum suction flow rate: 300 L/min (ANR)
- Vacuum generation time: 1.5 s/cycle
(Air is only consumed for 1.5 s per cycle (15 s) during
workpiece adsorption.)
- Annual operating cycles: 300000
(120 cycles/h, 10 h/day, 250 days/year)

Air consumption (When placed):

3.4 L/cycle (ANR)**1013 m³/year (ANR)** **91% reduction**CO₂ emissions: **60 kg/year****606 kg reduction in annual CO₂ emissions**

(¥1519/year)

(¥15356/year reduction)

Energy-saving Model

Existing Model

- Air consumption: 150 L/min (ANR)
Vacuum suction flow rate: 250 L/min (ANR)
- Vacuum generation time: 15 s/cycle
(Vacuum is continuously generated and air is
consumed for 15 s (1 cycle))
- Annual operating cycles: 300000
(120 cycles/h, 10 h/day, 250 days/year)

Air consumption (When placed):

37.5 L/cycle (ANR)**11250 m³/year (ANR)**CO₂ emissions: **666 kg/year**

(¥16875/year)


Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)**40%
reduction**^{*1}^{*1} Based on SMC's measuring conditions**Operation noise: 65 dB(A)**^{*2}^{*2} Based on SMC's measuring conditions**15 dB (A) reduction compared with
the existing model (VBA series)**

- Exhaust noise: Reduced noise due to exhaust of reused low-pressure air
- Metal noise: Reduced noise due to the adoption of a construction in which the internal switching part doesn't come into contact with any metal parts

- **3 piston construction**
- **The drive chamber on one side can be operated by the exhaust return circuit.**

**Energy-saving Model**

Bore size: $\phi 50$
 Stroke: 200 mm
 Pressure: 0.47 MPa
 Pressure increase: 0.8 MPa

Booster regulator air consumption per cycle^{*3}
4.4 L (ANR)

When it is operated
 900000 times/year

3960 m³/year (ANR)

CO₂ emissions: **232 kg/year**

153 kg reduction in annual CO₂ emissions

(¥5940/year)

(¥3915/year reduction)

**40%
reduction**

Energy-saving Model

**Effects of
Energy
Saving****Existing Model**

Bore size: $\phi 50$
 Stroke: 200 mm
 Pressure: 0.47 MPa
 Pressure increase: 0.8 MPa

Booster regulator air consumption per cycle^{*3}
7.3 L (ANR)

When it is operated
 900000 times/year

6570 m³/year (ANR)

CO₂ emissions: **385 kg/year**

(¥9855/year)

Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)



^{*3} Air consumption = Inlet flow rate – Outlet flow rate

Air consumption “0”

Bleed air “0”

Air consumption is reduced with a new original structure.

With this new original structure, running costs are reduced.




• No fixed throttle in the new design.


* Poor quality of air may cause operation failure. Select a model that is suitable for the desired air cleanliness by referring to “Air Preparation Equipment Model Selection Guide” for air quality.




[Calculation conditions] Electric power cost: 1.55 yen/m³
[Work model] Working hours: 6000 h (250 days/year)
Supply pressure: 1.0 MPa Set pressure: 0.2 MPa

Annual cost reduction effect



Comparison between IR1200-A/IR2200-A and the current IR1000/IR2000



CO₂ emissions
(Air consumption)**25%
reduction****Reduce air consumption just by
mounting to your current
air cylinder!**Mounting and operation are
the same as a regular speed controller.With pressure-
reduction function
AS-R SeriesBy reducing the pressure on the return
stroke to 0.2 MPa, air consumption
can be reduced.When it is not necessary to apply force at the end of
the working stroke, by using a lifter, pusher, etc.**Energy-saving Model**Bore size: $\phi 50$
Stroke: 200 mm
Pressure on the extension side: 0.5 MPa
Pressure on the retraction side: 0.2 MPaAir consumption:
3.5 L (ANR)/cycleWhen it is operated
900000 times/year**3150 m³/year (ANR)** **25% reduction**CO₂ emissions: **185 kg/year****63 kg reduction in annual CO₂ emissions**

(¥4725/year)

(¥1620/year reduction)

Energy-saving Model

**Effects of
Energy
Saving****Existing Model**Bore size: $\phi 50$
Stroke: 200 mm
Pressure: 0.5 MPaAir consumption:
4.7 L (ANR)/cycleWhen it is operated
900000 times/year**4230 m³/year (ANR)**CO₂ emissions: **248 kg/year**

(¥6345/year)

Existing Model


Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)**60%**
reduction

Air consumption when a
workpiece is seated is
now **0 L/min** due to the
new detection principle.



Comparison of detection circuit



Due to the new detection principle, the need for air to be exhausted from the product has been eliminated. This makes the flow consumption 0 L/min when a workpiece is seated.

The result is a great reduction in air consumption compared with the existing model.

* Conditions: Unseated for 5 seconds and seated for 20 seconds (For the G type)

Energy-saving Model

- Air consumption
When placed: 0 L/min (ANR)
When not placed: 10 L/min (ANR)
- Air consumption per cycle:
0.83 L/cycle (ANR)
- Annual operating cycles: 860000

Air consumption (When placed):

0 L/min (ANR)

717 m³/year (ANR)

CO₂ emissions: **42 kg/year**

63 kg reduction in annual CO₂ emissions

(¥1076/year)

(¥1608/year reduction)

60%
reduction

Energy-saving Model

Effects of
Energy
Saving

Existing Model

- Air consumption
When placed: 4 L/min (ANR)
When not placed: 10 L/min (ANR)
- Air consumption per cycle:
208 L/cycle (ANR)
- Annual operating cycles: 860000

Air consumption (When placed):

4 L/min (ANR)

1789 m³/year (ANR)

CO₂ emissions: **105 kg/year**

(¥2684/year)

Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)**50%
reduction**


By using intermittent blow
based on an intermittent
control timer,
air consumption can be
reduced by **50%.**



Energy-saving Circuit


Intermittent Blow Circuit

[Output under timer control]




The duty ratio can be freely adjusted.
By setting the duty ratio to one that has the same blow
effectiveness, air consumption can be reduced.

Example:




Existing Circuit

Continuous Blow Circuit



The duty ratio is equivalent to 100%.



Energy-saving Circuit

Pressure right before: 0.2 MPa
Blow time: 10 s
(Frequency: 12 times/h)
One blow operation:
ON for 1 s, OFF for 1 s;
Repeated a total of 5 times
Working hours: 10 h/day
(250 days/year)
Nozzle diameter: 1 mm

318.2 m³/year (ANR)CO₂ emissions: **19 kg/year****19 kg reduction in annual CO₂ emissions**(**¥477/year**)(**¥477/year reduction**)**50%
reduction**

Energy-saving Circuit

Effects of
Energy
Saving

Existing Circuit


Pressure right before: 0.2 MPa
Blow time: 10 s
(Frequency: 12 times/h)
Working hours:
10 h/day (250 days/year)
Nozzle diameter: 1 mm

636.3 m³/year (ANR)CO₂ emissions: **38 kg/year**(**¥954/year**)

Existing Circuit

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

Peak pressure

15%
increase^{*1}CO₂ emissions
(Air consumption)**35%**
reduction^{*1}**High peak pressure and
low air consumption****Energy-saving Model**

- Optimized internal geometry
- Improved response

Injection quantity per cycle:
57 L/cycle (ANR)Pressure: 0.9 MPa
Energizing time: 100 ms
Annual operating cycles:
240000**13680 m³/year (ANR)** **35% reduction**CO₂ emissions: **802 kg/year****436 kg reduction in annual CO₂ emissions**

(¥20520/year)

(¥11160/year reduction)

Energy-saving Model

**Effects of
Energy
Saving****Existing Model**

- Flow path construction with a large pressure loss
- Long response time

Injection quantity per cycle:
88 L/cycle (ANR)Pressure: 0.9 MPa
Energizing time: 100 ms
Annual operating cycles: 240000**21120 m³/year (ANR)**CO₂ emissions: **1238 kg/year**

(¥31680/year)

Existing Model

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

6

Air/Power
saving equipmentRefrigerated Air Dryer
IDF□FS SeriesDouble Energy-saving
Function SeriesCO₂ emissions
(Power consumption)76%
reduction


The addition of a second re-heater + digital scroll results in high energy savings.

Energy-saving design

Up to a **76%** (1 kW)*¹
reduction

*1 Operating conditions: The IDF125FS in energy-saving operation mode

- Ambient temperature 32°C ● Inlet air temperature 40°C
- Inlet air pressure 0.7 MPa ● Air flow rate = Rated flow x 0.4
- Power supply frequency 60 Hz ● Power supply voltage 200 V ● Set dew point = 30°C



Example 1 year (Spring to Winter) power consumption

Reduced



Compared with the standard model (constant compressor operation), the

Double Energy-saving Function Series

*1 The IDF125FS was used for this example.

per year **can reduce power consumption by 43%!**

Double energy-saving function series (IDF125FS)

Standard model (IDF125F)

* [Trial calculation conditions] Days of operation per year = 240 days (60 days each in spring, summer, autumn, and winter),
Operating hours per day = 12 hours
For details about the dryer operating conditions for each season, refer to the **Web Catalog** (IDF□FS series.).

Corresponding value: Power consumption – CO₂ conversion factor 0.587 kg - CO₂/kWh

7

Energy-saving circuit

Two-pressure drive circuit	p. 49
Energy-saving lifter circuit	p. 50
Optimized cylinder driving system	p. 51
Optimized vacuum adsorption transfer system	p. 52

1

Air consumption
calculation

2

Air blow efficiency

3

Reduce air
leakage

4

Reduce
pressure loss

5

Air pressure
source efficiency

6

Air/Power saving
equipment

7

Energy-saving
circuit

8

Compact and
lightweight products

9


Technical data

CO₂ emissions
(Air consumption)**24%
reduction****Two-pressure Drive Circuit**


By installing a regulator with backflow function in the piping between the rod side cylinder port and the solenoid valve port, it is possible to set the set pressure to low pressure, resulting in a reduction in the amount of compressed air consumed on the return stroke. For the two-pressure drive circuit, sudden extension may occur at the beginning of the working stroke, which may result in a delayed start of the return stroke. In order to resolve this phenomenon, we recommend incorporating an SMC air-saving speed controller.

Low pressure is supplied during the non-working return stroke.

In general usage, a cylinder is used to clamp, press fit, or transfer workpieces during the working stroke, with no work taking place during the return stroke. Therefore, it is sufficient to only supply low pressure during the return stroke. In this way, by using a two-pressure drive circuit as the driving circuit, it is possible to reduce the amount of compressed air used to supply pressure on the return side.

**Energy-saving Circuit**

Cylinder
I.O.: ø100
Rod size: ø30
Stroke: 400 mm
Piping I.O.: 8 mm
Length: 4 m
Rod side supply pressure:
0.5 MPa
Head side supply pressure:
0.2 MPa
Operating frequency:
5 cycles/min
Operating hours:
2000 hours/year



Air consumption
28.8 L (ANR)/cycle


Air consumption
17280 m³/year (ANR)
CO₂ emissions: **1013 kg/year**
323 kg reduction
in annual CO₂ emissions

Cost of compressed air
(¥25920/year)
(¥8280/year reduction)

Energy-saving Circuit

**Effects of
Energy
Saving****Existing Circuit**

Cylinder
I.O.: ø100
Rod size: ø30
Stroke: 400 mm
Piping I.O.: 8 mm
Length: 4 m
Supply pressure: 0.5 MPa
Operating frequency:
5 cycles/min
Operating hours:
2000 hours/year



Air consumption
38 L (ANR)/cycle

Air consumption
22800 m³/year (ANR)
CO₂ emissions: **1336 kg/year**

Cost of compressed air
(¥34200/year)

Existing Circuit



Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)**71%
reduction****Energy-saving Lifter Circuit**

When the cylinder rises, the compressed air in the upper cylinder chamber is exhausted, and the compressed air accumulated in the air tank is supplied to the lower cylinder chamber. Then, when the cylinder lowers, low-pressure compressed air is supplied to the upper cylinder chamber, and the compressed air from the lower cylinder chamber is accumulated in the air tank. The only compressed air consumed during a cycle operation is the low-pressure compressed air supplied to the upper cylinder chamber. Compared with a regular circuit, air consumption can be reduced by 70 to 80%.

By using an air tank, a substantial reduction in air consumption is possible.

An air tank can be used to substantially reduce the amount of air consumed by the lifter circuit, which is used to raise and lower loads.


**Energy-saving Circuit**

Cylinder
I.O.: ø180
Rod size: ø45
Stroke: 500 mm
Tank capacity: 100 L
Head pressure: 0.36 to 0.42 MPa
Rod side supply pressure: 0.2 MPa
Operating frequency: 1 cycle/min
Operating hours: 2000 hours/year

Air consumption

35.8 L (ANR)/cycle

Air consumption

4286 m³/year (ANR)CO₂ emissions: **251 kg/year****614 kg reduction in
annual CO₂ emissions**Cost of compressed air
(¥6444/year)**(¥15696/year reduction)****71%
reduction****Energy-saving Circuit****Effects of
Energy
Saving****Existing Circuit**

Cylinder
I.O.: ø180
Rod size: ø45
Stroke: 500 mm
Supply pressure: 0.5 MPa
Operating frequency: 1 cycle/min
Operating hours: 2000 hours/year

Air consumption

123 L (ANR)/cycle


Air consumption

14760 m³/year (ANR)CO₂ emissions: **865 kg/year**Cost of compressed air
(¥22140/year)**Existing Circuit**

CO₂ emissions
(Air consumption)**42%
reduction**

Our model selection software can be used to find the smallest possible model which meets your requirements, helping you reduce your air consumption.

Example


Stroke: 200 mm
Stroke time: 1 second

Selection of the optimal size via the selection software

- 1 Input operating conditions.
- 2 Conduct a simulation.
- 3 The optimal size model will be displayed.

Operating condition input screen

Results screen



Energy-saving Circuit

Bore size: $\phi 32$ CQ2□32-200
Piping I.O.: $\phi 4$ T0425

Air consumption
1.885 L (ANR)/cycle

When it is operated 900000 times/year

1696.5 m³/year (ANR) **42% reduction**
CO₂ emissions: **100 kg/year**

73 kg reduction
in annual CO₂ emissions

(¥2545/year)

(¥1879/year reduction)

Energy-saving Circuit

Effects of
Energy
Saving

Existing Circuit

Bore size: $\phi 40$ CQ2□40-200
Piping I.O.: $\phi 6$ T0604

Air consumption
3.277 L (ANR)/cycle


When it is operated 900000 times/year

2,949 m³/year (ANR)
CO₂ emissions: **173 kg/year**

(¥4424/year)


Existing Circuit

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

CO₂ emissions
(Air consumption)**59%
reduction**

By selecting optimal size piping, a smaller ejector can also be used, resulting in reduced air consumption.


Optimization by
the selection
software



The larger the piping is, the larger the ejector must be, and the greater the amount of air that is consumed.

Energy-saving Circuit

Ejector: ZK2A07K-06
(Orifice: $\phi 0.7$)
Tubing: TU0425
Pad: ZP2-TB30MTN-H5
Suction time: 0.042 seconds
Safety factor: 4.2
Air consumption: 26.5 L/min (ANR)
Operating frequency: 10 times/h
Operating time: 5 s/time
Operating hours: 2000 hours/year
Number of circuits: 30



CO₂ emissions: **78 kg/year**
113 kg reduction
in annual CO₂ emissions


Cost of compressed air
(¥1988/year)
(¥2887/year reduction)

Energy-saving Circuit

Effects of
Energy
Saving

Existing Circuit

Ejector: ZK2A12K-06
(Orifice: $\phi 1.2$)
Tubing: TU0805
Pad: ZP2-TB30MTN-H5
Suction time: 0.079 seconds
Safety factor: 4.3
Air consumption: 65 L/min (ANR)
Operating frequency: 10 times/h
Operating time: 5 s/time
Operating hours: 2000 hours/year
Number of circuits: 30

CO₂ emissions: **191 kg/year**

Cost of compressed air
(¥4875/year)

Existing Circuit

Corresponding value: Air unit ¥1.5/m³ (ANR), Air – CO₂ conversion factor 0.0586 kg/m³ (ANR)

8

Compact and lightweight products

Plug-in Type	Compact 5-Port Solenoid Valve JSY Series	p. 54
Non Plug-in Type	Compact 5-Port Solenoid Valve JSY Series	p. 55
	Air Cylinder JCM Series	p. 56
	Air Cylinder JMB Series	p. 57
	Air Cylinder CS2 Series	p. 58
	Mini Free Mount Cylinder CUJ Series	p. 59
	Compact Air Cylinder JCQ Series	p. 60
	Floating Joint JT Series	p. 61
	Compact Slide MXH Series	p. 62
	Air Slide Table MXQ Series	p. 63
	Air Slide Table MXJ Series	p. 64
	Compact Guide Cylinder JMGP Series	p. 65
	Micro Clamp Cylinder CKZM16-X2800 (Base Type)- X2900 (Tandem Type)	p. 66
	Rotary Actuator/Vane Type CRB Series	p. 67
	Body Ported Type Vacuum Ejector ZH Series	p. 68
	In-line Type Vacuum Ejector ZU□A Series	p. 69
	Vacuum Pad ZP3 Series	p. 70
	One-touch Fittings KQ2 Series	p. 71
	Speed Controller with One-touch Fitting (Push-lock Type) AS Series	p. 72
	Speed Controller with One-touch Fitting (Push-lock/Compact Type) JAS Series	p. 73
3-Screen Display	High-Precision Digital Pressure Switch ZSE20(F)/ISE20 Series	p. 74
	Digital Flow Switch PF2M/PFMB/PF2MC Series	p. 75

Weight





Max. **59%**
reduction

3700 g → 1500 g

Valve width

Max. **39%**
reduction

24.6 mm → 15 mm





*1 Compared with the existing
VQ4000 series

Weight**Max. 57%^{*1}
reduction**

560 g → 240 g

Valve width**Max. 36%^{*1}
reduction**

10 mm → 6.4 mm

^{*1} Compared with the existing
SY3000 series

Weight

Max. **54%**
reduction0.69 kg → **0.32 kg**

Overall length

Approx. **1/3**154 mm → **57 mm***1 Compared with the existing
CM2B series, ø40, 50 mm stroke


Shortened height

New mounting band for auto switch

Mounting height


Approx. **8 mm** shorter

Overall length shortened



Various cover types available

Direct mounting is possible.



Weight

Max. **36%**
reduction

1.56 kg → **1.00 kg**

Overall length

Max. **11%**
reduction

256 mm → **229 mm**

*1 Compared with the existing
MB series, ø50, 100 mm stroke


Overall length shortened




Intermediary bore sizes

○ Air saving

○ Space saving



Weight

**62%
reduction**21.4 kg → **8.2 kg**Compared with a ø140, 100 mm
stroke CS1 (steel tube) series model**More lightweight due to the aluminum
covers on both ends****Weight reduced by a change in the cover
material**

* Compared at a 100 mm stroke

Bore size [mm]	CS2 (Aluminum tube) [kg]	CS1 (Steel tube) [kg]	Reduction rate [%]
125	7.0	17.9	61
140	8.2	21.4	62
160	11.3	28.8	61

■ Miniature body

Overall length

Max. **20%**^{*1}
reduction29.5 mm → **23.5 mm**

Volume

Max. **45%**^{*1}
reduction382 cm³ → **211 cm³***1 Compared with the CQS series
cylinders, ø20

Dimensions (With Magnet)

[mm]

Bore size	A(a)	B(b)	C(c)
12	17(25)	26.5(25)	19.5(22)
16	21(29)	29.5(29)	21(22)
20	25(36)	36(36)	23.5(29.5)

(): Dimensions of the CQS series cylinders

Overall length

Max. **64%**^{*2}
reduction36 mm → **13 mm**

Volume


Max. **70%**^{*2}
reduction129 cm³ → **38.6 cm³***2 Compared with the CU series
cylinders, ø10

Dimensions (Without Magnet)

[mm]

Bore size	A(a)	B(b)	C(c)
4	10(—)	15(—)	13(—)
6	13(13)	19(22)	13(33)
8	13(—)	21(—)	13(—)
10	13.5(15)	22(24)	13(36)
12	17(—)	26.5(—)	15.5(—)
16	21(20)	29.5(32)	16.5(30)
20	25(26)	36(40)	19.5(36)

(): Dimensions of the CU series cylinders



Weight


Max. **45%**
reduction150 g → **82 g**

Volume


Max. **37%**
reduction76 cm³ → **48 cm³**

*1 Compared with the existing CDQS series, ø25, 10 mm stroke

Overall length shortened

6.5 mmExisting model ø20
(CDQS series)

Width shortened

6 mmExisting model ø20
(CDQS series)

Height shortened

4 mm

JCQ ø20





Weight

Max. **56%**
reduction

50 g → 22 g

Compared with the existing JA20



Weight Comparison

Model	JA Series	JT Series	Reduction rate
JT20	50 g	22 g	56%
JT32	70 g	38 g	46%
JT40	160 g	98 g	39%


Overall Length Comparison

Model	Connection thread	Shortened dimensions	Overall length	Overall length
JT20	M8 x 1.25	12.3 mm	27.2 mm	
JT32	M10 x 1.25	13.0 mm	33.0 mm	
JT40	M14 x 1.5	19 mm	43.0 mm	



More compact and lightweight combination are available by using the JT series with a JCM series cylinder.

Reduction of length when using JT and JCM



Overall Length Comparison

Model	JA + CM2 Series	JT + JCM Series	Reduction rate
JT20	139.5 mm	90.2 mm	35%
JT32	149.0 mm	96.0 mm	36%
JT40	189.0 mm	112.0 mm	41%


Weight Comparison

Model	JA + CM2 Series	JT + JCM Series	Reduction rate
JT20	190 g	102 g	46%
JT32	350 g	188 g	46%
JT40	720 g	378 g	48%


Weight

Max. **19%**
reduction

455 g → 369 g

(Existing MXH series,
ø20-10 mm stroke)Allowable moment
Improved
by up to
240%With new high rigidity
linear guideAllowable moment
improvement illustrated below^{*1}

^{*1} Allowable moment caused by static load
(The above graph is a comparison between the new MXH and the existing MXH6.)



Reduced in height and weight with thinner table


Height

Max. **10%**^{*1}
reduction30 mm → **27 mm**

Weight

Max. **22%**^{*1}
reduction380 g → **298 g**Allowable
kinetic energyMax. **64%**^{*1}
increase0.055 J → **0.09 J**

*1 Compared between the double-ported type and the existing MXQ12-30

Guide Size and Cylinder Bore Size
Combination Chart

Guide size		Max. load mass	Double-ported type MXQ□A		Low thrust with high rigidity type MXQ□B		Single side-ported type MXQ□C		Height interchangeable type MXQ□	
Guide size			Bore size		Bore size		Bore size		Bore size	
Small guide ↑	32 mm	0.6 kg	ø6	<p>■ Height reduced by 10% of the existing model 30 mm → 27 mm</p> <p>■ Weight reduced by 22% 380 g → 298 g For MXQ12A-302N</p> <p>■ A piping port and auto switch mounting groove are provided on both sides.</p> <p>Improved visibility</p> <p>Pilot port For ø16</p> <p>Two auto switch mounting grooves</p> <p>Purpose of usage ① Guide rigidity and a large table surface are necessary but thrust is not needed.</p> <p>Application examples • Horizontal transfer of workpieces, transfer of tools, low thrust clamping</p>	—	ø6	—	Not available Use the MXQ□, height interchangeable type.	ø6	<p>■ Same height as the existing model</p> <p>■ Visibility of auto switches improved</p> <p>■ Interchangeable in mounting with the existing model</p> <p>Standard/Symmetric type (Figure shows standard model)</p>
	32 mm	1 kg	ø8	<p>23 mm</p> <p>Purpose of usage ②</p>	ø6	20 mm	ø8	21 mm	ø8	23 mm
	40 mm	2 kg	ø12	<p>27 mm</p> <p>Purpose of usage ③ A guide with higher rigidity is necessary without changing the thrust from the existing model.</p> <p>Application examples • Transfer of workpieces with increased overhang • High-accuracy and high-thrust clamping</p>	ø8	23 mm	ø12	27 mm	ø12	30 mm
	50 mm	4 kg	ø16	35 mm	ø12	30 mm	ø16	37 mm	ø16	37 mm
	60 mm	6 kg	ø20	43 mm	ø16	37 mm	ø20	46 mm	ø20	46 mm
	70 mm	9 kg	ø25	52 mm	ø20	46 mm	ø25	55 mm	ø25	55 mm
Large guide ↓				<p>When the height needs to be the same as the existing model, choose the MXQ□, height interchangeable type.</p>				Not available Use the MXQ□A, double-ported type.		

Compact

Height: **10 mm**/Width: **20 mm**/Length: **43 mm** (MXJ4)Traveling parallelism: **0.005 mm**Front mounting accuracy*1: **0.01 mm**/Top mounting accuracy*2: **0.03 mm**



Integrated front mounting part and table result in a highly accurate and rigid top and front mounting surface.

ø12, ø16

Auto switch and adjuster
can be mounted on
the same side.Short pitch mounting
is possible.

Auto switch

Adjuster

*1 Right angle degree of the front mounting surface
to the body mounting surface*2 Parallelism of the top mounting surface to the
body mounting surface

Weight**Max. 69%**
reduction0.32 kg → **0.1 kg****Overall length****Max. 31%**
reduction100 mm → **69.5 mm****Height****33%**
reduction48 mm → **32 mm**

*1 Compared with the existing MGP-Z series, ø16, 10 mm stroke *2 Compared with the existing MGP-Z series, ø32, 25 mm stroke

Overall length shortened**Height shortened**Suitable for pushing, lifting, or clamping
in a transport line

Compact

Lightweight

High clamping force

High holding force

Width

20 mmBase type,
Tandem type

Weight

250 g

Base type

Max. clamping force: 200 N


(Tandem type)

* Operating pressure: 0.6 MPa

Max. holding force: 300 N


(Base type, Tandem type)

* When operating pressure of 0.2 to 0.6 MPa is applied



Reduction of *design assembly* labor by unitization

Arm assembly Mounting assembly
added to clamp cylinder



Overall length

Max. **44%**^{*1}
reduction100 mm \Rightarrow **55.6 mm**^{*1} Compared with the existing
CDRB2□WU, Size 20

Weight


Max. **48%**^{*2}
reduction222 g \Rightarrow **115 g**^{*2} Compared with the existing
CDRB2□WU, Size 20,
Rotating angle 90°Features a compact body
with a built-in

angle adjuster unit

and

auto switch unit

(Size: 20, 30, 40)



**Rotation time of
0.5 s/90° is possible.**

(CRB2: 0.3 s/90°)

* Excluding size 40




■ Compact and lightweight

Overall length

Max. **11%**
reduction58.5 mm → **51.8 mm**


Compared with the previous ZH05D□



Port height

Max. **25%**
reduction35.5 mm → **26.4 mm**

Compared with the previous ZH20D□



Weight


Max. **74%**
reduction88.4 g → **23.3 g**

Compared with the previous ZH20D□




4 mounting types

Direct mounting



Standard bracket mounting



L-bracket mounting



DIN rail mounting



Variations

Model	Nozzle nominal size [mm]	Ultimate vacuum pressure*1 [kPa]		Max. suction flow rate [L/min (ANR)]		Air consumption [L/min (ANR)]
		Type S	Type L	Type S	Type L	
ZH05D□A	0.5	-90	-48	6	13	13
ZH07D□A	0.7			12	28	27
ZH10D□A	1.0			26	52	52
ZH13D□A	1.3			40	78	84
ZH15D□A	1.5		-66	58	78	113
ZH18D□A	1.8			76	128	162
ZH20D□A	2.0			90	155	196

*1 Supply pressure: 0.45 MPa

Compact and lightweight

O.D.

 $\varnothing 10.4^{*1}$ mm

 Previous model:
 $\varnothing 12.8$ mm

Weight

 3.9^{*1} g


 Previous model:
 6.5 g

Overall length

 52^{*1} mm


 Previous model:
 59 mm

*1 Compared with the previous ZU05□




Application Examples

For preventing pad adsorption failures from the vacuum source




Numerous pads can be used to adsorb workpieces with holes.

For improving responsiveness by installing on flexible parts



Can be used to open and close plastic bags


 For mounting
on the end of a Z-axis air cylinder

Variations

Model	Nozzle size [mm]	Standard supply pressure [MPa]	Ultimate vacuum pressure [kPa]		Maximum suction flow rate [L/min (ANR)]		Air consumption [L/min (ANR)]	Port size
			Type S	Type L	Type S	Type L		
ZU03□A	0.3	0.35	-85	-40	1.8	3.4	4.2	ø4 One-touch fitting ø5/32"
ZU04□A	0.4		-87		3.2	5.8	7.7	
ZU05□A	0.5	0.45	-90	-48	7	13	14	ø6 One-touch fitting Rc1/8
ZU07□A	0.7				11	16	28	

Overall length shortened


Overall length

Max. **9**^{*1} mm
shorter

12 mm → **3** mm

* Pad unit

*1 For the flat type (Pad diameter: ø2)




Overall length


Max. **11**^{*1} mm
shorter

19.5 mm → **8.5** mm

* With adapter




Space saving ø2 piping reduces working space!




Vertical

- Male thread
- Female thread
- Barb fitting (Applicable tubing: ø2)
- One-touch fitting (Applicable tubing: ø2)



Lateral

- Female thread
- Barb fitting (Applicable tubing: ø2)
- One-touch fitting (Applicable tubing: ø2)




Variations

Form	Pad diameter								
	ø1.5	ø2	ø3.5	ø4	ø6	ø8	ø10	ø13	ø16
Flat type	●	●	●						
Flat type with groove				●	●	●	●	●	●
Bellows type				●	●	●	●	●	●




WeightMax. **57%**^{*1}
reduction12 g → **5.2 g****Height**Max. **24%**^{*1}
reduction25.5 mm → **19.4 mm****Length**Max. **23%**^{*1}
reduction20 mm → **15.5 mm**

*1 Compared with the previous KQ2 series model: Male elbow, applicable tubing O.D. ø6, connection thread R1/8

■ **Compact and lightweight***1 Compared with the previous KQ2 series model:
Male elbow, applicable tubing O.D. ø6, connection thread R1/8■ **Improved tube insertion/removal**

*1 Tube removal strength is ensured to be equivalent to previous model.

◎ **Face seal adopted for threading****Improved installability** (Reduction in amount of tool-tightening required after hand-tightening)◎ **Uniform height when using multiple fittings**

8

Compact and
lightweight
products

Speed Controller with One-touch Fitting (Push-lock Type) *AS Series*

Reduced labor time and weight!

Weight

Reduced by up to
approx. **50%**^{*1}

*1 Compared with the existing
AS22□1F, ø12

Tubing O.D.	Thread	Part no.	Weight
ø6	1/4	AS22□1F-02-06A	18 g
ø12	1/2	AS42□1F-04-12A	56 g

Push-lock type



Existing model




Tubing O.D.	Thread	Part no.	Weight
ø6	1/4	AS22□1F-02-06	32 g
ø12	1/2	AS42□1F-04-12	101 g

Easy
to use

Push-lock type

- Easy to lock



Larger knob

Body size	ØD [mm]
1	9.4
2	12 (Port size: 1/8)
	13 (Port size: 1/4)
3	16.6
4	18.8



Improved tube insertion/removal

Insertion force:


Max. **30% (8 N) reduction**

Removal force:

Max. **20% (5 N) reduction**^{*1}


*1 Tube pulling out strength is ensured to be
equivalent to the existing model.

More space beneath the tube. Easier installation/removal of the tube.



AS22□1F-02-□SA

AS22□1F-02-□



Sealant/Gasket seal	Elbow	Universal	Brass	Stainless steel
M/UNF/R/NPT	●	●	●	●
Face seal	●	●	●	●
R/NPT/G	●	●	●	●
Gasket seal	●	●	●	●
Uni	●	●	●	●

* Only G thread

* Only G thread

8

Compact and
lightweight
products

Speed Controller with One-touch Fitting (Push-lock/Compact Type) *JAS Series*

Height


**9.7^{*1} mm
shorter**

22.4 mm → 12.7 mm


*1 Compared with the existing AS12□1F, M5



**Possible to adjust flow rate
even in a narrow space**




Easily mounted using a hexagon wrench





Minimum operating pressure: 0.05 MPa



Now more compact and lightweight due to the M5 pressure port being located on the inside of the product



*1 When an M5 female thread is used.




Piping: M5 female thread type

	Z/ISE20	Z/ISE30A	Reduction rate
Weight (g)	22	43	49%
Depth (mm)	25	42.5	41%
Height (mm)	30	30	—
Width (mm)	30	30	—

Piping: R1/8 type

	Z/ISE20	Z/ISE30A	Reduction rate
Weight (g)	32	43	26%
Depth (mm)	40.2	42.5	5%
Height (mm)	30	30	—
Width (mm)	30	30	—



Volume

Max. **85%**
reduction^{*1}287.9 cm³ → **42.2 cm³**^{*1} Compared with the existing
PF2A series, 200 L type

Weight


Max. **86%**
reduction^{*2}1100 g → **155 g**^{*2} Compared with the existing
PF2A series, 3000 L type

Compared with the Existing PF2A


	PF2M	PFMB		PF2MC
Series	200 L type	500 L type	2000 L type	2000 L type
Weight	83% reduction 290 g → 48 g	66% reduction 290 g → 100 g	86% reduction^{*1} 1100 g → 155 g	78% reduction^{*1} 1100 g → 240 g
Volume	85% reduction 287.9 cm ³ → 42.2 cm³	67% reduction 287.9 cm ³ → 94.9 cm³	80% reduction^{*1} 809.6 cm ³ → 159.7 cm³	74% reduction^{*1} 809.6 cm ³ → 208.2 cm³

^{*1} Compared with the existing PF2A series, 3000 L type


Applications

Accumulated indication shows the operating flow rate
or residual amount (of N₂, etc.) in a gas cylinder.

Flow control of the air for spray painting

^{*} The product is not designed to be explosion proof.

For suction verification



9 Technical data



Energy-saving mindset.....	p. 77
Changes in upstream conductance pressure loss	p. 78
Flow rate calculation	p. 79
Conductances combined	p. 80
Main piping pressure loss calculation	p. 81
Amount of air consumed by the cylinder and tubing 1	p. 82
Amount of air consumed by the cylinder and tubing 2	p. 83

Energy-saving measures can be divided into two main categories. They are either energy efficient or energy saving.

Easy-to-implement, effective measures with a priority on energy efficiency can help you take your energy savings to the next level!

Factory production examples

A: Fluctuation amount in proportion to production
B: Fixed amount during operation
C: Fixed amount during non-operation



Energy efficient

Energy is only used when and where it is required.
Eliminates wasted energy!



Energy-saving

Only the required amount of energy is used.
Improves energy usage efficiency!


- Consumption in proportion to the min. production ratio
- No air is consumed during non-operation!

Energy-efficient and energy-saving examples

	Energy efficient	Energy-saving
Air pressure source	For the control of multiple units 	For reducing the specific power
Blow system	For intermittent blow 	For adopting smaller nozzles with higher pressure
Piping system	For reducing air leakage to 0 	For the leveling of pressure with loop piping


Changes in upstream conductance pressure loss

Since the amount of pressure loss changes depending on the blow nozzle conductance ratio and the upstream (piping, valves, etc.) conductance ratio, the pressure right before the nozzle will also change.



$$\left. \begin{array}{l} P_s : \text{Supply pressure} \\ P_o : \text{Pressure right before the nozzle} \end{array} \right\} \text{Pressure ratio } \frac{P_o + 0.1}{P_s + 0.1}$$

$$\left. \begin{array}{l} C_s : \text{Upstream conductance} \\ C_n : \text{Nozzle conductance} \end{array} \right\} \text{Conductance ratio } \frac{C_s}{C_n}$$




Conductance ratio	Pressure drop [%]
1	20
2	5
3	2



When selecting the size of upstream piping, we recommend staying within 2 to 3 of the conductance ratio.

Tube conductance example



Nozzle conductance example

Nozzle size [mm]	C_n	Nozzle size [mm]	C_n
1	0.14	3	1.27
1.5	0.32	3.5	1.73
2	0.57	4	2.26
2.5	0.88	6	5.09
		8	9.05

Valve conductance example


Body material	Port size	Orifice diameter mmφ	Model	Flow rate characteristics	
				C	b
Al	1/4 (8A)	10	VXD230	8.5	0.35
	3/8 (10A)			9.2	
	1/2 (15A)			9.2	
Resin	φ10	15	VXD240	5.6	0.33
	φ3/8"			4.8	
	φ12			7.2	
Stainless steel C37	3/8 (10A)	20	VXD250	18.0	0.35
	1/2 (15A)			20.0	
	3/4 (20A)			38.0	0.30

By using the flow rate calculation graph, it is possible to easily calculate the flow rate of a nozzle, tube, or valve.

Formula for flow rate

Choked flow

$$Q = 600 \times C (P_1 + 0.1) \sqrt{\frac{293}{273 + T}}$$




Subsonic flow

$$Q = 600 \times C (P_1 + 0.1) \sqrt{1 - \left[\frac{P_2 + 0.1}{P_1 + 0.1} \right]^2} \sqrt{\frac{293}{273 + T}}$$

When the critical pressure ratio is 0.5

Q : Air flow rate [L/min (ANR)]
 C : Sonic conductance [L/(s·bar)]
 b : Critical pressure ratio [–]
 P_1 : Upstream pressure [MPa]
 P_2 : Downstream pressure [MPa]
 T : Temperature [°C]

Flow rate calculation graph



Calculation example

For nozzles

- ① Go up in a vertical line from the nozzle I.D.
- ② From the point of intersection with the operating pressure (diagonal line), go horizontally to the left to find the flow rate.

For tubes


- ① Find the point of intersection of the tube I.D. (diagonal line) and the piping length, and go up in a vertical line.
- ② From the point of intersection with the operating pressure (diagonal line), go horizontally to the left to find the flow rate.

Calculation method for combining the conductance of each device and finding the equivalent conductance of each device in order to figure out the flow capacity of a pneumatic system

Formula for finding the combined total


Connected in series

$$C_s = \frac{1}{\sqrt[3]{\frac{1}{C_1^3} + \frac{1}{C_2^3} + \dots + \frac{1}{C_n^3}}}$$




Connected in parallel

$$C_s = C_1 + C_2 + \dots + C_n$$



There is also a formula for finding the critical pressure ratio (b), but it's easier to just use the smallest device possible.

Graph for when connected in series



Ex.) When connecting a device (sonic conductance: $C_1 = 0.8$) to another device (sonic conductance: $C_2 = 0.5$), 0.46 is required.

Main piping pressure loss calculation

Pressure loss formula


Pressure loss Δp

$$\Delta p = \frac{2.466 \times 10^3 L}{d^{5.31} (p_1 + 0.1)} Q^2$$

Δp : Pressure loss [MPa] (= $p_1 - p_2$)

Q : Standard volume flow [m³/min (ANR)]


p_1 : Upstream pressure [MPa]
(= Gauge pressure)



d : Pipe bore [mm]

L : Piping length [m]

Pressure loss calculation graph




Calculation example

For 1B (25A), $L = 10$ m, $p_1 = 0.5$ MPa, and $Q = 2$ m³/min (ANR), the pressure loss per 1 m can be found to be 0.0004 [MPa/m] and, therefore, for 10 m, it is $\Delta p = 0.0004 \times 10 = 0.004$ [MPa].

Amount of air consumed by the cylinder and tubing 1

By using the graph, it is possible to easily calculate the amount of air consumed by a cylinder and the tubing in 1 cylinder cycle.

Graph for finding the amount of air consumed by the cylinder in 1 cycle




How to find the amount of air consumed by the cylinder

How much air is consumed in 1 cycle when 10 cylinders (Bore size: 50 mm, Stroke: 600 mm) are operated at a pressure of 0.5 MPa?

- ① Find the point of intersection of the operating pressure (diagonal line) and the stroke length, and go up in a vertical line.
- ② From the point of intersection with the tube I.D. (diagonal line), go horizontally to the left to find the amount of air required for 1 cylinder cycle.
- ③ Furthermore, by multiplying this number by 10, the amount of air required for 1 cycle of 10 cylinders can be found.

Amount of air consumed by the cylinder and tubing 2

Graph for finding the amount of air consumed by the tubing in 1 cylinder cycle



How to find the amount of air consumed by the tubing

How much air is consumed in 1 cycle of a cylinder operating at a pressure of 0.5 MPa when 2 tubes (I.D.: 6 mm, Piping length: 2 m) are used?

- ① Find the point of intersection of the operating pressure (diagonal line) and the piping length, and go up in a vertical line.
- ② From the point of intersection with the tube I.D. (diagonal line), go horizontally to the left to find the amount of air consumed by the tubing in 1 cylinder cycle.

How to find the total amount of air consumed

The amount air consumed by the cylinder and tubing can be found using the formula below.

Total air consumption = (the amount of air consumed by the cylinder in 1 cycle + the amount of air consumed by the piping in 1 cylinder cycle) x the number of operations

Revision History

- * Additional conditions of successful cases have been added, and the units of CO₂ emissions have been changed (page 5).
- * The AXTS series pulse blow valve photos have been modified, and related components have been removed (page 17).
- * The power consumption value has been changed for the low-wattage 3, 4, and 5-port solenoid valves (page 32).
- * The CDQ2A-X3260 end power cylinder has been added (page 37).
- * The L-type has been added to the ZU03/04 (page 69).
- * Discontinued digital flow switches (PFM and PFMC) have been changed to the new types (page 75).

AP

Proposal for Energy Saving in Factories

SMC Corporation

Akihabara UDX 15F,
4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN
Phone: 03-5207-8249 Fax: 03-5298-5362
<https://www.smcworld.com>
© 2022 SMC Corporation All Rights Reserved

Specifications are subject to change without prior notice
and any obligation on the part of the manufacturer.

D-G