
Direct Operated 3 Port Solenoid Valve

VX31/32/33 Series

For Air, Water, Oil, Steam



Solenoid valves for various fluids used in a wide variety of applications



VXK VXD VXZ VXS **VXB** VXE VXP VXR VXH VXF VX3 VXA

VX31/32/33 Series

For Air, Water, Oil, Steam



Single Unit

■ Valve

Normally closed (N.C.) Normally open (N.O.) Common (COM.)

■ Solenoid Coil

Coil: Class B, Class H

■ Rated Voltage

100 VAC, 200 VAC, 110 VAC, 220 VAC, 240 VAC, 230 VAC, 48 VAC, 24 VDC, 12 VDC

■ Material

Body — Brass (C37), Stainless steel Seal — NBR, FKM, EPDM, PTFE, FFKM

■ Electrical Entry

- Grommet
- ConduitDIN terminal
- Conduit terminal



Normally Closed (N.C.) / Normally Open (N.O.) / Common (COM.)

	Model	VX31	VX32	VX33
ä.	1.5 mmø	•	_	_
g	2.2 mmø	•	•	•
Orifice dia.	3 mmø	•	•	•
ŏ	4 mmø	_	•	•
_	ort size	1/8	1/4	1/4
	UIT SIZE	1/4	3/8	3/8

Manifold

■ Valve

Normally closed (N.C.) Normally open (N.O.) Common (COM.)

■ Base

Common SUP/EXH type

■ Solenoid Coil

Coil: Class B, Class H

■ Rated Voltage


100 VAC, 200 VAC, 110 VAC, 220 VAC, 240 VAC, 230 VAC, 48 VAC, 24 VDC, 12 VDC

■ Material

Body — Brass (C37) Base — Aluminum Seal — NBR, FKM, EPDM

■ Electrical Entry

- Grommet
- Conduit
- DIN terminal
- Conduit terminal



Normally Closed (N.C.) / Normally Open (N.O.) / Common (COM.)

	Mod	el	VX31	VX32	VX33		
ä.	1.5	mmø	•	_			
g	2.2 mmø		•	•	•		
Orifice dia.	3	mmø	•	•	•		
ŏ	4 mmø		_	•	•		
(amt H	(adk)	IN port		1/4			
(Common SUP/EXH type) Port size		EXH port OUT port IN port	1/8, 1/4				
		EXH port		1/4			

VX2 VXK

VXD

VXZ

VXS

VXE

VXP

VXR

VXF

VX3 VXA

VX31/32/33 Series

Common Specifications

Standard Specifications

	Valve cons	truction	Direct operated poppet		
	Withstand pressure (MPa)		3.0		
Valve	Body mate	rial	Brass (C37), Stainless steel		
specifications	Seal mater	ial	NBR, FKM, EPDM, PTFE, FFKM		
	Enclosure		Dusttight, Low jetproof (equivalent to IP65)*		
Environment		nt	Location without the presence of corrosive gases, explosive gases, or constant water adhesion		
	Rated voltage	AC (Class B coil, Built-in full-wave rectifier type)	100 VAC, 200 VAC, 110 VAC, 220 VAC, 230 VAC, 240 VAC, 48 VAC		
		AC (Class H coil)			
		DC	24 VDC, 12 VDC		
Coil	Allowable	voltage fluctuation	±10% of rated voltage		
specifications	Allowable leakage	AC (Class B coil, Built-in full-wave rectifier type)	±5% or less of rated voltage		
	voltage	AC (Class H coil)	±20% or less of rated voltage		
	Tomage	DC	±2% or less of rated voltage		
	Coil insula	tion type	Class B, Class H		

^{*} Electrical entry, Grommet with surge voltage suppressor (GS) has a rating of IP40. For enclosure, refer to "Glossary of Terms" on page 403.

Solenoid Coil Specifications

DC Specification

Model	Power consumption (W)	Temperature rise (°C) Note)
VX31	4.5	45
VX32	7	45
VX33	10.5	60

Note) The values are for an ambient temperature of 20°C and at the rated voltage.

AC Specification (Class B coil, Built-in full-wave rectifier type)

Model	Apparent power (VA)*	Temperature rise (°C) Note)
VX31	7	55
VX32	9.5	60
VX33	12	65

^{*} There is no difference in the frequency and the inrush and energized apparent power, since a rectifying circuit is used in the AC (Class B). Note) The values are for an ambient temperature of 20°C and at the rated voltage.

AC Specification (Class H coil)

Model		Apparent p	Temperature rise (°C) Note)	
Model	Frequency (Hz)	Inrush	Energized	remperature rise (C)
VX31	50	33	14	65
VASI	60	28	12	60
VX32	50	65	33	100
V A 3 2	60	55	27	95
VX33	50	94	50	120
V A 3 3	60	79	41	115

Note) The values are for an ambient temperature of 20°C and at the rated voltage.

Contents

For Air /Single Unit ···· P.382	For Vacuum Pad /Single Unit ····· P.394
For Air /Manifold ····· P.384	For Vacuum Pad /Manifold ····· P.396
For Water /Single Unit P.386	Construction ····· P.398
For Oil /Single Unit ····· P.388	Dimensions /Single Unit ····· P.399
For Oil /Manifold ····· P.390	Dimensions /Manifold ····· P.400
For Steam /Single Unit P.392	Replacement Parts P.401


Direct Operated 3 Port Solenoid Valve

VX31/32/33 Series

Applicable Fluid Check List

All Options (Single Unit)

Refer to page 382 and after for specifications and models.



Fluid and application	Option	Seal m	naterial	Body material/	Guide pin	Coil insulation	Note	
Fluid and application	symbol	Main valve poppet	Fixed sealant	Shading coil material Note 6)	material	type Note 4)	Note	
Air	Nil	NBR NBR		Brass (C37)	PPS	В		
All	G	INDIN	NDN	Stainless steel	113	В		
Medium vacuum, Non-leak,	M Note 1, 2)	FKM	FKM	Stainless steel	PPS	В		
Oil-free	V Note 1, 2)	FRIVI	FRIVI	Brass (C37)	FF3	В		
Water	Nil	NBR	NBR	Brass (C37)	PPS	В]	
vvaler	G	INDIN	INDIT	Stainless steel	FF3	В		
Heated water	E	EPDM	EPDM	Brass (C37)/Cu	Stainless steel	Н	_	
Heated water	Р	EPDINI	EPDIVI	Stainless steel/Ag	Stairliess steel			
	Α	FKM	FKM	Brass (C37)	PPS Stainless steel	В		
Oil Note 3)	Н			Stainless steel				
Oll Hote 57	D			Brass (C37)/Cu				
	N			Stainless steel/Ag				
Steam (Max.183°C)	S FFKM		PTFE	Brass (C37)/Cu	Stainless steel	Н	COM. only	
Steam (Wax. 165 C)	Q	FFRIVI	FIFE	Stainless steel/Ag	Stairliess steel		COIVI. OTHY	
Copper-free, Fluorine-free Note 5)	J	EPDM	EPDM	Stainless steel	PPS	В		
Copper-free, Fluorine-free	Р	EPDIN	EPDIVI	Stainless steel/Ag	Stainless steel	Н	_	
	В	EPDM	EPDM	Dross (C07)	PPS			
Others	С	FFKM	PTFE	Brass (C37)	Stainless steel	В	COM. only	
	K Note 1, 2)	FFKIVI	FIFE	Stainless steel	Gianness steel		COM. only, Oil-free	

All Options (Manifold)

Refer to page 384 and after for specifications and models.





Fluid and application	Option	Seal n	naterial	Body material/	Guide pin	Coil insulation	
Fidia and application	symbol	Main valve poppet	Fixed sealant	Shading coil material Note 6)	material	type Note 4)	
Air	Nil	NBR NBR		Brass (C37)	PPS	В	
Medium vacuum, Non-leak, Oil-free	V Note 1, 2)	FKM	FKM	Brass (C37)	PPS	В	
Oil Note 3)	Α	FKM	FKM	Brass (C37)	PPS	В	
Oll Note 3)	D	FKM		Brass (C37)/Cu	Stainless steel	Н	
Oth	В		50014	Brass (C37)	PPS	В	
Others	E	EPDM	EPDM	Brass (C37)/Cu	Stainless steel	Н	

^{*} Aluminum is only available with the material for a manifold base.

Note 1) The leakage amount (10⁻⁶ Pa·m³/s) of "V", "M" options are values when differential pressure is 0.1 MPa. Note 2) "V", "M" and "K" options are for oil-free treatment.

Note 3) The dynamic viscosity of the fluid must not exceed 50 mm²/s.

Note 4) Coil insulation type Class H: AC spec. only, Class B/AC spec.: built-in full-wave rectifier type only

Note 5) The nuts (non-welded parts) are nickel plated on the Brass (C37) material

Note 6) There is no shading coil attached to DC spec. or Class B/AC spec.

VXK

VX2

VXD VXZ

VXS **VXB**

VXE

VXP

VXR VXH

VXF VX3

VXA

For Air /Single Unit

(Non-leak, Medium vacuum)

Model / Valve Specifications

N.C.

N.O.

COM.

Symbol









Note) Symbols for N.C. and N.O. types

The symbols show that the N.C. type: port 3 and N.O. type: port 1 are in a blocked state (T). However, use each port pressure in the state shown below

N.C. type: Pressure at port 1 ≥ Pressure at port 2 ≥ Pressure at port 3

N.O. type: Pressure at port 3 ≥ Pressure at port 2 ≥ Pressure at port 1

Port size Orifice diameter (mmø)	Model	Max. operating pressure differential Note 3) (MPa)		Flow rate characteristics Note 1)			Max. system	Weight		
		N.C.	N.O.	COM.	C[dm3/(s·bar)]	b	Cv	(MPa)	(g)	
1/8	1.5	VX311□-01	1	1	0.7	0.29	0.32	0.08		
(6A)	2.2	VX312□-01	0.7	0.5	0.4	0.60	0.25	0.15	1	
(UA)	3	VX313□-01	0.3	0.3	0.2	0.82	0.20	0.20		380
	1.5	VX311□-02	1	1	0.7	0.29	0.32	0.08	1	
		VX312□-02	0.7	0.5	0.4	0.60	0.25	0.15	1	
	2.2	VX322□-02	1.2	1	0.7	0.64	0.40	0.17	7 [530
1/4		VX332□-02	1.6	1.6	1	0.64	0.40	0.17		730
(8A)		VX313□-02	0.3	0.3	0.2	0.82	0.20	0.20	2.0	380
	3	VX323□-02	0.6	0.5	0.3	1.1	1.1 0.25	0.27		530
		VX333□-02	1	0.9	0.6					730
	4	VX324□-02	0.3	0.25	0.2	4.0	0.20	0.38		530
	4	VX334□-02	0.5	0.4	0.3	1.6				730
		VX322□-03	1.2	1	0.7	0.04	0.40	0.47	1	530
	2.2	VX332□-03	1.6	1.6	1	0.64	0.40	0.17		730
3/8	_	VX323□-03	0.6	0.5	0.3	1.1	0.05	0.07	1	530
(10A) 3	3	VX333□-03	1	0.9	0.6	1.1	0.25	0.27		730
		VX324□-03	0.3	0.25	0.2	1.6	0.00	0.00	1 1	530
	4	VX334□-03	0.5	0.4	0.3	1.6	0.20	0.38		730

Note 1) The flow rate characteristics of this product have variations.

When the highly precise flow control is required according to the system to be used, select an orifice diameter 1.3 times larger than that shown above and install a restrictor on the downstream side of the solenoid valve to make the adjustment.

Note 2) Weight of grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.

Also, add 60 g for VX31□□, 80 g for VX32□□ and VX33□□ respectively for bracket option.

Note 3) Refer to "Glossary of Terms" on page 403, for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

	Fluid tempe	Ambient	
Power source	Solenoid valve	temperature	
	Nil, G	V, M	(°C)
AC	-10 Note) to 60	-10 Note) to 40	-20 to 60
DC	-10 Note) to 60	-10 Note) to 40	-20 to 40

Note) Dew point temperature: -10°C or less

Valve Leakage Rate

Internal Leakage / External Leakage Leakage rate Max. operating Seal material Non-leak, Medium pressure differential vacuum Note) From 0 to less than 1 MPa 1 cm3/min or less 10⁻⁶ Pa⋅m³/sec NBR, FKM 1 MPa or more 2 cm³/min or less or less

Note) The leakage amount (10-8 Pa-m3/sec) for the "V" and "M" option are values when the differential pressure is 0.1 MPa.

For Air / Single Unit

How to Order (Single Unit)






Table (1) Model/Orifice Diameter/Port Size

· abic (rable (1) model/office Blametei/1 off Gize								
	Solenoid valve model			Orifice symbol (Diameter)					
Model	VX31	VX32	VX33	1	2	3	4		
Model	VASI	V A 3 2	VASS	(1.5 mmø)	(2.2 mmø)	(3 mmø)	(4 mmø)		
ъ.	01 (1/8)	_	_	•	•	•	_		
Port symbol	02 (1/4)	_	_	•	•	•	_		
(Port size)	_	02 (1/4)	02 (1/4)	_	•	•	•		
(1 011 0120)		03 (3/8)	03 (3/8)	_	•	•	•		

Table (2) Solenoid Valve Option

. ab.o (2) co.oo.a rairo opiio									
Option symbol	Seal ma Main valve poppet		Body material/ Shading coil material		Coil insulation type	Note Note)			
Nil			Brass (C37)						
G	NBR	NBR	Stainless steel			_			
М			Stainless steel	PPS	В	Non-leak (10 ⁻⁶ Pa·m ³ /sec),			
٧	V FKM	FKM	Brass (C37)			Medium vacuum (0.1 Pa.abs), Oil-free			

Note) The leakage amount (10-6 Pa·m3/sec) for the "V" and "M" option are values when the differential pressure is 0.1 MPa.

Table (3) Rated Voltage - Flectrical Ontion

* Surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

Table (3) Hated Voltage – Electrical Option							
Rated voltage			Class B				
-	taled volla	ige	S	L	Z		
AC/ DC	Voltage symbol	Voltage	With surge voltage suppressor	With light	With light and surge voltage suppressor		
	1	100 V		•			
	2	200 V		•			
	3	110 V		•			
AC	4	220 V	Note)	•	Note)		
	7	240 V		_			
	8	48 V		_			
	J	230 V		_			
DC	5	24 V	•	•	•		
DC	6	12 V	•	_	_		

Note 1) Option S, Z are not available as surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

^{*} Class H coil is not available.

VVX31/32/33 Series

For Air /Manifold

(Non-leak, Medium vacuum)

Solenoid Valve for Manifold / Valve Specifications


N.C. N.O. COM.



Symbol



Symbol



Symbol



Note) Symbols for N.C. and N.O. types

The symbols show that the N.C. type: port 3 and N.O. type: port 1 are in a blocked state (\top) .

However, use each port pressure in the state shown below.

N.C. type: Pressure at port 1 ≥ Pressure at port 2 ≥ Pressure at port 3

N.O. type: Pressure at port 3 ≥ Pressure at port 2 ≥ Pressure at port 1

Orifice diameter	Model	Max. operating	Max. operating pressure differential Note 2) (MPa)		Flow rate characteristics Note 1)			Max. system pressure
(mmø)		N.C.	N.O.	COM.	C[dm3/(s·bar)]	b	Cv	(MPa)
1.5	VX311□-00	1	1	0.7	0.29	0.32	0.08	
	VX312□-00	0.7	0.5	0.4	0.60	0.25	0.15	
2.2	VX322□-00	1.2	1	0.7	0.64	0.40	0.17	1
	VX332□-00	1.6	1.6	1	0.64	0.40	0.17	
	VX313□-00	0.3	0.3	0.2	0.82	0.20	0.20	2.0
3	VX323□-00	0.6	0.5	0.3	4.4	0.25	0.27	1
	VX333□-00	1	0.9	0.6	1.1	0.25	0.27	
4	VX324□-00	0.3	0.25	0.2	1.6	0.20	0.38	7
4	VX334□-00	0.5	0.4	0.3	1.0	0.20	0.36	

Note 1) The flow rate characteristics of this product have variations.

When the highly precise flow control is required according to the system to be used, select an orifice diameter 1.3 times larger than that shown above and install a restrictor on the downstream side of the solenoid valve to make the adjustment.

Note 2) Refer to "Glossary of Terms" on page 403 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

	Fluid tempe	Ambient	
Power source	Solenoid valve option (symbol)		temperature (°C)
	Nil	Nil V	
AC	-10 Note) to 60	-10 Note) to 40	-20 to 60
DC	-10 Note) to 60	-10 Note) to 40	-20 to 40

Note) Dew point temperature: -10°C or less

Valve Leakage Rate

Internal Leakage / External Leakage

	Max. operating	Leakage rate			
Seal material	pressure differential	Air	Non-leak, Medium vacuum Note)		
NBR, FKM	From 0 to less than 1 MPa	1 cm³/min or less	10 ⁻⁶ Pa⋅m³/sec		
NBH, FKM	1 MPa or more	2 cm³/min or less	or less		

Note) The leakage amount (10⁻⁶ Pa·m³/sec) for the "V" option are values when the differential pressure is 0.1 MPa.

How to Order (Solenoid Valve for Manifold)



Electrical entry

VX2

VXK

VXD

VXZ

VXS

VXB

VXE

VXP


VXR


VXH

VXF

VX3

VXA






. Blanking plate part no.

Manifold base

VVX31-4A-For VX31: For VX32/33: VVX32-4A-Seal material Nil NBR

FKM How to Order Manifold Assemblies (Example)

Enter the valve and blanking plate to be mounted under the manifold base part number.



Nil Z Oil-free spec. G -Grommet

Built-in full-wave rectifier type

GS-With grommet surge voltage suppressor

C -Conduit

- DIN terminal

T -With conduit termina TS - With conduit terminal and surge voltage suppressor

TL -With conduit terminal and light TZ - With conduit terminal, surge voltage suppressor and light

(S, L, Z) and rated voltage.

DS -DIN terminal with surge voltage suppressor

DL -DIN terminal with light DZ - DIN terminal with surge voltage suppressor and light

DO - For DIN terminal (without connector, gasket is included.)

* DIN type is available with class B only

Refer to Table (3) for available combinations between each electrical option * Surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

Table (1) Model/Orifice Diameter

mø)
-
,
,

Table (2) Calencid Value Ontion

i abie	Table (2) Solenoid valve Option										
Seal material		Body		Coil							
Option symbol	Main valve poppet	Fixed sealant	material	Guide pin material	insulation type	Note Note)					
Nil	NBR	NBR	Brass			_					
V	FKM	FKM	(C37)	PPS	В	Non-leak (10 ⁻⁶ Pa·m³/ sec), Medium vacuum (0.1 Pa.abs), Oil-free					

* Aluminum is only available as a material for the manifold base

Note) The leakage amount (10-6 Pa-m3/sec) for the "V"option are values when the differential pressure is 0.1 MPa.

Table (3) Rated Voltage - Electrical Option

rable (3) hated voltage – Electrical Option							
	Rated volta		Class B				
'	nateu voita	iye	S	L	Z		
AC/ DC	Voltage symbol	Voltage	With surge voltage suppressor	With light	With light and surge voltage suppressor		
	1	100 V		•			
	2	200 V		•			
	3	110 V		•			
AC	4	220 V	Note)	•	Note)		
	7	240 V		_			
	8	48 V		_			
	J	230 V		_			
DC	5	24 V	•	•	•		
DC	6	12 V	•		_		

* Class H coil is not available.

Note) Option S. Z are not available as surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

For Water /Single Unit

Model / Valve Specifications

N.C.

N.O.

COM.

Symbol



Symbol 2



Note) Symbols for N.C. and N.O. types

The symbols show that the N.C. type: port 3 and N.O. type: port 1 are in a blocked state (\top).

However, use each port pressure in the state shown below

N.C. type: Pressure at port $1 \ge Pressure$ at port $2 \ge Pressure$ at port 3

N.O. type: Pressure at port 3 ≥ Pressure at port 2 ≥ Pressure at port 1

Port size	Orifice rt size diameter	Model	Max. operating	Max. operating pressure differential Note 3) (MPa) Flow rate characteristics Note 1			aracteristics Note 1)	Max. system pressure	Weight
	(mmø)		N.C.	N.O.	COM.	Kv	Cv converted	(MPa)	(g)
1/8	1.5	VX311□-01	1	1	0.7	0.07	0.08		
(6A)	2.2	VX312□-01	0.7	0.5	0.4	0.14	0.16		
(0A)	3	VX313□-01	0.3	0.3	0.2	0.21	0.24		380
	1.5	VX311□-02	1	1	0.7	0.07	0.08	1	
		VX312□-02	0.7	0.5	0.4	0.14	0.16		
	2.2	VX322□-02	1.2	1	0.7	0.16	0.19		530
1/4	VX332□-02	1.6	1.6	1	0.16	0.19	. [730	
(8A)		VX313□-02	0.3	0.3	0.2	0.21	0.24	[380
	3	VX323□-02	0.6	0.5	0.3	0.28 0.33	2.0	530	
		VX333□-02	1	0.9	0.6	0.26	0.33	2.0	730
		VX324□-02	0.3	0.25	0.2	0.43	0.50] F	530
	4	VX334□-02	0.5	0.4	0.3	0.43	0.50		730
	0.0	VX322□-03	1.2	1	0.7	0.16	0.19	Ι Γ	530
	2.2	VX332□-03	1.6	1.6	1	0.16	0.19		730
3/8		VX323□-03	0.6	0.5	0.3	0.00	0.00	1 [530
(10A) 3	3	VX333□-03	1	0.9	0.6	0.28 0.33		730	
	4	VX324□-03	0.3	0.25	0.2	0.40	0.50	1	530
4	4	VX334□-03	0.5	0.4	0.3	0.43 0.50	0.50		730

Note 1) The flow rate characteristics of this product have variations

When the highly precise flow control is required according to the system to be used, select an orifice diameter 1.3 times larger than that shown above and install a restrictor on the downstream side of the solenoid valve to make the adjustment.

Note 2) Weight of grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.

Also, add 60 g for VX31□□, 80 g for VX32□□ and VX33□□ respectively for bracket option.

Note 3) Refer to "Glossary of Terms" on page 403, for details on the max. operating pressure differential and the max. system pressure

Fluid and Ambient Temperature

	Fluid tempe	erature (°C)	Ambient	
Power source	Solenoid valve	temperature		
	Nil, G, H	E, P	(°C)	
AC	1 to 60	1 to 99	-20 to 60	
DC	1 to 40	_	-20 to 40	

Note) With no freezing

Valve Leakage Rate

Internal Leakage / External Leakage

Seal material	Max. operating pressure differential	Leakage rate (Water)
NBR, FKM, EPDM	From 0 to less than 1 MPa 1 MPa or more	0.1 cm³/min or less 0.2 cm³/min or less

How to Order (Single Unit)






Table (1) Model/Orifice Diameter/Port Size

Table (1)	Table (1) Model/Offlice Diameter/Port Size										
Solenoid valve model				Orifice symbol (Diameter)							
Madal	VX31	VX32	VX33	1	2	3	4				
Model	VASI	V A 3 2	V X 3 3	(1.5 mmø)	(2.2 mmø)	(3 mmø)	(4 mmø)				
	01 (1/8)	_	_	•	•	•	_				
Port symbol	02 (1/4)	_	_	•	•	•	_				
(Port size)	_	02 (1/4)	02 (1/4)	_	•	•	•				
, , , , , , ,	_	03 (3/8)	03 (3/8)	_	•	•	•				

Table (2) Solenoid Valve Ontion

Table (2)	able (2) Soleliold valve Option									
Option	Seal m	naterial	Body material/	Guide pin	Coil					
symbol	Main valve	Fixed	Shading coil	material	insulation	Note				
Syllibol	poppet sealant	material	material	type						
Nil	NBR	NBR	Brass (C37)	PPS	В	_				
G	NDH	NDH	Stainless steel	PPS	В					
E	EPDM	EPDM	Brass (C37)/Cu	Stainless	н	Heated water				
P	EPDINI	EPDINI	Stainless steel/Ag	steel	П	nealed water				
Н	FKM	FKM	Stainless steel	PPS	В					

Table	Table (3) Rated Voltage – Electrical Option								
	-4		Class B						
, n	Rated voltage		s	L	Z				
AC/ DC	Voltage symbol	Voltage	With surge voltage suppressor	With light	With light and surge voltage suppressor				
	1	100 V		•					
	2	200 V] [•					
	3	110 V		•					
AC	4	220 V	Note)	•	Note)				
	7	240 V		_					
	8	48 V		_					
	J	230 V		_					
DC	5	24 V	•	•	•				
DC	DC 6		•	_	_				

Note) Option S, Z are not available as surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

В	ated volt	2000	Class H				
n	aleu voil	age	S	L	Z		
AC/ DC	Voltage symbol	Voltage	With surge voltage suppressor	With light	With light and surge voltage suppressor		
	1	100 V	•	•	•		
	2	200 V	•	•	•		
	3	110 V	•	•	•		
AC	4	220 V	•	•	•		
	7	240 V	•	_	_		
	8	48 V	•	_	_		
	J	230 V	•	_	_		
DC	5	24 V	DC specifi	cation is n	ot available.		
ы	6	12 V	DO Specifi	caucii is i	iot available.		

For Oil /Single Unit

Model / Valve Specifications

N.C.

N.O.

сом.

Symbol









Note) Symbols for N.C. and N.O. types

The symbols show that the N.C. type: port 3 and N.O. type: port 1 are in a blocked state (T).

However, use each port pressure in the state shown below

N.C. type: Pressure at port $1 \ge Pressure$ at port $2 \ge Pressure$ at port 3

N.O. type: Pressure at port 3 ≥ Pressure at port 2 ≥ Pressure at port 1

Port size	- diamotoi		Max. operating	Max. operating pressure differential Note 3) (MPa)			racteristics Note 1)	Max. system pressure	Note 2) Weight
	(mmø)		N.C.	N.O.	COM.	Kv	Cv converted	(MPa)	(g)
1/8	1.5	VX311□-01	1	1	0.7	0.07	0.08		
(6A)	2.2	VX312□-01	0.7	0.5	0.4	0.14	0.16		
(OA)	3	VX313□-01	0.3	0.3	0.2	0.21	0.24		380
	1.5	VX311□-02	1	1	0.7	0.07	0.08		
		VX312□-02	0.7	0.5	0.4	0.14	0.16		
	2.2	VX322□-02	1.2	1	0.7	0.16	0.19		530
1/4		VX332□-02	1.6	1.6	1	0.16	0.19		730
(8A)		VX313□-02	0.3	0.3	0.2	0.21	0.24		380
	3	VX323□-02	0.6	0.5	0.3	0.28	0.33	2.0	530
		VX333□-02	1	0.9	0.6	0.26	0.33	2.0	730
	4	VX324□-02	0.3	0.25	0.2	0.43	0.50		530
	4	VX334□-02	0.5	0.4	0.3	0.43	0.50	[730
	2.2	VX322□-03	1.2	1	0.7	0.16	0.19	[530
	2.2	VX332□-03	1.6	1.6	1	0.16	0.19		730
3/8	3	VX323□-03	0.6	0.5	0.3	0.28	0.33		530
(10A)	3	VX333□-03	1	0.9	0.6	0.28	0.33		730
	4	VX324□-03	0.3	0.25	0.2	0.43	0.50		530
	4	VX334□-03	0.5	0.4	0.3	0.43	0.50		730

Note 1) The flow rate characteristics of this product have variations.

When the highly precise flow control is required according to the system to be used, select an orifice diameter 1.3 times larger than that shown above and install a restrictor on the downstream side of the solenoid valve to make the adjustment.

Note 2) Weight of grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.

Also, add 60 g for VX31□□, 80 g for VX32□□ and VX33□□ respectively for bracket option.

Note 3) Refer to "Glossary of Terms" on page 403, for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

	Fluid tempe	Ambient	
Power source	Solenoid valve	temperature	
	A, H	A, H D, N	
AC	-5 Note) to 60	-5 Note) to 120	-20 to 60
DC	-5 Note) to 40	-20 to 40	

Note) Dynamic viscosity: 50 mm²/s or less

Valve Leakage Rate

Internal Leakage / External Leakage

Max. operating pressure differential	Leakage rate (Oil)
From 0 to less than 1 MPa	0.1 cm³/min or less 0.2 cm³/min or less
	pressure differential

For Oil / Single Unit

How to Order (Single Unit)






Table (1) Model/Orifice Diameter/Port Size

Solenoid va	alve model		Orifice symbol (Diameter)						
VV21	WY22	WY22	1	2	3	4			
fodel VX31 VX3	V A 3 2	VASS	(1.5 mmø)	(2.2 mmø)	(3 mmø)	(4 mmø)			
01 (1/8)	_	_	•	•	•	_			
02 (1/4)	_	_	•	•	•	_			
-	02 (1/4)	02 (1/4)	_	•	•	•			
_	03 (3/8)	03 (3/8)	_	•	•	•			
	VX31 01 (1/8) 02 (1/4)	01 (1/8) — 02 (1/4) — — 02 (1/4)	VX31 VX32 VX33 01 (1/8) — — 02 (1/4) — — — 02 (1/4) 02 (1/4)	VX31 VX32 VX33 1 (1.5 mme) 01 (1/8) — — ● 02 (1/4) — — ● — 02 (1/4) 02 (1/4) — —	VX31 VX32 VX33 1 (1.5 mme) (2.2 mme) 2 (2.2 mme) 01 (1/8) — — ● ● 02 (1/4) — — ● ● — 02 (1/4) 02 (1/4) — ●	VX31 VX32 VX33 1 (2.2 mmo) 2 (3 mmo) 01 (1/8) — — — — 02 (1/4) — — — — — 02 (1/4) 02 (1/4) — —			

Table (2) Solenoid Valve Ontion

Table (2)	e (2) Soleriold valve Option										
0-4:	Option Seal material		Body material/	Outdo sin	Coil						
symbol	Main valve poppet	Fixed sealant	Shading coil material	Guide pin material	insulation type						
Α			Brass (C37)	PPS	В						
Н	FKM	FKM	Stainless steel	FFS	В						
D] FKIM	LVM	Brass (C37)/Cu	Stainless	н						
N	1		Stainless steel/An	steel							

Table (3) Pated Voltage

Table	Table (3) Rated Voltage – Electrical Option									
	ated volt		Class B							
l R	ated voit	age	S	L	Z					
AC/ DC	Voltage symbol	Voltage	With surge voltage suppressor	With light	With light and surge voltage suppressor					
	1	100 V		•						
	2	200 V] [•						
	3	110 V		•						
AC	4	220 V	Note)	•	Note)					
	7	240 V		_						
	8	48 V		_						
	J	230 V		_						
DC	5	24 V	•	•	•					
DC	6	12 V	•		_					

Note) Option S, Z are not available as surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

	_4_4		Class H				
, n	ated volt	age	S	L	Z		
AC/ DC	Voltage symbol	Voltage	With surge voltage suppressor	With light	With light and surge voltage suppressor		
	1	100 V	•	•	•		
	2	200 V	•	•	•		
	3	110 V	•	•	•		
AC	4	220 V	•	•	•		
	7	240 V	•	_	_		
	8	48 V	•	_	_		
	J	230 V	•	_			
DC	5	24 V	V DCiftiitibi				
DC	6	12 V	DC specification is not availab				

VVX31/32/33 Series

For Oil /Manifold


Solenoid Valve for Manifold / Valve Specifications

N.C. N.O.







Symbol



Symbol



Symbol



Note) Symbols for N.C. and N.O. types

The symbols show that the N.C. type: port 3 and N.O. type: port 1 are in a blocked state (T).

However, use each port pressure in the state shown below.

N.C. type: Pressure at port $1 \ge Pressure$ at port $2 \ge Pressure$ at port 3

N.O. type: Pressure at port 3 ≥ Pressure at port 2 ≥ Pressure at port 1

Orifice diameter (mmø)	Model	Max. operating	Max. operating pressure differential Note 2) (MPa)			Flow rate characteristics Note 1)		
(1111119)		N.C.	N.O.	COM.	Kv	Cv converted	pressure (MPa)	
1.5	VX311□-00	1	1	0.7	0.07	0.08		
	VX312□-00	0.7	0.5	0.4	0.14	0.16		
2.2	VX322□-00	1.2	1	0.7	0.16	0.19		
	VX332□-00	1.6	1.6	1				
	VX313□-00	0.3	0.3	0.2	0.21	0.24	2.0	
3	VX323□-00	0.6	0.5	0.3	0.28	0.33		
	VX333□-00	1	0.9	0.6	0.28	0.33		
	VX324□-00	0.3	0.25	0.2	0.43	0.50		
4	VX334□-00	0.5	0.4	0.3	0.43	0.50		

Note 1) The flow rate characteristics of this product have variations.

When the highly precise flow control is required according to the system to be used, select an orifice diameter 1.3 times larger than that shown above and install a restrictor on the downstream side of the solenoid valve to make the adjustment.

Note 2) Refer to "Glossary of Terms" on page 403 for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

	Fluid tempe	Ambient		
Power source	Solenoid valve	temperature		
	Α	D	(°C)	
AC	-5 Note) to 60	-5 Note) to 120	-20 to 60	
DC	-5 Note) to 40 —		-20 to 40	

Note) Dynamic viscosity: 50 mm²/s or less


Valve Leakage Rate


Internal Leakage / External Leakage

Seal material	Max. operating pressure differential	Leakage rate (Oil)	
FKM	From 0 to less than 1 MPa	0.1 cm³/min or less	
FRIVI	1 MPa or more	0.2 cm³/min or less	

How to Order (Solenoid Valve for Manifold)







- * Common port sizes are all Rc 1/4.

· · indica	ung numbers	SHOWIT DOIO	w are ror	common po
Type	SUP port	EXH port		
N.C.	1	3		
N.O.	3	1		

. Blanking plate part no.

VVX31-4A-F For VX31: For VX32/33: VVX32-4A-F

VVX311-05-1 1 set

* VX3111A-00-1GR1.. 4 sets


Seal material: FKM

"*" is the symbol for mounting.

Add an "*" in front of the part numbers

How to Order Manifold Assemblies (Example)

Enter the valve and blanking plate to be mounted under the manifold base part number. Example



Enter the product's part number in order, counting the 1st station from the left in the manifold arrangement, when viewing the individual port in

The common port on the right side is plugged.

coil, as a standard Table (1) Model/Orifice/Diameter

Table (1) Wodel/Office/Diameter							
Solenoid	Orifice symbol (Diameter)						
valve	1	2	3	4			
model	(1.5 mmø)	(2.2 mmø)	(3 mmø)	(4 mmø)			
VX31	•	•	•	_			
VX32	_	•	•	•			
VX33	_	•	•	•			

Table (2) Calencid Value Ontion

Table (2) Solehold Valve Option									
Option	Seal m	naterial	Body material/	Guide pin	Coil				
symbol	Main valve poppet	Fixed sealant	Shading coil material	material	insulation type				
A	FKM	FKM	Brass (C37)	PPS	В				
D	LVM	LIVIVI	Brass (C37)/Cu	Stainless steel	н				

^{*} Aluminum is only available as a material for the manifold base.

Table (3) Rated Voltage - Electrical Entry - Electrical Option

	(-,		9-			,		~ p
Rated voltage			Class B			Class H		
n	aleu voil	aye	S	L	Z	S	L	Z
AC/ DC	Voltage symbol	Voltage	With surge voltage suppressor	With light	With light and surge voltage suppressor	With surge voltage suppressor	With light	With light and surge voltage suppressor
	1	100 V		•		•	•	•
	2	200 V		•		•	•	•
	3	110 V		•		•	•	•
AC	4	220 V	Note)	•	— Note)	•	•	•
	7	240 V		_		•	_	_
	8	48 V		_	1	•	_	_
	J	230 V		_		•	_	_
DC	5	24 V	•	•	•	DC spe	ecification	n is not
DC	6	12 V	•	_	_	available.		

Note) Option S, Z are not available as surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

For Steam /Single Unit

Model / Valve Specifications

COM.





Port size	Port size Orifice diameter (mmø)		Max. operating pressure differential Note 3) (MPa)	Flow rate characteristics Note 1)		Max. system pressure	Note 2) Weight
	(IIIIII)		COM.	Kv	Cv converted	· (MPa)	(g)
1/8	1.5	VX3114-01	0.7	0.07	0.08		
(6A)	2.2	VX3124-01	0.4	0.14	0.16		
(OA)	3	VX3134-01	0.2	0.21	0.24		380
	1.5	VX3114-02	0.7	0.07	0.08		
		VX3124-02	0.4	0.14	0.16		
	2.2	VX3224-02	0.7	0.16	0.19	1.0	530
1/4		VX3324-02	1		0.19		730
(8A)	3	VX3134-02	0.2	0.21	0.24		380
		VX3234-02	0.3	0.28	0.33		530
		VX3334-02	0.6		0.33		730
	4	VX3244-02	0.2	0.43	0.50		530
	4	VX3344-02	0.3	0.43	0.50		730
	2.2	VX3224-03	0.7	0.16	0.19		530
	2.2	VX3324-03	1	0.16	0.19		730
3/8	3	VX3234-03	0.3	0.28	0.33		530
(10A)	3	VX3334-03	0.6] 0.26	0.33		730
	4	VX3244-03	0.2	0.43	0.50	1	530
	4	VX3344-03	0.3	0.43	0.50		730

Note 1) The flow rate characteristics of this product have variations.

When the highly precise flow control is required according to the system to be used, select an orifice diameter 1.3 times larger than that shown above and install a restrictor on the downstream side of the solenoid valve to make the adjustment.

Note 2) Weight of grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.

Also, add 60 g for VX31□□, 80 g for VX32□□ and VX33□□ respectively for bracket option.

Note 3) Refer to "Glossary of Terms" on page 403, for details on the max. operating pressure differential and the max. system pressure.

Fluid and Ambient Temperature

Power source	Fluid temperature (°C) Solenoid valve option (Symbol) S, Q	Ambient temperature (°C)
AC	183	-20 to 60

Valve Leakage Rate

Internal Leakage	
Seal material	Leakage rate (Air)
FFKM	150 cm³/min or less
External Leakage	
Seal material	Leakage rate (Air)
PTFE	1 cm³/min or less

How to Order (Single Unit)






Table (1) Model/Orifice Diameter/Port Size

(1) 11111111111111111111111111111111111							
	Solenoid v	alve model		Orifice symbol (Diameter)			
Model	VX31	VX32	VX33	1 (1.5 mmø)	2 (2.2 mmø)	3 (3 mmø)	4 (4 mmø)
ъ.	01 (1/8)	_	_	•	•	•	_
Port symbol	02 (1/4)	_	_	•	•	•	_
(Port size)	_	02 (1/4)	02 (1/4)	_	•	•	•
	_	03 (3/8)	03 (3/8)	_	•	•	•

Table (2) Solenoid Valve Option

Option	Seal m	naterial	Body material/	Guide pin	Coil	
symbol	Main valve poppet	Fixed sealant	Shading coil material	material	insulation type	
S	FFKM	PTFE	Brass (C37)/Cu	Stainless	н	
Q	FEKIVI	FIFE	Stainless steel/Ag	steel	п	

Solenoid coil: AC/Class H only

Table (2) Dated Valtage Electrical Option

rabie	Table (3) Rated Voltage – Electrical Option							
Rated voltage				Class H				
n	aleu voii	aye	S	L	Z			
AC/ DC			With surge voltage suppressor	With light	With light and surge voltage suppressor			
	1	100 V	•	•	•			
	2	200 V	•	•	•			
	3	110 V	•	•	•			
AC	4	220 V	•	•	•			
	7	240 V	•	_	_			
	8	48 V	•	_	_			
	J	230 V	•	_	_			
DC	5	24 V	DC aposifi	antion in n	ot available			
DC	6	12 V	DC specification is not availab					

For Vacuum Pad / Single Unit VXV31/32/33 Series

- Vacuum circuit side is suited for a large orifice. Supply pressure side is suited for high pressure and a vacuum pad.
- Construction and dimensions are the same as the VX3 series.

Model / Valve Specifications



	Orifice of	diameter		Operating pressure*		Flow rate characteristics Note 1)				Note 3) Max.	Note 2)		
Port size	(mı	nø)	Model		(MPa)		Passage: 1⇔2		Pa	Passage: 2⇔3		system	Weight
1 011 3120	Port 1 side	Port 3 side	Wiodei	Port 1 side	Port 3 side	C[dm ³ / (s·bar)]	b	Cv	C[dm ³ / (s·bar)]	b	Cv	pressure (MPa)	(g)
1/8	3	1.5	VXV3130-01	Low vacuum	0 to 0.5	0.82	0.20	0.20	0.29	0.32	0.08		
(6A)	1.5	3	VXV3132-01	0 to 0.5	Low vacuum	0.29	0.32	0.08	0.82	0.20	0.20		380
	3	1.5	VXV3130-02	Low vacuum	0 to 0.5	0.82	0.20	0.20	0.29	0.32	0.08		360
	1.5	3	VXV3132-02	0 to 0.5	Low vacuum	0.29	0.32	0.08	0.82	0.20	0.20		
1/4	4 :	2.2	VXV3240-02	Laurinanium	0 to 0.5	1.6	0.20	0.30	0.38 0.64	0.40	0.17	2.0	530
(8A)	4	2.2	VXV3340-02	Low vacuum	0 to 0.9	1.0	0.20	0.36	0.04	0.40	0.17		730
	2.2	4	VXV3242-02	0 to 0.5	Low vacuum	0.64	0.40	0.17	1.6	0.20	0.38	2.0	530
	2.2	4	VXV3342-02	0 to 0.9	Low vacuum	0.64	0.40	0.17	1.0	0.20	0.36		730
		0.0	VXV3240-03	Low vacuum	0 to 0.5	1.6	0.20	0.38	0.64	0.40	0.17		530
3/8	4	2.2	VXV3340-03	LOW VACUUM	0 to 0.9	1.0	0.20	0.36	0.04	0.40	0.17		730
(10A)	2.2	00 4	VXV3242-03	0 to 0.5	Low vacuum	0.64	0.40	0.17	1.6	0.20	0.38	1 1	530
	2.2	4	VXV3342-03	0 to 0.9	LOW VdCuulli	0.04	0.40	0.17	1.6	0.20	0.36		730

Note 1) The flow rate characteristics of this product have variations.

When the highly precise flow control is required according to the system to be used, select an orifice diameter 1.3 times larger than that shown above and install a restrictor on the downstream side of the solenoid valve to make the adjustment.

Note 2) Weight of grommet type. Add 10 g for conduit, 30 g for DIN terminal, and 60 g for conduit terminal type respectively.

Also, add 60 g for VX31□□, 80 g for VX32□□ and VX33□□ respectively for bracket option.

Note 3) Refer to "Glossary of Terms" on page 403, for details on the max. system pressure

Fluid and Ambient Temperature

Power source	Fluid temperature (°C)	Ambient temperature (°C)
AC	-10 Note) to 60	-20 to 60
DC	-10 Note) to 60	-20 to 40
•		

Note 1) Dew point temperature: -10°C or less

Valve Leakage Rate

Internal Leakage / External Leakage

Seal material	Leakage rate Note)		
Seai materiai	Air		
NBR, FKM	1 cm³/min or less		


Note) Value when air pressure is applied.

^{*} Low vacuum: Up to 1.3 x 10²Pa-abs



How to Order (Single Unit)





* Refer to Table (3) for available combinations between each electrical option (S, L, Z) and rated voltage.

Table (1) Model/Orifice Diameter/Port Size

, ,	Solenoid v	Orifice symbol (Diameter) Note)			
		2	4		
Model	VXV31	VXV32	VXV33	(1.5/3 mmø)	(2.2/4 mmø)
-	01 (1/8)	_	_	•	_
Port symbol	02 (1/4)	_	_	•	
(Port size)	_	02 (1/4)	02 (1/4)	_	•
	_	03 (3/8)	03 (3/8)	_	•

Note) The orifice diameter shown above are for the supply pressure side/ vacuum side port.

Table (2) Solenoid Valve Option

Table (2) Colonica Tarre option									
0-4:	Seal m	aterial		Guide pin	Coil				
Option symbol	Main valve poppet	Fixed sealant	Body material	material	insulation type				
Nil	NBR	NBR	D (007)		В				
Α	FKM	FKM	Brass (C37)	PPS					
G	NBR	NBR	Stainless steel	PPS					
н	FKM	FKM	Stainless steel						

Table (3) Rated Voltage - Electrical Option

Iable	(3) na	teu voi	tage – E	iecuica	Option		
В	ated volt	200	Class B				
п	aleu voil	age	S	L	Z		
AC/ DC	Voltage symbol	Voltage	With surge voltage suppressor	With light	With light and surge voltage suppressor		
	1	100 V		•			
	2	200 V		•			
	3	110 V		•			
AC	4	220 V	Note)	•	Note)		
	7	240 V		_			
	8	48 V		_			
	J	230 V		_			
DC	5	24 V	•	•	•		
DC	6	12 V		_	_		

12 V Note) Option S, Z are not available as surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

^{*} Surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

^{*} Class H coil is not available

For Vacuum Pad / Manifold **VVXV31/32/33** Series


• Construction and dimensions are the same as those of the VVX3 series.


Model / Valve Specifications

N.C. N.O.

Symbol (example)

Symbol (example)





Orifice diameter (mmø) Port 1 side Port 3 side			Operating pressure*		Flow rate characteristics Passage: 1⇔2 Passage: 2⇔3					3	Max.
		Model	Port 1 side	Port 3 side	C[dm ³ / (s·bar)]	b	Cv	C[dm ³ / (s·bar)]	b	Cv	system pressure (MPa)
3	1.5	VXV3131-00	Low vacuum	0 to 0.5	0.82	0.20	0.20	0.29	0.32	0.08	` '
1.5	3	VXV3133-00	0 to 0.5	Low vacuum	0.29	0.32	0.08	0.82	0.20	0.20	
4	2.2	VXV3241-00	Low vacuum	0 to 0.5	1.6	0.20	0.38	0.64	0.40	0.17	2.0
4	2.2	VXV3341-00	LOW Vacuum	0 to 0.9	1.0	0.20	0.36	0.64	0.40	0.17	2.0
2.2		VXV3243-00	0 to 0.5		0.64	0.40	0.17	1.6	0.20	0.38	
2.2	4	VXV3343-00	0 to 0.9	Low vacuum	0.04	0.40	0.17	1.0	0.20	0.36	

Note) Refer to "Glossary of Terms" on page 403 for details on the max. system pressure.

Fluid and Ambient Temperature

Power source	Fluid temperature (°C)	Ambient temperature (°C)
AC	-10 Note) to 60	-20 to 60
DC	-10 Note) to 60	-20 to 40

Note 1) Dew point temperature: -10°C or less

Valve Leakage Rate

Internal Leakage / External Leakage


Seal material	Leakage rate Note)
Seai materiai	Air
NBR, FKM	1 cm³/min or less

Note) Value when air pressure is applied.

^{*} Low vacuum: Up to 1.3 x 102Pa-abs

How to Order (Solenoid Valve for Manifold)





3 110 VAC 50/60 Hz 8 48 VAC 50/60 Hz 220 VAC 50/60 Hz J 230 VAC 50/60 Hz


* Refer to Table (3) shown below for availability Refer to page 401 for ordering coil only.

24 VDC

How to Order Manifold Bases

4


5



• Blanking plate part no.

For VXV31: VVX31-4A-For VXV32/33: VVX32-4A-Seal material Nil

How to Order Manifold Assemblies (Example)



F FKM

NBR

- With conduit termina TS - With conduit terminal and surge voltage suppressor TL - With conduit terminal and light TZ - With conduit terminal, surge voltage suppressor and light

- DIN terminal DS - DIN terminal with surge voltage suppressor DI - DIN terminal with light

DZ - DIN terminal with surge voltage suppressor and light

VXE

VXP

VXR

VXH

VXF

VX3

DO-For DIN terminal (without connector. gasket is included.) DIN type is available with class B

only. * Refer to Table (3) for available combinations between each electrical option

(S, L, Z) and rated voltage. * Surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

Table (1) Model/Orifice Diameter

Table (1)	WOUE!/OTT	ice Diamet				
Solenoid	Orifice symbol	Orifice symbol (Diameter) Note)				
valve	3	4				
model	(1.5/3 mmø)	(2.2/4 mmø)				
VXV31	•	_				
VXV32	_	•				
VXV33	_	•				
	Solenoid valve model VXV31 VXV32	valve model 3 (1.5/3 mmø) VXV31 ● VXV32 —				

Note) The orifice diameter shows the supply pressure side/vacuum side.

Table (2) Solenoid Valve Ontion

(-,		• p	•		
Option	Seal m	aterial		Guide	Coil
symbol	Main valve poppet	Fixed sealant	Body material	pin material	insulation type
Nil	NBR	NBR	Brass (C37)	PPS	В
Α	FKM	FKM	Brass (C37)	PPS	В

^{*} Aluminum is only available as a material for the manifold base.

Table	e (3) Ra	ated Vo	oltage – E	lectrica	I Option		
	ated volt	000	Class B				
n	aleu voii	aye	S	L	Z		
AC/ DC	Voltage symbol	Voltage	With surge voltage suppressor	With light	With surge voltage suppressor		
	1	100 V		•			
	2	200 V		•	Note)		
	3	110 V		•			
AC	4	220 V	Note)	•			
	7	240 V		_			
	8	48 V					
	J	230 V		_			
DC	5	24 V	•	•	•		
DC	6	12 V	•	_	_		


* Class H coil is not available.

Note) Option S, Z are not available as surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

Construction

Single unit

Body material: Brass (C37), Stainless steel



Component Parts

No.	Description	Mat	erial		
140.	Description	Standard	Option		
1	Body	Brass (C37)	Stainless steel		
2	Tube assembly Note)	Stainless steel, Cu	Stainless steel, Ag		
3	Armature assembly	Stainless steel, C36, PTFE (NBR)	Stainless steel, PTFE (FKM, EPDM, FFKM)		
4	Return spring	Stainle	ss steel		
5	Nut	Brass (C37)	Brass (C37)/Ni plated		
6	Solenoid coil	Class B molded	Class H molded		
7	O-ring	(NBR)	(FKM, EPDM, PTFE)		
8	Clip	S	K		
9	Guide pin assembly	PPS, C36 (NBR)	Stainless steel (FKM, EPDM, FFKM)		
10	Support spring	Stainle	ss steel		
11	O-ring	(NBR)	(FKM, EPDM, PTFE)		
12	Plate	Stainle	ss steel		


The materials in parentheses are the seal materials.

Note) Cu and Ag are not applicable to the DC spec and to the AC spec with built-in full-wave rectifier.

Manifold

Base material: Aluminum

Manifold body material: Brass (C37)



Component Parts

	_	Mat	orial				
No.	Description	Standard	Option				
1	Manifold body	Brass	(C37)				
2	Tube assembly Note)	Stainless	steel, Cu				
3	Armature assembly	Stainless steel, C36, PTFE (NBR)	Stainless steel, PTFE (FKM, EPDM)				
4	Return spring	Stainless steel					
5	Nut	Brass (C37)	Brass (C37)/Ni plated				
6	Solenoid coil	Class B molded	Class H molded				
7	O-ring	(NBR)	(FKM, EPDM)				
8	Clip	S	K				
9	Guide pin assembly	PPS, C36 (NBR)	Stainless steel (FKM, EPDM)				
10	Support spring	Stainle	ss steel				
11	O-ring	(NBR)	(FKM, EPDM)				
12	Plate	Stainles	ss steel				
13	Gasket	(NBR)	(FKM, EPDM)				
14	Base	Aluminum					

The materials in parentheses are the seal materials.

Note) Cu is not applicable to the DC spec and to the AC spec with built-in full-wave rectifier.



VX2

VXK

VXD

VXZ

VXS

VXB

VXE VXP

VXR

VXH VXF


VX3

VXA


Dimensions: Single Unit / Body Material: Brass (C37), Stainless Steel

Normally closed (N.C.): VX31□0/VX32□0/VX33□0 Normally open (N.O.) : VX31□2/VX32□2/VX33□2 Common (COM.) : VX31 4/VX32 4/VX33 4


Grommet: G




Conduit: C




DIN terminal: D



Conduit terminal: T





														(mm)
	Model	0.5				E	lectri	cal er	ntry (A	AC/CI	ass B)		
	iviouei	Orifice diameter	Port size	Gror	nmet	Cor	duit	DIN	l term	inal	Co	onduit	termir	nal
N.C	C., N.O., COM.	ulailletei	P	J	K	J	Κ	J	K	M	J	K	М	N
	VX31□□	ø1.5, ø2.2, ø3	1/8	30	46	48.5	44	65.5	40		100.5	44	69.5	91.5
	VX31□□	ø1.5, ø2.2, ø3	1/4	30	46	48.5	41	00.0	42	53.5	100.5	41	09.5	91.5
	VX32□□	ø2.2, ø3, ø4	1/4, 3/8	33	56	51.5	51	68.5	52	56.5	103.5	51	72.5	105
	VX33□□	ø2.2, ø3, ø4	1/4, 3/8	36	64.5	54	59.5	71	60.5	59	106	59.5	75	113

																									(mm)
Model	0.7	D			В								Ele	ctrica	l entr	y (DC	, AC/0	Class	H)			Bro	okot	moun	tina
Wodei	Orifice diameter	Port size	Α	٠		С	D	Е	F	Н	Gron	nmet	Cor	nduit	DIN	l termi	nal	C	onduit	termin	nal	Dia	CKEL	Houri	ung
N.C., N.O., COM.	ulameter	Р		B ₁	B2						J	K	J	K	J	K	M	J	K	M	N	Q	R	S	Т
VX31□□	ø1.5, ø2.2, ø3	1/8	22	36	18	76.5	30	19	19.5	27	19.5	En	40	42.5	E0 E	40	46.5	92	42.5	61	93	17.5	40	50	75.5
VX31□□	ø1.5, ø2.2, ø3	1/4	22	41	20.5	70.5	30	19	19.5	21	19.5	30	40	42.5	30.5	42	40.5	92	42.5	01	93	17.5	40	30	75.5
VX32□□	ø2.2, ø3, ø4	1/4, 3/8	24	42	21	90	35	22	22.5	32	22.5	60	43	52.5	61.5	52	49.5	95	52.5	64	106.5	21	47	57	89
VX33□□	ø2.2, ø3, ø4	1/4, 3/8	24	42	21	98	40	22	25	36	25.5	68.5	46	61	64	60.5	52	98	61	66.5	114.5	21	47	57	97

VVX31/32/33 Series


For Air Oil / Manifold


Dimensions: Manifold / Base Material: Aluminum

Normally closed (N.C.):

Normally open (N.O.) : VVX31/VVX32/VVX33

Common (COM.) :





										(mm)			
Model	Dimen-				n	(station	ations)						
Model	sion	2	3	4	5	6	7	8	9	10			
VVX31	L ₁	96	132	168	204	240	276	312	348	384			
VVASI	L2	84	120	156	192	228	264	300	336	372			
VVX32	L ₁	126	172	218	264	310	356	402	448	494			
VVX33	L2	108	154	200	246	292	338	384	430	476			

																						(mm)
																Electri	cal ent	ry (DC,	AC/CI	ass H)		
Model	Α	В	С	D	E	F	Н	J	K	L	M	N	Q	Grommet	Cor	nduit	DII	N termi	nal	Con	duit terr	ninal
														R	s	Т	Т	U	٧	W	Х	Υ
VVX31	40	20	9	22	6.5	33	24	26	36	6	49	19.5	80.5	19.5	40	45.5	45	58.5	46.5	92	61	97
VVX32	44	22	10	24	8.5	34	25	31	46	9	55	22.5	91	22.5	43	54	53.5	61.5	49.5	95	64	107.5
VVX33	44	22	10	24	8.5	34	25	31	46	9	55	25	99.5	25.5	46	62	61.5	64	52	98	66.5	116


									(mm)
			Elec	trical e	entry (A	C/Clas	is B)		
Model	Grommet	Con	duit	DII	N termi	nal	Con	duit terr	ninal
	R	S	Т	Т	U	٧	W	Х	Υ
VVX31	30	48.5	44	45	65.5	53.5	100.5	69.5	95.5
VVX32	33	51.5	52.5	53.5	68.5	56.5	103.5	72.5	106
VVX33	36	54	60.5	61.5	71	59	106	75	114.5

Direct Operated 3 Port Solenoid Valve VX31/32/33 Series

Replacement Parts

Solenoid coil assembly part no.





light * Refer to Table (1) for available combinations between each electrical option and rated voltage.

voltage suppressor

(without connector)


and light -For DIN terminal

AC/Class H coil

TZ - With conduit


terminal,

surge voltage suppressor and






- -With conduit terminal
- TS With conduit terminal and surge voltage suppressor TL -With conduit terminal and light
- TZ With conduit terminal, surge voltage suppressor and light



AC/Class B coil (Built-in full-wave rectifier type)



Electrical entry

VX2

VXK

VXD

VXZ

VXS

VXB

VXE


VXP

VXH

VXF

VX3

VXA




- * Refer to Table (1) for available combinations between each electrical option and rated voltage.
- * Surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

Table (1) Rated Voltage - Electrical Option

			=100ti.10ti.10ti.								
atad valt	000		Class B		Class H						
aleu voil	aye	S	L	Z	S	L	Z				
Voltage symbol	Voltage	With surge voltage suppressor	With light	With light and surge voltage suppressor	With surge voltage suppressor	With light	With light and surge voltage suppressor				
1	100 V		•		•	•	•				
2	200 V		•		•	•	•				
3	110 V	Note)	•		•	•	•				
4	220 V		•	Note)	•	•	•				
7	240 V		_		•	_	_				
8	48 V		_		•	_	_				
J	230 V		_		•	_	_				
5	24 V	•	•	•	DC spe	ecification	n is not				
DC 6 12 V		•	_	_	available.						
	Voltage symbol 1 2 3 4 7 8 J	Voltage Voltage symbol Voltage 1 100 V 2 200 V 3 110 V 4 220 V 7 240 V 8 48 V J 230 V 5 24 V	Voltage symbol 1 100 V 2 200 V 4 220 V 7 240 V 8 48 V J 230 V 5 24 V •	Class B Clas	Class B Clas	Class B Z S S S S S S S S S	Voltage Voltage Voltage voltage Suppressor With surge Suppressor With With With With With Suppressor With Suppressor With With				

Note) Option S, Z are not available since a surge voltage suppressor is integrated into the AC/Class B coil, as a standard.

* When changing coils, AC/DC are not interchangeable with each other, and Class B and H coils are also not interchangeable with each other.



For Air, Water, Oil, Steam

Replacement Parts


· Name plate part no.

AZ-T-VX Valve model

† Enter by referring to "How to Order".

• Clip part no.

For VX31: VX021N-10 For VX32: VX022N-10 For VX33: VX023N-10



• DIN connector part no.

Without electrical option 3G-GDM2A

With electrical option

GDM2A-



	Electrical option							
S	With surge voltage suppressor							
L	With light							
Z	With light and surge voltage suppressor							
Refer to Table (1) for available combination between each electrical option (S. I. Z) and rate.								

voltage.

Rated voltage

1 100 VAC, 110 VAC 2 200 VAC, 220 VAC, 230 VAC, 240 VAC 5 24 VDC 6 12 VDC 15 48 VAC

• Gasket part no. for DIN connector

VCW20-1-29-1

VX3 Series

Glossary of Terms

Pressure Terminology

1. Maximum operating pressure differential

The maximum pressure differential (the difference between the inlet and outlet pressure) which is allowed for operation. When the outlet pressure is 0 MPa, this becomes the maximum operating pressure.

2. Minimum operating pressure differential

The minimum pressure differential (the difference between the inlet pressure and outlet pressure) required to keep the main valve fully opened.

3. Maximum system pressure

The maximum pressure that can be applied inside the pipelines (line pressure).

(The pressure differential of the solenoid valve portion must be less than the maximum operating pressure differential.)

4. Proof pressure

The pressure in which the valve must be withstood without a drop in performance after holding for one minute under prescribed pressure and returning to the operating pressure range. (value under the prescribed conditions)

Electrical Terminology

1. Apparent power (VA)

Volt-ampere is the product of voltage (V) and current (A). Power consumption (W): For AC, W = V·A·cosθ. For DC, W = V·A. Note) cosθ shows power factor. cosθ = 0.6

2. Surge voltage

A high voltage which is momentarily generated by shutting off the power in the shut-off area.

3. Enclosure

A degree of protection defined in the "JIS C 0920: Waterproof test of electric machinery/appliance and the degree of protection against the intrusion of solid foreign objects".

Verify the degree of protection for each product.



■ First Characteristics:

Degrees of protection against solid foreign objects

	regione of protection against come foreign expects
0	Non-protected
1	Protected against solid foreign objects of 50 mm ø and greater
2	Protected against solid foreign objects of 12 mm ø and greater
3	Protected against solid foreign objects of 2.5 mm ø and greater
4	Protected against solid foreign objects of 1.0 mm ø and greater
5	Dust-protected
6	Dusttight

Second Characteristics: Degrees of protection again

_	regrees or protection against water	
0	Non-protected	_
1	Protected against vertically falling water drops	Dripproof type 1
2	Protected against vertically falling water drops when enclosure tilted up to 15°	Dripproof type 2
3	Protected against rainfall when enclosure tilted up to 60°	Rainproof type
4	Protected against splashing water	Splashproof type
5	Protected against water jets	Low jetproof type
6	Protected against powerful water jets	Strong jetproof type
7	Protected against the effects of temporary immersion in water	Immersible type
8	Protected against the effects of continuous immersion in water	Submersible type

Example) IP65: Dusttight, Low jetproof type

"Low jetproof type" means that no water intrudes inside an equipment that could hinder from operating normally by means of applying water for 3 minutes in the prescribed manner. Take appropriate protection measures, since a device is not usable in an environment where a droplet of water is splashed constantly.

Others

1. Material

NBR: Nitrile rubber FKM: Fluororubber

EPDM: Ethylene propylene rubber

PTFE: Polytetrafluoroethylene resin

FFKM: Perfluoroelastomer

2. Oil-free treatment

The degreasing and washing of wetted parts.

3. Passage symbol

In the symbol (complex) Port 1 (IN) and Port 2 (OUT) are shown in a blocked condition (\pm), but it is not possible to use the valve in cases of reverse pressure, where the Port 2 pressure is higher than the Port 1 pressure.

VX2

VXK

VXD VXZ

VXS

VXB

VXE

VYR

VXH

VXF

VXA



VX3 Series 2/3 Port Solenoid Valves for Fluid Control Specific Product Precautions 1

Be sure to read this before handling the products. For detailed precautions on each series, refer to the main text.

Selection

⚠ Warning


Minimum operating pressure differential (VXED, VXP, VXR)

Select an appropriate valve size while referring to the solenoid valve flow rate characteristics.

⚠ Caution

1. Leakage voltage

When the solenoid valve is operated using the controller, etc., the leakage voltage should be the product allowable leakage voltage or less. Particularly when using a resistor in parallel with a switching element and using a C-R element (surge voltage suppressor) to protect the switching element, take note that leakage current will flow through the resistor, C-R element, etc., creating a possible danger that the valve may not turn off.



AC/Class B built-in full-wave rectifier coil: 10% or less of rated voltage (VX3: 5% or less)

AC/Class B/H coil: 20% or less of rated voltage DC coil: 2% or less of rated voltage

2. Selecting options

The fluid handled will differ depending on the valve options. Select optimal options for the fluid.

3. When the fluid is oil.

Generally, FKM is used as seal material, as it is resistant to oil. The resistance of the seal material may deteriorate depending on the type of oil, manufacturer or additives. Check the resistance before using. The kinematic viscosity must not exceed 50 mm²/s. The special construction of the armature adopted in the built-in full-wave rectifier type gives an improvement in OFF response by providing clearance on the absorbed surface when it is switched ON. Select the DC spec. or AC spec. built-in full-wave rectifier type when the dynamic viscosity is higher than water or when the OFF response is prioritized.

Piping

- If a regulator and valve are connected directly, they may vibrate together and cause chattering. Do not connect directly.
- 2. If the cross-sectional area of piping for the fluid supply side is restricted, operation will become unstable due to inadequate pressure differential during valve operation. Use piping size for the fluid supply side that is suited to the port size.
- 3. The behavior of the diaphragm valve becomes unstable under the conditions that the circuit flow rate is restricted to 40% or less of the maximum flow rate on the solenoid valve flow rate characteristics. This may cause unstable valve activation. So, select a solenoid valve with an appropriate flow rate size while carefully checking the circuit flow rate.

Wiring

⚠ Caution

As a rule, use electrical wire with a cross sectional area of 0.5 to 1.25 mm² for wiring.

Furthermore, do not allow excessive force to be applied to the lines.

- 2. Use electrical circuits which do not generate chattering in their contacts.
- 3. Use voltage which is within ±10% of the rated voltage. In cases with a DC power supply where importance is placed on responsiveness, stay within ±5% of the rated value. The voltage drop is the value in the lead wire section connecting the coil.
- 4. When a surge from the solenoid affects the electrical circuitry, install a surge voltage suppressor, etc., in parallel with the solenoid. Or, adopt an option that comes with the surge voltage protection circuit. (However, a surge voltage occurs even if the surge voltage protection circuit is used.)

Operating Precautions

1. Make sure when using pilot type 2-port solenoid valves that the flow direction is from 1 (IN) to 2 (OUT). The valve is designed based on a flow direction of 1(IN) to 2 (OUT) and harnesses the fluid pressure of port 1 (IN) when the valve opens or closes. If reverse pressure (2 (OUT) to 1 (IN)) is applied, it may lead to a reduced service life or cause damage to parts early on due to chattering or pulses from the main valve (diaphragm, piston, etc.). If there is a possibility that reverse pressure will be applied, take countermeasures by installing the check valve, etc. at the downstream side.

When installing the check valve, allow ample space between the valve and the check valve. If it is placed near the valve, it may cause chattering and pulses in the main valve.



VX3 Series 2/3 Port Solenoid Valves for Fluid Control Specific Product Precautions 2

Be sure to read this before handling the products. For detailed precautions on each series, refer to the main text.

Electrical Connections

⚠ Caution

Grommet Class H coil: AWG18 Insulator O.D. 2.2 mm

Class B coil: AWG20 Insulator O.D. 2.5 mm

Rated voltage	Lead w	ire color	
DC (Class B only)	Black	Red	
100 VAC	Blue	Blue	
200 VAC	Red	Red	2
Other AC	Grav	Grav	


* There is no polarity.

DIN terminal

Internal connections are as shown below. Make connections to the power supply accordingly.

Terminal no.	1	2
DIN terminal	+ (-)	- (+)

* There is no polarity



DIN (EN175301-803) Terminal

This DIN terminal corresponds to the Form A DIN connector with an 18 mm terminal pitch, which complies with EN175301-803B.



Disassembly

- After loosening the binding head screw with flange, then if the housing is pulled in the direction of the arrow, the connector will be removed from the solenoid valve.
- 2. Pull out the binding head screw with flange from the housing.
- There is a cutout on the bottom of the terminal block. Insert a small flat head screwdriver, etc. into this cutout, and remove the terminal block from the housing. (See figure below.)
- 4. Remove the ground nut, and pull out the washer and the rubber seal. Wiring
- 1. Pass the cable through the ground nut, washer and rubber seal in this order, and insert these parts into the housing.
- Loosen the binding head screw of the terminal block, then insert the core wire or the crimped terminal of the lead wire into the terminal, and securely fix it with the binding head screw. The binding head screw of the terminal block is M3.

Note 1) Tighten the screw to a torque of between 0.5 and 0.6 N·m. Note 2) Cable O.D.: $\emptyset 6$ to $\emptyset 12$ mm

Note 3) For an outside cable diameter of ø9 to 12 mm, remove the internal parts of the rubber seal before using.

⚠ Caution

Assembly

1. Pass the cable through the ground nut, washer, rubber seal and the housing in this order, and connect to the terminal block. Then, set the terminal block inside the housing. (Push in the terminal block until it snaps into position.) VX2

VXK

VXD

VXZ

VXS

VXB

VXE

VXP


VXR

VXH

VXF

VXA


- 2. Insert the rubber seal and the washer in this order into the cable entry of the housing, and then tighten the ground nut securely.
- 3. Insert the gasket between the bottom part of the terminal block and the plug attached to the equipment, and then insert the binding head screw with flange from the top of the housing, and tighten it. Note 1) Tighten the screw to a torque of between 0.5 and 0.6 N·m. Note 2) The orientation of the connector can be changed in steps of 90° by changing the method of assembling the housing and the terminal block.



Conduit terminal

Make connections according to the marks shown below.

- Use the tightening torques below for each section.
- . Properly seal the terminal connection (G1/2) with the special wiring conduit, etc.



(Internal connection diagram)

Disassembly

 Loosen the mounting screw, and remove the terminal cover from the conduit terminal.

Wiring

- Insert the cable into the conduit terminal.
- Loosen the screw with UP terminal of the conduit terminal, then insert the core wire or the crimped terminal of the lead wire into the terminal, and securely fix it with the screw with UP terminal. Note 1) Tighten the screw to a torque of between 0.5 and 0.6 N·m.



VX3 Series 2/3 Port Solenoid Valves for Fluid Control **Specific Product Precautions 3**

Be sure to read this before handling the products. For detailed precautions on each series, refer to the main text.

Electrical Connections


Assembly

1. Insert the gasket into the conduit terminal, and then clamp the terminal cover with the mounting screw.

Note 1) Tighten the screw to a torque of between 0.5 and 0.6 N·m. Note 2) When changing the orientation of the conduit terminal, carry out the following procedure.

- 1. Apply a tool (monkey wrench, spanner, etc.) to the width across flats of the conduit terminal, and turn the terminal in the counterclockwise direction.
- 2. Loosen the lock nut.
- 3. Turn the conduit terminal in the clamping direction (clockwise direction) to about 15° ahead of the desired position.
- 4. Turn the lock nut by hand to the coil side until it is lightly tightened.
- 5. Apply a tool to the width across flats of the conduit terminal, and turn it to the desired position (through an angle of about 15°) so as to clamp the conduit terminal.


Note: When changing the orientation by applying additional tightening force to the conduit terminal from the factory-set position, turn no more than one half a turn.



Conduit

When used as an IP65 equivalent, use seal (part no. VCW20-15-6) to install the wiring conduit. Also, use the tightening torque below for the conduit

Class H coil: AWG18 Insulator O.D. 2.2 mm Class B coil: AWG20 Insulator O.D. 2.5 mm



Tightening torque 0.5 to 0.6 N·m)

Rated voltage	Lead wire color	
	1)	2
DC	Black	Red
100 VAC	Blue	Blue
200 VAC	Red	Red
Other AC	Gray	Gray

^{*} There is no polarity for DC.


Description	Part no.	
Seal	VCW20-15-6	

Note) Please order separately.


Electrical Circuits

[DC circuit]


Grommet, Conduit, Conduit terminal, DIN type




Grommet, Conduit terminal, DIN type




Conduit terminal. DIN type



Conduit terminal,



[AC, Class B (Built-in full wave rectifier type) Circuit] * For AC/Class B, the standard product is equipped with surge voltage suppressor.




Conduit terminal. DIN type Varistor Rectifie element SOL

Without electrical option


With light

[AC, Class B/H Circuit]


Grommet, Conduit, Conduit terminal




Grommet, Conduit terminal



Conduit terminal



Conduit terminal



With light/surge voltage suppressor

